

Coupling connectors

Sicma

6 way sealed coupling housings for 2.8 mm terminals

Features

- Double row 5 x 6 mm pitch
- Circumferential interface seal
- Waterproof application with single wire seal
- Corrugated tube locking device
- Plastic locking feature
- Mechanical polarization
- Several colour codings available



Performance characteristics

- Temperature range: from -40°C to +125°C
- Contact retention force: > 120 N
- Contact insertion force: < 15 N
- Connector mating force: < 70 N
- Sealing protection: IP 68

Construction

- Housing material: PBT
- Interface seal: Silicone

Tooling

- Terminal removal tool
 - Female terminal: 210S045
 - Male terminal: 210S047

Connector compatibility

- Usable terminals:
 - Sicma-2 2.8 mm female terminals
 - Sicma-2 2.8 mm male terminals
 - Sicma-3 2.8 mm female terminals
 - Sicma-3 2.8 mm male terminals

Part Numbers	No. of position	Terminal size	Type	Colour
211 PC063S0003	6	2.8 mm	Female housing	Black
211 PC063S1003	6	2.8 mm	Female housing	Brown
211 PC063S8003	6	2.8 mm	Female housing	Grey
211 PL063S0003	6	2.8 mm	Male housing	Black
211 PL063S1003	6	2.8 mm	Male housing	Brown
211 PL063S8003	6	2.8 mm	Male housing	Grey

Coupling connectors

Sicma

6 way sealed coupling housings for 2.8 mm terminals

Dimensional characteristics

Notes:

