


**OMNIMATE Signal - series BL/SL 5.08  
SL 5.08HC/04/180LF 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

**General ordering data**

|              |                                                                                                                                                          |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type         | SL 5.08HC/04/180LF 3.2SN OR BX                                                                                                                           |
| Order No.    | <a href="#">1147950000</a>                                                                                                                               |
| Version      | PCB plug-in connector, male header, Solder flange, Solder connection, 5.08 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Orange, Box |
| GTIN (EAN)   | 4032248931606                                                                                                                                            |
| Qty.         | 100 pc(s).                                                                                                                                               |
| Product data | IEC: 400 V / 24 A<br>UL: 300 V / 18.5 A                                                                                                                  |
| Packaging    | Box                                                                                                                                                      |

**OMNIMATE Signal - series BL/SL 5.08**  
**SL 5.08HC/04/180LF 3.2SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight 2.7 g

**System parameters**

|                                                   |                                     |                                 |                     |
|---------------------------------------------------|-------------------------------------|---------------------------------|---------------------|
| Product family                                    | OMNIMATE Signal - series BL/SL 5.08 | Mounting onto the PCB           | Solder connection   |
| Outgoing elbow                                    | 180°                                | Pitch in mm (P)                 | 5.08 mm             |
| Pitch in inches (P)                               | 0.2 inch                            | No. of poles                    | 4                   |
| Solder pin length (l)                             | 3.2 mm                              | Solder pin length tolerance     | 0 / -0.3 mm         |
| Solder pin dimensions                             | d = 1.2 mm, Octagonal               | Can be coded                    | Yes                 |
| Number of solder pins per pole                    | 1                                   | Solder eyelet hole diameter (D) | 1.3 mm              |
| Solder eyelet hole diameter tolerance (D)+ 0,1 mm |                                     | L1 in mm                        | 15.24 mm            |
| L1 in inches                                      | 0.6 inch                            | Insulation resistance           | ≥ 10 <sup>8</sup> Ω |

**Material data**

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Insulating material                   | PA GF  | Colour                                | Orange |
| Insulating material group             | II     | UL 94 flammability rating             | V-0    |
| CTI                                   | ≥ 550  | Contact material                      | Cu-Leg |
| Contact surface                       | tinned | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 100 °C | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 100 °C | Max. relative humidity during storage | 80 %   |

**Rating data acc. to IEC 60664-1 / IEC 61984**

|                                                                |       |                                                                           |        |
|----------------------------------------------------------------|-------|---------------------------------------------------------------------------|--------|
| Rated current, min. no. of poles (Tu=20°C)                     | 24 A  | Rated current, max. no. of poles (Tu=20°C)                                | 19 A   |
| Rated current, number of poles (Tu=40°C), min                  | 21 A  | Rated current, number of poles (Tu=40°C), max.                            | 16.5 A |
| Rated voltage for surge voltage class / pollution degree III/3 | 250 V | Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV   |
| Rated voltage for surge voltage class / pollution degree III/2 | 320 V | Rated impulse voltage for surge voltage class/ pollution degree III/2     | 4 kV   |
| Rated voltage for surge voltage class / pollution degree II/2  | 400 V | Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV   |

**CSA rating data**

|                             |       |                             |        |
|-----------------------------|-------|-----------------------------|--------|
| Rated voltage (Use group B) | 300 V | Rated current (use group B) | 18.5 A |
| Rated voltage (use group D) | 300 V | Rated current (use group D) | 18.5 A |

**UL 1059 rating data**

|                             |                                                                                     |                             |        |
|-----------------------------|-------------------------------------------------------------------------------------|-----------------------------|--------|
| Institute (cURus)           |  | Certificate No. (cURus)     | E60693 |
| Rated voltage (use group B) | 300 V                                                                               | Rated current (use group B) | 18.5 A |
| Rated voltage (use group D) | 300 V                                                                               | Rated current (use group D) | 10 A   |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC002637    | ETIM 5.0   | EC002637    |
| ETIM 6.0   | EC002637    | eClass 6.2 | 27-26-07-04 |
| eClass 7.1 | 27-44-04-02 |            |             |

Creation date January 27, 2015 9:53:23 AM CET

## OMNIMATE Signal - series BL/SL 5.08 SL 5.08HC/04/180LF 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Notes

#### Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

#### IPC conformity

The products are developed, manufactured and delivered according to the internationally recognised IPC-A-610 standard, category "permissible". More extensive demands on the products can be evaluated on request.

### Approvals

#### Approvals



#### ROHS

Conform

## OMNIMATE Signal - series BL/SL 5.08 SL 5.08HC/04/180LF 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

# Drawings

