

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

39128 Hook-up/Lead - PPO Hook-up Wire 600V, 105°C AWM Style 11028



For more Information
please call

1-800-Belden1



General Description:

28 AWG stranded (7x36) tinned copper conductor, PPO insulation. Rated 105°C, 600V.

Usage (Overall)

Suitable Applications:	Electrical panel builders, Electrical/electronic manufacturers, Appliance manufacturers, Furniture, Computer manufacturers, Automotive companies and their sub-suppliers
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	28	7x36	TC - Tinned Copper

Total Number of Conductors:

1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PPO - Polyphenylene Oxide	0.012

Overall Insulation

Overall Cable

Overall Nominal Diameter:

0.039 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:

-40°C To +105°C Dry

Bulk Cable Weight:

1 lbs/1000 ft.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	600 V, 105°C
UL Type:	AWM 11028
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:

VW-1

Plenum/Non-Plenum

Plenum (Y/N):

No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
59.250

Max. Operating Voltage - UL:

Voltage
600 Vac

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

39128 Hook-up/Lead - PPO Hook-up Wire 600V, 105°C AWM Style 11028

Max. Recommended Current:

Description	Current
Single conductor in free air @ 30C ambient	5 amps

Notes (Overall)

Notes: Halogen-free.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
39128 001100	100 FT	0.200 LB	BROWN	C	#28 STR PPO BRN
39128 0011000	1,000 FT	1.000 LB	BROWN	C	#28 STR PPO BRN
39128 0015000	5,000 FT	5.000 LB	BROWN	C Z	#28 STR PPO BRN
39128 002100	1,000 FT	2.000 LB	RED	C	#28 STR PPO RED
39128 0021000	1,000 FT	1.000 LB	RED	C	#28 STR PPO RED
39128 0025000	5,000 FT	5.000 LB	RED	C Z	#28 STR PPO RED
39128 003100	100 FT	0.200 LB	ORANGE	C	#28 STR PPO ORG
39128 0031000	1,000 FT	1.000 LB	ORANGE	C	#28 STR PPO ORG
39128 0035000	5,000 FT	5.000 LB	ORANGE	C Z	#28 STR PPO ORG
39128 004100	100 FT	0.200 LB	YELLOW	C	#28 STR PPO YEL
39128 0041000	1,000 FT	1.000 LB	YELLOW	C	#28 STR PPO YEL
39128 0045000	5,000 FT	5.000 LB	YELLOW	C Z	#28 STR PPO YEL
39128 005100	100 FT	0.200 LB	GREEN, DARK	C	#28 STR PPO DGRN
39128 0051000	1,000 FT	1.000 LB	GREEN, DARK	C	#28 STR PPO DGRN
39128 0055000	5,000 FT	5.000 LB	GREEN, DARK	C Z	#28 STR PPO DGRN
39128 007100	100 FT	0.200 LB	VIOLET	C	#28 STR PPO VIO
39128 0071000	1,000 FT	1.000 LB	VIOLET	C	#28 STR PPO VIO
39128 0075000	5,000 FT	5.000 LB	VIOLET	C Z	#28 STR PPO VIO
39128 008100	100 FT	0.200 LB	GRAY	C	#28 STR PPO GRY
39128 0081000	1,000 FT	1.000 LB	GRAY	C	#28 STR PPO GRY
39128 0085000	5,000 FT	5.000 LB	GRAY	C Z	#28 STR PPO GRY
39128 009100	100 FT	0.200 LB	WHITE	C	#28 STR PPO WHT
39128 0091000	1,000 FT	1.000 LB	WHITE	C	#28 STR PPO WHT
39128 0095000	5,000 FT	5.000 LB	WHITE	C Z	#29 STR PPO WHT
39128 010100	100 FT	0.200 LB	BLACK	C	#28 STR PPO BLK
39128 0101000	1,000 FT	1.000 LB	BLACK	C	#28 STR PPO BLK
39128 0105000	5,000 FT	5.000 LB	BLACK	C Z	#28 STR PPO BLK
39128 013100	100 FT	0.200 LB	BLUE, DARK	C	#28 STR PPO DBLU
39128 0131000	1,000 FT	1.000 LB	BLUE, DARK	C	#28 STR PPO DBLU
39128 0135000	5,000 FT	5.000 LB	BLUE, DARK	C Z	#28 STR PPO DBLU

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 0 Revision Date: 02-28-2012

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.