






NOTA / NOTE :

- CDC CONNECTIQUE PSA : No 9629966099.
- PSA SPECIFICATION: 14: No 9629966099.
- PLAN D'INTERFACE : TE Connectivity No 1544681 .
: PSA STE No 9638276999
- INTERFACE DRAWING : TE Connectivity No 1544681 .
: PSA STE No 9638276999
- PLAN D'ALVEOLE : TE Connectivity No : 1544995
: PSA STE No 9641756399
- CAVITY DRAWING : TE Connectivity No : 1544995
: PSA STE No 9641756399
- CAHIER DE PRECONISATIONS : TE Connectivity No 411-15697 .
: PSA STE No 9641781799
- UTILIZATIONS FILE : TE Connectivity No 411-15697
: PSA STE No 9641781799
- MSP : COTES SUIVIES EN MSP 1 SPC DIMENSIONS .




COMPOSANTS COMPONENTS	REFERENCES PART NUMBERS	MATIERE MATERIAL	COULEUR COLOR
Langouette 1 Tob 8mm NG1 Section 3 à 6 mm2 Wire section 3 to 6 mm2	P790861 (2) 1544332-1 (3)	Laiton pré-étamé Pre-lined brass	1
Langouette 1 Tob 8mm NG1 Section 7 à 10 mm2 Wire section 7 to 10 mm2	P790862 (2) 1544333-1 (3)	Laiton pré-étamé Pre-lined brass	1
Joint unifié à sertir Single wire seal Section 3 à 6 mm2 Wire section 3 to 6 mm2	P8010489526 (2) 1544316-1 (3)	Silicone 50sh A autolubrifié Silicone 50sh A self-lubricated	VERT Green
Joint unifié à sertir Single wire seal Section 7 à 10 mm2 Wire section 7 to 10 mm2	P8010589526 (2) 1544316-2 (3)	Silicone 50sh A autolubrifié Silicone 50sh A self-lubricated	ORANGE Orange
Bouchon Bundle	P8010689526 (2) 1544316-3 (3)	Silicone 50sh A non-lubrifié Silicone 50sh A no-lubricated	BLANC White

B	I	GRILLE DE DETECTION (DV) <i>Detection Grid (DV)</i>	PBT GF-10	JAUNE <i>Yellow</i>
A	I	PORTE-LANGUETTE <i>Tab Housing</i>	PBT GF-10	VOIR TABLEAU <i>See table</i>
Rep	Qté	DÉSIGNATION <i>Description</i>	MATIERE <i>Material</i>	COULEUR <i>Color</i>



(2) : REF / PN PRONER COMATEL
(3) : REF / PN TE CONNECTIVITY

CARACTERISTIQUES MECANQUES CDC PSA PSA MECHANICAL SPECIFICATIONS	VALEURS RESULTS
EFFORT D'INSERTION LANGUETTE / ALVEOLE (AVEC JOINT) : F < 35N TAB / CAVITY MATING FORCE (WITH SEAL) : F < 35N	27 N MAXI 27 N MAXI
EFFORT DE FERMETURE DU DV : 20N<F<40N SECONDARY LOCK CLOSING FORCE : 20N<F<40N	39 N MAXI 39 N MAXI
EFFORT D'ACCOUPLEMENT PC/PL : F < 80N REC HOUSING / TAB HOUSING CONNECTION FORCE : F < 80N	73 N MAXI 73 N MAXI

DIMENSIONS :  mm		TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS DECIMALS P L C / DEC ± 0.2 P L C / DEC ± 0.2 P L C / DEC ± 0.2 P L C / DEC ± 0.2 P L C / DEC ± 0.2 P L C / DEC ± 0.2		OW/VERSIE 29JUN2005 E CHARLES 29JUN2005 CH/VERTEIC 29JUN2005 CORONELL DAHER 29jun2005		 TE Connectivity	
		ANGLES : ° ± 3°		NAME PORTE-LANGUETTES 2V 8mm NG1 ETANCHE 2 WAY SEALED 8mm NG1 TAB HOUSING		PRODUCTIONS SPEC. PROJECT 108-15346	
MATERIAL : MATIERE : TABLE		FINITION : REVISION : MASSE : APPROX. 4 gr		APPLICATION SPEC. SPEC. APPLICATION 411-15697		SIZE FORM : CASE CODE : Dwg No : A 00779 G = 54334	
		CUSTOMER DRAWING : /PLAN CLIENT/POUR REFERENCE		SCALE : 1/1000 SHEET TOTAL : 1 OF : 1 REV : D1			