







SECTION A-A

mat'l. code		surface	tolerance	projection	product family
ISDI302		ISDI302	ISDI302	ISDI302	MOD JACK
l	tr	ec	n	dr	date
M	T00202	MM	07/04/00	angle	0°
N	N04-0102	YS	11/23/04	angle	0°
P	N06-0039	DT	3/10/06	0°±2'	0°
R	N08-0097	SI	MM	09/25/08	chr
S	ELX-N-01080	SI	MM	3/14/12	en
T	ELX-N-15908	Henry	09/23/13	chr	
sheet revision		T		appd	JENN TSAO
index	sheet	1	2		


8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG
P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY
awg no	awg no	awg no	awg no	awg no	awg no
90598	90598	90598	90598	90598	90598
size	size	size	size	size	size
A4	A4	A4	A4	A4	A4
type	type	type	type	type	type
Product	Product	Product	Product	Product	Product
Customer	Customer	Customer	Customer	Customer	Customer
Drawing	Drawing	Drawing	Drawing	Drawing	Drawing

PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	MOUNTING EARS
90598-001 -001LF	ALL	5u" Au + high performance lubricant	Y
-002 -002LF	2,3,4,5,6,7	5u" Au + high performance lubricant	Y
-003 -003LF	ALL	5u" Au + high performance lubricant	Y
-004 -004LF	ALL	50u" / 1.27u GXT	Y
-005 -005LF	1,2,7,8	5u" Au + high performance lubricant	Y
-006 -006LF	ALL	5u" Au + high performance lubricant	N
-007 -007LF	ALL	50u" / 1.27u GXT	N
-008 -008LF	ALL	5u" Au + high performance lubricant	N
-009 -009LF	2-7	5u" Au + high performance lubricant	N
-010 -010LF	2-7	5u" Au + high performance lubricant	N
-011 -011LF	3,4,5,6	50u" / 1.27u GXT	N
-012 -012LF	ALL	15u" / 0.37u GXT	N
-013 -013LF	ALL	6u" / 0.15u GXT	Y
-014 -014LF	ALL	15u" / 0.37u GXT	Y
-015 -015LF	ALL	30u" / 0.76u GXT	Y


LEAD FREE PRODUCT NO.

NOTES :

- 1 P/N/O WITH DASH 0XX –NOTMAL WAVE SOLDERING APPLICATION.
- 2 P/N/O WITH DASH 1XX –1R REFLOW APPLICATION.
- 3 PACKAGING SPEC. BUS-14-164.
- 4 SCRATCH MARKS ACCEPTABLE ON THESE SURFACES.
- 5 JACK IS FOR 1,57/062 THICK PCB.
- 6 SHOULD THE JACK NEED TO BE DISMOUNTED FROM THE PCB, PLS REMOVE JACK AS PER RECOMMENDED METHOD HEREIN. (DETAIL A) NIPPING THE LEGS OF THE PEG TOGETHER IS DISALLOWED, OTHERWISE LEG BREAKAGE MAY OCCUR.
- 7 THESE DIMENSIONS ARE TAKEN FROM THE TOP OF THE PEG.
- 8 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 10 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 11 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD
- 12 IF L/F P/N PACKAGING MEETS GS-14-920 SPECIFICATION EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOMER.



DIRECTION OF DISMOUNT



JACK DISMOUNT METHOD

DETAIL A

NOTE 5

mat'l. code		surface		tolerance		projection		product family	
ISO1302 ✓		ISO1302 ✓		ISO1302 ✓		ISO1302 ✓		MOD JACK	
date		date		date		date		date	
M T0202	YW	07/04/00	07/04/00	07/04/00	07/04/00	07/04/00	07/04/00	07/04/00	07/04/00
N N04-0102	MS	11/23/04	11/23/04	11/23/04	11/23/04	11/23/04	11/23/04	11/23/04	11/23/04
P N06-0039	DT	3/10/06	0' ±2'	0' ±2'	0' ±2'	0' ±2'	0' ±2'	0' ±2'	0' ±2'
R N08-0097	SH	09/25/08	dr	C L FENG	01/08/97	01/08/97	01/08/97	01/08/97	01/08/97
S ELX-W-01090	SH	3/14/12	eng	TONY CHIEN	01/08/97	01/08/97	01/08/97	01/08/97	01/08/97
T ELX-W-15900	Henry	09/23/13	chr	TONY CHIEN	01/08/97	01/08/97	01/08/97	01/08/97	01/08/97
sheet	revision			appd JENN TSAO		01/08/97			
index	sheet								