

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH - BASIC**

CATALOG LISTING

YZ-2RW8435114-D5-S**YZ-2RW8435114-D5-S**

PAGE 1 OF 1

MDRAWING
NUMBER**6**

ISSUE

RELEASE NO.

PR-8793

CHECK

REVISIONS

A	CO	52433
14	WJM	DEC 82
B	CO	53238
21	WJM	JUN 83
C	CO	77590
10	SAD	JUN 94
D	CO	93346
17	DLT	AUG 98
E	CO	94212-K
5	DLT	NOV 99

CHECK

16 MAY 80

DWJ

CHECK


15 MAY 80

FORMTEK

FO-52848-A

DRAWN


WJM

**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - PLASTIC PARTS ARE MADE OF MINERAL FILLED PHENOLICS
- 3 - LEVER IS NOT NECESSARILY SELF RETURNING WHEN SWITCH IS IN THE UPRIGHT POSITION

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**OPERATING FORCE --- 5 GRAM MAX
(MEASURED WITH
SWITCH ON SIDE)**ELECTRICAL DATA**CONTACT ARRANGEMENT
S P N OUL LISTED - FILE E12252
CODE L9 10A-125, 250 OR 480 VAC
1/2A-125 VDC; 1/4A-250 VDC

L288

**SCALE FULL**

DO NOT SCALE PRINT

TOLERANCESAPPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/.04	
ONE PLACE	X,X	0.47/.016	X,X 0.81/.03
TWO PLACES	X,XX	0.15/.006	X,XX 0.38/.015
THREE PLACES	X,XXX		X,XXX 0.13/.005
ANGLES			

SI METRIC

DESIGN UNITS



US CUSTOMARY



WEIGHT .060 LB