


Restricted to: General Release


USED ON

1907124-1
THIS DRAWING IS A CONTROLLED DOCUMENT



Left Side

Connector(s): MT-RJ (No Pins)
Mode: MM
Housing Color: Black
Geom. Spec: 115-1215



Fiber Path

Fiber A - ——— - B
Fiber B - ——— - A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).

Right Side

Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Red
Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED AND MAY NOT BE DISCLOSED TO ANY OTHER PARTY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev. D

	A	Rev Per EC#	RELEASE	9/11/2006	-	DF			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	±
		1 PLC	±
		2 PLC	±
		3 PLC	±
		4 PLC	±
Customer Print			

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Dave Fennell				
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE NTS	SIZE A2	DRAWING NO C- 1907124	SHEET 1 of 4	REV A

8

7

6

5

4

3

2

1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS TO BE USED ONLY FOR THE PURPOSES AND IN THE MANNER SPECIFIED HEREIN. IT IS NOT TO BE REPRODUCED, COPIED, OR OTHERWISE TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex Secure, Red	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907124-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-1907124-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-1907124-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-1907124-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-1907124-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-1907124-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-1907124-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-1907124-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-1907124-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-1907124-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-1907124-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-1907124-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-1907124-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-1907124-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-1907124-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-1907124-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-1907124-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-1907124-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-1907124-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-1907124-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-1907124-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-1907124-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-1907124-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-1907124-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-1907124-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-1907124-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-1907124-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-1907124-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-1907124-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-1907124-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-1907124-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-1907124-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-1907124-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-1907124-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-1907124-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-1907124-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-1907124-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-1907124-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-1907124-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-1907124-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
4-1907124-1	40.590 - 41.410	133.16 - 135.85	0.56	20	0.56	-
4-1907124-2	41.580 - 42.420	136.41 - 139.17	0.56	20	0.56	-

Qty	U of M	Description	Item No.
1	piece	HOUSING, CONN, MT-RJ,BLACK	1
1	piece	DUST COVER, MT-RJ	2
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	PIN KEEPER, 3.8MM	4
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	CRIMP EYELET, MT-RJ	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	LC Duplex clip, black	8
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	9
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	10
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	Eyelet/Shrink tube assembly - White	13
2	piece	Trace Label	14

A	Rev Per EC#	RELEASE	9/11/2006	-	DF		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS:
meters

CUSTOMER PRINT

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ± .

1 P.L.C. ± .

2 P.L.C. ± .

3 P.L.C. ± .

4 P.L.C. ± .

DIN	Cable Assy Configurator		MATERIAL	HEAT TREAT
CHK	Dave Fennell		-	-
APVD	Dave Fennell		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 1907124	2 of 4	A

8 7 6 5 4 3 2 1

THIS DRAWING IS A CONTROLLED DOCUMENT.
DWG NO

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex Secure, Red	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1907124-3	42.570 - 43.430	139.66 - 142.48	0.56	20	0.56	-
4-1907124-4	43.560 - 44.440	142.91 - 145.80	0.57	20	0.57	-
4-1907124-5	44.550 - 45.450	146.16 - 149.11	0.57	20	0.57	-
4-1907124-6	45.540 - 46.460	149.40 - 152.42	0.57	20	0.57	-
4-1907124-7	46.530 - 47.470	152.65 - 155.74	0.57	20	0.57	-
4-1907124-8	47.520 - 48.480	155.90 - 159.05	0.57	20	0.57	-
4-1907124-9	48.510 - 49.490	159.15 - 162.36	0.57	20	0.57	-
5-1907124-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-
5-1907124-1	50.490 - 51.510	165.64 - 168.99	0.58	20	0.58	-
5-1907124-2	51.480 - 52.520	168.89 - 172.30	0.58	20	0.58	-
5-1907124-3	52.470 - 53.530	172.14 - 175.62	0.58	20	0.58	-
5-1907124-4	53.460 - 54.540	175.39 - 178.93	0.58	20	0.58	-
5-1907124-5	54.450 - 55.550	178.64 - 182.25	0.58	20	0.58	-
5-1907124-6	55.440 - 56.560	181.88 - 185.56	0.58	20	0.58	-
5-1907124-7	56.430 - 57.570	185.13 - 188.87	0.59	20	0.59	-
5-1907124-8	57.420 - 58.580	188.38 - 192.19	0.59	20	0.59	-
5-1907124-9	58.410 - 59.590	191.63 - 195.50	0.59	20	0.59	-
6-1907124-0	59.400 - 60.600	194.88 - 198.81	0.59	20	0.59	-
6-1907124-1	60.390 - 61.610	198.12 - 202.13	0.59	20	0.59	-
6-1907124-2	61.380 - 62.620	201.37 - 205.44	0.59	20	0.59	-
6-1907124-3	62.370 - 63.630	204.62 - 208.75	0.59	20	0.59	-
6-1907124-4	63.360 - 64.640	207.87 - 212.07	0.6	20	0.6	-
6-1907124-5	64.350 - 65.650	211.12 - 215.38	0.6	20	0.6	-
6-1907124-6	65.340 - 66.660	214.37 - 218.70	0.6	20	0.6	-
6-1907124-7	66.330 - 67.670	217.61 - 222.01	0.6	20	0.6	-
6-1907124-8	67.320 - 68.680	220.86 - 225.32	0.6	20	0.6	-
6-1907124-9	68.310 - 69.690	224.11 - 228.64	0.6	20	0.6	-
7-1907124-0	69.300 - 70.700	227.36 - 231.95	0.61	20	0.61	-
7-1907124-1	70.290 - 71.710	230.61 - 235.26	0.61	20	0.61	-
7-1907124-2	71.280 - 72.720	233.85 - 238.58	0.61	20	0.61	-
7-1907124-3	72.270 - 73.730	237.10 - 241.89	0.61	20	0.61	-
7-1907124-4	73.260 - 74.740	240.35 - 245.20	0.61	20	0.61	-
7-1907124-5	74.250 - 75.750	243.60 - 248.52	0.61	20	0.61	-
7-1907124-6	75.240 - 76.760	246.85 - 251.83	0.61	20	0.61	-
7-1907124-7	76.230 - 77.770	250.09 - 255.15	0.62	20	0.62	-
7-1907124-8	77.220 - 78.780	253.34 - 258.46	0.62	20	0.62	-
7-1907124-9	78.210 - 79.790	256.59 - 261.77	0.62	20	0.62	-
8-1907124-0	79.200 - 80.800	259.84 - 265.09	0.62	20	0.62	-

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS TO BE KEPT CONFIDENTIAL AND NOT DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev. D

A	Rev Per EC#	RELEASE	9/11/2006	-	DF		
P	LTR	REVISION RECORD	DATE	DWG	APVD		

DIMENSIONS:
meters

CUSTOMER PRINT

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLG ± .
1 PLG ± .
2 PLG ± .
3 PLG ± .
4 PLG ± .

DWG Cable Assy Configurator	MATERIAL -	HEAT TREAT -
CHK Dave Fennell		
APVD Dave Fennell		
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure		
SCALE NTS	SIZE A2	DRAWING NO C- 1907124
SHEET 3 of 4		REV A

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

Restricted to: General Release

Label 1

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

A	Rev Per EC#	RELEASE	9/11/2006	-	DF		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

Ø	PLC	±	-
1	PLC	±	-
2	PLC	±	-
3	PLC	±	-
4	PLC	±	-

Customer Print

DIN Cable Assy Configurator		MATERIAL-	HEAT TREAT-		
CHK	Dave Fennell	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Dave Fennell				
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex Secure					
SCALE NTS	SIZE A2	DRAWING NO C- 1907124	SHEET 4 of 4	REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[TMRJ-1SURG-AL001M](#)