





1. MATERIAL:
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - BERYLLIUM COPPER,
ALLOY UNS C17300 CONDITION TD04, PER ASTM B196.
INSULATORS - TEFLON (PTFE) ROD, PER ASTM D 1710.
MODULE BODY - STAINLESS STEEL, PER UNS S30300
SLOTTED SPRIN PIN - NICKEL STAINLESS STEEL

2. FINISH:
SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - GOLD PLATE OVER NICKEL
MODULE BODY & SLOTTED PIN - PASSIVATED

3. SMPM MALE SMOOTH BORE INTERFACE PER MIL-STD-348, EXCEPT AS NOTED.

LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
J		REV PER ECO 16-014836		11-11-16	CT	DW	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.T. Morley 29MAY2009	 TE Connectivity		NAME 8 POSITION R.F. MODULE P.C.B. MOUNT - BACKPLANE VITA67,		SIZE A1		CAGE CODE 00779		DRAWING NO C=1996706		RESTRICTED TO -	
DIMENSIONS: INCHES/mm		CHK S.T. Morley 29MAY2009												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.T. Morley 29MAY2009												
		PRODUCT SPEC -												
		APPLICATION SPEC -												
MATERIAL NOTE 1		FINISH NOTE 2		WEIGHT -		SCALE 8:1		SHEET 1		OF 1		REV J		