






CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
7	LABLE	MYLAR	BLACK/YELLOW
6	O-RING	VITON	RED
5	COUPLER	BRASS	NICKEL PLATED
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	PUR	BLACK
2	OVERMOLD	POLYURETHANE (PUR)	YELLOW
1	CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PUR	BLACK

DESCRIPTION EC NO: WEU2010-0288 DRWN: LSTEMMLE 2010/01/22 CHKD: NS APPR: NSTAUDIG 2010/01/29	DESCRIPTION	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY LSTEMMLE	DATE 2010/01/22	MICRO-CHANGE JUMPER CONNECTOR LEAD 3/4/5 P. FE 90 TO MA STR					
			4 PLACES	±---	±---	CHECKED BY	DATE						
			3 PLACES	±---	±---	RE	2010/01/22						
			2 PLACES	±---	±.01	APPROVED BY	DATE						
			1 PLACE	±0.3	±---	NSTAUDIG	2010/01/29						
			ANGULAR ± --- °			MATERIAL NO. SEE TABLE SHEET 2		DOCUMENT NO. SD-120066-009			SHEET NO. 1 OF 1		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
1	REV												

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
3	1200070142	883031P03M010	1.0M +55.6 -0 [3.28' +2.19" -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
4	1200060056	884031P03M010	1.0M +55.6 -0 [3.28' +2.19" -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
5	1200668188	885031P03M010	1.0M +55.6 -0 [3.28' +2.19" -0]

DESCRIPTION EC NO: WEU2010-0288 DRWN: LSTEMMLE 2010/01/22 CHKD: NS APPR: NSTAUDIG 2010/01/29	DESCRIPTION REV	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY LSTEMMLE		DATE 2010/01/22		MICRO-CHANGE JUMPER CONNECTOR LEAD 3/4/5 P. FE 90 TO MA STR			
			4 PLACES	±---	±---	CHECKED BY		DATE 2010/01/22					
			3 PLACES	±---	±---	RE							
			2 PLACES	±---	±.01	APPROVED BY		DATE					
			1 PLACE	±0.3	±---	NSTAUDIG		2010/01/29					
			ANGULAR ± --- °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-120066-009		1 OF 1			
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						