

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED

LOC

DIST

AD

39

REVISIONS

P

LTR	
-----	--

DESCRIPTION

DATE _____

NAME	
------	--

vn

P

REV PER OG3C-0770-04

30NOV0

RR	
----	--

6



P1

REVISÉ PER ECO-09-021826


6JAN10

KK	A
----	---

EG



1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
2. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
3. .000100—.000200 MATTE TIN—LEAD OVER .000050 NICKEL.
4. .000100—.000200 BRIGHT TIN OVER .000050 NICKEL.
5. PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
6. HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR—BLACK.
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

A		Δ	Δ	1.684	1.600	16	34	4-103328-9
		Δ	Δ	1.284	1.200	12	26	4-103328-8
			Δ	.884	.800	8	18	4-103328-7
			Δ	.584	.500	5	12	4-103328-6
		Δ	Δ	3.984	3.900	39	80	4-103328-5
		Δ	Δ	.984	.900	9	20	4-103328-4
			Δ	.684	.600	6	14	4-103328-3
A			Δ	.284	.200	2	6	4-103328-2
			Δ	.084	—	—	2	4-103328-1
			Δ	3.984	3.900	39	80	4-103328-0
		OBSOLETE	Δ	3.884	3.800	38	78	3-103328-9
		OBSOLETE	Δ	3.784	3.700	37	76	3-103328-8
		OBSOLETE	Δ	3.684	3.600	36	74	3-103328-7
		OBSOLETE	Δ	3.584	3.500	35	72	3-103328-6
		OBSOLETE	Δ	3.484	3.400	34	70	3-103328-5
		OBSOLETE	Δ	3.384	3.300	33	68	3-103328-4
		OBSOLETE	Δ	3.284	3.200	32	66	3-103328-3
A			Δ	3.184	3.100	31	64	3-103328-2
			Δ	3.084	3.000	30	62	3-103328-1
			Δ	2.984	2.900	29	60	3-103328-0
			Δ	2.884	2.800	28	58	2-103328-9
			Δ	2.784	2.700	27	56	2-103328-8
			Δ	2.684	2.600	26	54	2-103328-7
			Δ	2.584	2.500	25	52	2-103328-6
			Δ	2.484	2.400	24	50	2-103328-5
		OBSOLETE	Δ	2.384	2.300	23	48	2-103328-4
		OBSOLETE	Δ	2.284	2.200	22	46	2-103328-3
A			Δ	2.184	2.100	21	44	2-103328-2
			Δ	2.084	2.000	20	42	2-103328-1
			Δ	1.984	1.900	19	40	2-103328-0
			Δ	1.884	1.800	18	38	1-103328-9
			Δ	1.784	1.700	17	36	1-103328-8
			Δ	1.684	1.600	16	34	1-103328-7
			Δ	1.584	1.500	15	32	1-103328-6
		OBSOLETE	Δ	1.484	1.400	14	30	1-103328-5
			Δ	1.384	1.300	13	28	1-103328-4
			Δ	1.284	1.200	12	26	1-103328-3
Y 6-146254-1			Δ	1.184	1.100	11	24	1-103328-2
			Δ	1.084	1.000	10	22	1-103328-1
			Δ	.984	.900	9	20	1-103328-0
			Δ	.884	.800	8	18	103328-9
			Δ	.784	.700	7	16	103328-8
			Δ	.684	.600	6	14	103328-7
			Δ	.584	.500	5	12	103328-6
			Δ	.484	.400	4	10	103328-5
			Δ	.384	.300	3	8	103328-4
			Δ	.284	.200	2	6	103328-3
Y 6-146254-1			Δ	.184	.100	1	4	103328-2
			Δ	.084	—	—	2	103328-1

THIS DRAWING IS A CONTROLLED DOCUMENT.						DATE 10/15/92		Tyo Electronics Corporation	
						CIR. 23NOV92		Harrisburg, PA 17105	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		DRAWN BY JOHN KNITTLE CHECKED BY P. FLINCHBAUGH		NAME			
		0 PLG ± — 1 PLG ± — 3 PLG ± .005 4 ANGLES ± — FINISH		PRODUCT SPEC —		ASSEMBLY, HEADER, BREAKAWAY, MOD II, DOUBLE ROW, .100 X .100 C/L VERTICAL, WITH .025 SQUARE POSTS			
MATERIAL PHOSPHOR BRONZE		SEE TABLE		APPLICATION SPEC —		SIZE A1		CAGE CODE 00779	DRAWING NO. C=103328
				WEIGHT —		RESTRICTED TO		—	
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1	REV P1