




Features:

- Low Impedance characteristics.
- Case sizes are smaller than conventional general-purpose capacitors, with very high performance.
- Can size larger than 8mm diameter has safety vent on rubber bun.
- General purpose 85°C.
- Axial leaded electrolytic.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

S. Ram

DATE:

08/05/06

CHECKED BY:

K. Suresh

DATE:

08/05/06

APPROVED BY:

N. Kiwomya

DATE:

22/05/06

DRAWING TITLE:

LV Series - Axial Electrolytic Capacitors

SIZE
A

DWG NO.

M10000226

ELECTRONIC FILE
208517_2_DWG

REV
A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 6

	PART NO. LV Series	REVISIONS								
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		-	A	RELEASED	S. R	8/5/06	K. S	8/5/06	N. K	22/5/06

Allowable ripple current Vs ambient temperature

Ambient Temperature (°C)	Under 50	70°C	85
Multiplier	1.78	1.40	1.00

Frequency coefficient of allowable ripple current

Frequency (Hz) \ Capacitance (µF)	60	120	500	1K	10K up
Under 100	0.70	1.00	1.30	1.40	1.50
100 - 1000	0.75		1.20	1.30	1.35
1000 up above	0.80		1.12	1.12	1.15

Specifications

Voltage (V)	Capacitance (µF)	Case Size Length (L) x Diameter (φD)	Allowable Ripple Current (mA)*	Lead Diameter	Part Number
10	470	16 x 8	350	0.6	LV471M1AB-0816(E)
	1000	17 x 10	640		LV102M1AB-1017(E)
	2200	22 x 13	1051		LV222M1AB-1322(E)
	4700	28 x 16	1552	0.8	LV472M1AB-1628(E)
16	22	13 x 5	60	0.6	LV220M1CB-0513(E)
	100	14 x 6.3	160		LV101M1CB-6.314(E)
	220	13 x 8	260		LV221M1CB-0813(E)
	470	16 x 8	430		LV471M1CB-0816(E)
	1000	21 x 10	770		LV102M1CB-1021(E)
	2200	24 x 13	1125		LV222M1CB-1324(E)
	4700	33 x 16	1650	0.8	LV472M1CB-1633(E)
25	10	13 x 5	40	0.6	LV100M1EB-0513(E)
	22		65		LV220M1EB-0513(E)
	47	13 x 6	100		LV470M1EB-0613(E)
	100	13 x 8	170		LV101M1EB-0813(E)

* Ripple Current at 85°C, 120Hz

Dimensions : Millimetres

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2004.	TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:				
		S. Ram	08/05/06	LV Series - Axial Electrolytic Capacitors				
		CHECKED BY:	DATE:	SIZE	DWG NO.	ELECTRONIC FILE		REV
		K. Suresh	08/05/06	A	M10000226	208517_2_DWG		A
		APPROVED BY:	DATE:					
		N. Kiwomya	22/05/06					
		SCALE: NTS		U.O.M.: mm		SHEET: 3 OF 6		

multicomp	PART NO. LV Series	REVISIONS								
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		-	A	RELEASED	S. R	8/5/06	K. S	8/5/06	N. K	22/5/06

Specifications

Voltage (V)	Capacitance (µF)	Case Size Length (L) x Diameter (φD)	Allowable Ripple Current (mA)*	Lead Diameter	Part Number
25	220	16 x 8	280	0.6	LV221M1EB-0816(E)
	470	21 x 10	510		LV471M1EB-1021(E)
	1000	22 x 13	873		LV102M1EB-1322(E)
	2200	28 x 16	1344	0.8	LV222M1EB-1628(E)
	4700	36 x 18	1881		LV472M1EB-1836(E)
35	22	13 x 6	70	0.6	LV220M1VB-0613(E)
	100	16 x 8	210		LV101M1VB-0816(E)
	220	17 x 10	340		LV221M1VB-1017(E)
	470	22 x 13	610		LV471M1VB-1322(E)
	1000	27 x 13	955		LV102M1VB-1327(E)
	2200	36 x 16	1421	0.8	LV222M1VB-1636(E)
	4700	43 x 22	2280		LV472M1VB-2243(E)
63	22	14 x 6.3	90	0.6	LV220M1JB-6.314(E)
	47	16 x 8	160		LV470M1JB-0816(E)
	100	17 x 10	260		LV101M1JB-1017(E)

*Ripple Current at 85°C, 120Hz.

Dimensions : Millimetres

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2004.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

S. Ram

CHECKED BY:

K. Suresh

APPROVED BY:

N. Kiwomya

DATE:

08/05/06

DATE:

08/05/06

DATE:

22/05/06

DRAWING TITLE:

LV Series - Axial Electrolytic Capacitors

SIZE

A

DWG NO.

M10000226

ELECTRONIC FILE

208517_2_DWG

REV

A

SCALE: NTS

U.O.M.: mm

SHEET: 4 OF 6

SHEET: 6 OF 6