




COMPRESSION SPRINGS

Century Spring warehouses the largest inventory of high-grade, straight, cylindrically-shaped compression springs in the world. All the springs found in this section of the catalog are fabricated from round wire. Rectangular wire is sometimes employed to reduce the

solid (totally compressed) height or increase the space efficiency of the design. **Century Spring's** die springs are made from rectangular wire for this reason. (See the "Die Spring" section of this catalog.)

Selecting a Compression Spring:



Turn to the inventory page with the desired outside diameter (O.D.). Outside diameters increase as page numbers increase and are found in the left column of the page.

- Next, find the length or rate (strength) you require. These, too, are normally in increasing order.

Spring rate is the load (pounds) it takes to deflect (compress) the spring one theoretical inch, i.e., if the rate = 40 lbs./in., it would take 10 pounds to deflect it 1/4 inch, or 80 pounds for 2 inches, etc..

- If the length or rate is not known but the installed working length (W.L.) is, then select a spring — say 30% longer — than the W.L..

You must know the load at the W.L.. Just subtract the W.L. from the spring's selected free length and

multiply by its rate to obtain the load to compare with your required value.

- If the load required is not obtained, select a new candidate with either an increase or decrease in rate (strength) or free length.
- Be certain that the tabulated solid length (completely compressed) for your candidate spring indicates enough room for deflection and, also, that the deflection is not significantly greater than the tabulated "Maximum Suggested" for stress reasons.

Note: If the spring needed for your application cannot be found in our catalog inventory, we can fabricate it for you. Often, there is no cost increase for this service as we have low quantity requirements.

Design Information

The basic compression rate and wire stress for a compression spring can be estimated with the following:

$$R = \frac{Gd^4}{8nD^3} \quad \text{and} \quad R = \frac{P}{\Delta}$$

$$S = \frac{8PDk}{\pi d^3} \quad \text{or} \quad S = \frac{8RDK\Delta}{\pi d^3}$$

Note: One should not employ the curvature (k) correction stress in an expression solving for deflection. Use the uncorrected stress only or errors will occur. The uncorrected stress can be used for static applications.

Large wire and bar stock sizes also require an empirically-derived reduction in the standard rate calculation of up to 9%.

For these reasons, refinements in large spring design should be left to the experienced spring designer.

Where: **D** = Mean diameter, (O.D. - d) inches

d = Wire diameter, inches

G = Modulus (spring steel = 11.5×10^6 , stainless = 10×10^6), p.s.i.

K = Stress correction factor (see plot)

N = Number of total coils

n = Number of active coils (see table)

P = Applied load, pounds

p = Pitch, distance between centerlines of wires of adjoining coils

R = Spring rate, pounds per inch (lbs./in.)

S = Wire stress, psi

Δ = Deflection, inches

$\pi = 3.14$




Design Information (continued)

The suggested maximum allowable spring-wire stress values can be derived from the "Minimum Tensile Strength" (MTS) tables found in the "Material Properties" section of this catalog. The MTS values vary with the spring-wire diameter. Further, 30 to 45 percent of the MTS value, depending on the material type, is used as a corrected stress target to produce a long fatigue life. The table, "Properties of Common Spring Materials", found also in the "Material Properties" section of this catalog, indicates the appropriate percentage value of the MTS to use for a given spring material.

For free custom spring designs, call or fax our **Custom Spring Department**. For quick stress checks on stock or custom spring designs, or technical information, call or fax our **Engineering Department**.

SPRING CHARACTERISTICS	TYPE OF ENDS			
	OPEN	OPEN & GROUND	CLOSED	CLOSED & GROUND
SOLID LENGTH	$d(N+1)$	$d \times N$	$d(N+1)$	$d \times N$
ACTIVE COILS (n)	N	$N - 1$	$N - 2$	$N - 2$
TOTAL COILS (N)	n	N	$n + 2$	$n + 2$
FREE LENGTH (L)	$(p \times N) + d$	$p \times N$	$(p \times n) + 3d$	$(p \times n) + 2d$

WAHL CURVATURE STRESS CORRECTION



Spring Characteristics

Service Life

It should be noted that if critical force-versus-deflection linearity is required, only the center 60 to 80 percent of the available deflection range should be employed. Thus, reserve at least the first and last 15 to 20 percent of the range for potential spring-end and adjacent coil-contact effects. These effects can be largely ignored for the majority of spring applications.

The column "Suggested Maximum Deflection" found in the following pages of inventory reflects the recommended inches of travel to obtain a statistical service-life of approximately 100,000 cycles (deflections) with infrequent breakage. This can be realized if the spring in question is not subjected to shock loads, rapid cycling, temperature extremes, corrosion or stress values above those previously recommended. If the spring is statically loaded (not cycling), a near-infinite life can be expected. Extended spring service-life can be expected by applying recommendations found in the "Material Properties" section of this catalog.

Materials

The highest grades of spring wire are used for fabricating our springs. To create cost-effective warehousing of our stock spring inventory for our customers, we offer material certification for custom springs only. Certifications of conformance for geometric tolerances set by the Spring Manufacturers Institute (SMI) are available for our stock springs upon request. See the "Custom Spring" section of this catalog if material trace certifications or unique materials are required.

"Spring Steel" is a stock inventory term covering:

- Music wire
- Hard-drawn (MB) wire
- Oil-tempered wire

Additionally, stock compression-spring materials include:

- Stainless Steel (300 series)
- Beryllium Copper
- Phosphor Bronze



Spring Characteristics (continued)

Tolerances

Century Spring manufactures stock springs to commercial tolerances defined by the SMI. Calculated rates and loads based on the SMI geometric tolerances have an approximate +/- ten percent. Low or high-index springs will have higher values. Compression springs characteristically have an hourglass shape when coiled on an automatic coiler; therefore, outside/inside tolerancing is applied to end coils only. This is an important consideration when selecting a spring that fits over a rod or inside a cylinder. Call us if tighter tolerance values are required.

Regarding angle tolerance, the plane of the ground end of a spring is usually within three degrees of the perpendicular-to-the-body axis of the spring.

Direction of Helix (wind)

The wind direction of our stock springs varies, both RHW and LHW. Stock springs are not sorted for wind direction. To order springs wound to a specific direction, please see page 376 for more information or contact our Custom Division at 800-237-5225.

Ends

The compression spring ends configuration is indicated in the "Ends" column of our inventory listings which are:

Closed (C) - The last coil at each end is bent back to touch the previous coil to create a flat base.

Closed and Ground (C&G) - The closed ends of a spring ground to a more accurate flat base. This will also reduce the solid length.



Open (O) - The spring end coils remain open, maintaining the spring machine's helical wind shape.

Finish

The finishes available for our compression springs are as indicated in the "Finish" column of our inventory listing which include:

Zinc
Gold Iridite
Black Oxide
Passivated (upon request)
None (can be plated upon request)

Data Required For Compression Springs



CURRENT DESIGN

Outside Diameter _____ in.

Free Length _____ in.

Wire Dia. _____ dec.

Material _____

Total Coils _____ (or pitch) _____ in.

Finish _____

SPRING TO BE DESIGNED

To work in _____ in. hole

To work over _____ in. dia. shaft

To support ____ lbs. $\pm$ ____ lbs. at _____ in.

Rate per in. _____ lbs. $\pm$

Max. solid height _____ in.

Max. deflection _____

ADD'L. INFO IF AVAILABLE

Material _____


Wind: Optional ____ Right ____ Left ____

Finish _____


Style of ends: Cl. & Grd. _____

Closed only _____

Open or Plain _____




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.036	.91	10075	.59	15.1	.022	.6	2.6	.46	.15	3.8	.39	1.7	.35	8.9	0.007	0.2	49.0	SST	C	N
0.036	.91	JJ-7	.63	15.9	.024	.6	1.6	.28	.16	4.1	.25	1.1	.25	6.2	0.006	0.2	40.0	SST	C	N
0.040	1.02	2924	.66	16.8	.020	.5	11	2.0	.13	3.2	1.4	6.4	.50	12.6	0.010	0.3	48.5	MW	C	N
0.040	1.02	10778	.69	17.5	.028	.7	1.0	.17	.35	8.9	.35	1.6	.30	7.7	0.006	0.2	49.5	MW	C	N
0.054	1.37	RR-6	.25	6.4	.036	.9	6.2	1.1	.09	2.2	.56	2.5	.16	4.1	0.009	0.2	16.5	SST	C	N
0.054	1.37	10619	.72	18.3	.038	1.0	1.6	.29	.37	9.3	.60	2.7	.32	8.1	0.008	0.2	39.0	MW	C	N
0.057	1.45	70000	.13	3.3	.045	1.1	3.7	.66	.07	1.7	.25	1.1	.04	1.0	0.006	0.2	5.75	MW	C	N
0.057	1.45	70000S	.13	3.3	.045	1.1	3.3	.57	.05	1.3	.17	.74	.04	1.0	0.006	0.2	5.75	SST	C	N
0.057	1.45	70009	.13	3.3	.043	1.1	6.9	1.2	.06	1.5	.40	1.8	.05	1.2	0.007	0.2	6.00	MW	C	N
0.057	1.45	70009S	.13	3.3	.043	1.1	6.0	1.1	.04	1.1	.26	1.2	.05	1.2	0.007	0.2	6.00	SST	C	N
0.057	1.45	70018	.13	3.3	.041	1.0	12	2.1	.05	1.2	.57	2.5	.06	1.4	0.008	0.2	6.13	MW	C	N
0.057	1.45	70018S	.13	3.3	.041	1.0	11	1.8	.03	.88	.37	1.6	.06	1.4	0.008	0.2	6.13	SST	C	N
0.057	1.45	70001	.19	4.8	.045	1.1	2.3	.40	.11	2.8	.25	1.1	.06	1.4	0.006	0.2	8.13	MW	C	N
0.057	1.45	70001S	.19	4.8	.045	1.1	2.0	.35	.08	2.1	.17	.74	.06	1.4	0.006	0.2	8.13	SST	C	N
0.057	1.45	70010	.19	4.8	.043	1.1	4.0	.70	.10	2.5	.40	1.8	.07	1.8	0.007	0.2	8.88	MW	C	N
0.057	1.45	70010S	.19	4.8	.043	1.1	3.5	.61	.07	1.9	.26	1.2	.07	1.8	0.007	0.2	8.88	SST	C	N
0.057	1.45	70019	.19	4.8	.041	1.0	7.4	1.3	.08	2.0	.57	2.5	.08	2.0	0.008	0.2	8.75	MW	C	N
0.057	1.45	70019S	.19	4.8	.041	1.0	6.4	1.1	.06	1.4	.37	1.6	.08	2.0	0.008	0.2	8.75	SST	C	N
0.057	1.45	70002	.25	6.4	.045	1.1	1.7	.30	.15	3.8	.25	1.1	.07	1.7	0.006	0.2	10.3	MW	C	N
0.057	1.45	70002S	.25	6.4	.045	1.1	1.5	.26	.11	2.8	.17	.74	.07	1.7	0.006	0.2	10.3	SST	C	N
0.057	1.45	70011	.25	6.4	.043	1.1	3.1	.54	.13	3.3	.40	1.8	.08	2.1	0.007	0.2	11.0	MW	C	N
0.057	1.45	70011S	.25	6.4	.043	1.1	2.7	.47	.10	2.5	.26	1.2	.08	2.1	0.007	0.2	11.0	SST	C	N
0.057	1.45	70020	.25	6.4	.041	1.0	5.3	.92	.11	2.8	.57	2.5	.10	2.5	0.008	0.2	11.5	MW	C	N
0.057	1.45	70020S	.25	6.4	.041	1.0	4.6	.80	.08	2.0	.37	1.6	.10	2.5	0.008	0.2	11.5	SST	C	N
0.057	1.45	70003	.31	7.9	.045	1.1	1.4	.24	.19	4.7	.25	1.1	.08	2.0	0.006	0.2	12.4	MW	C	N
0.057	1.45	70003S	.31	7.9	.045	1.1	1.2	.21	.14	3.6	.17	.74	.08	2.0	0.006	0.2	12.4	SST	C	N
0.057	1.45	70012	.31	7.9	.043	1.1	2.4	.42	.17	4.2	.40	1.8	.10	2.6	0.007	0.2	13.5	MW	C	N
0.057	1.45	70012S	.31	7.9	.043	1.1	2.1	.37	.12	3.2	.26	1.2	.10	2.6	0.007	0.2	13.5	SST	C	N
0.057	1.45	70021	.31	7.9	.041	1.0	4.1	.72	.14	3.6	.57	2.5	.12	3.1	0.008	0.2	14.3	MW	C	N
0.057	1.45	70021S	.31	7.9	.041	1.0	3.6	.62	.10	2.6	.37	1.6	.12	3.1	0.008	0.2	14.3	SST	C	N
0.057	1.45	70004	.38	9.7	.045	1.1	1.1	.19	.23	5.8	.25	1.1	.10	2.4	0.006	0.2	14.8	MW	C	N
0.057	1.45	70004S	.38	9.7	.045	1.1	.96	.17	.17	4.4	.17	.74	.10	2.4	0.006	0.2	14.8	SST	C	N
0.057	1.45	70013	.38	9.7	.043	1.1	2.0	.35	.20	5.0	.40	1.8	.12	3.0	0.007	0.2	15.8	MW	C	N
0.057	1.45	70013S	.38	9.7	.043	1.1	1.7	.31	.15	3.8	.26	1.2	.12	3.0	0.007	0.2	15.8	SST	C	N
0.057	1.45	70022	.38	9.7	.041	1.0	3.4	.59	.17	4.3	.57	2.5	.14	3.6	0.008	0.2	16.8	MW	C	N
0.057	1.45	70022S	.38	9.7	.041	1.0	3.0	.52	.12	3.1	.37	1.6	.14	3.6	0.008	0.2	16.8	SST	C	N
0.057	1.45	70005	.44	11.2	.045	1.1	.95	.17	.26	6.7	.25	1.1	.11	2.7	0.006	0.2	16.8	MW	C	N
0.057	1.45	70005S	.44	11.2	.045	1.1	.83	.14	.20	5.1	.17	.74	.11	2.7	0.006	0.2	16.8	SST	C	N
0.057	1.45	70014	.44	11.2	.043	1.1	1.7	.30	.23	5.9	.40	1.8	.14	3.4	0.007	0.2	18.3	MW	C	N
0.057	1.45	70014S	.44	11.2	.043	1.1	1.5	.26	.18	4.5	.26	1.2	.14	3.4	0.007	0.2	18.3	SST	C	N
0.057	1.45	70023	.44	11.2	.041	1.0	2.8	.50	.20	5.1	.57	2.5	.17	4.2	0.008	0.2	19.6	MW	C	N
0.057	1.45	70023S	.44	11.2	.041	1.0	2.5	.43	.15	3.8	.37	1.6	.17	4.2	0.008	0.2	19.6	SST	C	N
0.057	1.45	70006	.50	12.7	.045	1.1	.85	.15	.30	7.5	.25	1.1	.12	3.0	0.006	0.2	18.5	MW	C	N
0.057	1.45	70006S	.50	12.7	.045	1.1	.74	.13	.22	5.7	.17	.74	.12	3.0	0.006	0.2	18.5	SST	C	N
0.057	1.45	70015	.50	12.7	.043	1.1	1.5	.26	.26	6.7	.40	1.8	.15	3.8	0.007	0.2	20.4	MW	C	N
0.057	1.45	70015S	.50	12.7	.043	1.1	1.3	.23	.20	5.1	.26	1.2	.15	3.8	0.007	0.2	20.4	SST	C	N
0.057	1.45	70024	.50	12.7	.041	1.0	2.5	.43	.23	5.9	.57	2.5	.19	4.7	0.008	0.2	22.4	MW	C	N
0.057	1.45	70024S	.50	12.7	.041	1.0	2.1	.37	.17	4.3	.37	1.6	.19	4.7	0.008	0.2	22.4	SST	C	N
0.057	1.45	70007	.56	14.2	.045	1.1	.75	.13	.34	8.6	.25	1.1	.13	3.3	0.006	0.2	20.8	MW	C	N
0.057	1.45	70007S	.56	14.2	.045	1.1	.65	.11	.25	6.5	.17	.74	.13	3.3	0.006	0.2	20.8	SST	C	N
0.057	1.45	70016	.56	14.2	.043	1.1	1.3	.23	.31	7.7	.40	1.8	.17	4.3	0.007	0.2	23.3	MW	C	N
0.057	1.45	70016S	.56	14.2	.043	1.1	1.1	.20	.23	5.9	.26	1.2	.17	4.3	0.007	0.2	23.3	SST	C	N
0.057	1.45	70025	.56	14.2	.041	1.0	2.2	.39	.26	6.6	.57	2.5	.21	5.2	0.008	0.2	24.8	MW	C	N
0.057	1.45	70025S	.56	14.2	.041	1.0	1.9	.34	.19	4.8	.37	1.6	.21	5.2	0.008	0.2	24.8	SST	C	N
0.057	1.45	70008	.63	16.0	.045	1.1	.65	.11	.39	9.9	.25	1.1	.15	3.8	0.006	0.2	23.6	MW	C	N
0.057	1.45	70008S	.63	16.0	.045	1.1	.57	.10	.29	7.5	.17	.74	.15	3.8	0.006	0.2	23.6	SST	C	N
0.057	1.45	70017	.63	16.0	.043	1.1	1.2	.20	.34	8.8	.40	1.8	.19	4.8	0.007	0.2	26.0	MW	C	N
0.057	1.45	70017S	.63	16.0	.043	1.1	1.0	.18	.26	6.6	.26	1.2	.19	4.8	0.007	0.2	26.0	SST	C	N
0.057	1.45	70026	.63	16.0	.041	1.0	2.0	.35	.29	7.3	.57	2.5	.22	5.7	0.008	0.2	27.0	MW	C	N
0.057	1.45	70026S	.63	16.0	.041	1.0	1.7	.30	.21	5.3	.37	1.6	.22	5.7	0.008	0.2	27.0	SST	C	N
0.062	1.57	FF-21	.13	3.2	.048	1.2	4.1	.73	.07	1.8	.29	1.3	.06	1.4	0.007	0.2	7.00	MW	C	N
0.062	1.57	HH-3	.13	3.2	.044	1.1	11	1.8	.04	1.1	.46	2.1	.08	2.1	0.009	0.2	8.00	MW	C	N
0.062	1.57	3724	.13	3.3	.042	1.1	20	3.6	.05	1.3	1.0	4.5	.08	2.0	0.010	0.3	7.00	MW	C	N
0.062	1.57	N-157	.14	3.6	.036	.9	50	8.7	.01	.25	.50	2.2	.13	3.3	0.013	0.3	9.00	MW	C	N
0.062	1.57	3723	.16	4.0	.052	1.3	.33	.06	.07	1.7	.02	.10	.09	2.2	0.005	0.1	16.5	MW	C	N
0.062	1.57	S-1011	.16	4.0	.034	.9	72	13	.02	.59	1.7	7.4	.13	3.2	0.014	0.4	8.00	SST	C	N
0.062	1.57	B1-7	.16	4.0	.032	.8	156	27	.02	.47	2.9	13	.11	2.9	0.015	0.4	6.50	MW	C	N
0.062	1.57	12496	.19	4.7	.050	1.3	1.8	.31	.13	3.3	.23	1.0	.05	1.4	0.006	0.2	8.00	MW	C	N
0.062	1.57	JJ-49	.25	6.4	.048	1.2	2.6	.45	.09	2.4	.24	1.1	.07	1.8	0.007	0.2	9.00	SST	C	N
0.062	1.57	B1-2	.25	6.4	.046	1.2	5.3	.94	.10	2.5	.53	2.4	.08	2.0						




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.062	1.57	2534	.91	23.0	.044	1.1	1.3	.23	.45	11	.60	2.7	.46	11.6	0.009	0.2	49.8	MW	C	N
0.062	1.57	N-18	.97	24.6	.052	1.3	.06	.01	.61	16	.04	.17	.36	9.0	0.005	0.1	70.0	SST	C	N
0.068	1.73	10938	.31	8.0	.046	1.2	8.1	1.4	.10	2.5	.78	3.5	.17	4.3	0.011	0.3	14.5	SST	C	N
0.068	1.73	A10-13	.34	8.7	.052	1.3	2.6	.45	.19	4.8	.49	2.2	.11	2.7	0.008	0.2	12.5	MW	C	GI
0.072	1.83	A10-3	.50	12.7	.042	1.1	56	9.8	.05	1.2	2.6	11	.15	3.8	0.015	0.4	9.00	MW	C	N
0.075	1.91	KK-29	.20	5.2	.059	1.5	4.4	.76	.10	2.6	.44	2.0	.06	1.5	0.008	0.2	6.50	MW	C	N
0.078	1.98	N-2	.19	4.8	.068	1.7	.21	.04	.12	3.0	.02	.11	.07	1.8	0.005	0.1	13.0	MW	C	N
0.078	1.98	N-11	.22	5.6	.058	1.5	9.5	1.7	.06	1.4	.53	2.3	.07	1.8	0.010	0.3	6.25	SST	C	N
0.078	1.98	N-78	.25	6.4	.068	1.7	.38	.07	.21	5.2	.08	.35	.05	1.1	0.005	0.1	8.00	MW	C	N
0.078	1.98	S-1013	.25	6.4	.050	1.3	24	4.3	.06	1.4	1.4	6.2	.15	3.7	0.014	0.4	9.50	SST	C	N
0.078	1.98	12526	.25	6.4	.048	1.2	49	8.5	.05	1.3	2.4	11	.14	3.4	0.015	0.4	8.00	MW	C	N
0.078	1.98	M-6	.25	6.4	.044	1.1	56	9.8	.04	.95	2.1	9.3	.21	5.4	0.017	0.4	11.5	MW	C	N
0.078	1.98	S-904	.28	7.1	.054	1.4	12	2.1	.07	1.9	.89	4.0	.13	3.2	0.012	0.3	9.50	SST	C	N
0.078	1.98	LL-1	.31	7.9	.046	1.2	61	11	.05	1.2	2.9	13	.15	3.9	0.016	0.4	8.50	MW	C	N
0.078	1.98	11146	.34	8.7	.054	1.4	12	2.0	.12	3.1	1.4	6.2	.14	3.7	0.012	0.3	11.0	MW	C	N
0.078	1.98	DD-73	.34	8.7	.058	1.5	5.1	.89	.16	4.1	.82	3.7	.12	3.0	0.010	0.3	11.0	MW	C	N
0.078	1.98	4345	.50	12.7	.066	1.7	.19	.03	.32	8.2	.06	.27	.18	4.5	0.006	0.2	28.5	MW	C	N
0.078	1.98	10213	1.13	28.6	.054	1.4	2.6	.45	.54	14	1.4	6.2	.52	13.1	0.012	0.3	42.0	MW	C	Z
0.078	1.98	B4-1	1.50	38.1	.054	1.4	2.9	.51	.31	7.8	.89	4.0	.41	10.4	0.012	0.3	33.0	SST	C	N
0.083	2.11	LL-66	.25	6.4	.055	1.4	22	3.9	.06	1.5	1.3	5.9	.13	3.4	0.014	0.4	8.50	SST	C	N
0.083	2.11	NN-81	.88	22.2	.059	1.5	2.2	.38	.39	9.9	.84	3.8	.44	11.3	0.012	0.3	36.0	SST	C	N
0.084	2.13	B6-19	.28	7.0	.074	1.9	.36	.06	.00	.00	.00	.00	.04	1.0	0.005	0.1	7.00	SPR	C	N
0.088	2.24	70027	.13	3.3	.072	1.8	5.8	1.0	.07	1.7	.38	1.7	.04	1.0	0.008	0.2	4.00	MW	C	N
0.088	2.24	70027S	.13	3.3	.072	1.8	5.0	.88	.05	1.2	.24	1.1	.04	1.0	0.008	0.2	4.00	SST	C	N
0.088	2.24	70036	.13	3.3	.068	1.7	13	2.2	.06	1.5	.74	3.3	.05	1.4	0.010	0.3	4.38	MW	C	N
0.088	2.24	70036S	.13	3.3	.068	1.7	11	1.9	.04	1.1	.47	2.1	.05	1.4	0.010	0.3	4.38	SST	C	N
0.088	2.24	70047	.13	3.3	.064	1.6	26	4.5	.05	1.2	1.3	5.6	.07	1.7	0.012	0.3	4.63	MW	C	N
0.088	2.24	70047S	.13	3.3	.064	1.6	22	3.9	.04	.90	.80	3.6	.07	1.7	0.012	0.3	4.63	SST	C	N
0.088	2.24	KK-17	.19	4.7	.068	1.7	10	1.8	.07	1.9	.74	3.3	.06	1.5	0.010	0.3	5.00	MW	C	N
0.088	2.24	70028	.19	4.8	.072	1.8	3.5	.62	.11	2.7	.38	1.7	.05	1.3	0.008	0.2	5.25	MW	C	N
0.088	2.24	70028S	.19	4.8	.072	1.8	3.1	.54	.08	2.0	.24	1.1	.05	1.3	0.008	0.2	5.25	SST	C	N
0.088	2.24	70037	.19	4.8	.068	1.7	6.9	1.2	.11	2.7	.74	3.3	.07	1.9	0.010	0.3	6.38	MW	C	N
0.088	2.24	70037S	.19	4.8	.068	1.7	6.0	1.1	.08	2.0	.47	2.1	.07	1.9	0.010	0.3	6.38	SST	C	N
0.088	2.24	70048	.19	4.8	.064	1.6	15	2.6	.09	2.2	1.3	5.6	.09	2.3	0.012	0.3	6.63	MW	C	N
0.088	2.24	70048S	.19	4.8	.064	1.6	13	2.2	.06	1.6	.80	3.6	.09	2.3	0.012	0.3	6.63	SST	C	N
0.088	2.24	70029	.25	6.4	.072	1.8	2.5	.44	.15	3.9	.38	1.7	.06	1.5	0.008	0.2	6.63	MW	C	N
0.088	2.24	70029S	.25	6.4	.072	1.8	2.2	.38	.11	2.9	.24	1.1	.06	1.5	0.008	0.2	6.63	SST	C	N
0.088	2.24	70038	.25	6.4	.068	1.7	5.0	.88	.15	3.7	.74	3.3	.09	2.3	0.010	0.3	8.00	MW	C	N
0.088	2.24	70038S	.25	6.4	.068	1.7	4.4	.77	.11	2.7	.47	2.1	.09	2.3	0.010	0.3	8.00	SST	C	N
0.088	2.24	70049	.25	6.4	.064	1.6	11	1.9	.12	3.0	1.3	5.6	.11	2.9	0.012	0.3	8.38	MW	C	N
0.088	2.24	70049S	.25	6.4	.064	1.6	9.3	1.6	.09	2.2	.80	3.6	.11	2.9	0.012	0.3	8.38	SST	C	N
0.088	2.24	70030	.31	7.9	.072	1.8	2.0	.36	.19	4.8	.38	1.7	.07	1.8	0.008	0.2	7.63	MW	C	N
0.088	2.24	70030S	.31	7.9	.072	1.8	1.8	.31	.14	3.5	.24	1.1	.07	1.8	0.008	0.2	7.63	SST	C	N
0.088	2.24	70039	.31	7.9	.068	1.7	3.9	.68	.19	4.8	.74	3.3	.11	2.7	0.010	0.3	9.75	MW	C	N
0.088	2.24	70039S	.31	7.9	.068	1.7	3.4	.60	.14	3.5	.47	2.1	.11	2.7	0.010	0.3	9.75	SST	C	N
0.088	2.24	70050	.31	7.9	.064	1.6	8.2	1.4	.15	3.9	1.3	5.6	.14	3.4	0.012	0.3	10.3	MW	C	N
0.088	2.24	70050S	.31	7.9	.064	1.6	7.2	1.3	.11	2.8	.80	3.6	.14	3.4	0.012	0.3	10.3	SST	C	N
0.088	2.24	12767	.34	8.7	.056	1.4	39	6.8	.07	1.7	2.6	12	.15	3.9	0.016	0.4	8.50	MW	C	N
0.088	2.24	70031	.38	9.7	.072	1.8	1.6	.27	.25	6.2	.38	1.7	.08	2.1	0.008	0.2	9.38	MW	C	N
0.088	2.24	70031S	.38	9.7	.072	1.8	1.4	.24	.18	4.6	.24	1.1	.08	2.1	0.008	0.2	9.38	SST	C	N
0.088	2.24	70040	.38	9.7	.068	1.7	3.3	.58	.22	5.6	.74	3.3	.12	3.1	0.010	0.3	11.1	MW	C	N
0.088	2.24	70040S	.38	9.7	.068	1.7	2.9	.51	.16	4.1	.47	2.1	.12	3.1	0.010	0.3	11.1	SST	C	N
0.088	2.24	70051	.38	9.7	.064	1.6	6.6	1.2	.19	4.8	1.3	5.6	.16	4.0	0.012	0.3	12.3	MW	C	N
0.088	2.24	70051S	.38	9.7	.064	1.6	5.8	1.0	.14	3.5	.80	3.6	.16	4.0	0.012	0.3	12.3	SST	C	N
0.088	2.24	70032	.44	11.2	.072	1.8	1.4	.24	.27	7.0	.38	1.7	.09	2.3	0.008	0.2	10.3	MW	C	N
0.088	2.24	70032S	.44	11.2	.072	1.8	1.2	.21	.20	5.1	.24	1.1	.09	2.3	0.008	0.2	10.3	SST	C	N
0.088	2.24	70041	.44	11.2	.068	1.7	2.9	.50	.26	6.6	.74	3.3	.14	3.5	0.010	0.3	12.6	MW	C	N
0.088	2.24	70041S	.44	11.2	.068	1.7	2.5	.43	.19	4.8	.47	2.1	.14	3.5	0.010	0.3	12.6	SST	C	N
0.088	2.24	70052	.44	11.2	.064	1.6	5.8	1.0	.22	5.5	1.3	5.6	.18	4.5	0.012	0.3	13.8	MW	C	N
0.088	2.24	70052S	.44	11.2	.064	1.6	5.0	.88	.16	4.0	.80	3.6	.18	4.5	0.012	0.3	13.8	SST	C	N
0.088	2.24	70033	.50	12.7	.072	1.8	1.2	.21	.32	8.1	.38	1.7	.10	2.6	0.008	0.2	11.6	MW	C	N
0.088	2.24	70033S	.50	12.7	.072	1.8	1.0	.18	.23	6.0	.24	1.1	.10	2.6	0.008	0.2	11.6	SST	C	N
0.088	2.24	70042	.50	12.7	.068	1.7	2.4	.42	.31	7.8	.74	3.3	.16	4.0	0.010	0.3	14.6	MW	C	N
0.088	2.24	70042S	.50	12.7	.068	1.7	2.1	.37	.23	5.7	.47	2.1	.16	4.0	0.010	0.3	14.6	SST	C	N
0.088	2.24	70053	.50	12.7	.064	1.6	4.9	.86	.25	6.5	1.3	5.6	.20	5.1	0.012	0.3	15.8	MW	C	N
0.088	2.24	70053S	.50	12.7	.064	1.6	4.3	.75	.19	4.7	.80	3.6	.20	5.1	0.012	0.3	15.8	SST	C	N
0.088	2.24	70034	.56	14.2	.072	1.8	1.0	.18	.37	9.3	.38	1.7	.11	2.8	0.008	0.2	13.0	MW	C	N
0.088	2.24	70034S	.56	14.2	.072	1.8	.91	.16	.27	6.8	.24	1.1	.11	2.8	0.008	0.2	13.0	SST	C	N
0.088	2.24	70043	.56	14.2	.068	1.7	2.1	.38	.34	8.7	.74	3.3	.17	4.3	0.010					




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.088	2.24	70056	.69	17.5	.064	1.6	3.5	.61	.36	9.1	1.3	5.6	.27	6.8	0.012	0.3	21.4	MW	C	N
0.088	2.24	70056S	.69	17.5	.064	1.6	3.0	.53	.26	6.7	.80	3.6	.27	6.8	0.012	0.3	21.4	SST	C	N
0.088	2.24	70046	.75	19.1	.068	1.7	1.6	.28	.46	12	.74	3.3	.22	5.6	0.010	0.3	20.9	MW	C	N
0.088	2.24	70046S	.75	19.1	.068	1.7	1.4	.24	.34	8.5	.47	2.1	.22	5.6	0.010	0.3	20.9	SST	C	N
0.088	2.24	70057	.75	19.1	.064	1.6	3.1	.54	.40	10	1.3	5.6	.30	7.6	0.012	0.3	23.9	MW	C	N
0.088	2.24	70057S	.75	19.1	.064	1.6	2.7	.47	.30	7.5	.80	3.6	.30	7.6	0.012	0.3	23.9	SST	C	N
0.092	2.34	11161	.50	12.7	.072	1.8	1.6	.29	.33	8.5	.55	2.4	.12	3.0	0.010	0.3	11.0	BC	C	N
0.094	2.39	EE-21	.13	3.2	.066	1.7	48	8.4	.02	.63	1.2	5.2	.07	1.8	0.014	0.4	4.00	SST	C	N
0.094	2.39	S-1010	.14	3.6	.054	1.4	144	25	.01	.25	1.4	6.4	.13	3.3	0.020	0.5	5.50	SST	C	N
0.094	2.39	3719	.16	4.0	.068	1.7	24	4.2	.06	1.6	1.5	6.6	.08	2.1	0.013	0.3	5.25	MW	C	N
0.094	2.39	BB-5	.17	4.3	.078	2.0	2.3	.41	.12	2.9	.27	1.2	.06	1.4	0.008	0.2	6.00	MW	C	N
0.094	2.39	O-23	.19	4.7	.074	1.9	2.7	.47	.07	1.7	.18	.80	.12	3.0	0.010	0.3	11.0	MW	C	Z
0.094	2.39	2870	.19	4.8	.072	1.8	7.2	1.3	.10	2.5	.71	3.1	.09	2.3	0.011	0.3	7.13	MW	C	Z
0.094	2.39	II-22	.22	5.5	.074	1.9	1.9	.33	.06	1.5	.11	.48	.16	4.1	0.010	0.3	15.0	MW	C	N
0.094	2.39	BB-21	.22	5.6	.078	2.0	2.7	.47	.09	2.2	.23	1.0	.05	1.2	0.008	0.2	5.00	SST	C	N
0.094	2.39	N-79	.25	6.4	.084	2.1	.18	.03	.20	5.1	.04	.16	.05	1.3	0.005	0.1	9.00	MW	C	N
0.094	2.39	JJ-68	.25	6.4	.074	1.9	4.3	.75	.10	2.6	.44	2.0	.08	2.0	0.010	0.3	7.00	SST	C	N
0.094	2.39	N-99	.25	6.4	.070	1.8	6.7	1.2	.12	3.0	.78	3.4	.13	3.4	0.012	0.3	10.1	MW	C	GI
0.094	2.39	11923	.25	6.4	.070	1.8	7.7	1.4	.13	3.3	1.0	4.5	.12	3.0	0.012	0.3	9.00	MW	C	N
0.094	2.39	3648	.25	6.4	.066	1.7	22	3.8	.09	2.2	1.9	8.2	.11	2.8	0.014	0.4	7.00	MW	C	Z
0.094	2.39	M-118	.25	6.4	.064	1.6	30	5.2	.07	1.8	2.1	9.1	.12	3.0	0.015	0.4	7.00	MW	C	Z
0.094	2.39	II-96	.25	6.4	.052	1.3	125	22	.03	.72	3.5	16	.17	4.3	0.021	0.5	7.00	SST	C	N
0.094	2.39	O-148	.28	7.1	.048	1.2	250	44	.03	.69	6.8	30	.17	4.4	0.023	0.6	6.50	MW	C	N
0.094	2.39	DD-7	.30	7.5	.068	1.7	7.7	1.4	.13	3.4	1.0	4.6	.14	3.6	0.013	0.3	10.0	HD	O	Z
0.094	2.39	LL-37	.31	7.9	.074	1.9	3.0	.53	.15	3.7	.44	2.0	.10	2.5	0.010	0.3	9.00	SST	C	N
0.094	2.39	10219	.31	7.9	.072	1.8	4.6	.81	.19	4.9	.88	3.9	.12	3.1	0.011	0.3	10.0	MW	C	N
0.094	2.39	10083	.31	7.9	.068	1.7	15	2.7	.10	2.5	1.5	6.6	.10	2.6	0.013	0.3	7.00	MW	C	N
0.094	2.39	O-56	.31	8.0	.070	1.8	5.4	.95	.16	4.0	.85	3.8	.16	4.0	0.012	0.3	12.0	MW	C	Z
0.094	2.39	00-10	.31	7.9	.052	1.3	82	14	.06	1.6	5.3	24	.20	5.2	0.021	0.5	8.75	MW	O	N
0.094	2.39	10874	.34	8.7	.064	1.6	16	2.8	.09	2.2	1.4	6.1	.17	4.3	0.015	0.4	10.3	SST	C	N
0.094	2.39	S-1526	.34	8.7	.060	1.5	35	6.2	.06	1.4	2.0	8.7	.16	4.1	0.017	0.4	8.50	SST	C	N
0.094	2.39	11113	.34	8.7	.058	1.5	43	7.5	.08	2.0	3.5	15	.20	5.0	0.018	0.5	10.0	MW	C	N
0.094	2.39	M-56	.34	8.7	.052	1.3	62	11	.06	1.4	3.5	16	.27	6.9	0.021	0.5	12.0	SST	C	N
0.094	2.39	N-315	.34	8.7	.066	1.7	13	2.4	.14	3.5	1.9	8.2	.15	3.9	0.014	0.4	10.0	MW	C	N
0.094	2.39	10932	.34	8.7	.062	1.6	24	4.2	.10	2.6	2.5	11	.18	4.6	0.016	0.4	10.3	MW	C	GI
0.094	2.39	FF-33	.38	9.5	.070	1.8	5.7	1.0	.21	5.3	1.2	5.3	.15	3.8	0.012	0.3	11.5	MW	C	N
0.094	2.39	LL-2	.38	9.5	.070	1.8	2.0	.34	.16	4.0	.31	1.4	.22	5.5	0.012	0.3	17.0	MW	C	N
0.094	2.39	3778	.38	9.5	.066	1.7	13	2.4	.14	3.5	1.9	8.2	.15	3.9	0.014	0.4	10.0	MW	C	Z
0.094	2.39	N-15	.41	10.3	.074	1.9	2.9	.50	.24	6.2	.69	3.1	.12	2.9	0.010	0.3	10.5	MW	C	N
0.094	2.39	V-92	.41	10.3	.058	1.5	43	7.5	.08	2.0	3.5	15	.20	5.0	0.018	0.5	10.0	MW	C	N
0.094	2.39	11127	.44	11.1	.066	1.7	9.0	1.6	.21	5.2	1.9	8.2	.21	5.3	0.014	0.4	14.0	MW	C	N
0.094	2.39	O-8	.44	11.1	.064	1.6	15	2.6	.14	3.5	2.1	9.1	.20	5.0	0.015	0.4	12.0	MW	C	N
0.094	2.39	2541	.44	11.1	.062	1.6	18	3.2	.14	3.5	2.5	11	.22	5.7	0.016	0.4	13.0	MW	C	Z
0.094	2.39	N-40	.44	11.1	.062	1.6	17	2.9	.15	3.8	2.5	11	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.094	2.39	N-26	.44	11.1	.060	1.5	24	4.2	.12	3.1	2.9	13	.24	6.0	0.017	0.4	13.0	MW	C	N
0.094	2.39	N-149	.44	11.1	.058	1.5	31	5.4	.11	2.9	3.5	15	.26	6.5	0.018	0.5	13.3	MW	C	Z
0.094	2.39	3902	.44	11.1	.054	1.4	52	9.0	.09	2.3	4.6	21	.28	7.1	0.020	0.5	13.0	MW	C	N
0.094	2.39	CC-92	.44	11.1	.050	1.3	69	12	.09	2.2	5.9	26	.35	8.9	0.022	0.6	15.0	MW	C	Z
0.094	2.39	N-7	.47	11.9	.066	1.7	8.0	1.4	.23	5.9	1.9	8.2	.23	5.9	0.014	0.4	15.5	MW	C	N
0.094	2.39	10782	.50	12.7	.078	2.0	.64	.11	.26	6.6	.17	.74	.09	2.4	0.008	0.2	10.8	BC	C	N
0.094	2.39	1904	.50	12.7	.074	1.9	1.6	.28	.32	8.1	.52	2.3	.18	4.6	0.010	0.3	17.0	MW	C	Z
0.094	2.39	A9-20	.50	12.7	.074	1.9	2.6	.45	.27	6.9	.69	3.1	.13	3.2	0.010	0.3	11.5	MW	C	Z
0.094	2.39	B-403	.50	12.7	.074	1.9	1.8	.31	.33	8.4	.59	2.6	.17	4.3	0.010	0.3	15.8	MW	C	Z
0.094	2.39	B-404	.50	12.7	.070	1.8	3.5	.61	.28	7.1	.97	4.3	.22	5.6	0.012	0.3	17.5	MW	C	Z
0.094	2.39	G-6	.50	12.7	.068	1.7	7.4	1.3	.20	5.2	1.5	6.6	.18	4.5	0.013	0.3	12.5	MW	C	BO
0.094	2.39	B-405	.50	12.7	.066	1.7	6.7	1.2	.23	5.9	1.6	7.0	.27	6.8	0.014	0.4	18.0	MW	C	Z
0.094	2.39	B-406	.50	12.7	.062	1.6	12	2.2	.20	5.0	2.4	11	.30	7.7	0.016	0.4	18.0	MW	C	Z
0.094	2.39	S-860	.53	13.5	.068	1.7	6.1	1.1	.16	4.0	.95	4.2	.18	4.6	0.013	0.3	13.0	SST	C	N
0.094	2.39	B15-14	.53	13.5	.066	1.7	5.8	1.0	.23	5.8	1.3	6.0	.30	7.6	0.014	0.4	20.5	MW	C	N
0.094	2.39	N-101	.53	13.5	.064	1.6	7.4	1.3	.19	4.7	1.4	6.1	.35	8.8	0.015	0.4	22.0	MW	C	Z
0.094	2.39	HH-62	.56	14.3	.078	2.0	.77	.14	.44	11	.34	1.5	.12	3.0	0.008	0.2	14.0	MW	C	GI
0.094	2.39	3066	.56	14.3	.074	1.9	1.7	.29	.39	9.8	.65	2.9	.18	4.4	0.010	0.3	16.5	MW	C	Z
0.094	2.39	B10-14	.56	14.3	.068	1.7	4.0	.70	.27	6.9	1.1	4.9	.29	7.3	0.013	0.3	21.3	MW	C	Z
0.094	2.39	YY-9	.56	14.3	.066	1.7	7.2	1.3	.16	4.2	1.2	5.2	.22	5.7	0.014	0.4	15.0	SST	C	N
0.094	2.39	G-14	.59	15.1	.066	1.7	6.5	1.1	.28	7.2	1.9	8.2	.27	6.9	0.014	0.4	18.5	MW	C	N
0.094	2.39	S-1577	.59	15.1	.054	1.4	63	11	.05	1.2	3.1	14	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.094	2.39	II-10	.63	15.9	.082	2.1	.24	.04	.43	11	.10	.46	.08	2.0	0.006	0.2	12.0	SST	C	N
0.094	2.39	B2-3	.63	15.9	.070	1.8	3.2	.56	.37	9.4	1.2	5.3	.24	6.1	0.012	0.3	19.0	MW	C	N
0.094	2.39	3642	.63	15.9	.066	1.7	9.0	1.6	.21	5.2	1.9	8.2	.21	5.3	0.014	0.4	14.0	MW	C	Z
0.094	2.39	VV-24	.75	19.1	.074	1.9	.94	.16	.47	12	.44	2.0	.26	6.5	0.010					




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.100	2.54	10434	.22	5.6	.086	2.2	.86	.15	.16	4.1	.14	.62	.06	1.4	0.007	0.2	7.00	MW	C	N
0.100	2.54	A9-16	.25	6.4	.082	2.1	2.3	.40	.17	4.4	.39	1.8	.08	1.9	0.009	0.2	7.50	MW	C	N
0.100	2.54	00-41	.31	7.9	.076	1.9	6.3	1.1	.11	2.9	.71	3.2	.11	2.7	0.012	0.3	8.00	SST	C	N
0.100	2.54	10007	.34	8.7	.068	1.7	18	3.1	.13	3.4	2.3	10	.19	4.9	0.016	0.4	11.0	MW	C	N
0.100	2.54	00-25	.38	9.5	.060	1.5	57	10	.05	1.3	2.9	13	.20	5.1	0.020	0.5	9.00	SST	C	N
0.100	2.54	NN-7	.44	11.1	.060	1.5	35	6.1	.08	2.2	2.9	13	.25	6.4	0.020	0.5	11.5	SST	C	N
0.105	2.67	BB-31	.28	7.0	.089	2.3	.86	.15	.20	5.1	.17	.76	.08	1.9	0.008	0.2	8.50	SST	C	N
0.109	2.77	A9-10	.13	3.2	.065	1.7	227	40	.02	.38	3.4	15	.11	2.8	0.022	0.6	4.00	SST	C	N
0.109	2.77	N-17	.16	4.0	.101	2.6	.03	.005	.10	2.6	.003	.01	.05	1.3	0.004	0.1	12.0	SST	C	N
0.109	2.77	EE-23	.17	4.4	.069	1.8	124	22	.03	.84	4.1	18	.11	2.7	0.020	0.5	4.00	MW	C	GI
0.109	2.77	L-71	.19	4.7	.093	2.4	1.1	.20	.12	3.1	.14	.63	.06	1.6	0.008	0.2	7.00	MW	C	N
0.109	2.77	2500	.19	4.8	.089	2.3	3.7	.65	.12	3.0	.44	1.9	.07	1.8	0.010	0.3	6.00	MW	C	Z
0.109	2.77	B15-29	.22	5.6	.091	2.3	1.3	.24	.13	3.3	.17	.77	.09	2.3	0.009	0.2	9.00	MW	C	Z
0.109	2.77	JJ-20	.25	6.4	.093	2.4	.99	.17	.19	4.7	.18	.82	.06	1.6	0.008	0.2	7.00	SST	C	N
0.109	2.77	3722	.25	6.4	.089	2.3	2.5	.43	.16	4.1	.40	1.8	.09	2.3	0.010	0.3	8.00	MW	C	N
0.109	2.77	JJ-1	.25	6.4	.089	2.3	4.3	.74	.09	2.3	.38	1.7	.06	1.5	0.010	0.3	5.00	SST	C	N
0.109	2.77	N-9	.25	6.4	.085	2.2	5.3	.92	.12	3.2	.66	2.9	.10	2.6	0.012	0.3	7.50	SST	C	N
0.109	2.77	V-70	.25	6.4	.081	2.1	5.9	1.0	.05	1.4	.32	1.4	.20	5.0	0.014	0.4	13.0	MW	C	N
0.109	2.77	B-21	.25	6.4	.079	2.0	25	4.4	.05	1.2	1.2	5.3	.09	2.3	0.015	0.4	5.00	SST	C	N
0.109	2.77	O-118	.28	7.1	.091	2.3	1.3	.24	.20	5.1	.27	1.2	.08	2.1	0.009	0.2	9.00	MW	CG	N
0.109	2.77	O-5	.28	7.1	.085	2.2	6.5	1.1	.16	4.0	1.0	4.6	.10	2.4	0.012	0.3	7.00	MW	C	N
0.109	2.77	A15-49	.28	7.1	.073	1.9	33	5.8	.09	2.3	3.0	14	.14	3.7	0.018	0.5	8.00	MW	CG	N
0.109	2.77	QQ-11	.28	7.1	.067	1.7	59	10	.05	1.3	3.1	14	.19	4.8	0.021	0.5	8.00	SST	C	N
0.109	2.77	12527	.30	7.5	.079	2.0	15	2.6	.12	3.1	1.8	8.0	.14	3.4	0.015	0.4	8.00	MW	C	N
0.109	2.77	B15-45	.31	7.9	.095	2.4	.58	.10	.24	6.2	.14	.63	.06	1.4	0.007	0.2	7.00	SST	C	N
0.109	2.77	S-1089	.31	7.9	.091	2.3	1.6	.29	.17	4.4	.28	1.3	.07	1.8	0.009	0.2	7.00	SST	C	N
0.109	2.77	G-16	.31	7.9	.085	2.2	3.2	.55	.17	4.3	.53	2.4	.14	3.7	0.012	0.3	11.0	SST	C	N
0.109	2.77	BB-12	.31	7.9	.083	2.1	5.8	1.0	.14	3.7	.83	3.7	.13	3.3	0.013	0.3	9.00	SST	C	N
0.109	2.77	N-1	.31	7.9	.081	2.1	9.9	1.7	.16	4.1	1.6	7.2	.13	3.4	0.014	0.4	8.50	MW	C	GI
0.109	2.77	12531	.31	7.9	.079	2.0	17.5	3.0	.11	2.8	1.8	8.0	.12	3.0	0.015	0.4	7.00	MW	C	N
0.109	2.77	BB-14	.31	7.9	.069	1.8	50	8.8	.08	2.1	4.1	18	.19	4.8	0.020	0.5	8.50	MW	C	N
0.109	2.77	12454	.34	8.7	.085	2.2	4.8	.85	.14	3.5	.66	2.9	.11	2.7	0.012	0.3	8.00	SST	C	N
0.109	2.77	J-48	.34	8.7	.069	1.8	33	5.7	.08	2.1	2.7	12	.26	6.6	0.020	0.5	12.0	MW	C	N
0.109	2.77	LL-63	.34	8.7	.065	1.7	74	13	.05	1.2	3.6	16	.20	5.0	0.022	0.6	8.00	SST	C	N
0.109	2.77	12534	.34	8.7	.093	2.4	.66	.12	.26	6.6	.17	.77	.08	2.1	0.008	0.2	9.50	SST	C	N
0.109	2.77	00-26	.34	8.7	.073	1.9	22	3.9	.09	2.3	2.0	9.0	.20	5.0	0.018	0.5	10.0	SST	C	N
0.109	2.77	A12-33	.38	9.5	.093	2.4	.71	.13	.29	7.3	.20	.91	.09	2.2	0.008	0.2	10.0	MW	C	N
0.109	2.77	KK-10	.38	9.5	.071	1.8	33	5.7	.07	1.8	2.4	11	.19	4.8	0.019	0.5	9.00	SST	C	N
0.109	2.77	A9-17	.38	9.5	.069	1.8	59	10	.07	1.8	4.1	18	.17	4.3	0.020	0.5	7.50	MW	C	N
0.109	2.77	GG-19	.38	9.5	.069	1.8	23	4.1	.10	2.4	2.2	9.9	.28	7.1	0.020	0.5	14.0	SST	CG	N
0.109	2.77	2937	.41	10.3	.087	2.2	1.8	.31	.24	6.0	.42	1.9	.17	4.3	0.011	0.3	14.5	MW	C	Z
0.109	2.77	1501	.44	11.1	.065	1.7	49	8.5	.11	2.8	5.4	24	.30	7.5	0.022	0.6	12.5	MW	C	Z
0.109	2.77	B2-27	.45	11.5	.077	2.0	9.0	1.6	.20	5.0	1.8	7.9	.26	6.5	0.016	0.4	15.0	MW	C	Z
0.109	2.77	S-829	.47	11.9	.071	1.8	32	5.6	.07	1.9	2.4	11	.19	4.8	0.019	0.5	9.00	SST	C	N
0.109	2.77	L-2	.47	11.9	.069	1.8	27	4.8	.15	3.8	4.1	18	.30	7.6	0.020	0.5	14.0	MW	C	GI
0.109	2.77	N-69	.47	11.9	.065	1.7	57	10	.09	2.4	5.4	24	.26	6.7	0.022	0.6	11.0	MW	C	N
0.109	2.77	V-16	.50	12.7	.089	2.3	.81	.14	.31	7.9	.25	1.1	.19	4.8	0.010	0.3	18.0	SST	C	N
0.109	2.77	B2-33	.50	12.7	.085	2.2	4.4	.76	.24	6.0	1.0	4.6	.13	3.2	0.012	0.3	9.50	MW	C	N
0.109	2.77	S-814	.50	12.7	.063	1.6	51	9.0	.08	2.0	4.1	18	.32	8.0	0.023	0.6	12.8	SST	C	N
0.109	2.77	B-54	.50	12.7	.059	1.5	95	17	.08	1.9	7.2	32	.33	8.3	0.025	0.6	12.0	MW	C	N
0.109	2.77	B15-50	.53	13.5	.087	2.2	2.5	.44	.32	8.2	.80	3.5	.13	3.4	0.011	0.3	11.0	MW	C	N
0.109	2.77	N-19	.53	13.5	.075	1.9	15	2.7	.17	4.3	2.6	11	.22	5.6	0.017	0.4	12.0	MW	C	N
0.109	2.77	L-72	.56	14.3	.095	2.4	.17	.03	.42	11	.07	.31	.14	3.6	0.007	0.2	19.0	SST	C	N
0.109	2.77	N-6	.56	14.3	.093	2.4	.48	.08	.44	11	.21	.94	.12	3.0	0.008	0.2	14.0	MW	C	N
0.109	2.77	AA-37	.56	14.3	.089	2.3	.68	.12	.32	8.2	.22	.98	.24	6.1	0.010	0.3	23.0	MW	C	Z
0.109	2.77	A-38	.59	15.1	.085	2.2	3.0	.52	.35	8.8	1.0	4.6	.17	4.3	0.012	0.3	13.0	MW	C	N
0.109	2.77	U-76	.63	15.9	.085	2.2	2.0	.36	.40	10	.81	3.6	.23	5.8	0.012	0.3	18.0	MW	C	N
0.109	2.77	12529	.63	15.9	.077	2.0	11	1.9	.20	5.2	2.2	9.6	.22	5.7	0.016	0.4	13.0	MW	C	N
0.109	2.77	G-82	.63	15.9	.069	1.8	15	2.6	.18	4.7	2.7	12	.44	11.2	0.020	0.5	21.0	SST	C	N
0.109	2.77	DD-32	.63	15.9	.069	1.8	24	4.2	.17	4.3	4.1	18	.30	7.6	0.020	0.5	15.0	MW	CG	N
0.109	2.77	A9-21	.63	15.9	.067	1.7	29	5.1	.16	4.1	4.7	21	.36	9.1	0.021	0.5	16.0	MW	C	N
0.109	2.77	PP-33	.66	16.7	.081	2.1	2.9	.51	.31	7.8	.90	4.0	.35	8.9	0.014	0.4	24.0	MW	C	Z
0.109	2.77	H-76	.69	17.4	.079	2.0	4.0	.70	.33	8.3	1.3	5.8	.36	9.1	0.015	0.4	24.0	MW	CG	N
0.109	2.77	JJ-57	.75	19.1	.087	2.2	.97	.17	.50	13	.48	2.1	.25	6.4	0.011	0.3	22.0	SST	C	N
0.109	2.77	U-83	.75	19.1	.085	2.2	1.7	.30	.49	12	.84	3.7	.26	6.7	0.012	0.3	21.0	MW	C	Z
0.109	2.77	U-55	.81	20.6	.085	2.2	1.9	.33	.35	8.8	.66	2.9	.22	5.5	0.012	0.3	17.0	SST	C	N
0.109	2.77	A10-37	.84	21.4	.083	2.1	2.3	.40	.36	9.2	.83	3.7	.27	6.9	0.013	0.3	20.0	SST	C	N
0.109	2.77	W-54	.88	22.2	.095	2.4	.19	.03	.74	19	.14	.63	.14	3.6	0.007	0.2	19.0	MW	C	GI
0.109	2.77	MM-47	.88	22.2	.089	2.3	.85	.15	.45	11	.38	1.7	.17	4.3	0.010	0.3	17.0	SST	CG	N
0.109	2.77	KK-5	.94	23.8	.059	1.5	34	5.9	.14	3.7										





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.114	2.90	GG-7	.16	4.0	.090	2.3	8.1	1.4	.08	2.0	.63	2.8	.07	1.8	0.012	0.3	5.00	SST	C	N
0.114	2.90	00-7	.16	4.0	.070	1.8	192	34	.02	.46	3.5	15	.11	2.8	0.022	0.6	4.00	SST	C	N
0.114	2.90	V-79	.25	6.4	.082	2.1	15	2.6	.07	1.9	1.1	4.8	.18	4.5	0.016	0.4	10.3	MW	C	N
0.114	2.90	10442	.31	7.9	.086	2.2	9.6	1.7	.16	4.1	1.6	6.9	.12	3.1	0.014	0.4	7.75	MW	C	N
0.114	2.90	B12-39	.44	11.1	.074	1.9	30	5.3	.09	2.2	2.6	12	.22	5.6	0.020	0.5	10.0	SST	C	N
0.114	2.90	10909	1.00	25.4	.094	2.4	.91	.16	.63	16	.58	2.6	.17	4.3	0.010	0.3	16.0	MW	C	Z
0.114	2.90	A11-5	1.34	34.1	.068	1.7	12	2.1	.33	8.4	3.9	17	.99	25.1	0.023	0.6	42.0	SST	C	N
0.117	2.97	12747	.27	6.8	.083	2.1	21	3.7	.08	2.0	1.6	7.2	.14	3.5	0.017	0.4	7.00	SST	C	N
0.120	3.05	70109	.19	4.8	.088	2.2	26	4.5	.08	2.0	2.0	8.8	.08	2.1	0.016	0.4	5.25	MW	CG	N
0.120	3.05	70109S	.19	4.8	.088	2.2	22	3.9	.06	1.5	1.3	5.9	.08	2.1	0.016	0.4	5.25	SST	CG	N
0.120	3.05	70131	.19	4.8	.084	2.1	41	7.1	.07	1.7	2.8	12	.10	2.5	0.018	0.5	5.50	MW	CG	N
0.120	3.05	70131S	.19	4.8	.084	2.1	35	6.2	.05	1.3	1.9	8.3	.10	2.5	0.018	0.5	5.50	SST	CG	N
0.120	3.05	70058	.25	6.4	.100	2.5	3.2	.56	.17	4.4	.55	2.4	.05	1.4	0.010	0.3	5.38	MW	CG	N
0.120	3.05	70058S	.25	6.4	.100	2.5	2.8	.49	.13	3.2	.35	1.6	.05	1.4	0.010	0.3	5.38	SST	CG	N
0.120	3.05	70074	.25	6.4	.096	2.4	6.3	1.1	.15	3.8	.94	4.2	.07	1.8	0.012	0.3	5.75	MW	CG	N
0.120	3.05	70074S	.25	6.4	.096	2.4	5.5	.96	.11	2.8	.60	2.7	.07	1.8	0.012	0.3	5.75	SST	CG	N
0.120	3.05	70090	.25	6.4	.092	2.3	11	2.0	.13	3.3	1.5	6.6	.09	2.2	0.014	0.4	6.13	MW	CG	N
0.120	3.05	70090S	.25	6.4	.092	2.3	9.8	1.7	.10	2.5	.94	4.2	.09	2.2	0.014	0.4	6.13	SST	CG	N
0.120	3.05	70110	.25	6.4	.088	2.2	18	3.1	.11	2.9	2.0	8.8	.11	2.7	0.016	0.4	6.75	MW	CG	N
0.120	3.05	70110S	.25	6.4	.088	2.2	15	2.7	.09	2.2	1.3	5.9	.11	2.7	0.016	0.4	6.75	SST	CG	N
0.120	3.05	B3-56	.25	6.4	.088	2.2	15	2.6	.09	2.2	1.3	5.9	.11	2.8	0.016	0.4	6.88	SST	CG	N
0.120	3.05	70132	.25	6.4	.084	2.1	28	5.0	.10	2.5	2.8	12	.13	3.2	0.018	0.5	7.00	MW	CG	N
0.120	3.05	70132S	.25	6.4	.084	2.1	25	4.3	.08	1.9	1.9	8.3	.13	3.2	0.018	0.5	7.00	SST	CG	N
0.120	3.05	70153	.25	6.4	.080	2.0	46	8.1	.08	2.1	3.8	17	.14	3.6	0.020	0.5	7.00	MW	CG	N
0.120	3.05	70153S	.25	6.4	.080	2.0	40	7.0	.06	1.6	2.5	11	.14	3.6	0.020	0.5	7.00	SST	CG	N
0.120	3.05	70171	.25	6.4	.076	1.9	70	12	.07	1.8	5.0	22	.16	4.0	0.022	0.6	7.13	MW	CG	N
0.120	3.05	70171S	.25	6.4	.076	1.9	61	11	.05	1.4	3.3	15	.16	4.0	0.022	0.6	7.13	SST	CG	N
0.120	3.05	70190	.25	6.4	.072	1.8	108	19	.06	1.5	6.4	28	.17	4.3	0.024	0.6	7.00	MW	CG	N
0.120	3.05	70190S	.25	6.4	.072	1.8	94	16	.05	1.1	4.2	19	.17	4.3	0.024	0.6	7.00	SST	CG	N
0.120	3.05	70059	.31	7.9	.100	2.5	2.5	.43	.22	5.7	.55	2.4	.06	1.6	0.010	0.3	6.38	MW	CG	N
0.120	3.05	70059S	.31	7.9	.100	2.5	2.1	.38	.16	4.1	.35	1.6	.06	1.6	0.010	0.3	6.38	SST	CG	N
0.120	3.05	70075	.31	7.9	.096	2.4	5.0	.87	.19	4.8	.94	4.2	.08	2.1	0.012	0.3	6.75	MW	CG	N
0.120	3.05	70075S	.31	7.9	.096	2.4	4.3	.76	.14	3.5	.60	2.7	.08	2.1	0.012	0.3	6.75	SST	CG	N
0.120	3.05	70091	.31	7.9	.092	2.3	8.8	1.5	.17	4.3	1.5	6.6	.10	2.6	0.014	0.4	7.25	MW	CG	N
0.120	3.05	70091S	.31	7.9	.092	2.3	7.7	1.3	.12	3.1	.94	4.2	.10	2.6	0.014	0.4	7.25	SST	CG	N
0.120	3.05	70111	.31	7.9	.088	2.2	14	2.4	.14	3.6	2.0	8.8	.13	3.3	0.016	0.4	8.00	MW	CG	N
0.120	3.05	70111S	.31	7.9	.088	2.2	12	2.1	.11	2.8	1.3	5.9	.13	3.3	0.016	0.4	8.00	SST	CG	N
0.120	3.05	70133	.31	7.9	.084	2.1	22	3.8	.13	3.2	2.8	12	.15	3.9	0.018	0.5	8.50	MW	CG	N
0.120	3.05	70133S	.31	7.9	.084	2.1	19	3.3	.10	2.5	1.9	8.3	.15	3.9	0.018	0.5	8.50	SST	CG	N
0.120	3.05	70154	.31	7.9	.080	2.0	35	6.2	.11	2.7	3.8	17	.17	4.3	0.020	0.5	8.50	MW	CG	N
0.120	3.05	70154S	.31	7.9	.080	2.0	31	5.4	.08	2.1	2.5	11	.17	4.3	0.020	0.5	8.50	SST	CG	N
0.120	3.05	70172	.31	7.9	.076	1.9	54	9.5	.09	2.3	5.0	22	.19	4.8	0.022	0.6	8.63	MW	CG	N
0.120	3.05	70172S	.31	7.9	.076	1.9	47	8.2	.07	1.8	3.3	15	.19	4.8	0.022	0.6	8.63	SST	CG	N
0.120	3.05	70191	.31	7.9	.072	1.8	83	15	.08	1.9	6.4	28	.20	5.2	0.024	0.6	8.50	MW	CG	N
0.120	3.05	70191S	.31	7.9	.072	1.8	72	13	.06	1.5	4.2	19	.20	5.2	0.024	0.6	8.50	SST	CG	N
0.120	3.05	70060	.38	9.7	.100	2.5	2.0	.35	.27	7.0	.55	2.4	.07	1.9	0.010	0.3	7.38	MW	CG	N
0.120	3.05	70060S	.38	9.7	.100	2.5	1.7	.31	.20	5.1	.35	1.6	.07	1.9	0.010	0.3	7.38	SST	CG	N
0.120	3.05	70076	.38	9.7	.096	2.4	4.0	.71	.23	5.9	.94	4.2	.10	2.4	0.012	0.3	7.88	MW	CG	N
0.120	3.05	70076S	.38	9.7	.096	2.4	3.5	.61	.17	4.4	.60	2.7	.10	2.4	0.012	0.3	7.88	SST	CG	N
0.120	3.05	70092	.38	9.7	.092	2.3	7.0	1.2	.21	5.4	1.5	6.6	.12	3.1	0.014	0.4	8.63	MW	CG	N
0.120	3.05	70092S	.38	9.7	.092	2.3	6.1	1.1	.16	3.9	.94	4.2	.12	3.1	0.014	0.4	8.63	SST	CG	N
0.120	3.05	70112	.38	9.7	.088	2.2	11	2.0	.18	4.5	2.0	8.8	.15	3.9	0.016	0.4	9.50	MW	CG	N
0.120	3.05	70112S	.38	9.7	.088	2.2	9.7	1.7	.14	3.5	1.3	5.9	.15	3.9	0.016	0.4	9.50	SST	CG	N
0.120	3.05	70134	.38	9.7	.084	2.1	18	3.2	.15	3.9	2.8	12	.18	4.5	0.018	0.5	9.88	MW	CG	N
0.120	3.05	70134S	.38	9.7	.084	2.1	16	2.7	.12	3.0	1.9	8.3	.18	4.5	0.018	0.5	9.88	SST	CG	N
0.120	3.05	70155	.38	9.7	.080	2.0	28	5.0	.13	3.4	3.8	17	.20	5.2	0.020	0.5	10.1	MW	CG	N
0.120	3.05	70155S	.38	9.7	.080	2.0	25	4.3	.10	2.6	2.5	11	.20	5.2	0.020	0.5	10.1	SST	CG	N
0.120	3.05	70173	.38	9.7	.076	1.9	41	7.3	.12	3.0	5.0	22	.23	5.9	0.022	0.6	10.6	MW	CG	N
0.120	3.05	70173S	.38	9.7	.076	1.9	36	6.3	.09	2.3	3.3	15	.23	5.9	0.022	0.6	10.6	SST	CG	N
0.120	3.05	70192	.38	9.7	.072	1.8	65	11	.10	2.5	6.4	28	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.120	3.05	70192S	.38	9.7	.072	1.8	57	9.9	.07	1.9	4.2	19	.25	6.2	0.024	0.6	10.3	SST	CG	N
0.120	3.05	B3-57	.44	11.1	.092	2.3	5.8	1.0	.26	6.5	1.5	6.6	.14	3.6	0.014	0.4	10.0	MW	CG	N
0.120	3.05	70061	.44	11.2	.100	2.5	1.7	.30	.32	8.2	.55	2.4	.08	2.1	0.010	0.3	8.38	MW	CG	N
0.120	3.05	70061S	.44	11.2	.100	2.5	1.5	.26	.24	6.0	.35	1.6	.08	2.1	0.010	0.3	8.38	SST	CG	N
0.120	3.05	70077	.44	11.2	.096	2.4	3.4	.59	.28	7.1	.94	4.2	.11	2.7	0.012	0.3	9.00	MW	CG	N
0.120	3.05	70077S	.44	11.2	.096	2.4	2.9	.51	.20	5.2	.60	2.7	.11	2.7	0.012	0.3	9.00	SST	CG	N
0.120	3.05	70093	.44	11.2	.092	2.3	6.0	1.0	.25	6.3	1.5	6.6	.14	3.5	0.014	0.4	9.75	MW	CG	N
0.120	3.05	70093S	.44	11.2	.092	2.3	5.2	.91	.18	4.6	.94	4.2	.14	3.5	0.014	0.4	9.75	SST	CG	N
0.120	3.05	70113	.44	11.2	.088	2.2	9.4	1.7	.21	5.3	2.0	8.8	.17	4.4	0.016	0.4	10.9	MW	CG	N




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70078	.50	12.7	.096	2.4	3.0	.53	.31	8.0	.94	4.2	.12	3.0	0.012	0.3	9.88	MW	CG	N
0.120	3.05	70078S	.50	12.7	.096	2.4	2.6	.46	.23	5.8	.60	2.7	.12	3.0	0.012	0.3	9.88	SST	CG	N
0.120	3.05	70094	.50	12.7	.092	2.3	5.2	.91	.28	7.2	1.5	6.6	.15	3.9	0.014	0.4	10.9	MW	CG	N
0.120	3.05	70094S	.50	12.7	.092	2.3	4.5	.80	.21	5.3	.94	4.2	.15	3.9	0.014	0.4	10.9	SST	CG	N
0.120	3.05	70114	.50	12.7	.088	2.2	8.4	1.5	.24	6.0	2.0	8.8	.19	4.9	0.016	0.4	12.0	MW	CG	N
0.120	3.05	70114S	.50	12.7	.088	2.2	7.3	1.3	.18	4.6	1.3	5.9	.19	4.9	0.016	0.4	12.0	SST	CG	N
0.120	3.05	70136	.50	12.7	.084	2.1	13	2.3	.21	5.4	2.8	12	.23	5.9	0.018	0.5	12.9	MW	CG	N
0.120	3.05	70136S	.50	12.7	.084	2.1	11	2.0	.16	4.1	1.9	8.3	.23	5.9	0.018	0.5	12.9	SST	CG	N
0.120	3.05	70157	.50	12.7	.080	2.0	21	3.7	.18	4.6	3.8	17	.26	6.6	0.020	0.5	13.0	MW	CG	N
0.120	3.05	70157S	.50	12.7	.080	2.0	18	3.2	.14	3.5	2.5	11	.26	6.6	0.020	0.5	13.0	SST	CG	N
0.120	3.05	70175	.50	12.7	.076	1.9	31	5.4	.16	4.1	5.0	22	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.120	3.05	70175S	.50	12.7	.076	1.9	27	4.7	.12	3.1	3.3	15	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.120	3.05	70194	.50	12.7	.072	1.8	48	8.4	.13	3.4	6.4	28	.32	8.1	0.024	0.6	13.3	MW	CG	N
0.120	3.05	70194S	.50	12.7	.072	1.8	42	7.3	.10	2.6	4.2	19	.32	8.1	0.024	0.6	13.3	SST	CG	N
0.120	3.05	70063	.56	14.2	.100	2.5	1.4	.24	.39	10	.55	2.4	.10	2.5	0.010	0.3	9.75	MW	CG	N
0.120	3.05	70063S	.56	14.2	.100	2.5	1.2	.21	.29	7.3	.35	1.6	.10	2.5	0.010	0.3	9.75	SST	CG	N
0.120	3.05	70079	.56	14.2	.096	2.4	2.6	.45	.36	9.2	.94	4.2	.13	3.4	0.012	0.3	11.1	MW	CG	N
0.120	3.05	70079S	.56	14.2	.096	2.4	2.3	.39	.27	6.8	.60	2.7	.13	3.4	0.012	0.3	11.1	SST	CG	N
0.120	3.05	70095	.56	14.2	.092	2.3	4.6	.80	.32	8.2	1.5	6.6	.17	4.3	0.014	0.4	12.1	MW	CG	N
0.120	3.05	70095S	.56	14.2	.092	2.3	4.0	.70	.24	6.0	.94	4.2	.17	4.3	0.014	0.4	12.1	SST	CG	N
0.120	3.05	70115	.56	14.2	.088	2.2	7.4	1.3	.27	6.8	2.0	8.8	.21	5.4	0.016	0.4	13.4	MW	CG	N
0.120	3.05	70115S	.56	14.2	.088	2.2	6.4	1.1	.21	5.2	1.3	5.9	.21	5.4	0.016	0.4	13.4	SST	CG	N
0.120	3.05	70137	.56	14.2	.084	2.1	11	2.0	.24	6.2	2.8	12	.26	6.6	0.018	0.5	14.4	MW	CG	N
0.120	3.05	70137S	.56	14.2	.084	2.1	10	1.7	.19	4.7	1.9	8.3	.26	6.6	0.018	0.5	14.4	SST	CG	N
0.120	3.05	70158	.56	14.2	.080	2.0	18	3.2	.21	5.3	3.8	17	.29	7.4	0.020	0.5	14.6	MW	CG	N
0.120	3.05	70158S	.56	14.2	.080	2.0	16	2.8	.16	4.0	2.5	11	.29	7.4	0.020	0.5	14.6	SST	CG	N
0.120	3.05	70176	.56	14.2	.076	1.9	28	4.9	.18	4.5	5.0	22	.33	8.3	0.022	0.6	14.8	MW	CG	N
0.120	3.05	70176S	.56	14.2	.076	1.9	24	4.3	.14	3.4	3.3	15	.33	8.3	0.022	0.6	14.8	SST	CG	N
0.120	3.05	70195	.56	14.2	.072	1.8	42	7.4	.15	3.8	6.4	28	.35	9.0	0.024	0.6	14.8	MW	CG	N
0.120	3.05	70195S	.56	14.2	.072	1.8	37	6.4	.12	2.9	4.2	19	.35	9.0	0.024	0.6	14.8	SST	CG	N
0.120	3.05	70064	.63	16.0	.100	2.5	1.2	.21	.46	12	.55	2.4	.11	2.8	0.010	0.3	11.0	MW	CG	N
0.120	3.05	70064S	.63	16.0	.100	2.5	1.0	.18	.34	8.5	.35	1.6	.11	2.8	0.010	0.3	11.0	SST	CG	N
0.120	3.05	70080	.63	16.0	.096	2.4	2.4	.42	.39	10	.94	4.2	.14	3.6	0.012	0.3	11.9	MW	CG	N
0.120	3.05	70080S	.63	16.0	.096	2.4	2.1	.36	.29	7.3	.60	2.7	.14	3.6	0.012	0.3	11.9	SST	CG	N
0.120	3.05	70096	.63	16.0	.092	2.3	4.1	.72	.36	9.1	1.5	6.6	.19	4.7	0.014	0.4	13.3	MW	CG	N
0.120	3.05	70096S	.63	16.0	.092	2.3	3.6	.63	.26	6.7	.94	4.2	.19	4.7	0.014	0.4	13.3	SST	CG	N
0.120	3.05	70116	.63	16.0	.088	2.2	6.6	1.2	.30	7.7	2.0	8.8	.24	6.0	0.016	0.4	14.8	MW	CG	N
0.120	3.05	70116S	.63	16.0	.088	2.2	5.7	1.0	.23	5.9	1.3	5.9	.24	6.0	0.016	0.4	14.8	SST	CG	N
0.120	3.05	70138	.63	16.0	.084	2.1	11	1.9	.26	6.6	2.8	12	.27	6.9	0.018	0.5	15.1	MW	CG	N
0.120	3.05	70138S	.63	16.0	.084	2.1	9.4	1.6	.20	5.0	1.9	8.3	.27	6.9	0.018	0.5	15.1	SST	CG	N
0.120	3.05	70159	.63	16.0	.080	2.0	16	2.9	.23	5.9	3.8	17	.32	8.2	0.020	0.5	16.1	MW	CG	N
0.120	3.05	70159S	.63	16.0	.080	2.0	14	2.5	.18	4.5	2.5	11	.32	8.2	0.020	0.5	16.1	SST	CG	N
0.120	3.05	70177	.63	16.0	.076	1.9	25	4.4	.20	5.1	5.0	22	.36	9.1	0.022	0.6	16.4	MW	CG	N
0.120	3.05	70177S	.63	16.0	.076	1.9	22	3.8	.15	3.9	3.3	15	.36	9.1	0.022	0.6	16.4	SST	CG	N
0.120	3.05	70196	.63	16.0	.072	1.8	38	6.6	.17	4.3	6.4	28	.39	10.0	0.024	0.6	16.4	MW	CG	N
0.120	3.05	70196S	.63	16.0	.072	1.8	33	5.7	.13	3.3	4.2	19	.39	10.0	0.024	0.6	16.4	SST	CG	N
0.120	3.05	70065	.69	17.5	.100	2.5	1.1	.19	.50	13	.55	2.4	.12	3.0	0.010	0.3	11.9	MW	CG	N
0.120	3.05	70065S	.69	17.5	.100	2.5	.95	.17	.37	9.4	.35	1.6	.12	3.0	0.010	0.3	11.9	SST	CG	N
0.120	3.05	70081	.69	17.5	.096	2.4	2.1	.37	.45	11	.94	4.2	.16	4.0	0.012	0.3	13.3	MW	CG	N
0.120	3.05	70081S	.69	17.5	.096	2.4	1.8	.32	.33	8.3	.60	2.7	.16	4.0	0.012	0.3	13.3	SST	CG	N
0.120	3.05	70097	.69	17.5	.092	2.3	3.7	.66	.40	10	1.5	6.6	.20	5.1	0.014	0.4	14.4	MW	CG	N
0.120	3.05	70097S	.69	17.5	.092	2.3	3.3	.57	.29	7.4	.94	4.2	.20	5.1	0.014	0.4	14.4	SST	CG	N
0.120	3.05	70117	.69	17.5	.088	2.2	5.9	1.0	.34	8.6	2.0	8.8	.26	6.6	0.016	0.4	16.3	MW	CG	N
0.120	3.05	70117S	.69	17.5	.088	2.2	5.1	.90	.26	6.6	1.3	5.9	.26	6.6	0.016	0.4	16.3	SST	CG	N
0.120	3.05	70139	.69	17.5	.084	2.1	9.4	1.6	.30	7.5	2.8	12	.31	7.8	0.018	0.5	17.1	MW	CG	N
0.120	3.05	70139S	.69	17.5	.084	2.1	8.2	1.4	.23	5.8	1.9	8.3	.31	7.8	0.018	0.5	17.1	SST	CG	N
0.120	3.05	70160	.69	17.5	.080	2.0	15	2.6	.26	6.5	3.8	17	.35	9.0	0.020	0.5	17.6	MW	CG	N
0.120	3.05	70160S	.69	17.5	.080	2.0	13	2.2	.20	5.0	2.5	11	.35	9.0	0.020	0.5	17.6	SST	CG	N
0.120	3.05	70178	.69	17.5	.076	1.9	22	3.8	.23	5.9	5.0	22	.41	10.4	0.022	0.6	18.6	MW	CG	N
0.120	3.05	70178S	.69	17.5	.076	1.9	19	3.3	.18	4.5	3.3	15	.41	10.4	0.022	0.6	18.6	SST	CG	N
0.120	3.05	70197	.69	17.5	.072	1.8	34	5.9	.19	4.8	6.4	28	.43	11.0	0.024	0.6	18.0	MW	CG	N
0.120	3.05	70197S	.69	17.5	.072	1.8	29	5.1	.14	3.7	4.2	19	.43	11.0	0.024	0.6	18.0	SST	CG	N
0.120	3.05	70066	.75	19.1	.100	2.5	1.0	.18	.55	14	.55	2.4	.13	3.3	0.010	0.3	12.8	MW	CG	N
0.120	3.05	70066S	.75	19.1	.100	2.5	.87	.15	.40	10	.35	1.6	.13	3.3	0.010	0.3	12.8	SST	CG	N
0.120	3.05	70082	.75	19.1	.096	2.4	2.0	.35	.47	12	.94	4.2	.17	4.2	0.012	0.3	13.9	MW	CG	N
0.120	3.05	70082S	.75	19.1	.096	2.4	1.7	.30	.35	8.8	.60	2.7	.17	4.2	0.012	0.3	13.9	SST	CG	N
0.120	3.05	70098	.75	19.1	.092	2.3	3.4	.60	.44	11	1.5	6.6	.22	5.6	0.014	0.4	15.6	MW	CG	N
0.120	3.05	70098S	.75	19.1	.092	2.3	3.0	.52	.32	8.1	.94	4.2	.22	5.6	0.014	0.4	15.6	SST	CG	N
0.120	3.05	7011																		




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70083	.81	20.6	.096	2.4	1.8	.32	.52	13	.94	4.2	.18	4.6	0.012	0.3	15.1	MW	CG	N
0.120	3.05	70083S	.81	20.6	.096	2.4	1.6	.27	.38	9.7	.60	2.7	.18	4.6	0.012	0.3	15.1	SST	CG	N
0.120	3.05	70099	.81	20.6	.092	2.3	3.1	.54	.48	12	1.5	6.6	.24	6.0	0.014	0.4	17.0	MW	CG	N
0.120	3.05	70099S	.81	20.6	.092	2.3	2.7	.47	.35	8.9	.94	4.2	.24	6.0	0.014	0.4	17.0	SST	CG	N
0.120	3.05	70120	.81	20.6	.088	2.2	5.0	.88	.40	10	2.0	8.8	.30	7.6	0.016	0.4	18.8	MW	CG	N
0.120	3.05	70120S	.81	20.6	.088	2.2	4.3	.76	.30	7.7	1.3	5.9	.30	7.6	0.016	0.4	18.8	SST	CG	N
0.120	3.05	70142	.81	20.6	.084	2.1	7.9	1.4	.35	9.0	2.8	12	.36	9.1	0.018	0.5	20.0	MW	CG	N
0.120	3.05	70142S	.81	20.6	.084	2.1	6.9	1.2	.27	6.9	1.9	8.3	.36	9.1	0.018	0.5	20.0	SST	CG	N
0.120	3.05	70162	.81	20.6	.080	2.0	12	2.2	.31	7.8	3.8	17	.41	10.5	0.020	0.5	20.6	MW	CG	N
0.120	3.05	70162S	.81	20.6	.080	2.0	11	1.9	.23	6.0	2.5	11	.41	10.5	0.020	0.5	20.6	SST	CG	N
0.120	3.05	70180	.81	20.6	.076	1.9	18	3.2	.27	6.9	5.0	22	.47	12.0	0.022	0.6	21.5	MW	CG	N
0.120	3.05	70180S	.81	20.6	.076	1.9	16	2.8	.21	5.3	3.3	15	.47	12.0	0.022	0.6	21.5	SST	CG	N
0.120	3.05	70199	.81	20.6	.072	1.8	28	5.0	.22	5.7	6.4	28	.50	12.8	0.024	0.6	21.0	MW	CG	N
0.120	3.05	70199S	.81	20.6	.072	1.8	25	4.3	.17	4.4	4.2	19	.50	12.8	0.024	0.6	21.0	SST	CG	N
0.120	3.05	70068	.88	22.4	.100	2.5	.90	.16	.61	16	.55	2.4	.14	3.6	0.010	0.3	14.0	MW	CG	N
0.120	3.05	70068S	.88	22.4	.100	2.5	.78	.14	.45	11	.35	1.6	.14	3.6	0.010	0.3	14.0	SST	CG	N
0.120	3.05	70084	.88	22.4	.096	2.4	1.7	.30	.55	14	.94	4.2	.19	4.9	0.012	0.3	15.9	MW	CG	N
0.120	3.05	70084S	.88	22.4	.096	2.4	1.5	.26	.40	10	.60	2.7	.19	4.9	0.012	0.3	15.9	SST	CG	N
0.120	3.05	70100	.88	22.4	.092	2.3	2.9	.51	.51	13	1.5	6.6	.25	6.4	0.014	0.4	18.0	MW	CG	N
0.120	3.05	70100S	.88	22.4	.092	2.3	2.5	.44	.37	9.5	.94	4.2	.25	6.4	0.014	0.4	18.0	SST	CG	N
0.120	3.05	70122	.88	22.4	.088	2.2	4.6	.80	.43	11	2.0	8.8	.32	8.2	0.016	0.4	20.3	MW	CG	N
0.120	3.05	70122S	.88	22.4	.088	2.2	4.0	.70	.33	8.4	1.3	5.9	.32	8.2	0.016	0.4	20.3	SST	CG	N
0.120	3.05	70144	.88	22.4	.084	2.1	7.3	1.3	.38	9.7	2.8	12	.39	9.8	0.018	0.5	21.5	MW	CG	N
0.120	3.05	70144S	.88	22.4	.084	2.1	6.3	1.1	.29	7.4	1.9	8.3	.39	9.8	0.018	0.5	21.5	SST	CG	N
0.120	3.05	70163	.88	22.4	.080	2.0	11	2.0	.34	8.6	3.8	17	.45	11.4	0.020	0.5	22.5	MW	CG	N
0.120	3.05	70163S	.88	22.4	.080	2.0	9.8	1.7	.26	6.6	2.5	11	.45	11.4	0.020	0.5	22.5	SST	CG	N
0.120	3.05	70182	.88	22.4	.076	1.9	17	3.0	.29	7.4	5.0	22	.50	12.8	0.022	0.6	22.9	MW	CG	N
0.120	3.05	70182S	.88	22.4	.076	1.9	15	2.6	.22	5.6	3.3	15	.50	12.8	0.022	0.6	22.9	SST	CG	N
0.120	3.05	70200	.88	22.4	.072	1.8	26	4.5	.24	6.2	6.4	28	.55	13.9	0.024	0.6	22.8	MW	CG	N
0.120	3.05	70200S	.88	22.4	.072	1.8	23	4.0	.19	4.8	4.2	19	.55	13.9	0.024	0.6	22.8	SST	CG	N
0.120	3.05	70101	.91	23.1	.092	2.3	8.6	1.5	.17	4.4	1.5	6.6	.10	2.6	0.014	0.4	7.38	MW	CG	N
0.120	3.05	70101S	.91	23.1	.092	2.3	7.5	1.3	.13	3.2	.94	4.2	.10	2.6	0.014	0.4	7.38	SST	CG	N
0.120	3.05	70069	.94	23.9	.100	2.5	.80	.14	.69	17	.55	2.4	.16	3.9	0.010	0.3	15.5	MW	CG	N
0.120	3.05	70069S	.94	23.9	.100	2.5	.70	.12	.50	13	.35	1.6	.16	3.9	0.010	0.3	15.5	SST	CG	N
0.120	3.05	70085	.94	23.9	.096	2.4	1.5	.26	.63	16	.94	4.2	.21	5.4	0.012	0.3	17.8	MW	CG	N
0.120	3.05	70085S	.94	23.9	.096	2.4	1.3	.23	.46	12	.60	2.7	.21	5.4	0.012	0.3	17.8	SST	CG	N
0.120	3.05	70102	.94	23.9	.092	2.3	2.7	.47	.55	14	1.5	6.6	.27	6.8	0.014	0.4	19.1	MW	CG	N
0.120	3.05	70102S	.94	23.9	.092	2.3	2.4	.41	.40	10	.94	4.2	.27	6.8	0.014	0.4	19.1	SST	CG	N
0.120	3.05	70124	.94	23.9	.088	2.2	4.3	.75	.46	12	2.0	8.8	.34	8.7	0.016	0.4	21.5	MW	CG	N
0.120	3.05	70124S	.94	23.9	.088	2.2	3.7	.65	.35	9.0	1.3	5.9	.34	8.7	0.016	0.4	21.5	SST	CG	N
0.120	3.05	70146	.94	23.9	.084	2.1	6.8	1.2	.41	10	2.8	12	.41	10.5	0.018	0.5	22.9	MW	CG	N
0.120	3.05	70146S	.94	23.9	.084	2.1	5.9	1.0	.31	8.0	1.9	8.3	.41	10.5	0.018	0.5	22.9	SST	CG	N
0.120	3.05	70164	.94	23.9	.080	2.0	11	1.9	.36	9.1	3.8	17	.48	12.1	0.020	0.5	23.8	MW	CG	N
0.120	3.05	70164S	.94	23.9	.080	2.0	9.2	1.6	.27	7.0	2.5	11	.48	12.1	0.020	0.5	23.8	SST	CG	N
0.120	3.05	70183	.94	23.9	.076	1.9	16	2.8	.31	8.0	5.0	22	.54	13.8	0.022	0.6	24.6	MW	CG	N
0.120	3.05	70183S	.94	23.9	.076	1.9	14	2.4	.24	6.1	3.3	15	.54	13.8	0.022	0.6	24.6	SST	CG	N
0.120	3.05	70201	.94	23.9	.072	1.8	24	4.3	.26	6.6	6.4	28	.58	14.7	0.024	0.6	24.1	MW	CG	N
0.120	3.05	70201S	.94	23.9	.072	1.8	21	3.7	.20	5.1	4.2	19	.58	14.7	0.024	0.6	24.1	SST	CG	N
0.120	3.05	70070	1.00	25.4	.100	2.5	.70	.12	.78	20	.55	2.4	.17	4.4	0.010	0.3	17.4	MW	CG	N
0.120	3.05	70070S	1.00	25.4	.100	2.5	.61	.11	.57	15	.35	1.6	.17	4.4	0.010	0.3	17.4	SST	CG	N
0.120	3.05	70086	1.00	25.4	.096	2.4	1.5	.26	.63	16	.94	4.2	.21	5.4	0.012	0.3	17.8	MW	CG	N
0.120	3.05	70086S	1.00	25.4	.096	2.4	1.3	.23	.46	12	.60	2.7	.21	5.4	0.012	0.3	17.8	SST	CG	N
0.120	3.05	70103	1.00	25.4	.092	2.3	2.5	.44	.59	15	1.5	6.6	.29	7.3	0.014	0.4	20.5	MW	CG	N
0.120	3.05	70103S	1.00	25.4	.092	2.3	2.2	.38	.43	11	.94	4.2	.29	7.3	0.014	0.4	20.5	SST	CG	N
0.120	3.05	70125	1.00	25.4	.088	2.2	4.1	.71	.49	12	2.0	8.8	.36	9.2	0.016	0.4	22.6	MW	CG	N
0.120	3.05	70125S	1.00	25.4	.088	2.2	3.5	.62	.37	9.5	1.3	5.9	.36	9.2	0.016	0.4	22.6	SST	CG	N
0.120	3.05	70147	1.00	25.4	.084	2.1	6.4	1.1	.44	11	2.8	12	.44	11.1	0.018	0.5	24.3	MW	CG	N
0.120	3.05	70147S	1.00	25.4	.084	2.1	5.6	.97	.33	8.5	1.9	8.3	.44	11.1	0.018	0.5	24.3	SST	CG	N
0.120	3.05	70165	1.00	25.4	.080	2.0	9.9	1.7	.38	9.7	3.8	17	.51	12.8	0.020	0.5	25.3	MW	CG	N
0.120	3.05	70165S	1.00	25.4	.080	2.0	8.6	1.5	.29	7.4	2.5	11	.51	12.8	0.020	0.5	25.3	SST	CG	N
0.120	3.05	70184	1.00	25.4	.076	1.9	15	2.6	.34	8.5	5.0	22	.58	14.6	0.022	0.6	26.1	MW	CG	N
0.120	3.05	70184S	1.00	25.4	.076	1.9	13	2.3	.26	6.5	3.3	15	.58	14.6	0.022	0.6	26.1	SST	CG	N
0.120	3.05	70202	1.00	25.4	.072	1.8	23	4.0	.28	7.1	6.4	28	.62	15.7	0.024	0.6	25.8	MW	CG	N
0.120	3.05	70202S	1.00	25.4	.072	1.8	20	3.5	.21	5.4	4.2	19	.62	15.7	0.024	0.6	25.8	SST	CG	N
0.120	3.05	70071	1.13	28.7	.100	2.5	.70	.12	.78	20	.55	2.4	.17	4.4	0.010	0.3	17.4	MW	CG	N
0.120	3.05	70071S	1.13	28.7	.100	2.5	.61	.11	.57	15	.35	1.6	.17	4.4	0.010	0.3	17.4	SST	CG	N
0.120	3.05	70087	1.13	28.7	.096	2.4	1.3	.23	.73	18	.94	4.2	.24	6.2	0.012	0.3	20.3	MW	CG	N
0.120	3.05	70087S	1.13	28.7	.096	2.4	1.1	.20	.53	14	.60	2.7	.24	6.2	0.012	0.3	20.3	SST	CG	N




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70072	1.25	31.8	.100	2.5	.60	.11	.92	23	.55	2.4	.20	5.1	0.010	0.3	20.0	MW	CG	N
0.120	3.05	70072S	1.25	31.8	.100	2.5	.52	.09	.67	17	.35	1.6	.20	5.1	0.010	0.3	20.0	SST	CG	N
0.120	3.05	70088	1.25	31.8	.096	2.4	1.2	.21	.79	20	.94	4.2	.26	6.6	0.012	0.3	21.8	MW	CG	N
0.120	3.05	70088S	1.25	31.8	.096	2.4	1.0	.18	.58	15	.60	2.7	.26	6.6	0.012	0.3	21.8	SST	CG	N
0.120	3.05	70105	1.25	31.8	.092	2.3	2.0	.35	.74	19	1.5	6.6	.35	8.9	0.014	0.4	25.1	MW	CG	N
0.120	3.05	70105S	1.25	31.8	.092	2.3	1.7	.31	.54	14	.94	4.2	.35	8.9	0.014	0.4	25.1	SST	CG	N
0.120	3.05	70127	1.25	31.8	.088	2.2	3.2	.56	.62	16	2.0	8.8	.45	11.4	0.016	0.4	28.1	MW	CG	N
0.120	3.05	70127S	1.25	31.8	.088	2.2	2.8	.49	.47	12	1.3	5.9	.45	11.4	0.016	0.4	28.1	SST	CG	N
0.120	3.05	70149	1.25	31.8	.084	2.1	5.1	.89	.55	14	2.8	12	.54	13.8	0.018	0.5	30.1	MW	CG	N
0.120	3.05	70149S	1.25	31.8	.084	2.1	4.4	.77	.42	11	1.9	8.3	.54	13.8	0.018	0.5	30.1	SST	CG	N
0.120	3.05	70167	1.25	31.8	.080	2.0	7.9	1.4	.48	12	3.8	17	.62	15.8	0.020	0.5	31.1	MW	CG	N
0.120	3.05	70167S	1.25	31.8	.080	2.0	6.9	1.2	.37	9.3	2.5	11	.62	15.8	0.020	0.5	31.1	SST	CG	N
0.120	3.05	70186	1.25	31.8	.076	1.9	12	2.1	.42	11	5.0	22	.72	18.2	0.022	0.6	32.5	MW	CG	N
0.120	3.05	70186S	1.25	31.8	.076	1.9	10	1.8	.32	8.2	3.3	15	.72	18.2	0.022	0.6	32.5	SST	CG	N
0.120	3.05	70204	1.25	31.8	.072	1.8	18	3.1	.35	9.0	6.4	28	.77	19.5	0.024	0.6	32.0	MW	CG	N
0.120	3.05	70204S	1.25	31.8	.072	1.8	16	2.7	.27	6.9	4.2	19	.77	19.5	0.024	0.6	32.0	SST	CG	N
0.120	3.05	70107	1.38	35.1	.092	2.3	1.8	.32	.82	21	1.5	6.6	.39	9.9	0.014	0.4	27.8	MW	CG	N
0.120	3.05	70107S	1.38	35.1	.092	2.3	1.6	.27	.60	15	.94	4.2	.39	9.9	0.014	0.4	27.8	SST	CG	N
0.120	3.05	70129	1.38	35.1	.088	2.2	2.9	.51	.68	17	2.0	8.8	.49	12.5	0.016	0.4	30.9	MW	CG	N
0.120	3.05	70129S	1.38	35.1	.088	2.2	2.5	.44	.52	13	1.3	5.9	.49	12.5	0.016	0.4	30.9	SST	CG	N
0.120	3.05	70151	1.38	35.1	.084	2.1	4.6	.81	.61	15	2.8	12	.59	15.0	0.018	0.5	32.9	MW	CG	N
0.120	3.05	70151S	1.38	35.1	.084	2.1	4.0	.70	.46	12	1.9	8.3	.59	15.0	0.018	0.5	32.9	SST	CG	N
0.120	3.05	70169	1.38	35.1	.080	2.0	7.0	1.2	.54	14	3.8	17	.70	17.7	0.020	0.5	34.9	MW	CG	N
0.120	3.05	70169S	1.38	35.1	.080	2.0	6.1	1.1	.41	11	2.5	11	.70	17.7	0.020	0.5	34.9	SST	CG	N
0.120	3.05	70188	1.38	35.1	.076	1.9	11	1.9	.47	12	5.0	22	.78	19.8	0.022	0.6	35.5	MW	CG	N
0.120	3.05	70188S	1.38	35.1	.076	1.9	9.3	1.6	.36	9.0	3.3	15	.78	19.8	0.022	0.6	35.5	SST	CG	N
0.120	3.05	70073	1.50	38.1	.100	2.5	.50	.09	1.1	28	.55	2.4	.24	6.0	0.010	0.3	23.6	MW	CG	N
0.120	3.05	70073S	1.50	38.1	.100	2.5	.43	.08	.81	20	.35	1.6	.24	6.0	0.010	0.3	23.6	SST	CG	N
0.120	3.05	70089	1.50	38.1	.096	2.4	1.0	.18	.94	24	.94	4.2	.31	7.8	0.012	0.3	25.6	MW	CG	N
0.120	3.05	70089S	1.50	38.1	.096	2.4	.87	.15	.69	17	.60	2.7	.31	7.8	0.012	0.3	25.6	SST	CG	N
0.120	3.05	70108	1.50	38.1	.092	2.3	1.7	.30	.85	22	1.5	6.6	.40	10.2	0.014	0.4	28.8	MW	CG	N
0.120	3.05	70108S	1.50	38.1	.092	2.3	1.5	.26	.63	16	.94	4.2	.40	10.2	0.014	0.4	28.8	SST	CG	N
0.120	3.05	70130	1.50	38.1	.088	2.2	2.7	.48	.72	18	2.0	8.8	.52	13.2	0.016	0.4	32.5	MW	CG	N
0.120	3.05	70130S	1.50	38.1	.088	2.2	2.4	.42	.55	14	1.3	5.9	.52	13.2	0.016	0.4	32.5	SST	CG	N
0.120	3.05	70152	1.50	38.1	.084	2.1	4.2	.73	.67	17	2.8	12	.65	16.6	0.018	0.5	36.3	MW	CG	N
0.120	3.05	70152S	1.50	38.1	.084	2.1	3.6	.63	.51	13	1.9	8.3	.65	16.6	0.018	0.5	36.3	SST	CG	N
0.120	3.05	70170	1.50	38.1	.080	2.0	6.5	1.1	.59	15	3.8	17	.75	19.1	0.020	0.5	37.6	MW	CG	N
0.120	3.05	70170S	1.50	38.1	.080	2.0	5.6	.98	.45	11	2.5	11	.75	19.1	0.020	0.5	37.6	SST	CG	N
0.120	3.05	70189	1.50	38.1	.076	1.9	9.7	1.7	.51	13	5.0	22	.86	21.7	0.022	0.6	38.9	MW	CG	N
0.120	3.05	70189S	1.50	38.1	.076	1.9	8.4	1.5	.39	10	3.3	15	.86	21.7	0.022	0.6	38.9	SST	CG	N
0.120	3.05	70205	1.50	38.1	.072	1.8	15	2.6	.43	11	6.4	28	.92	23.2	0.024	0.6	38.1	MW	CG	N
0.120	3.05	70205S	1.50	38.1	.072	1.8	13	2.3	.33	8.3	4.2	19	.92	23.2	0.024	0.6	38.1	SST	CG	N
0.125	3.18	DD-65	.13	3.2	.105	2.7	3.2	.55	.08	1.9	.24	1.1	.05	1.3	0.010	0.3	5.00	MW	CG	GI
0.125	3.18	10195	.13	3.2	.095	2.4	36	6.4	.04	1.1	1.6	7.0	.07	1.7	0.015	0.4	3.50	MW	C	N
0.125	3.18	LL-57	.16	4.0	.085	2.2	99	17	.04	.93	3.7	16	.10	2.5	0.020	0.5	4.00	MW	C	N
0.125	3.18	DD-57	.19	4.8	.095	2.4	11	1.9	.08	1.9	.81	3.6	.11	2.9	0.015	0.4	6.50	SST	C	N
0.125	3.18	B14-3	.19	4.8	.087	2.2	52	9.2	.06	1.5	3.2	14	.11	2.9	0.019	0.5	5.00	MW	C	N
0.125	3.18	B-83	.19	4.8	.085	2.2	66	12	.06	1.4	3.7	16	.12	3.0	0.020	0.5	5.00	MW	C	N
0.125	3.18	N-4	.22	5.6	.111	2.8	.35	.06	.16	4.0	.05	.24	.06	1.6	0.007	0.2	8.00	MW	C	N
0.125	3.18	S-1576	.22	5.6	.109	2.8	.65	.11	.16	3.9	.10	.45	.06	1.6	0.008	0.2	7.00	SST	C	N
0.125	3.18	B15-7	.22	5.6	.104	2.6	1.9	.34	.12	3.2	.24	1.1	.09	2.4	0.011	0.3	8.00	MW	C	N
0.125	3.18	DD-1	.22	5.6	.097	2.5	6.5	1.1	.10	2.5	.65	2.9	.12	3.0	0.014	0.4	7.50	SST	C	N
0.125	3.18	MM-80	.22	5.6	.097	2.5	10	1.8	.09	2.3	.91	4.0	.09	2.3	0.014	0.4	5.50	SST	C	N
0.125	3.18	B7-3	.22	5.6	.097	2.5	13	2.4	.11	2.7	1.4	6.3	.08	2.1	0.014	0.4	5.00	MW	C	N
0.125	3.18	A10-4	.22	5.6	.075	1.9	112	20	.04	1.1	4.9	22	.18	4.4	0.025	0.6	7.00	MW	CG	N
0.125	3.18	A12-9	.25	6.4	.107	2.7	1.0	.18	.17	4.3	.17	.76	.08	2.1	0.009	0.2	8.00	MW	C	Z
0.125	3.18	BB-49	.25	6.4	.105	2.7	1.2	.21	.14	3.6	.17	.74	.11	2.8	0.010	0.3	10.0	MW	C	N
0.125	3.18	B1-25	.25	6.4	.095	2.4	12	2.1	.13	3.3	1.6	7.0	.10	2.5	0.015	0.4	6.50	MW	CG	GI
0.125	3.18	B1-8	.25	6.4	.093	2.4	16	2.8	.12	3.0	1.9	8.5	.10	2.6	0.016	0.4	6.50	MW	CG	N
0.125	3.18	FF-43	.25	6.4	.093	2.4	12	2.1	.11	2.8	1.3	5.7	.14	3.5	0.016	0.4	7.50	SST	C	N
0.125	3.18	S-834	.25	6.4	.093	2.4	10	1.8	.10	2.6	1.1	4.8	.15	3.7	0.016	0.4	8.13	SST	C	N
0.125	3.18	B5-53	.25	6.4	.091	2.3	22	3.9	.10	2.6	2.3	10	.12	3.1	0.017	0.4	6.25	MW	C	N
0.125	3.18	2628	.25	6.4	.089	2.3	23	4.1	.10	2.6	2.4	11	.15	3.8	0.018	0.5	7.50	MW	C	Z
0.125	3.18	B1-20	.25	6.4	.089	2.3	21	3.6	.09	2.2	1.8	8.0	.13	3.3	0.018	0.5	7.25	SST	CG	N
0.125	3.18	M-14	.25	6.4	.087	2.2	23	4.0	.09	2.3	2.1	9.3	.15	3.9	0.019	0.5	8.00	SST	CG	N
0.125	3.18	B5-3	.25	6.4	.087	2.2	30	5.2	.11	2.7	3.2	14	.14	3.5	0.019	0.5	7.25	MW	CG	N
0.125	3.18	10814	.25	6.4	.085	2.2	39	6.9	.06	1.6	2.4	11	.15	3.8	0.020	0.5	6.50	SST	C	N
0.125	3.18	J-68	.25	6.4	.085	2.2	31	5.5	.10	2.5	3.1	14	.15	3.9	0.020	0.5	7.00	MW	C	Z
0.125	3.18	KK-27	.25	6.4																




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	B1-14	.31	7.9	.091	2.3	16	2.8	.14	3.6	2.3	10	.14	3.5	0.017	0.4	8.00	MW	CG	GI
0.125	3.18	G-66	.31	7.9	.091	2.3	14	2.5	.15	3.7	2.1	9.2	.17	4.2	0.017	0.4	8.75	MW	C	Z
0.125	3.18	U-79	.31	7.9	.091	2.3	11	1.9	.11	2.7	1.1	5.1	.20	5.2	0.017	0.4	11.0	MW	C	N
0.125	3.18	A13-23	.31	7.9	.089	2.3	16	2.8	.11	2.8	1.8	8.0	.18	4.5	0.018	0.5	8.75	SST	C	N
0.125	3.18	L-91	.31	7.9	.083	2.1	41	7.3	.10	2.6	4.2	19	.19	4.8	0.021	0.5	8.00	MW	C	GI
0.125	3.18	L-1	.31	7.9	.081	2.1	49	8.6	.10	2.5	4.8	21	.20	5.2	0.022	0.6	8.25	MW	C	N
0.125	3.18	TT-3	.31	7.9	.081	2.1	45	7.8	.07	1.8	3.2	14	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.125	3.18	NN-60	.31	7.9	.077	2.0	93	16	.07	1.7	6.2	27	.17	4.3	0.024	0.6	7.00	MW	C	N
0.125	3.18	KK-18	.31	7.9	.075	1.9	81	14	.05	1.4	4.4	19	.23	5.7	0.025	0.6	8.00	SST	C	N
0.125	3.18	3196	.34	8.7	.101	2.6	3.9	.68	.23	5.9	.91	4.0	.10	2.5	0.012	0.3	7.33	MW	C	Z
0.125	3.18	FF-86	.34	8.7	.101	2.6	2.8	.48	.22	5.5	.60	2.7	.13	3.2	0.012	0.3	9.50	MW	C	N
0.125	3.18	V-69	.34	8.7	.095	2.4	5.5	.96	.16	4.1	.89	4.0	.18	4.6	0.015	0.4	12.0	MW	CG	N
0.125	3.18	N-16	.34	8.7	.093	2.4	12	2.1	.16	4.0	1.9	8.5	.14	3.7	0.016	0.4	8.00	MW	C	N
0.125	3.18	B6-5	.34	8.7	.085	2.2	22	3.9	.11	2.8	2.4	11	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.125	3.18	G-18	.34	8.7	.083	2.1	45	7.9	.09	2.4	4.2	19	.18	4.5	0.021	0.5	7.50	MW	C	N
0.125	3.18	A13-21	.34	8.7	.079	2.0	50	8.7	.07	1.8	3.6	16	.22	5.7	0.023	0.6	8.75	SST	C	N
0.125	3.18	B-57	.34	8.7	.073	1.9	113	20	.06	1.6	7.3	32	.23	5.9	0.026	0.7	8.00	MW	C	N
0.125	3.18	L-11	.38	9.5	.099	2.5	2.7	.47	.21	5.4	.57	2.5	.16	4.1	0.013	0.3	11.5	SST	C	N
0.125	3.18	II-94	.38	9.5	.095	2.4	6.8	1.2	.15	3.9	1.1	4.7	.15	3.8	0.015	0.4	10.0	SST	C	N
0.125	3.18	U-9	.38	9.5	.095	2.4	6.8	1.2	.23	5.7	1.5	6.8	.15	3.8	0.015	0.4	10.0	MW	CG	N
0.125	3.18	O-15	.38	9.5	.093	2.4	10	1.8	.18	4.7	1.9	8.5	.16	4.1	0.016	0.4	9.00	MW	C	N
0.125	3.18	A11-11	.38	9.5	.091	2.3	11	1.9	.14	3.6	1.5	6.7	.17	4.3	0.017	0.4	10.0	SST	CG	N
0.125	3.18	O-7	.38	9.5	.091	2.3	13	2.2	.18	4.6	2.3	10	.18	4.5	0.017	0.4	9.50	MW	C	N
0.125	3.18	B1-27	.38	9.5	.089	2.3	13	2.3	.14	3.4	1.8	8.0	.18	4.7	0.018	0.5	10.3	SST	CG	N
0.125	3.18	G-15	.38	9.5	.089	2.3	14	2.4	.16	4.0	2.2	9.7	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.125	3.18	H-98	.38	9.5	.085	2.2	22	3.8	.11	2.9	2.4	11	.22	5.6	0.020	0.5	10.0	SST	C	N
0.125	3.18	Q-93	.38	9.5	.085	2.2	17	2.9	.08	1.9	1.2	5.5	.30	7.6	0.020	0.5	14.0	MW	C	GI
0.125	3.18	UU-14	.38	9.5	.085	2.2	33	5.8	.11	2.8	3.7	16	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.125	3.18	DD-69	.38	9.5	.081	2.1	34	6.0	.13	3.4	4.6	20	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.125	3.18	LL-5	.38	9.5	.081	2.1	38	6.7	.08	2.1	3.2	14	.22	5.6	0.022	0.6	9.00	SST	C	N
0.125	3.18	S-700	.38	9.5	.081	2.1	33	5.9	.10	2.4	3.2	14	.24	6.1	0.022	0.6	10.0	SST	C	N
0.125	3.18	A12-7	.38	9.5	.079	2.0	54	9.5	.10	2.6	5.5	24	.23	5.8	0.023	0.6	9.00	MW	C	N
0.125	3.18	10172	.38	9.5	.077	2.0	56	9.8	.11	2.8	6.2	27	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.125	3.18	G-5	.38	9.5	.075	1.9	102	18	.06	1.6	6.5	29	.21	5.4	0.025	0.6	7.50	MW	C	BO
0.125	3.18	NN-85	.38	9.5	.075	1.9	70	12	.06	1.6	4.4	19	.23	5.7	0.025	0.6	9.00	SST	CG	N
0.125	3.18	N-14	.41	10.3	.095	2.4	7.8	1.4	.20	5.1	1.6	7.0	.15	3.8	0.015	0.4	9.00	MW	C	N
0.125	3.18	M-113	.41	10.3	.091	2.3	11	1.9	.20	5.1	2.1	9.5	.20	5.2	0.017	0.4	11.0	MW	C	N
0.125	3.18	B-60	.41	10.3	.089	2.3	14	2.4	.19	4.8	2.6	12	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.125	3.18	B-82	.41	10.3	.089	2.3	14	2.4	.20	5.0	2.7	12	.20	5.0	0.018	0.5	11.0	MW	CG	GI
0.125	3.18	F-74	.41	10.3	.089	2.3	15	2.7	.17	4.4	2.7	12	.20	5.0	0.018	0.5	10.0	MW	C	Z
0.125	3.18	NN-13	.41	10.3	.081	2.1	33	5.9	.10	2.4	3.2	14	.22	5.6	0.022	0.6	10.0	SST	CG	N
0.125	3.18	GG-51	.44	11.1	.095	2.4	4.2	.74	.20	5.0	.83	3.7	.24	6.1	0.015	0.4	15.0	MW	C	GI
0.125	3.18	F-88	.44	11.1	.089	2.3	13	2.2	.21	5.3	2.6	12	.23	5.8	0.018	0.5	11.8	MW	C	Z
0.125	3.18	V-43	.44	11.1	.087	2.2	15	2.7	.14	3.5	2.1	9.3	.23	5.8	0.019	0.5	11.0	SST	C	N
0.125	3.18	S-846	.44	11.1	.081	2.1	27	4.7	.12	3.0	3.2	14	.29	7.3	0.022	0.6	12.0	SST	C	N
0.125	3.18	B12-9	.44	11.1	.079	2.0	37	6.5	.15	3.7	5.5	24	.28	7.2	0.023	0.6	12.3	MW	CG	BO
0.125	3.18	W-79	.44	11.1	.075	1.9	62	11	.07	1.8	4.4	19	.25	6.4	0.025	0.6	10.0	SST	CG	N
0.125	3.18	10832	.47	11.9	.105	2.7	1.3	.22	.36	9.2	.46	2.0	.11	2.7	0.010	0.3	9.50	MW	C	N
0.125	3.18	2765	.47	11.9	.093	2.4	7.7	1.3	.25	6.3	1.9	8.5	.20	5.1	0.016	0.4	11.5	MW	C	Z
0.125	3.18	A10-21	.47	11.9	.083	2.1	23	4.1	.12	3.1	2.8	12	.24	6.1	0.021	0.5	11.5	SST	CG	N
0.125	3.18	A13-12	.47	11.9	.077	2.0	47	8.3	.13	3.3	6.2	27	.31	7.8	0.024	0.6	11.8	MW	C	N
0.125	3.18	11400	.47	11.9	.075	1.9	64	11	.07	1.7	4.4	19	.24	6.2	0.025	0.6	9.75	SST	CG	N
0.125	3.18	DD-3	.50	12.7	.109	2.8	.19	.03	.34	8.6	.06	.28	.16	4.1	0.008	0.2	19.0	SST	C	N
0.125	3.18	B5-67	.50	12.7	.107	2.7	.83	.15	.41	10	.34	1.5	.09	2.3	0.009	0.2	9.25	MW	C	N
0.125	3.18	10068	.50	12.7	.105	2.7	.50	.09	.28	7.1	.14	.62	.22	5.6	0.010	0.3	21.0	MW	C	Z
0.125	3.18	Q-81	.50	12.7	.105	2.7	.33	.06	.18	4.6	.06	.26	.32	8.1	0.010	0.3	31.0	MW	C	N
0.125	3.18	11123	.50	12.7	.105	2.7	1.1	.19	.39	9.8	.43	1.9	.12	2.9	0.010	0.3	10.5	MW	C	N
0.125	3.18	LL-23	.50	12.7	.105	2.7	1.2	.21	.28	7.1	.34	1.5	.10	2.5	0.010	0.3	9.00	SST	C	N
0.125	3.18	B-407	.50	12.7	.101	2.6	2.2	.39	.35	9.0	.79	3.5	.15	3.7	0.012	0.3	11.3	MW	C	Z
0.125	3.18	B-408	.50	12.7	.099	2.5	3.0	.52	.33	8.5	1.0	4.5	.17	4.2	0.013	0.3	11.8	MW	C	Z
0.125	3.18	U-85	.50	12.7	.097	2.5	3.7	.64	.30	7.7	1.1	5.0	.20	5.0	0.014	0.4	13.0	MW	C	N
0.125	3.18	S-202	.50	12.7	.095	2.4	7.3	1.3	.14	3.7	1.1	4.7	.14	3.6	0.015	0.4	8.50	SST	C	N
0.125	3.18	3117	.50	12.7	.093	2.4	7.8	1.4	.25	6.2	1.9	8.5	.20	5.0	0.016	0.4	11.3	MW	C	GI
0.125	3.18	A14-11	.50	12.7	.093	2.4	6.1	1.1	.21	5.3	1.3	5.7	.20	5.1	0.016	0.4	12.5	SST	CG	N
0.125	3.18	B-409	.50	12.7	.093	2.4	7.1	1.2	.27	6.8	1.9	8.5	.21	5.4	0.016	0.4	12.3	MW	C	Z
0.125	3.18	G-90	.50	12.7	.093	2.4	7.3	1.3	.26	6.7	1.9	8.5	.21	5.3	0.016	0.4	12.0	MW	C	N
0.125	3.18	S-320	.50	12.7	.093	2.4	6.7	1.2	.19	4.8	1.3	5.7	.18	4.7	0.016	0.4	11.5	SST	CG	N
0.125	3.18	F-100	.50	12.7	.093	2.4	6.9	1.2	.28	7.0	1.9	8.5	.20	5.1	0.016	0.4	12.5	MW	CG	N
0.125	3.18	A14-21	.50	12.7	.089	2.3	9.5	1.7	.19	4.8	1.8	8.0	.24	6.2	0.018	0.5	13.5	SST	CG	N
0.125	3.18	B-410	.50	12.7	.089	2.3	11	1.9	.24	6.1	2.6	11	.26	6.6	0.018</					




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	A-21	.53	13.5	.085	2.2	18	3.1	.14	3.5	2.4	11	.26	6.6	0.020	0.5	12.0	SST	C	N
0.125	3.18	B10-25	.56	14.3	.097	2.5	3.4	.60	.36	9.0	1.2	5.4	.21	5.2	0.014	0.4	13.8	MW	C	N
0.125	3.18	J-69	.56	14.3	.091	2.3	7.3	1.3	.29	7.4	2.1	9.5	.27	6.9	0.017	0.4	15.0	MW	C	Z
0.125	3.18	L-79	.56	14.3	.083	2.1	15	2.7	.18	4.5	2.7	12	.38	9.7	0.021	0.5	18.3	MW	CG	Z
0.125	3.18	S-1012	.59	15.1	.099	2.5	2.3	.40	.32	8.2	.73	3.2	.19	4.7	0.013	0.3	13.3	SST	C	N
0.125	3.18	S-937	.59	15.1	.089	2.3	7.7	1.4	.23	5.9	1.8	8.0	.30	7.7	0.018	0.5	15.9	SST	C	N
0.125	3.18	G-27	.59	15.1	.063	1.6	133	23	.09	2.2	12	52	.47	11.8	0.031	0.8	14.0	MW	C	N
0.125	3.18	A-1	.63	15.9	.105	2.7	.95	.17	.50	13	.47	2.1	.13	3.3	0.010	0.3	12.0	MW	C	N
0.125	3.18	390	.63	15.9	.103	2.6	1.6	.28	.44	11	.70	3.1	.13	3.4	0.011	0.3	11.0	MW	C	Z
0.125	3.18	A-43	.63	15.9	.103	2.6	1.2	.22	.47	12	.58	2.6	.16	4.1	0.011	0.3	13.5	MW	C	BO
0.125	3.18	N-22	.63	15.9	.103	2.6	1.3	.23	.47	12	.61	2.7	.15	3.9	0.011	0.3	13.0	MW	C	N
0.125	3.18	S-1445	.63	15.9	.099	2.5	1.3	.23	.35	8.8	.45	2.0	.28	7.1	0.013	0.3	21.5	SST	CG	N
0.125	3.18	J-89	.63	15.9	.097	2.5	3.3	.58	.41	10	1.4	6.0	.21	5.4	0.014	0.4	14.3	MW	C	N
0.125	3.18	B14-9	.63	15.9	.097	2.5	3.1	.54	.40	10	1.2	5.5	.22	5.7	0.014	0.4	15.0	MW	C	N
0.125	3.18	EE-61	.63	15.9	.095	2.4	4.2	.74	.38	9.6	1.6	7.0	.24	6.1	0.015	0.4	15.0	MW	C	N
0.125	3.18	S-1543	.63	15.9	.095	2.4	4.4	.77	.24	6.1	1.1	4.7	.21	5.3	0.015	0.4	13.0	SST	C	N
0.125	3.18	A10-20	.63	15.9	.089	2.3	11	2.0	.24	6.0	2.7	12	.25	6.3	0.018	0.5	12.8	MW	C	N
0.125	3.18	F-5	.63	15.9	.089	2.3	8.8	1.5	.31	7.8	2.7	12	.31	7.8	0.018	0.5	16.0	MW	C	Z
0.125	3.18	B1-19	.63	15.9	.079	2.0	25	4.4	.22	5.5	5.5	24	.39	9.9	0.023	0.6	17.0	MW	CG	GI
0.125	3.18	G-2	.63	15.9	.075	1.9	28	4.8	.10	2.5	2.8	12	.53	13.3	0.025	0.6	20.0	SST	C	N
0.125	3.18	2544	.63	15.9	.073	1.9	68	12	.11	2.7	7.3	32	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.125	3.18	903	.63	15.9	.069	1.8	97	17	.09	2.3	8.9	40	.36	9.2	0.028	0.7	12.0	MW	C	Z
0.125	3.18	J-64	.66	16.7	.095	2.4	2.4	.42	.33	8.3	.79	3.5	.33	8.4	0.015	0.4	22.0	SST	CG	N
0.125	3.18	S-11	.66	16.7	.095	2.4	2.4	.41	.30	7.7	.72	3.2	.35	9.0	0.015	0.4	22.5	SST	C	N
0.125	3.18	3546	.66	16.7	.085	2.2	16	2.8	.23	5.8	3.7	16	.31	7.9	0.020	0.5	14.5	MW	C	Z
0.125	3.18	FF-51	.69	17.4	.105	2.7	.35	.06	.39	9.8	.14	.60	.30	7.6	0.010	0.3	29.0	MW	C	N
0.125	3.18	A-80	.69	17.4	.101	2.6	1.4	.25	.41	10	.58	2.6	.19	4.9	0.012	0.3	15.0	SST	C	N
0.125	3.18	A13-22	.69	17.4	.089	2.3	6.8	1.2	.26	6.7	1.8	8.0	.32	8.2	0.018	0.5	18.0	SST	CG	N
0.125	3.18	F-72	.69	17.4	.085	2.2	12	2.2	.29	7.5	3.7	16	.38	9.7	0.020	0.5	18.0	MW	C	Z
0.125	3.18	NN-9	.69	17.4	.079	2.0	22	3.9	.24	6.2	5.5	24	.44	11.1	0.023	0.6	19.0	MW	CG	N
0.125	3.18	J-75	.69	17.4	.075	1.9	26	4.5	.14	3.5	3.5	16	.55	14.0	0.025	0.6	21.0	SST	C	N
0.125	3.18	B4-9	.70	17.9	.095	2.4	4.3	.76	.24	6.2	1.1	4.7	.20	5.0	0.015	0.4	13.0	SST	CG	N
0.125	3.18	B12-7	.72	18.2	.095	2.4	3.7	.65	.43	11	1.6	7.0	.25	6.4	0.015	0.4	16.8	MW	CG	N
0.125	3.18	S-1687	.73	18.6	.095	2.4	4.0	.69	.27	6.7	1.1	4.7	.23	5.7	0.015	0.4	14.0	SST	C	N
0.125	3.18	B4-4	.73	18.6	.089	2.3	7.5	1.3	.36	9.2	2.7	12	.35	8.9	0.018	0.5	18.5	MW	C	N
0.125	3.18	915	.75	19.1	.101	2.6	1.5	.26	.55	14	.81	3.6	.20	5.2	0.012	0.3	16.0	MW	C	Z
0.125	3.18	JJ-27	.75	19.1	.101	2.6	1.6	.28	.56	14	.91	4.0	.19	4.8	0.012	0.3	14.8	MW	C	N
0.125	3.18	A11-15	.75	19.1	.093	2.4	3.9	.68	.32	8.3	1.3	5.7	.30	7.5	0.016	0.4	18.5	SST	CG	N
0.125	3.18	F-3	.75	19.1	.089	2.3	7.0	1.2	.38	9.7	2.7	12	.37	9.4	0.018	0.5	19.5	MW	C	Z
0.125	3.18	A13-50	.75	19.1	.087	2.2	8.9	1.6	.36	9.0	3.2	14	.38	9.5	0.019	0.5	19.8	MW	CG	GI
0.125	3.18	00-21	.75	19.1	.085	2.2	11	1.9	.33	8.4	3.6	16	.42	10.7	0.020	0.5	20.0	MW	C	N
0.125	3.18	KK-31	.75	19.1	.085	2.2	12	2.0	.31	7.9	3.7	16	.40	10.2	0.020	0.5	19.0	MW	C	N
0.125	3.18	S-702	.75	19.1	.081	2.1	15	2.6	.21	5.4	3.2	14	.46	11.7	0.022	0.6	20.0	SST	C	N
0.125	3.18	B14-18	.75	19.1	.081	2.1	20	3.5	.24	6.1	4.8	21	.44	11.2	0.022	0.6	20.0	MW	CG	N
0.125	3.18	A10-24	.75	19.1	.079	2.0	20	3.5	.18	4.7	3.6	16	.46	11.7	0.023	0.6	19.0	SST	C	N
0.125	3.18	10957	.78	19.8	.101	2.6	1.3	.22	.55	14	.68	3.0	.23	5.9	0.012	0.3	18.5	MW	C	Z
0.125	3.18	TT-9	.78	19.8	.089	2.3	5.6	.98	.32	8.1	1.8	8.0	.41	10.3	0.018	0.5	21.5	SST	C	N
0.125	3.18	B5-54	.78	19.8	.079	2.0	19	3.3	.28	7.0	5.2	23	.51	12.9	0.023	0.6	22.0	MW	CG	GI
0.125	3.18	AA-70	.81	20.6	.109	2.8	.30	.05	.57	14	.17	.77	.11	2.7	0.008	0.2	12.5	SST	C	N
0.125	3.18	1719	.81	20.6	.105	2.7	.84	.15	.63	16	.53	2.4	.14	3.6	0.010	0.3	13.3	MW	C	Z
0.125	3.18	S-881	.81	20.6	.099	2.5	1.3	.23	.52	13	.68	3.0	.29	7.4	0.013	0.3	21.5	SST	C	N
0.125	3.18	B4-3	.81	20.6	.095	2.4	5.0	.87	.32	8.1	1.6	7.0	.21	5.3	0.015	0.4	13.0	MW	C	N
0.125	3.18	S-792	.84	21.4	.101	2.6	1.0	.18	.57	14	.58	2.6	.25	6.4	0.012	0.3	20.0	SST	C	N
0.125	3.18	10943	.84	21.4	.091	2.3	8.3	1.5	.28	7.0	2.3	10	.25	6.3	0.017	0.4	13.5	MW	C	Z
0.125	3.18	KK-41	.84	21.4	.081	2.1	20	3.5	.16	4.1	3.2	14	.36	9.2	0.022	0.6	15.5	SST	C	N
0.125	3.18	00-69	.88	22.2	.105	2.7	.30	.05	.53	13	.16	.70	.35	8.8	0.010	0.3	33.8	MW	C	N
0.125	3.18	S-1511	.88	22.2	.095	2.4	4.0	.69	.27	6.7	1.1	4.7	.23	5.7	0.015	0.4	14.0	SST	C	N
0.125	3.18	B7-15	.91	23.0	.091	2.3	5.4	.95	.42	11	2.3	10	.35	8.9	0.017	0.4	19.5	MW	C	N
0.125	3.18	KK-82	.91	23.0	.085	2.2	10	1.8	.35	8.9	3.7	16	.44	11.2	0.020	0.5	21.0	MW	C	N
0.125	3.18	Y-85	.91	23.0	.085	2.2	9.7	1.7	.38	9.6	3.7	16	.47	11.9	0.020	0.5	22.5	MW	C	GI
0.125	3.18	LL-89	.94	23.8	.085	2.2	8.6	1.5	.42	11	3.6	16	.52	13.2	0.020	0.5	25.0	MW	C	N
0.125	3.18	MM-66	.94	23.8	.065	1.7	55	9.6	.13	3.3	7.2	32	.71	17.9	0.030	0.8	23.5	SST	CG	N
0.125	3.18	10745	1.00	25.4	.107	2.7	.42	.07	.85	21	.36	1.6	.16	3.9	0.009	0.2	16.3	MW	C	N
0.125	3.18	391	1.00	25.4	.103	2.6	.96	.17	.73	18	.70	3.1	.20	5.0	0.011	0.3	16.8	MW	C	Z
0.125	3.18	354-A	1.00	25.4	.097	2.5	2.2	.39	.64	16	1.4	6.3	.30	7.6	0.014	0.4	20.3	MW	C	Z
0.125	3.18	G-7	1.00	25.4	.097	2.5	1.9	.33	.66	17	1.2	5.5	.34	8.7	0.014	0.4	23.5	MW	C	BO
0.125	3.18	II-59	1.00	25.4	.095	2.4	3.0	.53	.52	13	1.6	7.0	.32	8.0	0.015	0.4	20.0	MW	C	Z
0.125	3.18	M-143	1.00	25.4	.095	2.4	2.1	.37	.57	14	1.2	5.3	.44	11.0	0.015	0.4	28.0	MW	C	Z
0.125	3.18	00-15	1.00	25.4	.095	2.4	3.4	.60	.46	12	1.6	7.0	.29	7.2	0.015	0.4	18.0	MW	C	N




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	B15-63	1.22	31.0	.099	2.5	1.0	.18	.80	20	.81	3.6	.42	10.6	0.013	0.3	31.0	MW	C	N
0.125	3.18	S-1085	1.25	31.8	.095	2.4	2.4	.43	.43	11	1.1	4.7	.34	8.6	0.015	0.4	21.5	SST	C	N
0.125	3.18	PP-9	1.25	31.8	.065	1.7	100	18	.07	1.8	7.2	32	.45	11.4	0.030	0.8	14.0	SST	C	N
0.125	3.18	AA-7	1.38	34.9	.105	2.7	.47	.08	.72	18	.34	1.5	.21	5.3	0.010	0.3	20.0	SST	C	N
0.125	3.18	354-B	1.38	34.9	.097	2.5	1.6	.28	.90	23	1.4	6.3	.40	10.1	0.014	0.4	27.5	MW	C	Z
0.125	3.18	1827	1.38	34.9	.093	2.4	2.3	.41	.81	21	1.9	8.5	.54	13.8	0.016	0.4	33.0	MW	C	Z
0.125	3.18	KK-90	1.38	34.9	.089	2.3	4.9	.86	.55	14	2.7	12	.50	12.8	0.018	0.5	27.0	MW	C	N
0.125	3.18	MM-82	1.38	34.9	.087	2.2	6.6	1.1	.48	12	3.2	14	.51	13.0	0.019	0.5	26.0	MW	C	Z
0.125	3.18	FF-54	1.38	34.9	.085	2.2	7.9	1.4	.46	12	3.7	16	.56	14.2	0.020	0.5	27.0	MW	C	N
0.125	3.18	NN-94	1.50	38.1	.075	1.9	13	2.3	.33	8.4	4.4	19	1.00	25.4	0.025	0.6	39.0	SST	C	N
0.125	3.18	2982	1.53	38.9	.095	2.4	3.1	.55	.51	13	1.6	7.0	.31	7.8	0.015	0.4	19.5	MW	C	Z
0.125	3.18	354-C	1.75	44.5	.097	2.5	1.2	.22	1.1	29	1.4	6.3	.50	12.6	0.014	0.4	34.5	MW	C	Z
0.125	3.18	BB-34	2.25	57.2	.085	2.2	5.7	.99	.64	16	3.7	16	.76	19.3	0.020	0.5	37.0	MW	C	N
0.125	3.18	Y-65	3.00	76.2	.105	2.7	.21	.04	2.5	64	.52	2.3	.49	12.4	0.010	0.3	48.0	MW	C	N
0.125	3.18	S-1474	4.25	108.0	.105	2.7	.08	.01	3.2	82	.27	1.2	1.02	25.9	0.010	0.3	101.0	SST	C	N
0.140	3.56	10224	.16	4.0	.122	3.1	1.2	.21	.10	2.5	.12	.52	.06	1.5	0.009	0.2	5.50	MW	C	N
0.140	3.56	DD-49	.19	4.8	.116	2.9	4.2	.74	.12	2.9	.49	2.2	.07	1.8	0.012	0.3	5.00	SST	C	N
0.140	3.56	J-84	.20	5.2	.100	2.5	67	12	.05	1.3	3.3	15	.08	2.0	0.020	0.5	4.00	MW	CG	N
0.140	3.56	U-93	.25	6.4	.118	3.0	1.6	.29	.15	3.8	.25	1.1	.10	2.5	0.011	0.3	8.00	MW	C	Z
0.140	3.56	Z-7	.25	6.4	.112	2.8	3.8	.67	.12	3.1	.46	2.1	.13	3.3	0.014	0.4	8.25	SST	C	N
0.140	3.56	II-9	.25	6.4	.096	2.4	102	18	.04	1.1	4.4	19	.11	2.8	0.022	0.6	4.00	MW	C	N
0.140	3.56	JJ-72	.25	6.4	.080	2.0	155	27	.04	1.1	6.6	30	.18	4.6	0.030	0.8	5.00	SST	O	N
0.140	3.56	OO-19	.28	7.1	.120	3.0	1.0	.18	.19	4.7	.19	.83	.10	2.4	0.010	0.3	8.50	MW	C	N
0.140	3.56	L-97	.28	7.1	.116	2.9	2.0	.36	.16	4.1	.33	1.5	.12	3.0	0.012	0.3	9.00	MW	C	N
0.140	3.56	GG-60	.31	7.9	.112	2.8	2.7	.47	.16	4.0	.42	1.9	.15	3.9	0.014	0.4	11.0	SST	CG	N
0.140	3.56	BB-8	.31	7.9	.104	2.6	14	2.4	.15	3.8	2.1	9.2	.16	4.1	0.018	0.5	8.00	MW	C	N
0.140	3.56	AA-6	.31	7.9	.100	2.5	27	4.7	.12	3.2	3.3	15	.14	3.6	0.020	0.5	7.00	MW	CG	Z
0.140	3.56	LL-69	.31	7.9	.090	2.3	49	8.6	.08	2.0	4.0	18	.21	5.4	0.025	0.6	8.50	SST	CG	N
0.140	3.56	A9-27	.34	8.7	.098	2.5	27	4.7	.09	2.4	2.5	11	.18	4.5	0.021	0.5	7.50	SST	C	N
0.140	3.56	CC-91	.34	8.7	.088	2.2	57	10	.08	2.0	4.4	20	.23	5.8	0.026	0.7	8.75	SST	CG	N
0.140	3.56	NN-41	.34	8.7	.088	2.2	66	11	.07	1.7	4.4	20	.21	5.3	0.026	0.7	8.00	SST	CG	N
0.140	3.56	H-77	.34	8.7	.084	2.1	78	14	.07	1.8	5.5	24	.25	6.4	0.028	0.7	9.00	SST	CG	N
0.140	3.56	A-27	.34	8.7	.082	2.1	110	19	.05	1.4	6.0	27	.26	6.6	0.029	0.7	8.00	SST	C	N
0.140	3.56	A12-1	.35	8.9	.112	2.8	4.0	.70	.20	5.2	.82	3.6	.13	3.2	0.014	0.4	8.00	SST	C	N
0.140	3.56	O-80	.36	9.1	.100	2.5	41	7.2	.05	1.4	2.2	9.8	.12	3.0	0.020	0.5	4.88	SST	C	N
0.140	3.56	J-26	.38	9.5	.116	2.9	2.8	.50	.28	7.1	.79	3.5	.10	2.4	0.012	0.3	7.00	MW	C	GI
0.140	3.56	12619	.38	9.5	.116	2.9	2.6	.45	.27	6.9	.71	3.1	.10	2.6	0.012	0.3	7.50	MW	C	N
0.140	3.56	B2-23	.38	9.5	.116	2.9	2.2	.38	.26	6.6	.57	2.5	.11	2.9	0.012	0.3	8.50	MW	C	Z
0.140	3.56	A15-25	.38	9.5	.114	2.9	4.0	.70	.26	6.5	1.0	4.6	.10	2.5	0.013	0.3	7.00	MW	C	GI
0.140	3.56	FF-22	.38	9.5	.114	2.9	4.0	.70	.20	5.1	.80	3.6	.10	2.6	0.013	0.3	7.00	BC	C	N
0.140	3.56	M-129	.38	9.5	.110	2.8	5.7	1.0	.23	5.9	1.3	5.9	.14	3.6	0.015	0.4	8.50	MW	C	N
0.140	3.56	A15-6	.38	9.5	.100	2.5	21	3.6	.11	2.7	2.2	9.8	.18	4.4	0.020	0.5	7.75	SST	C	N
0.140	3.56	AA-42	.38	9.5	.100	2.5	13	2.3	.16	3.9	2.0	8.9	.22	5.6	0.020	0.5	11.0	SST	CG	N
0.140	3.56	GG-38	.38	9.5	.100	2.5	18	3.1	.12	3.1	2.2	9.8	.19	4.8	0.020	0.5	8.50	SST	C	N
0.140	3.56	3762	.38	9.5	.084	2.1	157	28	.05	1.3	8.2	36	.20	5.0	0.028	0.7	6.00	MW	C	Z
0.140	3.56	H-95	.38	9.5	.084	2.1	126	22	.06	1.6	8.2	36	.22	5.7	0.028	0.7	7.00	MW	C	N
0.140	3.56	S-1535	.39	9.9	.078	2.0	162	28.3	.045	1.14	7.3	32.5	.23	5.9	0.031	0.8	7.50	SST	CG	N
0.140	3.56	11375	.41	10.3	.108	2.7	7.0	1.2	.16	4.1	1.1	5.1	.15	3.8	0.016	0.4	8.25	SST	C	N
0.140	3.56	3633	.41	10.3	.104	2.6	14	2.4	.18	4.5	2.4	11	.14	3.7	0.018	0.5	8.00	MW	CG	N
0.140	3.56	J-80	.41	10.3	.102	2.6	14	2.4	.14	3.5	1.9	8.4	.17	4.2	0.019	0.5	8.75	SST	CG	N
0.140	3.56	UU-4	.42	10.7	.100	2.5	17	3.0	.13	3.3	2.2	9.8	.20	5.1	0.020	0.5	9.00	SST	C	N
0.140	3.56	B1-10	.44	11.1	.124	3.1	.26	.05	.34	8.7	.09	.40	.09	2.4	0.008	0.2	10.8	SST	C	N
0.140	3.56	J-99	.44	11.1	.116	2.9	1.1	.19	.25	6.2	.27	1.2	.19	4.9	0.012	0.3	15.0	MW	C	Z
0.140	3.56	3793	.44	11.1	.108	2.7	7.9	1.4	.22	5.5	1.7	7.7	.15	3.8	0.016	0.4	8.25	MW	C	Z
0.140	3.56	V-40	.44	11.1	.106	2.7	6.5	1.1	.22	5.5	1.4	6.2	.22	5.6	0.017	0.4	12.0	MW	C	N
0.140	3.56	B14-56	.44	11.1	.104	2.6	17	2.9	.15	3.7	2.4	11	.14	3.7	0.018	0.5	7.00	MW	C	N
0.140	3.56	J-90	.44	11.1	.102	2.6	13	2.3	.22	5.5	2.8	13	.21	5.3	0.019	0.5	10.0	MW	C	Z
0.140	3.56	V-41	.44	11.1	.102	2.6	11	1.9	.19	4.9	2.0	9.0	.25	6.3	0.019	0.5	12.0	MW	C	N
0.140	3.56	OO-22	.45	11.5	.100	2.5	27	4.7	.12	3.2	3.3	15	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.140	3.56	2674	.47	11.9	.104	2.6	12	2.1	.20	5.2	2.4	11	.18	4.6	0.018	0.5	9.00	MW	C	Z
0.140	3.56	CC-19	.47	11.9	.100	2.5	13	2.3	.21	5.3	2.8	12	.26	6.6	0.020	0.5	12.0	MW	C	N
0.140	3.56	J-55	.50	12.7	.120	3.0	.65	.11	.37	9.4	.24	1.1	.13	3.3	0.010	0.3	12.0	MW	C	Z
0.140	3.56	11255	.50	12.7	.116	2.9	1.1	.18	.32	8.1	.34	1.5	.18	4.6	0.012	0.3	14.0	SST	C	N
0.140	3.56	N-35	.50	12.7	.090	2.3	41	7.2	.14	3.7	5.9	26	.28	7.0	0.025	0.6	11.0	MW	CG	N
0.140	3.56	S-236	.50	12.7	.088	2.2	64	11	.07	1.8	4.4	20	.23	5.9	0.026	0.7	8.00	SST	C	N
0.140	3.56	B18-144	.53	13.5	.124	3.1	.32	.06	.44	11	.14	.63	.09	2.2	0.008	0.2	10.0	MW	C	Z
0.140	3.56	S-191	.56	14.3	.104	2.6	13	2.3	.12	3.1	1.6	7.2	.15	3.9	0.018	0.5	7.50	SST	C	N
0.140	3.56	S-1331	.56	14.3	.100	2.5	17	2.9	.13	3.4	2.2	9.8	.20	5.1	0.020	0.5	9.00	SST	C	N
0.140	3.56	10025	.56	14.3	.094	2.4	28	4.9	.18	4.5	4.9	22	.28	7.0	0.023	0.6	11.0	MW	CL	N
0.140	3.56	XX-38	.58	14.7	.100	2.5	17	2.9	.20	5.0	3									




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.140	3.56	Q-83	.72	18.2	.092	2.3	21	3.7	.27	6.7	5.6	25	.42	10.7	0.024	0.6	16.5	MW	C	N
0.140	3.56	10968	.75	19.1	.120	3.0	.50	.09	.59	15	.30	1.3	.16	4.1	0.010	0.3	15.0	MW	C	Z
0.140	3.56	RR-35	.75	19.1	.100	2.5	4.5	.79	.18	4.6	.82	3.6	.57	14.5	0.020	0.5	27.5	SST	C	N
0.140	3.56	JJ-25	.78	19.8	.088	2.2	21	3.8	.21	5.3	4.4	20	.52	13.2	0.026	0.7	20.0	SST	CG	N
0.140	3.56	11464	.81	20.6	.114	2.9	2.2	.39	.30	7.5	.66	2.9	.14	3.6	0.013	0.3	10.0	SST	C	N
0.140	3.56	RR-44	.81	20.6	.100	2.5	6.4	1.1	.34	8.7	2.2	9.8	.42	10.7	0.020	0.5	20.0	SST	C	N
0.140	3.56	FF-53	.88	22.2	.120	3.0	.47	.08	.71	18	.33	1.5	.17	4.3	0.010	0.3	16.0	MW	C	N
0.140	3.56	3195	.88	22.2	.116	2.9	1.0	.18	.67	17	.68	3.0	.20	5.2	0.012	0.3	16.0	MW	C	Z
0.140	3.56	1831	.91	23.0	.116	2.9	1.1	.19	.71	18	.78	3.5	.19	4.9	0.012	0.3	15.0	MW	C	Z
0.140	3.56	3707	.94	23.8	.120	3.0	.33	.06	.71	18	.23	1.0	.23	5.8	0.010	0.3	22.0	MW	C	Z
0.140	3.56	B5-69	.94	23.8	.118	3.0	.34	.06	.59	15	.20	.88	.35	8.9	0.011	0.3	31.0	MW	C	N
0.140	3.56	S-393	.94	23.8	.108	2.7	2.2	.39	.51	13	1.1	5.1	.36	9.1	0.016	0.4	21.5	SST	C	N
0.140	3.56	A10-34	1.00	25.4	.116	2.9	.61	.11	.72	18	.43	1.9	.29	7.2	0.012	0.3	22.8	SST	C	N
0.140	3.56	3773	1.00	25.4	.108	2.7	3.5	.62	.49	12	1.7	7.7	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.140	3.56	11254	1.00	25.4	.102	2.6	4.7	.82	.40	10	1.9	8.4	.44	11.1	0.019	0.5	22.0	SST	C	N
0.140	3.56	NN-55	1.03	26.2	.108	2.7	3.3	.58	.52	13	1.7	7.7	.29	7.3	0.016	0.4	17.0	MW	C	N
0.140	3.56	BB-83	1.06	27.0	.096	2.4	7.1	1.2	.41	10	2.9	13	.62	15.6	0.022	0.6	27.0	SST	C	N
0.140	3.56	LL-19	1.13	28.6	.120	3.0	.26	.05	.85	21	.22	.98	.28	7.1	0.010	0.3	27.0	MW	C	N
0.140	3.56	PP-54	1.13	28.6	.108	2.7	1.8	.31	.63	16	1.1	4.9	.50	12.6	0.016	0.4	30.0	MW	C	Z
0.140	3.56	LL-91	1.25	31.8	.124	3.1	.14	.02	1.1	27	.15	.68	.17	4.3	0.008	0.2	20.0	MW	C	N
0.140	3.56	4223	1.25	31.8	.110	2.8	1.3	.22	.76	19	.96	4.3	.49	12.4	0.015	0.4	31.5	MW	C	Z
0.140	3.56	S-1020	1.31	33.3	.100	2.5	4.0	.70	.55	14	2.2	9.8	.64	16.3	0.020	0.5	31.0	SST	C	N
0.140	3.56	B3-41	1.31	33.3	.080	2.0	30	5.3	.33	8.3	9.9	44	.93	23.6	0.030	0.8	31.0	MW	CG	N
0.140	3.56	AA-68	1.34	34.1	.104	2.6	4.9	.86	.33	8.3	1.6	7.2	.32	8.2	0.018	0.5	17.0	SST	C	N
0.140	3.56	1755	1.38	34.9	.108	2.7	1.6	.28	.84	21	1.4	6.0	.54	13.6	0.016	0.4	32.5	MW	C	Z
0.140	3.56	2638	1.38	34.9	.102	2.6	3.6	.62	.75	19	2.7	12	.62	15.8	0.019	0.5	31.8	MW	C	Z
0.140	3.56	N-108	1.44	36.5	.092	2.3	10	1.8	.55	14	5.6	25	.79	20.1	0.024	0.6	32.0	MW	C	GI
0.140	3.56	A12-34	1.44	36.6	.116	2.9	.43	.07	1.1	27	.45	2.0	.38	9.8	0.012	0.3	31.0	SST	C	N
0.140	3.56	1922	1.50	38.1	.108	2.7	1.7	.30	.98	25	1.7	7.4	.52	13.1	0.016	0.4	31.3	MW	C	Z
0.140	3.56	O-128	1.94	49.2	.090	2.3	7.1	1.2	.56	14	4.0	18	1.20	30.5	0.025	0.6	47.0	SST	C	N
0.148	3.76	70206	.25	6.4	.106	2.7	34	6.0	.11	2.7	3.6	16	.13	3.2	0.021	0.5	6.00	MW	CG	N
0.148	3.76	70206S	.25	6.4	.106	2.7	30	5.2	.08	2.1	2.4	11	.13	3.2	0.021	0.5	6.00	SST	CG	N
0.148	3.76	70225	.25	6.4	.102	2.6	50	8.7	.09	2.4	4.7	21	.14	3.6	0.023	0.6	6.13	MW	CG	N
0.148	3.76	70225S	.25	6.4	.102	2.6	43	7.6	.07	1.8	3.1	14	.14	3.6	0.023	0.6	6.13	SST	CG	N
0.148	3.76	70207	.31	7.9	.106	2.7	27	4.7	.14	3.5	3.6	16	.15	3.8	0.021	0.5	7.13	MW	CG	N
0.148	3.76	70207S	.31	7.9	.106	2.7	23	4.1	.10	2.6	2.4	11	.15	3.8	0.021	0.5	7.13	SST	CG	N
0.148	3.76	70226	.31	7.9	.102	2.6	38	6.7	.12	3.1	4.7	21	.17	4.3	0.023	0.6	7.38	MW	CG	N
0.148	3.76	70226S	.31	7.9	.102	2.6	33	5.8	.09	2.4	3.1	14	.17	4.3	0.023	0.6	7.38	SST	CG	N
0.148	3.76	70208	.38	9.7	.106	2.7	21	3.7	.17	4.4	3.6	16	.18	4.5	0.021	0.5	8.50	MW	CG	N
0.148	3.76	70208S	.38	9.7	.106	2.7	18	3.2	.13	3.3	2.4	11	.18	4.5	0.021	0.5	8.50	SST	CG	N
0.148	3.76	70227	.38	9.7	.102	2.6	31	5.3	.15	3.9	4.7	21	.20	5.1	0.023	0.6	8.75	MW	CG	N
0.148	3.76	70227S	.38	9.7	.102	2.6	27	4.6	.12	3.0	3.1	14	.20	5.1	0.023	0.6	8.75	SST	CG	N
0.148	3.76	70209	.44	11.2	.106	2.7	18	3.1	.20	5.1	3.6	16	.20	5.1	0.021	0.5	9.63	MW	CG	N
0.148	3.76	70209S	.44	11.2	.106	2.7	16	2.7	.15	3.9	2.4	11	.20	5.1	0.021	0.5	9.63	SST	CG	N
0.148	3.76	70228	.44	11.2	.102	2.6	26	4.6	.18	4.6	4.7	21	.23	5.8	0.023	0.6	9.88	MW	CG	N
0.148	3.76	70228S	.44	11.2	.102	2.6	23	4.0	.14	3.5	3.1	14	.23	5.8	0.023	0.6	9.88	SST	CG	N
0.148	3.76	70210	.50	12.7	.106	2.7	15	2.7	.24	6.0	3.6	16	.23	5.8	0.021	0.5	10.9	MW	CG	N
0.148	3.76	70210S	.50	12.7	.106	2.7	13	2.3	.18	4.6	2.4	11	.23	5.8	0.021	0.5	10.9	SST	CG	N
0.148	3.76	70229	.50	12.7	.102	2.6	23	4.0	.21	5.3	4.7	21	.26	6.5	0.023	0.6	11.1	MW	CG	N
0.148	3.76	70229S	.50	12.7	.102	2.6	20	3.4	.16	4.1	3.1	14	.26	6.5	0.023	0.6	11.1	SST	CG	N
0.148	3.76	70211	.56	14.2	.106	2.7	14	2.4	.27	6.7	3.6	16	.25	6.4	0.021	0.5	12.0	MW	CG	N
0.148	3.76	70211S	.56	14.2	.106	2.7	12	2.1	.20	5.1	2.4	11	.25	6.4	0.021	0.5	12.0	SST	CG	N
0.148	3.76	70230	.56	14.2	.102	2.6	20	3.5	.24	6.0	4.7	21	.29	7.2	0.023	0.6	12.4	MW	CG	N
0.148	3.76	70230S	.56	14.2	.102	2.6	17	3.0	.18	4.6	3.1	14	.29	7.2	0.023	0.6	12.4	SST	CG	N
0.148	3.76	70212	.63	16.0	.106	2.7	12	2.1	.29	7.5	3.6	16	.28	7.0	0.021	0.5	13.1	MW	CG	N
0.148	3.76	70212S	.63	16.0	.106	2.7	11	1.9	.23	5.7	2.4	11	.28	7.0	0.021	0.5	13.1	SST	CG	N
0.148	3.76	70231	.63	16.0	.102	2.6	18	3.1	.27	6.7	4.7	21	.31	8.0	0.023	0.6	13.6	MW	CG	N
0.148	3.76	70231S	.63	16.0	.102	2.6	15	2.7	.20	5.2	3.1	14	.31	8.0	0.023	0.6	13.6	SST	CG	N
0.148	3.76	70213	.69	17.5	.106	2.7	11	1.9	.33	8.3	3.6	16	.30	7.7	0.021	0.5	14.4	MW	CG	N
0.148	3.76	70213S	.69	17.5	.106	2.7	9.6	1.7	.25	6.4	2.4	11	.30	7.7	0.021	0.5	14.4	SST	CG	N
0.148	3.76	70232	.69	17.5	.102	2.6	16	2.8	.29	7.5	4.7	21	.34	8.7	0.023	0.6	14.9	MW	CG	N
0.148	3.76	70232S	.69	17.5	.102	2.6	14	2.4	.22	5.7	3.1	14	.34	8.7	0.023	0.6	14.9	SST	CG	N
0.148	3.76	70214	.75	19.1	.106	2.7	10	1.8	.36	9.1	3.6	16	.33	8.3	0.021	0.5	15.5	MW	CG	N
0.148	3.76	70214S	.75	19.1	.106	2.7	8.8	1.5	.27	6.9	2.4	11	.33	8.3	0.021	0.5	15.5	SST	CG	N
0.148	3.76	70233	.75	19.1	.102	2.6	15	2.6	.32	8.2	4.7	21	.37	9.4	0.023	0.6	16.1	MW	CG	N
0.148	3.76	70233S	.75	19.1	.102	2.6	13	2.2	.25	6.3	3.1	14	.37	9.4	0.023	0.6	16.1	SST	CG	N
0.148	3.76	70215	.81	20.6	.106	2.7	9.3	1.6	.39	9.8	3.6	16	.35	8.9	0.021	0.5	16.6	MW	CG	N
0.148	3.76	70215S	.81	20.6	.106	2.7	8.1	1.4	.30	7.5	2.4	11	.35	8.9	0.021	0.5	16.6	SST	CG	N
0.148	3.76	70234	.81	20.6	.102	2.6	13	2.3	.35</											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.148	3.76	70237	1.00	25.4	.102	2.6	11	1.9	.44	11	4.7	21	.49	12.4	0.023	0.6	21.3	MW	CG	N
0.148	3.76	70237S	1.00	25.4	.102	2.6	9.3	1.6	.34	8.5	3.1	14	.49	12.4	0.023	0.6	21.3	SST	CG	N
0.148	3.76	70220	1.13	28.7	.106	2.7	6.8	1.2	.53	14	3.6	16	.47	11.8	0.021	0.5	22.1	MW	CG	N
0.148	3.76	70220S	1.13	28.7	.106	2.7	5.9	1.0	.41	10	2.4	11	.47	11.8	0.021	0.5	22.1	SST	CG	N
0.148	3.76	70239	1.13	28.7	.102	2.6	9.8	1.7	.48	12	4.7	21	.53	13.4	0.023	0.6	23.0	MW	CG	N
0.148	3.76	70239S	1.13	28.7	.102	2.6	8.5	1.5	.37	9.3	3.1	14	.53	13.4	0.023	0.6	23.0	SST	CG	N
0.148	3.76	70221	1.25	31.8	.106	2.7	5.9	1.0	.61	15	3.6	16	.53	13.3	0.021	0.5	25.0	MW	CG	N
0.148	3.76	70221S	1.25	31.8	.106	2.7	5.2	.90	.47	12	2.4	11	.53	13.3	0.021	0.5	25.0	SST	CG	N
0.148	3.76	70240	1.25	31.8	.102	2.6	8.5	1.5	.55	14	4.7	21	.60	15.3	0.023	0.6	26.1	MW	CG	N
0.148	3.76	70240S	1.25	31.8	.102	2.6	7.4	1.3	.42	11	3.1	14	.60	15.3	0.023	0.6	26.1	SST	CG	N
0.148	3.76	70223	1.38	35.1	.106	2.7	5.6	.98	.65	16	3.6	16	.55	14.1	0.021	0.5	26.4	MW	CG	N
0.148	3.76	70223S	1.38	35.1	.106	2.7	4.9	.85	.49	13	2.4	11	.55	14.1	0.021	0.5	26.4	SST	CG	N
0.148	3.76	70242	1.38	35.1	.102	2.6	8.0	1.4	.59	15	4.7	21	.64	16.2	0.023	0.6	27.8	MW	CG	N
0.148	3.76	70242S	1.38	35.1	.102	2.6	7.0	1.2	.45	11	3.1	14	.64	16.2	0.023	0.6	27.8	SST	CG	N
0.148	3.76	70224	1.50	38.1	.106	2.7	4.9	.87	.73	19	3.6	16	.62	15.8	0.021	0.5	29.6	MW	CG	N
0.148	3.76	70224S	1.50	38.1	.106	2.7	4.3	.75	.56	14	2.4	11	.62	15.8	0.021	0.5	29.6	SST	CG	N
0.148	3.76	70243	1.50	38.1	.102	2.6	7.1	1.2	.66	17	4.7	21	.71	18.1	0.023	0.6	31.0	MW	CG	N
0.148	3.76	70243S	1.50	38.1	.102	2.6	6.2	1.1	.51	13	3.1	14	.71	18.1	0.023	0.6	31.0	SST	CG	N
0.156	3.96	HH-70	.19	4.8	.116	2.9	46	8.0	.07	1.7	3.0	13	.10	2.5	0.020	0.5	4.00	MW	C	N
0.156	3.96	HH-57	.25	6.4	.132	3.4	2.5	.43	.17	4.4	.43	1.9	.08	2.0	0.012	0.3	5.50	SST	C	N
0.156	3.96	V-18	.25	6.4	.126	3.2	7.5	1.3	.11	2.9	.85	3.8	.09	2.3	0.015	0.4	5.00	SST	C	N
0.156	3.96	904	.25	6.4	.116	2.9	30	5.3	.10	2.5	3.0	13	.12	3.0	0.020	0.5	5.00	MW	C	Z
0.156	3.96	J-86	.25	6.4	.106	2.7	83	15	.06	1.6	5.4	24	.13	3.2	0.025	0.6	5.00	MW	CG	Z
0.156	3.96	KK-7	.28	7.1	.136	3.5	1.3	.23	.20	5.2	.27	1.2	.06	1.5	0.010	0.3	5.00	SST	C	N
0.156	3.96	H-18	.28	7.1	.106	2.7	62	11	.09	2.2	5.4	24	.15	3.8	0.025	0.6	6.00	MW	CG	Z
0.156	3.96	B-46	.28	7.1	.104	2.6	88	15	.05	1.2	4.0	18	.16	4.0	0.026	0.7	5.00	SST	C	N
0.156	3.96	3721	.31	7.9	.142	3.6	.09	.01	.21	5.2	.02	.08	.11	2.7	0.007	0.2	14.3	MW	C	N
0.156	3.96	FF-37	.31	7.9	.126	3.2	3.7	.65	.16	4.1	.60	2.7	.15	3.8	0.015	0.4	9.00	MW	C	Z
0.156	3.96	U-16	.31	7.9	.126	3.2	5.2	.91	.19	4.9	1.0	4.4	.12	3.0	0.015	0.4	7.00	MW	C	Z
0.156	3.96	EE-95	.31	7.9	.124	3.1	8.6	1.5	.18	4.6	1.6	6.9	.11	2.8	0.016	0.4	6.00	MW	C	N
0.156	3.96	S-1038	.31	7.9	.120	3.0	17	2.9	.09	2.2	1.5	6.5	.11	2.7	0.018	0.5	5.00	SST	C	N
0.156	3.96	B8-6	.31	7.9	.118	3.0	12	2.1	.16	4.1	1.9	8.6	.15	3.9	0.019	0.5	8.00	MW	CG	N
0.156	3.96	J-82	.31	7.9	.114	2.9	17	2.9	.12	3.1	2.1	9.2	.19	4.8	0.021	0.5	8.00	SST	C	N
0.156	3.96	Q-11	.31	7.9	.106	2.7	62	11	.09	2.2	5.4	24	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.156	3.96	U-90	.31	7.9	.090	2.3	153	27	.05	1.2	7.3	33	.26	6.7	0.033	0.8	8.00	MW	CG	Z
0.156	3.96	N-5	.34	8.7	.140	3.6	.15	.03	.24	6.0	.04	.16	.11	2.7	0.008	0.2	12.5	SST	C	N
0.156	3.96	S-301	.34	8.7	.140	3.6	.14	.03	.23	5.9	.03	.15	.11	2.8	0.008	0.2	13.0	SST	C	N
0.156	3.96	LL-38	.34	8.7	.118	3.0	13	2.2	.14	3.4	1.7	7.6	.15	3.9	0.019	0.5	7.00	SST	C	N
0.156	3.96	Y-67	.34	8.7	.118	3.0	12	2.1	.17	4.4	2.1	9.3	.17	4.3	0.019	0.5	8.00	MW	C	N
0.156	3.96	2815	.34	8.7	.086	2.2	244	43	.05	1.4	13	59	.25	6.2	0.035	0.9	7.00	MW	CG	Z
0.156	3.96	B4-6	.34	8.7	.114	2.9	21	3.6	.17	4.2	3.4	15	.18	4.5	0.021	0.5	7.50	MW	C	N
0.156	3.96	S-1095	.38	9.5	.126	3.2	2.1	.36	.17	4.2	.34	1.5	.21	5.3	0.015	0.4	13.0	SST	C	N
0.156	3.96	10111	.38	9.5	.124	3.1	7.6	1.3	.20	5.2	1.6	6.9	.12	3.0	0.016	0.4	6.50	MW	C	Z
0.156	3.96	N-28	.38	9.5	.120	3.0	7.2	1.3	.20	5.0	1.4	6.2	.18	4.6	0.018	0.5	10.0	MW	CG	Z
0.156	3.96	O-37	.38	9.5	.116	2.9	18	3.2	.16	4.2	3.0	13	.16	4.1	0.020	0.5	7.00	MW	C	N
0.156	3.96	EE-1	.38	9.5	.116	2.9	9.4	1.6	.15	3.7	1.4	6.0	.23	5.8	0.020	0.5	10.5	SST	C	N
0.156	3.96	BB-73	.38	9.5	.116	2.9	7.1	1.2	.11	2.7	.74	3.3	.27	6.9	0.020	0.5	13.5	SST	CG	N
0.156	3.96	O-104	.38	9.5	.114	2.9	23	4.0	.15	3.9	3.4	15	.17	4.3	0.021	0.5	7.00	MW	C	N
0.156	3.96	B12-34	.38	9.5	.112	2.8	22	3.8	.18	4.7	3.9	18	.19	4.7	0.022	0.6	8.50	MW	CG	GI
0.156	3.96	B3-37	.38	9.5	.110	2.8	31	5.4	.14	3.7	4.5	20	.17	4.4	0.023	0.6	7.50	MW	CG	N
0.156	3.96	H-97	.38	9.5	.106	2.7	45	8.0	.12	3.0	5.4	24	.19	4.8	0.025	0.6	7.50	MW	CG	GI
0.156	3.96	MM-25	.38	9.5	.102	2.6	59	10	.11	2.9	6.7	30	.22	5.5	0.027	0.7	8.00	MW	CG	N
0.156	3.96	G-31	.38	9.5	.100	2.5	94	16	.08	2.0	7.5	33	.21	5.3	0.028	0.7	6.50	MW	C	N
0.156	3.96	W-76	.38	9.5	.096	2.4	84	15	.07	1.8	6.1	27	.27	6.9	0.030	0.8	8.00	SST	C	N
0.156	3.96	B12-29	.38	9.5	.080	2.0	365	64	.03	.84	12	54	.27	6.8	0.038	1.0	7.00	SPR	CG	N
0.156	3.96	B17-135	.41	10.3	.140	3.6	.23	.04	.32	8.1	.07	.32	.09	2.2	0.008	0.2	10.0	MW	C	N
0.156	3.96	M-72	.41	10.3	.138	3.5	.30	.05	.29	7.3	.09	.38	.12	3.0	0.009	0.2	12.0	MW	C	N
0.156	3.96	B15-11	.41	10.3	.122	3.1	6.4	1.1	.24	6.0	1.5	6.7	.17	4.3	0.017	0.4	9.00	MW	C	N
0.156	3.96	B11-50	.41	10.3	.116	2.9	11	2.0	.21	5.2	2.4	10	.20	5.1	0.020	0.5	10.0	MW	CG	N
0.156	3.96	B15-37	.41	10.3	.112	2.8	28	4.9	.14	3.6	3.9	18	.18	4.5	0.022	0.6	7.00	MW	C	N
0.156	3.96	B18-138	.44	11.1	.136	3.5	1.2	.20	.37	9.3	.42	1.9	.07	1.8	0.010	0.3	6.00	MW	C	GI
0.156	3.96	3726	.44	11.1	.124	3.1	4.3	.75	.26	6.7	1.1	5.0	.18	4.5	0.016	0.4	10.0	MW	C	Z
0.156	3.96	2942	.44	11.1	.116	2.9	18	3.2	.16	4.2	3.0	13	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.156	3.96	3729	.47	11.9	.130	3.3	2.2	.38	.30	7.5	.64	2.8	.12	3.1	0.013	0.3	8.50	HD	C	Z
0.156	3.96	2806	.47	11.9	.124	3.1	5.5	.96	.28	7.2	1.6	6.9	.15	3.8	0.016	0.4	8.25	MW	C	Z
0.156	3.96	S-497	.50	12.7	.144	3.7	.06	.01	.43	11	.03	.12	.07	1.7	0.006	0.2	10.0	SST	C	N
0.156	3.96	A10-42	.50	12.7	.138	3.5	.31	.05	.40	10	.12	.55	.10	2.6	0.009	0.2	10.5	SST	C	N
0.156	3.96	B18-128	.50	12.7	.136	3.5	1.3	.22	.22	5.5	.27	1.2	.06	1.6	0.010	0.3	5.25	SST	C	N
0.156	3.96	U-92	.50	12.7	.128	3.3	1.2	.21	.23	5.9	.28	1.3	.27	6.8	0.014	0.4	18.0	MW	C	Z
0.156	3.96	CC-18	.50	12.7	.124	3.1														




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.156	3.96	2916	.56	14.3	.116	2.9	11	1.9	.28	7.2	3.0	13	.23	5.9	0.020	0.5	10.6	MW	C	Z
0.156	3.96	906	.56	14.3	.110	2.8	19	3.3	.24	6.0	4.5	20	.28	7.0	0.023	0.6	11.0	MW	C	Z
0.156	3.96	3923	.56	14.3	.106	2.7	26	4.5	.14	3.6	3.6	16	.26	6.7	0.025	0.6	10.5	SST	CG	N
0.156	3.96	3982	.56	14.3	.106	2.7	25	4.4	.22	5.5	5.4	24	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.156	3.96	10074	.56	14.3	.104	2.6	36	6.3	.17	4.2	6.0	27	.27	6.8	0.026	0.7	10.3	MW	CG	Z
0.156	3.96	A15-42	.56	14.3	.102	2.6	47	8.3	.14	3.6	6.7	30	.26	6.5	0.027	0.7	9.50	MW	CG	GI
0.156	3.96	L-75	.56	14.3	.082	2.1	178	31	.06	1.6	11	50	.44	11.3	0.037	0.9	11.0	SPR	C	N
0.156	3.96	11112	.59	15.1	.128	3.3	2.5	.44	.29	7.4	.74	3.3	.14	3.5	0.014	0.4	8.75	SST	C	N
0.156	3.96	EE-51	.59	15.1	.116	2.9	11	2.0	.26	6.6	3.0	13	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.156	3.96	NN-66	.59	15.1	.110	2.8	14	2.5	.21	5.4	3.0	13	.31	7.9	0.023	0.6	12.5	SST	C	N
0.156	3.96	392	.63	15.9	.134	3.4	1.2	.21	.47	12	.57	2.5	.10	2.4	0.011	0.3	7.75	MW	C	Z
0.156	3.96	11404	.63	15.9	.130	3.3	2.3	.41	.40	10	.93	4.1	.12	3.0	0.013	0.3	8.00	MW	C	Z
0.156	3.96	GG-52	.63	15.9	.126	3.2	1.7	.30	.36	9.0	.61	2.7	.27	6.9	0.015	0.4	17.0	MW	C	N
0.156	3.96	10016	.63	15.9	.116	2.9	15	2.7	.20	5.0	3.0	13	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.156	3.96	GG-45	.63	15.9	.116	2.9	18	3.2	.16	4.2	3.0	13	.16	4.1	0.020	0.5	7.00	MW	C	N
0.156	3.96	S-704	.63	15.9	.112	2.8	11	2.0	.23	5.9	2.6	12	.30	7.7	0.022	0.6	12.8	SST	C	N
0.156	3.96	S-859	.63	15.9	.112	2.8	9.7	1.7	.27	6.8	2.6	12	.34	8.7	0.022	0.6	14.5	SST	C	N
0.156	3.96	S-1101	.63	15.9	.108	2.7	16	2.7	.22	5.5	3.4	15	.32	8.2	0.024	0.6	13.5	SST	CG	N
0.156	3.96	M-121	.66	16.7	.118	3.0	5.2	.91	.33	8.5	1.7	7.7	.32	8.2	0.019	0.5	16.0	MW	C	BO
0.156	3.96	B2-32	.67	17.1	.136	3.5	.39	.07	.52	13	.20	.89	.15	3.8	0.010	0.3	14.0	MW	C	N
0.156	3.96	U-17	.69	17.4	.126	3.2	1.9	.33	.45	12	.85	3.8	.23	5.7	0.015	0.4	14.0	SST	C	N
0.156	3.96	WW-23	.69	17.4	.124	3.1	1.9	.34	.39	9.9	.75	3.3	.30	7.5	0.016	0.4	17.5	SST	C	N
0.156	3.96	LL-82	.69	17.4	.118	3.0	7.9	1.4	.22	5.5	1.7	7.6	.21	5.3	0.019	0.5	10.0	SST	C	N
0.156	3.96	CC-90	.69	17.4	.116	2.9	6.1	1.1	.33	8.3	2.0	8.8	.30	7.6	0.020	0.5	15.0	SST	CG	N
0.156	3.96	S-1179	.69	17.4	.116	2.9	11	1.9	.19	4.8	2.0	8.8	.21	5.3	0.020	0.5	9.50	SST	C	N
0.156	3.96	H-57	.69	17.4	.112	2.8	11	1.9	.36	9.1	3.8	17	.33	8.4	0.022	0.6	15.0	MW	CG	N
0.156	3.96	LL-11	.69	17.4	.096	2.4	40	7.0	.15	3.9	6.1	27	.48	12.2	0.030	0.8	15.0	SST	C	N
0.156	3.96	W-34	.72	18.2	.118	3.0	3.8	.67	.37	9.3	1.4	6.3	.35	8.9	0.019	0.5	18.5	SST	CG	N
0.156	3.96	1837	.75	19.1	.140	3.6	.17	.03	.65	16	.11	.47	.10	2.6	0.008	0.2	13.0	MW	C	N
0.156	3.96	2505	.75	19.1	.136	3.5	.36	.06	.59	15	.21	.93	.16	4.1	0.010	0.3	15.0	MW	C	Z
0.156	3.96	PP-30	.75	19.1	.136	3.5	.31	.05	.57	14	.18	.78	.18	4.6	0.010	0.3	17.0	MW	C	N
0.156	3.96	JJ-84	.75	19.1	.124	3.1	2.5	.43	.48	12	1.2	5.2	.27	6.9	0.016	0.4	16.0	MW	C	GI
0.156	3.96	II-50	.75	19.1	.120	3.0	3.6	.63	.43	11	1.5	6.8	.32	8.2	0.018	0.5	18.0	MW	CG	Z
0.156	3.96	S-705	.75	19.1	.112	2.8	9.2	1.6	.29	7.3	2.6	12	.36	9.1	0.022	0.6	15.3	SST	C	N
0.156	3.96	KK-37	.75	19.1	.110	2.8	17	3.0	.26	6.7	4.5	20	.30	7.6	0.023	0.6	12.0	MW	C	GI
0.156	3.96	V-25	.81	20.6	.116	2.9	4.8	.84	.39	10	1.9	8.4	.42	10.7	0.020	0.5	21.0	MW	CG	Z
0.156	3.96	B7-6	.81	20.6	.116	2.9	5.0	.88	.39	9.8	1.9	8.6	.43	10.8	0.020	0.5	20.3	MW	C	Z
0.156	3.96	10313	.81	20.6	.100	2.5	26	4.6	.28	7.2	7.5	33	.50	12.8	0.028	0.7	18.0	MW	CG	GI
0.156	3.96	B15-67	.84	21.4	.132	3.4	.59	.10	.60	15	.35	1.6	.24	6.1	0.012	0.3	19.0	MW	C	N
0.156	3.96	CC-25	.88	22.2	.132	3.4	.74	.13	.68	17	.50	2.2	.20	5.0	0.012	0.3	15.5	MW	C	Z
0.156	3.96	II-45	.88	22.2	.132	3.4	.21	.04	.34	8.5	.07	.31	.54	13.7	0.012	0.3	44.0	SST	C	N
0.156	3.96	2658	.88	22.2	.130	3.3	.83	.14	.62	16	.51	2.3	.26	6.6	0.013	0.3	19.0	MW	C	GI
0.156	3.96	00-83	.88	22.2	.126	3.2	1.6	.28	.59	15	.96	4.3	.29	7.2	0.015	0.4	18.0	MW	C	N
0.156	3.96	3777	.88	22.2	.124	3.1	2.2	.39	.58	15	1.3	5.7	.30	7.5	0.016	0.4	17.5	MW	C	Z
0.156	3.96	V-31	.88	22.2	.118	3.0	3.4	.60	.47	12	1.6	7.1	.41	10.4	0.019	0.5	20.5	SST	C	N
0.156	3.96	1619	.88	22.2	.112	2.8	12	2.0	.34	8.6	3.9	18	.33	8.4	0.022	0.6	14.0	MW	C	Z
0.156	3.96	S-706	.88	22.2	.112	2.8	7.7	1.4	.34	8.6	2.6	12	.41	10.5	0.022	0.6	17.8	SST	C	N
0.156	3.96	00-17	.88	22.2	.096	2.4	45	7.8	.20	5.1	9.1	40	.48	12.2	0.030	0.8	15.0	MW	C	N
0.156	3.96	Y-48	.91	23.0	.106	2.7	21	3.6	.26	6.6	5.4	24	.38	9.5	0.025	0.6	14.0	MW	C	N
0.156	3.96	B15-20	.94	23.8	.102	2.6	27	4.8	.25	6.2	6.7	30	.41	10.3	0.027	0.7	15.0	MW	CG	Z
0.156	3.96	S-1165	.94	23.8	.096	2.4	25	4.4	.24	6.1	6.1	27	.66	16.8	0.030	0.8	22.0	SST	CG	N
0.156	3.96	393	1.00	25.4	.134	3.4	.73	.13	.78	20	.57	2.5	.14	3.5	0.011	0.3	11.5	MW	C	Z
0.156	3.96	356-A	1.00	25.4	.130	3.3	1.2	.22	.74	19	.93	4.1	.19	4.7	0.013	0.3	13.3	MW	C	Z
0.156	3.96	355-A	1.00	25.4	.128	3.3	1.6	.28	.72	18	1.2	5.1	.21	5.3	0.014	0.4	14.0	MW	C	Z
0.156	3.96	S-1025	1.00	25.4	.128	3.3	.99	.17	.72	18	.71	3.2	.28	7.1	0.014	0.4	19.0	SST	C	N
0.156	3.96	PP-7	1.00	25.4	.128	3.3	1.2	.21	.73	19	.88	3.9	.27	6.8	0.014	0.4	18.0	MW	C	N
0.156	3.96	157-A	1.00	25.4	.124	3.1	2.5	.45	.61	16	1.6	6.9	.26	6.7	0.016	0.4	15.5	MW	C	Z
0.156	3.96	TT-27	1.00	25.4	.124	3.1	1.4	.24	.55	14	.76	3.4	.45	11.4	0.016	0.4	27.0	MW	C	N
0.156	3.96	158-A	1.00	25.4	.100	2.5	23	4.0	.32	8.2	7.5	33	.60	15.1	0.028	0.7	20.3	MW	C	Z
0.156	3.96	2938	1.06	27.0	.136	3.5	.26	.04	.85	22	.22	.97	.21	5.3	0.010	0.3	20.0	MW	C	Z
0.156	3.96	A9-36	1.06	27.0	.126	3.2	1.4	.24	.63	16	.85	3.8	.30	7.6	0.015	0.4	19.0	SST	C	N
0.156	3.96	PP-18	1.25	31.8	.116	2.9	3.8	.67	.71	18	2.7	12	.54	13.7	0.020	0.5	26.0	MW	C	N
0.156	3.96	3823	1.25	31.8	.110	2.8	10	1.8	.45	11	4.5	20	.46	11.7	0.023	0.6	19.0	MW	C	GI
0.156	3.96	S-1318	1.25	31.8	.094	2.4	21	3.7	.32	8.0	6.7	30	.93	23.6	0.031	0.8	30.0	SST	CG	N
0.156	3.96	907	1.25	31.8	.086	2.2	68	12	.20	5.0	13	59	.74	18.7	0.035	0.9	20.0	MW	C	Z
0.156	3.96	B9-47	1.25	31.8	.084	2.1	53	9.2	.20	5.0	10	46	1.03	26.1	0.036	0.9	28.5	SPR	CG	Z
0.156	3.96	JJ-48	1.34	34.1	.118	3.0	2.9	.51	.81	21	2.4	11	.53	13.5	0.019	0.5	27.0	MW	C	N
0.156	3.96	356-B	1.38	34.9	.130	3.3	.89	.16	1.0	26	.93	4.1	.24	6.2	0.013	0.3	17.8	MW	C	Z
0.156	3.96	355-B	1.38	34.9	.128	3.3	1.2	.20	1.0	26	1.2	5.1	.28	7.0	0.014	0.4	18.8			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.156	3.96	157-C	1.75	44.5	.124	3.1	1.4	.25	1.1	28	1.6	6.9	.43	11.0	0.016	0.4	26.0	MW	C	Z
0.156	3.96	0-114	1.75	44.5	.102	2.6	9.8	1.7	.46	12	4.5	20	.93	23.7	0.027	0.7	33.5	SST	C	N
0.156	3.96	158-C	1.75	44.5	.100	2.5	13	2.2	.59	15	7.5	33	1.02	25.8	0.028	0.7	35.3	MW	C	Z
0.156	3.96	1575	2.88	73.0	.126	3.2	.25	.04	1.3	33	.32	1.4	1.59	40.4	0.015	0.4	105.0	MW	C	Z
0.156	3.96	10851	3.31	84.1	.110	2.8	3.7	.64	.82	21	3.0	13	1.02	26.0	0.023	0.6	43.5	SST	C	N
0.156	3.96	A10-63	3.75	95.3	.110	2.8	3.3	.57	.92	23	3.0	13	1.14	28.9	0.023	0.6	48.5	SST	C	N
0.158	4.01	10242	.75	19.1	.116	2.9	14	2.4	.25	6.4	3.4	15	.23	5.9	0.021	0.5	10.0	MW	C	Z
0.168	4.27	12749	.47	11.9	.120	3.0	21	3.7	.22	5.5	4.6	21	.25	6.4	0.024	0.6	9.50	MW	C	N
0.172	4.37	S-1093	.19	4.8	.152	3.9	1.2	.21	.13	3.4	.16	.70	.06	1.4	0.010	0.3	4.50	SST	C	N
0.172	4.37	L-80	.19	4.8	.140	3.6	8.3	1.4	.09	2.3	.76	3.4	.10	2.4	0.016	0.4	5.00	MW	C	N
0.172	4.37	M-31	.19	4.8	.114	2.9	103	18	.04	1.1	4.4	19	.15	3.7	0.029	0.7	5.00	SST	CG	N
0.172	4.37	BB-45	.22	5.6	.136	3.5	13	2.3	.10	2.5	1.3	5.9	.09	2.2	0.018	0.5	4.75	SST	CG	N
0.172	4.37	KK-23	.25	6.4	.144	3.7	5.6	.98	.17	4.4	.97	4.3	.08	2.0	0.014	0.4	4.50	MW	C	N
0.172	4.37	B5-8	.25	6.4	.140	3.6	9.9	1.7	.14	3.6	1.4	6.3	.07	1.8	0.016	0.4	4.50	MW	CG	N
0.172	4.37	CC-37	.25	6.4	.132	3.4	16	2.8	.11	2.8	1.8	8.1	.13	3.3	0.020	0.5	5.50	SST	C	N
0.172	4.37	B-17	.25	6.4	.116	2.9	64	11	.05	1.4	3.5	15	.20	5.0	0.028	0.7	6.00	SST	C	N
0.172	4.37	J-43	.25	6.4	.116	2.9	118	21	.06	1.5	6.9	30	.15	3.9	0.028	0.7	4.50	MW	C	N
0.172	4.37	AA-77	.25	6.4	.112	2.8	136	24	.06	1.6	8.4	37	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.172	4.37	NN-82	.28	7.1	.156	4.0	.24	.04	.21	5.4	.05	.23	.07	1.7	0.008	0.2	7.50	MW	C	N
0.172	4.37	Y-92	.28	7.1	.136	3.5	12	2.1	.16	4.2	1.9	8.6	.12	3.0	0.018	0.5	5.50	MW	C	N
0.172	4.37	W-1	.28	7.1	.108	2.7	136	24	.05	1.3	6.7	30	.18	4.5	0.032	0.8	5.50	SST	CG	N
0.172	4.37	A9-24	.31	7.9	.148	3.8	3.6	.64	.18	4.7	.67	3.0	.06	1.5	0.012	0.3	4.00	MW	C	N
0.172	4.37	00-38	.31	7.9	.148	3.8	1.5	.25	.23	5.8	.33	1.5	.08	2.1	0.012	0.3	7.00	MW	CG	N
0.172	4.37	A14-10	.31	7.9	.140	3.6	8.3	1.4	.17	4.4	1.4	6.3	.08	2.0	0.016	0.4	5.00	MW	CG	N
0.172	4.37	S-1202	.31	7.9	.128	3.3	17	3.0	.14	3.5	2.4	10	.18	4.5	0.022	0.6	7.00	SST	C	N
0.172	4.37	A11-22	.31	7.9	.126	3.2	32	5.7	.13	3.2	4.1	18	.13	3.4	0.023	0.6	5.75	MW	CG	GI
0.172	4.37	A15-19	.34	8.7	.140	3.6	6.2	1.1	.23	5.8	1.4	6.3	.11	2.8	0.016	0.4	6.00	MW	CG	N
0.172	4.37	B18-127	.34	8.7	.136	3.5	6.9	1.2	.22	5.5	1.5	6.6	.13	3.2	0.018	0.5	6.00	MW	O	N
0.172	4.37	10768	.34	8.7	.122	3.1	51	8.8	.10	2.5	4.9	22	.16	4.1	0.025	0.6	5.50	MW	C	N
0.172	4.37	N-301	.34	8.7	.120	3.0	62	11	.06	1.5	3.7	16	.16	4.0	0.026	0.7	5.00	SST	C	N
0.172	4.37	GG-37	.34	8.7	.102	2.6	122	21	.06	1.6	7.7	34	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.172	4.37	12654	.34	8.7	.142	3.6	4.7	.82	.24	6.1	1.1	5.0	.11	2.7	0.015	0.4	6.00	MW	C	N
0.172	4.37	00-30	.38	9.5	.148	3.8	1.1	.18	.27	6.8	.28	1.3	.11	2.7	0.012	0.3	8.00	SST	C	N
0.172	4.37	JJ-41	.38	9.5	.138	3.5	6.4	1.1	.24	6.1	1.5	6.9	.14	3.5	0.017	0.4	7.00	MW	C	Z
0.172	4.37	JJ-50	.38	9.5	.132	3.4	15	2.5	.13	3.2	1.8	8.1	.14	3.6	0.020	0.5	6.00	SST	C	N
0.172	4.37	0-71	.38	9.5	.132	3.4	13	2.3	.21	5.3	2.7	12	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.172	4.37	AA-3	.38	9.5	.122	3.1	44	7.7	.11	2.8	4.9	22	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.172	4.37	DD-2	.38	9.5	.108	2.7	96	17	.07	1.8	6.7	30	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.172	4.37	J-95	.41	10.3	.142	3.6	2.4	.41	.24	6.1	.57	2.5	.17	4.2	0.015	0.4	10.0	MW	C	Z
0.172	4.37	NN-18	.41	10.3	.142	3.6	2.5	.44	.26	6.7	.66	2.9	.14	3.6	0.015	0.4	9.50	MW	CG	N
0.172	4.37	NN-63	.41	10.3	.126	3.2	20	3.5	.20	5.1	4.0	18	.21	5.3	0.023	0.6	8.00	MW	C	N
0.172	4.37	B5-21	.41	10.3	.120	3.0	42	7.4	.13	3.3	5.5	25	.21	5.3	0.026	0.7	7.00	MW	C	N
0.172	4.37	B-56	.41	10.3	.116	2.9	66	11	.07	1.8	4.6	20	.20	5.0	0.028	0.7	6.00	SST	C	N
0.172	4.37	EE-85	.41	10.3	.112	2.8	74	13	.11	2.9	8.4	37	.26	6.5	0.030	0.8	7.50	MW	C	N
0.172	4.37	J-3	.41	10.3	.096	2.4	208	36	.05	1.4	11	50	.30	7.7	0.038	1.0	8.00	SPR	CG	Z
0.172	4.37	12642	.42	10.7	.112	2.8	59	10	.09	2.4	5.6	25	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.172	4.37	S-1463	.44	11.1	.160	4.1	.06	.01	.38	9.8	.02	.10	.05	1.4	0.006	0.2	8.00	SST	C	N
0.172	4.37	I-6	.44	11.1	.152	3.9	.16	.03	.20	5.0	.03	.14	.24	6.1	0.010	0.3	23.0	MW	C	BO
0.172	4.37	3795	.44	11.1	.144	3.7	2.0	.35	.31	7.9	.62	2.8	.13	3.2	0.014	0.4	9.00	MW	CG	Z
0.172	4.37	JJ-66	.44	11.1	.136	3.5	3.4	.60	.21	5.4	.73	3.2	.23	5.7	0.018	0.5	12.5	SST	CG	N
0.172	4.37	B5-5	.44	11.1	.136	3.5	7.2	1.3	.28	7.1	2.0	8.9	.16	4.0	0.018	0.5	7.75	MW	C	N
0.172	4.37	NN-23	.44	11.1	.134	3.4	11	2.0	.14	3.5	1.6	7.0	.13	3.4	0.019	0.5	6.00	SST	C	N
0.172	4.37	FF-74	.44	11.1	.132	3.4	9.4	1.6	.24	6.0	2.2	9.9	.20	5.1	0.020	0.5	9.00	MW	C	Z
0.172	4.37	M-1	.44	11.1	.132	3.4	8.2	1.4	.22	5.5	1.8	7.9	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.172	4.37	00-65	.44	11.1	.132	3.4	14	2.5	.19	4.9	2.7	12	.22	5.6	0.020	0.5	9.00	MW	C	Z
0.172	4.37	U-57	.44	11.1	.132	3.4	11	2.0	.16	4.1	1.8	8.1	.16	4.1	0.020	0.5	7.00	SST	C	N
0.172	4.37	V-47	.44	11.1	.132	3.4	4.8	.85	.14	3.5	.67	3.0	.30	7.6	0.020	0.5	14.0	SST	C	N
0.172	4.37	A14-2	.44	11.1	.122	3.1	26	4.6	.13	3.2	3.3	15	.20	5.1	0.025	0.6	8.00	SST	CG	N
0.172	4.37	AA-45	.44	11.1	.118	3.0	44	7.6	.09	2.4	4.1	18	.22	5.5	0.027	0.7	7.00	SST	C	N
0.172	4.37	TT-7	.44	11.1	.112	2.8	68	12	.12	3.1	8.4	37	.27	6.9	0.030	0.8	8.00	MW	C	Z
0.172	4.37	12528	.45	11.5	.124	3.1	16	2.9	.17	4.2	2.7	12	.29	7.3	0.024	0.6	11.0	MW	C	N
0.172	4.37	A12-19	.45	11.5	.122	3.1	22	3.9	.18	4.5	3.9	17	.28	7.0	0.025	0.6	10.0	MW	C	N
0.172	4.37	LL-45	.47	11.9	.146	3.7	1.0	.18	.32	8.1	.33	1.5	.15	3.8	0.013	0.3	10.5	SST	C	N
0.172	4.37	0-120	.47	11.9	.136	3.5	14	2.4	.15	3.7	2.0	8.9	.11	2.7	0.018	0.5	5.00	MW	C	Z
0.172	4.37	12485	.47	11.9	.122	3.1	20	3.4	.17	4.3	3.3	15	.30	7.6	0.025	0.6	11.0	MW	C	N
0.172	4.37	HH-24	.47	11.9	.112	2.8	51	8.9	.16	4.2	8.4	37	.30	7.6	0.030	0.8	10.0	MW	CG	Z
0.172	4.37	KK-19	.50	12.7	.152	3.9	.30	.05	.37	9.4	.11	.49	.13	3.3	0.010	0.3	12.0	SST	C	N
0.172	4.37	A-9	.50	12.7	.148	3.8	.67	.12	.35	8.9	.23	1.0	.15	3.8	0.012	0.3	11.5	SST	C	N
0.172	4.37	DD-25	.50	12.7	.144	3.7	3.0	.53	.22	5.6	.67	3.0	.10	2.5	0.014	0.4	6.00	SST	C	N
0.172	4.37	PP-83	.50	12.7	.142	3.6	3.1	.55	.37	9.3	1.1									




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.172	4.37	A14-24	.53	13.5	.108	2.7	65	11	.16	3.9	10	45	.34	8.5	0.032	0.8	10.5	MW	CG	GI
0.172	4.37	S-332	.56	14.3	.152	3.9	.27	.05	.42	11	.11	.50	.14	3.6	0.010	0.3	13.0	SST	C	N
0.172	4.37	CC-41	.56	14.3	.148	3.8	.37	.07	.32	8.2	.12	.53	.24	6.1	0.012	0.3	19.0	SST	C	N
0.172	4.37	DD-19	.56	14.3	.148	3.8	.97	.17	.44	11	.42	1.9	.13	3.2	0.012	0.3	9.50	MW	C	N
0.172	4.37	B-8	.56	14.3	.132	3.4	4.6	.80	.25	6.4	1.1	5.1	.31	7.9	0.020	0.5	14.5	SST	C	N
0.172	4.37	K-75	.56	14.3	.120	3.0	22	3.9	.24	6.0	5.3	23	.33	8.3	0.026	0.7	11.5	MW	C	N
0.172	4.37	F-17	.56	14.3	.120	3.0	26	4.6	.21	5.3	5.5	25	.29	7.3	0.026	0.7	10.0	MW	C	Z
0.172	4.37	S-142	.56	14.3	.108	2.7	48	8.4	.14	3.6	6.7	30	.38	9.8	0.032	0.8	12.0	SST	CG	N
0.172	4.37	S-900	.59	15.1	.156	4.0	.13	.02	.50	13	.07	.30	.09	2.4	0.008	0.2	10.7	SST	C	N
0.172	4.37	10265	.59	15.1	.152	3.9	.56	.10	.50	13	.28	1.3	.09	2.3	0.010	0.3	8.00	MW	C	N
0.172	4.37	B15-47	.59	15.1	.136	3.5	5.2	.90	.39	9.9	2.0	8.9	.20	5.0	0.018	0.5	10.0	MW	C	N
0.172	4.37	U-96	.59	15.1	.132	3.4	8.2	1.4	.33	8.5	2.7	12	.20	5.1	0.020	0.5	10.0	MW	CG	N
0.172	4.37	FF-39	.59	15.1	.120	3.0	16	2.7	.21	5.3	3.3	15	.38	9.7	0.026	0.7	13.8	SST	C	N
0.172	4.37	S-487	.59	15.1	.114	2.9	30	5.3	.17	4.3	5.1	23	.38	9.6	0.029	0.7	12.0	SST	C	N
0.172	4.37	W-67	.59	15.1	.088	2.2	226	40	.07	1.7	15	65	.46	11.7	0.042	1.1	11.0	SPR	CG	N
0.172	4.37	L-28	.63	15.9	.144	3.7	1.2	.20	.42	11	.48	2.2	.21	5.3	0.014	0.4	14.0	MW	C	N
0.172	4.37	A14-18	.63	15.9	.136	3.5	6.7	1.2	.20	5.1	1.3	5.9	.14	3.4	0.018	0.5	7.50	SST	CG	N
0.172	4.37	S-835	.63	15.9	.136	3.5	2.8	.48	.34	8.6	.93	4.1	.29	7.3	0.018	0.5	15.0	SST	C	N
0.172	4.37	J-44	.63	15.9	.128	3.3	14	2.5	.25	6.4	3.6	16	.22	5.6	0.022	0.6	9.00	MW	C	Z
0.172	4.37	AA-65	.63	15.9	.122	3.1	14	2.4	.23	5.7	3.1	14	.40	10.2	0.025	0.6	15.0	MW	C	Z
0.172	4.37	A15-17	.63	15.9	.120	3.0	23	4.1	.24	6.0	5.5	25	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.172	4.37	2520	.63	15.9	.118	3.0	36	6.3	.17	4.4	6.2	27	.27	6.9	0.027	0.7	9.00	MW	C	Z
0.172	4.37	N-109	.63	15.9	.112	2.8	37	6.5	.15	3.8	5.6	25	.35	8.8	0.030	0.8	11.5	SST	CG	N
0.172	4.37	B5-4	.66	16.7	.130	3.3	8.8	1.5	.36	9.1	3.2	14	.24	6.0	0.021	0.5	11.3	MW	CG	N
0.172	4.37	S-220	.66	16.7	.120	3.0	14	2.5	.24	6.1	3.4	15	.42	10.6	0.026	0.7	15.0	SST	C	N
0.172	4.37	DD-58	.66	16.7	.112	2.8	52	9.0	.11	2.8	5.6	25	.27	6.9	0.030	0.8	9.00	SST	CG	N
0.172	4.37	FF-38	.66	16.7	.112	2.8	34	6.0	.16	4.1	5.6	25	.38	9.5	0.030	0.8	12.5	SST	CG	N
0.172	4.37	S-1227	.69	17.4	.132	3.4	3.4	.59	.29	7.3	.96	4.3	.40	10.2	0.020	0.5	19.0	SST	C	N
0.172	4.37	BB-33	.69	17.4	.132	3.4	3.8	.66	.33	8.3	1.2	5.5	.36	9.1	0.020	0.5	17.0	SST	C	N
0.172	4.37	11364	.69	17.4	.132	3.4	5.3	.92	.34	8.7	1.8	8.1	.28	7.1	0.020	0.5	13.0	SST	C	N
0.172	4.37	FF-17	.69	17.4	.128	3.3	11	1.9	.22	5.6	2.4	11	.24	6.1	0.022	0.6	10.0	SST	C	N
0.172	4.37	L-93	.72	18.2	.128	3.3	8.1	1.4	.38	9.7	3.1	14	.34	8.5	0.022	0.6	14.3	MW	C	Z
0.172	4.37	B7-48	.72	18.2	.122	3.1	17	3.0	.29	7.3	4.9	22	.31	7.8	0.025	0.6	12.3	MW	CG	N
0.172	4.37	B-13	.72	18.2	.120	3.0	16	2.8	.23	5.9	3.7	16	.38	9.6	0.026	0.7	13.5	SST	C	N
0.172	4.37	PP-22	.72	18.2	.098	2.5	108	19	.09	2.3	9.7	43	.44	11.3	0.037	0.9	11.0	SST	C	N
0.172	4.37	PP-26	.75	19.1	.156	4.0	.13	.02	.65	16	.09	.38	.10	2.6	0.008	0.2	12.0	MW	C	N
0.172	4.37	WW-31	.75	19.1	.146	3.7	.89	.16	.58	15	.52	2.3	.17	4.3	0.013	0.3	12.0	SST	C	N
0.172	4.37	S-1069	.75	19.1	.144	3.7	.87	.15	.51	13	.45	2.0	.24	6.0	0.014	0.4	16.0	SST	C	N
0.172	4.37	11457	.75	19.1	.144	3.7	1.6	.27	.43	11	.67	3.0	.15	3.9	0.014	0.4	10.0	SST	C	N
0.172	4.37	O-110	.75	19.1	.142	3.6	2.4	.41	.50	13	1.2	5.2	.15	3.8	0.015	0.4	10.0	MW	CG	N
0.172	4.37	3582	.75	19.1	.140	3.6	2.3	.40	.53	13	1.2	5.3	.22	5.7	0.016	0.4	13.0	MW	C	GI
0.172	4.37	MM-21	.75	19.1	.140	3.6	1.8	.31	.51	13	.90	4.0	.24	6.1	0.016	0.4	14.0	MW	O	Z
0.172	4.37	KK-15	.75	19.1	.132	3.4	6.7	1.2	.27	6.9	1.8	8.1	.23	5.8	0.020	0.5	10.5	SST	C	N
0.172	4.37	A12-26	.75	19.1	.132	3.4	5.5	.96	.45	11	2.5	11	.30	7.6	0.020	0.5	14.0	MW	C	Z
0.172	4.37	B-75	.75	19.1	.130	3.3	8.1	1.4	.39	9.9	3.2	14	.27	6.9	0.021	0.5	12.0	MW	C	Z
0.172	4.37	J-93	.75	19.1	.090	2.3	139	24	.10	2.5	14	61	.62	15.6	0.041	1.0	15.0	SPR	CG	N
0.172	4.37	AA-29	.78	19.8	.152	3.9	.38	.07	.66	17	.25	1.1	.12	3.0	0.010	0.3	11.0	MW	C	Z
0.172	4.37	A15-11	.78	19.8	.140	3.6	3.1	.54	.46	12	1.4	6.3	.18	4.5	0.016	0.4	10.0	MW	C	N
0.172	4.37	B10-38	.81	20.6	.152	3.9	.29	.05	.67	17	.20	.87	.15	3.7	0.010	0.3	13.5	MW	C	N
0.172	4.37	W-36	.84	21.4	.110	2.8	43	7.5	.21	5.4	9.2	41	.43	11.0	0.031	0.8	13.0	MW	C	N
0.172	4.37	G-56	.88	22.2	.142	3.6	1.3	.24	.62	16	.83	3.7	.26	6.5	0.015	0.4	16.0	MW	C	N
0.172	4.37	1829	.88	22.2	.140	3.6	1.8	.31	.60	15	1.1	4.8	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.172	4.37	B-59	.88	22.2	.138	3.5	2.3	.40	.59	15	1.3	6.0	.29	7.3	0.017	0.4	16.0	MW	C	N
0.172	4.37	G-38	.88	22.2	.130	3.3	4.8	.84	.46	12	2.2	9.7	.42	10.7	0.021	0.5	19.0	MW	C	Z
0.172	4.37	10186	.88	22.2	.128	3.3	8.3	1.5	.43	11	3.6	16	.33	8.4	0.022	0.6	14.0	MW	C	Z
0.172	4.37	V-56	.88	22.2	.128	3.3	5.9	1.0	.44	11	2.6	11	.44	11.2	0.022	0.6	19.0	MW	C	N
0.172	4.37	S-1693	.89	22.6	.124	3.1	9.8	1.7	.31	8.0	3.1	14	.36	9.1	0.024	0.6	15.0	SST	CG	N
0.172	4.37	00-42	.94	23.8	.140	3.6	2.1	.36	.69	17	1.4	6.3	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.172	4.37	Z-79	.94	23.8	.108	2.7	37	6.4	.18	4.7	6.7	30	.51	13.0	0.032	0.8	15.0	SST	C	N
0.172	4.37	J-9	1.00	25.4	.150	3.8	.27	.05	.79	20	.22	.96	.21	5.3	0.011	0.3	18.0	SST	C	N
0.172	4.37	00-81	1.00	25.4	.148	3.8	.73	.13	.84	21	.61	2.7	.16	4.0	0.012	0.3	12.0	MW	C	BO
0.172	4.37	S-1077	1.00	25.4	.136	3.5	3.6	.63	.37	9.4	1.3	5.9	.23	5.9	0.018	0.5	12.0	SST	C	N
0.172	4.37	S-1346	1.00	25.4	.132	3.4	4.4	.77	.41	11	1.8	8.1	.32	8.1	0.020	0.5	15.0	SST	C	N
0.172	4.37	A12-28	1.00	25.4	.120	3.0	13	2.3	.42	11	5.5	25	.49	12.5	0.026	0.7	18.0	MW	C	N
0.172	4.37	B2-36	1.00	25.4	.118	3.0	24	4.2	.26	6.6	6.2	27	.37	9.3	0.027	0.7	12.5	MW	C	Z
0.172	4.37	10635	1.00	25.4	.102	2.6	59	10	.15	3.8	8.9	40	.60	15.3	0.035	0.9	16.3	SPR	C	N
0.172	4.37	GG-31	1.06	27.0	.108	2.7	27	4.7	.27	6.9	7.2	32	.72	18.3	0.032	0.8	22.5	SPR	CG	N
0.172	4.37	A15-12	1.09	27.8	.106	2.7	39	6.8	.19	4.8	7.3	33	.54	13.8	0.033	0.8	16.5	SST	CG	N
0.172	4.37	JJ-31	1.09	27.8	.102	2.6	37	6.6	.22	5.7	8.3	37	.75	19.1	0.035	0.9	21.5	SST	CG	N</




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.172	4.37	Q-79	1.38	34.9	.142	3.6	.72	.13	.94	24	.68	3.0	.44	11.0	0.015	0.4	28.0	MW	C	N
0.172	4.37	LL-74	1.50	38.1	.128	3.3	3.1	.54	.77	20	2.4	11	.68	17.3	0.022	0.6	30.0	SST	C	N
0.172	4.37	10261	1.56	39.7	.122	3.1	5.9	1.0	.74	19	4.3	19	.83	21.0	0.025	0.6	32.0	MW	C	Z
0.172	4.37	10859	1.75	44.5	.102	2.6	39	6.9	.21	5.4	8.3	37	.74	18.7	0.035	0.9	21.0	SST	CG	N
0.172	4.37	Y-61	1.94	49.2	.136	3.5	.92	.16	1.2	30	1.1	4.8	.76	19.2	0.018	0.5	41.0	SST	C	N
0.172	4.37	B15-41	2.25	57.2	.156	4.0	.07	.01	2.1	53	.15	.69	.17	4.3	0.008	0.2	20.0	MW	C	N
0.172	4.37	B18-185	2.50	63.5	.122	3.1	5.1	.88	.98	25	4.9	22	.93	23.5	0.025	0.6	37.0	MW	CG	Z
0.172	4.37	Y-64	2.75	69.9	.116	2.9	4.3	.75	.99	25	4.2	19	1.76	44.8	0.028	0.7	62.0	SST	C	N
0.172	4.37	S-3214	2.91	73.8	.134	3.4	1.1	.18	1.5	38	1.6	7.0	.89	22.7	0.019	0.5	46.0	SST	O	N
0.172	4.37	3968	3.00	76.2	.118	3.0	4.3	.75	1.3	34	5.7	26	1.66	42.2	0.027	0.7	60.5	MW	C	N
0.172	4.37	B15-44	3.19	81.0	.146	3.7	.33	.06	2.6	65	.85	3.8	.44	11.2	0.013	0.3	33.0	MW	C	N
0.172	4.37	FF-48	3.25	82.6	.152	3.9	.08	.01	2.8	72	.24	1.1	.43	10.9	0.010	0.3	42.0	MW	C	N
0.175	4.45	B3-49	.47	11.9	.103	2.6	98	17	.09	2.3	8.9	40	.36	9.1	0.036	0.9	10.0	SST	CG	N
0.180	4.57	70244	.25	6.4	.156	4.0	3.6	.63	.18	4.5	.64	2.8	.05	1.1	0.012	0.3	3.75	MW	CG	N
0.180	4.57	70244S	.25	6.4	.156	4.0	3.1	.55	.13	3.3	.41	1.8	.05	1.1	0.012	0.3	3.75	SST	CG	N
0.180	4.57	70259	.25	6.4	.152	3.9	6.0	1.1	.17	4.2	1.0	4.5	.06	1.4	0.014	0.4	4.00	MW	CG	N
0.180	4.57	70259S	.25	6.4	.152	3.9	5.2	.92	.12	3.1	.64	2.9	.06	1.4	0.014	0.4	4.00	SST	CG	N
0.180	4.57	70280	.25	6.4	.148	3.8	9.0	1.6	.15	3.9	1.4	6.0	.07	1.8	0.016	0.4	4.38	MW	CG	N
0.180	4.57	70280S	.25	6.4	.148	3.8	7.6	1.3	.12	3.0	.90	4.0	.07	1.8	0.016	0.4	4.38	SST	CG	N
0.180	4.57	70301	.25	6.4	.144	3.7	14	2.4	.14	3.6	1.9	8.5	.08	2.1	0.018	0.5	4.63	MW	CG	N
0.180	4.57	70301S	.25	6.4	.144	3.7	11	2.0	.11	2.8	1.3	5.7	.08	2.1	0.018	0.5	4.63	SST	CG	N
0.180	4.57	70322	.25	6.4	.140	3.6	21	3.7	.12	3.2	2.6	12	.09	2.3	0.020	0.5	4.63	MW	CG	N
0.180	4.57	70322S	.25	6.4	.140	3.6	18	3.1	.10	2.5	1.7	7.7	.09	2.3	0.020	0.5	4.63	SST	CG	N
0.180	4.57	70343	.25	6.4	.136	3.5	30	5.2	.12	3.0	3.5	15	.11	2.7	0.022	0.6	4.88	MW	CG	N
0.180	4.57	70343S	.25	6.4	.136	3.5	25	4.4	.09	2.3	2.3	10	.11	2.7	0.022	0.6	4.88	SST	CG	N
0.180	4.57	A12-37	.25	6.4	.136	3.5	30	5.2	.08	2.0	2.3	10	.10	2.5	0.022	0.6	4.50	SST	CG	N
0.180	4.57	70363	.25	6.4	.132	3.4	43	7.6	.10	2.6	4.5	20	.12	3.0	0.024	0.6	4.88	MW	CG	N
0.180	4.57	70363S	.25	6.4	.132	3.4	37	6.4	.08	2.1	3.0	13	.12	3.0	0.024	0.6	4.88	SST	CG	N
0.180	4.57	70386	.25	6.4	.128	3.3	59	10	.09	2.3	5.3	24	.13	3.3	0.026	0.7	5.00	MW	CG	N
0.180	4.57	70386S	.25	6.4	.128	3.3	50	8.8	.07	1.8	3.6	16	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.180	4.57	70407	.25	6.4	.122	3.1	95	17	.08	1.9	7.3	32	.15	3.8	0.029	0.7	5.13	MW	CG	N
0.180	4.57	70407S	.25	6.4	.122	3.1	81	14	.06	1.5	4.9	22	.15	3.8	0.029	0.7	5.13	SST	CG	N
0.180	4.57	B4-67	.30	7.5	.152	3.9	2.8	.50	.20	5.0	.55	2.5	.10	2.6	0.014	0.4	6.25	MW	C	N
0.180	4.57	70245	.31	7.9	.156	4.0	3.0	.52	.22	5.5	.64	2.8	.05	1.3	0.012	0.3	4.13	MW	CG	N
0.180	4.57	70245S	.31	7.9	.156	4.0	2.6	.45	.16	4.0	.41	1.8	.05	1.3	0.012	0.3	4.13	SST	CG	N
0.180	4.57	70260	.31	7.9	.152	3.9	4.8	.85	.21	5.3	1.0	4.5	.06	1.6	0.014	0.4	4.50	MW	CG	N
0.180	4.57	70260S	.31	7.9	.152	3.9	4.2	.74	.15	3.9	.64	2.9	.06	1.6	0.014	0.4	4.50	SST	CG	N
0.180	4.57	70281	.31	7.9	.148	3.8	7.5	1.3	.18	4.6	1.4	6.0	.08	2.0	0.016	0.4	4.88	MW	CG	N
0.180	4.57	70281S	.31	7.9	.148	3.8	6.4	1.1	.14	3.6	.90	4.0	.08	2.0	0.016	0.4	4.88	SST	CG	N
0.180	4.57	70302	.31	7.9	.144	3.7	11	2.0	.17	4.4	1.9	8.5	.09	2.3	0.018	0.5	5.13	MW	CG	N
0.180	4.57	70302S	.31	7.9	.144	3.7	9.5	1.7	.13	3.4	1.3	5.7	.09	2.3	0.018	0.5	5.13	SST	CG	N
0.180	4.57	70323	.31	7.9	.140	3.6	16	2.8	.16	4.1	2.6	12	.11	2.8	0.020	0.5	5.50	MW	CG	N
0.180	4.57	70323S	.31	7.9	.140	3.6	14	2.4	.13	3.2	1.7	7.7	.11	2.8	0.020	0.5	5.50	SST	CG	N
0.180	4.57	70344	.31	7.9	.136	3.5	24	4.2	.15	3.7	3.5	15	.12	3.1	0.022	0.6	5.63	MW	CG	N
0.180	4.57	70344S	.31	7.9	.136	3.5	20	3.6	.11	2.9	2.3	10	.12	3.1	0.022	0.6	5.63	SST	CG	N
0.180	4.57	70364	.31	7.9	.132	3.4	33	5.7	.14	3.5	4.5	20	.14	3.6	0.024	0.6	5.88	MW	CG	N
0.180	4.57	70364S	.31	7.9	.132	3.4	28	4.9	.11	2.7	3.0	13	.14	3.6	0.024	0.6	5.88	SST	CG	N
0.180	4.57	70387	.31	7.9	.128	3.3	47	8.2	.11	2.9	5.3	24	.15	3.9	0.026	0.7	5.88	MW	CG	N
0.180	4.57	70387S	.31	7.9	.128	3.3	40	7.0	.09	2.3	3.6	16	.15	3.9	0.026	0.7	5.88	SST	CG	N
0.180	4.57	70408	.31	7.9	.122	3.1	74	13	.10	2.5	7.3	32	.17	4.4	0.029	0.7	6.00	MW	CG	N
0.180	4.57	70408S	.31	7.9	.122	3.1	62	11	.08	2.0	4.9	22	.17	4.4	0.029	0.7	6.00	SST	CG	N
0.180	4.57	70426	.31	7.9	.116	2.9	122	21	.08	2.0	9.7	43	.18	4.7	0.032	0.8	5.75	MW	CG	N
0.180	4.57	70426S	.31	7.9	.116	2.9	104	18	.06	1.6	6.5	29	.18	4.7	0.032	0.8	5.75	SST	CG	N
0.180	4.57	70246	.38	9.7	.156	4.0	2.3	.40	.28	7.1	.64	2.8	.06	1.4	0.012	0.3	4.75	MW	CG	N
0.180	4.57	70246S	.38	9.7	.156	4.0	2.0	.35	.20	5.2	.41	1.8	.06	1.4	0.012	0.3	4.75	SST	CG	N
0.180	4.57	70261	.38	9.7	.152	3.9	3.9	.68	.26	6.6	1.0	4.5	.07	1.8	0.014	0.4	5.13	MW	CG	N
0.180	4.57	70261S	.38	9.7	.152	3.9	3.4	.59	.19	4.9	.64	2.9	.07	1.8	0.014	0.4	5.13	SST	CG	N
0.180	4.57	70282	.38	9.7	.148	3.8	6.0	1.0	.23	5.8	1.4	6.0	.09	2.3	0.016	0.4	5.63	MW	CG	N
0.180	4.57	70282S	.38	9.7	.148	3.8	5.1	.89	.18	4.5	.90	4.0	.09	2.3	0.016	0.4	5.63	SST	CG	N
0.180	4.57	70303	.38	9.7	.144	3.7	9.2	1.6	.21	5.3	1.9	8.5	.11	2.7	0.018	0.5	5.88	MW	CG	N
0.180	4.57	70303S	.38	9.7	.144	3.7	7.8	1.4	.16	4.2	1.3	5.7	.11	2.7	0.018	0.5	5.88	SST	CG	N
0.180	4.57	70324	.38	9.7	.140	3.6	13	2.3	.20	5.1	2.6	12	.13	3.2	0.020	0.5	6.38	MW	CG	N
0.180	4.57	70324S	.38	9.7	.140	3.6	11	1.9	.16	4.0	1.7	7.7	.13	3.2	0.020	0.5	6.38	SST	CG	N
0.180	4.57	70345	.38	9.7	.136	3.5	20	3.5	.17	4.4	3.5	15	.14	3.5	0.022	0.6	6.25	MW	CG	N
0.180	4.57	70345S	.38	9.7	.136	3.5	17	3.0	.14	3.5	2.3	10	.14	3.5	0.022	0.6	6.25	SST	CG	N
0.180	4.57	70365	.38	9.7	.132	3.4	26	4.6	.17	4.3	4.5	20	.17	4.2	0.024	0.6	6.88	MW	CG	N
0.180	4.57	70365S	.38	9.7	.132	3.4	22	3.9	.13	3.4	3.0	13	.17	4.2	0.024	0.6	6.88	SST	CG	N
0.180	4.57	70388	.38	9.7	.128	3.3	37	6.5	.14	3.6	5.3	24	.18	4.5	0.026	0.7	6.88	MW	CG	N
0.180	4.57	70388S	.38	9.7	.128	3.3	32	5.5	.11	2.9	3.6	16	.18	4.5	0.026	0.7	6.88	SST</		




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70283S	.44	11.2	.148	3.8	4.2	.74	.21	5.4	.90	4.0	.10	2.6	0.016	0.4	6.38	SST	CG	N
0.180	4.57	70304	.44	11.2	.144	3.7	7.9	1.4	.24	6.2	1.9	8.5	.12	3.0	0.018	0.5	6.50	MW	CG	N
0.180	4.57	70304S	.44	11.2	.144	3.7	6.7	1.2	.19	4.8	1.3	5.7	.12	3.0	0.018	0.5	6.50	SST	CG	N
0.180	4.57	70325	.44	11.2	.140	3.6	11	1.9	.24	6.0	2.6	12	.14	3.6	0.020	0.5	7.13	MW	CG	N
0.180	4.57	70325S	.44	11.2	.140	3.6	9.4	1.6	.19	4.7	1.7	7.7	.14	3.6	0.020	0.5	7.13	SST	CG	N
0.180	4.57	70346	.44	11.2	.136	3.5	17	3.0	.20	5.2	3.5	15	.15	3.9	0.022	0.6	7.00	MW	CG	N
0.180	4.57	70346S	.44	11.2	.136	3.5	14	2.5	.16	4.1	2.3	10	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.180	4.57	70366	.44	11.2	.132	3.4	22	3.8	.20	5.2	4.5	20	.19	4.7	0.024	0.6	7.75	MW	CG	N
0.180	4.57	70366S	.44	11.2	.132	3.4	19	3.3	.16	4.1	3.0	13	.19	4.7	0.024	0.6	7.75	SST	CG	N
0.180	4.57	70389	.44	11.2	.128	3.3	31	5.4	.17	4.3	5.3	24	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.180	4.57	70389S	.44	11.2	.128	3.3	26	4.6	.13	3.4	3.6	16	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.180	4.57	70410	.44	11.2	.122	3.1	48	8.5	.15	3.8	7.3	32	.24	6.0	0.029	0.7	8.13	MW	CG	N
0.180	4.57	70410S	.44	11.2	.122	3.1	41	7.2	.12	3.0	4.9	22	.24	6.0	0.029	0.7	8.13	SST	CG	N
0.180	4.57	70428	.44	11.2	.116	2.9	79	14	.12	3.1	9.7	43	.25	6.4	0.032	0.8	7.88	MW	CG	N
0.180	4.57	70428S	.44	11.2	.116	2.9	67	12	.10	2.5	6.5	29	.25	6.4	0.032	0.8	7.88	SST	CG	N
0.180	4.57	70445	.44	11.2	.110	2.8	115	20	.10	2.6	12	53	.28	7.2	0.035	0.9	8.13	MW	CG	N
0.180	4.57	70445S	.44	11.2	.110	2.8	97	17	.08	2.1	8.0	36	.28	7.2	0.035	0.9	8.13	SST	CG	N
0.180	4.57	70248	.50	12.7	.156	4.0	1.7	.29	.38	9.7	.64	2.8	.07	1.8	0.012	0.3	5.75	MW	CG	N
0.180	4.57	70248S	.50	12.7	.156	4.0	1.5	.26	.28	7.1	.41	1.8	.07	1.8	0.012	0.3	5.75	SST	CG	N
0.180	4.57	70263	.50	12.7	.152	3.9	2.8	.50	.35	9.0	1.0	4.5	.09	2.2	0.014	0.4	6.25	MW	CG	N
0.180	4.57	70263S	.50	12.7	.152	3.9	2.5	.43	.26	6.6	.64	2.9	.09	2.2	0.014	0.4	6.25	SST	CG	N
0.180	4.57	70284	.50	12.7	.148	3.8	4.4	.76	.31	7.9	1.4	6.0	.11	2.8	0.016	0.4	6.88	MW	CG	N
0.180	4.57	70284S	.50	12.7	.148	3.8	3.7	.65	.24	6.2	.90	4.0	.11	2.8	0.016	0.4	6.88	SST	CG	N
0.180	4.57	70305	.50	12.7	.144	3.7	6.9	1.2	.28	7.1	1.9	8.5	.13	3.3	0.018	0.5	7.13	MW	CG	N
0.180	4.57	70305S	.50	12.7	.144	3.7	5.8	1.0	.22	5.6	1.3	5.7	.13	3.3	0.018	0.5	7.13	SST	CG	N
0.180	4.57	70326	.50	12.7	.140	3.6	9.5	1.7	.28	7.0	2.6	12	.16	4.0	0.020	0.5	7.88	MW	CG	N
0.180	4.57	70326S	.50	12.7	.140	3.6	8.1	1.4	.22	5.5	1.7	7.7	.16	4.0	0.020	0.5	7.88	SST	CG	N
0.180	4.57	70347	.50	12.7	.136	3.5	14	2.5	.25	6.2	3.5	15	.18	4.5	0.022	0.6	8.00	MW	CG	N
0.180	4.57	70347S	.50	12.7	.136	3.5	12	2.1	.19	4.9	2.3	10	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.180	4.57	70367	.50	12.7	.132	3.4	19	3.3	.24	6.0	4.5	20	.21	5.3	0.024	0.6	8.63	MW	CG	N
0.180	4.57	70367S	.50	12.7	.132	3.4	16	2.8	.18	4.7	3.0	13	.21	5.3	0.024	0.6	8.63	SST	CG	N
0.180	4.57	70390	.50	12.7	.128	3.3	27	4.7	.20	5.0	5.3	24	.22	5.7	0.026	0.7	8.63	MW	CG	N
0.180	4.57	70390S	.50	12.7	.128	3.3	23	4.0	.16	4.0	3.6	16	.22	5.7	0.026	0.7	8.63	SST	CG	N
0.180	4.57	70411	.50	12.7	.122	3.1	42	7.3	.17	4.4	7.3	32	.26	6.7	0.029	0.7	9.13	MW	CG	N
0.180	4.57	70411S	.50	12.7	.122	3.1	35	6.2	.14	3.5	4.9	22	.26	6.7	0.029	0.7	9.13	SST	CG	N
0.180	4.57	70429	.50	12.7	.116	2.9	65	11	.15	3.8	9.7	43	.29	7.4	0.032	0.8	9.13	MW	CG	N
0.180	4.57	70429S	.50	12.7	.116	2.9	55	9.7	.12	3.0	6.5	29	.29	7.4	0.032	0.8	9.13	SST	CG	N
0.180	4.57	70446	.50	12.7	.110	2.8	99	17	.12	3.1	12	53	.32	8.1	0.035	0.9	9.13	MW	CG	N
0.180	4.57	70446S	.50	12.7	.110	2.8	84	15	.10	2.4	8.0	36	.32	8.1	0.035	0.9	9.13	SST	CG	N
0.180	4.57	B2-34	.55	13.9	.134	3.4	13	2.3	.29	7.5	3.9	18	.22	5.7	0.023	0.6	9.75	MW	CG	N
0.180	4.57	70249	.56	14.2	.156	4.0	1.5	.26	.43	11	.64	2.8	.08	1.9	0.012	0.3	6.25	MW	CG	N
0.180	4.57	70249S	.56	14.2	.156	4.0	1.3	.23	.32	8.0	.41	1.8	.08	1.9	0.012	0.3	6.25	SST	CG	N
0.180	4.57	70264	.56	14.2	.152	3.9	2.5	.43	.41	10	1.0	4.5	.10	2.4	0.014	0.4	6.88	MW	CG	N
0.180	4.57	70264S	.56	14.2	.152	3.9	2.2	.38	.30	7.6	.64	2.9	.10	2.4	0.014	0.4	6.88	SST	CG	N
0.180	4.57	70285	.56	14.2	.148	3.8	3.9	.67	.35	9.0	1.4	6.0	.12	3.0	0.016	0.4	7.50	MW	CG	N
0.180	4.57	70285S	.56	14.2	.148	3.8	3.3	.57	.28	7.0	.90	4.0	.12	3.0	0.016	0.4	7.50	SST	CG	N
0.180	4.57	70306	.56	14.2	.144	3.7	5.9	1.0	.33	8.3	1.9	8.5	.15	3.7	0.018	0.5	8.13	MW	CG	N
0.180	4.57	70306S	.56	14.2	.144	3.7	5.0	.87	.26	6.5	1.3	5.7	.15	3.7	0.018	0.5	8.13	SST	CG	N
0.180	4.57	70327	.56	14.2	.140	3.6	8.4	1.5	.31	7.9	2.6	12	.17	4.4	0.020	0.5	8.63	MW	CG	N
0.180	4.57	70327S	.56	14.2	.140	3.6	7.2	1.3	.24	6.2	1.7	7.7	.17	4.4	0.020	0.5	8.63	SST	CG	N
0.180	4.57	70348	.56	14.2	.136	3.5	12	2.1	.29	7.4	3.5	15	.20	5.1	0.022	0.6	9.13	MW	CG	N
0.180	4.57	70348S	.56	14.2	.136	3.5	10	1.8	.23	5.8	2.3	10	.20	5.1	0.022	0.6	9.13	SST	CG	N
0.180	4.57	70368	.56	14.2	.132	3.4	17	2.9	.27	6.8	4.5	20	.23	5.9	0.024	0.6	9.63	MW	CG	N
0.180	4.57	70368S	.56	14.2	.132	3.4	14	2.5	.21	5.3	3.0	13	.23	5.9	0.024	0.6	9.63	SST	CG	N
0.180	4.57	70391	.56	14.2	.128	3.3	23	4.1	.23	5.8	5.3	24	.25	6.4	0.026	0.7	9.75	MW	CG	N
0.180	4.57	70391S	.56	14.2	.128	3.3	20	3.5	.18	4.6	3.6	16	.25	6.4	0.026	0.7	9.75	SST	CG	N
0.180	4.57	70412	.56	14.2	.122	3.1	37	6.4	.20	5.1	7.3	32	.29	7.5	0.029	0.7	10.1	MW	CG	N
0.180	4.57	70412S	.56	14.2	.122	3.1	31	5.4	.16	4.0	4.9	22	.29	7.5	0.029	0.7	10.1	SST	CG	N
0.180	4.57	70430	.56	14.2	.116	2.9	58	10	.17	4.2	9.7	43	.32	8.1	0.032	0.8	10.0	MW	CG	N
0.180	4.57	70430S	.56	14.2	.116	2.9	50	8.7	.13	3.3	6.5	29	.32	8.1	0.032	0.8	10.0	SST	CG	N
0.180	4.57	70447	.56	14.2	.110	2.8	87	15	.14	3.5	12	53	.35	9.0	0.035	0.9	10.1	MW	CG	N
0.180	4.57	70447S	.56	14.2	.110	2.8	74	13	.11	2.8	8.0	36	.35	9.0	0.035	0.9	10.1	SST	CG	N
0.180	4.57	70250	.63	16.0	.156	4.0	1.4	.24	.46	12	.64	2.8	.08	2.0	0.012	0.3	6.50	MW	CG	N
0.180	4.57	70250S	.63	16.0	.156	4.0	1.2	.21	.33	8.5	.41	1.8	.08	2.0	0.012	0.3	6.50	SST	CG	N
0.180	4.57	70265	.63	16.0	.152	3.9	2.2	.39	.45	11	1.0	4.5	.10	2.6	0.014	0.4	7.38	MW	CG	N
0.180	4.57	70265S	.63	16.0	.152	3.9	2.0	.34	.33	8.4	.64	2.9	.10	2.6	0.014	0.4	7.38	SST	CG	N
0.180	4.57	70286	.63	16.0	.148	3.8	3.5	.60	.39	10	1.4	6.0	.13	3.4	0.016	0.4	8.25	MW	CG	N
0.180	4.57	70286S	.63	16.0	.148	3.8	2.9	.51	.31	7.8	.90	4.0	.13	3.4	0.016	0.4	8.25	SST	CG	N
0.180	4.57	70307	.63																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70431	.63	16.0	.116	2.9	51	9.0	.19	4.8	9.7	43	.36	9.0	0.032	0.8	11.1	MW	CG	N
0.180	4.57	70431S	.63	16.0	.116	2.9	43	7.6	.15	3.8	6.5	29	.36	9.0	0.032	0.8	11.1	SST	CG	N
0.180	4.57	70448	.63	16.0	.110	2.8	77	14	.15	3.9	12	53	.39	9.9	0.035	0.9	11.1	MW	CG	N
0.180	4.57	70448S	.63	16.0	.110	2.8	66	11	.12	3.1	8.0	36	.39	9.9	0.035	0.9	11.1	SST	CG	N
0.180	4.57	70251	.69	17.5	.156	4.0	1.2	.21	.53	14	.64	2.8	.09	2.2	0.012	0.3	7.25	MW	CG	N
0.180	4.57	70251S	.69	17.5	.156	4.0	1.0	.18	.39	9.9	.41	1.8	.09	2.2	0.012	0.3	7.25	SST	CG	N
0.180	4.57	70266	.69	17.5	.152	3.9	2.0	.35	.50	13	1.0	4.5	.11	2.8	0.014	0.4	8.00	MW	CG	N
0.180	4.57	70266S	.69	17.5	.152	3.9	1.8	.31	.37	9.3	.64	2.9	.11	2.8	0.014	0.4	8.00	SST	CG	N
0.180	4.57	70287	.69	17.5	.148	3.8	3.1	.53	.45	11	1.4	6.0	.14	3.7	0.016	0.4	9.00	MW	CG	N
0.180	4.57	70287S	.69	17.5	.148	3.8	2.6	.45	.35	8.8	.90	4.0	.14	3.7	0.016	0.4	9.00	SST	CG	N
0.180	4.57	70308	.69	17.5	.144	3.7	4.6	.80	.42	11	1.9	8.5	.18	4.5	0.018	0.5	9.75	MW	CG	N
0.180	4.57	70308S	.69	17.5	.144	3.7	3.9	.68	.33	8.4	1.3	5.7	.18	4.5	0.018	0.5	9.75	SST	CG	N
0.180	4.57	70329	.69	17.5	.140	3.6	6.7	1.2	.39	10	2.6	12	.21	5.3	0.020	0.5	10.5	MW	CG	N
0.180	4.57	70329S	.69	17.5	.140	3.6	5.7	.99	.31	7.8	1.7	7.7	.21	5.3	0.020	0.5	10.5	SST	CG	N
0.180	4.57	70350	.69	17.5	.136	3.5	9.6	1.7	.36	9.2	3.5	15	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.180	4.57	70350S	.69	17.5	.136	3.5	8.1	1.4	.28	7.2	2.3	10	.24	6.1	0.022	0.6	11.0	SST	CG	N
0.180	4.57	70371	.69	17.5	.132	3.4	13	2.3	.34	8.6	4.5	20	.28	7.0	0.024	0.6	11.5	MW	CG	N
0.180	4.57	70371S	.69	17.5	.132	3.4	11	2.0	.26	6.7	3.0	13	.28	7.0	0.024	0.6	11.5	SST	CG	N
0.180	4.57	70393	.69	17.5	.128	3.3	19	3.3	.28	7.1	5.3	24	.30	7.6	0.026	0.7	11.5	MW	CG	N
0.180	4.57	70393S	.69	17.5	.128	3.3	16	2.8	.22	5.6	3.6	16	.30	7.6	0.026	0.7	11.5	SST	CG	N
0.180	4.57	70414	.69	17.5	.122	3.1	29	5.1	.25	6.3	7.3	32	.35	8.9	0.029	0.7	12.1	MW	CG	N
0.180	4.57	70414S	.69	17.5	.122	3.1	25	4.3	.20	5.0	4.9	22	.35	8.9	0.029	0.7	12.1	SST	CG	N
0.180	4.57	70432	.69	17.5	.116	2.9	47	8.3	.20	5.2	9.7	43	.38	9.7	0.032	0.8	11.9	MW	CG	N
0.180	4.57	70432S	.69	17.5	.116	2.9	40	7.0	.16	4.1	6.5	29	.38	9.7	0.032	0.8	11.9	SST	CG	N
0.180	4.57	70449	.69	17.5	.110	2.8	69	12	.17	4.4	12	53	.43	11.0	0.035	0.9	12.4	MW	CG	N
0.180	4.57	70449S	.69	17.5	.110	2.8	58	10	.14	3.5	8.0	36	.43	11.0	0.035	0.9	12.4	SST	CG	N
0.180	4.57	70252	.75	19.1	.156	4.0	1.1	.19	.58	15	.64	2.8	.09	2.4	0.012	0.3	7.75	MW	CG	N
0.180	4.57	70252S	.75	19.1	.156	4.0	.95	.17	.43	11	.41	1.8	.09	2.4	0.012	0.3	7.75	SST	CG	N
0.180	4.57	70267	.75	19.1	.152	3.9	1.9	.33	.54	14	1.0	4.5	.12	3.0	0.014	0.4	8.50	MW	CG	N
0.180	4.57	70267S	.75	19.1	.152	3.9	1.6	.28	.40	10	.64	2.9	.12	3.0	0.014	0.4	8.50	SST	CG	N
0.180	4.57	70288	.75	19.1	.148	3.8	2.7	.46	.51	13	1.4	6.0	.16	4.1	0.016	0.4	10.0	MW	CG	N
0.180	4.57	70288S	.75	19.1	.148	3.8	2.3	.39	.40	10	.90	4.0	.16	4.1	0.016	0.4	10.0	SST	CG	N
0.180	4.57	70309	.75	19.1	.144	3.7	4.1	.71	.47	12	1.9	8.5	.19	4.9	0.018	0.5	10.8	MW	CG	N
0.180	4.57	70309S	.75	19.1	.144	3.7	3.4	.60	.37	9.4	1.3	5.7	.19	4.9	0.018	0.5	10.8	SST	CG	N
0.180	4.57	70330	.75	19.1	.140	3.6	6.2	1.1	.43	11	2.6	12	.22	5.7	0.020	0.5	11.1	MW	CG	N
0.180	4.57	70330S	.75	19.1	.140	3.6	5.2	.92	.33	8.5	1.7	7.7	.22	5.7	0.020	0.5	11.1	SST	CG	N
0.180	4.57	70351	.75	19.1	.136	3.5	8.6	1.5	.40	10	3.5	15	.26	6.6	0.022	0.6	11.9	MW	CG	N
0.180	4.57	70351S	.75	19.1	.136	3.5	7.3	1.3	.31	8.0	2.3	10	.26	6.6	0.022	0.6	11.9	SST	CG	N
0.180	4.57	70372	.75	19.1	.132	3.4	12	2.1	.37	9.4	4.5	20	.30	7.5	0.024	0.6	12.4	MW	CG	N
0.180	4.57	70372S	.75	19.1	.132	3.4	10	1.8	.29	7.3	3.0	13	.30	7.5	0.024	0.6	12.4	SST	CG	N
0.180	4.57	70394	.75	19.1	.128	3.3	17	3.0	.31	7.9	5.3	24	.33	8.3	0.026	0.7	12.6	MW	CG	N
0.180	4.57	70394S	.75	19.1	.128	3.3	14	2.5	.25	6.3	3.6	16	.33	8.3	0.026	0.7	12.6	SST	CG	N
0.180	4.57	B4-33	.75	19.1	.128	3.3	14	2.5	.25	6.4	3.6	16	.34	8.6	0.026	0.7	13.0	SST	CG	N
0.180	4.57	70415	.75	19.1	.122	3.1	26	4.6	.28	7.0	7.3	32	.38	9.7	0.029	0.7	13.1	MW	CG	N
0.180	4.57	70415S	.75	19.1	.122	3.1	22	3.9	.22	5.5	4.9	22	.38	9.7	0.029	0.7	13.1	SST	CG	N
0.180	4.57	70433	.75	19.1	.116	2.9	41	7.2	.23	6.0	9.7	43	.42	10.8	0.032	0.8	13.3	MW	CG	N
0.180	4.57	70433S	.75	19.1	.116	2.9	35	6.1	.19	4.7	6.5	29	.42	10.8	0.032	0.8	13.3	SST	CG	N
0.180	4.57	70450	.75	19.1	.110	2.8	62	11	.19	4.8	12	53	.47	11.9	0.035	0.9	13.4	MW	CG	N
0.180	4.57	70450S	.75	19.1	.110	2.8	53	9.3	.15	3.8	8.0	36	.47	11.9	0.035	0.9	13.4	SST	CG	N
0.180	4.57	70253	.81	20.6	.156	4.0	1.0	.18	.63	16	.64	2.8	.10	2.5	0.012	0.3	8.25	MW	CG	N
0.180	4.57	70253S	.81	20.6	.156	4.0	.88	.15	.46	12	.41	1.8	.10	2.5	0.012	0.3	8.25	SST	CG	N
0.180	4.57	70269	.81	20.6	.152	3.9	1.7	.30	.60	15	1.0	4.5	.13	3.3	0.014	0.4	9.13	MW	CG	N
0.180	4.57	70269S	.81	20.6	.152	3.9	1.5	.26	.44	11	.64	2.9	.13	3.3	0.014	0.4	9.13	SST	CG	N
0.180	4.57	70290	.81	20.6	.148	3.8	2.6	.46	.52	13	1.4	6.0	.16	4.2	0.016	0.4	10.3	MW	CG	N
0.180	4.57	70290S	.81	20.6	.148	3.8	2.2	.39	.41	10	.90	4.0	.16	4.2	0.016	0.4	10.3	SST	CG	N
0.180	4.57	70311	.81	20.6	.144	3.7	3.9	.68	.49	13	1.9	8.5	.20	5.1	0.018	0.5	11.1	MW	CG	N
0.180	4.57	70311S	.81	20.6	.144	3.7	3.3	.58	.39	9.8	1.3	5.7	.20	5.1	0.018	0.5	11.1	SST	CG	N
0.180	4.57	70332	.81	20.6	.140	3.6	5.6	.98	.47	12	2.6	12	.24	6.1	0.020	0.5	12.0	MW	CG	N
0.180	4.57	70332S	.81	20.6	.140	3.6	4.8	.83	.37	9.3	1.7	7.7	.24	6.1	0.020	0.5	12.0	SST	CG	N
0.180	4.57	70352	.81	20.6	.136	3.5	7.6	1.3	.46	12	3.5	15	.29	7.4	0.022	0.6	13.3	MW	CG	N
0.180	4.57	70352S	.81	20.6	.136	3.5	6.5	1.1	.36	9.1	2.3	10	.29	7.4	0.022	0.6	13.3	SST	CG	N
0.180	4.57	70374	.81	20.6	.132	3.4	11	1.9	.41	10	4.5	20	.32	8.2	0.024	0.6	13.4	MW	CG	N
0.180	4.57	70374S	.81	20.6	.132	3.4	9.4	1.6	.32	8.1	3.0	13	.32	8.2	0.024	0.6	13.4	SST	CG	N
0.180	4.57	70395	.81	20.6	.128	3.3	16	2.8	.34	8.5	5.3	24	.35	8.8	0.026	0.7	13.4	MW	CG	N
0.180	4.57	70395S	.81	20.6	.128	3.3	13	2.4	.26	6.7	3.6	16	.35	8.8	0.026	0.7	13.4	SST	CG	N
0.180	4.57	70416	.81	20.6	.122	3.1	24	4.3	.30	7.6	7.3	32	.41	10.4	0.029	0.7	14.1	MW	CG	N
0.180	4.57	70416S	.81	20.6	.122	3.1	21	3.6	.24	6.0	4.9	22	.41	10.4	0.029	0.7	14.1	SST	CG	N
0.180	4.57	70434	.81	20.6	.116	2.9	37	6.5	.26	6.6	9.7	43	.46	11.8	0.032	0.8	14.5	MW	CG	N
0.180	4.57	70434S	.81	20.6	.116	2.9	32	5.5	.20	5.2	6.5	29	.46	11.8	0.					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70333	.88	22.4	.140	3.6	5.2	.91	.50	13	2.6	12	.26	6.5	0.020	0.5	12.8	MW	CG	N
0.180	4.57	70333S	.88	22.4	.140	3.6	4.4	.77	.39	10	1.7	7.7	.26	6.5	0.020	0.5	12.8	SST	CG	N
0.180	4.57	70354	.88	22.4	.136	3.5	7.4	1.3	.47	12	3.5	15	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.180	4.57	70354S	.88	22.4	.136	3.5	6.3	1.1	.37	9.3	2.3	10	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.180	4.57	70375	.88	22.4	.132	3.4	10	1.8	.43	11	4.5	20	.34	8.7	0.024	0.6	14.3	MW	CG	N
0.180	4.57	70375S	.88	22.4	.132	3.4	8.7	1.5	.34	8.6	3.0	13	.34	8.7	0.024	0.6	14.3	SST	CG	N
0.180	4.57	70396	.88	22.4	.128	3.3	15	2.6	.36	9.2	5.3	24	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.180	4.57	70396S	.88	22.4	.128	3.3	12	2.2	.28	7.2	3.6	16	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.180	4.57	70417	.88	22.4	.122	3.1	22	3.9	.33	8.3	7.3	32	.44	11.1	0.029	0.7	15.1	MW	CG	N
0.180	4.57	70417S	.88	22.4	.122	3.1	19	3.3	.26	6.5	4.9	22	.44	11.1	0.029	0.7	15.1	SST	CG	N
0.180	4.57	70435	.88	22.4	.116	2.9	34	5.9	.29	7.3	9.7	43	.50	12.8	0.032	0.8	15.8	MW	CG	N
0.180	4.57	70435S	.88	22.4	.116	2.9	29	5.0	.23	5.7	6.5	29	.50	12.8	0.032	0.8	15.8	SST	CG	N
0.180	4.57	70453	.88	22.4	.110	2.8	52	9.2	.23	5.8	12	53	.54	13.8	0.035	0.9	15.5	MW	CG	N
0.180	4.57	70453S	.88	22.4	.110	2.8	45	7.8	.18	4.6	8.0	36	.54	13.8	0.035	0.9	15.5	SST	CG	N
0.180	4.57	70255	.94	23.9	.156	4.0	.90	.16	.71	18	.64	2.8	.11	2.7	0.012	0.3	9.00	MW	CG	N
0.180	4.57	70255S	.94	23.9	.156	4.0	.78	.14	.52	13	.41	1.8	.11	2.7	0.012	0.3	9.00	SST	CG	N
0.180	4.57	70272	.94	23.9	.152	3.9	1.5	.26	.67	17	1.0	4.5	.14	3.6	0.014	0.4	10.0	MW	CG	N
0.180	4.57	70272S	.94	23.9	.152	3.9	1.3	.23	.49	12	.64	2.9	.14	3.6	0.014	0.4	10.0	SST	CG	N
0.180	4.57	70293	.94	23.9	.148	3.8	2.3	.40	.59	15	1.4	6.0	.18	4.6	0.016	0.4	11.3	MW	CG	N
0.180	4.57	70293S	.94	23.9	.148	3.8	2.0	.34	.46	12	.90	4.0	.18	4.6	0.016	0.4	11.3	SST	CG	N
0.180	4.57	70314	.94	23.9	.144	3.7	3.4	.60	.57	14	1.9	8.5	.23	5.7	0.018	0.5	12.5	MW	CG	N
0.180	4.57	70314S	.94	23.9	.144	3.7	2.9	.51	.44	11	1.3	5.7	.23	5.7	0.018	0.5	12.5	SST	CG	N
0.180	4.57	70335	.94	23.9	.140	3.6	4.9	.86	.53	14	2.6	12	.27	6.9	0.020	0.5	13.5	MW	CG	N
0.180	4.57	70335S	.94	23.9	.140	3.6	4.2	.73	.42	11	1.7	7.7	.27	6.9	0.020	0.5	13.5	SST	CG	N
0.180	4.57	70355	.94	23.9	.136	3.5	6.8	1.2	.51	13	3.5	15	.32	8.1	0.022	0.6	14.5	MW	CG	N
0.180	4.57	70355S	.94	23.9	.136	3.5	5.8	1.0	.40	10	2.3	10	.32	8.1	0.022	0.6	14.5	SST	CG	N
0.180	4.57	70377	.94	23.9	.132	3.4	9.5	1.7	.47	12	4.5	20	.37	9.3	0.024	0.6	15.3	MW	CG	N
0.180	4.57	70377S	.94	23.9	.132	3.4	8.1	1.4	.37	9.3	3.0	13	.37	9.3	0.024	0.6	15.3	SST	CG	N
0.180	4.57	70398	.94	23.9	.128	3.3	13	2.3	.41	10	5.3	24	.41	10.5	0.026	0.7	15.9	MW	CG	N
0.180	4.57	70398S	.94	23.9	.128	3.3	11	1.9	.32	8.2	3.6	16	.41	10.5	0.026	0.7	15.9	SST	CG	N
0.180	4.57	70418	.94	23.9	.122	3.1	21	3.6	.35	8.9	7.3	32	.47	12.0	0.029	0.7	16.3	MW	CG	N
0.180	4.57	70418S	.94	23.9	.122	3.1	18	3.1	.28	7.0	4.9	22	.47	12.0	0.029	0.7	16.3	SST	CG	N
0.180	4.57	70436	.94	23.9	.116	2.9	32	5.5	.31	7.8	9.7	43	.54	13.6	0.032	0.8	16.8	MW	CG	N
0.180	4.57	70436S	.94	23.9	.116	2.9	27	4.7	.24	6.1	6.5	29	.54	13.6	0.032	0.8	16.8	SST	CG	N
0.180	4.57	70452	.94	23.9	.110	2.8	49	8.5	.24	6.2	12	53	.58	14.7	0.035	0.9	16.5	MW	CG	N
0.180	4.57	70452S	.94	23.9	.110	2.8	41	7.3	.19	4.9	8.0	36	.58	14.7	0.035	0.9	16.5	SST	CG	N
0.180	4.57	70256	1.00	25.4	.156	4.0	.80	.14	.80	20	.64	2.8	.12	3.0	0.012	0.3	9.88	MW	CG	N
0.180	4.57	70256S	1.00	25.4	.156	4.0	.69	.12	.59	15	.41	1.8	.12	3.0	0.012	0.3	9.88	SST	CG	N
0.180	4.57	70273	1.00	25.4	.152	3.9	1.4	.24	.74	19	1.0	4.5	.15	3.9	0.014	0.4	10.9	MW	CG	N
0.180	4.57	70273S	1.00	25.4	.152	3.9	1.2	.20	.56	14	.64	2.9	.15	3.9	0.014	0.4	10.9	SST	CG	N
0.180	4.57	70294	1.00	25.4	.148	3.8	2.1	.36	.66	17	1.4	6.0	.20	5.0	0.016	0.4	12.4	MW	CG	N
0.180	4.57	70294S	1.00	25.4	.148	3.8	1.7	.31	.52	13	.90	4.0	.20	5.0	0.016	0.4	12.4	SST	CG	N
0.180	4.57	70315	1.00	25.4	.144	3.7	3.2	.55	.61	15	1.9	8.5	.24	6.1	0.018	0.5	13.3	MW	CG	N
0.180	4.57	70315S	1.00	25.4	.144	3.7	2.7	.47	.48	12	1.3	5.7	.24	6.1	0.018	0.5	13.3	SST	CG	N
0.180	4.57	70336	1.00	25.4	.140	3.6	4.6	.80	.58	15	2.6	12	.29	7.3	0.020	0.5	14.4	MW	CG	N
0.180	4.57	70336S	1.00	25.4	.140	3.6	3.9	.68	.45	11	1.7	7.7	.29	7.3	0.020	0.5	14.4	SST	CG	N
0.180	4.57	70356	1.00	25.4	.136	3.5	6.4	1.1	.54	14	3.5	15	.34	8.6	0.022	0.6	15.4	MW	CG	N
0.180	4.57	70356S	1.00	25.4	.136	3.5	5.4	.95	.42	11	2.3	10	.34	8.6	0.022	0.6	15.4	SST	CG	N
0.180	4.57	70378	1.00	25.4	.132	3.4	9.0	1.6	.50	13	4.5	20	.38	9.8	0.024	0.6	16.0	MW	CG	N
0.180	4.57	70378S	1.00	25.4	.132	3.4	7.7	1.3	.39	9.9	3.0	13	.38	9.8	0.024	0.6	16.0	SST	CG	N
0.180	4.57	70399	1.00	25.4	.128	3.3	12	2.1	.43	11	5.3	24	.44	11.1	0.026	0.7	16.8	MW	CG	N
0.180	4.57	70399S	1.00	25.4	.128	3.3	10	1.8	.34	8.7	3.6	16	.44	11.1	0.026	0.7	16.8	SST	CG	N
0.180	4.57	70419	1.00	25.4	.122	3.1	19	3.4	.38	9.6	7.3	32	.50	12.8	0.029	0.7	17.4	MW	CG	N
0.180	4.57	70419S	1.00	25.4	.122	3.1	16	2.9	.30	7.6	4.9	22	.50	12.8	0.029	0.7	17.4	SST	CG	N
0.180	4.57	70437	1.00	25.4	.116	2.9	29	5.1	.33	8.4	9.7	43	.57	14.5	0.032	0.8	17.9	MW	CG	N
0.180	4.57	70437S	1.00	25.4	.116	2.9	25	4.3	.26	6.6	6.5	29	.57	14.5	0.032	0.8	17.9	SST	CG	N
0.180	4.57	70454	1.00	25.4	.110	2.8	46	8.0	.26	6.6	12	53	.61	15.6	0.035	0.9	17.5	MW	CG	N
0.180	4.57	70454S	1.00	25.4	.110	2.8	39	6.8	.21	5.2	8.0	36	.61	15.6	0.035	0.9	17.5	SST	CG	N
0.180	4.57	70275	1.13	28.7	.152	3.9	1.2	.21	.84	21	1.0	4.5	.17	4.3	0.014	0.4	12.0	MW	CG	N
0.180	4.57	70275S	1.13	28.7	.152	3.9	1.0	.18	.63	16	.64	2.9	.17	4.3	0.014	0.4	12.0	SST	CG	N
0.180	4.57	70296	1.13	28.7	.148	3.8	1.9	.33	.71	18	1.4	6.0	.21	5.4	0.016	0.4	13.3	MW	CG	N
0.180	4.57	70296S	1.13	28.7	.148	3.8	1.6	.28	.56	14	.90	4.0	.21	5.4	0.016	0.4	13.3	SST	CG	N
0.180	4.57	70317	1.13	28.7	.144	3.7	2.8	.49	.69	17	1.9	8.5	.26	6.7	0.018	0.5	14.6	MW	CG	N
0.180	4.57	70317S	1.13	28.7	.144	3.7	2.4	.42	.54	14	1.3	5.7	.26	6.7	0.018	0.5	14.6	SST	CG	N
0.180	4.57	70338	1.13	28.7	.140	3.6	4.0	.70	.65	17	2.6	12	.32	8.1	0.020	0.5	16.0	MW	CG	N
0.180	4.57	70338S	1.13	28.7	.140	3.6	3.4	.60	.51	13	1.7	7.7	.32	8.1	0.020	0.5	16.0	SST	CG	N
0.180	4.57	70357	1.13	28.7	.136	3.5	5.7	.99	.61	16	3.5	15	.38	9.6	0.022	0.6	17.1	MW	CG	N
0.180	4.57	70357S	1.13	28.7	.136	3.5	4.8	.84	.48	12</										




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70276	1.25	31.8	.152	3.9	1.1	.19	.92	23	1.0	4.5	.18	4.6	0.014	0.4	13.0	MW	CG	N
0.180	4.57	70276S	1.25	31.8	.152	3.9	.94	.16	.69	17	.64	2.9	.18	4.6	0.014	0.4	13.0	SST	CG	N
0.180	4.57	70297	1.25	31.8	.148	3.8	1.6	.28	.85	22	1.4	6.0	.25	6.2	0.016	0.4	15.4	MW	CG	N
0.180	4.57	70297S	1.25	31.8	.148	3.8	1.4	.24	.66	17	.90	4.0	.25	6.2	0.016	0.4	15.4	SST	CG	N
0.180	4.57	70318	1.25	31.8	.144	3.7	2.6	.45	.75	19	1.9	8.5	.29	7.3	0.018	0.5	15.9	MW	CG	N
0.180	4.57	70318S	1.25	31.8	.144	3.7	2.2	.38	.59	15	1.3	5.7	.29	7.3	0.018	0.5	15.9	SST	CG	N
0.180	4.57	70339	1.25	31.8	.140	3.6	3.6	.63	.73	18	2.6	12	.35	9.0	0.020	0.5	17.6	MW	CG	N
0.180	4.57	70339S	1.25	31.8	.140	3.6	3.1	.54	.57	14	1.7	7.7	.35	9.0	0.020	0.5	17.6	SST	CG	N
0.180	4.57	70358	1.25	31.8	.136	3.5	5.1	.89	.68	17	3.5	15	.41	10.5	0.022	0.6	18.8	MW	CG	N
0.180	4.57	70358S	1.25	31.8	.136	3.5	4.3	.76	.53	13	2.3	10	.41	10.5	0.022	0.6	18.8	SST	CG	N
0.180	4.57	70380	1.25	31.8	.132	3.4	7.1	1.2	.63	16	4.5	20	.48	12.1	0.024	0.6	19.9	MW	CG	N
0.180	4.57	70380S	1.25	31.8	.132	3.4	6.0	1.0	.50	13	3.0	13	.48	12.1	0.024	0.6	19.9	SST	CG	N
0.180	4.57	70401	1.25	31.8	.128	3.3	9.7	1.7	.55	14	5.3	24	.53	13.5	0.026	0.7	20.5	MW	CG	N
0.180	4.57	70401S	1.25	31.8	.128	3.3	8.2	1.4	.43	11	3.6	16	.53	13.5	0.026	0.7	20.5	SST	CG	N
0.180	4.57	70421	1.25	31.8	.122	3.1	15	2.7	.48	12	7.3	32	.62	15.7	0.029	0.7	21.4	MW	CG	N
0.180	4.57	70421S	1.25	31.8	.122	3.1	13	2.3	.38	9.6	4.9	22	.62	15.7	0.029	0.7	21.4	SST	CG	N
0.180	4.57	70439	1.25	31.8	.116	2.9	23	4.1	.42	11	9.7	43	.71	18.0	0.032	0.8	22.1	MW	CG	N
0.180	4.57	70439S	1.25	31.8	.116	2.9	20	3.4	.33	8.4	6.5	29	.71	18.0	0.032	0.8	22.1	SST	CG	N
0.180	4.57	70456	1.25	31.8	.110	2.8	36	6.3	.33	8.4	12	53	.76	19.2	0.035	0.9	21.6	MW	CG	N
0.180	4.57	70456S	1.25	31.8	.110	2.8	31	5.4	.26	6.7	8.0	36	.76	19.2	0.035	0.9	21.6	SST	CG	N
0.180	4.57	70277	1.38	35.1	.152	3.9	.98	.17	1.0	26	1.0	4.5	.20	5.1	0.014	0.4	14.4	MW	CG	N
0.180	4.57	70277S	1.38	35.1	.152	3.9	.83	.15	.78	20	.64	2.9	.20	5.1	0.014	0.4	14.4	SST	CG	N
0.180	4.57	70298	1.38	35.1	.148	3.8	1.5	.25	.94	24	1.4	6.0	.27	6.8	0.016	0.4	16.8	MW	CG	N
0.180	4.57	70298S	1.38	35.1	.148	3.8	1.2	.22	.73	19	.90	4.0	.27	6.8	0.016	0.4	16.8	SST	CG	N
0.180	4.57	70319	1.38	35.1	.144	3.7	2.3	.40	.84	21	1.9	8.5	.32	8.1	0.018	0.5	17.6	MW	CG	N
0.180	4.57	70319S	1.38	35.1	.144	3.7	1.9	.34	.66	17	1.3	5.7	.32	8.1	0.018	0.5	17.6	SST	CG	N
0.180	4.57	70340	1.38	35.1	.140	3.6	3.3	.57	.81	20	2.6	12	.39	9.8	0.020	0.5	19.3	MW	CG	N
0.180	4.57	70340S	1.38	35.1	.140	3.6	2.8	.48	.63	16	1.7	7.7	.39	9.8	0.020	0.5	19.3	SST	CG	N
0.180	4.57	70360	1.38	35.1	.136	3.5	4.6	.81	.75	19	3.5	15	.45	11.5	0.022	0.6	20.5	MW	CG	N
0.180	4.57	70360S	1.38	35.1	.136	3.5	3.9	.68	.59	15	2.3	10	.45	11.5	0.022	0.6	20.5	SST	CG	N
0.180	4.57	70382	1.38	35.1	.132	3.4	6.4	1.1	.70	18	4.5	20	.52	13.2	0.024	0.6	21.6	MW	CG	N
0.180	4.57	70382S	1.38	35.1	.132	3.4	5.4	.95	.55	14	3.0	13	.52	13.2	0.024	0.6	21.6	SST	CG	N
0.180	4.57	70403	1.38	35.1	.128	3.3	8.7	1.5	.61	16	5.3	24	.59	14.9	0.026	0.7	22.6	MW	CG	N
0.180	4.57	70403S	1.38	35.1	.128	3.3	7.4	1.3	.48	12	3.6	16	.59	14.9	0.026	0.7	22.6	SST	CG	N
0.180	4.57	70422	1.38	35.1	.122	3.1	14	2.4	.53	13	7.3	32	.68	17.3	0.029	0.7	23.5	MW	CG	N
0.180	4.57	70422S	1.38	35.1	.122	3.1	12	2.0	.42	11	4.9	22	.68	17.3	0.029	0.7	23.5	SST	CG	N
0.180	4.57	70440	1.38	35.1	.116	2.9	21	3.6	.46	12	9.7	43	.78	19.8	0.032	0.8	24.4	MW	CG	N
0.180	4.57	70440S	1.38	35.1	.116	2.9	18	3.1	.37	9.3	6.5	29	.78	19.8	0.032	0.8	24.4	SST	CG	N
0.180	4.57	70258	1.50	38.1	.156	4.0	.60	.10	1.1	27	.64	2.8	.15	3.8	0.012	0.3	12.5	MW	CG	N
0.180	4.57	70258S	1.50	38.1	.156	4.0	.52	.09	.78	20	.41	1.8	.15	3.8	0.012	0.3	12.5	SST	CG	N
0.180	4.57	70278	1.50	38.1	.152	3.9	.89	.15	1.1	29	1.0	4.5	.22	5.6	0.014	0.4	15.6	MW	CG	N
0.180	4.57	70278S	1.50	38.1	.152	3.9	.75	.13	.85	22	.64	2.9	.22	5.6	0.014	0.4	15.6	SST	CG	N
0.180	4.57	70299	1.50	38.1	.148	3.8	1.3	.23	1.0	27	1.4	6.0	.29	7.5	0.016	0.4	18.4	MW	CG	N
0.180	4.57	70299S	1.50	38.1	.148	3.8	1.1	.19	.82	21	.90	4.0	.29	7.5	0.016	0.4	18.4	SST	CG	N
0.180	4.57	70320	1.50	38.1	.144	3.7	2.1	.36	.94	24	1.9	8.5	.35	8.9	0.018	0.5	19.4	MW	CG	N
0.180	4.57	70320S	1.50	38.1	.144	3.7	1.7	.31	.73	19	1.3	5.7	.35	8.9	0.018	0.5	19.4	SST	CG	N
0.180	4.57	70341	1.50	38.1	.140	3.6	3.0	.52	.89	23	2.6	12	.42	10.7	0.020	0.5	21.0	MW	CG	N
0.180	4.57	70341S	1.50	38.1	.140	3.6	2.5	.44	.69	18	1.7	7.7	.42	10.7	0.020	0.5	21.0	SST	CG	N
0.180	4.57	70361	1.50	38.1	.136	3.5	4.2	.74	.82	21	3.5	15	.49	12.5	0.022	0.6	22.4	MW	CG	N
0.180	4.57	70361S	1.50	38.1	.136	3.5	3.6	.63	.64	16	2.3	10	.49	12.5	0.022	0.6	22.4	SST	CG	N
0.180	4.57	70383	1.50	38.1	.132	3.4	5.8	1.0	.77	19	4.5	20	.57	14.4	0.024	0.6	23.6	MW	CG	N
0.180	4.57	70383S	1.50	38.1	.132	3.4	5.0	.87	.60	15	3.0	13	.57	14.4	0.024	0.6	23.6	SST	CG	N
0.180	4.57	70404	1.50	38.1	.128	3.3	8.0	1.4	.66	17	5.3	24	.64	16.2	0.026	0.7	24.5	MW	CG	N
0.180	4.57	70404S	1.50	38.1	.128	3.3	6.8	1.2	.52	13	3.6	16	.64	16.2	0.026	0.7	24.5	SST	CG	N
0.180	4.57	70423	1.50	38.1	.122	3.1	13	2.2	.58	15	7.3	32	.74	18.8	0.029	0.7	25.5	MW	CG	N
0.180	4.57	70423S	1.50	38.1	.122	3.1	11	1.9	.46	12	4.9	22	.74	18.8	0.029	0.7	25.5	SST	CG	N
0.180	4.57	70441	1.50	38.1	.116	2.9	19	3.4	.50	13	9.7	43	.84	21.3	0.032	0.8	26.3	MW	CG	N
0.180	4.57	70441S	1.50	38.1	.116	2.9	16	2.9	.40	10	6.5	29	.84	21.3	0.032	0.8	26.3	SST	CG	N
0.180	4.57	70457	1.50	38.1	.110	2.8	30	5.2	.40	10	12	53	.91	23.0	0.035	0.9	25.9	MW	CG	N
0.180	4.57	70457S	1.50	38.1	.110	2.8	25	4.4	.32	8.1	8.0	36	.91	23.0	0.035	0.9	25.9	SST	CG	N
0.180	4.57	70300	1.75	44.5	.148	3.8	1.1	.19	1.2	32	1.4	6.0	.35	8.8	0.016	0.4	21.6	MW	CG	N
0.180	4.57	70300S	1.75	44.5	.148	3.8	.93	.16	.97	25	.90	4.0	.35	8.8	0.016	0.4	21.6	SST	CG	N
0.180	4.57	70321	1.75	44.5	.144	3.7	1.7	.31	1.1	28	1.9	8.5	.40	10.2	0.018	0.5	22.4	MW	CG	N
0.180	4.57	70321S	1.75	44.5	.144	3.7	1.5	.26	.86	22	1.3	5.7	.40	10.2	0.018	0.5	22.4	SST	CG	N
0.180	4.57	70342	1.75	44.5	.140	3.6	2.5	.44	1.0	26	2.6	12	.49	12.3	0.020	0.5	24.3	MW	CG	N
0.180	4.57	70342S	1.75	44.5	.140	3.6	2.1	.38	.81	21	1.7	7.7	.49	12.3	0.020	0.5	24.3	SST	CG	N
0.180	4.57	70362	1.75	44.5	.136	3.5	3.6	.64	.95	24	3.5	15	.56	14.2	0.022	0.6	25.5	MW	CG	N
0.180	4.57	70362S	1.75	44.5	.136	3.5	3.1	.54	.75	19	2.3	10	.56	14.2	0.022	0.6	25.5	SST</		




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70406	2.00	50.8	.128	3.3	6.0	1.0	.89	23	5.3	24	.84	21.3	0.026	0.7	32.3	MW	CG	N
0.180	4.57	70406S	2.00	50.8	.128	3.3	5.1	.89	.70	18	3.6	16	.84	21.3	0.026	0.7	32.3	SST	CG	N
0.180	4.57	70425	2.00	50.8	.122	3.1	9.4	1.6	.78	20	7.3	32	.98	24.8	0.029	0.7	33.6	MW	CG	N
0.180	4.57	70425S	2.00	50.8	.122	3.1	7.9	1.4	.61	16	4.9	22	.98	24.8	0.029	0.7	33.6	SST	CG	N
0.180	4.57	70443	2.00	50.8	.116	2.9	14	2.5	.69	17	9.7	43	1.12	28.4	0.032	0.8	35.0	MW	CG	N
0.180	4.57	70443S	2.00	50.8	.116	2.9	12	2.1	.54	14	6.5	29	1.12	28.4	0.032	0.8	35.0	SST	CG	N
0.180	4.57	70459	2.00	50.8	.110	2.8	22	3.9	.54	14	12	53	1.19	30.3	0.035	0.9	34.1	MW	CG	N
0.180	4.57	70459S	2.00	50.8	.110	2.8	19	3.3	.43	11	8.0	36	1.19	30.3	0.035	0.9	34.1	SST	CG	N
0.184	4.67	12764	.25	6.4	.164	4.2	.78	.14	.19	4.7	.14	.64	.07	1.7	0.010	0.3	5.50	MW	CG	N
0.184	4.67	B4-24	.86	21.8	.138	3.5	7.4	1.3	.51	13	3.8	17	.35	8.8	0.023	0.6	15.0	MW	CG	BO
0.188	4.78	00-60	.19	4.8	.160	4.1	11	1.9	.09	2.3	.97	4.3	.06	1.4	0.014	0.4	3.00	MW	C	N
0.188	4.78	AA-33	.19	4.8	.156	4.0	8.4	1.5	.10	2.6	.87	3.9	.08	2.0	0.016	0.4	4.00	SST	C	N
0.188	4.78	CC-5	.19	4.8	.140	3.6	110	19	.04	.99	4.3	19	.10	2.4	0.024	0.6	3.00	MW	C	N
0.188	4.78	V-75	.19	4.8	.140	3.6	64	11	.04	1.1	2.9	13	.11	2.7	0.024	0.6	3.50	SST	C	N
0.188	4.78	U-15	.19	4.8	.130	3.3	258	45	.03	.69	7.0	31	.12	2.9	0.029	0.7	3.00	MW	C	Z
0.188	4.78	PP-69	.22	5.6	.148	3.8	15	2.6	.10	2.5	1.4	6.4	.12	3.0	0.020	0.5	5.00	SST	C	N
0.188	4.78	B1-22	.23	5.9	.138	3.5	38	6.6	.08	2.1	3.1	14	.15	3.8	0.025	0.6	5.00	SST	C	N
0.188	4.78	FF-62	.25	6.4	.158	4.0	7.2	1.3	.15	3.8	1.1	4.8	.08	1.9	0.015	0.4	4.00	MW	C	N
0.188	4.78	S-1460	.25	6.4	.158	4.0	4.5	.79	.16	4.0	.72	3.2	.09	2.2	0.015	0.4	4.75	SST	C	N
0.188	4.78	B9-31	.25	6.4	.150	3.8	16	2.7	.14	3.5	2.2	9.6	.09	2.2	0.019	0.5	4.50	MW	CG	Z
0.188	4.78	LL-15	.25	6.4	.148	3.8	22	3.8	.08	2.0	1.7	7.4	.10	2.5	0.020	0.5	4.00	SST	C	N
0.188	4.78	II-2	.25	6.4	.144	3.7	26	4.6	.08	2.2	2.2	9.8	.12	3.1	0.022	0.6	4.50	SST	C	N
0.188	4.78	A10-6	.25	6.4	.142	3.6	30	5.3	.12	3.2	3.8	17	.12	2.9	0.023	0.6	5.00	MW	CG	GI
0.188	4.78	S-1280	.25	6.4	.138	3.5	33	5.7	.09	2.4	3.1	14	.14	3.5	0.025	0.6	5.50	SST	CG	N
0.188	4.78	EE-3	.25	6.4	.136	3.5	52	9.2	.09	2.4	4.9	22	.16	4.0	0.026	0.7	5.00	MW	C	N
0.188	4.78	O-13	.25	6.4	.136	3.5	63	11	.08	2.1	5.1	23	.14	3.6	0.026	0.7	4.50	MW	C	N
0.188	4.78	V-83	.25	6.4	.136	3.5	155	27	.03	.84	5.1	23	.10	2.6	0.026	0.7	3.00	MW	C	N
0.188	4.78	A-44	.25	6.4	.132	3.4	64	11	.07	1.7	4.2	19	.14	3.6	0.028	0.7	5.00	SST	CG	N
0.188	4.78	AA-2	.25	6.4	.104	2.6	639	112	.02	.55	14	61	.19	4.7	0.042	1.1	4.25	SPR	CG	N
0.188	4.78	G-60	.28	7.1	.154	3.9	5.3	.93	.16	4.1	.86	3.8	.12	3.0	0.017	0.4	6.00	SST	C	N
0.188	4.78	O-119	.28	7.1	.154	3.9	8.1	1.4	.18	4.6	1.5	6.5	.10	2.6	0.017	0.4	5.00	MW	C	N
0.188	4.78	EE-11	.28	7.1	.142	3.6	13	2.3	.10	2.5	1.3	5.7	.18	4.7	0.023	0.6	8.00	SST	CG	N
0.188	4.78	F-18	.28	7.1	.138	3.5	38	6.6	.12	3.0	4.5	20	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.188	4.78	908	.31	7.9	.170	4.3	.37	.07	.24	6.2	.09	.40	.07	1.7	0.009	0.2	6.50	MW	C	Z
0.188	4.78	FF-7	.31	7.9	.170	4.3	.35	.06	.24	6.2	.09	.38	.07	1.8	0.009	0.2	6.75	MW	C	N
0.188	4.78	A9-2	.31	7.9	.164	4.2	1.2	.20	.23	5.7	.26	1.2	.09	2.2	0.012	0.3	6.25	SST	C	N
0.188	4.78	10063	.31	7.9	.158	4.0	2.9	.50	.19	4.9	.55	2.4	.12	3.0	0.015	0.4	7.00	MW	C	GI
0.188	4.78	V-14	.31	7.9	.158	4.0	1.6	.27	.15	3.7	.23	1.0	.17	4.2	0.015	0.4	10.0	SST	C	N
0.188	4.78	G-70	.31	7.9	.158	4.0	3.5	.62	.21	5.3	.73	3.2	.11	2.7	0.015	0.4	6.00	MW	C	N
0.188	4.78	F-76	.31	7.9	.156	4.0	5.5	.96	.16	4.0	.87	3.9	.08	2.0	0.016	0.4	5.00	SST	CG	N
0.188	4.78	DD-70	.31	7.9	.152	3.9	8.4	1.5	.15	3.7	1.2	5.5	.11	2.9	0.018	0.5	5.25	SST	C	N
0.188	4.78	S-1007	.31	7.9	.152	3.9	11	1.9	.11	2.9	1.2	5.5	.10	2.5	0.018	0.5	4.50	SST	C	N
0.188	4.78	M-119	.31	7.9	.150	3.8	17	3.0	.08	2.1	1.4	6.4	.10	2.4	0.019	0.5	4.00	SST	C	N
0.188	4.78	2983	.31	7.9	.148	3.8	20	3.5	.13	3.2	2.5	11	.11	2.8	0.020	0.5	4.50	MW	C	Z
0.188	4.78	II-49	.31	7.9	.148	3.8	9.9	1.7	.17	4.4	1.7	7.6	.14	3.6	0.020	0.5	7.00	MW	CG	Z
0.188	4.78	DD-12	.31	7.9	.144	3.7	22	3.8	.10	2.6	2.2	9.8	.13	3.4	0.022	0.6	5.00	SST	C	N
0.188	4.78	J-96	.31	7.9	.144	3.7	18	3.2	.18	4.6	3.3	15	.13	3.4	0.022	0.6	6.00	MW	CG	GI
0.188	4.78	2522	.31	7.9	.128	3.3	118	21	.07	1.7	7.7	34	.17	4.2	0.030	0.8	4.50	MW	C	Z
0.188	4.78	A15-7	.31	7.9	.122	3.1	117	20	.06	1.6	7.3	33	.20	5.0	0.033	0.8	6.00	SPR	CG	N
0.188	4.78	A9-22	.34	8.7	.166	4.2	.86	.15	.27	6.8	.23	1.0	.08	2.0	0.011	0.3	6.00	SST	C	N
0.188	4.78	S-853	.34	8.7	.156	4.0	3.6	.64	.22	5.7	.81	3.6	.12	3.0	0.016	0.4	6.50	SST	C	N
0.188	4.78	S-1003	.34	8.7	.152	3.9	6.4	1.1	.19	4.9	1.2	5.5	.13	3.3	0.018	0.5	6.25	SST	C	N
0.188	4.78	F-66	.34	8.7	.136	3.5	39	6.8	.13	3.4	5.1	23	.18	4.6	0.026	0.7	6.00	MW	C	Z
0.188	4.78	F-16	.34	8.7	.122	3.1	114	20	.06	1.6	7.3	33	.23	5.9	0.033	0.8	6.00	HD	C	Z
0.188	4.78	II-86	.38	9.5	.172	4.4	.14	.02	.30	7.6	.04	.18	.08	1.9	0.008	0.2	8.50	SST	C	N
0.188	4.78	VW-13	.38	9.5	.168	4.3	.75	.13	.30	7.7	.23	1.0	.06	1.5	0.010	0.3	5.00	SST	C	N
0.188	4.78	PP-98	.38	9.5	.164	4.2	1.1	.19	.28	7.1	.31	1.4	.10	2.4	0.012	0.3	7.00	MW	C	N
0.188	4.78	II-14	.38	9.5	.156	4.0	4.7	.82	.26	6.7	1.2	5.5	.11	2.8	0.016	0.4	6.00	MW	C	N
0.188	4.78	B12-17	.38	9.5	.152	3.9	8.2	1.4	.23	5.7	1.8	8.2	.10	2.6	0.018	0.5	5.75	MW	CG	N
0.188	4.78	J-39	.38	9.5	.150	3.8	8.8	1.5	.25	6.3	2.2	9.6	.12	3.1	0.019	0.5	6.50	MW	CG	N
0.188	4.78	Y-78	.38	9.5	.146	3.7	20	3.5	.15	3.7	2.9	13	.13	3.2	0.021	0.5	5.00	MW	C	N
0.188	4.78	3425	.38	9.5	.144	3.7	25	4.4	.13	3.4	3.3	15	.13	3.4	0.022	0.6	5.00	MW	C	Z
0.188	4.78	JJ-62	.38	9.5	.144	3.7	19	3.3	.12	3.0	2.2	9.8	.12	3.1	0.022	0.6	5.50	SST	CG	N
0.188	4.78	B5-6	.38	9.5	.142	3.6	19	3.3	.20	5.1	3.8	17	.16	3.9	0.023	0.6	6.75	MW	CG	N
0.188	4.78	10748	.38	9.5	.140	3.6	23	4.0	.19	4.8	4.3	19	.19	4.7	0.024	0.6	6.75	MW	C	N
0.188	4.78	F-87	.38	9.5	.136	3.5	33	5.7	.16	4.0	5.1	23	.20	5.1	0.026	0.7	6.75	MW	C	Z
0.188	4.78	B1-11	.38	9.5	.134	3.4	33	5.8	.12	2.9	3.8	17	.19	4.8	0.027	0.7	7.00	SST	CG	N
0.188	4.78	AA-25	.38	9.5	.132	3.4	29	5.1	.11	2.8	3.2	14	.27	6.8	0.028	0.7	8.50	SST	C	N
0.188	4.78	VV-5	.38	9.5	.132	3.4	42	7.4	.10	2.5	4.2	19	.21	5.3	0.028	0.7	6.50	SST	C	N
0.188	4.78	919																		




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	J-33	.41	10.3	.144	3.7	10	1.8	.20	5.0	2.0	8.8	.21	5.3	0.022	0.6	8.50	SST	C	N
0.188	4.78	L-49	.41	10.3	.142	3.6	21	3.8	.18	4.5	3.8	17	.17	4.2	0.023	0.6	6.25	MW	C	N
0.188	4.78	J-20	.41	10.3	.138	3.5	44	7.7	.10	2.6	4.6	20	.15	3.8	0.025	0.6	5.00	MW	C	Z
0.188	4.78	Z-86	.41	10.3	.136	3.5	27	4.8	.12	3.2	3.4	15	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.188	4.78	GG-14	.41	10.3	.134	3.4	57	10	.10	2.5	5.7	25	.14	3.6	0.027	0.7	5.25	MW	CG	N
0.188	4.78	J-83	.41	10.3	.134	3.4	31	5.4	.18	4.7	5.7	25	.22	5.5	0.027	0.7	8.00	MW	CG	N
0.188	4.78	F-4	.41	10.3	.134	3.4	37	6.4	.16	4.0	5.7	25	.22	5.5	0.027	0.7	7.00	MW	C	Z
0.188	4.78	JJ-29	.41	10.3	.132	3.4	34	5.9	.13	3.2	4.2	19	.22	5.5	0.028	0.7	7.75	SST	CG	N
0.188	4.78	11108	.41	10.3	.126	3.2	47	8.2	.12	3.1	5.7	25	.26	6.7	0.031	0.8	8.50	SST	CG	N
0.188	4.78	F-68	.41	10.3	.124	3.1	81	14	.08	2.1	6.7	30	.26	6.5	0.032	0.8	7.00	SPR	C	Z
0.188	4.78	3449	.41	10.3	.112	2.8	139	24	.07	1.9	10	46	.32	8.2	0.038	1.0	8.50	SPR	CG	GI
0.188	4.78	S-1427	.44	11.1	.166	4.2	.84	.15	.36	9.1	.30	1.3	.08	2.0	0.011	0.3	6.00	SST	C	N
0.188	4.78	10679	.44	11.1	.164	4.2	.81	.14	.33	8.4	.27	1.2	.11	2.7	0.012	0.3	8.03	SST	C	N
0.188	4.78	10590	.44	11.1	.162	4.1	1.5	.27	.33	8.5	.51	2.3	.10	2.6	0.013	0.3	7.00	MW	C	N
0.188	4.78	M-8	.44	11.1	.152	3.9	6.1	1.1	.29	7.5	1.8	8.0	.14	3.7	0.018	0.5	7.00	MW	C	N
0.188	4.78	W-60A	.44	11.1	.152	3.9	4.9	.87	.25	6.3	1.2	5.5	.15	3.9	0.018	0.5	7.50	SST	C	N
0.188	4.78	4329	.44	11.1	.140	3.6	13	2.2	.16	4.0	2.0	8.7	.28	7.2	0.024	0.6	10.8	MW	C	N
0.188	4.78	A9-9	.44	11.1	.138	3.5	19	3.3	.16	4.1	3.1	14	.21	5.2	0.025	0.6	8.25	SST	CG	N
0.188	4.78	F-98	.44	11.1	.138	3.5	22	3.9	.21	5.3	4.6	20	.23	5.7	0.025	0.6	8.00	MW	C	Z
0.188	4.78	S-1432	.44	11.1	.130	3.3	50	8.7	.09	2.4	4.7	21	.22	5.5	0.029	0.7	6.50	SST	C	N
0.188	4.78	FF-2	.44	11.1	.128	3.3	42	7.4	.17	4.3	7.1	32	.27	6.9	0.030	0.8	9.00	MW	CG	Z
0.188	4.78	F-71	.44	11.1	.124	3.1	62	11	.11	2.7	6.7	30	.30	7.7	0.032	0.8	8.50	SPR	C	Z
0.188	4.78	Z-12	.44	11.1	.124	3.1	64	11	.10	2.5	6.2	28	.27	6.9	0.032	0.8	7.50	SST	C	N
0.188	4.78	S-1512	.47	11.9	.164	4.2	1.1	.20	.34	8.7	.39	1.7	.09	2.2	0.012	0.3	6.25	SST	C	N
0.188	4.78	2553	.47	11.9	.148	3.8	11	1.9	.23	5.9	2.5	11	.15	3.8	0.020	0.5	6.50	MW	C	Z
0.188	4.78	MM-26	.47	11.9	.148	3.8	9.7	1.7	.26	6.6	2.5	11	.16	4.1	0.020	0.5	7.00	MW	C	N
0.188	4.78	Y-77	.47	11.9	.140	3.6	22	3.9	.19	4.9	4.3	19	.19	4.9	0.024	0.6	7.00	MW	C	Z
0.188	4.78	J-78	.47	11.9	.138	3.5	26	4.6	.17	4.4	4.6	20	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.188	4.78	Q-22	.47	11.9	.136	3.5	26	4.6	.19	4.9	5.1	23	.23	5.9	0.026	0.7	8.00	MW	C	Z
0.188	4.78	GG-3	.47	11.9	.130	3.3	51	8.9	.09	2.3	4.7	21	.19	4.8	0.029	0.7	6.50	SST	CG	N
0.188	4.78	FF-59	.47	11.9	.126	3.2	55	9.7	.10	2.6	5.7	25	.26	6.7	0.031	0.8	7.50	SST	C	N
0.188	4.78	II-63	.47	11.9	.118	3.0	102	18	.08	2.1	8.3	37	.28	7.1	0.035	0.9	8.00	SPR	CG	N
0.188	4.78	M-125	.47	11.9	.112	2.8	178	31	.06	1.5	10	46	.30	7.7	0.038	1.0	7.00	SPR	C	N
0.188	4.78	A14-5	.50	12.7	.168	4.3	.26	.04	.38	9.7	.10	.43	.12	3.0	0.010	0.3	11.0	SST	C	N
0.188	4.78	11355	.50	12.7	.164	4.2	1.3	.23	.30	7.7	.39	1.7	.08	2.1	0.012	0.3	5.75	SST	C	N
0.188	4.78	GG-18	.50	12.7	.160	4.1	.93	.16	.32	8.1	.29	1.3	.18	4.6	0.014	0.4	12.0	SST	C	N
0.188	4.78	B5-11	.50	12.7	.158	4.0	2.8	.49	.38	9.7	1.1	4.8	.12	3.0	0.015	0.4	7.00	MW	C	N
0.188	4.78	3727	.50	12.7	.154	3.9	2.3	.41	.27	6.9	.63	2.8	.23	5.8	0.017	0.4	12.5	MW	C	Z
0.188	4.78	CC-61	.50	12.7	.148	3.8	8.2	1.4	.31	7.8	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.188	4.78	K-13	.50	12.7	.148	3.8	6.2	1.1	.28	7.1	1.7	7.7	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.188	4.78	B4-18	.50	12.7	.148	3.8	8.1	1.4	.31	7.9	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	N
0.188	4.78	NN-29	.50	12.7	.146	3.7	9.0	1.6	.21	5.4	1.9	8.6	.19	4.8	0.021	0.5	8.00	SST	C	N
0.188	4.78	3530	.50	12.7	.144	3.7	8.3	1.5	.26	6.6	2.1	9.6	.24	6.1	0.022	0.6	11.0	MW	CG	Z
0.188	4.78	A13-1	.50	12.7	.144	3.7	12	2.1	.28	7.0	3.3	15	.18	4.6	0.022	0.6	8.25	MW	CG	GI
0.188	4.78	920	.50	12.7	.142	3.6	11	2.0	.25	6.3	2.8	13	.25	6.4	0.023	0.6	10.0	MW	C	Z
0.188	4.78	FF-27	.50	12.7	.140	3.6	28	4.8	.10	2.6	2.9	13	.17	4.3	0.024	0.6	6.00	SST	C	N
0.188	4.78	O-108	.50	12.7	.140	3.6	22	3.9	.19	4.9	4.3	19	.19	4.9	0.024	0.6	7.00	MW	C	BO
0.188	4.78	VV-69	.50	12.7	.140	3.6	16	2.8	.18	4.5	2.9	13	.22	5.5	0.024	0.6	8.00	SST	C	N
0.188	4.78	3986	.50	12.7	.138	3.5	26	4.6	.17	4.4	4.6	20	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.188	4.78	LL-42	.50	12.7	.138	3.5	20	3.6	.22	5.7	4.6	20	.24	6.0	0.025	0.6	8.50	MW	C	N
0.188	4.78	B7-18	.50	12.7	.138	3.4	19	3.4	.24	6.0	4.6	20	.22	5.6	0.025	0.6	8.75	MW	CG	N
0.188	4.78	W-69	.50	12.7	.134	3.4	18.04	3.1	.16	4.1	2.9	12.8	.297	7.4	0.027	0.69	11.0	SST	CG	N
0.188	4.78	528	.50	12.7	.132	3.4	34	5.9	.19	4.8	6.3	28	.27	6.8	0.028	0.7	8.50	MW	C	Z
0.188	4.78	DD-9	.50	12.7	.128	3.3	37	6.5	.14	3.5	5.2	23	.30	7.6	0.030	0.8	9.00	SST	C	N
0.188	4.78	EE-29	.50	12.7	.128	3.3	30	5.3	.14	3.6	4.2	19	.36	9.1	0.030	0.8	12.0	MW	CG	N
0.188	4.78	NN-3	.50	12.7	.128	3.3	42	7.4	.18	4.7	7.7	34	.30	7.6	0.030	0.8	9.00	MW	C	N
0.188	4.78	BE-15	.50	12.7	.126	3.2	47	8.3	.18	4.6	8.5	38	.29	7.3	0.031	0.8	9.25	MW	CG	N
0.188	4.78	PP-82	.50	12.7	.124	3.1	44	7.7	.14	3.6	6.2	28	.35	8.9	0.032	0.8	10.0	SST	C	N
0.188	4.78	S-709	.50	12.7	.124	3.1	50	8.8	.12	3.1	6.2	28	.32	8.1	0.032	0.8	9.00	SST	C	N
0.188	4.78	F-22	.50	12.7	.122	3.1	62	11	.12	3.0	7.3	33	.35	8.8	0.033	0.8	9.50	SPR	C	Z
0.188	4.78	B15-18	.53	13.5	.144	3.7	29	5.2	.11	2.9	3.3	15	.10	2.5	0.022	0.6	4.50	MW	CG	GI
0.188	4.78	F-89	.53	13.5	.136	3.5	23	4.0	.22	5.7	5.1	23	.25	6.4	0.026	0.7	8.75	MW	C	Z
0.188	4.78	2637	.53	13.5	.132	3.4	27	4.8	.22	5.7	6.1	27	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.188	4.78	NN-74	.53	13.5	.132	3.4	21	3.7	.20	5.1	4.2	19	.31	7.8	0.028	0.7	11.0	SST	CG	N
0.188	4.78	FF-29	.56	14.3	.164	4.2	.93	.16	.45	12	.42	1.9	.11	2.7	0.012	0.3	8.00	MW	C	Z
0.188	4.78	J-21	.56	14.3	.158	4.0	1.2	.21	.34	8.6	.40	1.8	.23	5.7	0.015	0.4	14.0	MW	C	Z
0.188	4.78	KK-14	.56	14.3	.158	4.0	.65	.11	.23	5.9	.15	.68	.33	8.4	0.015	0.4	21.0	SST	C	N
0.188	4.78	VV-11	.56	14.3	.158	4.0	2.4	.42	.43	11	1.0	4.5	.14	3.4	0.015	0.4	8.00	MW	C	N
0.188	4.78	H-8	.56	14.3	.154	3.9	2.0	.36	.32	8.2	.66	2.9	.24	6.0	0.017	0.4	14.0	MW	CG	Z
0.188	4.78	Q-17	.56	14.3	.150	3.8	4.4	.77	.35	9.0	1.5	6.9	.21							




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	II-3	.56	14.3	.130	3.3	52	9.0	.14	3.5	7.0	31	.23	5.9	0.029	0.7	7.00	MW	C	Z
0.188	4.78	Z-91	.56	14.3	.128	3.3	50	8.8	.15	3.9	7.7	34	.27	6.9	0.030	0.8	8.00	MW	C	Z
0.188	4.78	N-25	.56	14.3	.118	3.0	91	16	.09	2.2	7.7	34	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.188	4.78	JJ-18	.59	15.1	.160	4.1	1.1	.19	.41	10	.44	1.9	.18	4.6	0.014	0.4	12.0	MW	C	N
0.188	4.78	U-100	.59	15.1	.160	4.1	1.7	.31	.48	12	.84	3.7	.11	2.8	0.014	0.4	8.00	MW	CG	N
0.188	4.78	O-36	.59	15.1	.152	3.9	6.1	1.1	.30	7.6	1.8	8.2	.14	3.7	0.018	0.5	7.00	MW	C	N
0.188	4.78	A9-15	.59	15.1	.148	3.8	3.1	.55	.27	6.9	.85	3.8	.32	8.1	0.020	0.5	16.0	SST	CG	N
0.188	4.78	Z-46	.59	15.1	.148	3.8	4.8	.84	.35	8.9	1.7	7.4	.22	5.6	0.020	0.5	11.0	SST	CG	N
0.188	4.78	B14-43	.59	15.1	.146	3.7	6.0	1.1	.34	8.7	2.0	9.1	.25	6.4	0.021	0.5	12.0	MW	CG	N
0.188	4.78	B14-48	.59	15.1	.132	3.4	22	3.8	.26	6.5	5.5	25	.34	8.5	0.028	0.7	12.0	MW	CG	N
0.188	4.78	V-50	.59	15.1	.130	3.3	18	3.2	.17	4.4	3.2	14	.42	10.7	0.029	0.7	14.5	SST	CG	N
0.188	4.78	B1-9	.59	15.1	.122	3.1	44	7.6	.16	4.0	6.8	30	.38	9.6	0.033	0.8	11.5	SST	CG	N
0.188	4.78	F-73	.59	15.1	.122	3.1	54	9.4	.14	3.5	7.3	33	.38	9.6	0.033	0.8	10.5	HD	C	N
0.188	4.78	B15-6	.59	15.1	.114	2.9	87	15	.11	2.8	9.7	43	.41	10.3	0.037	0.9	11.0	SPR	CG	N
0.188	4.78	B4-5	.59	15.1	.138	3.5	16	2.8	.29	7.4	4.6	20	.28	7.1	0.025	0.6	10.3	MW	C	N
0.188	4.78	10896	.63	15.9	.170	4.3	.16	.03	.52	13	.08	.37	.11	2.7	0.009	0.2	11.0	SST	C	N
0.188	4.78	RR-13	.63	15.9	.164	4.2	.54	.09	.48	12	.26	1.1	.14	3.7	0.012	0.3	11.0	SST	C	N
0.188	4.78	N-314	.63	15.9	.158	4.0	1.8	.31	.47	12	.83	3.7	.15	3.9	0.015	0.4	10.1	MW	CG	N
0.188	4.78	00-11	.63	15.9	.156	4.0	.86	.15	.27	6.9	.24	1.0	.35	8.9	0.016	0.4	21.0	SST	C	N
0.188	4.78	B9-63	.63	15.9	.150	3.8	6.5	1.1	.33	8.5	2.2	9.6	.15	3.9	0.019	0.5	8.00	MW	CG	N
0.188	4.78	PP-19	.63	15.9	.144	3.7	6.2	1.1	.30	7.5	1.8	8.2	.33	8.4	0.022	0.6	14.0	MW	C	N
0.188	4.78	S-707	.63	15.9	.144	3.7	8.1	1.4	.27	6.9	2.2	9.8	.24	6.1	0.022	0.6	10.0	SST	C	N
0.188	4.78	921	.63	15.9	.142	3.6	13	2.2	.30	7.7	3.8	17	.24	6.0	0.023	0.6	9.25	MW	C	Z
0.188	4.78	A-83	.63	15.9	.138	3.5	11	2.0	.27	6.8	3.1	14	.33	8.3	0.025	0.6	12.0	SST	C	N
0.188	4.78	F-19	.63	15.9	.138	3.5	12	2.1	.28	7.0	3.3	15	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.188	4.78	Q-71	.63	15.9	.136	3.5	14	2.5	.26	6.6	3.7	17	.36	9.2	0.026	0.7	13.0	MW	C	N
0.188	4.78	AA-67	.63	15.9	.128	3.3	33	5.7	.24	6.0	7.7	34	.36	9.1	0.030	0.8	11.0	MW	C	Z
0.188	4.78	NN-84	.63	15.9	.124	3.1	54	9.5	.12	3.2	6.7	30	.30	7.7	0.032	0.8	9.50	SPR	CG	N
0.188	4.78	S-710	.63	15.9	.124	3.1	38	6.7	.16	4.2	6.2	28	.39	10.0	0.032	0.8	11.3	SST	C	N
0.188	4.78	10604	.63	15.9	.122	3.1	51	8.9	.14	3.7	7.3	33	.40	10.1	0.033	0.8	11.0	SPR	C	Z
0.188	4.78	A9-18	.66	16.7	.168	4.3	.24	.04	.53	13	.13	.57	.13	3.2	0.010	0.3	11.5	SST	C	N
0.188	4.78	PP-35	.66	16.7	.152	3.9	3.4	.60	.36	9.2	1.2	5.5	.20	5.0	0.018	0.5	10.0	SST	C	N
0.188	4.78	H-15	.66	16.7	.148	3.8	8.1	1.4	.31	7.9	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	N
0.188	4.78	G-9	.66	16.7	.140	3.6	13	2.3	.33	8.4	4.3	19	.25	6.4	0.024	0.6	10.5	MW	CG	N
0.188	4.78	F-69	.66	16.7	.136	3.5	18	3.1	.29	7.3	5.1	23	.31	7.8	0.026	0.7	10.8	MW	C	Z
0.188	4.78	Q-18	.69	17.4	.160	4.1	.53	.09	.39	10	.21	.92	.29	7.5	0.014	0.4	20.0	SST	C	N
0.188	4.78	YY-45	.69	17.4	.158	4.0	1.6	.28	.51	13	.81	3.6	.18	4.6	0.015	0.4	11.0	MW	C	N
0.188	4.78	B5-23	.69	17.4	.154	3.9	2.6	.46	.40	10	1.0	4.6	.17	4.3	0.017	0.4	10.0	SST	CG	N
0.188	4.78	A9-47	.69	17.4	.152	3.9	3.9	.68	.47	12	1.8	8.2	.20	5.0	0.018	0.5	10.0	MW	C	BO
0.188	4.78	O-149	.69	17.4	.150	3.8	4.9	.85	.45	11	2.2	9.6	.19	4.8	0.019	0.5	10.0	MW	CG	N
0.188	4.78	I-68	.69	17.4	.148	3.8	3.8	.67	.39	10	1.5	6.6	.30	7.5	0.020	0.5	14.8	MW	CG	N
0.188	4.78	II-30	.69	17.4	.148	3.8	4.9	.85	.43	11	2.1	9.2	.26	6.6	0.020	0.5	12.0	MW	C	N
0.188	4.78	G-76	.69	17.4	.142	3.6	10	1.7	.38	9.7	3.8	17	.25	6.4	0.023	0.6	11.0	MW	CG	N
0.188	4.78	PP-15	.69	17.4	.138	3.5	22	3.9	.21	5.3	4.6	20	.23	5.7	0.025	0.6	8.00	MW	C	BO
0.188	4.78	A14-13	.69	17.4	.132	3.4	23	3.9	.28	7.1	6.3	28	.33	8.4	0.028	0.7	11.8	MW	CG	GI
0.188	4.78	B9-36	.69	17.4	.130	3.3	27	4.7	.26	6.6	7.0	31	.33	8.3	0.029	0.7	11.3	MW	CG	N
0.188	4.78	2610	.69	17.4	.124	3.1	45	7.9	.21	5.3	9.3	41	.38	9.8	0.032	0.8	11.0	MW	C	Z
0.188	4.78	A-30	.69	17.4	.122	3.1	52	9.1	.20	5.0	10	45	.40	10.1	0.033	0.8	11.0	MW	C	N
0.188	4.78	F-90	.69	17.4	.122	3.1	48	8.4	.15	3.9	7.3	33	.41	10.5	0.033	0.8	11.5	HD	C	Z
0.188	4.78	Q0-7	.69	17.4	.108	2.7	105	18	.11	2.9	12	54	.52	13.2	0.040	1.0	13.0	SPR	CG	Z
0.188	4.78	2809	.72	18.2	.158	4.0	1.8	.31	.55	14	.99	4.4	.17	4.2	0.015	0.4	10.0	MW	C	Z
0.188	4.78	S-1115	.72	18.2	.158	4.0	1.8	.31	.40	10	.72	3.2	.15	3.8	0.015	0.4	9.00	SST	C	N
0.188	4.78	2584	.72	18.2	.156	4.0	1.7	.30	.49	13	.85	3.8	.22	5.7	0.016	0.4	13.0	MW	C	GI
0.188	4.78	10890	.72	18.2	.148	3.8	4.9	.85	.46	12	2.2	9.9	.26	6.6	0.020	0.5	12.0	MW	C	N
0.188	4.78	F-83	.72	18.2	.136	3.5	15	2.7	.33	8.4	5.1	23	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.188	4.78	S-1333	.75	19.1	.166	4.2	.48	.08	.63	16	.30	1.3	.11	2.8	0.011	0.3	9.00	SST	C	N
0.188	4.78	KK-96	.75	19.1	.160	4.1	.93	.16	.57	14	.53	2.3	.18	4.6	0.014	0.4	12.0	SST	C	N
0.188	4.78	U-25	.75	19.1	.158	4.0	.73	.13	.45	11	.33	1.5	.30	7.6	0.015	0.4	19.0	SST	C	N
0.188	4.78	V-72	.75	19.1	.156	4.0	2.1	.36	.56	14	1.1	5.1	.19	4.9	0.016	0.4	11.0	MW	C	N
0.188	4.78	3927	.75	19.1	.154	3.9	2.7	.48	.55	14	1.5	6.6	.20	5.2	0.017	0.4	11.0	MW	C	Z
0.188	4.78	10184	.75	19.1	.152	3.9	3.6	.63	.51	13	1.8	8.2	.21	5.3	0.018	0.5	10.5	MW	C	Z
0.188	4.78	00-57	.75	19.1	.152	3.9	2.5	.43	.50	13	1.2	5.5	.25	6.4	0.018	0.5	13.0	SST	C	N
0.188	4.78	A15-23	.75	19.1	.144	3.7	7.5	1.3	.44	11	3.3	15	.26	6.7	0.022	0.6	12.0	MW	CG	N
0.188	4.78	B7-14	.75	19.1	.144	3.7	7.7	1.4	.43	11	3.3	15	.25	6.4	0.022	0.6	11.5	MW	CG	Z
0.188	4.78	S-708	.75	19.1	.144	3.7	6.5	1.1	.34	8.6	2.2	9.8	.29	7.3	0.022	0.6	12.0	SST	C	N
0.188	4.78	A15-18	.75	19.1	.138	3.5	12	2.1	.38	9.6	4.6	20	.33	8.3	0.025	0.6	13.0	MW	CG	N
0.188	4.78	HH-42	.75	19.1	.128	3.3	23	4.0	.30	7.6	6.8	30	.45	11.4	0.030	0.8	15.0	MW	CG	N
0.188	4.78	NN-89	.75	19.1	.128	3.3	20	3.5	.26	6.7	5.2	23	.47	11.8	0.030	0.8	15.5	SST	CG	N
0.188	4.78	NN-42	.75	19.1	.126	3.2	25	4.4	.22	5.7	5.7	25	.43	11.0	0.031	0.8	14.0	SST	CG	N
0.188	4.78	F-85	.																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	UU-5	.81	20.6	.152	3.9	3.4	.60	.36	9.2	1.2	5.5	.20	5.0	0.018	0.5	10.0	SST	C	N
0.188	4.78	II-26	.81	20.6	.142	3.6	8.5	1.5	.45	11	3.8	17	.32	8.0	0.023	0.6	12.8	MW	C	N
0.188	4.78	M-40	.81	20.6	.138	3.5	24	4.1	.19	4.9	4.6	20	.19	4.8	0.025	0.6	7.50	MW	CG	Z
0.188	4.78	A14-16	.81	20.6	.136	3.5	10	1.8	.34	8.7	3.6	16	.47	11.9	0.026	0.7	17.0	MW	C	Z
0.188	4.78	2970	.81	20.6	.134	3.4	16	2.7	.37	9.3	5.7	25	.41	10.3	0.027	0.7	14.0	MW	C	GI
0.188	4.78	KK-99	.81	20.6	.098	2.5	179	31	.09	2.4	17	74	.61	15.4	0.045	1.1	13.5	SPR	CG	Z
0.188	4.78	A10-57	.84	21.4	.160	4.1	.86	.15	.71	18	.61	2.7	.14	3.5	0.014	0.4	8.75	PB	C	N
0.188	4.78	B5-70	.84	21.4	.156	4.0	2.2	.38	.60	15	1.3	5.8	.18	4.7	0.016	0.4	10.5	MW	C	N
0.188	4.78	KK-12	.84	21.4	.152	3.9	1.7	.30	.50	13	.85	3.8	.34	8.7	0.018	0.5	18.0	SST	C	N
0.188	4.78	3026	.84	21.4	.138	3.5	12	2.1	.39	9.9	4.6	20	.36	9.0	0.025	0.6	13.3	MW	C	Z
0.188	4.78	F-80	.84	21.4	.136	3.5	13	2.3	.40	10	5.1	23	.39	9.9	0.026	0.7	14.0	MW	C	Z
0.188	4.78	F-75	.84	21.4	.122	3.1	35	6.2	.21	5.3	7.3	33	.53	13.4	0.033	0.8	15.0	HD	C	Z
0.188	4.78	GG-49	.88	22.2	.160	4.1	.32	.06	.43	11	.14	.61	.45	11.4	0.014	0.4	31.0	SST	C	N
0.188	4.78	922	.88	22.2	.156	4.0	1.3	.24	.60	15	.81	3.6	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.188	4.78	B14-61	.88	22.2	.152	3.9	3.1	.53	.60	15	1.8	8.2	.21	5.4	0.018	0.5	10.8	MW	C	Z
0.188	4.78	S-1161	.88	22.2	.144	3.7	6.5	1.1	.34	8.6	2.2	9.8	.29	7.3	0.022	0.6	12.0	SST	C	N
0.188	4.78	S-1340	.88	22.2	.142	3.6	9.9	1.7	.25	6.5	2.5	11	.25	6.4	0.023	0.6	10.0	SST	C	N
0.188	4.78	B1-18	.88	22.2	.136	3.5	12	2.2	.41	11	5.1	23	.38	9.7	0.026	0.7	14.8	MW	CG	N
0.188	4.78	L-87	.88	22.2	.126	3.2	31	5.5	.27	6.9	8.5	38	.43	11.0	0.031	0.8	13.0	MW	C	N
0.188	4.78	S-712	.88	22.2	.124	3.1	26	4.5	.24	6.2	6.2	28	.54	13.6	0.032	0.8	15.8	SST	C	N
0.188	4.78	B12-27	.88	22.2	.124	3.1	27	4.8	.24	6.2	6.7	30	.53	13.4	0.032	0.8	16.5	SPR	CG	Z
0.188	4.78	O-85	.88	22.2	.110	2.8	67	12	.17	4.3	11	50	.70	17.8	0.039	1.0	17.0	SPR	C	N
0.188	4.78	J-91	.88	22.2	.108	2.7	77	14	.16	3.9	12	53	.72	18.3	0.040	1.0	17.0	SPR	C	N
0.188	4.78	B14-23	.91	23.0	.154	3.9	3.0	.53	.52	13	1.6	6.9	.17	4.3	0.017	0.4	10.0	MW	CG	N
0.188	4.78	F-51	.91	23.0	.138	3.5	8.3	1.4	.43	11	3.6	16	.48	12.1	0.025	0.6	18.0	MW	C	Z
0.188	4.78	V-86	.91	23.0	.138	3.5	11	1.9	.43	11	4.6	20	.38	9.7	0.025	0.6	14.3	MW	C	N
0.188	4.78	J-58	.91	23.0	.136	3.5	12	2.1	.42	11	5.1	23	.41	10.5	0.026	0.7	14.9	MW	C	Z
0.188	4.78	F-77	.91	23.0	.124	3.1	29	5.1	.23	5.9	6.7	30	.54	13.8	0.032	0.8	16.0	SPR	C	Z
0.188	4.78	FF-65	.94	23.8	.152	3.9	1.5	.26	.56	14	.85	3.8	.38	9.6	0.018	0.5	20.0	SST	C	N
0.188	4.78	S-1334	.94	23.8	.142	3.6	5.7	.99	.44	11	2.5	11	.39	9.9	0.023	0.6	16.0	SST	C	N
0.188	4.78	V-27	.94	23.8	.142	3.6	6.1	1.1	.52	13	3.2	14	.41	10.5	0.023	0.6	17.0	MW	C	N
0.188	4.78	F-95	.94	23.8	.124	3.1	25	4.4	.26	6.7	6.7	30	.61	15.4	0.032	0.8	18.0	SPR	C	Z
0.188	4.78	H-67	.97	24.6	.144	3.7	4.1	.73	.53	14	2.2	9.8	.39	9.9	0.022	0.6	17.8	SST	CG	N
0.188	4.78	Q-55	1.00	25.4	.166	4.2	.17	.03	.77	20	.13	.59	.23	5.8	0.011	0.3	21.0	SST	C	N
0.188	4.78	152-A	1.00	25.4	.162	4.1	.99	.17	.79	20	.78	3.5	.14	3.6	0.013	0.3	9.75	MW	C	Z
0.188	4.78	153-A	1.00	25.4	.160	4.1	1.2	.22	.78	20	.97	4.3	.16	4.1	0.014	0.4	10.5	MW	C	Z
0.188	4.78	Q-69	1.00	25.4	.160	4.1	.43	.07	.63	16	.27	1.2	.37	9.4	0.014	0.4	26.5	MW	CG	N
0.188	4.78	353-A	1.00	25.4	.156	4.0	2.0	.35	.66	17	1.3	5.8	.20	5.1	0.016	0.4	11.5	MW	C	Z
0.188	4.78	N-37	1.00	25.4	.156	4.0	2.3	.41	.56	14	1.3	5.8	.18	4.5	0.016	0.4	10.0	MW	C	Z
0.188	4.78	352-A	1.00	25.4	.152	3.9	3.0	.52	.62	16	1.8	8.2	.24	6.2	0.018	0.5	12.5	MW	C	Z
0.188	4.78	B15-2	1.00	25.4	.152	3.9	2.0	.35	.61	15	1.2	5.5	.28	7.1	0.018	0.5	15.5	SST	CG	N
0.188	4.78	154-A	1.00	25.4	.148	3.8	4.2	.74	.60	15	2.5	11	.29	7.4	0.020	0.5	13.5	MW	C	Z
0.188	4.78	FF-57	1.00	25.4	.148	3.8	2.7	.47	.62	16	1.7	7.4	.36	9.1	0.020	0.5	18.0	SST	CG	N
0.188	4.78	V-9	1.00	25.4	.148	3.8	2.7	.47	.62	16	1.7	7.4	.38	9.7	0.020	0.5	18.0	SST	C	N
0.188	4.78	10171	1.00	25.4	.146	3.7	3.5	.61	.58	15	2.0	8.9	.43	10.8	0.021	0.5	19.3	MW	C	Z
0.188	4.78	2597	1.00	25.4	.146	3.7	4.2	.74	.63	16	2.7	12	.37	9.3	0.021	0.5	16.5	MW	C	Z
0.188	4.78	K-85	1.00	25.4	.144	3.7	6.8	1.2	.49	12	3.3	15	.31	7.8	0.022	0.6	13.0	MW	C	Z
0.188	4.78	155-A	1.00	25.4	.142	3.6	7.0	1.2	.54	14	3.8	17	.36	9.2	0.023	0.6	14.8	MW	C	Z
0.188	4.78	3692	1.00	25.4	.140	3.6	6.5	1.1	.52	13	3.4	15	.48	12.2	0.024	0.6	19.0	MW	C	Z
0.188	4.78	L-88	1.00	25.4	.138	3.5	9.4	1.7	.48	12	4.6	20	.40	10.2	0.025	0.6	16.0	MW	CG	N
0.188	4.78	LL-55	1.00	25.4	.138	3.5	10	1.8	.45	11	4.6	20	.38	9.5	0.025	0.6	15.0	MW	CG	Z
0.188	4.78	B15-52	1.00	25.4	.138	3.5	9.3	1.6	.49	12	4.6	20	.40	10.2	0.025	0.6	16.0	MW	CG	N
0.188	4.78	156-A	1.00	25.4	.132	3.4	15	2.7	.42	11	6.3	28	.48	12.3	0.028	0.7	16.3	MW	C	Z
0.188	4.78	S-713	1.00	25.4	.124	3.1	22	3.9	.28	7.2	6.2	28	.61	15.4	0.032	0.8	18.0	SST	C	N
0.188	4.78	B10-20	1.00	25.4	.124	3.1	26	4.5	.26	6.6	6.7	30	.59	15.0	0.032	0.8	17.5	SPR	C/G	N
0.188	4.78	1509	1.03	26.2	.144	3.7	8.2	1.4	.41	10	3.3	15	.26	6.7	0.022	0.6	11.0	MW	C	Z
0.188	4.78	G-72	1.03	26.2	.144	3.7	4.6	.81	.61	16	2.8	13	.42	10.6	0.022	0.6	18.0	MW	C	Z
0.188	4.78	A-88	1.06	27.0	.158	4.0	.73	.13	.76	19	.56	2.5	.30	7.6	0.015	0.4	19.0	SST	C	N
0.188	4.78	YY-10	1.06	27.0	.154	3.9	1.8	.32	.78	20	1.4	6.3	.28	7.1	0.017	0.4	15.5	MW	C	Z
0.188	4.78	W-23	1.06	27.0	.138	3.5	6.0	1.1	.50	13	3.1	14	.55	14.0	0.025	0.6	21.0	SST	C	N
0.188	4.78	LL-51	1.09	27.8	.152	3.9	2.2	.38	.56	14	1.2	5.5	.28	7.1	0.018	0.5	14.5	SST	C	N
0.188	4.78	M-68	1.09	27.8	.142	3.6	5.3	.93	.48	12	2.5	11	.39	9.9	0.023	0.6	17.0	SST	CG	N
0.188	4.78	10801	1.13	28.6	.154	3.9	2.1	.36	.50	13	1.0	4.6	.23	5.7	0.017	0.4	12.3	SST	C	N
0.188	4.78	3241	1.13	28.6	.120	3.0	36	6.3	.31	7.9	11	49	.61	15.5	0.034	0.9	17.0	MW	C	Z
0.188	4.78	B9-44	1.19	30.2	.138	3.5	12	2.2	.37	9.4	4.6	20	.31	7.9	0.025	0.6	12.5	MW	CG	Z
0.188	4.78	B14-24	1.22	31.0	.156	4.0	1.4	.25	.91	23	1.3	5.8	.26	6.5	0.016	0.4	15.0	MW	C	N
0.188	4.78	M-3	1.22	31.0	.128	3.3	16	2.8	.49	12	7.7	34	.63	16.0	0.030	0.8	21.0	MW	CG	N
0.188	4.78	10005	1.25	31.8	.142	3.6	5.1	.89	.75	19	3.8	17	.48	12.3	0.023	0.6	20.0	MW	C	Z
0.188	4.78	GG-17	1.28	32.5	.148	3.8	2.5	.43	.68	17	1.7	7.4	.39	9.9	0.020	0.5	19.5	SST	CG	N
0.188	4.78	AA-91	1.28	32.5																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	154-B	1.38	34.9	.148	3.8	3.0	.53	.83	21	2.5	11	.38	9.7	0.020	0.5	18.0	MW	C	Z
0.188	4.78	GG-28	1.38	34.9	.148	3.8	2.7	.47	.93	24	2.5	11	.40	10.2	0.020	0.5	20.0	MW	CG	N
0.188	4.78	B9-70	1.38	34.9	.148	3.8	2.9	.50	.88	22	2.5	11	.38	9.7	0.020	0.5	19.0	MW	CG	Z
0.188	4.78	Q-19	1.38	34.9	.144	3.7	4.1	.72	.81	21	3.3	15	.46	11.7	0.022	0.6	20.0	MW	C	Z
0.188	4.78	155-B	1.38	34.9	.142	3.6	5.0	.87	.76	19	3.8	17	.48	12.3	0.023	0.6	20.0	MW	C	Z
0.188	4.78	S-1157	1.38	34.9	.138	3.5	6.4	1.1	.48	12	3.1	14	.53	13.3	0.025	0.6	20.0	SST	C	N
0.188	4.78	156-B	1.38	34.9	.132	3.4	11	1.9	.59	15	6.3	28	.65	16.5	0.028	0.7	22.3	MW	C	Z
0.188	4.78	12024	1.41	35.7	.150	3.8	2.3	.40	.63	16	1.4	6.4	.34	8.7	0.019	0.5	17.0	SST	C	N
0.188	4.78	S-1105	1.44	36.5	.152	3.9	.94	.16	.86	22	.81	3.6	.58	14.6	0.018	0.5	31.0	SST	C	N
0.188	4.78	J-74	1.44	36.5	.138	3.5	5.6	.98	.54	14	3.1	14	.56	14.3	0.025	0.6	22.5	SST	CG	N
0.188	4.78	A10-61	1.44	36.5	.136	3.5	5.2	.91	.66	17	3.4	15	.78	19.8	0.026	0.7	29.0	SST	C	N
0.188	4.78	S-1317	1.44	36.5	.134	3.4	7.5	1.3	.51	13	3.8	17	.63	16.1	0.027	0.7	23.5	SST	CG	N
0.188	4.78	S-1071	1.44	36.5	.132	3.4	8.0	1.4	.53	14	4.2	19	.76	19.2	0.028	0.7	26.0	SST	C	N
0.188	4.78	923	1.50	38.1	.148	3.8	2.1	.38	.98	25	2.1	9.4	.52	13.2	0.020	0.5	25.0	MW	C	Z
0.188	4.78	B2-17	1.50	38.1	.148	3.8	1.8	.31	.90	23	1.6	7.2	.60	15.2	0.020	0.5	29.0	MW	C	N
0.188	4.78	11194	1.50	38.1	.138	3.5	5.6	.98	.54	14	3.1	14	.56	14.3	0.025	0.6	22.5	SST	CG	N
0.188	4.78	11264	1.50	38.1	.124	3.1	19	3.4	.49	12	9.3	41	.76	19.3	0.032	0.8	22.8	MW	C	N
0.188	4.78	11206	1.56	39.7	.138	3.5	5.8	1.0	.53	13	3.1	14	.55	14.0	0.025	0.6	22.0	SST	CG	N
0.188	4.78	Z-3	1.63	41.3	.168	4.3	.15	.03	1.4	36	.21	.95	.20	5.1	0.010	0.3	19.0	MW	C	N
0.188	4.78	11240	1.63	41.3	.128	3.3	11	1.9	.71	18	7.7	34	.90	22.9	0.030	0.8	29.0	MW	C	Z
0.188	4.78	N-122	1.69	42.8	.148	3.8	2.5	.43	1.0	26	2.5	11	.46	11.7	0.020	0.5	22.0	MW	C	N
0.188	4.78	EE-47	1.69	42.8	.128	3.3	25	4.3	.31	8.0	7.7	34	.45	11.4	0.030	0.8	14.0	MW	C	N
0.188	4.78	152-C	1.75	44.5	.162	4.1	.56	.10	1.4	35	.78	3.5	.22	5.5	0.013	0.3	15.8	MW	C	Z
0.188	4.78	153-C	1.75	44.5	.160	4.1	.69	.12	1.4	36	.97	4.3	.26	6.5	0.014	0.4	17.3	MW	C	Z
0.188	4.78	353-C	1.75	44.5	.156	4.0	1.1	.19	1.2	30	1.3	5.8	.32	8.1	0.016	0.4	19.0	MW	C	Z
0.188	4.78	352-C	1.75	44.5	.152	3.9	1.7	.29	1.1	28	1.8	8.2	.39	9.9	0.018	0.5	20.8	MW	C	Z
0.188	4.78	154-C	1.75	44.5	.148	3.8	2.3	.41	1.1	27	2.5	11	.48	12.1	0.020	0.5	22.8	MW	C	Z
0.188	4.78	2503	1.75	44.5	.148	3.8	3.5	.61	.73	18	2.5	11	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.188	4.78	NN-34	1.75	44.5	.148	3.8	2.1	.37	1.2	30	2.5	11	.52	13.2	0.020	0.5	25.0	MW	C	Z
0.188	4.78	PP-84	1.75	44.5	.146	3.7	2.4	.42	1.2	29	2.8	12	.60	15.2	0.021	0.5	27.5	MW	C	N
0.188	4.78	155-C	1.75	44.5	.142	3.6	3.9	.68	.97	25	3.8	17	.60	15.2	0.023	0.6	25.0	MW	C	Z
0.188	4.78	11407	1.75	44.5	.136	3.5	6.4	1.1	.79	20	5.1	23	.70	17.8	0.026	0.7	26.0	MW	C	Z
0.188	4.78	156-C	1.75	44.5	.132	3.4	8.3	1.5	.76	19	6.3	28	.81	20.6	0.028	0.7	28.0	MW	C	Z
0.188	4.78	A15-48	1.75	44.5	.122	3.1	25	4.4	.27	6.9	6.8	30	.61	15.5	0.033	0.8	18.5	SST	CG	N
0.188	4.78	10003	1.88	47.6	.142	3.6	4.4	.77	.86	22	3.8	17	.52	13.3	0.023	0.6	22.8	MW	CG	Z
0.188	4.78	2631	1.88	47.6	.130	3.3	8.3	1.5	.84	21	7.0	31	.96	24.3	0.029	0.7	33.0	MW	CG	Z
0.188	4.78	Y-86	1.88	47.6	.122	3.1	18	3.2	.40	10	7.3	33	.94	23.9	0.033	0.8	27.5	SPR	C	N
0.188	4.78	S-1351	1.88	47.6	.118	3.0	24	4.3	.32	8.1	7.7	34	.84	21.3	0.035	0.9	24.0	SST	CG	N
0.188	4.78	N-50	1.94	49.2	.138	3.5	4.7	.83	.97	25	4.6	20	.78	19.7	0.025	0.6	30.0	MW	C	Z
0.188	4.78	EE-14	2.00	50.8	.168	4.3	.08	.01	1.7	43	.13	.56	.32	8.1	0.010	0.3	32.0	SST	CG	N
0.188	4.78	B14-42	2.25	57.2	.160	4.1	.50	.09	1.9	49	.96	4.2	.34	8.5	0.014	0.4	23.0	MW	C	Z
0.188	4.78	JJ-87	2.25	57.2	.130	3.3	6.0	1.0	.92	23	5.5	24	1.33	33.9	0.029	0.7	45.0	MW	C	BO
0.188	4.78	3575	2.50	63.5	.130	3.3	5.5	.96	1.1	27	5.8	26	1.45	36.8	0.029	0.7	49.0	MW	C	Z
0.188	4.78	N-27	2.53	64.3	.150	3.8	1.3	.23	1.7	42	2.2	9.6	.61	15.4	0.019	0.5	32.0	MW	CG	N
0.188	4.78	S-1237	2.75	69.9	.128	3.3	5.8	1.0	.89	23	5.2	23	1.44	36.6	0.030	0.8	47.0	SST	C	N
0.188	4.78	TT-44	2.75	69.9	.128	3.3	6.8	1.2	1.1	29	7.7	34	1.41	35.8	0.030	0.8	46.0	MW	C	N
0.188	4.78	B15-43	3.00	76.2	.136	3.5	2.7	.47	1.4	36	3.8	17	1.59	40.3	0.026	0.7	60.0	MW	C	N
0.188	4.78	VV-54	3.13	79.4	.140	3.6	2.2	.39	1.3	33	2.9	13	1.10	28.0	0.024	0.6	45.0	SST	C	N
0.188	4.78	O-72	4.00	101.6	.148	3.8	1.1	.19	1.6	40	1.7	7.4	.86	21.8	0.020	0.5	42.0	SST	C	N
0.195	4.95	B4-62	.47	11.9	.171	4.3	1.1	.19	.36	9.0	.38	1.7	.07	1.8	0.012	0.3	6.00	SST	CG	N
0.203	5.16	N-75	.13	3.2	.163	4.1	33	5.8	.05	1.1	1.5	6.7	.08	2.0	0.020	0.5	3.00	SST	C	N
0.203	5.16	G-74	.19	4.8	.175	4.4	2.2	.38	.10	2.6	.22	.98	.09	2.2	0.014	0.4	5.25	SST	C	N
0.203	5.16	Z-66	.25	6.4	.187	4.7	.09	.02	.16	4.0	.01	.07	.09	2.3	0.008	0.2	10.5	MW	C	N
0.203	5.16	3706	.25	6.4	.123	3.1	283	50	.04	1.0	11	50	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.203	5.16	DD-4	.28	7.1	.169	4.3	1.8	.32	.08	2.0	.14	.63	.20	5.2	0.017	0.4	11.0	SST	C	N
0.203	5.16	V-13	.28	7.1	.143	3.6	65	11	.07	1.9	4.8	22	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.203	5.16	W-29	.28	7.1	.123	3.1	246	43	.04	1.1	11	47	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.203	5.16	10918	.31	7.9	.173	4.4	2.2	.38	.19	4.9	.42	1.9	.12	3.0	0.015	0.4	7.00	MW	C	GI
0.203	5.16	O-109	.31	7.9	.167	4.2	7.9	1.4	.20	5.2	1.6	7.2	.11	2.7	0.018	0.5	5.00	MW	C	Z
0.203	5.16	S-1255	.31	7.9	.167	4.2	14	2.4	.08	2.1	1.1	5.1	.08	2.1	0.018	0.5	3.50	SST	C	N
0.203	5.16	2521	.31	7.9	.143	3.6	100	18	.07	1.8	7.2	32	.16	4.0	0.030	0.8	4.25	MW	C	Z
0.203	5.16	DD-54	.31	7.9	.131	3.3	158	28	.05	1.4	8.4	37	.20	5.0	0.036	0.9	4.50	SPR	C	Z
0.203	5.16	GG-44	.34	8.7	.167	4.2	2.3	.41	.13	3.2	.30	1.3	.22	5.5	0.018	0.5	11.0	SST	C	N
0.203	5.16	CC-49	.38	9.5	.163	4.1	7.7	1.3	.20	5.1	1.6	6.9	.15	3.7	0.020	0.5	6.25	SST	C	N
0.203	5.16	W-21	.38	9.5	.163	4.1	5.4	.95	.22	5.5	1.2	5.2	.16	4.1	0.020	0.5	8.00	SST	CG	N
0.203	5.16	MM-50	.38	9.5	.159	4.0	11	2.0	.20	5.1	2.3	10	.18	4.5	0.022	0.6	7.00	MW	C	GI
0.203	5.16	NN-37	.38	9.5	.153	3.9	16	2.8	.16	4.1	2.6	11	.21	5.4	0.025	0.6	7.50	SST	C	N
0.203	5.16	PP-66	.38	9.5	.153	3.9	14	2.5	.15	3.8	2.1	9.5	.23	5.7	0.025	0.6	9.00	MW	CG	BO
0.203	5.16	AA-19	.41	10.3	.143															




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.203	5.16	B18-190	.50	12.7	.181	4.6	.66	.12	.42	11	.28	1.2	.08	2.0	0.011	0.3	6.00	SST	C	N
0.203	5.16	S-1552	.50	12.7	.179	4.5	.99	.17	.36	9.3	.36	1.6	.08	2.1	0.012	0.3	5.75	SST	C	N
0.203	5.16	S-1083	.50	12.7	.175	4.4	.68	.12	.31	7.9	.21	.94	.19	4.8	0.014	0.4	12.5	SST	C	N
0.203	5.16	B12-54	.50	12.7	.175	4.4	.74	.13	.32	8.1	.24	1.1	.18	4.6	0.014	0.4	13.0	MW	CG	N
0.203	5.16	HH-34	.50	12.7	.173	4.4	1.1	.19	.31	7.7	.33	1.5	.20	5.0	0.015	0.4	12.0	MW	C	N
0.203	5.16	H-80	.50	12.7	.165	4.2	4.4	.76	.31	7.8	1.3	5.9	.15	3.9	0.019	0.5	8.00	SST	CG	N
0.203	5.16	B14-4	.50	12.7	.165	4.2	4.0	.70	.30	7.6	1.2	5.4	.20	5.1	0.019	0.5	9.50	MW	C	N
0.203	5.16	G-61	.50	12.7	.163	4.1	5.4	.95	.29	7.3	1.6	6.9	.18	4.6	0.020	0.5	8.00	SST	C	N
0.203	5.16	S-1380	.50	12.7	.159	4.0	9.9	1.7	.21	5.3	2.1	9.2	.18	4.5	0.022	0.6	7.00	SST	C	N
0.203	5.16	B8-21	.50	12.7	.157	4.0	8.6	1.5	.27	6.9	2.3	10	.23	5.8	0.023	0.6	10.0	MW	CG	N
0.203	5.16	NN-93	.50	12.7	.155	3.9	12	2.1	.26	6.6	3.1	14	.24	6.1	0.024	0.6	9.00	MW	C	N
0.203	5.16	O-81	.50	12.7	.155	3.9	18	3.1	.23	5.8	4.0	18	.16	4.1	0.024	0.6	6.75	MW	CG	N
0.203	5.16	N-110	.50	12.7	.153	3.9	18	3.2	.23	6.0	4.2	19	.19	4.8	0.025	0.6	7.50	MW	C	Z
0.203	5.16	G-26	.50	12.7	.143	3.6	28	4.9	.17	4.3	4.8	21	.33	8.4	0.030	0.8	10.0	MW	C	N
0.203	5.16	B15-30	.50	12.7	.139	3.5	38	6.7	.15	3.9	5.8	26	.29	7.3	0.032	0.8	9.00	SST	CG	N
0.203	5.16	Q-7	.50	12.7	.123	3.1	121	21	.09	2.4	11	50	.36	9.1	0.040	1.0	9.00	SPR	CG	Z
0.203	5.16	2501	.53	13.5	.143	3.6	32	5.6	.22	5.7	7.2	32	.30	7.6	0.030	0.8	9.00	MW	C	Z
0.203	5.16	LL-43	.56	14.3	.171	4.3	2.4	.42	.42	11	1.0	4.5	.14	3.7	0.016	0.4	8.00	MW	C	N
0.203	5.16	LL-56	.56	14.3	.171	4.3	2.1	.37	.39	9.8	.80	3.6	.14	3.7	0.016	0.4	8.00	SST	C	N
0.203	5.16	3997	.56	14.3	.161	4.1	7.1	1.2	.36	9.2	2.6	12	.20	5.1	0.021	0.5	8.50	MW	C	Z
0.203	5.16	W-78	.56	14.3	.139	3.5	35	6.0	.17	4.3	5.8	26	.31	7.9	0.032	0.8	9.75	SST	CG	N
0.203	5.16	EE-42	.56	14.3	.137	3.5	43	7.6	.16	4.0	6.8	30	.33	8.4	0.033	0.8	10.0	SPR	CG	N
0.203	5.16	GG-32	.56	14.3	.123	3.1	84	15	.12	3.1	10	45	.44	11.2	0.040	1.0	11.0	SST	CG	N
0.203	5.16	11428	.56	14.3	.101	2.6	427	75	.05	1.2	19	87	.40	10.0	0.051	1.3	7.75	SST	CG	N
0.203	5.16	Q-23	.59	15.1	.167	4.2	2.2	.38	.36	9.1	.78	3.5	.23	5.9	0.018	0.5	13.0	MW	CG	N
0.203	5.16	00-82	.63	15.9	.179	4.5	.48	.08	.48	12	.23	1.0	.14	3.7	0.012	0.3	11.0	MW	C	Z
0.203	5.16	A13-53	.63	15.9	.173	4.4	1.9	.32	.36	9.1	.66	3.0	.12	3.1	0.015	0.4	7.25	SST	C	N
0.203	5.16	2748	.63	15.9	.155	3.9	18	3.2	.22	5.5	4.0	18	.18	4.6	0.024	0.6	6.50	MW	C	Z
0.203	5.16	3782	.63	15.9	.155	3.9	8.3	1.5	.31	8.0	2.6	12	.31	7.9	0.024	0.6	12.0	MW	C	Z
0.203	5.16	B4-10	.63	15.9	.153	3.9	9.1	1.6	.31	7.9	2.8	13	.29	7.3	0.025	0.6	11.5	SST	CG	N
0.203	5.16	A10-23	.63	15.9	.147	3.7	15	2.7	.26	6.5	4.0	18	.32	8.2	0.028	0.7	11.5	SST	CG	N
0.203	5.16	JJ-71	.63	15.9	.123	3.1	142	25	.08	2.0	11	50	.32	8.1	0.040	1.0	8.00	SPR	CG	N
0.203	5.16	MM-3	.69	17.4	.179	4.5	.62	.11	.58	15	.36	1.6	.11	2.7	0.012	0.3	8.00	SST	C	N
0.203	5.16	CC-38	.69	17.4	.173	4.4	.95	.17	.49	12	.47	2.1	.20	5.0	0.015	0.4	12.0	SST	C	N
0.203	5.16	RR-38	.69	17.4	.171	4.3	1.2	.21	.45	11	.54	2.4	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.203	5.16	BB-84	.69	17.4	.149	3.8	18	3.1	.30	7.7	5.3	24	.30	7.5	0.027	0.7	10.0	MW	C	N
0.203	5.16	S-1120	.69	17.4	.147	3.7	17	3.0	.23	6.0	4.0	18	.32	8.2	0.028	0.7	10.5	SST	C	N
0.203	5.16	B10-12	.69	17.4	.131	3.3	175	31	.05	1.2	8.4	37	.18	4.6	0.036	0.9	5.00	SPR	CG	N
0.203	5.16	AA-23	.69	17.4	.123	3.1	85	15	.13	3.4	11	50	.48	12.2	0.040	1.0	12.0	SPR	CG	N
0.203	5.16	O-19	.72	18.2	.153	3.9	11	1.9	.38	9.8	4.2	19	.28	7.0	0.025	0.6	11.0	MW	CG	N
0.203	5.16	AA-1	.72	18.2	.143	3.6	22	3.9	.32	8.2	7.2	32	.36	9.1	0.030	0.8	12.0	MW	CG	N
0.203	5.16	A11-7	.72	18.2	.121	3.1	94	16	.12	3.1	11	51	.45	11.5	0.041	1.0	11.0	SST	CG	N
0.203	5.16	B-95	.75	19.1	.179	4.5	.71	.12	.64	16	.46	2.0	.11	2.7	0.012	0.3	8.00	MW	C	N
0.203	5.16	4291	.75	19.1	.173	4.4	.91	.16	.53	13	.48	2.1	.23	5.7	0.015	0.4	14.0	MW	C	Z
0.203	5.16	4171	.75	19.1	.165	4.2	5.5	.96	.37	9.3	2.0	8.9	.16	4.1	0.019	0.5	7.50	MW	C	Z
0.203	5.16	NN-45	.75	19.1	.163	4.1	1.8	.32	.33	8.4	.61	2.7	.42	10.7	0.020	0.5	20.0	SST	C	N
0.203	5.16	3290	.75	19.1	.159	4.0	7.6	1.3	.41	10	3.1	14	.23	5.9	0.022	0.6	9.50	MW	C	Z
0.203	5.16	Z-83	.75	19.1	.159	4.0	4.4	.76	.42	11	1.8	8.2	.33	8.4	0.022	0.6	15.0	MW	CG	Z
0.203	5.16	B10-17	.75	19.1	.153	3.9	18	3.2	.23	6.0	4.2	19	.19	4.8	0.025	0.6	7.50	MW	CG	N
0.203	5.16	HH-10	.75	19.1	.151	3.8	11	2.0	.28	7.1	3.2	14	.31	7.9	0.026	0.7	11.0	SST	C	N
0.203	5.16	FF-34	.75	19.1	.143	3.6	21	3.7	.23	5.9	4.8	22	.38	9.5	0.030	0.8	11.5	SST	C	N
0.203	5.16	BB-24	.75	19.1	.123	3.1	57	10	.15	3.8	8.5	38	.60	15.2	0.040	1.0	15.0	SST	CG	N
0.203	5.16	3235	.78	19.8	.149	3.8	12	2.0	.38	9.6	4.4	20	.41	10.3	0.027	0.7	14.0	MW	C	Z
0.203	5.16	J-79	.78	19.8	.127	3.2	58	10	.16	4.0	9.2	41	.46	11.6	0.038	1.0	12.0	SST	CG	N
0.203	5.16	II-42	.81	20.6	.163	4.1	4.7	.82	.50	13	2.3	10	.22	5.6	0.020	0.5	10.0	MW	C	GI
0.203	5.16	K-98	.81	20.6	.163	4.1	2.7	.47	.47	12	1.3	5.6	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.203	5.16	FF-49	.81	20.6	.143	3.6	15	2.7	.32	8.0	4.8	22	.45	11.4	0.030	0.8	15.0	SST	CG	N
0.203	5.16	B12-51	.84	21.4	.163	4.1	1.7	.30	.36	9.2	.62	2.8	.48	12.2	0.020	0.5	24.0	MW	CG	N
0.203	5.16	B4-16	.84	21.4	.147	3.7	11	2.0	.35	8.8	4.0	18	.41	10.3	0.028	0.7	14.5	SST	CG	N
0.203	5.16	L-94	.88	22.2	.173	4.4	.52	.09	.52	13	.27	1.2	.36	9.1	0.015	0.4	23.0	MW	C	Z
0.203	5.16	HH-95	.88	22.2	.143	3.6	16	2.9	.30	7.5	4.8	22	.45	11.4	0.030	0.8	14.0	SST	C	N
0.203	5.16	AA-38	.88	22.2	.133	3.4	40	6.9	.20	5.0	7.7	34	.47	12.0	0.035	0.9	13.5	SPR	CG	Z
0.203	5.16	J-31	.94	23.8	.159	4.0	5.2	.90	.60	15	3.1	14	.31	7.8	0.022	0.6	13.0	MW	C	N
0.203	5.16	A-14	.97	24.6	.183	4.6	.09	.02	.74	19	.07	.29	.23	5.8	0.010	0.3	22.0	SST	C	N
0.203	5.16	12535	.97	24.6	.147	3.7	16	2.9	.36	9.1	5.9	26	.36	9.2	0.028	0.7	12.0	MW	C	N
0.203	5.16	2561	1.00	25.4	.167	4.2	2.5	.44	.68	17	1.7	7.6	.23	5.7	0.018	0.5	11.5	MW	C	Z
0.203	5.16	3249	1.00	25.4	.151	3.8	8.8	1.5	.54	14	4.8	21	.43	10.9	0.026	0.7	15.5	MW	C	Z
0.203	5.16	B-1	1.00	25.4	.145	3.7	10	1.8	.42	11	4.4	19	.52	13.3	0.029	0.7	18.0	SST	CG	N
0.203	5.16	S-1500	1.00	25.4	.145	3.7	23	4.1	.19	4.8	4.4	19	.31	7.8	0.029	0.7	11.0	SST	CG	N
0.203	5.16	B2-35	1.00	25.4	.141	3.6	1													




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.203	5.16	PP-23	1.16	29.4	.133	3.4	29	5.1	.26	6.7	7.7	34	.65	16.4	0.035	0.9	17.5	SPR	C	N
0.203	5.16	12285	1.19	30.2	.123	3.1	61	11	.19	4.7	11	50	.68	17.3	0.040	1.0	16.0	SPR	C	N
0.203	5.16	VV-23	1.22	31.0	.143	3.6	14	2.5	.51	13	7.2	32	.57	14.5	0.030	0.8	18.0	MW	C	N
0.203	5.16	BB-26	1.22	31.0	.143	3.6	10	1.7	.48	12	4.8	22	.66	16.8	0.030	0.8	22.0	SS	CG	N
0.203	5.16	B2-25	1.25	31.8	.157	4.0	5.5	.97	.64	16	3.5	16	.36	9.1	0.023	0.6	14.5	MW	C	Z
0.203	5.16	W-74	1.25	31.8	.143	3.6	9.8	1.7	.49	13	4.8	22	.69	17.5	0.030	0.8	22.0	SST	C	N
0.203	5.16	Q-90	1.31	33.3	.171	4.3	.82	.14	1.0	25	.82	3.7	.31	7.9	0.016	0.4	19.5	MW	CG	N
0.203	5.16	S-481	1.31	33.3	.165	4.2	1.4	.25	.92	23	1.3	5.8	.39	9.9	0.019	0.5	20.5	SST	CG	N
0.203	5.16	3201	1.34	34.1	.163	4.1	2.7	.47	.87	22	2.3	10	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.203	5.16	10754	1.41	35.7	.141	3.6	9.3	1.6	.54	14	5.0	22	.87	22.0	0.031	0.8	27.0	SST	C	N
0.203	5.16	V-5	1.50	38.1	.153	3.9	5.0	.87	.85	22	4.2	19	.58	14.6	0.025	0.6	22.0	MW	C	Z
0.203	5.16	10026	1.50	38.1	.151	3.8	7.4	1.3	.64	16	4.8	21	.49	12.5	0.026	0.7	18.0	MW	C	Z
0.203	5.16	3012	1.56	39.7	.155	3.9	4.6	.81	.87	22	4.0	18	.50	12.8	0.024	0.6	20.0	MW	C	Z
0.203	5.16	2884	1.75	44.5	.159	4.0	2.5	.44	1.2	30	3.0	13	.56	14.2	0.022	0.6	24.5	MW	C	GI
0.203	5.16	10891	1.78	45.2	.153	3.9	3.0	.53	.91	23	2.7	12	.88	22.2	0.025	0.6	35.0	MW	CG	GI
0.203	5.16	12018	2.25	57.2	.101	2.6	107	19	.19	4.9	21	92	1.43	36.3	0.051	1.3	28.0	SPR	CG	Z
0.203	5.16	S-3140	4.00	101.6	.143	3.6	3.3	.57	1.5	38	4.8	22	1.89	48.0	0.030	0.8	62.0	SST	C	N
0.210	5.33	70460	.25	6.4	.174	4.4	11	1.9	.15	3.8	1.7	7.4	.07	1.8	0.018	0.5	4.00	MW	CG	N
0.210	5.33	70460S	.25	6.4	.174	4.4	9.4	1.6	.12	3.0	1.1	4.9	.07	1.8	0.018	0.5	4.00	SST	CG	N
0.210	5.33	70476	.25	6.4	.166	4.2	22	3.8	.14	3.5	3.0	13	.10	2.4	0.022	0.6	4.38	MW	CG	N
0.210	5.33	70476S	.25	6.4	.166	4.2	18	3.2	.11	2.7	2.0	8.9	.10	2.4	0.022	0.6	4.38	SST	CG	N
0.210	5.33	70498	.25	6.4	.158	4.0	41	7.2	.11	2.8	4.6	21	.12	3.0	0.026	0.7	4.50	MW	CG	N
0.210	5.33	70498S	.25	6.4	.158	4.0	35	6.1	.09	2.2	3.1	14	.12	3.0	0.026	0.7	4.50	SST	CG	N
0.210	5.33	70461	.31	7.9	.174	4.4	8.6	1.5	.19	4.9	1.7	7.4	.08	2.1	0.018	0.5	4.50	MW	CG	N
0.210	5.33	70461S	.31	7.9	.174	4.4	7.3	1.3	.15	3.8	1.1	4.9	.08	2.1	0.018	0.5	4.50	SST	CG	N
0.210	5.33	70477	.31	7.9	.166	4.2	17	2.9	.18	4.5	3.0	13	.11	2.8	0.022	0.6	5.00	MW	CG	N
0.210	5.33	70477S	.31	7.9	.166	4.2	14	2.5	.14	3.6	2.0	8.9	.11	2.8	0.022	0.6	5.00	SST	CG	N
0.210	5.33	70499	.31	7.9	.158	4.0	32	5.5	.15	3.7	4.6	21	.14	3.5	0.026	0.7	5.38	MW	CG	N
0.210	5.33	70499S	.31	7.9	.158	4.0	27	4.7	.12	2.9	3.1	14	.14	3.5	0.026	0.7	5.38	SST	CG	N
0.210	5.33	70462	.38	9.7	.174	4.4	6.8	1.2	.24	6.2	1.7	7.4	.09	2.3	0.018	0.5	5.13	MW	CG	N
0.210	5.33	70462S	.38	9.7	.174	4.4	5.8	1.0	.19	4.8	1.1	4.9	.09	2.3	0.018	0.5	5.13	SST	CG	N
0.210	5.33	70478	.38	9.7	.166	4.2	13	2.3	.22	5.7	3.0	13	.13	3.2	0.022	0.6	5.75	MW	CG	N
0.210	5.33	70478S	.38	9.7	.166	4.2	11	2.0	.18	4.5	2.0	8.9	.13	3.2	0.022	0.6	5.75	SST	CG	N
0.210	5.33	70500	.38	9.7	.158	4.0	25	4.4	.18	4.7	4.6	21	.16	4.1	0.026	0.7	6.25	MW	CG	N
0.210	5.33	70500S	.38	9.7	.158	4.0	21	3.7	.15	3.7	3.1	14	.16	4.1	0.026	0.7	6.25	SST	CG	N
0.210	5.33	70463	.44	11.2	.174	4.4	5.8	1.0	.29	7.3	1.7	7.4	.10	2.6	0.018	0.5	5.63	MW	CG	N
0.210	5.33	70463S	.44	11.2	.174	4.4	4.9	.86	.22	5.7	1.1	4.9	.10	2.6	0.018	0.5	5.63	SST	CG	N
0.210	5.33	70479	.44	11.2	.166	4.2	11	2.0	.26	6.7	3.0	13	.14	3.6	0.022	0.6	6.50	MW	CG	N
0.210	5.33	70479S	.44	11.2	.166	4.2	9.7	1.7	.21	5.2	2.0	8.9	.14	3.6	0.022	0.6	6.50	SST	CG	N
0.210	5.33	70501	.44	11.2	.158	4.0	21	3.7	.22	5.5	4.6	21	.18	4.6	0.026	0.7	7.00	MW	CG	N
0.210	5.33	70501S	.44	11.2	.158	4.0	18	3.1	.17	4.4	3.1	14	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.210	5.33	70464	.50	12.7	.174	4.4	5.1	.89	.33	8.3	1.7	7.4	.11	2.8	0.018	0.5	6.13	MW	CG	N
0.210	5.33	70464S	.50	12.7	.174	4.4	4.3	.76	.25	6.5	1.1	4.9	.11	2.8	0.018	0.5	6.13	SST	CG	N
0.210	5.33	70480	.50	12.7	.166	4.2	9.9	1.7	.30	7.7	3.0	13	.16	4.0	0.022	0.6	7.13	MW	CG	N
0.210	5.33	70480S	.50	12.7	.166	4.2	8.4	1.5	.24	6.0	2.0	8.9	.16	4.0	0.022	0.6	7.13	SST	CG	N
0.210	5.33	70502	.50	12.7	.158	4.0	18	3.2	.25	6.4	4.6	21	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.210	5.33	70502S	.50	12.7	.158	4.0	16	2.7	.20	5.1	3.1	14	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.210	5.33	70465	.56	14.2	.174	4.4	4.5	.79	.37	9.4	1.7	7.4	.12	3.1	0.018	0.5	6.75	MW	CG	N
0.210	5.33	70465S	.56	14.2	.174	4.4	3.8	.67	.29	7.3	1.1	4.9	.12	3.1	0.018	0.5	6.75	SST	CG	N
0.210	5.33	70481	.56	14.2	.166	4.2	8.7	1.5	.35	8.8	3.0	13	.17	4.4	0.022	0.6	7.88	MW	CG	N
0.210	5.33	70481S	.56	14.2	.166	4.2	7.4	1.3	.27	6.9	2.0	8.9	.17	4.4	0.022	0.6	7.88	SST	CG	N
0.210	5.33	70503	.56	14.2	.158	4.0	16	2.8	.29	7.3	4.6	21	.22	5.6	0.026	0.7	8.50	MW	CG	N
0.210	5.33	70503S	.56	14.2	.158	4.0	14	2.4	.23	5.7	3.1	14	.22	5.6	0.026	0.7	8.50	SST	CG	N
0.210	5.33	70466	.63	16.0	.174	4.4	4.0	.70	.41	11	1.7	7.4	.13	3.4	0.018	0.5	7.38	MW	CG	N
0.210	5.33	70466S	.63	16.0	.174	4.4	3.4	.60	.32	8.2	1.1	4.9	.13	3.4	0.018	0.5	7.38	SST	CG	N
0.210	5.33	70482	.63	16.0	.166	4.2	7.8	1.4	.39	9.8	3.0	13	.19	4.7	0.022	0.6	8.50	MW	CG	N
0.210	5.33	70482S	.63	16.0	.166	4.2	6.6	1.2	.30	7.7	2.0	8.9	.19	4.7	0.022	0.6	8.50	SST	CG	N
0.210	5.33	70504	.63	16.0	.158	4.0	14	2.5	.33	8.3	4.6	21	.24	6.2	0.026	0.7	9.38	MW	CG	N
0.210	5.33	70504S	.63	16.0	.158	4.0	12	2.1	.26	6.5	3.1	14	.24	6.2	0.026	0.7	9.38	SST	CG	N
0.210	5.33	12549	.67	17.1	.170	4.3	5.6	.98	.41	10	2.3	10	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.210	5.33	70467	.69	17.5	.174	4.4	3.6	.63	.46	12	1.7	7.4	.14	3.6	0.018	0.5	7.88	MW	CG	N
0.210	5.33	70467S	.69	17.5	.174	4.4	3.1	.54	.36	9.2	1.1	4.9	.14	3.6	0.018	0.5	7.88	SST	CG	N
0.210	5.33	70483	.69	17.5	.166	4.2	6.9	1.2	.43	11	3.0	13	.21	5.2	0.022	0.6	9.38	MW	CG	N
0.210	5.33	70483S	.69	17.5	.166	4.2	5.9	1.0	.34	8.6	2.0	8.9	.21	5.2	0.022	0.6	9.38	SST	CG	N
0.210	5.33	70505	.69	17.5	.158	4.0	13	2.3	.36	9.1	4.6	21	.27	6.8	0.026	0.7	10.3	MW	CG	N
0.210	5.33	70505S	.69	17.5	.158	4.0	11	1.9	.28	7.2	3.1	14	.27	6.8	0.026	0.7	10.3	SST	CG	N
0.210	5.33	70468	.75	19.1	.174	4.4	3.3	.58	.50	13	1.7	7.4	.15	3.9	0.018	0.5	8.50	MW	CG	N
0.210	5.33	70468S	.75	19.1	.174	4.4	2.8	.49	.39	10	1.1	4.9	.15	3.9	0.018	0.5	8.50	SST	CG	N




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.210	5.33	70486	.88	22.4	.166	4.2	5.8	1.0	.52	13	3.0	13	.24	6.0	0.022	0.6	10.8	MW	CG	N
0.210	5.33	70486S	.88	22.4	.166	4.2	4.9	.86	.40	10	2.0	8.9	.24	6.0	0.022	0.6	10.8	SST	CG	N
0.210	5.33	70508	.88	22.4	.158	4.0	11	1.8	.44	11	4.6	21	.31	7.9	0.026	0.7	12.0	MW	CG	N
0.210	5.33	70508S	.88	22.4	.158	4.0	8.9	1.6	.35	8.8	3.1	14	.31	7.9	0.026	0.7	12.0	SST	CG	N
0.210	5.33	70488	.94	23.9	.166	4.2	5.3	.93	.57	14	3.0	13	.26	6.5	0.022	0.6	11.6	MW	CG	N
0.210	5.33	70488S	.94	23.9	.166	4.2	4.5	.79	.44	11	2.0	8.9	.26	6.5	0.022	0.6	11.6	SST	CG	N
0.210	5.33	70510	.94	23.9	.158	4.0	9.7	1.7	.48	12	4.6	21	.33	8.5	0.026	0.7	12.9	MW	CG	N
0.210	5.33	70510S	.94	23.9	.158	4.0	8.2	1.4	.37	9.5	3.1	14	.33	8.5	0.026	0.7	12.9	SST	CG	N
0.210	5.33	70471	1.00	25.4	.174	4.4	2.4	.42	.69	18	1.7	7.4	.20	5.0	0.018	0.5	10.9	MW	CG	N
0.210	5.33	70471S	1.00	25.4	.174	4.4	2.0	.36	.54	14	1.1	4.9	.20	5.0	0.018	0.5	10.9	SST	CG	N
0.210	5.33	70489	1.00	25.4	.166	4.2	4.7	.81	.64	16	3.0	13	.28	7.2	0.022	0.6	12.9	MW	CG	N
0.210	5.33	70489S	1.00	25.4	.166	4.2	4.0	.69	.50	13	2.0	8.9	.28	7.2	0.022	0.6	12.9	SST	CG	N
0.210	5.33	70511	1.00	25.4	.158	4.0	8.6	1.5	.54	14	4.6	21	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.210	5.33	70511S	1.00	25.4	.158	4.0	7.3	1.3	.42	11	3.1	14	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.210	5.33	70491	1.13	28.7	.166	4.2	4.4	.77	.68	17	3.0	13	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.210	5.33	70491S	1.13	28.7	.166	4.2	3.7	.65	.53	14	2.0	8.9	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.210	5.33	70513	1.13	28.7	.158	4.0	8.0	1.4	.58	15	4.6	21	.39	10.0	0.026	0.7	15.1	MW	CG	N
0.210	5.33	70513S	1.13	28.7	.158	4.0	6.8	1.2	.45	12	3.1	14	.39	10.0	0.026	0.7	15.1	SST	CG	N
0.210	5.33	70472	1.25	31.8	.174	4.4	1.9	.33	.87	22	1.7	7.4	.24	6.1	0.018	0.5	13.3	MW	CG	N
0.210	5.33	70472S	1.25	31.8	.174	4.4	1.6	.28	.68	17	1.1	4.9	.24	6.1	0.018	0.5	13.3	SST	CG	N
0.210	5.33	70492	1.25	31.8	.166	4.2	3.7	.65	.81	21	3.0	13	.35	8.8	0.022	0.6	15.8	MW	CG	N
0.210	5.33	70492S	1.25	31.8	.166	4.2	3.1	.55	.63	16	2.0	8.9	.35	8.8	0.022	0.6	15.8	SST	CG	N
0.210	5.33	70514	1.25	31.8	.158	4.0	6.8	1.2	.68	17	4.6	21	.46	11.6	0.026	0.7	17.5	MW	CG	N
0.210	5.33	70514S	1.25	31.8	.158	4.0	5.8	1.0	.53	14	3.1	14	.46	11.6	0.026	0.7	17.5	SST	CG	N
0.210	5.33	70494	1.38	35.1	.166	4.2	3.6	.63	.83	21	3.0	13	.35	9.0	0.022	0.6	16.1	MW	CG	N
0.210	5.33	70494S	1.38	35.1	.166	4.2	3.1	.54	.65	17	2.0	8.9	.35	9.0	0.022	0.6	16.1	SST	CG	N
0.210	5.33	70516	1.38	35.1	.158	4.0	6.5	1.1	.71	18	4.6	21	.47	12.1	0.026	0.7	18.3	MW	CG	N
0.210	5.33	70516S	1.38	35.1	.158	4.0	5.5	.97	.56	14	3.1	14	.47	12.1	0.026	0.7	18.3	SST	CG	N
0.210	5.33	70473	1.50	38.1	.174	4.4	1.6	.28	1.0	26	1.7	7.4	.28	7.0	0.018	0.5	15.4	MW	CG	N
0.210	5.33	70473S	1.50	38.1	.174	4.4	1.4	.24	.81	21	1.1	4.9	.28	7.0	0.018	0.5	15.4	SST	CG	N
0.210	5.33	70495	1.50	38.1	.166	4.2	3.0	.53	.99	25	3.0	13	.41	10.5	0.022	0.6	18.8	MW	CG	N
0.210	5.33	70495S	1.50	38.1	.166	4.2	2.6	.45	.78	20	2.0	8.9	.41	10.5	0.022	0.6	18.8	SST	CG	N
0.210	5.33	70517	1.50	38.1	.158	4.0	5.6	.99	.82	21	4.6	21	.54	13.7	0.026	0.7	20.8	MW	CG	N
0.210	5.33	70517S	1.50	38.1	.158	4.0	4.8	.84	.65	16	3.1	14	.54	13.7	0.026	0.7	20.8	SST	CG	N
0.210	5.33	70474	1.75	44.5	.174	4.4	1.4	.25	1.2	30	1.7	7.4	.31	7.9	0.018	0.5	17.3	MW	CG	N
0.210	5.33	70474S	1.75	44.5	.174	4.4	1.2	.21	.93	24	1.1	4.9	.31	7.9	0.018	0.5	17.3	SST	CG	N
0.210	5.33	70496	1.75	44.5	.166	4.2	2.9	.51	1.0	26	3.0	13	.43	10.9	0.022	0.6	19.5	MW	CG	N
0.210	5.33	70496S	1.75	44.5	.166	4.2	2.5	.43	.81	21	2.0	8.9	.43	10.9	0.022	0.6	19.5	SST	CG	N
0.210	5.33	70518	1.75	44.5	.158	4.0	5.1	.89	.91	23	4.6	21	.59	14.9	0.026	0.7	22.6	MW	CG	N
0.210	5.33	70518S	1.75	44.5	.158	4.0	4.3	.76	.71	18	3.1	14	.59	14.9	0.026	0.7	22.6	SST	CG	N
0.210	5.33	70475	2.00	50.8	.174	4.4	1.2	.21	1.4	35	1.7	7.4	.36	9.0	0.018	0.5	19.8	MW	CG	N
0.210	5.33	70475S	2.00	50.8	.174	4.4	1.0	.18	1.1	27	1.1	4.9	.36	9.0	0.018	0.5	19.8	SST	CG	N
0.210	5.33	70497	2.00	50.8	.166	4.2	2.5	.44	1.2	30	3.0	13	.49	12.4	0.022	0.6	22.3	MW	CG	N
0.210	5.33	70497S	2.00	50.8	.166	4.2	2.1	.37	.94	24	2.0	8.9	.49	12.4	0.022	0.6	22.3	SST	CG	N
0.210	5.33	70519	2.00	50.8	.158	4.0	4.5	.79	1.0	26	4.6	21	.66	16.8	0.026	0.7	25.4	MW	CG	N
0.210	5.33	70519S	2.00	50.8	.158	4.0	3.8	.67	.81	21	3.1	14	.66	16.8	0.026	0.7	25.4	SST	CG	N
0.219	5.56	S-863	.22	5.6	.179	4.5	13	2.3	.11	2.8	1.4	6.4	.10	2.5	0.020	0.5	4.00	SST	C	N
0.219	5.56	MM-39	.25	6.4	.179	4.5	15	2.6	.15	3.8	2.2	9.7	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.219	5.56	II-38	.25	6.4	.173	4.4	15	2.7	.11	2.8	1.7	7.7	.14	3.5	0.023	0.6	5.00	SST	C	N
0.219	5.56	G-21	.31	7.9	.197	5.0	.26	.05	.18	4.6	.05	.21	.13	3.4	0.011	0.3	11.0	MW	C	BO
0.219	5.56	S-1531	.31	7.9	.195	5.0	1.2	.21	.25	6.2	.29	13	.07	1.7	0.012	0.3	4.50	SST	C	N
0.219	5.56	S-1547	.31	7.9	.193	4.9	1.6	.29	.24	6.1	.39	1.7	.07	1.8	0.013	0.3	4.50	SST	C	N
0.219	5.56	A-15	.31	7.9	.179	4.5	5.1	.89	.15	3.9	.77	3.4	.16	4.1	0.020	0.5	7.00	MW	C	N
0.219	5.56	B9-29	.31	7.9	.177	4.5	14	2.5	.17	4.4	2.5	11	.09	2.4	0.021	0.5	4.50	MW	CG	N
0.219	5.56	I-67	.31	7.9	.169	4.3	19	3.4	.14	3.5	2.6	12	.18	4.4	0.025	0.6	6.00	MW	C	GI
0.219	5.56	A10-18	.31	7.9	.167	4.2	27	4.7	.11	2.8	3.0	13	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.219	5.56	S-1553	.33	8.3	.195	5.0	1.2	.20	.26	6.7	.31	1.4	.07	1.7	0.012	0.3	4.50	SST	C	N
0.219	5.56	B14-38	.34	8.7	.179	4.5	5.8	1.0	.18	4.6	1.1	4.8	.16	4.1	0.020	0.5	7.00	MW	C	N
0.219	5.56	10355	.38	9.5	.185	4.7	4.9	.85	.27	6.9	1.3	5.9	.10	2.6	0.017	0.4	5.00	MW	C	N
0.219	5.56	S-1342	.38	9.5	.177	4.5	16	2.7	.11	2.7	1.7	7.4	.11	2.7	0.021	0.5	4.00	SST	C	N
0.219	5.56	Q-6	.38	9.5	.175	4.4	8.8	1.5	.20	5.1	1.8	7.8	.18	4.5	0.022	0.6	7.00	MW	C	Z
0.219	5.56	EE-12	.38	9.5	.159	4.0	25	4.4	.14	3.4	3.4	15	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.219	5.56	BB-7	.38	9.5	.145	3.7	97	17	.08	2.1	8.0	35	.22	5.6	0.037	0.9	6.00	SST	CG	N
0.219	5.56	HH-39	.38	9.5	.139	3.5	143	25	.07	1.9	11	47	.26	6.6	0.040	1.0	6.50	SPR	CG	GI
0.219	5.56	LL-41	.41	10.3	.199	5.1	.20	.03	.30	7.5	.06	.26	.11	2.8	0.010	0.3	10.0	MW	C	Z
0.219	5.56	10690	.41	10.3	.181	4.6	6.9	1.2	.18	4.6	1.2	5.5	.11	2.9	0.019	0.5	5.00	SST	C	N
0.219	5.56	B14-17	.41	10.3	.179	4.5	9.7	1.7	.22	5.7	2.2	9.7	.10	2.5	0.020	0.5	5.00	MW	CG	N
0.219	5.56	3883	.41	10.3	.165	4.2	27	4.7	.18	4.7	5.0	22	.16	4.1	0.027	0.7	6.00	MW	CG	GI
0.219	5.56	M-34	.41	10.3	.161	4.1	66	12	.06	1.6										




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.219	5.56	H-71	.44	11.1	.141	3.6	107	19	.09	2.3	9.9	44	.29	7.3	0.039	1.0	7.33	SPR	CG	N
0.219	5.56	HH-46	.44	11.1	.139	3.5	112	20	.09	2.3	9.9	44	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.219	5.56	L-29	.44	11.1	.139	3.5	214	37	.05	1.3	11	47	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.219	5.56	XX-21	.47	11.9	.145	3.7	78	14	.10	2.6	8.0	35	.30	7.5	0.037	0.9	7.00	SST	C	N
0.219	5.56	B15-4	.47	11.9	.145	3.7	72	13	.12	3.0	8.5	38	.31	7.8	0.037	0.9	8.25	SPR	CG	N
0.219	5.56	2703	.47	11.9	.143	3.6	126	22	.10	2.6	13	57	.27	6.8	0.038	1.0	6.00	MW	C	Z
0.219	5.56	A11-20	.47	11.9	.133	3.4	200	35	.06	1.6	12	54	.30	7.6	0.043	1.1	6.00	SST	C	N
0.219	5.56	EE-86	.50	12.7	.191	4.9	.46	.08	.29	7.4	.13	.60	.21	5.3	0.014	0.4	14.0	SST	C	N
0.219	5.56	B-66	.50	12.7	.187	4.7	1.7	.30	.35	8.8	.60	2.7	.15	3.9	0.016	0.4	8.50	MW	C	N
0.219	5.56	10314	.50	12.7	.179	4.5	7.3	1.3	.30	7.6	2.2	9.7	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.219	5.56	3161	.50	12.7	.179	4.5	5.1	.89	.33	8.3	1.6	7.3	.18	4.4	0.020	0.5	7.75	MW	C	Z
0.219	5.56	H-20	.50	12.7	.179	4.5	4.2	.73	.32	8.1	1.3	5.9	.18	4.6	0.020	0.5	9.00	MW	CG	Z
0.219	5.56	10353	.50	12.7	.177	4.5	4.6	.81	.27	7.0	1.3	5.7	.23	5.7	0.021	0.5	9.75	MW	C	BO
0.219	5.56	EE-24	.50	12.7	.175	4.4	7.7	1.3	.25	6.4	1.9	8.5	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.219	5.56	KK-83	.50	12.7	.175	4.4	4.8	.84	.26	6.6	1.2	5.5	.24	6.1	0.022	0.6	10.0	SST	C	N
0.219	5.56	H-78	.50	12.7	.169	4.3	11	2.0	.24	6.0	2.7	12	.20	5.1	0.025	0.6	8.00	SST	C	N
0.219	5.56	Q-4	.50	12.7	.169	4.3	13	2.2	.28	7.0	3.5	16	.23	5.7	0.025	0.6	8.00	MW	C	N
0.219	5.56	S-858	.50	12.7	.165	4.2	15	2.7	.22	5.5	3.3	15	.25	6.3	0.027	0.7	8.25	SST	C	N
0.219	5.56	10828	.50	12.7	.161	4.1	30	5.2	.21	5.2	6.1	27	.23	5.9	0.029	0.7	7.00	MW	C	N
0.219	5.56	3837	.50	12.7	.139	3.5	214	37	.05	1.3	11	47	.24	6.1	0.040	1.0	5.00	SPR	C	Z
0.219	5.56	Z-82	.50	12.7	.139	3.5	128	22	.08	2.1	11	47	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.219	5.56	LL-31	.50	12.7	.119	3.0	266	47	.05	1.3	13	59	.45	11.4	0.050	1.3	9.00	SPR	CG	N
0.219	5.56	B17-123	.53	13.5	.203	5.2	.10	.02	.46	12	.04	.20	.08	1.9	0.008	0.2	8.50	MW	C	N
0.219	5.56	10583	.53	13.5	.193	4.9	1.0	.18	.43	11	.45	2.0	.10	2.5	0.013	0.3	6.50	MW	C	N
0.219	5.56	RR-5	.53	13.5	.163	4.1	18	3.2	.20	5.1	3.7	16	.25	6.4	0.028	0.7	8.00	SST	C	N
0.219	5.56	B7-11	.53	13.5	.163	4.1	20	3.4	.28	7.2	5.5	25	.24	6.0	0.028	0.7	8.50	MW	CG	Z
0.219	5.56	BB-11	.53	13.5	.159	4.0	17	3.0	.20	5.1	3.4	15	.33	8.4	0.030	0.8	11.0	SST	CG	N
0.219	5.56	BB-95	.53	13.5	.155	3.9	22	3.9	.18	4.5	4.0	18	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.219	5.56	B-81	.53	13.5	.155	3.9	41	7.2	.13	3.4	5.4	24	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.219	5.56	MM-7	.53	13.5	.139	3.5	80	14	.13	3.3	11	47	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.219	5.56	B9-25	.56	14.3	.199	5.1	.16	.03	.43	11	.07	.31	.13	3.2	0.010	0.3	11.8	MW	C	N
0.219	5.56	A9-12	.56	14.3	.197	5.0	.17	.03	.40	10	.07	.31	.17	4.2	0.011	0.3	14.0	SST	C	N
0.219	5.56	EE-99	.56	14.3	.179	4.5	4.2	.73	.36	9.2	1.5	6.7	.20	5.1	0.020	0.5	9.00	MW	C	N
0.219	5.56	S-192	.56	14.3	.161	4.1	26	4.5	.16	4.0	4.1	18	.23	5.9	0.029	0.7	7.00	SST	C	N
0.219	5.56	S-1208	.56	14.3	.149	3.8	38	6.7	.18	4.5	6.8	30	.35	8.9	0.035	0.9	10.0	SST	CG	N
0.219	5.56	A10-14	.56	14.3	.147	3.7	66	11	.12	3.0	7.9	35	.32	8.2	0.036	0.9	8.00	SPR	C	N
0.219	5.56	11419	.56	14.3	.141	3.6	67	12	.14	3.5	9.3	41	.37	9.4	0.039	1.0	9.50	SST	CG	N
0.219	5.56	NN-70	.59	15.1	.179	4.5	4.9	.85	.41	10	2.0	8.9	.18	4.6	0.020	0.5	8.00	MW	C	N
0.219	5.56	Q-80	.59	15.1	.169	4.3	11	1.9	.36	9.2	4.0	18	.23	5.7	0.025	0.6	9.00	MW	CG	N
0.219	5.56	00-27	.59	15.1	.159	4.0	19	3.3	.24	6.0	4.5	20	.33	8.4	0.030	0.8	10.0	SST	C	N
0.219	5.56	A9-34	.59	15.1	.147	3.7	56	9.9	.14	3.5	7.9	35	.32	8.2	0.036	0.9	9.00	SPR	CG	N
0.219	5.56	H-5	.63	15.9	.189	4.8	.66	.12	.40	10	.26	1.2	.23	5.7	0.015	0.4	15.0	MW	CG	N
0.219	5.56	M-21	.63	15.9	.179	4.5	4.2	.73	.43	11	1.8	7.9	.20	5.1	0.020	0.5	9.00	MW	C	Z
0.219	5.56	Q-70	.63	15.9	.175	4.4	4.8	.84	.38	9.7	1.8	8.2	.24	6.1	0.022	0.6	10.0	SST	C	N
0.219	5.56	S-714	.63	15.9	.175	4.4	6.1	1.1	.31	7.9	1.9	8.5	.20	5.2	0.022	0.6	8.25	SST	C	N
0.219	5.56	2667	.63	15.9	.171	4.3	8.3	1.5	.37	9.3	3.0	14	.26	6.6	0.024	0.6	9.75	MW	C	Z
0.219	5.56	B14-1	.63	15.9	.171	4.3	13	2.3	.29	7.4	3.7	17	.19	4.9	0.024	0.6	7.00	MW	C	N
0.219	5.56	3790	.63	15.9	.169	4.3	7.7	1.3	.30	7.6	2.3	10	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.219	5.56	I-69	.63	15.9	.169	4.3	9.6	1.7	.38	9.5	3.6	16	.25	6.4	0.025	0.6	10.0	MW	CG	Z
0.219	5.56	EE-20	.63	15.9	.159	4.0	15	2.7	.27	6.7	4.1	18	.36	9.1	0.030	0.8	12.0	SST	CG	N
0.219	5.56	MM-19	.63	15.9	.159	4.0	22	3.8	.31	7.9	6.7	30	.30	7.6	0.030	0.8	10.0	MW	CG	Z
0.219	5.56	S-5	.63	15.9	.155	3.9	21	3.7	.23	5.7	4.7	21	.40	10.2	0.032	0.8	11.5	SST	C	N
0.219	5.56	GG-68	.63	15.9	.149	3.8	38	6.6	.18	4.6	6.8	30	.35	8.9	0.035	0.9	10.0	SST	CG	N
0.219	5.56	EE-35	.63	15.9	.119	3.0	310	54	.06	1.5	19	82	.40	10.2	0.050	1.3	8.00	SPR	CG	N
0.219	5.56	AA-89	.66	16.7	.195	5.0	.27	.05	.49	12	.13	.59	.17	4.3	0.012	0.3	13.0	SST	C	N
0.219	5.56	MM-33	.66	16.7	.179	4.5	4.9	.85	.45	11	2.2	9.7	.16	4.1	0.020	0.5	8.00	MW	CG	N
0.219	5.56	B5-68	.66	16.7	.169	4.3	14	2.4	.19	4.9	2.7	12	.20	5.1	0.025	0.6	7.00	SST	C	N
0.219	5.56	2912	.66	16.7	.167	4.2	12	2.0	.38	9.7	4.4	20	.26	6.5	0.026	0.7	9.88	MW	CG	Z
0.219	5.56	2882	.66	16.7	.159	4.0	27	4.6	.25	6.5	6.7	30	.29	7.2	0.030	0.8	8.50	MW	C	N
0.219	5.56	S-946	.66	16.7	.157	4.0	27	4.7	.19	4.7	5.0	22	.29	7.5	0.031	0.8	8.50	SST	C	N
0.219	5.56	A-93	.66	16.7	.149	3.8	33	5.8	.22	5.5	7.2	32	.44	11.1	0.035	0.9	12.5	SPR	CG	N
0.219	5.56	NN-69	.69	17.4	.193	4.9	.37	.07	.51	13	.19	.83	.18	4.6	0.013	0.3	13.0	SST	C	N
0.219	5.56	I-78	.69	17.4	.191	4.9	.24	.04	.32	8.2	.08	.35	.36	9.2	0.014	0.4	25.0	SST	C	N
0.219	5.56	BB-46	.69	17.4	.189	4.8	1.2	.21	.54	14	.66	2.9	.15	3.8	0.015	0.4	9.00	MW	C	GI
0.219	5.56	EE-46	.69	17.4	.187	4.7	1.1	.19	.50	13	.54	2.4	.19	4.9	0.016	0.4	11.0	SST	C	N
0.219	5.56	LL-86	.69	17.4	.183	4.6	1.3	.24	.42	11	.56	2.5	.27	6.9	0.018	0.5	14.0	SST	C	N
0.219	5.56	B8-13	.69	17.4	.147	3.7	36	6.3	.22	5.6	7.8	35	.47	11.9	0.036	0.9	13.0	SPR	CG	N
0.219	5.56	J-18	.69	17.4	.139	3.5	71	12	.15	3.8	11	47	.44	11.2	0.040	1.0	11.0	SPR	CG	GI
0.219	5.56	NN-31	.69	17.4	.125	3.2	230	40	.07	1.9	17	74	.42	10.7	0.047	1.2	8.00	SPR	C	N
0.219																				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.219	5.56	HH-43	.75	19.1	.159	4.0	19	3.4	.35	8.9	6.7	30	.33	8.4	0.030	0.8	11.0	MW	CG	N
0.219	5.56	TT-39	.75	19.1	.159	4.0	18	3.1	.26	6.5	4.5	20	.35	8.8	0.030	0.8	10.5	SST	C	N
0.219	5.56	11303	.75	19.1	.149	3.8	35	6.1	.19	4.9	6.8	30	.41	10.4	0.035	0.9	10.8	SST	C	N
0.219	5.56	A9-5	.78	19.8	.155	3.9	23	4.0	.35	9.0	8.1	36	.38	9.8	0.032	0.8	12.0	MW	CG	N
0.219	5.56	S-874	.78	19.8	.143	3.6	49	8.6	.18	4.5	8.6	38	.42	10.6	0.038	1.0	11.0	SST	CG	N
0.219	5.56	HH-16	.78	19.8	.099	2.5	514	90	.06	1.4	28	127	.60	15.2	0.060	1.5	10.0	SST	CG	N
0.219	5.56	V-61	.81	20.6	.179	4.5	2.8	.49	.51	13	1.4	6.4	.24	6.1	0.020	0.5	11.0	SST	C	N
0.219	5.56	MM-81	.81	20.6	.155	3.9	16	2.9	.30	7.6	4.9	22	.51	13.0	0.032	0.8	16.0	HD	CG	Z
0.219	5.56	Z-85	.81	20.6	.151	3.8	23	4.1	.30	7.6	7.0	31	.51	13.0	0.034	0.9	15.0	SPR	CG	N
0.219	5.56	1503	.81	20.6	.149	3.8	51	9.0	.20	5.0	10	45	.34	8.7	0.035	0.9	8.75	MW	C	Z
0.219	5.56	S-1555	.81	20.6	.143	3.6	49	8.6	.18	4.5	8.6	38	.46	11.6	0.038	1.0	11.0	SST	C	N
0.219	5.56	VV-38	.81	20.6	.129	3.3	118	21	.13	3.2	15	66	.56	14.3	0.045	1.1	11.5	SPR	C	Z
0.219	5.56	H-48	.84	21.4	.165	4.2	15	2.7	.32	8.2	5.0	22	.24	6.2	0.027	0.7	9.00	MW	CG	Z
0.219	5.56	II-58	.84	21.4	.153	3.9	20	3.6	.31	8.0	6.4	28	.50	12.6	0.033	0.8	15.0	SPR	CG	Z
0.219	5.56	10733	.88	22.2	.193	4.9	.64	.11	.67	17	.43	1.9	.12	3.1	0.013	0.3	8.50	SST	C	N
0.219	5.56	B-15	.88	22.2	.185	4.7	.79	.14	.55	14	.44	1.9	.32	8.2	0.017	0.4	18.0	SST	C	N
0.219	5.56	DD-38	.88	22.2	.179	4.5	2.6	.45	.56	14	1.4	6.4	.26	6.6	0.020	0.5	12.0	SST	C	N
0.219	5.56	S-716	.88	22.2	.175	4.4	4.3	.75	.45	11	1.9	8.5	.26	6.7	0.022	0.6	11.0	SST	C	N
0.219	5.56	S-1169	.88	22.2	.171	4.3	8.6	1.5	.29	7.3	2.5	11	.23	5.8	0.024	0.6	8.50	SST	C	N
0.219	5.56	S-1079	.88	22.2	.169	4.3	5.6	.98	.48	12	2.7	12	.35	8.9	0.025	0.6	14.0	SST	CG	N
0.219	5.56	2771	.88	22.2	.167	4.2	18	3.2	.24	6.2	4.4	20	.21	5.3	0.026	0.7	7.00	MW	C	Z
0.219	5.56	2900	.88	22.2	.163	4.1	9.8	1.7	.46	12	4.4	20	.42	10.7	0.028	0.7	15.0	MW	CG	Z
0.219	5.56	V-59	.88	22.2	.161	4.1	11	1.9	.38	9.7	4.1	18	.41	10.3	0.029	0.7	14.0	SST	CG	N
0.219	5.56	2529	.88	22.2	.139	3.5	58	10	.25	6.4	15	65	.56	14.2	0.040	1.0	13.0	MW	C	Z
0.219	5.56	HH-52	.88	22.2	.139	3.5	53	9.4	.20	5.0	11	47	.56	14.2	0.040	1.0	14.0	SPR	CG	Z
0.219	5.56	2801	.91	23.0	.181	4.6	2.0	.36	.63	16	1.3	5.7	.28	7.0	0.019	0.5	13.5	MW	C	Z
0.219	5.56	Z-27	.91	23.0	.173	4.4	7.3	1.3	.30	7.6	2.2	9.7	.22	5.5	0.023	0.6	8.50	SST	C	N
0.219	5.56	AA-15	.94	23.8	.191	4.9	.44	.08	.72	18	.31	1.4	.22	5.6	0.014	0.4	14.8	SST	C	N
0.219	5.56	W-42	.94	23.8	.167	4.2	5.0	.87	.47	12	2.3	10	.47	11.9	0.026	0.7	18.0	SST	CG	N
0.219	5.56	G-58	.94	23.8	.157	4.0	14	2.4	.43	11	5.9	26	.51	13.0	0.031	0.8	16.5	MW	CG	N
0.219	5.56	J-70	.94	23.8	.157	4.0	13	2.3	.41	10	5.5	24	.53	13.4	0.031	0.8	17.0	MW	CG	GI
0.219	5.56	A9-52	.97	24.6	.173	4.4	4.4	.78	.49	12	2.2	9.7	.29	7.4	0.023	0.6	12.7	SST	CG	N
0.219	5.56	2627	.97	24.6	.161	4.1	11	1.9	.52	13	5.7	25	.45	11.4	0.029	0.7	15.5	MW	CG	Z
0.219	5.56	159-A	1.00	25.4	.187	4.7	1.6	.28	.70	18	1.1	5.0	.16	4.1	0.016	0.4	9.00	MW	C	Z
0.219	5.56	160-A	1.00	25.4	.183	4.6	2.4	.42	.66	17	1.6	7.1	.19	4.9	0.018	0.5	9.75	MW	C	Z
0.219	5.56	4299	1.00	25.4	.183	4.6	2.0	.34	.78	20	1.5	6.7	.23	5.7	0.018	0.5	11.5	MW	C	Z
0.219	5.56	O-101	1.00	25.4	.183	4.6	1.9	.33	.77	19	1.4	6.3	.23	5.9	0.018	0.5	12.0	MW	C	N
0.219	5.56	A-65	1.00	25.4	.181	4.6	.58	.10	.28	7.1	.16	.72	.72	18.3	0.019	0.5	37.0	SST	C	N
0.219	5.56	351-A	1.00	25.4	.179	4.5	3.3	.58	.65	17	2.2	9.7	.24	6.0	0.020	0.5	10.8	MW	C	Z
0.219	5.56	12453	1.00	25.4	.175	4.4	3.7	.66	.68	17	2.5	11	.32	8.2	0.022	0.6	13.8	MW	C	Z
0.219	5.56	161-A	1.00	25.4	.173	4.4	5.5	.96	.60	15	3.3	15	.29	7.4	0.023	0.6	11.8	MW	C	N
0.219	5.56	K-39	1.00	25.4	.171	4.3	5.1	.89	.49	12	2.5	11	.34	8.5	0.024	0.6	13.0	SST	C	N
0.219	5.56	RR-39	1.00	25.4	.169	4.3	7.7	1.3	.51	13	4.0	18	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.219	5.56	2675	1.00	25.4	.167	4.2	6.3	1.1	.55	14	3.4	15	.46	11.6	0.026	0.7	16.5	MW	C	Z
0.219	5.56	O-46	1.00	25.4	.165	4.2	8.6	1.5	.57	15	5.0	22	.42	10.6	0.027	0.7	14.5	MW	C	Z
0.219	5.56	162-A	1.00	25.4	.163	4.1	11	2.0	.49	12	5.5	25	.40	10.1	0.028	0.7	13.3	MW	C	Z
0.219	5.56	A10-32	1.00	25.4	.149	3.8	27	4.7	.27	6.9	7.2	32	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.219	5.56	Z-89	1.06	27.0	.183	4.6	.48	.08	.40	10	.19	.84	.67	16.9	0.018	0.5	36.0	SST	C	N
0.219	5.56	J-2	1.06	27.0	.165	4.2	9.8	1.7	.51	13	5.0	22	.35	8.9	0.027	0.7	13.0	MW	CG	GI
0.219	5.56	KK-94	1.06	27.0	.151	3.8	22	3.8	.32	8.2	7.0	31	.58	14.7	0.034	0.9	16.0	SPR	C	N
0.219	5.56	B15-13	1.09	27.8	.141	3.6	36	6.2	.28	7.0	9.9	44	.70	17.8	0.039	1.0	18.0	SPR	CG	N
0.219	5.56	S-1054	1.13	28.6	.163	4.1	10	1.8	.37	9.4	3.7	16	.39	10.0	0.028	0.7	13.0	SST	C	N
0.219	5.56	FF-19	1.13	28.6	.159	4.0	9.6	1.7	.47	12	4.5	20	.54	13.7	0.030	0.8	18.0	SST	CG	N
0.219	5.56	Z-40	1.16	29.4	.159	4.0	17	3.0	.39	9.9	6.7	30	.36	9.1	0.030	0.8	12.0	MW	CG	N
0.219	5.56	2618	1.16	29.4	.147	3.7	26	4.6	.41	11	11	48	.65	16.5	0.036	0.9	17.0	MW	C	Z
0.219	5.56	10574	1.19	30.2	.171	4.3	4.0	.70	.76	19	3.0	14	.43	11.0	0.024	0.6	18.0	MW	CG	N
0.219	5.56	10065	1.25	31.8	.183	4.6	1.7	.30	.94	24	1.6	7.1	.25	6.4	0.018	0.5	13.0	MW	C	Z
0.219	5.56	11399	1.25	31.8	.179	4.5	2.5	.44	.86	22	2.2	9.7	.29	7.4	0.020	0.5	13.5	MW	C	Z
0.219	5.56	2861	1.25	31.8	.171	4.3	3.1	.54	.67	17	2.1	9.2	.58	14.6	0.024	0.6	23.0	MW	C	GI
0.219	5.56	S-145	1.25	31.8	.171	4.3	3.6	.63	.69	17	2.5	11	.44	11.3	0.024	0.6	17.5	SST	C	N
0.219	5.56	3779	1.25	31.8	.163	4.1	10	1.8	.54	14	5.5	25	.43	11.0	0.028	0.7	14.5	MW	C	Z
0.219	5.56	U-20	1.25	31.8	.141	3.6	38	6.7	.26	6.6	9.9	44	.70	17.8	0.039	1.0	17.0	SPR	C	N
0.219	5.56	A10-48	1.28	32.5	.181	4.6	1.0	.18	.84	21	.86	3.8	.44	11.3	0.019	0.5	22.3	SST	C	N
0.219	5.56	FF-91	1.31	33.3	.175	4.4	3.2	.56	.60	15	1.9	8.5	.33	8.4	0.022	0.6	14.0	SST	C	N
0.219	5.56	O-84	1.31	33.3	.163	4.1	9.9	1.7	.55	14	5.5	25	.44	11.2	0.028	0.7	14.8	MW	C	Z
0.219	5.56	S-891	1.38	34.9	.191	4.9	.43	.08	1.2	29	.49	2.2	.22	5.7	0.014	0.4	15.0	SST	C	N
0.219	5.56	159-B	1.38	34.9	.187	4.7	1.2	.20	.97	25	1.1	5.0	.20	5.2	0.016	0.4	11.8	MW	C	Z
0.219	5.56	160-B	1.38	34.9	.183	4.6	1.7	.30	.92	23	1.6	7.1	.25	6.3	0.018	0.5	12.8	MW	C	Z
0.219	5.56	1699	1.38	34.9	.179	4.5	1.5	.27	.94	24	1.4	6.4	.44	11.2	0.020	0.5	21.0	MW	C	Z
0.219	5.56																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.219	5.56	AA-97	1.50	38.1	.159	4.0	8.6	1.5	.78	20	6.7	30	.69	17.5	0.030	0.8	22.0	MW	C	Z
0.219	5.56	KK-50	1.53	38.9	.199	5.1	.07	.01	1.3	33	.09	.38	.24	6.1	0.010	0.3	23.0	SST	C	N
0.219	5.56	S-159	1.56	39.7	.175	4.4	2.4	.42	.80	20	1.9	8.5	.42	10.6	0.022	0.6	18.0	SST	C	N
0.219	5.56	GG-63	1.63	41.3	.179	4.5	1.9	.34	1.1	28	2.2	9.7	.36	9.1	0.020	0.5	17.0	MW	C	Z
0.219	5.56	10664	1.72	43.6	.183	4.6	1.0	.18	1.3	34	1.4	6.2	.38	9.6	0.018	0.5	20.0	MW	C	BO
0.219	5.56	10288	1.75	44.5	.189	4.8	.57	.10	1.5	38	.85	3.8	.27	6.9	0.015	0.4	17.0	MW	C	GI
0.219	5.56	159-C	1.75	44.5	.187	4.7	.90	.16	1.2	32	1.1	5.0	.25	6.3	0.016	0.4	14.5	MW	C	Z
0.219	5.56	160-C	1.75	44.5	.183	4.6	1.3	.23	1.2	31	1.6	7.1	.31	7.8	0.018	0.5	16.0	MW	C	Z
0.219	5.56	351-C	1.75	44.5	.179	4.5	1.9	.32	1.2	30	2.2	9.7	.38	9.5	0.020	0.5	17.8	MW	C	Z
0.219	5.56	161-C	1.75	44.5	.173	4.4	3.0	.53	1.1	28	3.3	15	.48	12.1	0.023	0.6	19.8	MW	C	Z
0.219	5.56	162-C	1.75	44.5	.163	4.1	6.2	1.1	.89	23	5.5	25	.66	16.7	0.028	0.7	22.5	MW	C	Z
0.219	5.56	MM-2	1.88	47.6	.171	4.3	4.6	.80	.81	21	3.7	17	.38	9.8	0.024	0.6	16.0	MW	C	Z
0.219	5.56	FF-46	1.94	49.2	.159	4.0	4.7	.82	.87	22	4.1	18	1.07	27.1	0.030	0.8	34.5	SST	C	N
0.219	5.56	10267	2.19	55.6	.163	4.1	3.4	.59	1.1	27	3.6	16	1.13	28.8	0.028	0.7	39.5	MW	C	GI
0.219	5.56	10436	2.28	57.9	.143	3.6	16	2.8	.58	15	9.2	41	1.33	33.8	0.038	1.0	34.0	SPR	C	GI
0.219	5.56	10640	2.44	61.9	.133	3.4	38	6.6	.35	8.8	13	58	1.16	29.5	0.043	1.1	26.0	SPR	C	Z
0.219	5.56	G-30	5.00	127.0	.181	4.6	.33	.06	3.6	91	1.2	5.2	1.43	36.2	0.019	0.5	74.0	MW	C	GI
0.234	5.94	CC-15	.16	4.0	.198	5.0	5.4	.95	.05	1.3	.29	1.3	.10	2.6	0.018	0.5	4.75	MW	C	N
0.234	5.94	G-8	.16	4.0	.190	4.8	21	3.7	.06	1.4	1.2	5.3	.10	2.5	0.022	0.6	3.50	SST	C	N
0.234	5.94	Z-14	.16	4.0	.164	4.2	238	42	.03	.68	6.4	28	.11	2.7	0.035	0.9	3.00	SST	CG	N
0.234	5.94	VV-8	.25	6.4	.194	4.9	10	1.8	.13	3.4	1.4	6.0	.10	2.5	0.020	0.5	4.00	SST	C	N
0.234	5.94	S-1530	.28	7.1	.190	4.8	31	5.4	.06	1.5	1.8	8.0	.09	2.2	0.022	0.6	3.00	SST	C	N
0.234	5.94	AA-26	.28	7.1	.188	4.8	19	3.3	.11	2.8	2.1	9.1	.09	2.3	0.023	0.6	4.00	SST	CG	N
0.234	5.94	10572	.31	7.9	.210	5.3	1.1	.19	.25	6.2	.27	1.2	.07	1.7	0.012	0.3	4.50	MW	C	N
0.234	5.94	O-41	.31	7.9	.194	4.9	6.7	1.2	.18	4.6	1.2	5.4	.13	3.3	0.020	0.5	5.50	MW	C	N
0.234	5.94	H-3	.31	7.9	.178	4.5	34	5.9	.15	3.9	5.2	23	.14	3.6	0.028	0.7	5.00	MW	CG	N
0.234	5.94	HH-30	.31	7.9	.176	4.5	39	6.9	.15	3.7	5.7	26	.15	3.7	0.029	0.7	5.00	MW	CG	Z
0.234	5.94	FF-10	.31	7.9	.170	4.3	91	16	.06	1.5	5.5	25	.16	4.1	0.032	0.8	4.00	SPR	C	N
0.234	5.94	VV-64	.31	7.9	.170	4.3	37	6.4	.06	1.4	2.0	9.1	.26	6.5	0.032	0.8	7.00	HD	C	Z
0.234	5.94	I-75	.31	7.9	.138	3.5	339	59	.05	1.2	16	72	.26	6.7	0.048	1.2	5.50	SPR	CG	N
0.234	5.94	O-107	.34	8.7	.186	4.7	18	3.2	.13	3.2	2.3	10	.13	3.4	0.024	0.6	4.50	SST	C	N
0.234	5.94	10616	.34	8.7	.174	4.4	35	6.1	.12	3.1	4.3	19	.17	4.2	0.030	0.8	5.50	SST	CG	N
0.234	5.94	G-4	.38	9.5	.208	5.3	.35	.06	.21	5.4	.07	.33	.16	4.1	0.013	0.3	11.5	SST	C	N
0.234	5.94	11450	.38	9.5	.208	5.3	1.0	.18	.30	7.5	.31	1.4	.08	2.0	0.013	0.3	5.00	MW	C	N
0.234	5.94	II-21	.38	9.5	.202	5.1	3.6	.64	.29	7.3	1.0	4.6	.09	2.2	0.016	0.4	4.50	MW	C	Z
0.234	5.94	A-68	.38	9.5	.194	4.9	4.1	.71	.24	6.0	.96	4.3	.14	3.6	0.020	0.5	7.00	SST	CG	N
0.234	5.94	B18-142	.38	9.5	.194	4.9	2.0	.34	.10	2.4	.19	.83	.28	7.1	0.020	0.5	14.0	MW	CG	GI
0.234	5.94	A13-19	.38	9.5	.188	4.8	13	2.2	.16	4.1	2.1	9.1	.12	2.9	0.023	0.6	5.00	SST	CG	N
0.234	5.94	A14-17	.38	9.5	.188	4.8	16	2.7	.20	5.0	3.1	14	.11	2.8	0.023	0.6	4.75	MW	CG	GI
0.234	5.94	S-1118	.38	9.5	.162	4.1	68	12	.10	2.6	6.9	31	.25	6.4	0.036	0.9	6.00	SST	C	N
0.234	5.94	B5-20	.38	9.5	.156	4.0	138	24	.07	1.7	9.3	42	.20	5.2	0.039	1.0	5.25	SPR	CG	Z
0.234	5.94	B15-69	.38	9.5	.152	3.9	141	25	.08	1.9	11	48	.25	6.2	0.041	1.0	6.00	SPR	CG	Z
0.234	5.94	YY-48	.38	9.5	.148	3.8	175	31	.07	1.7	12	51	.24	6.0	0.043	1.1	5.50	SST	CG	N
0.234	5.94	M-132	.41	10.3	.190	4.8	10	1.8	.18	4.5	1.8	8.0	.13	3.4	0.022	0.6	5.00	SST	C	N
0.234	5.94	RR-61	.41	10.3	.188	4.8	11	1.9	.25	6.2	2.6	12	.16	4.1	0.023	0.6	6.00	MW	C	Z
0.234	5.94	II-93	.41	10.3	.178	4.5	15	2.6	.15	3.9	2.3	10	.25	6.4	0.028	0.7	8.00	SST	C	N
0.234	5.94	2708	.41	10.3	.170	4.3	37	6.4	.15	3.8	5.5	24	.26	6.5	0.032	0.8	7.00	MW	C	Z
0.234	5.94	GG-21	.41	10.3	.154	3.9	89	16	.11	2.7	9.4	42	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.234	5.94	B3-64	.42	10.7	.170	4.3	37	6.4	.17	4.2	6.1	27	.26	6.5	0.032	0.8	7.00	MW	C	GI
0.234	5.94	A12-36	.42	10.7	.164	4.2	48	8.3	.13	3.4	6.4	28	.28	7.1	0.035	0.9	7.00	SST	C	N
0.234	5.94	S-813	.44	11.1	.202	5.1	1.3	.23	.29	7.5	.39	1.7	.14	3.7	0.016	0.4	8.00	SST	C	N
0.234	5.94	3564	.44	11.1	.186	4.7	13	2.3	.27	6.9	3.5	15	.17	4.3	0.024	0.6	6.00	MW	C	Z
0.234	5.94	VV-57	.44	11.1	.184	4.7	15	2.7	.24	6.1	3.7	17	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.234	5.94	B1-3	.44	11.1	.182	4.6	18	3.2	.15	3.8	2.8	12	.14	3.6	0.026	0.7	5.50	SST	CG	N
0.234	5.94	NN-64	.44	11.1	.176	4.5	18	3.2	.19	4.9	3.5	15	.25	6.3	0.029	0.7	8.50	MW	CG	N
0.234	5.94	B14-44	.44	11.1	.174	4.4	23	4.0	.17	4.3	3.8	17	.27	6.9	0.030	0.8	8.00	MW	C	N
0.234	5.94	U-41	.44	11.1	.174	4.4	61	11	.07	1.8	4.3	19	.15	3.8	0.030	0.8	4.00	SST	C	N
0.234	5.94	B9-35	.44	11.1	.156	4.0	128	22	.07	1.9	9.3	42	.21	5.4	0.039	1.0	5.50	SPR	CG	N
0.234	5.94	B7-21	.44	11.1	.154	3.9	144	25	.07	1.8	10	45	.22	5.6	0.040	1.0	5.50	SPR	CG	N
0.234	5.94	Z-97	.44	11.1	.154	3.9	92	16	.10	2.6	9.4	42	.27	6.9	0.040	1.0	6.75	SST	CG	N
0.234	5.94	3891	.44	11.1	.144	3.7	175	31	.08	2.0	14	62	.32	8.0	0.045	1.1	7.00	SPR	CG	Z
0.234	5.94	CC-45	.44	11.1	.134	3.4	251	44	.05	1.3	13	56	.39	9.8	0.050	1.3	7.75	SPR	CG	N
0.234	5.94	3991	.44	11.1	.132	3.4	577	101	.03	.82	19	83	.29	7.4	0.051	1.3	4.75	SPR	C	Z
0.234	5.94	B2-1	.45	11.5	.172	4.4	45	7.9	.15	3.9	7.0	31	.20	5.1	0.031	0.8	5.50	MW	CL	N
0.234	5.94	12763	.45	11.5	.170	4.3	46	8.0	.17	4.3	7.7	34	.22	5.7	0.032	0.8	6.00	MW	C	N
0.234	5.94	B12-13	.47	11.9	.190	4.8	9.4	1.7	.29	7.3	2.7	12	.13	3.2	0.022	0.6	5.75	MW	CG	Z
0.234	5.94	12585	.47	11.9	.172	4.4	40	6.9	.18	4.5	7.0	31	.22	5.5	0.031	0.8	6.00	MW	C	N
0.234	5.94	12491	.47	11.9	.170	4.3	49	8.5	.11	2.9	5.5	25	.22	5.5	0.032	0.8	5.75	SPR	C	N
0.234	5.94	A12-29	.47	11.9	.210	5.3	.45	.08	.36	9.2	.16	.73	.11	2.7	0.012					




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.234	5.94	B17-127	.50	12.7	.178	4.5	19	3.3	.27	6.9	5.2	23	.21	5.2	0.028	0.7	7.33	MW	CG	Z
0.234	5.94	K-9	.50	12.7	.176	4.5	20	3.4	.27	6.8	5.3	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.234	5.94	JJ-58	.50	12.7	.174	4.4	22	3.8	.20	5.0	4.3	19	.26	6.5	0.030	0.8	7.50	SST	C	N
0.234	5.94	S-1692	.50	12.7	.170	4.3	32	5.6	.16	4.1	5.1	23	.26	6.5	0.032	0.8	7.00	SST	C	N
0.234	5.94	IL-18	.50	12.7	.170	4.3	32	5.6	.22	5.6	7.0	31	.28	7.1	0.032	0.8	7.75	MW	C	N
0.234	5.94	S-3003	.50	12.7	.168	4.3	46	8.0	.12	3.1	5.6	25	.23	5.9	0.033	0.8	6.00	SST	C	N
0.234	5.94	A12-42	.50	12.7	.156	4.0	80	14	.11	2.8	8.7	39	.27	6.9	0.039	1.0	7.00	SST	CG	N
0.234	5.94	B-28	.50	12.7	.152	3.9	141	25	.08	1.9	11	48	.25	6.2	0.041	1.0	6.00	SPR	CG	GI
0.234	5.94	3518	.50	12.7	.150	3.8	253	44	.05	1.2	12	51	.19	4.8	0.042	1.1	4.50	SPR	CG	N
0.234	5.94	A13-13	.50	12.7	.150	3.8	112	20	.10	2.4	11	48	.29	7.5	0.042	1.1	7.00	SST	CG	N
0.234	5.94	Y-98	.50	12.7	.144	3.7	175	31	.08	2.0	14	62	.32	8.0	0.045	1.1	7.00	SPR	CG	Z
0.234	5.94	1505	.50	12.7	.140	3.6	268	47	.06	1.5	16	71	.28	7.2	0.047	1.2	6.00	HD	CG	Z
0.234	5.94	DD-39	.50	12.7	.134	3.4	481	84	.04	.93	18	78	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.234	5.94	2963	.53	13.5	.212	5.4	.63	.11	.47	12	.29	1.3	.07	1.7	0.011	0.3	5.00	MW	C	GI
0.234	5.94	FF-71	.53	13.5	.206	5.2	.77	.13	.41	10	.31	1.4	.13	3.2	0.014	0.4	8.00	SST	C	N
0.234	5.94	A10-8	.53	13.5	.196	5.0	3.4	.60	.37	9.4	1.3	5.6	.16	4.1	0.019	0.5	7.50	MW	C	N
0.234	5.94	S-1461	.53	13.5	.192	4.9	2.6	.46	.29	7.4	.77	3.4	.24	6.1	0.021	0.5	11.5	SST	CG	N
0.234	5.94	11216	.53	13.5	.190	4.8	7.8	1.4	.23	5.8	1.8	8.0	.13	3.4	0.022	0.6	6.00	SST	CG	N
0.234	5.94	3529	.53	13.5	.164	4.2	68	12	.14	3.5	9.5	42	.21	5.3	0.035	0.9	6.00	MW	CG	Z
0.234	5.94	M-102	.53	13.5	.160	4.1	45	7.8	.17	4.3	7.5	33	.33	8.5	0.037	0.9	9.00	SST	CG	N
0.234	5.94	CC-65	.53	13.5	.154	3.9	64	11	.15	3.7	9.4	42	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.234	5.94	HH-47	.56	14.3	.202	5.1	.61	.11	.31	7.8	.19	.83	.26	6.5	0.016	0.4	15.0	SST	C	N
0.234	5.94	10930	.56	14.3	.198	5.0	2.2	.39	.40	10	.89	3.9	.16	4.1	0.018	0.5	8.00	SST	C	N
0.234	5.94	LL-98	.56	14.3	.192	4.9	8.4	1.5	.19	4.8	1.6	7.0	.13	3.2	0.021	0.5	5.00	SST	C	N
0.234	5.94	A-85	.56	14.3	.188	4.8	7.1	1.2	.38	9.6	2.7	12	.18	4.7	0.023	0.6	8.00	MW	C	Z
0.234	5.94	B1-13	.56	14.3	.182	4.6	14	2.4	.21	5.2	2.8	12	.18	4.5	0.026	0.7	6.75	SST	CG	N
0.234	5.94	IL-13	.56	14.3	.180	4.6	18	3.2	.26	6.5	4.7	21	.21	5.3	0.027	0.7	6.75	MW	C	N
0.234	5.94	A10-12	.56	14.3	.178	4.5	14	2.4	.32	8.2	4.5	20	.24	6.0	0.028	0.7	8.50	MW	CG	N
0.234	5.94	W-63	.56	14.3	.170	4.3	27	4.6	.19	4.9	5.1	23	.26	6.5	0.032	0.8	8.00	SST	CG	N
0.234	5.94	3216	.56	14.3	.166	4.2	40	7.0	.16	4.2	6.6	29	.27	6.9	0.034	0.9	8.00	SPR	CG	GI
0.234	5.94	S-832	.56	14.3	.166	4.2	35	6.1	.18	4.5	6.1	27	.27	6.9	0.034	0.9	8.00	SST	CG	N
0.234	5.94	S-929	.56	14.3	.164	4.2	60	10	.11	2.7	6.4	28	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.234	5.94	12031	.59	15.1	.208	5.3	.76	.13	.49	12	.37	1.7	.10	2.6	0.013	0.3	7.00	MW	C	N
0.234	5.94	JJ-67	.59	15.1	.190	4.8	7.4	1.3	.36	9.2	2.7	12	.17	4.3	0.022	0.6	6.75	MW	C	N
0.234	5.94	M-81	.59	15.1	.170	4.3	41	7.1	.14	3.4	5.5	25	.24	6.1	0.032	0.8	6.50	SPR	C	N
0.234	5.94	Z-19	.59	15.1	.156	4.0	52	9.1	.17	4.3	8.7	39	.37	9.4	0.039	1.0	9.50	SST	CG	N
0.234	5.94	W-96	.59	15.1	.126	3.2	304	53	.07	1.7	21	91	.43	11.0	0.054	1.4	8.00	SST	CG	N
0.234	5.94	B2-26	.59	15.1	.144	3.7	159	28	.09	2.2	14	62	.34	8.6	0.045	1.1	7.50	SPR	CG	N
0.234	5.94	CC-14	.63	15.9	.214	5.4	.11	.02	.50	13	.06	.24	.13	3.3	0.010	0.3	12.0	SST	C	N
0.234	5.94	IL-95	.63	15.9	.194	4.9	2.1	.38	.38	9.5	.81	3.6	.25	6.4	0.020	0.5	11.5	SST	C	N
0.234	5.94	PP-2	.63	15.9	.194	4.9	3.0	.52	.45	11	1.3	5.9	.18	4.6	0.020	0.5	9.00	SST	CG	N
0.234	5.94	A9-14	.63	15.9	.190	4.8	6.3	1.1	.29	7.3	1.8	8.0	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.234	5.94	YY-20	.63	15.9	.190	4.8	3.7	.65	.35	8.9	1.3	5.8	.28	7.0	0.022	0.6	11.5	MW	C	N
0.234	5.94	FF-1	.63	15.9	.180	4.6	13	2.3	.35	8.9	4.7	21	.26	6.5	0.027	0.7	8.50	MW	C	N
0.234	5.94	VV-62	.63	15.9	.174	4.4	20	3.4	.32	8.2	6.3	28	.27	6.9	0.030	0.8	9.00	MW	CG	Z
0.234	5.94	B7-24	.63	15.9	.174	4.4	18	3.2	.34	8.6	6.2	28	.29	7.2	0.030	0.8	9.50	MW	CG	N
0.234	5.94	J-85	.63	15.9	.166	4.2	30	5.3	.22	5.6	6.6	29	.34	8.6	0.034	0.9	10.0	SPR	CG	N
0.234	5.94	11315	.63	15.9	.166	4.2	23	4.0	.21	5.3	4.8	21	.42	10.6	0.034	0.9	11.3	SST	C	N
0.234	5.94	B-12	.63	15.9	.158	4.0	43	7.6	.19	4.8	8.1	36	.38	9.7	0.038	1.0	10.0	SST	CG	N
0.234	5.94	GG-4	.63	15.9	.154	3.9	63	11	.16	4.0	10	45	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.234	5.94	11260	.63	15.9	.150	3.8	126	22	.09	2.3	12	51	.34	8.5	0.042	1.1	7.00	SPR	C	Z
0.234	5.94	DD-10	.66	16.7	.194	4.9	2.9	.51	.44	11	1.3	5.7	.22	5.6	0.020	0.5	10.0	MW	C	N
0.234	5.94	W-77	.66	16.7	.182	4.6	9.2	1.6	.30	7.7	2.8	12	.26	6.6	0.026	0.7	9.00	SST	C	N
0.234	5.94	I-92	.66	16.7	.174	4.4	20	3.4	.32	8.2	6.3	28	.27	6.9	0.030	0.8	9.00	MW	CG	N
0.234	5.94	B5-27	.66	16.7	.168	4.3	30	5.3	.20	5.1	6.0	27	.30	7.5	0.033	0.8	9.00	SPR	CG	N
0.234	5.94	M-32	.66	16.7	.168	4.3	21	3.6	.27	6.9	5.6	25	.36	9.2	0.033	0.8	11.0	SST	CG	N
0.234	5.94	VV-2	.69	17.4	.194	4.9	1.7	.30	.39	9.8	.66	2.9	.30	7.6	0.020	0.5	14.0	SST	C	N
0.234	5.94	YY-63	.69	17.4	.188	4.8	4.3	.75	.39	9.9	1.7	7.4	.30	7.6	0.023	0.6	12.0	MW	C	Z
0.234	5.94	IL-87	.69	17.4	.186	4.7	4.3	.75	.36	9.2	1.5	6.9	.32	8.2	0.024	0.6	12.5	SST	C	N
0.234	5.94	B-65	.69	17.4	.182	4.6	11	1.9	.26	6.7	2.8	12	.23	5.9	0.026	0.7	8.00	SST	C	N
0.234	5.94	A14-14	.69	17.4	.180	4.6	14	2.5	.32	8.3	4.7	21	.22	5.5	0.027	0.7	8.00	MW	CG	GI
0.234	5.94	S-3134	.69	17.4	.174	4.4	18	3.2	.23	5.9	4.3	19	.26	6.5	0.030	0.8	8.50	SST	CG	N
0.234	5.94	B2-24	.69	17.4	.158	4.0	50	8.7	.24	6.1	12	53	.42	10.6	0.038	1.0	10.0	MW	C	N
0.234	5.94	3632	.69	17.4	.154	3.9	63	11	.16	4.0	10	45	.44	11.2	0.040	1.0	10.0	SPR	C	Z
0.234	5.94	A14-53	.69	17.4	.150	3.8	77	14	.14	3.6	11	48	.39	9.9	0.042	1.1	9.25	SST	CG	N
0.234	5.94	Y-93	.69	17.4	.146	3.7	112	20	.12	3.0	13	59	.40	10.1	0.044	1.1	9.00	SPR	CG	Z
0.234	5.94	DD-75	.69	17.4	.134	3.4	288	51	.08	2.2	24	109	.35	8.9	0.050	1.3	7.00	MW	CG	N
0.234	5.94	10011	.69	17.5	.200	5.1	1.7	.29	.52	13	.87	3.9	.17	4.3	0.017	0.4	9.00	MW	C	Z
0.234	5.94	11163	.72	18.2	.214	5.4	.20	.03	.62	16	.12	.55	.10	2.4	0.010	0.3	8.50	MW	C	Z
0.234	5.94	B11-31	.72	18.2	.182	4.6	13	2.2	.33</											




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.234	5.94	W-33	.75	19.1	.186	4.7	5.0	.87	.46	12	2.3	10	.29	7.3	0.024	0.6	11.0	SST	C	N
0.234	5.94	10158	.75	19.1	.184	4.7	6.2	1.1	.43	11	2.6	12	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.234	5.94	A11-38	.75	19.1	.180	4.6	11	1.9	.29	7.3	3.1	14	.24	6.2	0.027	0.7	9.00	SST	CG	N
0.234	5.94	EE-25	.75	19.1	.176	4.5	11	2.0	.34	8.6	3.8	17	.32	8.1	0.029	0.7	11.0	SST	CG	N
0.234	5.94	O-112	.75	19.1	.172	4.4	20	3.5	.35	8.9	7.0	31	.34	8.7	0.031	0.8	10.0	MW	C	GI
0.234	5.94	B5-15	.75	19.1	.156	4.0	53	9.2	.18	4.5	9.3	42	.41	10.4	0.039	1.0	10.5	SPR	CG	N
0.234	5.94	2533	.78	19.8	.174	4.4	15	2.7	.42	11	6.3	28	.36	9.1	0.030	0.8	11.0	MW	C	Z
0.234	5.94	3549	.81	20.6	.192	4.9	2.4	.42	.50	13	1.2	5.3	.32	8.0	0.021	0.5	14.0	MW	C	Z
0.234	5.94	3661	.81	20.6	.190	4.8	3.5	.62	.53	13	1.9	8.3	.29	7.3	0.022	0.6	12.0	MW	C	Z
0.234	5.94	00-85	.81	20.6	.190	4.8	2.8	.50	.47	12	1.3	5.9	.34	8.7	0.022	0.6	14.5	MW	C	BO
0.234	5.94	S-1339	.81	20.6	.190	4.8	3.4	.60	.53	13	1.8	8.0	.24	6.1	0.022	0.6	11.0	SST	CG	N
0.234	5.94	B5-44	.81	20.6	.190	4.8	5.4	.95	.50	13	2.7	12	.19	4.7	0.022	0.6	8.50	MW	CG	Z
0.234	5.94	V-44	.81	20.6	.186	4.7	4.1	.72	.46	12	1.9	8.5	.35	8.8	0.024	0.6	14.5	MW	CG	N
0.234	5.94	00-74	.81	20.6	.178	4.5	13	2.2	.41	10	5.2	23	.31	7.8	0.028	0.7	10.0	MW	C	N
0.234	5.94	S-1177	.81	20.6	.174	4.4	11	2.0	.37	9.5	4.3	19	.41	10.3	0.030	0.8	12.5	SST	C	N
0.234	5.94	L-67	.81	20.6	.164	4.2	25	4.4	.27	7.0	6.8	30	.46	11.6	0.035	0.9	13.0	SPR	CG	Z
0.234	5.94	A9-7	.81	20.6	.162	4.1	36	6.3	.21	5.2	7.4	33	.38	9.8	0.036	0.9	10.7	SPR	CG	N
0.234	5.94	3000	.81	20.6	.154	3.9	59	10	.17	4.3	10	45	.42	10.7	0.040	1.0	10.5	SPR	CG	Z
0.234	5.94	B5-19	.81	20.6	.152	3.9	59	10	.18	4.6	11	48	.47	12.0	0.041	1.0	11.5	SPR	CG	N
0.234	5.94	LL-27	.84	21.4	.204	5.2	.80	.14	.69	17	.55	2.4	.16	4.0	0.015	0.4	9.50	SST	C	N
0.234	5.94	H-72	.84	21.4	.182	4.6	15	2.7	.27	6.9	4.2	19	.20	5.1	0.026	0.7	6.75	MW	C	N
0.234	5.94	JJ-79	.84	21.4	.164	4.2	20	3.5	.32	8.0	6.4	28	.48	12.2	0.035	0.9	13.8	SST	CG	N
0.234	5.94	GG-26	.84	21.4	.154	3.9	34	6.0	.24	6.2	8.4	37	.60	15.2	0.040	1.0	15.0	SST	CG	N
0.234	5.94	JJ-36	.84	21.4	.150	3.8	66	12	.16	4.2	11	48	.48	12.3	0.042	1.1	10.5	SST	C	N
0.234	5.94	4200	.88	22.2	.194	4.9	2.0	.36	.59	15	1.2	5.3	.29	7.4	0.020	0.5	13.5	MW	C	Z
0.234	5.94	B14-57	.88	22.2	.192	4.9	3.4	.60	.65	17	2.2	9.9	.22	5.6	0.021	0.5	10.5	MW	CG	Z
0.234	5.94	W-16	.88	22.2	.184	4.7	5.9	1.0	.42	11	2.5	11	.30	7.6	0.025	0.6	11.0	SST	C	N
0.234	5.94	G-47	.88	22.2	.180	4.6	13	2.3	.35	8.9	4.7	21	.26	6.5	0.027	0.7	8.50	MW	C	N
0.234	5.94	Q-21	.88	22.2	.170	4.3	18	3.2	.30	7.7	5.5	25	.38	9.8	0.032	0.8	12.0	SPR	CG	N
0.234	5.94	DD-17	.88	22.2	.170	4.3	12	2.1	.36	9.2	4.4	20	.51	13.0	0.032	0.8	15.0	SST	C	N
0.234	5.94	DD-52	.88	22.2	.154	3.9	63	11	.22	5.6	14	62	.40	10.2	0.040	1.0	10.0	MW	CG	N
0.234	5.94	LL-71	.88	22.2	.154	3.9	92	16	.11	2.8	10	45	.34	8.6	0.040	1.0	7.50	SPR	C	N
0.234	5.94	B5-62	.91	23.0	.210	5.3	.34	.06	.77	20	.26	1.2	.13	3.4	0.012	0.3	10.0	MW	C	N
0.234	5.94	FF-83	.91	23.0	.190	4.8	3.8	.67	.47	12	1.8	8.0	.24	6.1	0.022	0.6	10.0	SST	C	N
0.234	5.94	B10-1	.91	23.0	.166	4.2	25	4.3	.27	6.8	6.6	29	.40	10.1	0.034	0.9	11.8	SPR	CG	Z
0.234	5.94	GG-30	.94	23.8	.198	5.0	1.0	.17	.61	16	.61	2.7	.32	8.2	0.018	0.5	17.0	MW	C	N
0.234	5.94	S-3155	.94	23.8	.194	4.9	1.1	.20	.52	13	.59	2.6	.42	10.7	0.020	0.5	20.0	SST	C	N
0.234	5.94	HH-20	.97	24.6	.170	4.3	14	2.4	.38	9.6	5.1	23	.45	11.4	0.032	0.8	14.0	SST	CG	N
0.234	5.94	IL-82	.97	24.6	.166	4.2	16	2.8	.38	9.7	6.1	27	.51	13.0	0.034	0.9	15.0	SST	CG	N
0.234	5.94	O-100	.97	24.6	.160	4.1	35	6.2	.23	5.8	8.0	36	.44	11.3	0.037	0.9	12.0	SPR	CG	Z
0.234	5.94	H-6	.97	24.6	.152	3.9	56	9.8	.18	4.6	10	45	.45	11.5	0.041	1.0	11.0	SST	CG	N
0.234	5.94	3562	1.00	25.4	.202	5.1	.83	.14	.78	20	.64	2.9	.22	5.7	0.016	0.4	13.0	MW	C	GI
0.234	5.94	W-90	1.00	25.4	.202	5.1	.88	.15	.80	20	.70	3.1	.19	4.9	0.016	0.4	11.0	SST	C	N
0.234	5.94	GG-87	1.00	25.4	.194	4.9	1.5	.26	.66	17	.96	4.3	.34	8.6	0.020	0.5	16.0	SST	C	N
0.234	5.94	1565	1.00	25.4	.192	4.9	3.2	.56	.73	19	2.4	10	.25	6.4	0.021	0.5	11.0	MW	C	Z
0.234	5.94	2699	1.00	25.4	.188	4.8	3.9	.68	.68	17	2.6	12	.32	8.2	0.023	0.6	13.0	MW	C	Z
0.234	5.94	2939	1.00	25.4	.186	4.7	4.7	.82	.66	17	3.1	14	.34	8.5	0.024	0.6	13.0	MW	C	Z
0.234	5.94	K-88	1.00	25.4	.182	4.6	5.8	1.0	.48	12	2.8	12	.36	9.2	0.026	0.7	13.0	SST	C	N
0.234	5.94	N-131	1.00	25.4	.176	4.5	7.1	1.2	.52	13	3.7	16	.48	12.2	0.029	0.7	16.5	SST	CG	N
0.234	5.94	HH-1	1.00	25.4	.174	4.4	8.6	1.5	.46	12	3.9	18	.54	13.7	0.030	0.8	18.0	MW	CG	GI
0.234	5.94	10438	1.00	25.4	.168	4.3	17	3.1	.34	8.8	6.0	27	.50	12.6	0.033	0.8	14.0	SPR	C	N
0.234	5.94	M-99	1.00	25.4	.164	4.2	23	4.0	.30	7.6	6.8	30	.49	12.4	0.035	0.9	14.0	SPR	CG	BO
0.234	5.94	S-3126	1.00	25.4	.164	4.2	17	3.0	.37	9.4	6.4	28	.55	14.0	0.035	0.9	15.8	SST	CG	N
0.234	5.94	3783	1.00	25.4	.162	4.1	26	4.5	.29	7.3	7.4	33	.54	13.7	0.036	0.9	14.0	SPR	C	Z
0.234	5.94	HH-69	1.00	25.4	.158	4.0	29	5.1	.28	7.1	8.1	36	.53	13.5	0.038	1.0	14.0	SST	CG	N
0.234	5.94	BB-82	1.00	25.4	.154	3.9	37	6.5	.25	6.4	9.4	42	.56	14.2	0.040	1.0	14.0	SST	CG	N
0.234	5.94	I-10	1.03	26.2	.204	5.2	.56	.10	.82	21	.46	2.0	.21	5.3	0.015	0.4	13.0	SST	C	N
0.234	5.94	3526	1.03	26.2	.190	4.8	3.5	.62	.75	19	2.6	12	.29	7.3	0.022	0.6	12.0	MW	C	Z
0.234	5.94	1926	1.06	27.0	.194	4.9	2.6	.46	.78	20	2.0	9.1	.24	6.1	0.020	0.5	11.0	MW	C	Z
0.234	5.94	EE-7	1.06	27.0	.158	4.0	33	5.8	.25	6.3	8.1	36	.48	12.1	0.038	1.0	12.5	SST	CG	N
0.234	5.94	3551	1.09	27.8	.180	4.6	5.7	1.0	.64	16	3.6	16	.46	11.7	0.027	0.7	17.0	MW	CG	Z
0.234	5.94	10198	1.13	28.6	.208	5.3	.27	.05	.90	23	.25	1.1	.22	5.6	0.013	0.3	16.0	MW	C	N
0.234	5.94	B-90	1.13	28.6	.182	4.6	6.6	1.2	.63	16	4.2	19	.36	9.2	0.026	0.7	13.0	MW	C	N
0.234	5.94	A-34	1.13	28.6	.160	4.1	25	4.4	.32	8.1	8.0	36	.63	16.0	0.037	0.9	16.0	SPR	C	GI
0.234	5.94	3848	1.13	28.6	.150	3.8	53	9.2	.22	5.6	12	51	.63	16.0	0.042	1.1	14.0	SPR	C	Z
0.234	5.94	L-22	1.19	30.2	.184	4.7	4.0	.71	.62	16	2.5	11	.39	9.8	0.025	0.6	15.5	SST	CG	N
0.234	5.94	G-69	1.19	30.2	.178	4.5	6.7	1.2	.68	17	4.6	21	.50	12.8	0.028	0.7	17.0	MW	C	GI
0.234	5.94	K-10	1.19	30.2	.176	4.5	6.6	1.2	.58	15	3.8	17	.54	13.6	0.029	0.7	17.5	SST	C	N
0.234	5.94	S-796	1.19	30.2	.174	4.4	7.0	1.2	.61	15	4.3									




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.234	5.94	S-88	1.28	32.5	.186	4.7	4.1	.71	.57	15	2.3	10	.34	8.5	0.024	0.6	13.0	SST	C	N
0.234	5.94	B9-41	1.31	33.3	.192	4.9	3.0	.53	.78	20	2.4	10	.24	6.1	0.021	0.5	11.5	MW	CG	Z
0.234	5.94	W-6	1.31	33.3	.176	4.5	5.4	.95	.67	17	3.6	16	.64	16.2	0.029	0.7	21.0	SST	C	N
0.234	5.94	B3-43	1.33	33.7	.180	4.6	5.1	.89	.79	20	4.0	18	.54	13.7	0.027	0.7	19.0	MW	C	BO
0.234	5.94	DD-46	1.44	36.5	.194	4.9	1.2	.20	1.0	26	1.2	5.2	.42	10.7	0.020	0.5	20.0	SST	C	N
0.234	5.94	S-1540	1.50	38.1	.206	5.2	.50	.09	.99	25	.50	2.2	.17	4.3	0.014	0.4	11.0	SST	C	N
0.234	5.94	QQ-47	1.50	38.1	.192	4.9	1.3	.23	1.0	26	1.4	6.1	.46	11.7	0.021	0.5	21.0	SST	C	N
0.234	5.94	S-224	1.50	38.1	.186	4.7	2.8	.50	.82	21	2.3	10	.45	11.4	0.024	0.6	17.8	SST	C	N
0.234	5.94	B5-26	1.50	38.1	.160	4.1	20	3.5	.40	10	8.0	36	.73	18.6	0.037	0.9	19.8	SPR	CG	N
0.234	5.94	CC-3	1.50	38.1	.154	3.9	30	5.2	.34	8.6	10	45	.80	20.3	0.040	1.0	19.0	SPR	C	N
0.234	5.94	L-51	1.69	42.8	.206	5.2	.13	.02	1.1	27	.14	.60	.62	15.6	0.014	0.4	43.0	MW	C	N
0.234	5.94	DD-95	1.81	46.0	.188	4.8	2.1	.36	.99	25	2.1	9.1	.48	12.3	0.023	0.6	20.0	SST	C	N
0.234	5.94	TT-68	1.88	47.6	.194	4.9	.97	.17	1.4	35	1.4	6.0	.48	12.2	0.020	0.5	23.0	SST	C	N
0.234	5.94	2804	2.00	50.8	.164	4.2	11	2.0	.83	21	9.5	42	.91	23.1	0.035	0.9	26.0	MW	CG	Z
0.234	5.94	3976	2.22	56.4	.132	3.4	68	12	.28	7.0	19	83	1.35	34.3	0.051	1.3	25.5	SPR	C	Z
0.234	5.94	0-51	2.25	57.2	.204	5.2	.29	.05	1.8	47	.53	2.4	.41	10.3	0.015	0.4	26.0	MW	C	N
0.234	5.94	10431	2.25	57.2	.172	4.4	7.2	1.3	.97	25	7.0	31	.78	19.7	0.031	0.8	24.0	MW	C	GI
0.234	5.94	3680	2.44	61.9	.182	4.6	4.6	.81	.90	23	4.2	19	.49	12.4	0.026	0.7	17.8	MW	C	Z
0.234	5.94	B4-21	2.50	63.5	.174	4.4	5.0	.88	1.3	32	6.3	28	.91	23.1	0.030	0.8	29.3	MW	C	N
0.234	5.94	2653	2.53	64.3	.164	4.2	14	2.5	.49	12	6.8	30	.75	19.1	0.035	0.9	21.5	SPR	CG	Z
0.234	5.94	B12-68	2.56	65.1	.184	4.7	2.4	.41	1.6	40	3.7	17	.73	18.4	0.025	0.6	28.0	MW	C	Z
0.234	5.94	0-42	2.75	69.9	.150	3.8	15	2.7	.71	18	11	48	1.60	40.5	0.042	1.1	38.0	SST	CG	N
0.234	5.94	11306	3.25	82.6	.184	4.7	1.1	.19	2.0	50	2.2	9.7	1.30	33.0	0.025	0.6	51.0	SST	C	N
0.234	5.94	B2-68	3.33	84.5	.158	4.0	8.9	1.6	.97	25	8.7	39	1.81	45.8	0.038	1.0	46.5	SPR	CL	N
0.234	5.94	3636	4.50	114.3	.162	4.1	6.1	1.1	1.7	43	10	46	1.94	49.4	0.036	0.9	53.0	MW	C	Z
0.234	5.94	12738	7.25	184.2	.156	4.0	9.3	1.6	1.0	25	9.3	42	1.99	50.5	0.039	1.0	50.0	SPR	C	N
0.240	6.10	70520	.25	6.4	.208	5.3	6.2	1.1	.17	4.2	1.0	4.6	.05	1.4	0.016	0.4	3.38	MW	CG	N
0.240	6.10	70520S	.25	6.4	.208	5.3	5.3	.92	.13	3.3	.68	3.0	.05	1.4	0.016	0.4	3.38	SST	CG	N
0.240	6.10	70536	.25	6.4	.204	5.2	9.5	1.7	.15	3.9	1.5	6.5	.06	1.6	0.018	0.5	3.50	MW	CG	N
0.240	6.10	70536S	.25	6.4	.204	5.2	8.0	1.4	.12	3.1	.97	4.3	.06	1.6	0.018	0.5	3.50	SST	CG	N
0.240	6.10	70553	.25	6.4	.200	5.1	13	2.2	.16	4.0	2.0	8.9	.08	1.9	0.020	0.5	3.75	MW	CG	N
0.240	6.10	70553S	.25	6.4	.200	5.1	11	1.9	.12	3.2	1.3	5.9	.08	1.9	0.020	0.5	3.75	SST	CG	N
0.240	6.10	70577	.25	6.4	.196	5.0	19	3.3	.14	3.6	2.6	12	.08	2.1	0.022	0.6	3.75	MW	CG	N
0.240	6.10	70577S	.25	6.4	.196	5.0	16	2.8	.11	2.8	1.8	7.8	.08	2.1	0.022	0.6	3.75	SST	CG	N
0.240	6.10	70521	.31	7.9	.208	5.3	4.8	.84	.21	5.4	1.0	4.6	.06	1.5	0.016	0.4	3.75	MW	CG	N
0.240	6.10	70521S	.31	7.9	.208	5.3	4.1	.71	.17	4.3	.68	3.0	.06	1.5	0.016	0.4	3.75	SST	CG	N
0.240	6.10	70537	.31	7.9	.204	5.2	7.4	1.3	.20	5.0	1.5	6.5	.07	1.8	0.018	0.5	3.88	MW	CG	N
0.240	6.10	70537S	.31	7.9	.204	5.2	6.2	1.1	.16	3.9	.97	4.3	.07	1.8	0.018	0.5	3.88	SST	CG	N
0.240	6.10	70554	.31	7.9	.200	5.1	9.8	1.7	.20	5.2	2.0	8.9	.09	2.2	0.020	0.5	4.25	MW	CG	N
0.240	6.10	70554S	.31	7.9	.200	5.1	8.3	1.5	.16	4.0	1.3	5.9	.09	2.2	0.020	0.5	4.25	SST	CG	N
0.240	6.10	70578	.31	7.9	.196	5.0	15	2.6	.18	4.6	2.6	12	.09	2.4	0.022	0.6	4.25	MW	CG	N
0.240	6.10	70578S	.31	7.9	.196	5.0	12	2.2	.14	3.6	1.8	7.8	.09	2.4	0.022	0.6	4.25	SST	CG	N
0.240	6.10	70620	.31	7.9	.188	4.8	28	4.9	.14	3.7	4.1	18	.11	2.9	0.026	0.7	4.38	MW	CG	N
0.240	6.10	70620S	.31	7.9	.188	4.8	24	4.2	.11	2.9	2.7	12	.11	2.9	0.026	0.7	4.38	SST	CG	N
0.240	6.10	70642	.31	7.9	.182	4.6	40	7.0	.14	3.6	5.6	25	.14	3.5	0.029	0.7	4.75	MW	CG	N
0.240	6.10	70642S	.31	7.9	.182	4.6	34	6.0	.11	2.8	3.8	17	.14	3.5	0.029	0.7	4.75	SST	CG	N
0.240	6.10	70660	.31	7.9	.176	4.5	63	11	.12	3.0	7.5	33	.15	3.8	0.032	0.8	4.63	MW	CG	N
0.240	6.10	70660S	.31	7.9	.176	4.5	53	9.4	.09	2.4	5.0	22	.15	3.8	0.032	0.8	4.63	SST	CG	N
0.240	6.10	70679	.31	7.9	.170	4.3	88	15	.10	2.7	9.2	41	.17	4.3	0.035	0.9	4.88	MW	CG	N
0.240	6.10	70679S	.31	7.9	.170	4.3	75	13	.08	2.1	6.3	28	.17	4.3	0.035	0.9	4.88	SST	CG	N
0.240	6.10	70700	.31	7.9	.164	4.2	127	22	.09	2.3	12	52	.19	4.7	0.038	1.0	4.88	MW	CG	N
0.240	6.10	70700S	.31	7.9	.164	4.2	108	19	.07	1.9	7.9	35	.19	4.7	0.038	1.0	4.88	SST	CG	N
0.240	6.10	70720	.31	7.9	.160	4.1	155	27	.09	2.2	14	60	.20	5.1	0.040	1.0	5.00	MW	CG	N
0.240	6.10	70720S	.31	7.9	.160	4.1	132	23	.07	1.8	9.2	41	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.240	6.10	12732	.38	9.5	.204	5.2	8.7	1.5	.11	2.8	.97	4.3	.06	1.5	0.018	0.5	3.38	SST	CG	N
0.240	6.10	70522	.38	9.7	.208	5.3	3.9	.68	.26	6.7	1.0	4.6	.07	1.7	0.016	0.4	4.13	MW	CG	N
0.240	6.10	70522S	.38	9.7	.208	5.3	3.3	.58	.21	5.2	.68	3.0	.07	1.7	0.016	0.4	4.13	SST	CG	N
0.240	6.10	70538	.38	9.7	.204	5.2	5.9	1.0	.25	6.3	1.5	6.5	.08	2.0	0.018	0.5	4.38	MW	CG	N
0.240	6.10	70538S	.38	9.7	.204	5.2	5.0	.88	.19	4.9	.97	4.3	.08	2.0	0.018	0.5	4.38	SST	CG	N
0.240	6.10	70555	.38	9.7	.200	5.1	7.7	1.4	.26	6.6	2.0	8.9	.10	2.4	0.020	0.5	4.75	MW	CG	N
0.240	6.10	70555S	.38	9.7	.200	5.1	6.6	1.1	.20	5.1	1.3	5.9	.10	2.4	0.020	0.5	4.75	SST	CG	N
0.240	6.10	70579	.38	9.7	.196	5.0	12	2.1	.22	5.5	2.6	12	.10	2.6	0.022	0.6	4.63	MW	CG	N
0.240	6.10	70579S	.38	9.7	.196	5.0	10	1.8	.17	4.3	1.8	7.8	.10	2.6	0.022	0.6	4.63	SST	CG	N
0.240	6.10	70600	.38	9.7	.192	4.9	17	2.9	.21	5.2	3.4	15	.12	3.0	0.024	0.6	4.88	MW	CG	N
0.240	6.10	70600S	.38	9.7	.192	4.9	14	2.5	.16	4.1	2.3	10	.12	3.0	0.024	0.6	4.88	SST	CG	N
0.240	6.10	70621	.38	9.7	.188	4.8	24	4.1	.17	4.4	4.1	18	.13	3.2	0.026	0.7	4.88	MW	CG	N
0.240	6.10	70621S	.38	9.7	.188	4.8	20	3.5	.14	3.4	2.7	12	.13	3.2	0.026	0.7	4.88	SST	CG	N
0.240	6.10	70643	.38	9.7	.182	4.6	33	5.7	.17	4.4	5.6	25	.15	3.9	0.029	0.7	5.25	MW	CG	N
0.240	6.10	70643S	.38	9.7	.182	4.6	28	4.9	.14	3.4	3.8	17	.15	3						




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70761S	.38	9.7	.150	3.8	183	32	.07	1.8	13	57	.26	6.6	0.045	1.1	5.75	SST	CG	N
0.240	6.10	70523	.44	11.2	.208	5.3	3.3	.58	.31	7.9	1.0	4.6	.07	1.8	0.016	0.4	4.50	MW	CG	N
0.240	6.10	70523S	.44	11.2	.208	5.3	2.8	.49	.24	6.2	.68	3.0	.07	1.8	0.016	0.4	4.50	SST	CG	N
0.240	6.10	70539	.44	11.2	.204	5.2	5.0	.88	.29	7.4	1.5	6.5	.09	2.2	0.018	0.5	4.75	MW	CG	N
0.240	6.10	70539S	.44	11.2	.204	5.2	4.3	.74	.23	5.8	.97	4.3	.09	2.2	0.018	0.5	4.75	SST	CG	N
0.240	6.10	70556	.44	11.2	.200	5.1	6.5	1.1	.31	7.8	2.0	8.9	.11	2.7	0.020	0.5	5.38	MW	CG	N
0.240	6.10	70556S	.44	11.2	.200	5.1	5.5	.97	.24	6.1	1.3	5.9	.11	2.7	0.020	0.5	5.38	SST	CG	N
0.240	6.10	70580	.44	11.2	.196	5.0	9.9	1.7	.27	6.8	2.6	12	.12	2.9	0.022	0.6	5.25	MW	CG	N
0.240	6.10	70580S	.44	11.2	.196	5.0	8.4	1.5	.21	5.3	1.8	7.8	.12	2.9	0.022	0.6	5.25	SST	CG	N
0.240	6.10	70601	.44	11.2	.192	4.9	14	2.5	.24	6.2	3.4	15	.13	3.3	0.024	0.6	5.38	MW	CG	N
0.240	6.10	70601S	.44	11.2	.192	4.9	12	2.1	.19	4.8	2.3	10	.13	3.3	0.024	0.6	5.38	SST	CG	N
0.240	6.10	70622	.44	11.2	.188	4.8	20	3.5	.20	5.2	4.1	18	.14	3.5	0.026	0.7	5.38	MW	CG	N
0.240	6.10	70622S	.44	11.2	.188	4.8	17	3.0	.16	4.1	2.7	12	.14	3.5	0.026	0.7	5.38	SST	CG	N
0.240	6.10	70644	.44	11.2	.182	4.6	27	4.8	.21	5.2	5.6	25	.17	4.4	0.029	0.7	6.00	MW	CG	N
0.240	6.10	70644S	.44	11.2	.182	4.6	23	4.1	.16	4.1	3.8	17	.17	4.4	0.029	0.7	6.00	SST	CG	N
0.240	6.10	70662	.44	11.2	.176	4.5	43	7.5	.17	4.4	7.5	33	.19	4.8	0.032	0.8	5.88	MW	CG	N
0.240	6.10	70662S	.44	11.2	.176	4.5	37	6.4	.14	3.5	5.0	22	.19	4.8	0.032	0.8	5.88	SST	CG	N
0.240	6.10	70681	.44	11.2	.170	4.3	59	10	.16	4.0	9.2	41	.22	5.6	0.035	0.9	6.25	MW	CG	N
0.240	6.10	70681S	.44	11.2	.170	4.3	50	8.7	.13	3.2	6.3	28	.22	5.6	0.035	0.9	6.25	SST	CG	N
0.240	6.10	70702	.44	11.2	.164	4.2	84	15	.14	3.5	12	52	.24	6.2	0.038	1.0	6.38	MW	CG	N
0.240	6.10	70702S	.44	11.2	.164	4.2	72	13	.11	2.8	7.9	35	.24	6.2	0.038	1.0	6.38	SST	CG	N
0.240	6.10	70722	.44	11.2	.160	4.1	100	17	.14	3.5	14	60	.27	6.7	0.040	1.0	6.63	MW	CG	N
0.240	6.10	70722S	.44	11.2	.160	4.1	85	15	.11	2.8	9.2	41	.27	6.7	0.040	1.0	6.63	SST	CG	N
0.240	6.10	70743	.44	11.2	.156	4.0	123	22	.13	3.2	16	70	.28	7.1	0.042	1.1	6.63	MW	CG	N
0.240	6.10	70743S	.44	11.2	.156	4.0	105	18	.10	2.6	11	47	.28	7.1	0.042	1.1	6.63	SST	CG	N
0.240	6.10	70762	.44	11.2	.150	3.8	176	31	.11	2.8	19	85	.29	7.4	0.045	1.1	6.50	MW	CG	N
0.240	6.10	70762S	.44	11.2	.150	3.8	149	26	.09	2.2	13	57	.29	7.4	0.045	1.1	6.50	SST	CG	N
0.240	6.10	70524	.50	12.7	.208	5.3	2.9	.51	.36	9.0	1.0	4.6	.08	2.0	0.016	0.4	4.88	MW	CG	N
0.240	6.10	70524S	.50	12.7	.208	5.3	2.5	.43	.28	7.1	.68	3.0	.08	2.0	0.016	0.4	4.88	SST	CG	N
0.240	6.10	70540	.50	12.7	.204	5.2	4.4	.76	.34	8.5	1.5	6.5	.09	2.3	0.018	0.5	5.13	MW	CG	N
0.240	6.10	70540S	.50	12.7	.204	5.2	3.7	.65	.26	6.7	.97	4.3	.09	2.3	0.018	0.5	5.13	SST	CG	N
0.240	6.10	70557	.50	12.7	.200	5.1	5.7	.99	.35	9.0	2.0	8.9	.12	3.0	0.020	0.5	5.88	MW	CG	N
0.240	6.10	70557S	.50	12.7	.200	5.1	4.8	.84	.28	7.0	1.3	5.9	.12	3.0	0.020	0.5	5.88	SST	CG	N
0.240	6.10	70581	.50	12.7	.196	5.0	8.8	1.5	.30	7.7	2.6	12	.13	3.2	0.022	0.6	5.75	MW	CG	N
0.240	6.10	70581S	.50	12.7	.196	5.0	7.4	1.3	.24	6.0	1.8	7.8	.13	3.2	0.022	0.6	5.75	SST	CG	N
0.240	6.10	70602	.50	12.7	.192	4.9	12	2.1	.28	7.2	3.4	15	.14	3.6	0.024	0.6	5.88	MW	CG	N
0.240	6.10	70602S	.50	12.7	.192	4.9	10	1.8	.22	5.6	2.3	10	.14	3.6	0.024	0.6	5.88	SST	CG	N
0.240	6.10	70623	.50	12.7	.188	4.8	17	3.0	.24	6.0	4.1	18	.15	3.9	0.026	0.7	5.88	MW	CG	N
0.240	6.10	70623S	.50	12.7	.188	4.8	15	2.6	.19	4.7	2.7	12	.15	3.9	0.026	0.7	5.88	SST	CG	N
0.240	6.10	70645	.50	12.7	.182	4.6	24	4.1	.24	6.1	5.6	25	.19	4.9	0.029	0.7	6.63	MW	CG	N
0.240	6.10	70645S	.50	12.7	.182	4.6	20	3.5	.19	4.8	3.8	17	.19	4.9	0.029	0.7	6.63	SST	CG	N
0.240	6.10	12730	.50	12.7	.176	4.5	31	5.4	.16	4.2	5.0	22	.22	5.5	0.032	0.8	6.75	MW	CG	N
0.240	6.10	70663	.50	12.7	.176	4.5	36	6.4	.21	5.2	7.5	33	.21	5.4	0.032	0.8	6.63	MW	CG	N
0.240	6.10	70663S	.50	12.7	.176	4.5	31	5.4	.16	4.1	5.0	22	.21	5.4	0.032	0.8	6.63	SST	CG	N
0.240	6.10	70682	.50	12.7	.170	4.3	50	8.8	.18	4.7	9.2	41	.25	6.2	0.035	0.9	7.00	MW	CG	N
0.240	6.10	70682S	.50	12.7	.170	4.3	43	7.5	.15	3.7	6.3	28	.25	6.2	0.035	0.9	7.00	SST	CG	N
0.240	6.10	70703	.50	12.7	.164	4.2	72	13	.16	4.1	12	52	.27	6.8	0.038	1.0	7.00	MW	CG	N
0.240	6.10	70703S	.50	12.7	.164	4.2	61	11	.13	3.3	7.9	35	.27	6.8	0.038	1.0	7.00	SST	CG	N
0.240	6.10	70723	.50	12.7	.160	4.1	85	15	.16	4.1	14	60	.30	7.5	0.040	1.0	7.38	MW	CG	N
0.240	6.10	70723S	.50	12.7	.160	4.1	72	13	.13	3.2	9.2	41	.30	7.5	0.040	1.0	7.38	SST	CG	N
0.240	6.10	70744	.50	12.7	.156	4.0	106	19	.15	3.7	16	70	.31	7.9	0.042	1.1	7.38	MW	CG	N
0.240	6.10	70744S	.50	12.7	.156	4.0	90	16	.12	3.0	11	47	.31	7.9	0.042	1.1	7.38	SST	CG	N
0.240	6.10	70763	.50	12.7	.150	3.8	149	26	.13	3.2	19	85	.33	8.4	0.045	1.1	7.38	MW	CG	N
0.240	6.10	70763S	.50	12.7	.150	3.8	127	22	.10	2.6	13	57	.33	8.4	0.045	1.1	7.38	SST	CG	N
0.240	6.10	70525	.56	14.2	.208	5.3	2.5	.44	.41	10	1.0	4.6	.09	2.2	0.016	0.4	5.38	MW	CG	N
0.240	6.10	70525S	.56	14.2	.208	5.3	2.1	.37	.32	8.2	.68	3.0	.09	2.2	0.016	0.4	5.38	SST	CG	N
0.240	6.10	70541	.56	14.2	.204	5.2	3.9	.67	.38	9.6	1.5	6.5	.10	2.6	0.018	0.5	5.63	MW	CG	N
0.240	6.10	70541S	.56	14.2	.204	5.2	3.3	.57	.30	7.5	.97	4.3	.10	2.6	0.018	0.5	5.63	SST	CG	N
0.240	6.10	70558	.56	14.2	.200	5.1	5.1	.88	.39	10	2.0	8.9	.13	3.2	0.020	0.5	6.25	MW	CG	N
0.240	6.10	70558S	.56	14.2	.200	5.1	4.3	.75	.31	7.8	1.3	5.9	.13	3.2	0.020	0.5	6.25	SST	CG	N
0.240	6.10	70582	.56	14.2	.196	5.0	7.8	1.4	.34	8.7	2.6	12	.14	3.5	0.022	0.6	6.25	MW	CG	N
0.240	6.10	70582S	.56	14.2	.196	5.0	6.6	1.2	.27	6.8	1.8	7.8	.14	3.5	0.022	0.6	6.25	SST	CG	N
0.240	6.10	70603	.56	14.2	.192	4.9	11	1.9	.32	8.1	3.4	15	.15	3.9	0.024	0.6	6.38	MW	CG	N
0.240	6.10	70603S	.56	14.2	.192	4.9	9.1	1.6	.25	6.3	2.3	10	.15	3.9	0.024	0.6	6.38	SST	CG	N
0.240	6.10	70624	.56	14.2	.188	4.8	14	2.5	.28	7.2	4.1	18	.17	4.4	0.026	0.7	6.63	MW	CG	N
0.240	6.10	70624S	.56	14.2	.188	4.8	12	2.1	.22	5.7	2.7	12	.17	4.4	0.026	0.7	6.63	SST	CG	N
0.240	6.10	70646	.56	14.2	.182	4.6	21	3.6	.27	6.9	5.6	25	.21	5.3	0.029	0.7	7.25	MW	CG	N
0.240	6.10	70646S	.56	14.2	.182	4.6	18	3.1	.21	5.5	3.8	17	.21	5.3	0.029	0.7	7.25	SST	CG	N
0.240	6.10	70																		




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	B3-61	.59	15.1	.150	3.8	159	28	.12	3.0	19	85	.32	8.0	0.045	1.1	7.00	MW	CG	N
0.240	6.10	70526	.63	16.0	.208	5.3	2.3	.40	.45	11	1.0	4.6	.09	2.3	0.016	0.4	5.63	MW	CG	N
0.240	6.10	70526S	.63	16.0	.208	5.3	2.0	.34	.35	8.9	.68	3.0	.09	2.3	0.016	0.4	5.63	SST	CG	N
0.240	6.10	70542	.63	16.0	.204	5.2	3.5	.60	.42	11	1.5	6.5	.11	2.7	0.018	0.5	6.00	MW	CG	N
0.240	6.10	70542S	.63	16.0	.204	5.2	2.9	.51	.33	8.4	.97	4.3	.11	2.7	0.018	0.5	6.00	SST	CG	N
0.240	6.10	70560	.63	16.0	.200	5.1	5.1	.89	.39	9.9	2.0	8.9	.13	3.2	0.020	0.5	6.25	MW	CG	N
0.240	6.10	70560S	.63	16.0	.200	5.1	4.3	.76	.31	7.8	1.3	5.9	.13	3.2	0.020	0.5	6.25	SST	CG	N
0.240	6.10	70561	.63	16.0	.200	5.1	3.3	.58	.46	12	1.5	6.8	.17	4.3	0.020	0.5	8.50	MW	CG	N
0.240	6.10	70561S	.63	16.0	.200	5.1	2.8	.49	.46	12	1.3	5.7	.17	4.3	0.020	0.5	8.50	SST	CG	N
0.240	6.10	70583	.63	16.0	.196	5.0	6.9	1.2	.38	9.7	2.6	12	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.240	6.10	70583S	.63	16.0	.196	5.0	5.9	1.0	.30	7.6	1.8	7.8	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.240	6.10	70604	.63	16.0	.192	4.9	9.6	1.7	.36	9.1	3.4	15	.17	4.3	0.024	0.6	7.00	MW	CG	N
0.240	6.10	70604S	.63	16.0	.192	4.9	8.1	1.4	.28	7.1	2.3	10	.17	4.3	0.024	0.6	7.00	SST	CG	N
0.240	6.10	70625	.63	16.0	.188	4.8	13	2.2	.32	8.2	4.1	18	.19	4.9	0.026	0.7	7.38	MW	CG	N
0.240	6.10	70625S	.63	16.0	.188	4.8	11	1.9	.25	6.5	2.7	12	.19	4.9	0.026	0.7	7.38	SST	CG	N
0.240	6.10	70647	.63	16.0	.182	4.6	18	3.2	.30	7.7	5.6	25	.23	5.8	0.029	0.7	7.88	MW	CG	N
0.240	6.10	70647S	.63	16.0	.182	4.6	16	2.7	.24	6.1	3.8	17	.23	5.8	0.029	0.7	7.88	SST	CG	N
0.240	6.10	70665	.63	16.0	.176	4.5	28	4.9	.27	6.8	7.5	33	.26	6.5	0.032	0.8	8.00	MW	CG	N
0.240	6.10	70665S	.63	16.0	.176	4.5	24	4.2	.21	5.3	5.0	22	.26	6.5	0.032	0.8	8.00	SST	CG	N
0.240	6.10	70684	.63	16.0	.170	4.3	39	6.8	.24	6.0	9.2	41	.29	7.4	0.035	0.9	8.38	MW	CG	N
0.240	6.10	70684S	.63	16.0	.170	4.3	33	5.8	.19	4.8	6.3	28	.29	7.4	0.035	0.9	8.38	SST	CG	N
0.240	6.10	70705	.63	16.0	.164	4.2	57	9.9	.21	5.3	12	52	.32	8.1	0.038	1.0	8.38	MW	CG	N
0.240	6.10	70705S	.63	16.0	.164	4.2	48	8.4	.16	4.2	7.9	35	.32	8.1	0.038	1.0	8.38	SST	CG	N
0.240	6.10	70725	.63	16.0	.160	4.1	67	12	.20	5.2	14	60	.36	9.0	0.040	1.0	8.88	MW	CG	N
0.240	6.10	70725S	.63	16.0	.160	4.1	57	9.9	.16	4.1	9.2	41	.36	9.0	0.040	1.0	8.88	SST	CG	N
0.240	6.10	70746	.63	16.0	.156	4.0	85	15	.18	4.7	16	70	.37	9.3	0.042	1.1	8.75	MW	CG	N
0.240	6.10	70746S	.63	16.0	.156	4.0	72	13	.15	3.7	11	47	.37	9.3	0.042	1.1	8.75	SST	CG	N
0.240	6.10	70765	.63	16.0	.150	3.8	115	20	.17	4.2	19	85	.40	10.1	0.045	1.1	8.88	MW	CG	N
0.240	6.10	70765S	.63	16.0	.150	3.8	98	17	.13	3.3	13	57	.40	10.1	0.045	1.1	8.88	SST	CG	N
0.240	6.10	70527	.69	17.5	.208	5.3	2.0	.35	.51	13	1.0	4.6	.10	2.5	0.016	0.4	6.25	MW	CG	N
0.240	6.10	70527S	.69	17.5	.208	5.3	1.7	.30	.40	10	.68	3.0	.10	2.5	0.016	0.4	6.25	SST	CG	N
0.240	6.10	70543	.69	17.5	.204	5.2	3.1	.54	.47	12	1.5	6.5	.12	3.0	0.018	0.5	6.50	MW	CG	N
0.240	6.10	70543S	.69	17.5	.204	5.2	2.6	.46	.37	9.4	.97	4.3	.12	3.0	0.018	0.5	6.50	SST	CG	N
0.240	6.10	70562	.69	17.5	.200	5.1	4.1	.71	.49	13	2.0	8.9	.15	3.7	0.020	0.5	7.38	MW	CG	N
0.240	6.10	70562S	.69	17.5	.200	5.1	3.4	.60	.39	9.8	1.3	5.9	.15	3.7	0.020	0.5	7.38	SST	CG	N
0.240	6.10	70584	.69	17.5	.196	5.0	6.1	1.1	.43	11	2.6	12	.16	4.1	0.022	0.6	7.38	MW	CG	N
0.240	6.10	70584S	.69	17.5	.196	5.0	5.2	.91	.34	8.6	1.8	7.8	.16	4.1	0.022	0.6	7.38	SST	CG	N
0.240	6.10	70605	.69	17.5	.192	4.9	8.7	1.5	.39	10	3.4	15	.18	4.6	0.024	0.6	7.50	MW	CG	N
0.240	6.10	70605S	.69	17.5	.192	4.9	7.4	1.3	.31	7.8	2.3	10	.18	4.6	0.024	0.6	7.50	SST	CG	N
0.240	6.10	70626	.69	17.5	.188	4.8	11	1.9	.37	9.4	4.1	18	.21	5.4	0.026	0.7	8.13	MW	CG	N
0.240	6.10	70626S	.69	17.5	.188	4.8	9.4	1.6	.29	7.4	2.7	12	.21	5.4	0.026	0.7	8.13	SST	CG	N
0.240	6.10	70648	.69	17.5	.182	4.6	17	2.9	.34	8.6	5.6	25	.25	6.3	0.029	0.7	8.50	MW	CG	N
0.240	6.10	70648S	.69	17.5	.182	4.6	14	2.5	.27	6.8	3.8	17	.25	6.3	0.029	0.7	8.50	SST	CG	N
0.240	6.10	70666	.69	17.5	.176	4.5	25	4.4	.30	7.6	7.5	33	.28	7.1	0.032	0.8	8.75	MW	CG	N
0.240	6.10	70666S	.69	17.5	.176	4.5	21	3.7	.24	6.0	5.0	22	.28	7.1	0.032	0.8	8.75	SST	CG	N
0.240	6.10	70685	.69	17.5	.170	4.3	35	6.1	.27	6.7	9.2	41	.32	8.2	0.035	0.9	9.25	MW	CG	N
0.240	6.10	70685S	.69	17.5	.170	4.3	30	5.2	.21	5.4	6.3	28	.32	8.2	0.035	0.9	9.25	SST	CG	N
0.240	6.10	70706	.69	17.5	.164	4.2	51	8.9	.23	5.9	12	52	.35	8.8	0.038	1.0	9.13	MW	CG	N
0.240	6.10	70706S	.69	17.5	.164	4.2	43	7.6	.18	4.7	7.9	35	.35	8.8	0.038	1.0	9.13	SST	CG	N
0.240	6.10	70726	.69	17.5	.160	4.1	59	10	.23	5.8	14	60	.39	9.9	0.040	1.0	9.75	MW	CG	N
0.240	6.10	70726S	.69	17.5	.160	4.1	50	8.8	.18	4.6	9.2	41	.39	9.9	0.040	1.0	9.75	SST	CG	N
0.240	6.10	70747	.69	17.5	.156	4.0	75	13	.21	5.3	16	70	.40	10.3	0.042	1.1	9.63	MW	CG	N
0.240	6.10	70747S	.69	17.5	.156	4.0	64	11	.17	4.2	11	47	.40	10.3	0.042	1.1	9.63	SST	CG	N
0.240	6.10	70766	.69	17.5	.150	3.8	102	18	.19	4.7	19	85	.44	11.1	0.045	1.1	9.75	MW	CG	N
0.240	6.10	70766S	.69	17.5	.150	3.8	87	15	.15	3.8	13	57	.44	11.1	0.045	1.1	9.75	SST	CG	N
0.240	6.10	70528	.75	19.1	.208	5.3	1.9	.33	.54	14	1.0	4.6	.10	2.6	0.016	0.4	6.38	MW	CG	N
0.240	6.10	70528S	.75	19.1	.208	5.3	1.6	.28	.42	11	.68	3.0	.10	2.6	0.016	0.4	6.38	SST	CG	N
0.240	6.10	70544	.75	19.1	.204	5.2	2.8	.49	.52	13	1.5	6.5	.12	3.1	0.018	0.5	6.88	MW	CG	N
0.240	6.10	70544S	.75	19.1	.204	5.2	2.4	.42	.41	10	.97	4.3	.12	3.1	0.018	0.5	6.88	SST	CG	N
0.240	6.10	70563	.75	19.1	.200	5.1	3.7	.65	.54	14	2.0	8.9	.16	4.0	0.020	0.5	7.88	MW	CG	N
0.240	6.10	70563S	.75	19.1	.200	5.1	3.1	.55	.42	11	1.3	5.9	.16	4.0	0.020	0.5	7.88	SST	CG	N
0.240	6.10	70585	.75	19.1	.196	5.0	5.6	.97	.48	12	2.6	12	.17	4.4	0.022	0.6	7.88	MW	CG	N
0.240	6.10	70585S	.75	19.1	.196	5.0	4.7	.83	.37	9.5	1.8	7.8	.17	4.4	0.022	0.6	7.88	SST	CG	N
0.240	6.10	B4-35	.75	19.1	.196	5.0	4.7	.82	.37	9.5	1.8	7.8	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.240	6.10	70606	.75	19.1	.192	4.9	7.8	1.4	.44	11	3.4	15	.20	5.0	0.024	0.6	8.13	MW	CG	N
0.240	6.10	70606S	.75	19.1	.192	4.9	6.6	1.2	.34	8.7	2.3	10	.20	5.0	0.024	0.6	8.13	SST	CG	N
0.240	6.10	70627	.75	19.1	.188	4.8	10	1.8	.41	10	4.1	18	.23	5.8	0.026	0.7	8.75	MW	CG	N
0.240	6.10	70627S	.75	19.1	.188	4.8	8.5	1.5	.32	8.2	2.7	12	.23	5.8	0.026	0.7	8.75	SST	CG	N
0.240	6.10	70649	.75	19.1	.182	4.6	15	2.7	.37	9.3	5.6	25	.26	6.7	0.029	0				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70767	.75	19.1	.150	3.8	93	16	.21	5.2	19	85	.48	12.1	0.045	1.1	10.6	MW	CG	N
0.240	6.10	70767S	.75	19.1	.150	3.8	79	14	.16	4.1	13	57	.48	12.1	0.045	1.1	10.6	SST	CG	N
0.240	6.10	70529	.81	20.6	.208	5.3	1.7	.30	.61	15	1.0	4.6	.11	2.8	0.016	0.4	6.88	MW	CG	N
0.240	6.10	70529S	.81	20.6	.208	5.3	1.4	.25	.47	12	.68	3.0	.11	2.8	0.016	0.4	6.88	SST	CG	N
0.240	6.10	70545	.81	20.6	.204	5.2	2.6	.46	.56	14	1.5	6.5	.13	3.3	0.018	0.5	7.25	MW	CG	N
0.240	6.10	70545S	.81	20.6	.204	5.2	2.2	.39	.44	11	.97	4.3	.13	3.3	0.018	0.5	7.25	SST	CG	N
0.240	6.10	70564	.81	20.6	.200	5.1	3.4	.59	.60	15	2.0	8.9	.17	4.3	0.020	0.5	8.50	MW	CG	N
0.240	6.10	70564S	.81	20.6	.200	5.1	2.8	.50	.47	12	1.3	5.9	.17	4.3	0.020	0.5	8.50	SST	CG	N
0.240	6.10	70586	.81	20.6	.196	5.0	5.1	.89	.52	13	2.6	12	.18	4.7	0.022	0.6	8.38	MW	CG	N
0.240	6.10	70586S	.81	20.6	.196	5.0	4.3	.76	.41	10	1.8	7.8	.18	4.7	0.022	0.6	8.38	SST	CG	N
0.240	6.10	70607	.81	20.6	.192	4.9	7.2	1.3	.48	12	3.4	15	.21	5.3	0.024	0.6	8.63	MW	CG	N
0.240	6.10	70607S	.81	20.6	.192	4.9	6.1	1.1	.37	9.5	2.3	10	.21	5.3	0.024	0.6	8.63	SST	CG	N
0.240	6.10	70628	.81	20.6	.188	4.8	9.2	1.6	.45	11	4.1	18	.24	6.2	0.026	0.7	9.38	MW	CG	N
0.240	6.10	70628S	.81	20.6	.188	4.8	7.8	1.4	.35	8.9	2.7	12	.24	6.2	0.026	0.7	9.38	SST	CG	N
0.240	6.10	70650	.81	20.6	.182	4.6	14	2.4	.41	10	5.6	25	.29	7.3	0.029	0.7	9.88	MW	CG	N
0.240	6.10	70650S	.81	20.6	.182	4.6	12	2.1	.32	8.1	3.8	17	.29	7.3	0.029	0.7	9.88	SST	CG	N
0.240	6.10	70668	.81	20.6	.176	4.5	20	3.5	.37	9.5	7.5	33	.33	8.4	0.032	0.8	10.4	MW	CG	N
0.240	6.10	70668S	.81	20.6	.176	4.5	17	3.0	.29	7.5	5.0	22	.33	8.4	0.032	0.8	10.4	SST	CG	N
0.240	6.10	70687	.81	20.6	.170	4.3	29	5.0	.32	8.2	9.2	41	.38	9.6	0.035	0.9	10.8	MW	CG	N
0.240	6.10	70687S	.81	20.6	.170	4.3	24	4.3	.26	6.5	6.3	28	.38	9.6	0.035	0.9	10.8	SST	CG	N
0.240	6.10	70708	.81	20.6	.164	4.2	42	7.4	.28	7.1	12	52	.40	10.3	0.038	1.0	10.6	MW	CG	N
0.240	6.10	70708S	.81	20.6	.164	4.2	36	6.3	.22	5.6	7.9	35	.40	10.3	0.038	1.0	10.6	SST	CG	N
0.240	6.10	70728	.81	20.6	.160	4.1	49	8.5	.28	7.1	14	60	.46	11.6	0.040	1.0	11.4	MW	CG	N
0.240	6.10	70728S	.81	20.6	.160	4.1	41	7.3	.22	5.6	9.2	41	.46	11.6	0.040	1.0	11.4	SST	CG	N
0.240	6.10	70749	.81	20.6	.156	4.0	60	11	.26	6.6	16	70	.49	12.4	0.042	1.1	11.6	MW	CG	N
0.240	6.10	70749S	.81	20.6	.156	4.0	51	8.9	.21	5.3	11	47	.49	12.4	0.042	1.1	11.6	SST	CG	N
0.240	6.10	70768	.81	20.6	.150	3.8	85	15	.22	5.7	19	85	.51	13.0	0.045	1.1	11.4	MW	CG	N
0.240	6.10	70768S	.81	20.6	.150	3.8	72	13	.18	4.5	13	57	.51	13.0	0.045	1.1	11.4	SST	CG	N
0.240	6.10	70530	.88	22.4	.208	5.3	1.6	.28	.64	16	1.0	4.6	.12	2.9	0.016	0.4	7.25	MW	CG	N
0.240	6.10	70530S	.88	22.4	.208	5.3	1.4	.24	.50	13	.68	3.0	.12	2.9	0.016	0.4	7.25	SST	CG	N
0.240	6.10	70546	.88	22.4	.204	5.2	2.4	.42	.61	15	1.5	6.5	.14	3.5	0.018	0.5	7.75	MW	CG	N
0.240	6.10	70546S	.88	22.4	.204	5.2	2.0	.36	.48	12	.97	4.3	.14	3.5	0.018	0.5	7.75	SST	CG	N
0.240	6.10	70565	.88	22.4	.200	5.1	3.1	.54	.64	16	2.0	8.9	.18	4.6	0.020	0.5	9.00	MW	CG	N
0.240	6.10	70565S	.88	22.4	.200	5.1	2.6	.46	.50	13	1.3	5.9	.18	4.6	0.020	0.5	9.00	SST	CG	N
0.240	6.10	70588	.88	22.4	.196	5.0	4.7	.82	.56	14	2.6	12	.20	5.0	0.022	0.6	8.88	MW	CG	N
0.240	6.10	70588S	.88	22.4	.196	5.0	4.0	.70	.44	11	1.8	7.8	.20	5.0	0.022	0.6	8.88	SST	CG	N
0.240	6.10	70608	.88	22.4	.192	4.9	6.5	1.1	.53	13	3.4	15	.22	5.6	0.024	0.6	9.25	MW	CG	N
0.240	6.10	70608S	.88	22.4	.192	4.9	5.5	.97	.41	10	2.3	10	.22	5.6	0.024	0.6	9.25	SST	CG	N
0.240	6.10	70629	.88	22.4	.188	4.8	8.2	1.4	.50	13	4.1	18	.26	6.7	0.026	0.7	10.1	MW	CG	N
0.240	6.10	70629S	.88	22.4	.188	4.8	7.0	1.2	.39	9.9	2.7	12	.26	6.7	0.026	0.7	10.1	SST	CG	N
0.240	6.10	70651	.88	22.4	.182	4.6	13	2.2	.44	11	5.6	25	.30	7.7	0.029	0.7	10.5	MW	CG	N
0.240	6.10	70651S	.88	22.4	.182	4.6	11	1.9	.35	8.8	3.8	17	.30	7.7	0.029	0.7	10.5	SST	CG	N
0.240	6.10	70669	.88	22.4	.176	4.5	19	3.3	.40	10	7.5	33	.35	8.9	0.032	0.8	11.0	MW	CG	N
0.240	6.10	70669S	.88	22.4	.176	4.5	16	2.8	.32	8.0	5.0	22	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.240	6.10	70688	.88	22.4	.170	4.3	26	4.6	.35	8.9	9.2	41	.40	10.2	0.035	0.9	11.5	MW	CG	N
0.240	6.10	70688S	.88	22.4	.170	4.3	22	3.9	.28	7.1	6.3	28	.40	10.2	0.035	0.9	11.5	SST	CG	N
0.240	6.10	70709	.88	22.4	.164	4.2	38	6.7	.31	7.8	12	52	.44	11.2	0.038	1.0	11.6	MW	CG	N
0.240	6.10	70709S	.88	22.4	.164	4.2	32	5.7	.25	6.2	7.9	35	.44	11.2	0.038	1.0	11.6	SST	CG	N
0.240	6.10	70729	.88	22.4	.160	4.1	45	8.0	.30	7.6	14	60	.49	12.3	0.040	1.0	12.1	MW	CG	N
0.240	6.10	70729S	.88	22.4	.160	4.1	39	6.8	.24	6.1	9.2	41	.49	12.3	0.040	1.0	12.1	SST	CG	N
0.240	6.10	70750	.88	22.4	.156	4.0	56	9.8	.28	7.1	16	70	.51	13.1	0.042	1.1	12.3	MW	CG	N
0.240	6.10	70750S	.88	22.4	.156	4.0	48	8.3	.22	5.6	11	47	.51	13.1	0.042	1.1	12.3	SST	CG	N
0.240	6.10	70769	.88	22.4	.150	3.8	78	14	.24	6.2	19	85	.55	14.0	0.045	1.1	12.3	MW	CG	N
0.240	6.10	70769S	.88	22.4	.150	3.8	66	12	.19	4.9	13	57	.55	14.0	0.045	1.1	12.3	SST	CG	N
0.240	6.10	70547	.94	23.9	.204	5.2	2.2	.39	.66	17	1.5	6.5	.15	3.8	0.018	0.5	8.25	MW	CG	N
0.240	6.10	70547S	.94	23.9	.204	5.2	1.9	.33	.52	13	.97	4.3	.15	3.8	0.018	0.5	8.25	SST	CG	N
0.240	6.10	70567	.94	23.9	.200	5.1	3.2	.56	.62	16	2.0	8.9	.18	4.4	0.020	0.5	8.75	MW	CG	N
0.240	6.10	70567S	.94	23.9	.200	5.1	2.7	.48	.49	12	1.3	5.9	.18	4.4	0.020	0.5	8.75	SST	CG	N
0.240	6.10	70590	.94	23.9	.196	5.0	4.4	.77	.60	15	2.6	12	.21	5.2	0.022	0.6	9.38	MW	CG	N
0.240	6.10	70590S	.94	23.9	.196	5.0	3.7	.65	.47	12	1.8	7.8	.21	5.2	0.022	0.6	9.38	SST	CG	N
0.240	6.10	70610	.94	23.9	.192	4.9	5.9	1.0	.58	15	3.4	15	.24	6.1	0.024	0.6	10.0	MW	CG	N
0.240	6.10	70610S	.94	23.9	.192	4.9	5.0	.88	.45	12	2.3	10	.24	6.1	0.024	0.6	10.0	SST	CG	N
0.240	6.10	70631	.94	23.9	.188	4.8	7.8	1.4	.52	13	4.1	18	.28	7.0	0.026	0.7	10.6	MW	CG	N
0.240	6.10	70631S	.94	23.9	.188	4.8	6.6	1.2	.41	10	2.7	12	.28	7.0	0.026	0.7	10.6	SST	CG	N
0.240	6.10	70652	.94	23.9	.182	4.6	12	2.0	.48	12	5.6	25	.33	8.3	0.029	0.7	11.3	MW	CG	N
0.240	6.10	70652S	.94	23.9	.182	4.6	9.9	1.7	.38	9.6	3.8	17	.33	8.3	0.029	0.7	11.3	SST	CG	N
0.240	6.10	70670	.94	23.9	.176	4.5	17	3.0	.43	11	7.5	33	.37	9.4	0.032	0.8	11.6	MW	CG	N
0.240	6.10	70670S	.94	23.9	.176	4.5	15	2.6	.34	8.7	5.0	22	.37	9.4	0.032	0.8	11.6	SST	CG	N
0.240	6.10	70689	.94																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70548	1.00	25.4	.204	5.2	2.1	.37	.70	18	1.5	6.5	.16	3.9	0.018	0.5	8.63	MW	CG	N
0.240	6.10	70548S	1.00	25.4	.204	5.2	1.8	.31	.54	14	.97	4.3	.16	3.9	0.018	0.5	8.63	SST	CG	N
0.240	6.10	70568	1.00	25.4	.200	5.1	2.8	.48	.73	18	2.0	8.9	.20	5.0	0.020	0.5	9.88	MW	CG	N
0.240	6.10	70568S	1.00	25.4	.200	5.1	2.3	.41	.57	14	1.3	5.9	.20	5.0	0.020	0.5	9.88	SST	CG	N
0.240	6.10	70591	1.00	25.4	.196	5.0	4.2	.74	.63	16	2.6	12	.21	5.4	0.022	0.6	9.75	MW	CG	N
0.240	6.10	70591S	1.00	25.4	.196	5.0	3.6	.63	.49	12	1.8	7.8	.21	5.4	0.022	0.6	9.75	SST	CG	N
0.240	6.10	70611	1.00	25.4	.192	4.9	5.8	1.0	.59	15	3.4	15	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.240	6.10	70611S	1.00	25.4	.192	4.9	4.9	.86	.46	12	2.3	10	.25	6.2	0.024	0.6	10.3	SST	CG	N
0.240	6.10	70632	1.00	25.4	.188	4.8	7.4	1.3	.55	14	4.1	18	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.240	6.10	70632S	1.00	25.4	.188	4.8	6.3	1.1	.43	11	2.7	12	.29	7.3	0.026	0.7	11.0	SST	CG	N
0.240	6.10	70653	1.00	25.4	.182	4.6	11	2.0	.50	13	5.6	25	.34	8.7	0.029	0.7	11.8	MW	CG	N
0.240	6.10	70653S	1.00	25.4	.182	4.6	9.5	1.7	.40	10	3.8	17	.34	8.7	0.029	0.7	11.8	SST	CG	N
0.240	6.10	70671	1.00	25.4	.176	4.5	16	2.8	.47	12	7.5	33	.40	10.2	0.032	0.8	12.5	MW	CG	N
0.240	6.10	70671S	1.00	25.4	.176	4.5	14	2.4	.37	9.4	5.0	22	.40	10.2	0.032	0.8	12.5	SST	CG	N
0.240	6.10	70690	1.00	25.4	.170	4.3	23	4.0	.41	10	9.2	41	.46	11.6	0.035	0.9	13.0	MW	CG	N
0.240	6.10	70690S	1.00	25.4	.170	4.3	19	3.4	.32	8.2	6.3	28	.46	11.6	0.035	0.9	13.0	SST	CG	N
0.240	6.10	70711	1.00	25.4	.164	4.2	33	5.7	.36	9.1	12	52	.50	12.7	0.038	1.0	13.1	MW	CG	N
0.240	6.10	70711S	1.00	25.4	.164	4.2	28	4.9	.29	7.3	7.9	35	.50	12.7	0.038	1.0	13.1	SST	CG	N
0.240	6.10	70731	1.00	25.4	.160	4.1	39	6.9	.35	8.8	14	60	.55	14.0	0.040	1.0	13.8	MW	CG	N
0.240	6.10	70731S	1.00	25.4	.160	4.1	33	5.8	.28	7.0	9.2	41	.55	14.0	0.040	1.0	13.8	SST	CG	N
0.240	6.10	70752	1.00	25.4	.156	4.0	48	8.4	.33	8.3	16	70	.59	14.9	0.042	1.1	14.0	MW	CG	N
0.240	6.10	70752S	1.00	25.4	.156	4.0	41	7.1	.26	6.6	11	47	.59	14.9	0.042	1.1	14.0	SST	CG	N
0.240	6.10	70771	1.00	25.4	.150	3.8	67	12	.28	7.2	19	85	.62	15.7	0.045	1.1	13.8	MW	CG	N
0.240	6.10	70771S	1.00	25.4	.150	3.8	57	10	.22	5.7	13	57	.62	15.7	0.045	1.1	13.8	SST	CG	N
0.240	6.10	70770S	1.13	28.7	.200	5.1	2.7	.47	.74	19	2.0	8.9	.20	5.1	0.020	0.5	10.0	MW	CG	N
0.240	6.10	70593	1.13	28.7	.196	5.0	3.6	.63	.73	19	2.6	12	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.240	6.10	70593S	1.13	28.7	.196	5.0	3.1	.54	.57	15	1.8	7.8	.24	6.1	0.022	0.6	11.0	SST	CG	N
0.240	6.10	70613	1.13	28.7	.192	4.9	4.9	.86	.70	18	3.4	15	.28	7.1	0.024	0.6	11.6	MW	CG	N
0.240	6.10	70613S	1.13	28.7	.192	4.9	4.2	.73	.55	14	2.3	10	.28	7.1	0.024	0.6	11.6	SST	CG	N
0.240	6.10	70634	1.13	28.7	.188	4.8	6.4	1.1	.64	16	4.1	18	.33	8.3	0.026	0.7	12.5	MW	CG	N
0.240	6.10	70634S	1.13	28.7	.188	4.8	5.4	.95	.50	13	2.7	12	.33	8.3	0.026	0.7	12.5	SST	CG	N
0.240	6.10	70654	1.13	28.7	.182	4.6	9.7	1.7	.58	15	5.6	25	.38	9.7	0.029	0.7	13.1	MW	CG	N
0.240	6.10	70654S	1.13	28.7	.182	4.6	8.2	1.4	.46	12	3.8	17	.38	9.7	0.029	0.7	13.1	SST	CG	N
0.240	6.10	70673	1.13	28.7	.176	4.5	14	2.5	.53	14	7.5	33	.45	11.4	0.032	0.8	14.0	MW	CG	N
0.240	6.10	70673S	1.13	28.7	.176	4.5	12	2.1	.42	11	5.0	22	.45	11.4	0.032	0.8	14.0	SST	CG	N
0.240	6.10	70692	1.13	28.7	.170	4.3	20	3.4	.47	12	9.2	41	.52	13.1	0.035	0.9	14.8	MW	CG	N
0.240	6.10	70692S	1.13	28.7	.170	4.3	17	2.9	.38	9.5	6.3	28	.52	13.1	0.035	0.9	14.8	SST	CG	N
0.240	6.10	70712	1.13	28.7	.164	4.2	29	5.1	.41	10	12	52	.56	14.1	0.038	1.0	14.6	MW	CG	N
0.240	6.10	70712S	1.13	28.7	.164	4.2	25	4.3	.32	8.2	7.9	35	.56	14.1	0.038	1.0	14.6	SST	CG	N
0.240	6.10	70732	1.13	28.7	.160	4.1	35	6.1	.39	9.9	14	60	.61	15.5	0.040	1.0	15.3	MW	CG	N
0.240	6.10	70732S	1.13	28.7	.160	4.1	30	5.2	.31	7.9	9.2	41	.61	15.5	0.040	1.0	15.3	SST	CG	N
0.240	6.10	70753	1.13	28.7	.156	4.0	42	7.4	.37	9.4	16	70	.66	16.7	0.042	1.1	15.6	MW	CG	N
0.240	6.10	70753S	1.13	28.7	.156	4.0	36	6.3	.29	7.5	11	47	.66	16.7	0.042	1.1	15.6	SST	CG	N
0.240	6.10	70772	1.13	28.7	.150	3.8	59	10	.32	8.2	19	85	.69	17.6	0.045	1.1	15.4	MW	CG	N
0.240	6.10	70772S	1.13	28.7	.150	3.8	50	8.8	.26	6.5	13	57	.69	17.6	0.045	1.1	15.4	SST	CG	N
0.240	6.10	70532	1.25	31.8	.208	5.3	1.1	.19	.94	24	1.0	4.6	.15	3.9	0.016	0.4	9.63	MW	CG	N
0.240	6.10	70532S	1.25	31.8	.208	5.3	.94	.16	.73	19	.68	3.0	.15	3.9	0.016	0.4	9.63	SST	CG	N
0.240	6.10	70549	1.25	31.8	.204	5.2	1.7	.30	.86	22	1.5	6.5	.18	4.6	0.018	0.5	10.1	MW	CG	N
0.240	6.10	70549S	1.25	31.8	.204	5.2	1.4	.25	.67	17	.97	4.3	.18	4.6	0.018	0.5	10.1	SST	CG	N
0.240	6.10	70571	1.25	31.8	.200	5.1	2.2	.38	.93	24	2.0	8.9	.24	6.1	0.020	0.5	12.0	MW	CG	N
0.240	6.10	70571S	1.25	31.8	.200	5.1	1.8	.32	.73	18	1.3	5.9	.24	6.1	0.020	0.5	12.0	SST	CG	N
0.240	6.10	70594	1.25	31.8	.196	5.0	3.3	.58	.80	20	2.6	12	.26	6.6	0.022	0.6	11.9	MW	CG	N
0.240	6.10	70594S	1.25	31.8	.196	5.0	2.8	.49	.63	16	1.8	7.8	.26	6.6	0.022	0.6	11.9	SST	CG	N
0.240	6.10	70614	1.25	31.8	.192	4.9	4.6	.80	.75	19	3.4	15	.30	7.5	0.024	0.6	12.4	MW	CG	N
0.240	6.10	70614S	1.25	31.8	.192	4.9	3.9	.68	.59	15	2.3	10	.30	7.5	0.024	0.6	12.4	SST	CG	N
0.240	6.10	70635	1.25	31.8	.188	4.8	5.9	1.0	.69	18	4.1	18	.35	8.8	0.026	0.7	13.4	MW	CG	N
0.240	6.10	70635S	1.25	31.8	.188	4.8	5.0	.88	.54	14	2.7	12	.35	8.8	0.026	0.7	13.4	SST	CG	N
0.240	6.10	70655	1.25	31.8	.182	4.6	8.8	1.5	.64	16	5.6	25	.42	10.6	0.029	0.7	14.4	MW	CG	N
0.240	6.10	70655S	1.25	31.8	.182	4.6	7.5	1.3	.50	13	3.8	17	.42	10.6	0.029	0.7	14.4	SST	CG	N
0.240	6.10	70674	1.25	31.8	.176	4.5	13	2.3	.58	15	7.5	33	.48	12.1	0.032	0.8	14.9	MW	CG	N
0.240	6.10	70674S	1.25	31.8	.176	4.5	11	1.9	.45	12	5.0	22	.48	12.1	0.032	0.8	14.9	SST	CG	N
0.240	6.10	70693	1.25	31.8	.170	4.3	18	3.1	.52	13	9.2	41	.56	14.2	0.035	0.9	16.0	MW	CG	N
0.240	6.10	70693S	1.25	31.8	.170	4.3	15	2.7	.41	10	6.3	28	.56	14.2	0.035	0.9	16.0	SST	CG	N
0.240	6.10	70713	1.25	31.8	.164	4.2	26	4.5	.45	11	12	52	.61	15.4	0.038	1.0	16.0	MW	CG	N
0.240	6.10	70713S	1.25	31.8	.164	4.2	22	3.9	.36	9.2	7.9	35	.61	15.4	0.038	1.0	16.0	SST	CG	N
0.240	6.10	70733	1.25	31.8	.160	4.1	31	5.4	.44	11	14	60	.68	17.1	0.040	1.0	16.9	MW	CG	N
0.240	6.10	70733S	1.25	31.8	.160	4.1	26	4.6	.35	8.9	9.2	41	.68	17.1	0.040	1.0	16.9	SST	CG	N
0.240	6.10	70754	1.25	31.8	.156	4.0	38	6.6	.41	11	16	70	.72	18.4	0.042	1.1	17.3	MW	CG	N




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70656	1.38	35.1	.182	4.6	7.8	1.4	.72	18	5.6	25	.46	11.7	0.029	0.7	15.9	MW	CG	N
0.240	6.10	70656S	1.38	35.1	.182	4.6	6.6	1.2	.57	14	3.8	17	.46	11.7	0.029	0.7	15.9	SST	CG	N
0.240	6.10	70675	1.38	35.1	.176	4.5	12	2.0	.65	16	7.5	33	.53	13.4	0.032	0.8	16.5	MW	CG	N
0.240	6.10	70675S	1.38	35.1	.176	4.5	9.9	1.7	.51	13	5.0	22	.53	13.4	0.032	0.8	16.5	SST	CG	N
0.240	6.10	70694	1.38	35.1	.170	4.3	16	2.8	.58	15	9.2	41	.62	15.8	0.035	0.9	17.8	MW	CG	N
0.240	6.10	70694S	1.38	35.1	.170	4.3	14	2.4	.46	12	6.3	28	.62	15.8	0.035	0.9	17.8	SST	CG	N
0.240	6.10	70714	1.38	35.1	.164	4.2	23	4.1	.51	13	12	52	.67	17.0	0.038	1.0	17.6	MW	CG	N
0.240	6.10	70714S	1.38	35.1	.164	4.2	20	3.5	.40	10	7.9	35	.67	17.0	0.038	1.0	17.6	SST	CG	N
0.240	6.10	70734	1.38	35.1	.160	4.1	28	4.8	.49	13	14	60	.75	19.1	0.040	1.0	18.8	MW	CG	N
0.240	6.10	70734S	1.38	35.1	.160	4.1	23	4.1	.39	10	9.2	41	.75	19.1	0.040	1.0	18.8	SST	CG	N
0.240	6.10	70755	1.38	35.1	.156	4.0	34	6.0	.46	12	16	70	.80	20.3	0.042	1.1	19.0	MW	CG	N
0.240	6.10	70755S	1.38	35.1	.156	4.0	29	5.1	.37	9.3	11	47	.80	20.3	0.042	1.1	19.0	SST	CG	N
0.240	6.10	70533	1.50	38.1	.208	5.3	.90	.16	1.1	29	1.0	4.6	.18	4.6	0.016	0.4	11.4	MW	CG	N
0.240	6.10	70533S	1.50	38.1	.208	5.3	.77	.13	.89	23	.68	3.0	.18	4.6	0.016	0.4	11.4	SST	CG	N
0.240	6.10	70550	1.50	38.1	.204	5.2	1.4	.25	1.0	26	1.5	6.5	.21	5.4	0.018	0.5	11.9	MW	CG	N
0.240	6.10	70550S	1.50	38.1	.204	5.2	1.2	.21	.82	21	.97	4.3	.21	5.4	0.018	0.5	11.9	SST	CG	N
0.240	6.10	70574	1.50	38.1	.200	5.1	1.8	.31	1.1	28	2.0	8.9	.28	7.2	0.020	0.5	14.1	MW	CG	N
0.240	6.10	70574S	1.50	38.1	.200	5.1	1.5	.27	.87	22	1.3	5.9	.28	7.2	0.020	0.5	14.1	SST	CG	N
0.240	6.10	70597	1.50	38.1	.196	5.0	2.8	.49	.94	24	2.6	12	.30	7.6	0.022	0.6	13.6	MW	CG	N
0.240	6.10	70597S	1.50	38.1	.196	5.0	2.4	.42	.74	19	1.8	7.8	.30	7.6	0.022	0.6	13.6	SST	CG	N
0.240	6.10	70617	1.50	38.1	.192	4.9	3.7	.65	.92	23	3.4	15	.35	9.0	0.024	0.6	14.8	MW	CG	N
0.240	6.10	70617S	1.50	38.1	.192	4.9	3.2	.55	.72	18	2.3	10	.35	9.0	0.024	0.6	14.8	SST	CG	N
0.240	6.10	70638	1.50	38.1	.188	4.8	4.9	.86	.83	21	4.1	18	.41	10.3	0.026	0.7	15.6	MW	CG	N
0.240	6.10	70638S	1.50	38.1	.188	4.8	4.2	.73	.66	17	2.7	12	.41	10.3	0.026	0.7	15.6	SST	CG	N
0.240	6.10	70657	1.50	38.1	.182	4.6	7.3	1.3	.77	20	5.6	25	.49	12.4	0.029	0.7	16.9	MW	CG	N
0.240	6.10	70657S	1.50	38.1	.182	4.6	6.2	1.1	.61	15	3.8	17	.49	12.4	0.029	0.7	16.9	SST	CG	N
0.240	6.10	70676	1.50	38.1	.176	4.5	11	1.9	.70	18	7.5	33	.57	14.4	0.032	0.8	17.8	MW	CG	N
0.240	6.10	70676S	1.50	38.1	.176	4.5	9.1	1.6	.55	14	5.0	22	.57	14.4	0.032	0.8	17.8	SST	CG	N
0.240	6.10	70695	1.50	38.1	.170	4.3	15	2.6	.63	16	9.2	41	.67	16.9	0.035	0.9	19.0	MW	CG	N
0.240	6.10	70695S	1.50	38.1	.170	4.3	12	2.2	.50	13	6.3	28	.67	16.9	0.035	0.9	19.0	SST	CG	N
0.240	6.10	70715	1.50	38.1	.164	4.2	21	3.7	.55	14	12	52	.73	18.5	0.038	1.0	19.1	MW	CG	N
0.240	6.10	70715S	1.50	38.1	.164	4.2	18	3.2	.44	11	7.9	35	.73	18.5	0.038	1.0	19.1	SST	CG	N
0.240	6.10	70735	1.50	38.1	.160	4.1	25	4.5	.53	14	14	60	.81	20.4	0.040	1.0	20.1	MW	CG	N
0.240	6.10	70735S	1.50	38.1	.160	4.1	22	3.8	.43	11	9.2	41	.81	20.4	0.040	1.0	20.1	SST	CG	N
0.240	6.10	70756	1.50	38.1	.156	4.0	31	5.4	.51	13	16	70	.87	22.1	0.042	1.1	20.8	MW	CG	N
0.240	6.10	70756S	1.50	38.1	.156	4.0	26	4.6	.40	10	11	47	.87	22.1	0.042	1.1	20.8	SST	CG	N
0.240	6.10	70774	1.50	38.1	.150	3.8	43	7.6	.44	11	19	85	.91	23.1	0.045	1.1	20.3	MW	CG	N
0.240	6.10	70774S	1.50	38.1	.150	3.8	37	6.5	.35	8.9	13	57	.91	23.1	0.045	1.1	20.3	SST	CG	N
0.240	6.10	70534	1.75	44.5	.208	5.3	.80	.14	1.3	33	1.0	4.6	.20	5.1	0.016	0.4	12.5	MW	CG	N
0.240	6.10	70534S	1.75	44.5	.208	5.3	.68	.12	1.0	26	.68	3.0	.20	5.1	0.016	0.4	12.5	SST	CG	N
0.240	6.10	70551	1.75	44.5	.204	5.2	1.2	.21	1.2	31	1.5	6.5	.24	6.2	0.018	0.5	13.5	MW	CG	N
0.240	6.10	70551S	1.75	44.5	.204	5.2	1.0	.18	.95	24	.97	4.3	.24	6.2	0.018	0.5	13.5	SST	CG	N
0.240	6.10	70575	1.75	44.5	.200	5.1	1.5	.26	1.3	34	2.0	8.9	.33	8.3	0.020	0.5	16.3	MW	CG	N
0.240	6.10	70575S	1.75	44.5	.200	5.1	1.3	.22	1.0	26	1.3	5.9	.33	8.3	0.020	0.5	16.3	SST	CG	N
0.240	6.10	70598	1.75	44.5	.196	5.0	2.4	.41	1.1	29	2.6	12	.35	8.9	0.022	0.6	15.9	MW	CG	N
0.240	6.10	70598S	1.75	44.5	.196	5.0	2.0	.35	.88	22	1.8	7.8	.35	8.9	0.022	0.6	15.9	SST	CG	N
0.240	6.10	70618	1.75	44.5	.192	4.9	3.3	.57	1.1	27	3.4	15	.40	10.1	0.024	0.6	16.6	MW	CG	N
0.240	6.10	70618S	1.75	44.5	.192	4.9	2.8	.48	.82	21	2.3	10	.40	10.1	0.024	0.6	16.6	SST	CG	N
0.240	6.10	70639	1.75	44.5	.188	4.8	4.2	.73	.98	25	4.1	18	.47	12.0	0.026	0.7	18.1	MW	CG	N
0.240	6.10	70639S	1.75	44.5	.188	4.8	3.5	.62	.77	20	2.7	12	.47	12.0	0.026	0.7	18.1	SST	CG	N
0.240	6.10	70658	1.75	44.5	.182	4.6	6.2	1.1	.91	23	5.6	25	.57	14.4	0.029	0.7	19.5	MW	CG	N
0.240	6.10	70658S	1.75	44.5	.182	4.6	5.2	.92	.72	18	3.8	17	.57	14.4	0.029	0.7	19.5	SST	CG	N
0.240	6.10	70677	1.75	44.5	.176	4.5	9.2	1.6	.81	21	7.5	33	.65	16.5	0.032	0.8	20.3	MW	CG	N
0.240	6.10	70677S	1.75	44.5	.176	4.5	7.8	1.4	.64	16	5.0	22	.65	16.5	0.032	0.8	20.3	SST	CG	N
0.240	6.10	70696	1.75	44.5	.170	4.3	12	2.2	.75	19	9.2	41	.78	19.8	0.035	0.9	22.3	MW	CG	N
0.240	6.10	70696S	1.75	44.5	.170	4.3	11	1.8	.59	15	6.3	28	.78	19.8	0.035	0.9	22.3	SST	CG	N
0.240	6.10	70716	1.75	44.5	.164	4.2	18	3.1	.66	17	12	52	.86	21.8	0.038	1.0	22.6	MW	CG	N
0.240	6.10	70716S	1.75	44.5	.164	4.2	15	2.6	.53	13	7.9	35	.86	21.8	0.038	1.0	22.6	SST	CG	N
0.240	6.10	70736	1.75	44.5	.160	4.1	22	3.8	.63	16	14	60	.94	23.7	0.040	1.0	23.4	MW	CG	N
0.240	6.10	70736S	1.75	44.5	.160	4.1	18	3.2	.50	13	9.2	41	.94	23.7	0.040	1.0	23.4	SST	CG	N
0.240	6.10	70757	1.75	44.5	.156	4.0	27	4.6	.59	15	16	70	1.00	25.3	0.042	1.1	23.8	MW	CG	N
0.240	6.10	70757S	1.75	44.5	.156	4.0	23	3.9	.47	12	11	47	1.00	25.3	0.042	1.1	23.8	SST	CG	N
0.240	6.10	70775	1.75	44.5	.150	3.8	37	6.5	.52	13	19	85	1.06	26.9	0.045	1.1	23.5	MW	CG	N
0.240	6.10	70775S	1.75	44.5	.150	3.8	31	5.5	.41	10	13	57	1.06	26.9	0.045	1.1	23.5	SST	CG	N
0.240	6.10	70535	2.00	50.8	.208	5.3	.70	.12	1.5	37	1.0	4.6	.22	5.7	0.016	0.4	14.0	MW	CG	N
0.240	6.10	70535S	2.00	50.8	.208	5.3	.60	.10	1.2	29	.68	3.0	.22	5.7	0.016	0.4	14.0	SST	CG	N
0.240	6.10	70552	2.00	50.8	.204	5.2	1.0	.18	1.5	37	1.5	6.5	.28	7.2	0.018	0.5	15.8	MW	CG	N
0.240	6.10	70552S	2.00	50.8	.204	5.2	.85	.15	1.											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70697	2.00	50.8	.170	4.3	11	1.9	.85	22	9.2	41	.88	22.2	0.035	0.9	25.0	MW	CG	N
0.240	6.10	70697S	2.00	50.8	.170	4.3	9.3	1.6	.67	17	6.3	28	.88	22.2	0.035	0.9	25.0	SST	CG	N
0.240	6.10	70717	2.00	50.8	.164	4.2	16	2.7	.75	19	12	52	.96	24.5	0.038	1.0	25.4	MW	CG	N
0.240	6.10	70717S	2.00	50.8	.164	4.2	13	2.3	.60	15	7.9	35	.96	24.5	0.038	1.0	25.4	SST	CG	N
0.240	6.10	70737	2.00	50.8	.160	4.1	19	3.3	.72	18	14	60	1.05	26.7	0.040	1.0	26.3	MW	CG	N
0.240	6.10	70737S	2.00	50.8	.160	4.1	16	2.8	.57	15	9.2	41	1.05	26.7	0.040	1.0	26.3	SST	CG	N
0.240	6.10	70758	2.00	50.8	.156	4.0	23	4.0	.68	17	16	70	1.13	28.8	0.042	1.1	27.0	MW	CG	N
0.240	6.10	70758S	2.00	50.8	.156	4.0	20	3.4	.54	14	11	47	1.13	28.8	0.042	1.1	27.0	SST	CG	N
0.240	6.10	70776	2.00	50.8	.150	3.8	32	5.6	.59	15	19	85	1.20	30.6	0.045	1.1	26.8	MW	CG	N
0.240	6.10	70776S	2.00	50.8	.150	3.8	27	4.8	.47	12	13	57	1.20	30.6	0.045	1.1	26.8	SST	CG	N
0.240	6.10	70698	2.25	57.2	.170	4.3	9.7	1.7	.95	24	9.2	41	.98	24.8	0.035	0.9	27.9	MW	CG	N
0.240	6.10	70698S	2.25	57.2	.170	4.3	8.2	1.4	.76	19	6.3	28	.98	24.8	0.035	0.9	27.9	SST	CG	N
0.240	6.10	70718	2.25	57.2	.164	4.2	14	2.4	.85	22	12	52	1.08	27.5	0.038	1.0	28.5	MW	CG	N
0.240	6.10	70718S	2.25	57.2	.164	4.2	12	2.0	.68	17	7.9	35	1.08	27.5	0.038	1.0	28.5	SST	CG	N
0.240	6.10	70738	2.25	57.2	.160	4.1	17	2.9	.82	21	14	60	1.20	30.4	0.040	1.0	29.9	MW	CG	N
0.240	6.10	70738S	2.25	57.2	.160	4.1	14	2.5	.66	17	9.2	41	1.20	30.4	0.040	1.0	29.9	SST	CG	N
0.240	6.10	70759	2.25	57.2	.156	4.0	20	3.6	.76	19	16	70	1.27	32.1	0.042	1.1	30.1	MW	CG	N
0.240	6.10	70759S	2.25	57.2	.156	4.0	17	3.0	.61	15	11	47	1.27	32.1	0.042	1.1	30.1	SST	CG	N
0.240	6.10	70777	2.25	57.2	.150	3.8	28	5.0	.67	17	19	85	1.35	34.3	0.045	1.1	30.0	MW	CG	N
0.240	6.10	70777S	2.25	57.2	.150	3.8	24	4.2	.53	14	13	57	1.35	34.3	0.045	1.1	30.0	SST	CG	N
0.240	6.10	A12-23	2.34	59.5	.164	4.2	8.3	1.4	.56	14	4.6	21	1.79	45.4	0.038	1.0	46.0	MW	C	N
0.240	6.10	70699	2.50	63.5	.170	4.3	8.8	1.5	1.1	27	9.2	41	1.07	27.2	0.035	0.9	30.6	MW	CG	N
0.240	6.10	70699S	2.50	63.5	.170	4.3	7.4	1.3	.84	21	6.3	28	1.07	27.2	0.035	0.9	30.6	SST	CG	N
0.240	6.10	70719	2.50	63.5	.164	4.2	12	2.2	.95	24	12	52	1.20	30.5	0.038	1.0	31.6	MW	CG	N
0.240	6.10	70719S	2.50	63.5	.164	4.2	10	1.8	.76	19	7.9	35	1.20	30.5	0.038	1.0	31.6	SST	CG	N
0.240	6.10	70739	2.50	63.5	.160	4.1	15	2.6	.91	23	14	60	1.32	33.4	0.040	1.0	32.9	MW	CG	N
0.240	6.10	70739S	2.50	63.5	.160	4.1	13	2.2	.73	18	9.2	41	1.32	33.4	0.040	1.0	32.9	SST	CG	N
0.240	6.10	70760	2.50	63.5	.156	4.0	18	3.2	.87	22	16	70	1.42	36.1	0.042	1.1	33.9	MW	CG	N
0.240	6.10	70760S	2.50	63.5	.156	4.0	15	2.7	.69	18	11	47	1.42	36.1	0.042	1.1	33.9	SST	CG	N
0.240	6.10	70778	2.50	63.5	.150	3.8	25	4.4	.75	19	19	85	1.50	38.0	0.045	1.1	33.3	MW	CG	N
0.240	6.10	70778S	2.50	63.5	.150	3.8	22	3.8	.60	15	13	57	1.50	38.0	0.045	1.1	33.3	SST	CG	N
0.240	6.10	70740	3.25	82.6	.160	4.1	22	3.8	.63	16	14	60	.93	23.6	0.040	1.0	23.3	MW	CG	N
0.240	6.10	70740S	3.25	82.6	.160	4.1	18	3.2	.50	13	9.2	41	.93	23.6	0.040	1.0	23.3	SST	CG	N
0.240	6.10	70741	5.25	133.4	.160	4.1	17	2.9	.81	21	14	60	1.18	30.0	0.040	1.0	29.5	MW	CG	N
0.240	6.10	70741S	5.25	133.4	.160	4.1	14	2.5	.65	16	9.2	41	1.18	30.0	0.040	1.0	29.5	SST	CG	N
0.245	6.22	12691	3.67	93.2	.175	4.4	6.1	1.1	1.0	25	6.1	27	1.26	32.0	0.035	0.9	35.0	SST	C	N
0.250	6.35	B8-29	.16	4.0	.182	4.6	191	33	.03	.83	6.2	28	.10	2.6	0.034	0.9	3.00	SPR	CG	Z
0.250	6.35	10200	.19	4.8	.214	5.4	8.1	1.4	.11	2.7	.86	3.8	.08	2.1	0.018	0.5	3.50	MW	C	Z
0.250	6.35	A15-20	.19	4.8	.164	4.2	369	65	.03	.80	12	52	.15	3.8	0.043	1.1	3.50	SPR	CG	N
0.250	6.35	K-78	.22	5.6	.174	4.4	159	28	.05	1.2	7.7	34	.14	3.6	0.038	1.0	3.75	SST	CG	N
0.250	6.35	Q-94	.25	6.4	.222	5.6	.48	.08	.09	2.2	.04	.18	.16	4.2	0.014	0.4	10.8	MW	C	Z
0.250	6.35	10269	.25	6.4	.220	5.6	2.2	.39	.17	4.2	.37	1.7	.08	2.1	0.015	0.4	4.50	MW	C	N
0.250	6.35	U-24	.25	6.4	.200	5.1	16	2.9	.10	2.5	1.6	7.3	.15	3.8	0.025	0.6	5.00	MW	C	GI
0.250	6.35	CC-26	.25	6.4	.186	4.7	73	13	.09	2.3	6.5	29	.16	4.1	0.032	0.8	4.00	MW	C	N
0.250	6.35	L-40	.25	6.4	.178	4.5	123	22	.06	1.4	7.0	31	.14	3.7	0.036	0.9	4.00	SPR	CG	Z
0.250	6.35	DD-33	.28	7.1	.220	5.6	.98	.17	.18	4.5	.17	.76	.11	2.7	0.015	0.4	7.00	SST	CG	N
0.250	6.35	G-83	.28	7.1	.214	5.4	4.0	.71	.17	4.4	.70	3.1	.11	2.7	0.018	0.5	5.00	MW	C	GI
0.250	6.35	DD-63	.28	7.1	.210	5.3	6.3	1.1	.16	4.1	1.0	4.5	.12	3.0	0.020	0.5	5.00	MW	C	N
0.250	6.35	F-49	.28	7.1	.188	4.8	56	9.8	.08	2.0	4.4	20	.16	3.9	0.031	0.8	4.00	SST	C	N
0.250	6.35	S-116	.31	7.9	.226	5.7	.32	.06	.20	5.2	.07	.29	.11	2.7	0.012	0.3	8.00	SST	C	N
0.250	6.35	MM-9	.31	7.9	.210	5.3	5.5	.96	.21	5.4	1.2	5.2	.10	2.5	0.020	0.5	5.00	SST	C	N
0.250	6.35	A9-3	.31	7.9	.190	4.8	42	7.3	.10	2.4	4.0	18	.13	3.3	0.030	0.8	4.33	SST	CG	N
0.250	6.35	AA-16	.31	7.9	.190	4.8	27	4.8	.13	3.4	3.6	16	.18	4.6	0.030	0.8	6.00	MW	CG	Z
0.250	6.35	O-158	.31	7.9	.188	4.8	44	7.7	.10	2.5	4.4	20	.14	3.5	0.031	0.8	4.50	SST	CG	N
0.250	6.35	F-94	.31	7.9	.186	4.7	58	10	.09	2.3	5.2	23	.18	4.5	0.032	0.8	4.50	SPR	C	Z
0.250	6.35	B15-10	.31	7.9	.186	4.7	48	8.5	.11	2.7	5.2	23	.16	4.1	0.032	0.8	5.00	SPR	CG	Z
0.250	6.35	A15-8	.34	8.7	.172	4.4	105	18	.08	2.0	8.2	37	.20	5.0	0.039	1.0	5.00	SST	CG	N
0.250	6.35	RR-25	.34	8.7	.170	4.3	265	46	.04	.91	9.5	42	.18	4.6	0.040	1.0	3.50	SPR	C	N
0.250	6.35	PP-17	.34	8.7	.164	4.2	185	32	.06	1.6	12	52	.22	5.5	0.043	1.1	5.00	SPR	CG	GI
0.250	6.35	Z-2	.38	9.5	.210	5.3	3.7	.64	.23	5.7	.82	3.7	.15	3.8	0.020	0.5	6.50	SST	C	N
0.250	6.35	CC-63	.38	9.5	.210	5.3	6.7	1.2	.19	4.8	1.3	5.7	.09	2.3	0.020	0.5	4.50	SST	CG	N
0.250	6.35	LL-85	.38	9.5	.208	5.3	5.8	1.0	.23	5.8	1.3	5.9	.15	3.7	0.021	0.5	6.00	MW	C	N
0.250	6.35	EE-49	.38	9.5	.202	5.1	10	1.8	.21	5.3	2.1	9.5	.17	4.3	0.024	0.6	6.00	MW	C	Z
0.250	6.35	PP-55	.38	9.5	.202	5.1	14	2.4	.23	5.9	3.2	14	.14	3.7	0.024	0.6	5.00	MW	C	Z
0.250	6.35	II-41	.38	9.5	.198	5.0	19	3.4	.20	5.1	3.9	17	.16	4.0	0.026	0.7	5.00	MW	C	N
0.250	6.35	11366	.38	9.5	.194	4.9	19	3.3	.17	4.3	3.3	15	.16	4.1	0.028	0.7	5.75	SST	CG	N
0.250	6.35	BB-22	.38	9.5	.188	4.8	27	4.8	.16	4.1	4.4	20	.19	4.7	0.031	0.8	6.00	SST	CG	N
0.250	6.35	AA-39	.38	9.5	.186	4.7	42	7.4	.11	2.9	4.8	21	.16	4.1	0.032	0.8	5.00	SST	CG	N
0.250	6.35	3566	.38	9.5	.180	4.6	54	9.5	.16	4.2	8.9	40</								




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	CC-43	.44	11.1	.210	5.3	3.3	.58	.28	7.1	.91	4.1	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	L-14	.44	11.1	.210	5.3	2.3	.41	.24	6.0	.56	2.5	.20	5.1	0.020	0.5	9.00	SST	C	N
0.250	6.35	2821	.44	11.1	.206	5.2	8.1	1.4	.30	7.5	2.4	11	.14	3.6	0.022	0.6	5.50	MW	C	Z
0.250	6.35	AA-13	.44	11.1	.206	5.2	7.1	1.2	.28	7.2	2.0	9.0	.15	3.9	0.022	0.6	6.00	MW	C	Z
0.250	6.35	B18-156	.44	11.1	.202	5.1	12	2.1	.28	7.1	3.3	15	.13	3.4	0.024	0.6	5.50	MW	CG	N
0.250	6.35	F-97	.44	11.1	.200	5.1	14	2.5	.25	6.3	3.5	16	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.250	6.35	B5-24	.44	11.1	.194	4.9	20	3.5	.24	6.2	4.9	22	.13	3.4	0.028	0.7	6.00	MW	CG	N
0.250	6.35	F-25	.44	11.1	.184	4.7	48	8.3	.12	3.0	5.7	25	.21	5.4	0.033	0.8	5.50	SPR	C	Z
0.250	6.35	A12-22	.47	11.9	.228	5.8	.26	.05	.37	9.4	.09	.42	.10	2.5	0.011	0.3	8.00	MW	C	Z
0.250	6.35	V-98	.47	11.9	.212	5.4	1.9	.34	.30	7.5	.57	2.5	.17	4.3	0.019	0.5	9.00	SST	CG	N
0.250	6.35	4278	.47	11.9	.210	5.3	3.8	.66	.31	7.8	1.2	5.2	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.250	6.35	BB-74	.47	11.9	.210	5.3	2.8	.49	.31	7.8	.86	3.8	.16	4.1	0.020	0.5	8.00	SST	CG	N
0.250	6.35	G-98	.47	11.9	.206	5.2	7.2	1.3	.23	6.0	1.7	7.5	.12	3.1	0.022	0.6	5.50	SST	CG	N
0.250	6.35	L-92	.47	11.9	.190	4.8	22	3.8	.19	4.7	4.0	18	.20	5.0	0.030	0.8	6.50	SST	CG	N
0.250	6.35	F-23	.47	11.9	.184	4.7	42	7.3	.14	3.5	5.7	25	.23	5.9	0.033	0.8	6.00	SPR	C	Z
0.250	6.35	J-71	.47	11.9	.172	4.4	71	12	.12	3.2	8.8	39	.27	6.9	0.039	1.0	7.00	SPR	CG	Z
0.250	6.35	J-72	.47	11.9	.168	4.3	89	16	.11	2.9	10	45	.29	7.3	0.041	1.0	7.00	SPR	CG	N
0.250	6.35	B15-3	.47	11.9	.120	3.0	1351	237	.03	.65	34	153	.33	8.3	0.065	1.7	5.00	SPR	CG	N
0.250	6.35	S-794	.50	12.7	.210	5.3	3.5	.61	.35	8.8	1.2	5.3	.16	3.9	0.020	0.5	6.75	SST	C	N
0.250	6.35	V-100	.50	12.7	.210	5.3	3.2	.55	.32	8.1	1.0	4.5	.18	4.6	0.020	0.5	8.00	MW	C	N
0.250	6.35	H-94	.50	12.7	.208	5.3	3.1	.54	.30	7.5	.90	4.0	.20	5.2	0.021	0.5	8.75	SST	C	N
0.250	6.35	S-717	.50	12.7	.206	5.2	6.6	1.2	.26	6.5	1.7	7.5	.15	3.8	0.022	0.6	5.75	SST	C	N
0.250	6.35	BB-16	.50	12.7	.204	5.2	7.5	1.3	.26	6.5	1.9	8.6	.16	4.1	0.023	0.6	6.00	SST	C	N
0.250	6.35	HH-84	.50	12.7	.204	5.2	4.6	.81	.28	7.2	1.3	5.8	.22	5.5	0.023	0.6	8.50	SST	C	N
0.250	6.35	B15-68	.50	12.7	.204	5.2	4.4	.76	.29	7.4	1.3	5.7	.21	5.3	0.023	0.6	9.00	SST	CG	N
0.250	6.35	GG-46	.50	12.7	.202	5.1	10	1.8	.32	8.1	3.3	15	.17	4.3	0.024	0.6	6.00	MW	C	Z
0.250	6.35	3985	.50	12.7	.200	5.1	16	2.9	.21	5.4	3.5	16	.15	3.8	0.025	0.6	5.00	MW	C	Z
0.250	6.35	F-13	.50	12.7	.200	5.1	12	2.2	.28	7.2	3.5	16	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.250	6.35	S-1178	.50	12.7	.200	5.1	14	2.5	.16	4.2	2.3	10	.15	3.8	0.025	0.6	5.00	SST	C	N
0.250	6.35	Z-53	.50	12.7	.200	5.1	11	1.9	.22	5.5	2.3	10	.18	4.4	0.025	0.6	6.00	SST	C	N
0.250	6.35	B2-9	.50	12.7	.200	5.1	9.9	1.7	.30	7.6	3.0	13	.20	5.1	0.025	0.6	7.00	MW	C	N
0.250	6.35	2532	.50	12.7	.198	5.0	12	2.0	.29	7.4	3.4	15	.21	5.3	0.026	0.7	7.00	MW	C	Z
0.250	6.35	HH-13	.50	12.7	.196	5.0	8.6	1.5	.26	6.5	2.2	9.8	.24	6.2	0.027	0.7	9.00	SST	CG	N
0.250	6.35	XX-63	.50	12.7	.196	5.0	11	2.0	.26	6.5	3.0	13	.24	6.2	0.027	0.7	8.00	MW	C	Z
0.250	6.35	12734	.50	12.7	.192	4.9	17	3.0	.21	5.3	3.6	16	.20	5.0	0.029	0.7	6.75	SST	CG	N
0.250	6.35	B9-16	.50	12.7	.192	4.9	19	3.3	.29	7.3	5.4	24	.20	5.2	0.029	0.7	7.00	MW	CG	Z
0.250	6.35	NN-59	.50	12.7	.190	4.8	22	3.8	.26	6.6	5.7	25	.24	6.1	0.030	0.8	7.00	MW	CL	N
0.250	6.35	2556	.50	12.7	.186	4.7	29	5.1	.18	4.5	5.2	23	.26	6.5	0.032	0.8	7.00	HD	C	Z
0.250	6.35	529	.50	12.7	.180	4.6	42	7.4	.15	3.7	6.2	28	.29	7.2	0.035	0.89	7.13	HD	C	Z
0.250	6.35	NN-15	.50	12.7	.180	4.6	54	9.5	.12	3.0	6.4	29	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.250	6.35	NN-73	.50	12.7	.180	4.6	28	4.8	.19	4.7	5.1	23	.32	8.0	0.035	0.9	9.00	SST	CG	N
0.250	6.35	FF-13	.50	12.7	.180	4.6	31	5.5	.19	4.9	6.0	27	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.250	6.35	A9-11	.50	12.7	.178	4.5	49	8.6	.14	3.6	7.0	31	.25	6.4	0.036	0.9	7.00	SPR	CG	N
0.250	6.35	B1-48	.50	12.7	.172	4.4	64	11	.14	3.5	8.8	39	.29	7.4	0.039	1.0	7.50	SPR	CG	N
0.250	6.35	O-155	.50	12.7	.172	4.4	79	14	.11	2.8	8.8	39	.29	7.4	0.039	1.0	6.50	SPR	C	Z
0.250	6.35	BB-9	.50	12.7	.170	4.3	58	10	.15	3.9	8.9	39	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.250	6.35	518	.50	12.7	.168	4.3	85	15	.12	3.0	10	45	.34	8.6	0.041	1.0	7.25	HD	C	Z
0.250	6.35	FF-81	.50	12.7	.160	4.1	144	25	.09	2.3	13	59	.30	7.7	0.045	1.1	6.75	SPR	CG	Z
0.250	6.35	I-83	.50	12.7	.158	4.0	126	22	.11	2.8	14	63	.37	9.3	0.046	1.2	8.00	SPR	CG	N
0.250	6.35	NN-48	.50	12.7	.142	3.6	353	62	.06	1.4	20	87	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.250	6.35	L-100	.50	12.7	.130	3.3	429	75	.05	1.3	21	96	.45	11.4	0.060	1.5	7.50	SST	CG	N
0.250	6.35	00-58	.52	13.1	.210	5.3	4.7	.83	.38	9.5	1.8	7.9	.14	3.6	0.020	0.5	6.00	MW	C	N
0.250	6.35	S-163	.53	13.5	.214	5.4	1.8	.31	.37	9.4	.66	2.9	.16	4.1	0.018	0.5	8.00	SST	C	N
0.250	6.35	Q-14	.53	13.5	.192	4.9	13	2.4	.27	6.9	3.6	16	.26	6.6	0.029	0.7	9.00	MW	CG	Z
0.250	6.35	2929	.53	13.5	.180	4.6	54	9.5	.12	3.0	6.4	29	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.250	6.35	S-31	.53	13.5	.180	4.6	32	5.6	.19	4.8	6.0	27	.32	8.0	0.035	0.9	8.00	SST	C	N
0.250	6.35	2611	.53	13.5	.176	4.5	70	12	.15	3.8	10	47	.22	5.6	0.037	0.9	6.00	MW	CG	Z
0.250	6.35	A-23	.53	13.5	.172	4.4	54	9.4	.15	3.9	8.2	37	.30	7.7	0.039	1.0	7.75	SST	CG	N
0.250	6.35	A14-9	.53	13.5	.172	4.4	59	10	.15	3.8	8.8	39	.31	7.9	0.039	1.0	8.00	SPR	CG	GI
0.250	6.35	NN-39	.53	13.5	.170	4.3	79	14	.12	3.0	9.5	42	.32	8.1	0.040	1.0	7.00	SPR	C	N
0.250	6.35	EE-41	.53	13.5	.170	4.3	50	8.8	.17	4.3	8.6	38	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.250	6.35	H-92	.53	13.5	.166	4.2	75	13	.14	3.4	10	45	.33	8.3	0.042	1.1	7.75	SST	CG	N
0.250	6.35	S-836	.53	13.5	.166	4.2	77	13	.13	3.4	10	45	.37	9.3	0.042	1.1	7.75	SST	C	N
0.250	6.35	O-62	.53	13.5	.150	3.8	160	28	.08	2.1	13	58	.45	11.4	0.050	1.3	9.00	SPR	CG	Z
0.250	6.35	AA-11	.55	13.9	.170	4.3	79	14	.12	3.0	9.5	42	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.250	6.35	S-1239	.56	14.3	.218	5.5	.91	.16	.40	10	.37	1.6	.16	4.1	0.016	0.4	9.00	SST	C	N
0.250	6.35	J-10	.56	14.3	.206	5.2	4.1	.72	.36	9.2	1.5	6.7	.20	5.0	0.022	0.6	8.00	SST	C	N
0.250	6.35	F-50	.56	14.3	.194	4.9	12	2.0	.28	7.2	3.3	14	.28	7.1	0.028	0.7	9.00	MW	C	Z
0.250	6.35	926	.56	14.3	.186	4.7	26	4.6	.27	6.9	7.2	32	.27	6.9	0.032	0.8	7.50	MW	C	Z




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	A-62	.63	15.9	.214	5.4	1.1	.18	.41	10	.43	1.9	.22	5.5	0.018	0.5	12.0	SST	CG	N
0.250	6.35	MM-96	.63	15.9	.214	5.4	3.5	.60	.41	10	1.4	6.2	.12	3.0	0.018	0.5	5.50	MW	C	Z
0.250	6.35	BB-61	.63	15.9	.210	5.3	3.2	.55	.47	12	1.5	6.5	.16	4.1	0.020	0.5	8.00	MW	CG	N
0.250	6.35	GG-47	.63	15.9	.210	5.3	4.2	.73	.30	7.7	1.3	5.7	.12	3.0	0.020	0.5	6.00	SST	CG	N
0.250	6.35	A15-2	.63	15.9	.206	5.2	5.7	1.0	.45	11	2.5	11	.15	3.9	0.022	0.6	7.00	MW	CG	N
0.250	6.35	AA-30	.63	15.9	.206	5.2	3.3	.58	.39	10	1.3	5.8	.23	5.9	0.022	0.6	9.50	SST	C	N
0.250	6.35	S-718	.63	15.9	.206	5.2	5.2	.91	.32	8.3	1.7	7.5	.17	4.3	0.022	0.6	6.75	SST	C	N
0.250	6.35	O-60	.63	15.9	.200	5.1	5.4	.94	.35	8.9	1.9	8.3	.28	7.0	0.025	0.6	10.0	SST	C	N
0.250	6.35	10383	.63	15.9	.194	4.9	12	2.0	.37	9.5	4.3	19	.25	6.4	0.028	0.7	9.00	MW	CG	N
0.250	6.35	W-5	.63	15.9	.194	4.9	12	2.0	.28	7.1	3.3	15	.22	5.7	0.028	0.7	8.00	SST	CG	N
0.250	6.35	1931	.63	15.9	.192	4.9	21	3.7	.26	6.6	5.4	24	.22	5.5	0.029	0.7	6.50	MW	C	Z
0.250	6.35	JJ-95	.63	15.9	.190	4.8	18	3.2	.33	8.3	6.0	27	.27	6.9	0.030	0.8	8.00	MW	C	N
0.250	6.35	PP-11	.63	15.9	.186	4.7	19	3.4	.25	6.3	4.8	21	.27	6.9	0.032	0.8	8.50	SST	CG	N
0.250	6.35	F-10	.63	15.9	.186	4.7	24	4.2	.21	5.4	5.2	23	.29	7.3	0.032	0.8	8.00	HD	C	Z
0.250	6.35	212	.63	15.9	.182	4.6	27	4.8	.23	5.8	6.2	28	.34	8.6	0.034	0.9	9.00	HD	C	Z
0.250	6.35	A14-28	.63	15.9	.182	4.6	30	5.3	.20	5.2	6.2	28	.28	7.1	0.034	0.9	8.25	SPR	CG	GI
0.250	6.35	Y-10	.63	15.9	.176	4.5	56	9.8	.14	3.4	7.6	34	.26	6.6	0.037	0.9	7.00	SPR	CG	Z
0.250	6.35	A13-9	.63	15.9	.164	4.2	81	14	.14	3.7	12	52	.38	9.7	0.043	1.1	8.88	SPR	CG	N
0.250	6.35	10475	.63	15.9	.160	4.1	114	20	.12	3.0	13	59	.41	10.3	0.045	1.1	8.00	SPR	C	Z
0.250	6.35	N-8	.66	16.7	.202	5.1	7.5	1.3	.44	11	3.3	15	.18	4.6	0.024	0.6	7.50	MW	CG	Z
0.250	6.35	B7-7	.66	16.7	.198	5.0	9.4	1.6	.42	11	3.9	17	.21	5.4	0.026	0.7	8.25	MW	CG	N
0.250	6.35	10554	.66	16.7	.196	5.0	7.9	1.4	.34	8.6	2.7	12	.32	8.1	0.027	0.7	10.8	MW	C	Z
0.250	6.35	935	.66	16.7	.188	4.8	21	3.7	.31	7.9	6.6	29	.28	7.1	0.031	0.8	8.00	MW	C	Z
0.250	6.35	2524	.66	16.7	.186	4.7	22	3.9	.23	5.9	5.2	23	.30	7.7	0.032	0.8	8.50	HD	C	Z
0.250	6.35	Z-56	.66	16.7	.186	4.7	14	2.5	.30	7.7	4.4	19	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.250	6.35	A10-54	.66	16.7	.184	4.7	23	4.0	.23	5.9	5.3	23	.31	8.0	0.033	0.8	8.50	SPR	C	N
0.250	6.35	EE-81	.66	16.7	.176	4.5	40	7.0	.19	4.8	7.6	34	.33	8.5	0.037	0.9	9.00	SPR	CG	N
0.250	6.35	W-49	.66	16.7	.176	4.5	54	9.4	.13	3.3	7.1	32	.24	6.1	0.037	0.9	6.50	SST	CG	N
0.250	6.35	S-317	.69	17.4	.220	5.6	.54	.09	.51	13	.27	1.2	.18	4.6	0.015	0.4	11.0	SST	C	N
0.250	6.35	RR-46	.69	17.4	.210	5.3	3.3	.58	.39	9.9	1.3	5.7	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	KK-98	.69	17.4	.206	5.2	3.1	.54	.45	11	1.4	6.1	.24	6.1	0.022	0.6	10.0	SST	C	N
0.250	6.35	10609	.69	17.4	.202	5.1	6.4	1.1	.34	8.7	2.2	9.7	.21	5.3	0.024	0.6	7.75	SST	C	N
0.250	6.35	F-1	.69	17.4	.200	5.1	8.2	1.4	.43	11	3.5	16	.23	5.7	0.025	0.6	8.00	MW	C	Z
0.250	6.35	B1-44	.69	17.4	.198	5.0	8.3	1.5	.32	8.0	2.6	12	.21	5.4	0.026	0.7	8.25	SST	CG	N
0.250	6.35	HH-32	.69	17.4	.190	4.8	13	2.3	.34	8.7	4.4	20	.35	8.8	0.030	0.8	10.5	MW	C	Z
0.250	6.35	KK-24	.69	17.4	.190	4.8	11	1.9	.30	7.5	3.2	14	.39	9.9	0.030	0.8	12.0	MW	C	N
0.250	6.35	J-98	.69	17.4	.188	4.8	17	3.0	.26	6.5	4.4	20	.29	7.5	0.031	0.8	8.50	SST	C	N
0.250	6.35	J-49	.69	17.4	.186	4.7	21	3.6	.35	8.8	7.2	32	.32	8.1	0.032	0.8	9.00	MW	C	Z
0.250	6.35	B18-139	.69	17.4	.178	4.5	49	8.6	.14	3.6	7.0	31	.25	6.4	0.036	0.9	7.00	SPR	CG	Z
0.250	6.35	HH-94	.69	17.4	.174	4.4	36	6.4	.21	5.3	7.7	34	.36	9.2	0.038	1.0	9.50	SST	CG	N
0.250	6.35	AA-27	.69	17.4	.170	4.3	50	8.8	.18	4.5	8.9	39	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.250	6.35	3584	.69	17.4	.166	4.2	66	12	.23	5.8	15	67	.40	10.1	0.042	1.1	9.50	MW	CG	GI
0.250	6.35	B1-4	.69	17.4	.164	4.2	74	13	.16	4.0	12	52	.41	10.4	0.043	1.1	9.50	SPR	CG	GI
0.250	6.35	V-22	.72	18.2	.212	5.4	3.0	.53	.54	14	1.6	7.3	.15	3.9	0.019	0.5	7.00	MW	C	Z
0.250	6.35	B15-53	.72	18.2	.172	4.4	51	8.9	.17	4.4	8.8	39	.39	9.9	0.039	1.0	9.00	SPR	C	N
0.250	6.35	B3-46	.73	18.6	.168	4.3	39	6.8	.20	5.1	7.8	35	.53	13.5	0.041	1.0	12.0	SST	C	N
0.250	6.35	W-53	.75	19.1	.210	5.3	1.6	.29	.49	12	.81	3.6	.26	6.6	0.020	0.5	12.0	SST	C	N
0.250	6.35	J-54	.75	19.1	.206	5.2	1.9	.34	.38	9.7	.74	3.3	.37	9.3	0.022	0.6	16.7	MW	CG	N
0.250	6.35	S-719	.75	19.1	.206	5.2	4.1	.72	.41	10	1.7	7.5	.20	5.0	0.022	0.6	8.00	SST	C	N
0.250	6.35	Q-89	.75	19.1	.206	5.2	4.5	.80	.56	14	2.5	11	.18	4.6	0.022	0.6	8.25	MW	CG	N
0.250	6.35	A15-45	.75	19.1	.204	5.2	4.9	.85	.39	10	1.9	8.6	.19	4.8	0.023	0.6	8.25	SST	CG	N
0.250	6.35	B2-12	.75	19.1	.204	5.2	3.7	.65	.50	13	1.9	8.3	.25	6.4	0.023	0.6	10.0	SST	CL	N
0.250	6.35	A14-20	.75	19.1	.202	5.1	6.9	1.2	.48	12	3.3	15	.19	4.9	0.024	0.6	8.00	MW	CG	GI
0.250	6.35	F-41	.75	19.1	.198	5.0	8.3	1.5	.47	12	3.9	17	.26	6.6	0.026	0.7	9.00	MW	CG	Z
0.250	6.35	2977	.75	19.1	.194	4.9	10	1.8	.44	11	4.5	20	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.250	6.35	N-60	.75	19.1	.188	4.8	18	3.2	.36	9.2	6.6	29	.28	7.1	0.031	0.8	9.00	MW	CG	Z
0.250	6.35	Q-67	.75	19.1	.188	4.8	18	3.2	.36	9.2	6.6	29	.31	7.9	0.031	0.8	9.00	MW	C	N
0.250	6.35	3733	.75	19.1	.186	4.7	18	3.2	.29	7.2	5.2	23	.35	8.9	0.032	0.8	10.0	HD	C	Z
0.250	6.35	K-58	.75	19.1	.186	4.7	17	3.0	.30	7.7	5.2	23	.37	9.3	0.032	0.8	10.5	HD	C	GI
0.250	6.35	S-720	.75	19.1	.186	4.7	16	2.9	.30	7.5	4.8	21	.34	8.7	0.032	0.8	9.75	SST	C	N
0.250	6.35	H-19	.75	19.1	.186	4.7	15	2.5	.36	9.1	5.2	23	.38	9.8	0.032	0.8	12.0	HD	CG	N
0.250	6.35	W-83	.75	19.1	.184	4.7	18	3.2	.29	7.4	5.3	23	.36	9.2	0.033	0.8	10.0	SST	C	N
0.250	6.35	F-9	.75	19.1	.184	4.7	22	3.9	.26	6.5	5.7	25	.35	8.8	0.033	0.8	9.50	SPR	C	Z
0.250	6.35	K-90	.75	19.1	.180	4.6	29	5.1	.22	5.6	6.4	29	.33	8.4	0.035	0.9	9.50	SPR	CG	Z
0.250	6.35	B2-15	.75	19.1	.180	4.6	39	6.9	.23	5.7	8.9	40	.30	7.6	0.035	0.9	7.50	MW	C	N
0.250	6.35	B14-10	.75	19.1	.176	4.5	27	4.8	.26	6.5	7.1	32	.41	10.3	0.037	0.9	11.0	SST	CG	N
0.250	6.35	G-13	.75	19.1	.174	4.4	33	5.7	.23	5.9	7.7	34	.40	10.1	0.038	1.0	10.5	SST	CG	N
0.250	6.35	K-28	.75	19.1	.168	4.3	74	13	.14	3.5	10	45	.37	9.4	0.041	1.0	8.00	SPR	C	N
0.250	6.35	A15-10	.75	19.1	.166	4.2	52	9.1	.20	5.0	10	45	.44	11.2	0.042	1.1	10.5	SST	CG	N
0.250	6.35	NN-75	.75	19.1	.160	4.1	66	12	.19	4.8										




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	S-60	.81	20.6	.230	5.8	.10	.02	.69	18	.07	.31	.12	3.0	0.010	0.3	11.0	SST	C	N
0.250	6.35	B-69	.81	20.6	.218	5.5	.72	.13	.60	15	.43	1.9	.21	5.4	0.016	0.4	12.3	MW	C	N
0.250	6.35	A11-18	.81	20.6	.204	5.2	5.3	.93	.55	14	2.9	13	.20	5.0	0.023	0.6	8.50	MW	CG	GI
0.250	6.35	J-92	.81	20.6	.202	5.1	5.2	.90	.55	14	2.8	13	.26	6.7	0.024	0.6	10.0	MW	C	Z
0.250	6.35	B14-65	.81	20.6	.202	5.1	5.5	.96	.58	15	3.2	14	.23	5.8	0.024	0.6	9.50	MW	CG	N
0.250	6.35	YY-14	.81	20.6	.196	5.0	8.6	1.5	.51	13	4.4	19	.30	7.5	0.027	0.7	10.0	MW	CG	N
0.250	6.35	4289	.81	20.6	.194	4.9	8.1	1.4	.48	12	3.8	17	.34	8.5	0.028	0.7	12.0	MW	CG	Z
0.250	6.35	HH-5	.81	20.6	.186	4.7	14	2.5	.33	8.5	4.8	21	.34	8.7	0.032	0.8	10.8	SST	CG	N
0.250	6.35	F-8	.81	20.6	.184	4.7	20	3.4	.29	7.3	5.7	25	.38	9.6	0.033	0.8	10.5	SPR	C	Z
0.250	6.35	B-58	.81	20.6	.182	4.6	25	4.5	.24	6.2	6.2	28	.36	9.1	0.034	0.9	9.50	SPR	C	N
0.250	6.35	BB-23	.81	20.6	.180	4.6	19	3.3	.32	8.1	6.0	27	.46	11.6	0.035	0.9	12.0	SST	C	N
0.250	6.35	3866	.81	20.6	.172	4.4	35	6.2	.25	6.3	8.8	39	.47	11.9	0.039	1.0	12.0	SPR	CG	Z
0.250	6.35	A11-24	.81	20.6	.172	4.4	39	6.9	.22	5.7	8.8	39	.43	10.9	0.039	1.0	11.0	SPR	CG	N
0.250	6.35	A15-21	.81	20.6	.172	4.4	35	6.1	.24	6.0	8.2	37	.43	10.9	0.039	1.0	11.0	SST	CG	N
0.250	6.35	AA-99	.81	20.6	.156	4.0	93	16	.16	4.1	15	67	.52	13.1	0.047	1.2	11.0	SPR	CG	GI
0.250	6.35	S-486	.81	20.6	.124	3.1	376	66	.08	2.0	30	132	.63	16.0	0.063	1.6	10.0	SST	CG	N
0.250	6.35	S-9	.81	20.6	.100	2.5	941	165	.05	1.2	44	196	.75	19.1	0.075	1.9	10.0	SST	CG	N
0.250	6.35	J-23	.84	21.4	.198	5.0	7.3	1.3	.54	14	3.9	17	.26	6.6	0.026	0.7	10.0	MW	CG	Z
0.250	6.35	F-40	.84	21.4	.186	4.7	17	2.9	.31	7.9	5.2	23	.38	9.6	0.032	0.8	10.8	HD	C	Z
0.250	6.35	H-10	.84	21.4	.182	4.6	27	4.8	.23	5.8	6.2	28	.31	7.8	0.034	0.9	9.00	SPR	CG	GI
0.250	6.35	S-1313	.88	22.2	.224	5.7	.38	.07	.75	19	.29	1.3	.13	3.3	0.013	0.3	9.00	SST	C	N
0.250	6.35	AA-21	.88	22.2	.220	5.6	.81	.14	.67	17	.54	2.4	.14	3.4	0.015	0.4	8.00	SST	C	N
0.250	6.35	W-62	.88	22.2	.200	5.1	4.8	.83	.49	12	2.3	10	.28	7.0	0.025	0.6	11.0	SST	CG	N
0.250	6.35	2948	.88	22.2	.198	5.0	6.7	1.2	.59	15	3.9	17	.28	7.1	0.026	0.7	10.8	MW	CG	Z
0.250	6.35	F-91	.88	22.2	.198	5.0	7.3	1.3	.54	14	3.9	17	.29	7.3	0.026	0.7	10.0	MW	C	Z
0.250	6.35	A13-3	.88	22.2	.196	5.0	7.4	1.3	.40	10	2.9	13	.28	7.0	0.027	0.7	10.3	SST	CG	N
0.250	6.35	FF-98	.88	22.2	.194	4.9	12	2.0	.42	11	4.9	22	.28	7.1	0.028	0.7	9.00	MW	CG	Z
0.250	6.35	00-4	.88	22.2	.190	4.8	12	2.0	.52	13	6.0	27	.35	8.8	0.030	0.8	11.5	MW	CG	GI
0.250	6.35	S-721	.88	22.2	.186	4.7	14	2.4	.35	9.0	4.8	21	.39	10.0	0.032	0.8	11.3	SST	C	N
0.250	6.35	927	.88	22.2	.182	4.6	21	3.7	.29	7.4	6.2	28	.37	9.5	0.034	0.9	11.0	HD	CG	Z
0.250	6.35	10285	.88	22.2	.180	4.6	25	4.3	.26	6.6	6.4	29	.41	10.4	0.035	0.9	10.8	SPR	C	Z
0.250	6.35	B7-27	.88	22.2	.180	4.6	23	4.0	.28	7.2	6.4	29	.40	10.2	0.035	0.9	11.5	SPR	CG	N
0.250	6.35	928	.88	22.2	.168	4.3	49	8.7	.21	5.2	10	45	.49	12.5	0.041	1.0	11.0	HD	C	Z
0.250	6.35	S-723	.88	22.2	.166	4.2	43	7.6	.24	6.0	10	45	.55	13.9	0.042	1.1	12.0	SST	C	N
0.250	6.35	3874	.88	22.2	.114	2.9	850	149	.05	1.2	39	172	.54	13.8	0.068	1.7	8.00	SPR	CG	Z
0.250	6.35	B14-11	.91	23.0	.184	4.7	49	8.6	.11	2.7	5.3	23	.20	5.0	0.033	0.8	5.00	SST	C	N
0.250	6.35	10412	.91	23.0	.174	4.4	33	5.8	.25	6.3	8.2	36	.44	11.1	0.038	1.0	11.5	SPR	CG	Z
0.250	6.35	11899	.91	23.0	.160	4.1	76	13	.17	4.4	13	59	.54	13.7	0.045	1.1	11.0	SPR	C	N
0.250	6.35	10149	.94	23.8	.210	5.3	1.7	.29	.65	17	1.1	4.9	.29	7.2	0.020	0.5	13.3	MW	C	Z
0.250	6.35	O-314	.94	23.8	.202	5.1	4.4	.78	.64	16	2.8	13	.30	7.5	0.024	0.6	11.3	MW	C	Z
0.250	6.35	KK-43	.94	23.8	.198	5.0	6.5	1.1	.60	15	3.9	17	.31	7.9	0.026	0.7	11.0	MW	C	N
0.250	6.35	B5-65	.94	23.8	.196	5.0	6.3	1.1	.56	14	3.5	16	.38	9.6	0.027	0.7	13.0	MW	C	N
0.250	6.35	FF-89	.94	23.8	.190	4.8	9.9	1.7	.52	13	5.1	23	.42	10.7	0.030	0.8	13.0	MW	C	Z
0.250	6.35	L-84	.94	23.8	.190	4.8	11	1.9	.55	14	6.0	27	.39	9.9	0.030	0.8	12.0	MW	C	Z
0.250	6.35	F-39	.94	23.8	.186	4.7	15	2.5	.36	9.1	5.2	23	.42	10.6	0.032	0.8	12.0	SPR	C	Z
0.250	6.35	FF-50	.94	23.8	.180	4.6	20	3.6	.30	7.5	6.0	27	.39	10.0	0.035	0.9	11.3	SST	CG	N
0.250	6.35	2833	.94	23.8	.160	4.1	71	12	.26	6.6	18	82	.52	13.3	0.045	1.1	11.6	MW	CG	Z
0.250	6.35	S-930	.94	23.8	.158	4.0	73	13	.18	4.6	13	59	.55	14.0	0.046	1.2	11.0	SST	C	N
0.250	6.35	B-47	.94	23.8	.150	3.8	103	18	.15	3.9	16	70	.58	14.6	0.050	1.3	11.5	SST	CG	N
0.250	6.35	3519	.94	23.8	.138	3.5	176	31	.18	4.6	32	142	.73	18.5	0.056	1.4	13.0	MW	CG	Z
0.250	6.35	DD-43	.97	24.6	.210	5.3	1.7	.29	.71	18	1.2	5.3	.26	6.6	0.020	0.5	12.0	SST	C	N
0.250	6.35	3115	1.00	25.4	.214	5.4	1.3	.22	.78	20	.99	4.4	.23	5.7	0.018	0.5	11.5	MW	C	GI
0.250	6.35	W-47	1.00	25.4	.214	5.4	1.2	.20	.78	20	.92	4.1	.22	5.5	0.018	0.5	11.0	SST	C	N
0.250	6.35	151-A	1.00	25.4	.210	5.3	2.8	.49	.68	17	1.9	8.5	.20	5.0	0.020	0.5	8.75	MW	C	Z
0.250	6.35	3811	1.00	25.4	.210	5.3	2.4	.41	.78	20	1.8	8.2	.22	5.6	0.020	0.5	10.0	MW	C	GI
0.250	6.35	HH-67	1.00	25.4	.210	5.3	3.4	.59	.38	9.7	1.3	5.7	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	W-9	1.00	25.4	.210	5.3	1.5	.26	.72	18	1.1	4.8	.28	7.1	0.020	0.5	13.0	SST	C	N
0.250	6.35	4111	1.00	25.4	.208	5.3	1.9	.33	.67	17	1.3	5.6	.33	8.3	0.021	0.5	14.5	MW	C	Z
0.250	6.35	12667	1.00	25.4	.206	5.2	3.8	.66	.67	17	2.5	11	.21	5.3	0.022	0.6	9.50	MW	CG	N
0.250	6.35	3614	1.00	25.4	.204	5.2	3.1	.55	.68	17	2.1	9.4	.32	8.2	0.023	0.6	13.0	MW	C	Z
0.250	6.35	Q-68	1.00	25.4	.204	5.2	4.0	.71	.72	18	2.9	13	.24	6.1	0.023	0.6	10.5	MW	CG	N
0.250	6.35	12786	1.00	25.4	.196	5.0	6.3	1.1	.62	16	3.9	17	.38	9.6	0.027	0.7	13.0	MW	C	N
0.250	6.35	10019	1.00	25.4	.194	4.9	9.0	1.6	.54	14	4.9	22	.34	8.5	0.028	0.7	11.0	MW	C	Z
0.250	6.35	FF-11	1.00	25.4	.190	4.8	8.1	1.4	.49	13	4.0	18	.42	10.7	0.030	0.8	14.0	SST	CG	N
0.250	6.35	M-18	1.00	25.4	.190	4.8	13	2.3	.45	11	6.0	27	.34	8.6	0.030	0.8	10.3	MW	C	Z
0.250	6.35	MM-37	1.00	25.4	.190	4.8	15	2.6	.41	10	6.0	27	.29	7.2	0.030	0.8	9.50	MW	CG	Z
0.250	6.35	3567	1.00	25.4	.188	4.8	18	3.2	.36	9.2	6.6	29	.31	7.9	0.031	0.8	9.00	MW	C	Z
0.250	6.35	A-41	1.00	25.4	.186	4.7	11	2.0	.46	12	5.2	23	.51	13.0	0.032	0.8	15.0	SPR	C	BO
0.250	6.35	QQ-66	1.00	25.4	.186	4.7	22	3.9	.32	8.2	7.2	32	.30	7.7						




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	A10-25	1.03	26.2	.214	5.4	.56	.10	.64	16	.36	1.6	.40	10.1	0.018	0.5	21.0	SST	C	N
0.250	6.35	10179	1.03	26.2	.202	5.1	4.6	.80	.52	13	2.4	11	.26	6.7	0.024	0.6	11.0	HD	CG	N
0.250	6.35	S-999	1.03	26.2	.188	4.8	12	2.1	.36	9.2	4.4	20	.34	8.7	0.031	0.8	11.0	SST	CG	N
0.250	6.35	2621	1.03	26.2	.172	4.4	25	4.4	.35	8.8	8.8	39	.66	16.8	0.039	1.0	16.0	HD	C	Z
0.250	6.35	A15-15	1.05	26.6	.170	4.3	30	5.3	.30	7.5	8.9	39	.59	15.0	0.040	1.0	13.8	SST	C	N
0.250	6.35	YY-3	1.06	27.0	.210	5.3	2.1	.36	.62	16	1.3	5.7	.22	5.6	0.020	0.5	10.0	SST	C	N
0.250	6.35	TT-19	1.06	27.0	.204	5.2	2.5	.45	.72	18	1.8	8.2	.34	8.6	0.023	0.6	13.8	SST	C	N
0.250	6.35	11468	1.06	27.0	.204	5.2	3.5	.61	.55	14	1.9	8.6	.27	6.9	0.023	0.6	10.8	SST	C	N
0.250	6.35	WW-33	1.06	27.0	.202	5.1	3.8	.66	.73	18	2.7	12	.34	8.5	0.024	0.6	13.0	MW	C	N
0.250	6.35	HH-65	1.06	27.0	.186	4.7	13	2.3	.39	10	5.2	23	.42	10.6	0.032	0.8	13.0	SPR	CG	N
0.250	6.35	F-21	1.06	27.0	.184	4.7	16	2.7	.37	9.3	5.7	25	.45	11.5	0.033	0.8	12.8	SPR	C	Z
0.250	6.35	A9-19	1.06	27.0	.178	4.5	15	2.7	.41	11	6.4	28	.65	16.5	0.036	0.9	18.0	SPR	CG	N
0.250	6.35	F-31	1.06	27.0	.156	4.0	88	15	.17	4.3	15	67	.54	13.7	0.047	1.2	11.5	SPR	CG	Z
0.250	6.35	12407	1.09	27.8	.224	5.7	.19	.03	.85	22	.16	.73	.25	6.3	0.013	0.3	18.0	MW	C	N
0.250	6.35	3274	1.09	27.8	.174	4.4	26	4.6	.31	7.9	8.2	36	.53	13.5	0.038	1.0	14.0	SPR	CG	Z
0.250	6.35	AA-35	1.13	28.6	.230	5.8	.04	.01	.85	21	.03	.14	.28	7.1	0.010	0.3	27.0	SST	C	N
0.250	6.35	S-197	1.13	28.6	.222	5.6	.23	.04	.86	22	.20	.89	.26	6.7	0.014	0.4	17.8	SST	C	N
0.250	6.35	2834	1.13	28.6	.216	5.5	1.0	.17	.91	23	.91	4.1	.21	5.4	0.017	0.4	11.5	MW	C	Z
0.250	6.35	2877	1.13	28.6	.216	5.5	.45	.08	.72	18	.32	1.4	.41	10.4	0.017	0.4	23.0	MW	C	Z
0.250	6.35	4288	1.13	28.6	.216	5.5	.50	.09	.75	19	.38	1.7	.37	9.5	0.017	0.4	21.0	MW	C	Z
0.250	6.35	II-5	1.13	28.6	.210	5.3	1.5	.25	.81	20	1.2	5.2	.32	8.1	0.020	0.5	15.0	MW	C	Z
0.250	6.35	1890	1.13	28.6	.200	5.1	4.5	.78	.78	20	3.5	15	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.250	6.35	3561	1.13	28.6	.198	5.0	6.9	1.2	.57	14	3.9	17	.30	7.6	0.026	0.7	10.5	MW	C	Z
0.250	6.35	DD-8	1.13	28.6	.190	4.8	6.5	1.1	.59	15	3.8	17	.54	13.7	0.030	0.8	17.0	SST	C	N
0.250	6.35	S-1156	1.13	28.6	.186	4.7	13	2.2	.38	9.7	4.8	21	.42	10.6	0.032	0.8	12.0	SST	C	N
0.250	6.35	S-975	1.13	28.6	.180	4.6	16	2.8	.38	9.5	6.0	27	.48	12.2	0.035	0.9	13.8	SST	CG	N
0.250	6.35	YY-17	1.13	28.6	.178	4.5	18	3.1	.37	9.3	6.5	29	.50	12.8	0.036	0.9	14.0	SST	CG	N
0.250	6.35	A14-39	1.13	28.6	.174	4.4	24	4.2	.34	8.7	8.2	36	.58	14.7	0.038	1.0	15.3	SPR	CG	N
0.250	6.35	EE-34	1.13	28.6	.150	3.8	93	16	.17	4.3	16	70	.64	16.2	0.050	1.3	12.8	SST	CG	N
0.250	6.35	HH-55	1.16	29.4	.214	5.4	.58	.10	.78	20	.45	2.0	.38	9.6	0.018	0.5	20.0	SST	C	N
0.250	6.35	LL-70	1.16	29.4	.190	4.8	9.9	1.7	.60	15	6.0	27	.39	9.9	0.030	0.8	13.0	MW	CG	N
0.250	6.35	S-322	1.16	29.4	.156	4.0	66	12	.21	5.4	14	63	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.250	6.35	O-102	1.19	30.2	.212	5.4	.89	.16	.81	21	.72	3.2	.38	9.7	0.019	0.5	19.0	MW	C	Z
0.250	6.35	BB-30	1.19	30.2	.170	4.3	27	4.7	.33	8.3	8.9	39	.60	15.2	0.040	1.0	15.0	SST	CG	N
0.250	6.35	L-30	1.23	31.3	.150	3.8	140	25	.12	3.0	17	74	.50	12.7	0.050	1.3	10.0	SPR	CG	Z
0.250	6.35	CC-87	1.25	31.8	.226	5.7	.18	.03	1.1	27	.19	.84	.19	4.7	0.012	0.3	14.5	MW	C	N
0.250	6.35	B2-39	1.25	31.8	.210	5.3	1.6	.28	.95	24	1.5	6.7	.30	7.6	0.020	0.5	14.0	MW	C	N
0.250	6.35	7	1.25	31.8	.204	5.2	3.0	.52	.70	18	2.1	9.3	.33	8.5	0.023	0.6	13.5	HD	C	Z
0.250	6.35	S-138	1.25	31.8	.202	5.1	2.6	.45	.84	21	2.2	9.6	.41	10.4	0.024	0.6	16.0	SST	C	N
0.250	6.35	Y-81	1.25	31.8	.202	5.1	3.2	.56	.87	22	2.8	12	.38	9.8	0.024	0.6	15.0	MW	C	N
0.250	6.35	F-14	1.25	31.8	.198	5.0	4.9	.85	.81	20	3.9	17	.39	9.9	0.026	0.7	14.0	MW	C	Z
0.250	6.35	CC-4	1.25	31.8	.190	4.8	4.8	.83	.50	13	2.4	11	.75	19.1	0.030	0.8	25.0	MW	CG	N
0.250	6.35	A14-3	1.25	31.8	.170	4.3	27	4.8	.35	8.8	9.5	42	.66	16.8	0.040	1.0	16.5	SPR	CG	N
0.250	6.35	S-725	1.25	31.8	.166	4.2	29	5.0	.35	9.0	10	45	.76	19.2	0.042	1.1	17.0	SST	C	N
0.250	6.35	B10-6	1.25	31.8	.162	4.1	39	6.7	.32	8.2	12	55	.79	20.1	0.044	1.1	18.0	SPR	CG	N
0.250	6.35	CC-57	1.28	32.5	.190	4.8	9.9	1.7	.60	15	6.0	27	.39	9.9	0.030	0.8	13.0	MW	CG	Z
0.250	6.35	4296	1.31	33.3	.182	4.6	14	2.5	.44	11	6.2	28	.56	14.2	0.034	0.9	15.5	SPR	C	Z
0.250	6.35	M-148	1.31	33.3	.166	4.2	36	6.2	.31	7.8	11	48	.67	17.1	0.042	1.1	16.0	SPR	CG	Z
0.250	6.35	S-331	1.34	34.1	.214	5.4	1.1	.19	.87	22	.93	4.2	.23	5.9	0.018	0.5	12.0	SST	C	N
0.250	6.35	151-B	1.38	34.9	.210	5.3	2.0	.35	.96	24	1.9	8.5	.25	6.4	0.020	0.5	11.5	MW	C	Z
0.250	6.35	3780	1.38	34.9	.194	4.9	6.0	1.0	.82	21	4.9	22	.46	11.7	0.028	0.7	15.5	MW	C	Z
0.250	6.35	J-47	1.38	34.9	.190	4.8	5.0	.87	.66	17	3.3	14	.72	18.3	0.030	0.8	24.0	MW	CG	Z
0.250	6.35	PP-99	1.38	34.9	.190	4.8	11	1.9	.38	9.6	4.0	18	.36	9.1	0.030	0.8	11.0	SST	C	N
0.250	6.35	201-B	1.38	34.9	.180	4.6	15	2.6	.60	15	8.9	40	.61	15.6	0.035	0.9	16.5	MW	C	Z
0.250	6.35	II-66	1.38	34.9	.170	4.3	27	4.8	.35	8.8	9.5	42	.70	17.8	0.040	1.0	16.5	SPR	C	Z
0.250	6.35	S-1023	1.38	34.9	.160	4.1	44	7.7	.28	7.2	12	55	.70	17.7	0.045	1.1	15.5	SST	CG	N
0.250	6.35	10877	1.41	35.7	.210	5.3	1.0	.18	1.0	25	1.0	4.5	.41	10.4	0.020	0.5	20.5	MW	CG	N
0.250	6.35	2980	1.41	35.7	.210	5.3	1.3	.23	1.1	27	1.4	6.3	.35	8.8	0.020	0.5	16.3	MW	C	Z
0.250	6.35	JJ-21	1.44	36.5	.190	4.8	3.6	.63	.57	14	2.0	9.1	.87	22.1	0.030	0.8	29.0	SST	CG	N
0.250	6.35	3938	1.44	36.5	.156	4.0	47	8.2	.32	8.2	15	67	.94	23.9	0.047	1.2	20.0	SPR	CG	Z
0.250	6.35	B4-12	1.44	36.6	.156	4.0	51	8.9	.30	7.5	15	67	.87	22.1	0.047	1.2	18.5	SPR	CG	N
0.250	6.35	929	1.50	38.1	.198	5.0	2.7	.47	.85	22	2.3	10	.65	16.5	0.026	0.7	24.0	MW	C	Z
0.250	6.35	524	1.50	38.1	.182	4.6	10	1.8	.61	15	6.2	28	.74	18.8	0.034	0.9	20.8	HD	C	Z
0.250	6.35	10423	1.50	38.1	.178	4.5	12	2.1	.58	15	7.0	31	.85	21.5	0.036	0.9	22.5	SPR	C	N
0.250	6.35	MM-49	1.50	38.1	.170	4.3	22	3.9	.43	11	9.5	42	.80	20.3	0.040	1.0	20.0	SPR	CG	GI
0.250	6.35	12253	1.50	38.1	.170	4.3	22	3.9	.43	11	9.5	42	.80	20.3	0.040	1.0	20.0	SPR	CG	GI
0.250	6.35	S-726	1.50	38.1	.166	4.2	23	4.1	.44	11	10	45	.90	22.9	0.042	1.1	20.5	SST	C	N
0.250	6.35	BB-25	1.50	38.1	.156	4.0	41	7.1	.35	8.8	14	63	.94	23.9	0.047	1.2	20.0	SST	CG	N
0.250	6.35	S-1506	1.56	39.7	.206	5.2	2.2	.39	.75	19	1.7	7.5	.31	7.8	0					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	G-96	1.75	44.5	.210	5.3	1.4	.24	1.4	36	1.9	8.5	.34	8.6	0.020	0.5	16.0	MW	C	N
0.250	6.35	12620	1.75	44.5	.200	5.1	2.3	.41	1.2	29	2.7	12	.60	15.2	0.025	0.6	23.0	MW	C	N
0.250	6.35	B2-4	1.75	44.5	.200	5.1	4.7	.82	.74	19	3.5	16	.34	8.6	0.025	0.6	12.5	MW	CL	N
0.250	6.35	11349	1.75	44.5	.190	4.8	3.3	.58	.81	20	2.6	12	.95	24.0	0.030	0.8	31.5	SST	CG	N
0.250	6.35	J-61	1.75	44.5	.182	4.6	8.7	1.5	.71	18	6.2	28	.82	20.7	0.034	0.9	24.0	SPR	C	Z
0.250	6.35	201-C	1.75	44.5	.180	4.6	12	2.0	.77	20	8.9	40	.76	19.3	0.035	0.9	20.8	MW	C	Z
0.250	6.35	A12-18	1.78	45.2	.200	5.1	2.3	.40	1.2	30	2.7	12	.61	15.6	0.025	0.6	23.5	MW	C	N
0.250	6.35	1941	1.78	45.2	.182	4.6	10	1.8	.60	15	6.2	28	.73	18.6	0.034	0.9	20.5	SPR	C	Z
0.250	6.35	2746	1.78	45.2	.176	4.5	15	2.7	.68	17	10	47	.78	19.7	0.037	0.9	20.0	MW	C	Z
0.250	6.35	10937	1.78	45.2	.170	4.3	19	3.3	.51	13	9.5	42	.93	23.6	0.040	1.0	23.3	SPR	CG	N
0.250	6.35	3005	1.81	46.0	.174	4.4	17	3.0	.47	12	8.2	36	.81	20.5	0.038	1.0	20.3	SPR	C	Z
0.250	6.35	11109	1.88	47.6	.210	5.3	1.1	.18	1.5	37	1.5	6.8	.42	10.7	0.020	0.5	20.0	MW	C	Z
0.250	6.35	10860	1.88	47.6	.188	4.8	5.3	.93	1.0	27	5.6	25	.83	21.1	0.031	0.8	25.8	MW	C	BO
0.250	6.35	F-61	1.94	49.2	.142	3.6	83	15	.25	6.3	21	92	1.16	29.5	0.054	1.4	21.5	SPR	CG	Z
0.250	6.35	3730	2.00	50.8	.216	5.5	.68	.12	1.7	43	1.2	5.2	.29	7.3	0.017	0.4	16.0	MW	C	GI
0.250	6.35	2566	2.00	50.8	.214	5.4	.55	.10	1.6	39	.85	3.8	.45	11.4	0.018	0.5	24.0	MW	C	Z
0.250	6.35	B2-45	2.00	50.8	.206	5.2	2.3	.40	1.1	28	2.5	11	.34	8.7	0.022	0.6	14.5	MW	C	Z
0.250	6.35	10191	2.00	50.8	.200	5.1	2.7	.48	1.3	32	3.5	16	.53	13.3	0.025	0.6	20.0	MW	C	Z
0.250	6.35	4251	2.00	50.8	.200	5.1	1.9	.33	1.3	32	2.4	11	.73	18.4	0.025	0.6	28.0	MW	C	Z
0.250	6.35	3511	2.00	50.8	.198	5.0	2.7	.47	1.4	34	3.6	16	.65	16.5	0.026	0.7	24.0	MW	C	Z
0.250	6.35	A14-35	2.00	50.8	.178	4.5	11	1.9	.64	16	7.0	31	.89	22.6	0.036	0.9	24.8	SPR	CG	N
0.250	6.35	L-60	2.02	51.2	.170	4.3	17	2.9	.57	15	9.5	42	1.04	26.4	0.040	1.0	26.0	SPR	CG	Z
0.250	6.35	S-3183	2.13	54.0	.168	4.3	14	2.4	.70	18	9.5	42	1.25	31.8	0.041	1.0	30.5	SST	CG	N
0.250	6.35	10430	2.22	56.4	.180	4.6	16	2.7	.42	11	6.4	29	.60	15.1	0.035	0.9	16.0	SPR	C	Z
0.250	6.35	F-99	2.25	57.2	.192	4.9	3.1	.55	1.3	33	4.1	18	.96	24.3	0.029	0.7	32.0	MW	C	Z
0.250	6.35	O-43	2.34	59.5	.192	4.9	4.3	.75	1.3	32	5.4	24	.73	18.4	0.029	0.7	24.0	MW	C	N
0.250	6.35	B10-41	2.38	60.3	.200	5.1	3.8	.66	.92	23	3.5	16	.40	10.2	0.025	0.6	15.0	MW	C	Z
0.250	6.35	4119	2.50	63.5	.190	4.8	4.7	.81	1.3	33	6.0	27	.80	20.2	0.030	0.8	25.5	MW	C	Z
0.250	6.35	00-56	2.66	67.5	.170	4.3	12	2.1	.77	20	9.5	42	1.38	35.1	0.040	1.0	34.5	SPR	CG	BO
0.250	6.35	O-55	2.69	68.2	.202	5.1	2.0	.35	1.7	42	3.3	15	.57	14.5	0.024	0.6	22.8	MW	C	Z
0.250	6.35	A-79	2.75	69.9	.194	4.9	4.0	.71	1.2	31	4.9	22	.64	16.4	0.028	0.7	22.0	MW	C	N
0.250	6.35	LL-17	2.78	70.6	.190	4.8	2.6	.46	1.4	36	3.7	17	1.35	34.3	0.030	0.8	44.0	MW	C	N
0.250	6.35	W-55	3.00	76.2	.166	4.2	17	2.9	.66	17	11	48	1.39	35.2	0.042	1.1	32.0	SPR	C	Z
0.250	6.35	11477	3.03	77.0	.160	4.1	22	3.9	.60	15	13	59	1.53	38.9	0.045	1.1	33.0	SPR	CG	Z
0.250	6.35	12743	3.13	79.4	.178	4.5	5.6	.98	1.2	32	7.0	31	1.69	43.0	0.036	0.9	46.0	SPR	C	N
0.250	6.35	12505	3.38	85.7	.170	4.3	9.5	1.7	1.0	25	9.5	42	1.80	45.7	0.040	1.0	44.0	SPR	C	N
0.250	6.35	S-1001	3.75	95.3	.198	5.0	.91	.16	2.2	56	2.0	8.9	1.53	39.0	0.026	0.7	58.0	SST	C	N
0.250	6.35	S-1504	4.00	101.6	.200	5.1	.73	.13	2.5	62	1.8	7.9	1.55	39.4	0.025	0.6	61.0	SST	C	N
0.250	6.35	2822	4.75	120.7	.170	4.3	6.3	1.1	1.5	38	9.5	42	2.60	66.0	0.040	1.0	65.0	SPR	CG	GI
0.250	6.35	3946	4.88	123.8	.180	4.6	3.4	.59	1.9	48	6.4	29	2.31	58.7	0.035	0.9	66.0	SPR	CG	GI
0.250	6.35	B10-55	4.88	123.8	.174	4.4	4.8	.85	1.7	43	8.2	36	2.55	64.7	0.038	1.0	67.0	SPR	CG	Z
0.250	6.35	12708	6.50	165.1	.178	4.5	2.5	.44	2.9	73	7.2	32	3.64	92.4	0.036	0.9	100.0	MW	C	N
0.262	6.65	12798	.86	21.8	.166	4.2	80	14	.27	6.8	21	94	.56	14.3	0.048	1.2	11.8	MW	CG	N
0.266	6.76	W-46	.19	4.8	.232	5.9	5.2	.92	.11	2.8	.59	2.6	.08	1.9	0.017	0.4	3.50	MW	C	Z
0.266	6.76	J-77	.22	5.6	.176	4.5	277	48	.04	.99	11	48	.18	4.6	0.045	1.1	4.00	SPR	CG	N
0.266	6.76	EE-27	.28	7.1	.236	6.0	1.4	.24	.19	4.9	.26	1.2	.09	2.3	0.015	0.4	5.00	SST	C	N
0.266	6.76	B5-63	.31	7.9	.246	6.2	.17	.03	.23	5.9	.04	.18	.08	2.0	0.010	0.3	7.00	MW	C	N
0.266	6.76	CC-52	.31	7.9	.220	5.6	10	1.8	.18	4.6	1.9	8.3	.13	3.4	0.023	0.6	4.75	MW	C	N
0.266	6.76	O-27	.31	7.9	.206	5.2	45	7.9	.13	3.2	5.6	25	.15	3.8	0.030	0.8	4.00	MW	C	N
0.266	6.76	S-1389	.31	7.9	.206	5.2	31	5.5	.12	3.1	3.8	17	.17	4.2	0.030	0.8	4.50	SST	C	N
0.266	6.76	I-84	.31	7.9	.196	5.0	59	10	.10	2.6	6.1	27	.18	4.4	0.035	0.9	5.00	SPR	CG	Z
0.266	6.76	U-72	.34	8.7	.206	5.2	30	5.2	.19	4.8	5.6	25	.15	3.8	0.030	0.8	5.00	MW	CG	N
0.266	6.76	EE-26	.38	9.5	.214	5.4	8.4	1.5	.19	4.9	1.6	7.2	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.266	6.76	Y-5	.38	9.5	.210	5.3	19	3.4	.16	4.1	3.1	14	.14	3.6	0.028	0.7	5.00	SST	CG	N
0.266	6.76	S-1112	.38	9.5	.202	5.1	35	6.0	.13	3.4	4.6	20	.16	4.1	0.032	0.8	5.00	SST	CG	N
0.266	6.76	S-815	.38	9.5	.160	4.1	345	60	.05	1.3	18	78	.27	6.7	0.053	1.3	5.00	SST	CG	N
0.266	6.76	B2-38	.39	9.9	.210	5.3	22	3.8	.21	5.4	4.6	20	.17	4.3	0.028	0.7	5.00	MW	C	N
0.266	6.76	FF-5	.44	11.1	.242	6.1	.20	.04	.31	7.8	.06	.27	.13	3.4	0.012	0.3	10.0	SST	C	N
0.266	6.76	10790	.44	11.1	.206	5.2	20	3.4	.19	4.9	3.8	17	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.266	6.76	A9-6	.44	11.1	.184	4.7	90	16	.11	2.7	9.6	43	.25	6.2	0.041	1.0	6.00	SPR	CG	N
0.266	6.76	NN-43	.44	11.1	.184	4.7	58	10	.13	3.3	7.6	34	.31	7.8	0.041	1.0	7.50	SST	CG	N
0.266	6.76	12032	.47	11.9	.240	6.1	.53	.09	.37	9.3	.20	.87	.10	2.6	0.013	0.3	6.75	MW	C	N
0.266	6.76	KK-45	.47	11.9	.230	5.8	2.0	.35	.32	8.2	.65	2.9	.14	3.7	0.018	0.5	7.00	MW	C	Z
0.266	6.76	3416	.47	11.9	.226	5.7	3.1	.55	.31	7.8	.96	4.3	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.266	6.76	3232	.47	11.9	.214	5.4	19	3.4	.19	4.9	3.7	16	.14	3.6	0.026	0.7	4.50	MW	C	Z
0.266	6.76	S-1024	.47	11.9	.204	5.2	31	5.4	.14	3.4	4.2	18	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.266	6.76	S-1484	.47	11.9	.196	5.0	77	13	.07	1.9	5.7	25	.18	4.4	0.035	0.9	4.00	SST	C	N
0.266	6.76	I-36	.50	12.7	.226	5.7	3.2	.56	.36	9.0	1.1	5.1	.15	3.7	0.020	0.5	6.25	SST	C	N
0.266	6.76	L-																		




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.266	6.76	W-14	.50	12.7	.146	3.7	376	66	.07	1.7	25	111	.42	10.7	0.060	1.5	7.00	SST	CG	N
0.266	6.76	NN-49	.50	12.7	.142	3.6	491	86	.06	1.4	27	121	.40	10.2	0.062	1.6	6.50	SST	CG	N
0.266	6.76	O-146	.53	13.5	.202	5.1	26	4.5	.18	4.5	4.6	20	.19	4.9	0.032	0.8	6.00	SST	CG	N
0.266	6.76	UU-40	.53	13.5	.202	5.1	24	4.2	.21	5.2	4.9	22	.26	6.5	0.032	0.8	7.00	SPR	C	N
0.266	6.76	N-62	.53	13.5	.196	5.0	30	5.2	.21	5.2	6.1	27	.28	7.1	0.035	0.9	8.00	SPR	CG	N
0.266	6.76	B-53	.53	13.5	.180	4.6	95	17	.12	3.0	11	49	.29	7.4	0.043	1.1	6.75	SPR	CG	Z
0.266	6.76	A-73	.56	14.3	.238	6.0	.87	.15	.46	12	.41	1.8	.10	2.5	0.014	0.4	6.00	MW	C	GI
0.266	6.76	JJ-45	.56	14.3	.210	5.3	8.2	1.4	.28	7.2	2.3	10	.28	7.1	0.028	0.7	9.00	SST	C	N
0.266	6.76	JJ-91	.56	14.3	.210	5.3	9.5	1.7	.28	7.2	2.7	12	.28	7.1	0.028	0.7	9.00	MW	C	N
0.266	6.76	3713	.56	14.3	.202	5.1	24	4.2	.29	7.3	6.8	30	.22	5.7	0.032	0.8	7.00	MW	CG	Z
0.266	6.76	A11-60	.56	14.3	.202	5.1	17	2.9	.27	6.9	4.6	20	.27	6.8	0.032	0.8	8.33	SST	CG	N
0.266	6.76	L-85	.56	14.3	.192	4.9	41	7.2	.17	4.4	7.2	32	.28	7.0	0.037	0.9	7.50	SPR	CG	Z
0.266	6.76	B11-33	.59	15.1	.230	5.8	.82	.14	.34	8.7	.28	1.3	.25	6.4	0.018	0.5	14.0	MW	CG	N
0.266	6.76	A10-35	.59	15.1	.204	5.2	20	3.6	.20	5.2	4.2	18	.23	5.9	0.031	0.8	6.50	SST	C	N
0.266	6.76	O-143	.59	15.1	.186	4.7	70	12	.12	3.0	8.4	37	.28	7.1	0.040	1.0	6.00	SST	C	N
0.266	6.76	II-99	.59	15.1	.172	4.4	150	26	.09	2.3	13	59	.28	7.2	0.047	1.2	6.00	SST	CG	N
0.266	6.76	H-27	.63	15.9	.208	5.3	13	2.3	.39	10	5.1	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.266	6.76	S-156	.63	15.9	.204	5.2	30	5.3	.14	3.5	4.2	18	.19	4.7	0.031	0.8	5.00	SST	C	N
0.266	6.76	B8-34	.66	16.7	.212	5.4	9.0	1.6	.31	7.8	2.8	12	.20	5.1	0.027	0.7	7.50	SST	CG	N
0.266	6.76	3568	.66	16.7	.208	5.3	13	2.3	.40	10	5.1	23	.26	6.6	0.029	0.7	8.00	MW	C	Z
0.266	6.76	UU-37	.66	16.7	.186	4.7	35	6.1	.24	6.1	8.4	37	.40	10.2	0.040	1.0	10.0	SST	CG	N
0.266	6.76	N-12	.69	17.4	.248	6.3	.05	.01	.57	15	.03	.13	.11	2.9	0.009	0.2	11.8	SST	C	N
0.266	6.76	A13-51	.69	17.4	.238	6.0	.25	.04	.45	11	.11	.50	.24	6.0	0.014	0.4	16.0	SPR	C	N
0.266	6.76	II-88	.69	17.4	.216	5.5	3.5	.62	.36	9.2	1.3	5.7	.33	8.3	0.025	0.6	12.0	SST	C	N
0.266	6.76	B11-52	.69	17.4	.208	5.3	13	2.2	.40	10	5.1	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.266	6.76	10897	.69	17.4	.184	4.7	61	11	.15	3.8	9.0	40	.30	7.6	0.041	1.0	7.25	SST	CG	N
0.266	6.76	A9-64	.69	17.4	.180	4.6	72	13	.14	3.6	10	46	.32	8.1	0.043	1.1	7.50	SST	CG	N
0.266	6.76	L-90	.69	17.4	.168	4.3	127	22	.13	3.2	16	71	.42	10.6	0.049	1.2	8.50	SPR	CG	GI
0.266	6.76	HH-71	.72	18.2	.184	4.7	40	7.0	.24	6.1	9.6	43	.45	11.5	0.041	1.0	11.0	SPR	CG	GI
0.266	6.76	3104	.75	19.1	.238	6.0	.58	.10	.62	16	.36	1.6	.13	3.2	0.014	0.4	8.00	MW	C	Z
0.266	6.76	A-50	.75	19.1	.236	6.0	.29	.05	.47	12	.14	.60	.29	7.2	0.015	0.4	18.0	MW	C	Z
0.266	6.76	A-28	.75	19.1	.226	5.7	1.3	.23	.49	12	.64	2.9	.27	6.7	0.020	0.5	12.3	SST	C	N
0.266	6.76	A-72	.75	19.1	.216	5.5	5.1	.89	.50	13	2.5	11	.25	6.4	0.025	0.6	10.0	MW	CG	Z
0.266	6.76	4292	.75	19.1	.212	5.4	5.2	.90	.40	10	2.1	9.1	.35	8.9	0.027	0.7	13.0	MW	CG	Z
0.266	6.76	Y-76	.75	19.1	.206	5.2	9.8	1.7	.39	9.8	3.8	17	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.266	6.76	A15-22	.75	19.1	.202	5.1	12	2.1	.39	9.9	4.6	20	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.266	6.76	S-211	.75	19.1	.196	5.0	17	3.0	.33	8.4	5.7	25	.39	9.8	0.035	0.9	11.0	SST	CG	N
0.266	6.76	FF-28	.81	20.6	.222	5.6	3.4	.59	.59	15	2.0	8.8	.22	5.6	0.022	0.6	9.00	MW	C	Z
0.266	6.76	Q-66	.81	20.6	.220	5.6	6.2	1.1	.29	7.4	1.8	8.1	.16	4.1	0.023	0.6	6.00	SST	C	N
0.266	6.76	S-907	.81	20.6	.198	5.0	19	3.4	.28	7.1	5.4	24	.31	7.8	0.034	0.9	9.00	SST	CG	N
0.266	6.76	LL-46	.84	21.4	.222	5.6	2.2	.39	.57	15	1.3	5.6	.27	6.8	0.022	0.6	11.3	SST	C	N
0.266	6.76	N-128	.84	21.4	.206	5.2	20	3.4	.29	7.3	5.6	25	.23	5.7	0.030	0.8	6.50	MW	C	Z
0.266	6.76	VV-17	.88	22.2	.236	6.0	.31	.05	.64	16	.20	.88	.24	6.1	0.015	0.4	15.0	SST	C	N
0.266	6.76	Y-72	.88	22.2	.196	5.0	22	3.9	.27	7.0	6.1	27	.39	9.8	0.035	0.9	10.0	SPR	C	N
0.266	6.76	S-1585	.88	22.2	.184	4.7	29	5.0	.31	8.0	9.0	40	.53	13.5	0.041	1.0	13.0	SST	CG	N
0.266	6.76	XX-67	.88	22.2	.180	4.6	37	6.6	.27	6.9	10	45	.60	15.3	0.043	1.1	14.0	SPR	CG	Z
0.266	6.76	S-1527	.88	22.2	.176	4.5	51	8.9	.23	5.9	12	52	.56	14.3	0.045	1.1	11.5	SST	C	N
0.266	6.76	3774	.94	23.8	.216	5.5	2.9	.51	.54	14	1.6	6.9	.40	10.2	0.025	0.6	16.0	MW	CG	Z
0.266	6.76	3732	.94	23.8	.192	4.9	19	3.3	.38	9.6	7.2	32	.52	13.2	0.037	0.9	14.0	SPR	CG	Z
0.266	6.76	NN-71	.94	23.8	.146	3.7	251	44	.11	2.7	26	118	.63	16.0	0.060	1.5	10.5	SPR	CG	N
0.266	6.76	00-9	.97	24.6	.206	5.2	7.1	1.3	.53	13	3.8	17	.39	9.9	0.030	0.8	13.0	SST	CG	N
0.266	6.76	AA-41	1.00	25.4	.226	5.7	1.5	.26	.73	19	1.1	4.8	.27	6.9	0.020	0.5	12.5	MW	C	Z
0.266	6.76	KK-65	1.00	25.4	.208	5.3	8.1	1.4	.63	16	5.1	23	.36	9.2	0.029	0.7	11.5	MW	C	Z
0.266	6.76	L-43	1.00	25.4	.206	5.2	13	2.2	.44	11	5.6	25	.30	7.6	0.030	0.8	9.00	MW	C	Z
0.266	6.76	S-203	1.00	25.4	.202	5.1	9.4	1.6	.48	12	4.6	20	.45	11.4	0.032	0.8	13.0	SST	C	N
0.266	6.76	2895	1.00	25.4	.198	5.0	14	2.5	.56	14	7.9	35	.44	11.2	0.034	0.9	13.0	MW	CG	Z
0.266	6.76	JJ-69	1.00	25.4	.166	4.2	105	18	.15	3.8	16	71	.53	13.3	0.050	1.3	10.5	SPR	CG	N
0.266	6.76	12586	1.03	26.2	.216	5.5	3.3	.59	.66	17	2.2	9.8	.38	9.5	0.025	0.6	14.0	MW	C	Z
0.266	6.76	10537	1.03	26.2	.202	5.1	9.8	1.7	.58	15	5.7	25	.45	11.4	0.032	0.8	14.0	MW	CG	Z
0.266	6.76	B7-19	1.06	27.0	.210	5.3	5.7	1.0	.68	17	3.9	17	.38	9.6	0.028	0.7	13.5	MW	CG	N
0.266	6.76	A9-58	1.06	27.0	.204	5.2	6.8	1.2	.55	14	3.7	17	.51	13.0	0.031	0.8	15.5	SST	C	N
0.266	6.76	S-1151	1.06	27.0	.190	4.8	17	3.0	.42	11	7.2	32	.57	14.5	0.038	1.0	15.0	SST	CG	N
0.266	6.76	A15-28	1.09	27.8	.194	4.9	15	2.6	.44	11	6.6	29	.59	15.1	0.036	0.9	15.5	SPR	C	Z
0.266	6.76	N-43	1.13	28.6	.236	6.0	.31	.05	.89	22	.28	1.2	.24	6.1	0.015	0.4	15.0	SST	C	N
0.266	6.76	4195	1.13	28.6	.228	5.8	.90	.16	.80	20	.72	3.2	.32	8.2	0.019	0.5	16.0	MW	C	Z
0.266	6.76	VV-14	1.13	28.6	.220	5.6	2.9	.51	.63	16	1.8	8.1	.26	6.7	0.023	0.6	10.5	SST	C	N
0.266	6.76	2523	1.13	28.6	.208	5.3	5.7	.99	.65	16	3.7	16	.48	12.2	0.029	0.7	15.5	MW	C	Z
0.266	6.76	10350	1.13	28.6	.176	4.5	44	7.7	.29	7.3	13	56	.65	16.6	0.045	1.1	14.5	SPR	CG	N
0.266	6.76	B7-12	1.13	28.6	.176	4.5	38	6.7	.33	8.3	13	56	.73	18.6	0.045	1.1	16.3	SPR	CG	N
0.266	6.76	EE-43	1.13	28.6	.166															




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.266	6.76	M-26	1.38	34.9	.236	6.0	.38	.07	1.2	29	.44	2.0	.23	5.7	0.015	0.4	14.0	MW	C	Z
0.266	6.76	VV-59	1.38	34.9	.232	5.9	.79	.14	1.2	29	.91	4.0	.22	5.6	0.017	0.4	12.0	MW	C	Z
0.266	6.76	3264	1.38	34.9	.206	5.2	4.3	.75	.66	17	2.8	12	.72	18.3	0.030	0.8	23.0	MW	C	Z
0.266	6.76	3844	1.38	34.9	.206	5.2	3.9	.68	.60	15	2.3	10	.78	19.8	0.030	0.8	25.0	MW	C	N
0.266	6.76	S-1494	1.38	34.9	.170	4.3	39	6.8	.37	9.3	14	63	.90	22.9	0.048	1.2	18.8	SST	CG	N
0.266	6.76	10952	1.41	35.7	.184	4.7	28	4.9	.34	8.7	9.6	43	.65	16.4	0.041	1.0	14.8	SPR	C	N
0.266	6.76	12418	1.44	36.5	.218	5.5	3.1	.54	1.1	28	3.16	14.1	.34	8.5	0.024	0.6	13.0	MW	C	N
0.266	6.76	YY-57	1.44	36.5	.200	5.1	11	2.0	.47	12	5.4	24	.50	12.6	0.033	0.8	14.0	SPR	C	Z
0.266	6.76	11191	1.47	37.3	.186	4.7	24	4.2	.37	9.5	9.0	40	.65	16.5	0.040	1.0	15.3	SPR	C	Z
0.266	6.76	11418	1.50	38.1	.186	4.7	25	4.3	.37	9.3	9.0	40	.64	16.3	0.040	1.0	15.0	SPR	C	Z
0.266	6.76	2886	1.53	38.9	.200	5.1	8.0	1.4	.67	17	5.4	24	.53	13.4	0.033	0.8	16.0	SPR	CG	GI
0.266	6.76	1515	1.53	38.9	.196	5.0	12	2.2	.69	17	8.4	37	.57	14.5	0.035	0.9	16.3	MW	CG	GI
0.266	6.76	S-1354	1.56	39.7	.204	5.2	6.9	1.2	.60	15	4.2	18	.50	12.6	0.031	0.8	15.0	SST	C	N
0.266	6.76	3198	1.56	39.7	.202	5.1	9.2	1.6	.74	19	6.8	30	.51	13.0	0.032	0.8	15.0	MW	C	Z
0.266	6.76	NN-33	1.63	41.3	.222	5.6	1.3	.22	1.2	31	1.6	7.0	.40	10.1	0.022	0.6	18.0	SST	CG	N
0.266	6.76	3528	1.69	42.8	.212	5.4	2.0	.34	.85	22	1.7	7.4	.84	21.3	0.027	0.7	31.0	MW	CG	Z
0.266	6.76	2530	1.78	45.2	.220	5.6	.73	.13	.83	21	.60	2.7	.96	24.3	0.023	0.6	40.5	MW	C	Z
0.266	6.76	B11-56	1.88	47.6	.204	5.2	6.8	1.2	.91	23	6.2	28	.56	14.2	0.031	0.8	17.0	MW	C	Z
0.266	6.76	10043	1.88	47.6	.196	5.0	18	3.1	.34	8.7	6.1	27	.46	11.6	0.035	0.9	12.0	SPR	C	Z
0.266	6.76	A10-2	1.88	47.6	.170	4.3	88	15	.17	4.4	15	67	.50	12.8	0.048	1.2	10.5	SPR	CG	N
0.266	6.76	DD-66	1.94	49.2	.192	4.9	7.6	1.3	.88	22	6.7	30	1.04	26.3	0.037	0.9	28.0	SST	CG	N
0.266	6.76	3300	2.00	50.8	.210	5.3	3.7	.65	1.2	32	4.6	20	.59	14.9	0.028	0.7	20.0	MW	C	Z
0.266	6.76	3784	2.00	50.8	.190	4.8	9.9	1.7	.78	20	7.7	34	1.10	28.0	0.038	1.0	28.0	SPR	C	Z
0.266	6.76	10755	2.06	52.4	.192	4.9	7.7	1.3	.88	22	6.7	30	1.07	27.3	0.037	0.9	28.0	SST	C	N
0.266	6.76	10892	2.13	54.0	.222	5.6	1.0	.18	1.5	39	1.6	7.1	.48	12.3	0.022	0.6	22.0	SST	CG	N
0.266	6.76	YY-52	2.13	54.0	.176	4.5	25	4.4	.47	12	12	52	.99	25.1	0.045	1.1	21.0	SST	C	N
0.266	6.76	U-44	2.25	57.2	.214	5.4	1.9	.32	1.5	38	2.8	12	.75	19.2	0.026	0.7	28.0	MW	C	Z
0.266	6.76	K-91	2.25	57.2	.158	4.0	52	9.1	.38	9.6	20	88	1.46	37.0	0.054	1.4	27.0	SPR	CG	Z
0.266	6.76	II-28	2.28	57.9	.166	4.2	24	4.2	.53	13	13	57	1.75	44.5	0.050	1.3	35.0	SST	CG	N
0.266	6.76	3312	2.31	58.7	.212	5.4	2.5	.43	1.6	41	4.0	18	.70	17.8	0.027	0.7	25.0	MW	C	Z
0.266	6.76	00-5	2.31	58.7	.146	3.7	77	14	.34	8.7	26	118	1.77	45.0	0.060	1.5	29.5	SPR	CG	Z
0.266	6.76	3915	2.50	63.5	.190	4.8	9.0	1.6	.86	22	7.7	34	1.20	30.4	0.038	1.0	30.5	SPR	C	Z
0.266	6.76	11462	3.00	76.2	.190	4.8	9.0	1.6	1.2	30	11	48	1.14	29.0	0.038	1.0	30.0	MW	CG	Z
0.266	6.76	UU-55	4.00	101.6	.212	5.4	.88	.15	2.4	61	2.1	9.4	1.59	40.5	0.027	0.7	58.0	SST	C	N
0.266	6.76	10435	4.06	103.2	.184	4.7	7.9	1.4	1.2	31	9.6	43	1.93	48.9	0.041	1.0	47.0	SPR	CG	N
0.275	6.99	A16-69	.94	23.8	.177	4.5	80	14	.27	6.9	22	96	.54	13.7	0.049	1.2	11.0	MW	CG	Z
0.281	7.14	10688	.22	5.6	.231	5.9	33	5.9	.09	2.4	3.1	14	.10	2.5	0.025	0.6	3.00	MW	C	N
0.281	7.14	10684	.25	6.4	.221	5.6	29	5.1	.09	2.3	2.7	12	.16	4.0	0.030	0.8	4.25	SST	C	N
0.281	7.14	12653	.25	6.4	.221	5.6	49	8.6	.11	2.8	5.4	24	.14	3.4	0.030	0.8	3.50	MW	C	N
0.281	7.14	00-62	.25	6.4	.217	5.5	49	8.5	.10	2.4	4.7	21	.13	3.3	0.032	0.8	4.00	SPR	CG	N
0.281	7.14	DD-26	.28	7.1	.217	5.5	22	3.8	.09	2.3	1.9	8.6	.19	4.9	0.032	0.8	6.00	SST	CG	N
0.281	7.14	VV-63	.28	7.1	.211	5.4	72	13	.08	2.0	5.8	26	.18	4.4	0.035	0.9	4.00	SPR	C	Z
0.281	7.14	A9-56	.31	7.9	.257	6.5	.34	.06	.22	5.6	.08	.34	.09	2.3	0.012	0.3	6.50	MW	C	N
0.281	7.14	L-83	.31	7.9	.229	5.8	11	2.0	.18	4.6	2.1	9.3	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.281	7.14	11439	.34	8.7	.221	5.6	29	5.1	.12	3.1	3.6	16	.16	4.0	0.030	0.8	4.25	SST	C	N
0.281	7.14	933	.38	9.5	.201	5.1	75	13	.11	2.9	8.5	38	.26	6.6	0.040	1.0	5.50	HD	C	Z
0.281	7.14	VW-46	.38	9.5	.175	4.4	319	56	.06	1.4	18	80	.27	6.7	0.053	1.3	5.00	SPR	CG	Z
0.281	7.14	930	.38	9.5	.173	4.4	348	61	.05	1.3	18	79	.32	8.2	0.054	1.4	5.00	HD	C	Z
0.281	7.14	I-72	.38	9.5	.131	3.3	2601	456	.02	.43	44	196	.30	7.6	0.075	1.9	4.00	SPR	CG	N
0.281	7.14	II-51	.41	10.3	.249	6.3	.68	.12	.25	6.5	.17	.77	.15	3.9	0.016	0.4	8.50	SST	C	N
0.281	7.14	10744	.41	10.3	.225	5.7	18	3.2	.24	6.0	4.3	19	.17	4.3	0.028	0.7	5.00	MW	C	N
0.281	7.14	Z-13	.41	10.3	.211	5.4	32	5.5	.17	4.4	5.4	24	.21	5.3	0.035	0.9	6.00	SST	C	N
0.281	7.14	NN-17	.41	10.3	.147	3.7	985	173	.03	.89	34	153	.34	8.5	0.067	1.7	5.00	SPR	CG	Z
0.281	7.14	J-12	.41	10.3	.139	3.5	1315	230	.03	.74	38	170	.36	9.0	0.071	1.8	5.00	SPR	CG	N
0.281	7.14	MM-61	.44	11.1	.251	6.4	.34	.06	.24	6.2	.08	.36	.20	5.0	0.015	0.4	12.0	SST	C	N
0.281	7.14	NN-14	.44	11.1	.243	6.2	1.6	.29	.28	7.0	.46	2.0	.16	4.1	0.019	0.5	7.50	SST	C	N
0.281	7.14	2913	.44	11.1	.211	5.4	48	8.5	.12	3.0	5.8	26	.21	5.3	0.035	0.9	5.00	SPR	C	Z
0.281	7.14	EE-13	.44	11.1	.211	5.4	36	6.3	.15	3.8	5.4	24	.19	4.9	0.035	0.9	5.50	SST	CG	N
0.281	7.14	RR-56	.44	11.1	.209	5.3	41	7.2	.15	3.9	6.3	28	.25	6.4	0.036	0.9	6.00	SPR	C	Z
0.281	7.14	3900	.44	11.1	.201	5.1	66	12	.13	3.3	8.5	38	.28	7.1	0.040	1.0	6.00	SPR	C	Z
0.281	7.14	AA-20	.44	11.1	.201	5.1	47	8.2	.16	4.0	7.4	33	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.281	7.14	B-79	.44	11.1	.187	4.7	136	24	.09	2.4	13	57	.26	6.6	0.047	1.2	5.50	SST	CG	N
0.281	7.14	S-1058	.44	11.1	.173	4.4	260	45	.07	1.7	18	79	.30	7.5	0.054	1.4	5.50	SST	CG	N
0.281	7.14	A9-1	.47	11.9	.237	6.0	2.3	.40	.26	6.6	.59	2.6	.21	5.3	0.022	0.6	9.50	SST	CG	N
0.281	7.14	DD-18	.47	11.9	.217	5.5	9.6	1.7	.08	2.1	.81	3.6	.38	9.8	0.032	0.8	11.0	SST	C	N
0.281	7.14	10945	.47	11.9	.215	5.5	37	6.5	.19	4.8	7.1	31	.20	5.0	0.033	0.8	5.00	MW	C	Z
0.281	7.14	A-63	.47	11.9	.203	5.2	78	14	.10	2.6	7.9	35	.20	5.0	0.039	1.0	5.00	SPR	CG	Z
0.281	7.14	J-66	.47	11.9	.189	4.8	104	18	.12	3.1	13	57	.31	7.9	0.046	1.2	6.75	SPR	CG	N
0.281	7.14	W-87	.50	12.7																




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.281	7.14	B2-37	.55	13.9	.201	5.1	46	8.0	.17	4.4	8.0	36	.32	8.1	0.040	1.0	7.00	SST	C	N
0.281	7.14	S-1078	.56	14.3	.231	5.9	9.7	1.7	.22	5.5	2.1	9.3	.15	3.8	0.025	0.6	14.0	SST	C	N
0.281	7.14	3467	.56	14.3	.229	5.8	13	2.3	.19	4.9	2.5	11	.13	3.3	0.026	0.7	5.00	HD	CG	Z
0.281	7.14	A9-50	.56	14.3	.219	5.6	19	3.3	.31	7.9	5.9	26	.23	5.9	0.031	0.8	6.50	MW	C	GI
0.281	7.14	LL-21	.56	14.3	.219	5.6	21	3.7	.28	7.0	5.9	26	.22	5.5	0.031	0.8	6.00	MW	C	N
0.281	7.14	DD-36	.56	14.3	.205	5.2	30	5.3	.23	5.8	6.9	31	.30	7.7	0.038	1.0	8.00	SST	CG	N
0.281	7.14	K-6	.56	14.3	.201	5.1	66	12	.13	3.3	8.5	38	.24	6.1	0.040	1.0	6.00	SPR	CG	Z
0.281	7.14	Q-13	.56	14.3	.187	4.7	100	17	.14	3.5	14	60	.35	9.0	0.047	1.2	7.50	SPR	CG	Z
0.281	7.14	M-25	.56	14.3	.179	4.5	158	28	.10	2.4	15	67	.33	8.4	0.051	1.3	6.50	SST	CG	N
0.281	7.14	S-1181	.56	14.3	.177	4.5	169	30	.09	2.4	16	71	.34	8.6	0.052	1.3	6.50	SST	CG	N
0.281	7.14	S-1076	.56	14.3	.173	4.4	182	32	.10	2.5	18	79	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.281	7.14	J-57	.59	15.1	.233	5.9	6.6	1.2	.42	11	2.8	12	.17	4.4	0.024	0.6	6.25	MW	C	GI
0.281	7.14	10845	.59	15.1	.231	5.9	4.2	.74	.37	9.3	1.6	6.9	.23	5.7	0.025	0.6	9.00	SST	CG	N
0.281	7.14	S-1366	.59	15.1	.187	4.7	79	14	.16	4.1	13	57	.38	9.6	0.047	1.2	8.00	SST	CG	N
0.281	7.14	S-1044	.59	15.1	.185	4.7	89	16	.15	3.9	14	60	.38	9.8	0.048	1.2	8.00	SST	CG	N
0.281	7.14	11836	.59	15.1	.185	4.7	89	16	.15	3.9	14	60	.38	9.8	0.048	1.2	8.00	SST	CG	N
0.281	7.14	B9-4	.63	15.9	.237	6.0	8.6	1.5	.26	6.7	2.3	10	.12	2.9	0.022	0.6	4.25	MW	C	BO
0.281	7.14	A9-28	.63	15.9	.219	5.6	15	2.7	.36	9.2	5.6	25	.26	6.7	0.031	0.8	7.50	MW	C	GI
0.281	7.14	GG-33	.63	15.9	.205	5.2	29	5.0	.24	6.1	6.9	31	.32	8.2	0.038	1.0	8.50	SST	CG	N
0.281	7.14	3888	.63	15.9	.201	5.1	44	7.7	.19	4.9	8.5	38	.32	8.1	0.040	1.0	8.00	SPR	CG	Z
0.281	7.14	Y-32	.63	15.9	.195	5.0	54	9.4	.18	4.6	9.9	44	.34	8.7	0.043	1.1	8.00	SST	CG	N
0.281	7.14	B-76	.66	16.7	.223	5.7	10	1.8	.32	8.0	3.2	14	.25	6.3	0.029	0.7	7.50	SST	C	N
0.281	7.14	A9-53	.66	16.7	.219	5.6	13	2.2	.31	8.0	3.9	18	.25	6.3	0.031	0.8	8.00	SST	CG	N
0.281	7.14	BB-18	.69	17.4	.257	6.5	.10	.02	.48	12	.05	.20	.20	5.2	0.012	0.3	16.0	SST	C	N
0.281	7.14	12652	.69	17.4	.247	6.3	1.3	.23	.55	14	.72	3.2	.14	3.5	0.017	0.4	7.00	MW	C	Z
0.281	7.14	3543	.69	17.4	.233	5.9	8.0	1.4	.37	9.3	2.9	13	.16	4.0	0.024	0.6	5.50	MW	C	Z
0.281	7.14	B9-42	.69	17.4	.233	5.9	2.3	.41	.35	8.9	.82	3.7	.34	8.5	0.024	0.6	14.0	MW	CG	N
0.281	7.14	JJ-77	.69	17.4	.231	5.9	8.4	1.5	.37	9.5	3.1	14	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.281	7.14	10885	.69	17.4	.221	5.6	11	2.0	.40	10	4.6	20	.29	7.2	0.030	0.8	8.50	MW	C	GI
0.281	7.14	S-1252	.69	17.4	.219	5.6	15	2.6	.27	6.8	3.9	18	.22	5.5	0.031	0.8	7.00	SST	CG	N
0.281	7.14	3592	.69	17.4	.217	5.5	18	3.1	.36	9.3	6.5	29	.27	6.9	0.032	0.8	7.50	MW	C	Z
0.281	7.14	DD-91	.69	17.4	.215	5.5	14	2.4	.34	8.7	4.7	21	.33	8.4	0.033	0.8	9.00	SST	C	N
0.281	7.14	HH-17	.69	17.4	.205	5.2	34	5.9	.20	5.2	6.9	31	.29	7.2	0.038	1.0	7.50	SST	CG	N
0.281	7.14	XX-12	.69	17.4	.187	4.7	100	17	.14	3.5	14	60	.35	9.0	0.047	1.2	7.50	SPR	CG	Z
0.281	7.14	AA-32	.69	17.4	.181	4.6	104	18	.15	3.7	15	67	.45	11.4	0.050	1.3	9.00	SPR	CG	N
0.281	7.14	A-100	.72	18.2	.233	5.9	4.3	.76	.49	12	2.1	9.4	.23	5.8	0.024	0.6	8.50	MW	C	Z
0.281	7.14	10170	.72	18.2	.231	5.9	5.1	.90	.48	12	2.5	11	.24	6.0	0.025	0.6	8.50	MW	C	N
0.281	7.14	DD-41	.72	18.2	.201	5.1	67	12	.12	3.0	8.0	36	.26	6.6	0.040	1.0	5.50	SST	C	N
0.281	7.14	DD-53	.75	19.1	.249	6.3	1.1	.19	.53	14	.59	2.6	.11	2.8	0.016	0.4	6.00	SST	C	N
0.281	7.14	4294	.75	19.1	.231	5.9	5.1	.90	.51	13	2.6	12	.24	6.0	0.025	0.6	8.50	MW	C	N
0.281	7.14	3710	.75	19.1	.225	5.7	9.1	1.6	.48	12	4.4	19	.22	5.7	0.028	0.7	8.00	MW	CG	GI
0.281	7.14	S-927	.75	19.1	.225	5.7	10	1.8	.29	7.3	2.9	13	.22	5.5	0.028	0.7	6.75	SST	C	N
0.281	7.14	M-130	.75	19.1	.219	5.6	9.2	1.6	.41	10	3.8	17	.34	8.7	0.031	0.8	10.0	SST	C	N
0.281	7.14	G-20	.75	19.1	.217	5.5	9.8	1.7	.37	9.3	3.6	16	.38	9.8	0.032	0.8	12.0	HD	CG	N
0.281	7.14	B-91	.75	19.1	.217	5.5	12	2.1	.38	9.7	4.7	21	.35	8.9	0.032	0.8	10.0	HD	C	N
0.281	7.14	G-67	.75	19.1	.201	5.1	31	5.4	.26	6.5	8.0	36	.38	9.7	0.040	1.0	9.50	SST	CG	N
0.281	7.14	VV-68	.75	19.1	.199	5.1	37	6.4	.24	6.0	8.6	38	.41	10.4	0.041	1.0	9.00	SST	C	N
0.281	7.14	S-914	.78	19.8	.249	6.3	1.1	.20	.52	13	.59	2.6	.11	2.8	0.016	0.4	6.00	SST	C	N
0.281	7.14	I-97	.78	19.8	.245	6.2	1.2	.21	.62	16	.76	3.4	.16	4.1	0.018	0.5	8.00	SST	C	N
0.281	7.14	HH-49	.78	19.8	.229	5.8	6.0	1.0	.39	10	2.4	10	.23	5.8	0.026	0.7	7.75	SST	C	N
0.281	7.14	JJ-65	.78	19.8	.201	5.1	29	5.1	.29	7.4	8.5	38	.44	11.2	0.040	1.0	11.0	SPR	CG	Z
0.281	7.14	W-94	.81	20.6	.253	6.4	.42	.07	.69	17	.29	1.3	.13	3.2	0.014	0.4	8.00	SST	C	N
0.281	7.14	S-363	.81	20.6	.251	6.4	.19	.03	.50	13	.09	.41	.32	8.0	0.015	0.4	20.0	SST	C	N
0.281	7.14	O-64	.81	20.6	.219	5.6	10.6	1.9	.375	9.53	4.0	18.1	.280	7.08	0.031	0.8	9.00	SST	CG	N
0.281	7.14	3703	.84	21.4	.191	4.9	56	9.8	.21	5.4	12	53	.45	11.4	0.045	1.1	10.0	SPR	CG	Z
0.281	7.14	3609	.88	22.2	.249	6.3	.46	.08	.65	17	.30	1.3	.22	5.7	0.016	0.4	13.0	MW	C	Z
0.281	7.14	EE-28	.88	22.2	.241	6.1	2.0	.35	.69	17	1.4	6.1	.19	4.8	0.020	0.5	8.50	MW	C	N
0.281	7.14	S-1190	.88	22.2	.223	5.7	12	2.0	.28	7.1	3.2	14	.22	5.7	0.029	0.7	6.75	SST	C	N
0.281	7.14	A10-19	.88	22.2	.213	5.4	15	2.7	.50	13	7.7	34	.35	8.9	0.034	0.9	10.3	MW	CG	N
0.281	7.14	OO-64	.88	22.2	.211	5.4	18	3.2	.32	8.1	5.8	26	.35	8.9	0.035	0.9	10.0	SPR	CG	N
0.281	7.14	Q-88	.88	22.2	.209	5.3	21	3.6	.31	7.8	6.3	28	.40	10.1	0.036	0.9	10.0	SPR	C	GI
0.281	7.14	AA-17	.88	22.2	.181	4.6	79	14	.18	4.6	14	63	.50	12.7	0.050	1.3	10.0	SST	CG	N
0.281	7.14	3531	.91	23.0	.201	5.1	29	5.1	.40	10	12	53	.44	11.2	0.040	1.0	11.0	MW	CG	GI
0.281	7.14	U-14	.91	23.0	.199	5.1	37	6.4	.25	6.3	9.2	41	.41	10.4	0.041	1.0	10.0	SPR	CG	GI
0.281	7.14	G-53	.94	23.8	.245	6.2	1.3	.22	.77	19	.98	4.4	.17	4.3	0.018	0.5	8.50	MW	C	N
0.281	7.14	HH-28	.94	23.8	.245	6.2	1.1	.19	.75	19	.83	3.7	.19	4.8	0.018	0.5	9.50	MW	C	BO
0.281	7.14	CC-28	.94	23.8	.241	6.1	1.4	.25	.70	18	1.0	4.5	.24	6.1	0.020	0.5	11.0	MW	C	Z
0.281	7.14	S-107	.94	23.8	.225	5.7	5.8	1.0	.51	13	2.9	13	.32	8.0	0.028	0.7	10.3	SST	C	N
0.281	7.14	10827	1.00	25.4	.251	6.4	.62	.11	.78	20	.48	2.2	.11	2.9	0.015	0.4	7.50	SST	CG	N
0.281	7.14	2632	1.00	25.4	.251	6.4	.32	.06	.78	20</										




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.281	7.14	S-998	1.00	25.4	.181	4.6	63	11	.23	5.7	14	63	.60	15.2	0.050	1.3	12.0	SST	CG	N
0.281	7.14	BB-51	1.00	25.4	.181	4.6	81	14	.19	4.8	15	67	.55	14.0	0.050	1.3	11.0	SPR	CG	N
0.281	7.14	S-1053	1.00	25.4	.177	4.5	90	16	.18	4.5	16	71	.55	13.9	0.052	1.3	10.5	SST	CG	N
0.281	7.14	934	1.00	25.4	.173	4.4	149	26	.13	3.2	19	84	.54	13.7	0.054	1.4	9.00	HD	C	Z
0.281	7.14	BB-90	1.00	25.4	.173	4.4	104	18	.18	4.6	19	84	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.281	7.14	KK-88	1.00	25.4	.157	4.0	202	35	.14	3.5	28	124	.74	18.9	0.062	1.6	12.0	SPR	CG	N
0.281	7.14	10983	1.03	26.2	.219	5.6	8.4	1.5	.47	12	3.9	18	.34	8.7	0.031	0.8	11.0	SST	CG	N
0.281	7.14	11352	1.03	26.2	.211	5.4	9.3	1.6	.44	11	4.2	18	.59	14.9	0.035	0.9	15.8	SST	C	N
0.281	7.14	H-13	1.06	27.0	.237	6.0	1.2	.22	.71	18	.87	3.9	.35	8.9	0.022	0.6	16.0	SST	CG	N
0.281	7.14	Q-92	1.06	27.0	.201	5.1	22	3.8	.39	9.9	8.5	38	.56	14.2	0.040	1.0	14.0	SPR	CG	Z
0.281	7.14	2630	1.09	27.8	.245	6.2	.92	.16	.88	22	.81	3.6	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.281	7.14	L-7	1.09	27.8	.229	5.8	4.4	.77	.78	20	3.4	15	.31	7.9	0.026	0.7	11.0	MW	C	N
0.281	7.14	H-59	1.09	27.8	.211	5.4	11	2.0	.52	13	5.8	26	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.281	7.14	HH-99	1.13	28.6	.243	6.2	.82	.14	.86	22	.71	3.1	.27	6.8	0.019	0.5	13.0	SST	C	N
0.281	7.14	3995	1.13	28.6	.225	5.7	4.8	.85	.73	18	3.5	16	.40	10.1	0.028	0.7	13.3	MW	C	Z
0.281	7.14	EE-57	1.13	28.6	.221	5.6	6.7	1.2	.71	18	4.7	21	.42	10.7	0.030	0.8	13.0	MW	C	N
0.281	7.14	3510	1.13	28.6	.215	5.5	10	1.8	.66	17	6.7	30	.46	11.7	0.033	0.8	13.0	MW	C	Z
0.281	7.14	2839	1.13	28.6	.213	5.4	9.3	1.6	.56	14	5.2	23	.57	14.5	0.034	0.9	15.8	MW	C	Z
0.281	7.14	3767	1.13	28.6	.211	5.4	13	2.3	.44	11	5.8	26	.46	11.6	0.035	0.9	13.0	SPR	C	Z
0.281	7.14	3450	1.19	30.2	.233	5.9	2.6	.45	.85	22	2.2	9.7	.34	8.5	0.024	0.6	13.0	MW	C	Z
0.281	7.14	A13-52	1.19	30.2	.209	5.3	8.4	1.5	.49	13	4.2	19	.69	17.6	0.036	0.9	19.3	SST	CG	N
0.281	7.14	1729	1.25	31.8	.265	6.7	.04	.01	1.2	30	.04	.19	.09	2.2	0.008	0.2	10.0	MW	C	TI
0.281	7.14	DD-20	1.25	31.8	.245	6.2	1.0	.18	1.1	27	1.1	4.9	.20	5.0	0.018	0.5	10.0	MW	C	N
0.281	7.14	O-83	1.25	31.8	.243	6.2	.80	.14	.95	24	.76	3.4	.30	7.7	0.019	0.5	15.0	MW	C	N
0.281	7.14	410	1.25	31.8	.231	5.9	2.0	.34	.95	24	1.8	8	.31	7.8	0.025	0.6	11.3	B	C	BO
0.281	7.14	3806	1.25	31.8	.225	5.7	5.2	.91	.84	21	4.4	19	.38	9.6	0.028	0.7	12.5	MW	C	GI
0.281	7.14	I-65	1.25	31.8	.225	5.7	4.7	.83	.84	21	4.0	18	.41	10.3	0.028	0.7	13.5	MW	C	Z
0.281	7.14	4212	1.25	31.8	.219	5.6	7.1	1.2	.79	20	5.6	25	.47	11.8	0.031	0.8	14.0	MW	C	Z
0.281	7.14	A11-56	1.25	31.8	.215	5.5	9.3	1.6	.55	14	5.1	23	.46	11.7	0.033	0.8	14.0	SPR	CG	N
0.281	7.14	3585	1.25	31.8	.195	5.0	36	6.4	.29	7.3	11	47	.52	13.1	0.043	1.1	12.0	SPR	CG	Z
0.281	7.14	NN-99	1.25	31.8	.181	4.6	56	9.8	.27	6.9	15	67	.75	19.1	0.050	1.3	15.0	SPR	CG	Z
0.281	7.14	B10-46	1.28	32.5	.211	5.4	16	2.8	.36	9.1	5.8	26	.39	9.8	0.035	0.9	11.0	SPR	CG	N
0.281	7.14	1637	1.28	32.5	.165	4.2	173	30	.13	3.4	23	103	.61	15.5	0.058	1.5	10.5	SPR	CG	Z
0.281	7.14	1927	1.31	33.3	.237	6.0	2.4	.42	.94	24	2.3	10	.24	6.1	0.022	0.6	10.0	MW	C	GI
0.281	7.14	B11-49	1.31	33.3	.199	5.1	33	5.7	.28	7.1	9.2	41	.45	11.5	0.041	1.0	11.0	SPR	CG	Z
0.281	7.14	NN-65	1.34	34.1	.229	5.8	3.6	.63	.98	25	3.5	16	.36	9.2	0.026	0.7	13.0	MW	C	N
0.281	7.14	10911	1.34	34.1	.191	4.9	33	5.8	.36	9.2	12	53	.74	18.9	0.045	1.1	15.5	SPR	C	N
0.281	7.14	W-4	1.34	34.1	.161	4.1	125	22	.19	4.8	24	106	.84	21.3	0.060	1.5	14.0	SST	CG	N
0.281	7.14	00-92	1.38	34.9	.251	6.4	.39	.07	1.2	30	.46	2.0	.20	5.0	0.015	0.4	12.0	MW	C	N
0.281	7.14	4	1.38	34.9	.225	5.7	4.4	.76	.94	24	4.1	18	.43	11.0	0.028	0.7	14.5	MW	C	Z
0.281	7.14	3772	1.38	34.9	.221	5.6	4.1	.72	.75	19	3.0	14	.63	16.0	0.030	0.8	20.0	MW	C	Z
0.281	7.14	AA-9	1.38	34.9	.221	5.6	8.2	1.4	.65	17	5.4	24	.33	8.4	0.030	0.8	11.0	MW	CG	Z
0.281	7.14	3630	1.38	34.9	.181	4.6	43	7.5	.43	11	18	81	.95	24.1	0.050	1.3	19.0	MW	CG	Z
0.281	7.14	HH-9	1.38	34.9	.181	4.6	73	13	.21	5.3	15	67	.60	15.2	0.050	1.3	12.0	SPR	CG	N
0.281	7.14	2964	1.41	35.7	.219	5.6	6.1	1.1	.88	22	5.3	24	.53	13.4	0.031	0.8	16.0	MW	C	Z
0.281	7.14	2655	1.41	35.7	.215	5.5	10	1.8	.70	18	7.1	31	.46	11.7	0.033	0.8	13.0	MW	C	Z
0.281	7.14	LL-47	1.44	36.5	.221	5.6	7.0	1.2	.76	19	5.4	24	.41	10.3	0.030	0.8	12.5	MW	C	Z
0.281	7.14	S-1075	1.50	38.1	.217	5.5	5.3	.93	.82	21	4.3	19	.58	14.6	0.032	0.8	18.0	SST	CG	N
0.281	7.14	NN-72	1.50	38.1	.201	5.1	10	1.8	.50	13	5.1	23	1.00	25.4	0.040	1.0	25.0	SST	CG	N
0.281	7.14	JJ-85	1.50	38.1	.171	4.3	95	17	.21	5.3	20	88	.77	19.6	0.055	1.4	14.0	SPR	CG	Z
0.281	7.14	HH-41	1.56	39.7	.181	4.6	33	5.8	.43	11	14	63	1.08	27.3	0.050	1.3	21.5	SST	CG	N
0.281	7.14	L-60-A	1.63	41.3	.231	5.9	2.0	.36	1.1	29	2.3	10	.49	12.4	0.025	0.6	18.5	MW	C	N
0.281	7.14	S-1145	1.63	41.3	.231	5.9	.83	.15	.68	17	.56	2.5	.95	24.1	0.025	0.6	37.0	SST	C	N
0.281	7.14	2795	1.63	41.3	.223	5.7	4.0	.70	1.1	27	4.3	19	.55	14.0	0.029	0.7	18.0	MW	C	Z
0.281	7.14	HH-59	1.63	41.3	.221	5.6	5.3	.92	1.0	26	5.4	24	.48	12.2	0.030	0.8	16.0	MW	CG	GI
0.281	7.14	BB-91	1.63	41.3	.211	5.4	7.0	1.2	.77	20	5.4	24	.70	17.8	0.035	0.9	20.0	SST	CG	N
0.281	7.14	10433	1.63	41.3	.199	5.1	17	3.0	.54	14	9.2	41	.79	20.0	0.041	1.0	19.3	SPR	CG	N
0.281	7.14	UU-67	1.75	44.5	.243	6.2	.65	.11	1.4	36	.92	4.1	.32	8.2	0.019	0.5	16.0	SST	C	N
0.281	7.14	S-1338	1.75	44.5	.241	6.1	.75	.13	1.4	35	1.0	4.6	.36	9.1	0.020	0.5	17.0	SST	C	N
0.281	7.14	3622	1.84	46.8	.153	3.9	157	28	.27	6.8	42	187	1.15	29.3	0.064	1.6	17.0	MW	C	Z
0.281	7.14	K-33	2.00	50.8	.233	5.9	1.8	.32	1.6	40	2.8	13	.44	11.3	0.024	0.6	17.5	MW	C	Z
0.281	7.14	L-38	2.00	50.8	.225	5.7	2.6	.45	1.3	34	3.5	15	.67	17.1	0.028	0.7	23.0	MW	C	Z
0.281	7.14	S-1368	2.00	50.8	.215	5.5	3.8	.66	1.1	28	4.1	18	.92	23.3	0.033	0.8	27.8	SST	CG	N
0.281	7.14	NN-12	2.03	51.6	.201	5.1	8.6	1.5	.87	22	7.5	33	1.16	29.5	0.040	1.0	29.0	SST	CG	N
0.281	7.14	12331	2.06	52.4	.225	5.7	2.6	.45	1.4	35	3.6	16	.67	17.1	0.028	0.7	23.0	MW	C	Z
0.281	7.14	B10-35	2.44	61.9	.223	5.7	3.7	.64	1.3	33	4.8	22	.59	14.9	0.029	0.7	19.3	MW	C	Z
0.281	7.14	10812	2.50	63.5	.243	6.2	.31	.05	1.9	48	.58	2.6	.61	15.4	0.019	0.5	32.0	SST	CG	N
0.281	7.14	B11-65	2.53	64.3	.183	4.6	30	5.3	.51	13	15	68	1.23	31.1	0.049	1.2	24.0	SPR	C	Z
0.281	7.14	B1																		




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	GG-22	.25	6.4	.224	5.7	91	16	.07	1.7	6.0	27	.16	4.1	0.036	0.9	3.50	SPR	C	N
0.296	7.52	HH-19	.25	6.4	.216	5.5	130	23	.06	1.5	7.6	34	.14	3.6	0.040	1.0	3.50	SST	CG	N
0.296	7.52	Q-16	.28	7.1	.258	6.6	2.9	.51	.19	4.7	.54	2.4	.10	2.4	0.019	0.5	5.00	MW	CG	N
0.296	7.52	B-19	.28	7.1	.214	5.4	107	19	.08	1.9	8.2	36	.16	4.2	0.041	1.0	4.00	SST	CG	N
0.296	7.52	W-88	.28	7.1	.202	5.1	195	34	.06	1.6	12	54	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.296	7.52	M-11	.30	7.5	.226	5.7	42	7.3	.12	3.1	5.2	23	.16	4.0	0.035	0.9	4.50	SST	CG	N
0.296	7.52	12647	.30	7.5	.236	6.0	18	3.1	.15	3.7	2.6	12	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.296	7.52	B3-48	.30	7.5	.214	5.4	122	21	.09	2.3	11	50	.21	5.2	0.041	1.0	4.00	MW	C	GI
0.296	7.52	B-9	.31	7.9	.248	6.3	10	1.8	.18	4.6	1.9	8.3	.12	3.0	0.024	0.6	4.00	SST	C	N
0.296	7.52	IL-100	.31	7.9	.214	5.4	107	19	.08	1.9	8.2	36	.16	4.2	0.041	1.0	4.00	SST	CG	N
0.296	7.52	XX-6	.31	7.9	.176	4.5	933	163	.03	.66	24	108	.21	5.3	0.060	1.5	3.50	SPR	CG	N
0.296	7.52	O-127	.31	7.9	.172	4.4	818	143	.03	.83	27	119	.25	6.3	0.062	1.6	4.00	SPR	CG	N
0.296	7.52	F-47	.34	8.7	.266	6.8	.93	.16	.25	6.2	.23	1.0	.10	2.5	0.015	0.4	5.50	MW	C	Z
0.296	7.52	W-10	.34	8.7	.244	6.2	9.6	1.7	.19	4.7	1.8	8.0	.16	4.0	0.026	0.7	5.00	SST	C	N
0.296	7.52	EE-75	.34	8.7	.236	6.0	20	3.6	.16	4.1	3.3	15	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.296	7.52	W-32	.34	8.7	.214	5.4	86	15	.10	2.4	8.2	36	.23	5.7	0.041	1.0	4.50	SST	C	N
0.296	7.52	Q-78	.34	8.7	.196	5.0	238	42	.06	1.5	14	64	.23	5.7	0.050	1.3	4.50	SPR	CG	N
0.296	7.52	B18-131	.38	9.5	.278	7.1	.03	.01	.23	5.9	.01	.03	.14	3.7	0.009	0.2	15.0	MW	C	Z
0.296	7.52	NN-1	.38	9.5	.266	6.8	.54	.09	.24	6.1	.13	.58	.14	3.4	0.015	0.4	8.00	MW	C	N
0.296	7.52	WW-34	.38	9.5	.266	6.8	.46	.08	.23	5.7	.10	.46	.15	3.8	0.015	0.4	9.00	MW	C	Z
0.296	7.52	V-15	.38	9.5	.256	6.5	1.2	.21	.18	4.4	.21	.92	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.296	7.52	JJ-59	.38	9.5	.254	6.5	2.9	.51	.23	5.8	.66	2.9	.15	3.7	0.021	0.5	6.00	SST	C	N
0.296	7.52	G-77	.38	9.5	.248	6.3	5.1	.89	.21	5.3	1.1	4.7	.17	4.3	0.024	0.6	6.00	SST	C	N
0.296	7.52	B8-5	.38	9.5	.230	5.8	27	4.7	.18	4.6	4.9	22	.18	4.6	0.033	0.8	5.50	SPR	CG	N
0.296	7.52	M-55	.38	9.5	.222	5.6	68	12	.10	2.4	6.5	29	.16	4.0	0.037	0.9	4.25	SPR	CG	N
0.296	7.52	B12-41	.38	9.5	.220	5.6	78	14	.09	2.3	7.0	31	.16	4.1	0.038	1.0	4.25	SPR	CG	N
0.296	7.52	K-72	.38	9.5	.202	5.1	130	23	.09	2.4	12	54	.24	6.0	0.047	1.2	5.00	SST	CG	N
0.296	7.52	2966	.38	9.5	.196	5.0	199	35	.07	1.9	14	64	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.296	7.52	A10-22	.41	10.3	.256	6.5	2.2	.38	.27	6.8	.58	2.6	.14	3.6	0.020	0.5	7.00	MW	CG	N
0.296	7.52	11137	.41	10.3	.240	6.1	5.7	1.0	.10	2.5	.56	2.5	.31	7.8	0.028	0.7	10.0	MW	C	N
0.296	7.52	A15-34	.41	10.3	.230	5.8	31	5.4	.22	5.5	6.7	30	.17	4.2	0.033	0.8	5.00	MW	CG	N
0.296	7.52	A11-39	.41	10.3	.218	5.5	69	12	.10	2.6	7.1	31	.18	4.5	0.039	1.0	4.50	SST	CG	N
0.296	7.52	A15-31	.41	10.3	.212	5.4	96	17	.09	2.3	8.8	39	.19	4.8	0.042	1.1	4.50	SST	CG	N
0.296	7.52	L-5	.41	10.3	.202	5.1	120	21	.11	2.8	13	58	.27	6.9	0.047	1.2	5.75	SPR	CG	N
0.296	7.52	B1-24	.44	11.1	.246	6.2	9.9	1.7	.20	5.1	2.0	8.9	.14	3.5	0.025	0.6	4.50	SST	C	N
0.296	7.52	A11-6	.44	11.1	.244	6.2	13	2.3	.25	6.4	3.3	15	.12	3.0	0.026	0.7	4.50	MW	CG	GI
0.296	7.52	A10-10	.44	11.1	.236	6.0	18	3.2	.19	4.8	3.4	15	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.296	7.52	Z-98	.44	11.1	.234	5.9	21	3.7	.18	4.5	3.8	17	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.296	7.52	IL-98	.44	11.1	.232	5.9	20	3.6	.20	5.1	4.1	18	.19	4.7	0.032	0.8	5.00	SST	C	N
0.296	7.52	B-70	.44	11.1	.226	5.7	40	7.0	.14	3.5	5.5	25	.18	4.4	0.035	0.9	5.00	SPR	CG	GI
0.296	7.52	JJ-98	.44	11.1	.210	5.3	75	13	.13	3.2	9.4	42	.24	6.0	0.043	1.1	5.50	SST	CG	N
0.296	7.52	A-13	.47	11.9	.274	7.0	.30	.05	.40	10	.12	.54	.07	1.7	0.011	0.3	5.00	MW	C	N
0.296	7.52	PP-13	.47	11.9	.264	6.7	.94	.17	.35	8.8	.33	1.5	.12	3.0	0.016	0.4	6.50	MW	C	N
0.296	7.52	L-73	.47	11.9	.254	6.5	4.4	.78	.34	8.7	1.5	6.7	.13	3.2	0.021	0.5	5.00	MW	C	Z
0.296	7.52	O-82	.47	11.9	.244	6.2	10	1.8	.21	5.4	2.2	10	.12	3.1	0.026	0.7	4.75	SST	CG	N
0.296	7.52	Z-16	.47	11.9	.238	6.0	13	2.3	.29	7.5	3.9	17	.17	4.4	0.029	0.7	6.00	MW	CG	N
0.296	7.52	A13-59	.47	11.9	.214	5.4	61	11	.13	3.4	8.2	36	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.296	7.52	A11-10	.47	11.9	.210	5.3	67	12	.14	3.6	9.4	42	.26	6.6	0.043	1.1	6.00	SST	CG	N
0.296	7.52	LL-60	.50	12.7	.276	7.0	.20	.04	.44	11	.09	.40	.06	1.5	0.010	0.3	5.00	MW	C	Z
0.296	7.52	10834	.50	12.7	.272	6.9	.18	.03	.39	9.8	.07	.31	.11	2.9	0.012	0.3	8.50	SST	C	N
0.296	7.52	IL-84	.50	12.7	.272	6.9	.13	.02	.36	9.1	.05	.20	.14	3.6	0.012	0.3	10.8	SST	C	N
0.296	7.52	NN-58	.50	12.7	.272	6.9	.14	.03	.36	9.0	.05	.23	.14	3.7	0.012	0.3	11.0	MW	C	N
0.296	7.52	B15-35	.50	12.7	.272	6.9	.22	.04	.39	10	.09	.38	.11	2.7	0.012	0.3	8.00	MW	C	N
0.296	7.52	NN-62	.50	12.7	.264	6.7	.46	.08	.32	8.2	.15	.67	.18	4.5	0.016	0.4	10.0	SST	C	N
0.296	7.52	JJ-24	.50	12.7	.260	6.6	2.3	.41	.39	10	.91	4.0	.11	2.7	0.018	0.5	5.00	MW	C	N
0.296	7.52	XX-29	.50	12.7	.254	6.5	3.9	.67	.32	8.3	1.3	5.6	.13	3.2	0.021	0.5	5.00	SST	C	N
0.296	7.52	PP-70	.50	12.7	.252	6.4	5.4	.95	.37	9.3	2.0	8.8	.13	3.4	0.022	0.6	5.00	MW	C	Z
0.296	7.52	A15-9	.50	12.7	.250	6.4	7.8	1.4	.32	8.0	2.5	11	.10	2.6	0.023	0.6	4.50	MW	CG	N
0.296	7.52	AA-8	.50	12.7	.244	6.2	3.8	.67	.25	6.4	.97	4.3	.25	6.3	0.026	0.7	9.50	SST	CG	N
0.296	7.52	S-296	.50	12.7	.244	6.2	9.6	1.7	.23	5.9	2.2	10	.16	4.0	0.026	0.7	5.00	SST	C	N
0.296	7.52	B18-136	.50	12.7	.236	6.0	18	3.1	.29	7.3	5.1	23	.17	4.2	0.030	0.8	5.50	MW	CG	Z
0.296	7.52	K-1	.50	12.7	.234	5.9	14	2.5	.25	6.4	3.6	16	.25	6.3	0.031	0.8	7.00	MW	C	Z
0.296	7.52	I-71	.50	12.7	.232	5.9	27	4.8	.16	4.1	4.4	20	.16	4.1	0.032	0.8	5.00	SPR	CG	N
0.296	7.52	Z-43	.50	12.7	.230	5.8	19	3.2	.24	6.0	4.4	19	.26	6.7	0.033	0.8	7.00	SPR	C	Z
0.296	7.52	2563	.50	12.7	.218	5.5	65	11	.12	2.9	7.6	34	.23	5.9	0.039	1.0	5.00	SPR	C	Z
0.296	7.52	K-97	.50	12.7	.212	5.4	67	12	.13	3.3	8.8	39	.23	5.9	0.042	1.1	5.50	SST	CG	N
0.296	7.52	B15-59	.50	12.7	.208	5.3	84	15	.13	3.2	11	48	.26	6.7	0.044	1.1	6.00	SPR	CG	Z
0.296	7.52	M-22	.50	12.7	.204	5.2	118	21	.10	2.6	12	54	.25	6.4	0.046	1.2	5.50	SPR	CG	N
0.296	7.52	10962	.50	12.7	.194	4.9	147	26	.10	2.5	14	64	.31	7.8	0.051	1.3	6.00	SST	CG	Z
0.296	7.52	W-20	.50	12.7	.162	4.1	592	104	.05	1.3	31	138	.37	9.4	0.067	1.7				




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	S-1372	.56	14.3	.226	5.7	23	4.1	.22	5.7	5.2	23	.23	5.8	0.035	0.9	6.50	SST	CG	N
0.296	7.52	O-126	.56	14.3	.216	5.5	64	11	.12	3.0	7.6	34	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.296	7.52	J-65	.56	14.3	.202	5.1	112	20	.12	2.9	13	58	.33	8.4	0.047	1.2	6.00	SPR	C	Z
0.296	7.52	S-1696	.58	14.7	.234	5.9	16	2.7	.24	6.2	3.8	17	.22	5.5	0.031	0.8	6.00	SST	C	N
0.296	7.52	12404	.59	15.1	.268	6.8	.55	.10	.49	12	.27	1.2	.11	2.7	0.014	0.4	6.50	MW	C	N
0.296	7.52	B1-70	.59	15.1	.248	6.3	6.9	1.2	.27	6.8	1.9	8.3	.14	3.7	0.024	0.6	5.00	SST	C	N
0.296	7.52	M-103	.59	15.1	.246	6.2	5.4	.94	.37	9.4	2.0	8.9	.16	4.1	0.025	0.6	6.50	SST	CG	N
0.296	7.52	B8-17	.59	15.1	.228	5.8	21	3.7	.25	6.3	5.3	24	.24	6.0	0.034	0.9	7.00	SPR	CG	N
0.296	7.52	H-74	.59	15.1	.202	5.1	107	19	.11	2.9	12	54	.27	6.9	0.047	1.2	5.75	SST	CG	N
0.296	7.52	4283	.63	15.9	.270	6.9	.33	.06	.51	13	.17	.75	.11	2.8	0.013	0.3	7.50	MW	C	N
0.296	7.52	10854	.63	15.9	.262	6.7	1.2	.21	.51	13	.62	2.8	.12	3.0	0.017	0.4	6.00	SST	C	N
0.296	7.52	B12-36	.63	15.9	.252	6.4	5.5	.96	.40	10	2.2	9.6	.11	2.8	0.022	0.6	5.00	MW	CG	N
0.296	7.52	3193	.63	15.9	.246	6.2	8.0	1.4	.37	9.5	3.0	13	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.296	7.52	II-24	.63	15.9	.246	6.2	4.9	.85	.41	10	2.0	8.9	.20	5.1	0.025	0.6	7.00	SST	C	N
0.296	7.52	B3-60	.63	15.9	.246	6.2	4.3	.76	.41	10	1.8	8.0	.21	5.4	0.025	0.6	8.50	MW	CG	Z
0.296	7.52	AA-98	.63	15.9	.240	6.1	7.2	1.3	.39	9.9	2.8	12	.21	5.3	0.028	0.7	7.50	SST	CG	N
0.296	7.52	L-81	.63	15.9	.232	5.9	18	3.2	.25	6.3	4.4	20	.24	6.1	0.032	0.8	6.50	HD	C	N
0.296	7.52	10077	.63	15.9	.228	5.8	21	3.7	.25	6.4	5.3	24	.27	6.9	0.034	0.9	7.00	SPR	CG	Z
0.296	7.52	A12-39	.63	15.9	.216	5.5	58	10	.19	4.9	11	50	.23	5.8	0.040	1.0	5.75	MW	CG	GI
0.296	7.52	A11-19	.63	15.9	.204	5.2	66	11	.17	4.4	11	51	.35	8.8	0.046	1.2	7.50	SST	CG	N
0.296	7.52	F-65	.63	15.9	.202	5.1	90	16	.14	3.7	13	58	.38	9.6	0.047	1.2	7.00	HD	C	Z
0.296	7.52	BB-19	.63	15.9	.196	5.0	89	16	.15	3.9	14	61	.40	10.2	0.050	1.3	8.00	SST	CG	N
0.296	7.52	3861	.63	15.9	.192	4.9	102	18	.16	4.0	16	71	.47	11.9	0.052	1.3	9.00	SPR	CG	Z
0.296	7.52	I-16	.63	15.9	.188	4.8	148	26	.11	2.9	17	76	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.296	7.52	NN-61	.66	16.7	.256	6.5	2.2	.38	.50	13	1.1	4.8	.16	4.1	0.020	0.5	7.00	MW	C	N
0.296	7.52	S-1015	.66	16.7	.240	6.1	9.9	1.7	.28	7.2	2.8	12	.17	4.3	0.028	0.7	6.00	SST	CG	N
0.296	7.52	00-6	.66	16.7	.236	6.0	14	2.4	.37	9.4	5.1	23	.20	5.0	0.030	0.8	6.50	MW	CG	Z
0.296	7.52	EE-91	.66	16.7	.224	5.7	30	5.3	.20	5.0	6.0	27	.27	6.9	0.036	0.9	6.50	SPR	C	N
0.296	7.52	H-26	.66	16.7	.216	5.5	31	5.5	.24	6.2	7.6	34	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.296	7.52	JJ-32	.66	16.7	.192	4.9	104	18	.15	3.7	15	68	.42	10.6	0.052	1.3	8.00	SST	CG	N
0.296	7.52	B9-1	.69	17.4	.254	6.5	3.8	.67	.49	12	1.9	8.4	.12	2.9	0.021	0.5	5.50	MW	CG	Z
0.296	7.52	II-34	.69	17.4	.246	6.2	4.1	.72	.46	12	1.9	8.5	.23	5.7	0.025	0.6	8.00	SST	C	N
0.296	7.52	MM-14	.69	17.4	.238	6.0	9.6	1.7	.47	12	4.5	20	.22	5.5	0.029	0.7	7.50	MW	CG	GI
0.296	7.52	II-47	.69	17.4	.236	6.0	12	2.2	.41	10	5.1	23	.24	6.1	0.030	0.8	7.00	MW	C	N
0.296	7.52	MM-29	.69	17.4	.236	6.0	11.2	1.9	.46	12	3.8	17	.23	5.7	0.030	0.8	7.50	MW	CG	Z
0.296	7.52	RR-9	.69	17.4	.222	5.6	21	3.6	.30	7.5	6.1	27	.35	8.9	0.037	0.9	8.50	SST	C	N
0.296	7.52	A14-1	.69	17.4	.212	5.4	45	7.9	.21	5.3	9.4	42	.34	8.5	0.042	1.1	8.00	SPR	CG	GI
0.296	7.52	F-42	.69	17.4	.204	5.2	74	13	.16	4.2	12	54	.39	9.9	0.046	1.2	7.50	SPR	C	Z
0.296	7.52	F-43	.69	17.4	.202	5.1	83	14	.16	4.0	13	58	.40	10.1	0.047	1.2	7.50	HD	C	Z
0.296	7.52	NN-19	.69	17.4	.196	5.0	67	12	.19	4.7	13	56	.50	12.7	0.050	1.3	10.0	SST	CG	N
0.296	7.52	A10-16	.72	18.2	.264	6.7	.68	.12	.58	15	.40	1.8	.14	3.5	0.016	0.4	7.50	SST	C	N
0.296	7.52	B1-16	.72	18.2	.252	6.4	3.6	.63	.40	10	1.4	6.4	.13	3.4	0.022	0.6	6.00	SST	CG	N
0.296	7.52	J-88	.72	18.2	.238	6.0	8.8	1.5	.49	12	4.3	19	.23	5.9	0.029	0.7	8.00	MW	CG	Z
0.296	7.52	4396	.72	18.2	.180	4.6	238	42	.09	2.4	22	98	.41	10.3	0.058	1.5	7.00	SPR	CG	Z
0.296	7.52	S-3010	.75	19.1	.268	6.8	.34	.06	.62	16	.21	.94	.13	3.3	0.014	0.4	8.25	SST	C	N
0.296	7.52	3172	.75	19.1	.266	6.8	.52	.09	.61	16	.32	1.4	.14	3.5	0.015	0.4	8.25	MW	C	Z
0.296	7.52	KK-16	.75	19.1	.256	6.5	.84	.15	.45	11	.38	1.7	.30	7.6	0.020	0.5	15.0	MW	CG	N
0.296	7.52	KK-3	.75	19.1	.256	6.5	1.2	.21	.51	13	.61	2.7	.24	6.1	0.020	0.5	11.0	MW	C	N
0.296	7.52	W-75	.75	19.1	.252	6.4	2.5	.44	.54	14	1.3	6.0	.21	5.3	0.022	0.6	8.50	MW	C	N
0.296	7.52	G-25	.75	19.1	.252	6.4	4.1	.72	.53	13	2.2	9.6	.15	3.9	0.022	0.6	6.00	MW	C	N
0.296	7.52	10727	.75	19.1	.244	6.2	5.3	.94	.51	13	2.7	12	.24	6.1	0.026	0.7	8.25	MW	C	N
0.296	7.52	MM-22	.75	19.1	.236	6.0	6.9	1.2	.45	11	3.1	14	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.296	7.52	S-124	.75	19.1	.236	6.0	8.9	1.6	.39	9.8	3.4	15	.27	6.9	0.030	0.8	8.00	SST	C	N
0.296	7.52	3892	.75	19.1	.224	5.7	24	4.2	.25	6.3	6.0	27	.28	7.1	0.036	0.9	7.00	SPR	C	Z
0.296	7.52	O-76	.75	19.1	.216	5.5	37	6.4	.22	5.7	8.1	36	.32	8.1	0.040	1.0	8.00	SPR	CG	N
0.296	7.52	00-33	.75	19.1	.216	5.5	44	7.7	.19	4.7	8.1	36	.32	8.1	0.040	1.0	7.00	SPR	C	Z
0.296	7.52	I-45	.75	19.1	.206	5.2	55	9.6	.21	5.3	11	51	.39	10.0	0.045	1.1	8.75	SPR	CG	N
0.296	7.52	Q-86	.75	19.1	.202	5.1	75	13	.17	4.4	13	58	.38	9.6	0.047	1.2	8.00	SPR	CG	GI
0.296	7.52	J-6	.75	19.1	.202	5.1	64	11	.20	5.1	13	58	.47	11.9	0.047	1.2	9.00	SPR	C	Z
0.296	7.52	HH-21	.78	19.8	.256	6.5	2.7	.47	.60	15	1.6	7.2	.14	3.6	0.020	0.5	6.00	MW	C	N
0.296	7.52	O-157	.78	19.8	.246	6.2	5.4	.94	.37	9.4	2.0	8.9	.19	4.8	0.025	0.6	6.50	SST	C	N
0.296	7.52	10432	.78	19.8	.200	5.1	80	14	.17	4.4	14	61	.40	10.1	0.048	1.2	8.25	SPR	CG	BO
0.296	7.52	3523	.78	19.8	.176	4.5	155	27	.12	3.1	19	84	.66	16.8	0.060	1.5	11.0	SPR	CG	GI
0.296	7.52	L-57	.81	20.6	.260	6.6	.99	.17	.63	16	.63	2.8	.18	4.6	0.018	0.5	9.00	HD	C	Z
0.296	7.52	10869	.81	20.6	.256	6.5	1.9	.34	.56	14	1.1	4.8	.16	4.1	0.020	0.5	7.00	SST	C	N
0.296	7.52	A-19	.81	20.6	.256	6.5	1.2	.21	.59	15	.70	3.1	.22	5.6	0.020	0.5	10.0	SST	C	N
0.296	7.52	10221	.81	20.6	.246	6.2	5.6	.99	.53	13	3.0	13	.18	4.4	0.025	0.6	7.00	MW	CG	Z
0.296	7.52	A-96	.81	20.6	.232	5.9	12	2.0	.38	9.7	4.4	20	.29	7.3	0.032	0.8	9.00	SPR	CG	BO
0.296	7.52	B5-18	.81	20.6	.232	5.9	12	2.0	.38	9.6	4.4	20	.29	7.3	0.032	0.8	9.00	SPR	CG	N
0.296																				





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	A14-49	.84	21.4	.242	6.1	6.3	1.1	.40	10	2.5	11	.20	5.1	0.027	0.7	7.50	SST	CG	N
0.296	7.52	AA-60	.84	21.4	.202	5.1	36	6.3	.23	5.9	8.4	37	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.296	7.52	A12-8	.88	22.2	.270	6.9	.32	.06	.76	19	.24	1.1	.11	2.9	0.013	0.3	7.75	MW	C	N
0.296	7.52	EE-63	.88	22.2	.260	6.6	.73	.13	.65	17	.48	2.1	.23	5.7	0.018	0.5	11.5	MW	C	N
0.296	7.52	GG-93	.88	22.2	.260	6.6	.60	.11	.64	16	.39	1.7	.23	5.9	0.018	0.5	12.0	SST	C	N
0.296	7.52	BB-100	.88	22.2	.258	6.6	1.0	.18	.68	17	.68	3.0	.20	5.1	0.019	0.5	9.50	SST	C	N
0.296	7.52	2782	.88	22.2	.256	6.5	2.2	.38	.54	14	1.2	5.2	.16	4.1	0.020	0.5	7.00	HD	C	Z
0.296	7.52	B14-16	.88	22.2	.256	6.5	2.7	.48	.60	15	1.6	7.2	.12	3.0	0.020	0.5	6.00	MW	CG	N
0.296	7.52	S-1288	.88	22.2	.256	6.5	2.1	.37	.52	13	1.1	4.8	.15	3.8	0.020	0.5	6.50	SST	C	N
0.296	7.52	A13-6	.88	22.2	.250	6.4	4.3	.76	.57	14	2.5	11	.15	3.8	0.023	0.6	6.50	MW	CG	N
0.296	7.52	HH-51	.88	22.2	.248	6.3	2.1	.38	.58	15	1.2	5.5	.30	7.6	0.024	0.6	11.5	SST	C	N
0.296	7.52	A10-60	.88	22.2	.244	6.2	4.5	.79	.50	13	2.2	10	.22	5.6	0.026	0.7	8.50	SST	CG	N
0.296	7.52	GG-2	.88	22.2	.236	6.0	9.1	1.6	.37	9.5	3.4	15	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.296	7.52	B1-12	.88	22.2	.232	5.9	13	2.2	.48	12	6.2	27	.27	6.8	0.032	0.8	8.33	MW	CG	N
0.296	7.52	AA-50	.88	22.2	.220	5.6	20	3.5	.33	8.3	6.6	29	.40	10.1	0.038	1.0	9.50	SST	C	N
0.296	7.52	2812	.88	22.2	.214	5.4	24	4.2	.34	8.7	8.3	37	.53	13.5	0.041	1.0	12.0	HD	C	Z
0.296	7.52	A11-29	.88	22.2	.212	5.4	31	5.4	.28	7.2	8.8	39	.41	10.4	0.042	1.1	9.75	SST	CG	N
0.296	7.52	B11-40	.88	22.2	.208	5.3	42	7.4	.26	6.5	11	48	.44	11.2	0.044	1.1	10.0	SPR	CG	N
0.296	7.52	K-4	.88	22.2	.206	5.2	38	6.6	.28	7.2	11	48	.47	12.0	0.045	1.1	10.5	SST	CG	N
0.296	7.52	F-34	.88	22.2	.204	5.2	56	9.8	.22	5.5	12	54	.47	12.0	0.046	1.2	9.25	SPR	C	Z
0.296	7.52	B11-48	.88	22.2	.204	5.2	37	6.6	.28	7.0	10	46	.60	15.2	0.046	1.2	13.0	SPR	CG	N
0.296	7.52	V-4	.91	23.0	.172	4.4	221	39	.12	3.1	27	119	.59	15.0	0.062	1.6	9.50	SPR	CG	N
0.296	7.52	GG-50	.94	23.8	.266	6.8	.47	.08	.80	20	.38	1.7	.14	3.4	0.015	0.4	8.00	SST	C	N
0.296	7.52	Z-5	.94	23.8	.234	5.9	7.8	1.4	.60	15	4.7	21	.34	8.7	0.031	0.8	11.0	MW	CG	Z
0.296	7.52	S-1497	.94	23.8	.220	5.6	19	3.4	.34	8.6	6.6	29	.37	9.4	0.038	1.0	9.75	SST	CG	N
0.296	7.52	JJ-42	.94	23.8	.216	5.5	27	4.8	.30	7.5	8.1	36	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.296	7.52	JJ-13	.94	23.8	.216	5.5	16	2.8	.34	8.6	5.5	24	.60	15.2	0.040	1.0	14.0	SST	C	N
0.296	7.52	A14-31	.94	23.8	.202	5.1	44	7.7	.28	7.0	12	54	.52	13.1	0.047	1.2	11.0	SST	CG	N
0.296	7.52	3667	.97	24.6	.230	5.8	12	2.0	.58	15	6.7	30	.36	9.2	0.033	0.8	10.0	MW	C	Z
0.296	7.52	A15-64	.97	24.6	.230	5.8	13	2.3	.37	9.3	4.9	22	.33	8.4	0.033	0.8	9.00	SPR	C	N
0.296	7.52	B14-32	.97	24.6	.222	5.6	19	3.4	.33	8.5	6.5	29	.37	9.4	0.037	0.9	10.0	SPR	CG	N
0.296	7.52	B11-30	.97	24.6	.220	5.6	22	3.8	.32	8.2	7.0	31	.38	9.7	0.038	1.0	10.0	SPR	C	N
0.296	7.52	B2-29	.98	25.0	.210	5.3	36	6.3	.28	7.1	10	45	.45	11.5	0.043	1.1	10.5	SPR	CG	N
0.296	7.52	Z-76	1.00	25.4	.272	6.9	.29	.05	.87	22	.25	1.1	.08	2.1	0.012	0.3	6.00	SST	C	N
0.296	7.52	10266	1.00	25.4	.266	6.8	.51	.09	.86	22	.43	1.9	.14	3.6	0.015	0.4	8.50	MW	C	Z
0.296	7.52	PP-81	1.00	25.4	.250	6.4	.89	.16	.49	13	.44	2.0	.51	12.9	0.023	0.6	21.0	SST	C	N
0.296	7.52	Z-49	1.00	25.4	.246	6.2	3.7	.65	.53	14	2.0	8.9	.24	6.0	0.025	0.6	8.50	SST	C	N
0.296	7.52	G-62	1.00	25.4	.244	6.2	3.3	.59	.67	17	2.2	9.9	.33	8.5	0.026	0.7	11.9	MW	C	Z
0.296	7.52	JJ-43	1.00	25.4	.242	6.1	4.9	.85	.70	18	3.4	15	.30	7.5	0.027	0.7	10.0	MW	C	N
0.296	7.52	2643	1.00	25.4	.240	6.1	3.0	.52	.49	12	1.5	6.5	.51	13.0	0.028	0.7	17.3	MW	C	Z
0.296	7.52	3763	1.00	25.4	.236	6.0	12	2.1	.42	11	5.1	23	.24	6.1	0.030	0.8	7.00	MW	C	Z
0.296	7.52	3875	1.00	25.4	.236	6.0	7.6	1.3	.67	17	5.1	23	.33	8.4	0.030	0.8	10.0	MW	C	Z
0.296	7.52	2666	1.00	25.4	.232	5.9	9.0	1.6	.62	16	5.5	25	.38	9.8	0.032	0.8	11.0	MW	C	Z
0.296	7.52	B9-43	1.00	25.4	.226	5.7	15	2.7	.34	8.5	5.2	23	.32	8.0	0.035	0.9	9.00	SST	CG	N
0.296	7.52	S-230	1.00	25.4	.224	5.7	14	2.4	.40	10	5.6	25	.38	9.6	0.036	0.9	10.5	SST	CG	N
0.296	7.52	M-87	1.00	25.4	.206	5.2	34	5.9	.32	8.1	11	48	.56	14.3	0.045	1.1	11.5	SST	C	N
0.296	7.52	UU-46	1.00	25.4	.206	5.2	43	7.6	.26	6.7	11	51	.52	13.1	0.045	1.1	10.5	SPR	C	N
0.296	7.52	S-10	1.00	25.4	.202	5.1	33	5.7	.30	7.5	9.6	43	.71	17.9	0.047	1.2	14.0	SST	C	N
0.296	7.52	L-55	1.00	25.4	.196	5.0	52	9.1	.28	7.1	14	64	.68	17.1	0.050	1.3	13.5	SPR	CG	N
0.296	7.52	KK-33	1.00	25.4	.186	4.7	77	13	.23	5.9	18	80	.74	18.9	0.055	1.4	12.5	SST	C	N
0.296	7.52	G-49	1.00	25.4	.172	4.4	242	42	.11	2.8	27	119	.54	13.8	0.062	1.6	8.75	SPR	CG	Z
0.296	7.52	S-1306	1.03	26.2	.220	5.6	20	3.5	.33	8.3	6.6	29	.36	9.2	0.038	1.0	9.50	SST	CG	N
0.296	7.52	S-37	1.03	26.2	.152	3.9	365	64	.10	2.5	36	159	.81	20.6	0.072	1.8	10.3	SST	C	N
0.296	7.52	M-112	1.06	27.0	.254	6.5	1.5	.26	.81	21	1.2	5.3	.25	6.4	0.021	0.5	11.0	MW	C	Z
0.296	7.52	A15-29	1.06	27.0	.250	6.4	1.1	.19	.65	17	.72	3.2	.41	10.4	0.023	0.6	17.8	SST	CG	N
0.296	7.52	JJ-19	1.06	27.0	.176	4.5	105	18	.22	5.6	23	102	.84	21.3	0.060	1.5	14.0	SST	CG	N
0.296	7.52	S-1088	1.13	28.6	.268	6.8	.10	.02	.79	20	.08	.35	.34	8.5	0.014	0.4	23.0	SST	C	N
0.296	7.52	H-53	1.13	28.6	.252	6.4	1.8	.31	.82	21	1.4	6.4	.24	6.1	0.022	0.6	10.0	SST	C	N
0.296	7.52	CC-29	1.13	28.6	.248	6.3	2.5	.43	.83	21	2.0	9.1	.30	7.6	0.024	0.6	11.5	MW	C	Z
0.296	7.52	10627	1.13	28.6	.232	5.9	7.1	1.2	.69	18	4.9	22	.43	11.0	0.032	0.8	13.5	MW	CG	Z
0.296	7.52	S-1117	1.13	28.6	.232	5.9	8.8	1.5	.47	12	4.1	18	.35	8.9	0.032	0.8	10.0	SST	C	N
0.296	7.52	3628	1.13	28.6	.220	5.6	18	3.2	.53	14	9.7	43	.44	11.1	0.038	1.0	11.5	MW	CG	Z
0.296	7.52	S-793	1.13	28.6	.220	5.6	16	2.8	.42	11	6.6	29	.44	11.1	0.038	1.0	11.5	SST	CG	N
0.296	7.52	MM-31	1.13	28.6	.216	5.5	16	2.8	.47	12	7.6	34	.60	15.2	0.040	1.0	14.0	SST	C	N
0.296	7.52	A11-42	1.13	28.6	.210	5.3	30	5.3	.33	8.5	10	45	.52	13.1	0.043	1.1	12.0	SPR	CG	GI
0.296	7.52	B8-31	1.16	29.4	.234	5.9	9.0	1.6	.42	11	3.8	17	.28	7.1	0.031	0.8	9.00	SST	CG	N
0.296	7.52	B9-45	1.19	30.2	.256	6.5	1.3	.23	.98	25	1.3	5.6	.21	5.3	0.020	0.5	10.5	MW	CG	N
0.296	7.52	3219	1.19	30.2	.254	6.5	1.4	.25	.93	24	1.3	6.0	.26	6.5	0.021	0.5	11.3	MW	C	Z
0.296	7.52	QQ-46	1.19	30.2	.236	6.0	4.7	.82	.71	18	3.3	15	.48	12.2	0.030	0.8				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	M-96	1.28	32.5	.182	4.6	129	23	.16	4.1	21	94	.60	15.2	0.057	1.4	10.5	SPR	CG	Z
0.296	7.52	B7-9	1.31	33.3	.244	6.2	3.7	.65	.90	23	3.3	15	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.296	7.52	S-3076	1.31	33.3	.238	6.0	5.4	.95	.57	15	3.1	14	.33	8.5	0.029	0.7	10.5	SST	CG	N
0.296	7.52	I-77	1.31	33.3	.206	5.2	32	5.7	.35	9.0	11	51	.61	15.4	0.045	1.1	13.5	SPR	CG	N
0.296	7.52	AA-57	1.31	33.3	.176	4.5	98	17	.25	6.3	24	108	.99	25.1	0.060	1.5	16.5	SPR	CG	N
0.296	7.52	VW-56	1.38	34.9	.258	6.6	1.2	.22	1.1	29	1.4	6.2	.19	4.8	0.019	0.5	9.00	MW	C	Z
0.296	7.52	3855	1.38	34.9	.240	6.1	4.3	.76	.96	24	4.2	19	.38	9.6	0.028	0.7	12.5	MW	C	Z
0.296	7.52	KK-28	1.38	34.9	.236	6.0	6.2	1.1	.82	21	5.1	23	.36	9.1	0.030	0.8	12.0	MW	CG	GI
0.296	7.52	4319	1.38	34.9	.234	5.9	4.7	.82	.82	21	3.8	17	.56	14.2	0.031	0.8	17.0	MW	C	Z
0.296	7.52	A13-46	1.38	34.9	.218	5.5	15	2.6	.48	12	7.1	31	.54	13.6	0.039	1.0	13.8	SST	CG	N
0.296	7.52	A12-70	1.38	34.9	.218	5.5	20	3.4	.53	14	10	47	.51	12.9	0.039	1.0	12.0	MW	C	Z
0.296	7.52	2889	1.38	34.9	.214	5.4	16	2.8	.54	14	8.7	39	.74	18.7	0.041	1.0	17.0	SPR	CG	Z
0.296	7.52	B15-57	1.38	34.9	.210	5.3	24	4.3	.41	11	10	45	.62	15.8	0.043	1.1	14.5	SPR	CG	Z
0.296	7.52	A11-13	1.38	34.9	.200	5.1	34	5.9	.38	9.7	13	58	.72	18.3	0.048	1.2	15.0	SST	CG	N
0.296	7.52	11405	1.41	35.7	.248	6.3	2.6	.46	1.1	27	2.8	12	.29	7.3	0.024	0.6	11.0	MW	C	Z
0.296	7.52	Q-54	1.44	36.5	.202	5.1	28	4.9	.44	11	12	54	.75	19.1	0.047	1.2	16.0	SST	CG	N
0.296	7.52	K-86	1.44	36.5	.196	5.0	40	7.0	.34	8.7	14	61	.75	19.1	0.050	1.3	15.0	SST	CG	N
0.296	7.52	H-83	1.50	38.1	.256	6.5	.72	.13	1.2	30	.85	3.8	.32	8.1	0.020	0.5	15.0	SST	C	N
0.296	7.52	4280	1.50	38.1	.238	6.0	4.1	.71	1.0	26	4.2	19	.46	11.8	0.029	0.7	15.0	MW	C	Z
0.296	7.52	11408	1.50	38.1	.226	5.7	8.8	1.5	.86	22	7.6	34	.59	14.9	0.035	0.9	15.8	MW	C	Z
0.296	7.52	B9-10	1.50	38.1	.226	5.7	9.3	1.6	.59	15	5.5	25	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.296	7.52	11900	1.50	38.1	.222	5.6	11	1.9	.55	14	6.1	27	.54	13.6	0.037	0.9	14.5	SST	CG	N
0.296	7.52	A13-8	1.50	38.1	.212	5.4	17	3.0	.50	13	8.8	39	.66	16.8	0.042	1.1	15.8	SST	CG	N
0.296	7.52	10057	1.50	38.1	.206	5.2	26	4.6	.44	11	11	51	.77	19.4	0.045	1.1	16.0	SPR	C	GI
0.296	7.52	A14-36	1.50	38.1	.206	5.2	23	4.1	.46	12	11	48	.72	18.3	0.045	1.1	16.0	SST	CG	N
0.296	7.52	2840	1.63	41.3	.228	5.8	5.9	1.0	.95	24	5.6	25	.68	17.2	0.034	0.9	19.9	MW	CG	Z
0.296	7.52	S-1558	1.63	41.3	.228	5.8	4.5	.79	.83	21	3.7	17	.80	20.3	0.034	0.9	22.5	SPR	C	N
0.296	7.52	3532	1.66	42.1	.222	5.6	9.3	1.6	.70	18	6.5	29	.68	17.4	0.037	0.9	18.5	SPR	CG	GI
0.296	7.52	A-37	1.69	42.8	.170	4.3	105	18	.26	6.7	28	124	1.26	32.0	0.063	1.6	19.0	HD	C	N
0.296	7.52	U-36	1.72	43.6	.224	5.7	8.6	1.5	.70	18	6.0	27	.65	16.5	0.036	0.9	18.0	SPR	CG	GI
0.296	7.52	F-29	1.72	43.6	.172	4.4	126	22	.21	5.4	27	119	.99	25.2	0.062	1.6	15.0	SPR	C	Z
0.296	7.52	S-1433	1.75	44.5	.256	6.5	.99	.17	1.1	28	1.1	4.8	.25	6.4	0.020	0.5	11.5	SST	C	N
0.296	7.52	10203	1.75	44.5	.252	6.4	1.9	.34	1.1	29	2.2	9.6	.23	5.9	0.022	0.6	10.5	MW	CG	Z
0.296	7.52	AA-55	1.75	44.5	.246	6.2	2.5	.44	1.2	30	3.0	13	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.296	7.52	QQ-64	1.75	44.5	.246	6.2	1.6	.28	1.2	31	2.0	8.8	.51	13.0	0.025	0.6	19.5	MW	C	Z
0.296	7.52	3603	1.75	44.5	.232	5.9	6.6	1.2	.93	24	6.2	27	.49	12.4	0.032	0.8	14.3	MW	C	Z
0.296	7.52	B12-15	1.78	45.2	.214	5.4	16	2.7	.56	14	8.7	39	.73	18.5	0.041	1.0	17.8	SPR	CG	N
0.296	7.52	1747	1.81	46.0	.244	6.2	3.3	.58	1.0	25	3.3	15	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.296	7.52	M-124	1.88	47.6	.218	5.5	12	2.2	.61	15	7.6	34	.72	18.3	0.039	1.0	17.5	SPR	C	GI
0.296	7.52	3366	1.88	47.6	.216	5.5	14	2.4	.81	20	11	50	.74	18.8	0.040	1.0	17.5	MW	C	Z
0.296	7.52	2633	1.88	47.6	.172	4.4	109	19	.34	8.6	37	165	1.05	26.8	0.062	1.6	17.0	MW	CG	Z
0.296	7.52	11476	1.94	49.2	.236	6.0	4.4	.77	1.2	29	5.1	23	.51	13.0	0.030	0.8	16.0	MW	CG	GI
0.296	7.52	A10-68	1.94	49.2	.212	5.4	13	2.3	.66	17	8.8	39	.84	21.3	0.042	1.1	20.0	SST	CG	N
0.296	7.52	B4-14	1.95	49.6	.172	4.4	111	19	.24	6.1	27	119	1.12	28.3	0.062	1.6	17.0	SPR	C	N
0.296	7.52	S-1006	2.00	50.8	.234	5.9	3.5	.61	1.1	27	3.8	17	.64	16.1	0.031	0.8	19.5	SST	C	N
0.296	7.52	10071	2.00	50.8	.208	5.3	18	3.2	.58	15	11	48	.88	22.4	0.044	1.1	20.0	SPR	CG	Z
0.296	7.52	B10-7	2.09	53.2	.218	5.5	10	1.8	.74	19	7.6	34	.83	21.1	0.039	1.0	21.3	SPR	CG	N
0.296	7.52	B15-62	2.16	54.8	.204	5.2	17	3.0	.71	18	12	54	1.24	31.5	0.046	1.2	26.0	SPR	C	N
0.296	7.52	S-1026	2.16	54.8	.202	5.1	16	2.8	.75	19	12	54	1.27	32.2	0.047	1.2	26.0	SST	C	N
0.296	7.52	S-880	2.28	57.9	.238	6.0	1.4	.25	1.3	32	1.8	8.1	1.02	25.8	0.029	0.7	34.0	SST	C	N
0.296	7.52	Q-15	2.56	65.1	.218	5.5	9.6	1.7	.79	20	7.6	34	.88	22.3	0.039	1.0	22.5	SPR	CG	N
0.296	7.52	3651	2.56	65.1	.200	5.1	16	2.9	.84	21	14	61	1.54	39.0	0.048	1.2	32.0	SPR	CG	Z
0.296	7.52	S-1127	2.63	66.7	.224	5.7	5.8	1.0	.97	25	5.6	25	.85	21.5	0.036	0.9	22.5	SST	C	N
0.296	7.52	B8-18	2.75	69.9	.244	6.2	2.6	.45	1.3	33	3.3	15	.39	9.9	0.026	0.7	15.0	MW	CG	N
0.296	7.52	10625	2.75	69.9	.176	4.5	33	5.8	.74	19	24	108	1.50	38.1	0.060	1.5	25.0	PB	CG	N
0.296	7.52	S-190	2.78	70.6	.202	5.1	12	2.0	1.1	27	12	54	1.72	43.6	0.047	1.2	36.5	SST	CG	Z
0.296	7.52	2531	3.00	76.2	.226	5.7	3.2	.56	1.6	40	5.0	22	1.44	36.4	0.035	0.9	40.0	MW	C	Z
0.296	7.52	S-1441	3.00	76.2	.200	5.1	13	2.3	.99	25	13	58	1.68	42.7	0.048	1.2	35.0	SST	CG	N
0.296	7.52	S-1581	3.25	82.6	.204	5.2	11	1.9	1.0	26	11	51	1.62	41.2	0.046	1.2	35.3	SST	CG	N
0.296	7.52	S-1014	3.41	86.5	.202	5.1	16	2.7	.78	20	12	54	1.32	33.4	0.047	1.2	27.0	SST	C	N
0.296	7.52	10647	3.88	98.4	.236	6.0	2.0	.36	2.5	63	5.1	23	.99	25.1	0.030	0.8	33.0	MW	C	Z
0.296	7.52	2570	7.50	190.5	.224	5.7	2.0	.35	3.0	76	6.0	27	2.59	65.8	0.036	0.9	71.0	SPR	C	Z
0.296	7.52	10513	7.50	190.5	.214	5.4	3.6	.62	2.5	62	8.7	39	2.90	73.7	0.041	1.0	70.8	SPR	CG	N
0.300	7.62	B4-65	.34	8.7	.254	6.5	4.7	.82	.22	5.5	1.0	4.5	.13	3.2	0.023	0.6	5.50	SST	CG	N
0.300	7.62	70779	.38	9.7	.256	6.5	8.6	1.5	.25	6.3	2.1	9.5	.09	2.2	0.022	0.6	3.88	MW	CG	N
0.300	7.62	70779S	.38	9.7	.256	6.5	7.3	1.3	.19	4.9	1.4	6.3	.09	2.2	0.022	0.6	3.88	SST	CG	N
0.300	7.62	70802	.38	9.7	.248	6.3	15	2.7	.21	5.4	3.3	15	.11	2.7	0.026	0.7	4.13	MW	CG	N
0.300	7.62	70802S	.38	9.7	.248	6.3	13	2.3	.17	4.3	2.2	9								




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70944	.38	9.7	.210	5.3	124	22	.13	3.2	16	70	.22	5.6	0.045	1.1	4.88	MW	CG	N
0.300	7.62	70944S	.38	9.7	.210	5.3	105	18	.10	2.6	11	47	.22	5.6	0.045	1.1	4.88	SST	CG	N
0.300	7.62	70963	.38	9.7	.206	5.2	159	28	.11	2.8	18	79	.22	5.7	0.047	1.2	4.75	MW	CG	N
0.300	7.62	70963S	.38	9.7	.206	5.2	135	24	.09	2.3	12	53	.22	5.7	0.047	1.2	4.75	SST	CG	N
0.300	7.62	70984	.38	9.7	.202	5.1	190	33	.11	2.7	20	89	.23	5.9	0.049	1.2	4.75	MW	CG	N
0.300	7.62	70984S	.38	9.7	.202	5.1	161	28	.08	2.1	14	60	.23	5.9	0.049	1.2	4.75	SST	CG	N
0.300	7.62	71005	.38	9.7	.198	5.0	228	40	.09	2.3	21	94	.24	6.2	0.051	1.3	4.75	MW	CG	N
0.300	7.62	71005S	.38	9.7	.198	5.0	194	34	.07	1.9	14	63	.24	6.2	0.051	1.3	4.75	SST	CG	N
0.300	7.62	70780	.44	11.2	.256	6.5	7.2	1.3	.30	7.5	2.1	9.5	.09	2.3	0.022	0.6	4.13	MW	CG	N
0.300	7.62	70780S	.44	11.2	.256	6.5	6.1	1.1	.23	5.9	1.4	6.3	.09	2.3	0.022	0.6	4.13	SST	CG	N
0.300	7.62	70803	.44	11.2	.248	6.3	13	2.3	.25	6.4	3.3	15	.11	2.9	0.026	0.7	4.38	MW	CG	N
0.300	7.62	70803S	.44	11.2	.248	6.3	11	2.0	.20	5.0	2.2	9.8	.11	2.9	0.026	0.7	4.38	SST	CG	N
0.300	7.62	70826	.44	11.2	.240	6.1	21	3.6	.24	6.2	5.0	22	.15	3.7	0.030	0.8	4.88	MW	CG	N
0.300	7.62	70826S	.44	11.2	.240	6.1	18	3.1	.19	4.9	3.4	15	.15	3.7	0.030	0.8	4.88	SST	CG	N
0.300	7.62	70848	.44	11.2	.236	6.0	27	4.8	.22	5.7	6.1	27	.16	4.0	0.032	0.8	4.88	MW	CG	N
0.300	7.62	70848S	.44	11.2	.236	6.0	23	4.0	.18	4.5	4.1	18	.16	4.0	0.032	0.8	4.88	SST	CG	N
0.300	7.62	70869	.44	11.2	.230	5.8	38	6.7	.20	5.0	7.5	34	.18	4.4	0.035	0.9	5.00	MW	CG	N
0.300	7.62	70869S	.44	11.2	.230	5.8	33	5.7	.16	4.0	5.1	23	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.300	7.62	70888	.44	11.2	.224	5.7	53	9.3	.18	4.6	9.6	43	.19	4.9	0.038	1.0	5.13	MW	CG	N
0.300	7.62	70888S	.44	11.2	.224	5.7	45	7.9	.14	3.6	6.5	29	.19	4.9	0.038	1.0	5.13	SST	CG	N
0.300	7.62	70907	.44	11.2	.220	5.6	65	11	.17	4.3	11	50	.21	5.3	0.040	1.0	5.25	MW	CG	N
0.300	7.62	70907S	.44	11.2	.220	5.6	56	9.7	.14	3.4	7.5	33	.21	5.3	0.040	1.0	5.25	SST	CG	N
0.300	7.62	70926	.44	11.2	.216	5.5	89	16	.14	3.6	13	57	.20	5.2	0.042	1.1	4.88	MW	CG	N
0.300	7.62	70926S	.44	11.2	.216	5.5	76	13	.11	2.9	8.7	39	.20	5.2	0.042	1.1	4.88	SST	CG	N
0.300	7.62	70945	.44	11.2	.210	5.3	105	18	.15	3.8	16	70	.24	6.1	0.045	1.1	5.38	MW	CG	N
0.300	7.62	70945S	.44	11.2	.210	5.3	89	16	.12	3.0	11	47	.24	6.1	0.045	1.1	5.38	SST	CG	N
0.300	7.62	70964	.44	11.2	.206	5.2	132	23	.13	3.4	18	79	.25	6.3	0.047	1.2	5.25	MW	CG	N
0.300	7.62	70964S	.44	11.2	.206	5.2	112	20	.11	2.7	12	53	.25	6.3	0.047	1.2	5.25	SST	CG	N
0.300	7.62	70985	.44	11.2	.202	5.1	156	27	.13	3.3	20	89	.26	6.7	0.049	1.2	5.38	MW	CG	N
0.300	7.62	70985S	.44	11.2	.202	5.1	133	23	.10	2.6	14	60	.26	6.7	0.049	1.2	5.38	SST	CG	N
0.300	7.62	71006	.44	11.2	.198	5.0	187	33	.11	2.9	21	94	.27	7.0	0.051	1.3	5.38	MW	CG	N
0.300	7.62	71006S	.44	11.2	.198	5.0	159	28	.09	2.3	14	63	.27	7.0	0.051	1.3	5.38	SST	CG	N
0.300	7.62	B4-69	.47	11.9	.258	6.6	2.7	.47	.31	7.8	.83	3.7	.16	4.1	0.021	0.5	6.75	MW	C	GI
0.300	7.62	70781	.50	12.7	.256	6.5	6.6	1.1	.33	8.3	2.1	9.5	.10	2.4	0.022	0.6	4.38	MW	CG	N
0.300	7.62	70781S	.50	12.7	.256	6.5	5.6	.97	.25	6.5	1.4	6.3	.10	2.4	0.022	0.6	4.38	SST	CG	N
0.300	7.62	70804	.50	12.7	.248	6.3	11	2.0	.29	7.4	3.3	15	.13	3.2	0.026	0.7	4.88	MW	CG	N
0.300	7.62	70804S	.50	12.7	.248	6.3	9.6	1.7	.23	5.8	2.2	9.8	.13	3.2	0.026	0.7	4.88	SST	CG	N
0.300	7.62	70827	.50	12.7	.240	6.1	18	3.1	.28	7.2	5.0	22	.16	4.1	0.030	0.8	5.38	MW	CG	N
0.300	7.62	70827S	.50	12.7	.240	6.1	15	2.6	.22	5.7	3.4	15	.16	4.1	0.030	0.8	5.38	SST	CG	N
0.300	7.62	70849	.50	12.7	.236	6.0	23	4.1	.26	6.6	6.1	27	.17	4.4	0.032	0.8	5.38	MW	CG	N
0.300	7.62	70849S	.50	12.7	.236	6.0	20	3.5	.21	5.2	4.1	18	.17	4.4	0.032	0.8	5.38	SST	CG	N
0.300	7.62	70870	.50	12.7	.230	5.8	33	5.8	.23	5.8	7.5	34	.19	4.9	0.035	0.9	5.50	MW	CG	N
0.300	7.62	70870S	.50	12.7	.230	5.8	28	4.9	.18	4.6	5.1	23	.19	4.9	0.035	0.9	5.50	SST	CG	N
0.300	7.62	70889	.50	12.7	.224	5.7	46	8.1	.21	5.3	9.6	43	.21	5.4	0.038	1.0	5.63	MW	CG	N
0.300	7.62	70889S	.50	12.7	.224	5.7	39	6.9	.17	4.2	6.5	29	.21	5.4	0.038	1.0	5.63	SST	CG	N
0.300	7.62	70908	.50	12.7	.220	5.6	55	9.7	.20	5.1	11	50	.23	5.8	0.040	1.0	5.75	MW	CG	N
0.300	7.62	70908S	.50	12.7	.220	5.6	47	8.3	.16	4.1	7.5	33	.23	5.8	0.040	1.0	5.75	SST	CG	N
0.300	7.62	70927	.50	12.7	.216	5.5	70	12	.18	4.6	13	57	.24	6.1	0.042	1.1	5.75	MW	CG	N
0.300	7.62	70927S	.50	12.7	.216	5.5	60	10	.15	3.7	8.7	39	.24	6.1	0.042	1.1	5.75	SST	CG	N
0.300	7.62	70946	.50	12.7	.210	5.3	91	16	.17	4.4	16	70	.26	6.7	0.045	1.1	5.88	MW	CG	N
0.300	7.62	70946S	.50	12.7	.210	5.3	78	14	.14	3.5	11	47	.26	6.7	0.045	1.1	5.88	SST	CG	N
0.300	7.62	70965	.50	12.7	.206	5.2	112	20	.16	4.0	18	79	.28	7.0	0.047	1.2	5.88	MW	CG	N
0.300	7.62	70965S	.50	12.7	.206	5.2	95	17	.13	3.2	12	53	.28	7.0	0.047	1.2	5.88	SST	CG	N
0.300	7.62	70986	.50	12.7	.202	5.1	133	23	.15	3.8	20	89	.29	7.5	0.049	1.2	6.00	MW	CG	N
0.300	7.62	70986S	.50	12.7	.202	5.1	113	20	.12	3.0	14	60	.29	7.5	0.049	1.2	6.00	SST	CG	N
0.300	7.62	71007	.50	12.7	.198	5.0	158	28	.13	3.4	21	94	.31	7.8	0.051	1.3	6.00	MW	CG	N
0.300	7.62	71007S	.50	12.7	.198	5.0	134	24	.11	2.7	14	63	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.300	7.62	70782	.56	14.2	.256	6.5	6.0	1.0	.36	9.1	2.1	9.5	.10	2.6	0.022	0.6	4.63	MW	CG	N
0.300	7.62	70782S	.56	14.2	.256	6.5	5.1	.89	.28	7.1	1.4	6.3	.10	2.6	0.022	0.6	4.63	SST	CG	N
0.300	7.62	70805	.56	14.2	.248	6.3	10	1.8	.33	8.3	3.3	15	.13	3.4	0.026	0.7	5.13	MW	CG	N
0.300	7.62	70805S	.56	14.2	.248	6.3	8.6	1.5	.26	6.5	2.2	9.8	.13	3.4	0.026	0.7	5.13	SST	CG	N
0.300	7.62	70828	.56	14.2	.240	6.1	16	2.7	.32	8.1	5.0	22	.17	4.4	0.030	0.8	5.75	MW	CG	N
0.300	7.62	70828S	.56	14.2	.240	6.1	13	2.3	.25	6.4	3.4	15	.17	4.4	0.030	0.8	5.75	SST	CG	N
0.300	7.62	70850	.56	14.2	.236	6.0	20	3.5	.30	7.7	6.1	27	.19	4.8	0.032	0.8	5.88	MW	CG	N
0.300	7.62	70850S	.56	14.2	.236	6.0	17	3.0	.24	6.0	4.1	18	.19	4.8	0.032	0.8	5.88	SST	CG	N
0.300	7.62	70871	.56	14.2	.230	5.8	29	5.0	.26	6.7	7.5	34	.21	5.3	0.035	0.9	6.00	MW	CG	N
0.300	7.62	70871S	.56	14.2	.230	5.8	24	4.3	.21	5.3	5.1	23	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.300	7.62	70890	.56	14.2	.224	5.7	39	6.8	.25	6.3	9.6	43	.24	6.0	0.038	1.0	6.25	MW	CG	N
0.300	7.62	70890S	.56	14.2	.224	5.7	33	5.8	.20	5.0	6									




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F.N.D.S.	F.N.H.
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	71008S	.56	14.2	.198	5.0	116	20	.12	3.1	14	63	.34	8.6	0.051	1.3	6.63	SST	CG	N
0.300	7.62	B4-34	.56	14.3	.224	5.7	37	6.5	.26	6.6	9.6	43	.25	6.3	0.038	1.0	6.50	MW	CG	GI
0.300	7.62	70783	.63	16.0	.256	6.5	5.0	.88	.43	11	2.1	9.5	.11	2.9	0.022	0.6	5.13	MW	CG	N
0.300	7.62	70783S	.63	16.0	.256	6.5	4.3	.74	.33	8.5	1.4	6.3	.11	2.9	0.022	0.6	5.13	SST	CG	N
0.300	7.62	70806	.63	16.0	.248	6.3	9.0	1.6	.37	9.4	3.3	15	.15	3.7	0.026	0.7	5.63	MW	CG	N
0.300	7.62	70806S	.63	16.0	.248	6.3	7.6	1.3	.29	7.4	2.2	9.8	.15	3.7	0.026	0.7	5.63	SST	CG	N
0.300	7.62	70829	.63	16.0	.240	6.1	14	2.4	.36	9.2	5.0	22	.19	4.8	0.030	0.8	6.25	MW	CG	N
0.300	7.62	70829S	.63	16.0	.240	6.1	12	2.1	.28	7.2	3.4	15	.19	4.8	0.030	0.8	6.25	SST	CG	N
0.300	7.62	70851	.63	16.0	.236	6.0	18	3.2	.34	8.5	6.1	27	.20	5.2	0.032	0.8	6.38	MW	CG	N
0.300	7.62	70851S	.63	16.0	.236	6.0	15	2.7	.26	6.7	4.1	18	.20	5.2	0.032	0.8	6.38	SST	CG	N
0.300	7.62	70872	.63	16.0	.230	5.8	26	4.5	.29	7.5	7.5	34	.23	5.8	0.035	0.9	6.50	MW	CG	N
0.300	7.62	70872S	.63	16.0	.230	5.8	22	3.8	.23	6.0	5.1	23	.23	5.8	0.035	0.9	6.50	SST	CG	N
0.300	7.62	70891	.63	16.0	.224	5.7	35	6.1	.27	7.0	9.6	43	.26	6.5	0.038	1.0	6.75	MW	CG	N
0.300	7.62	70891S	.63	16.0	.224	5.7	30	5.2	.22	5.5	6.5	29	.26	6.5	0.038	1.0	6.75	SST	CG	N
0.300	7.62	70910	.63	16.0	.220	5.6	43	7.5	.26	6.6	11	50	.28	7.0	0.040	1.0	6.88	MW	CG	N
0.300	7.62	70910S	.63	16.0	.220	5.6	37	6.4	.21	5.2	7.5	33	.28	7.0	0.040	1.0	6.88	SST	CG	N
0.300	7.62	70929	.63	16.0	.216	5.5	52	9.1	.25	6.3	13	57	.29	7.5	0.042	1.1	7.00	MW	CG	N
0.300	7.62	70929S	.63	16.0	.216	5.5	44	7.7	.20	5.0	8.7	39	.29	7.5	0.042	1.1	7.00	SST	CG	N
0.300	7.62	70948	.63	16.0	.210	5.3	68	12	.23	5.8	16	70	.33	8.3	0.045	1.1	7.25	MW	CG	N
0.300	7.62	70948S	.63	16.0	.210	5.3	58	10	.18	4.6	11	47	.33	8.3	0.045	1.1	7.25	SST	CG	N
0.300	7.62	70967	.63	16.0	.206	5.2	86	15	.21	5.2	18	79	.33	8.4	0.047	1.2	7.00	MW	CG	N
0.300	7.62	70967S	.63	16.0	.206	5.2	73	13	.16	4.2	12	53	.33	8.4	0.047	1.2	7.00	SST	CG	N
0.300	7.62	70988	.63	16.0	.202	5.1	102	18	.20	5.0	20	89	.35	8.9	0.049	1.2	7.13	MW	CG	N
0.300	7.62	70988S	.63	16.0	.202	5.1	87	15	.16	4.0	14	60	.35	8.9	0.049	1.2	7.13	SST	CG	N
0.300	7.62	71009	.63	16.0	.198	5.0	121	21	.17	4.4	21	94	.37	9.4	0.051	1.3	7.25	MW	CG	N
0.300	7.62	71009S	.63	16.0	.198	5.0	103	18	.14	3.5	14	63	.37	9.4	0.051	1.3	7.25	SST	CG	N
0.300	7.62	70784	.69	17.5	.256	6.5	4.6	.81	.46	12	2.1	9.5	.12	3.0	0.022	0.6	5.38	MW	CG	N
0.300	7.62	70784S	.69	17.5	.256	6.5	3.9	.68	.36	9.2	1.4	6.3	.12	3.0	0.022	0.6	5.38	SST	CG	N
0.300	7.62	70807	.69	17.5	.248	6.3	7.9	1.4	.42	11	3.3	15	.16	4.0	0.026	0.7	6.00	MW	CG	N
0.300	7.62	70807S	.69	17.5	.248	6.3	6.7	1.2	.33	8.4	2.2	9.8	.16	4.0	0.026	0.7	6.00	SST	CG	N
0.300	7.62	70823	.69	17.5	.242	6.1	9.0	1.6	.47	12	4.2	19	.22	5.6	0.029	0.7	7.63	MW	CG	N
0.300	7.62	70823S	.69	17.5	.242	6.1	7.7	1.3	.40	10	3.1	14	.22	5.6	0.029	0.7	7.63	SST	CG	N
0.300	7.62	70830	.69	17.5	.240	6.1	13	2.2	.40	10	5.0	22	.20	5.1	0.030	0.8	6.75	MW	CG	N
0.300	7.62	70830S	.69	17.5	.240	6.1	11	1.9	.32	8.1	3.4	15	.20	5.1	0.030	0.8	6.75	SST	CG	N
0.300	7.62	70852	.69	17.5	.236	6.0	16	2.8	.38	9.6	6.1	27	.22	5.6	0.032	0.8	6.88	MW	CG	N
0.300	7.62	70852S	.69	17.5	.236	6.0	14	2.4	.30	7.5	4.1	18	.22	5.6	0.032	0.8	6.88	SST	CG	N
0.300	7.62	70873	.69	17.5	.230	5.8	23	4.0	.33	8.4	7.5	34	.25	6.3	0.035	0.9	7.13	MW	CG	N
0.300	7.62	70873S	.69	17.5	.230	5.8	19	3.4	.26	6.7	5.1	23	.25	6.3	0.035	0.9	7.13	SST	CG	N
0.300	7.62	70892	.69	17.5	.224	5.7	30	5.3	.32	8.1	9.6	43	.29	7.2	0.038	1.0	7.50	MW	CG	N
0.300	7.62	70892S	.69	17.5	.224	5.7	26	4.5	.25	6.4	6.5	29	.29	7.2	0.038	1.0	7.50	SST	CG	N
0.300	7.62	70911	.69	17.5	.220	5.6	38	6.7	.29	7.4	11	50	.30	7.6	0.040	1.0	7.50	MW	CG	N
0.300	7.62	70911S	.69	17.5	.220	5.6	32	5.7	.23	5.9	7.5	33	.30	7.6	0.040	1.0	7.50	SST	CG	N
0.300	7.62	70930	.69	17.5	.216	5.5	46	8.0	.28	7.2	13	57	.33	8.3	0.042	1.1	7.75	MW	CG	N
0.300	7.62	70930S	.69	17.5	.216	5.5	39	6.8	.22	5.7	8.7	39	.33	8.3	0.042	1.1	7.75	SST	CG	N
0.300	7.62	70949	.69	17.5	.210	5.3	62	11	.25	6.5	16	70	.35	8.9	0.045	1.1	7.75	MW	CG	N
0.300	7.62	70949S	.69	17.5	.210	5.3	52	9.2	.20	5.2	11	47	.35	8.9	0.045	1.1	7.75	SST	CG	N
0.300	7.62	70968	.69	17.5	.206	5.2	77	13	.23	5.9	18	79	.36	9.1	0.047	1.2	7.63	MW	CG	N
0.300	7.62	70968S	.69	17.5	.206	5.2	65	11	.18	4.7	12	53	.36	9.1	0.047	1.2	7.63	SST	CG	N
0.300	7.62	70989	.69	17.5	.202	5.1	90	16	.22	5.6	20	89	.38	9.6	0.049	1.2	7.75	MW	CG	N
0.300	7.62	70989S	.69	17.5	.202	5.1	77	13	.18	4.5	14	60	.38	9.6	0.049	1.2	7.75	SST	CG	N
0.300	7.62	71010	.69	17.5	.198	5.0	107	19	.20	5.0	21	94	.40	10.2	0.051	1.3	7.88	MW	CG	N
0.300	7.62	71010S	.69	17.5	.198	5.0	91	16	.16	4.0	14	63	.40	10.2	0.051	1.3	7.88	SST	CG	N
0.300	7.62	70785	.75	19.1	.256	6.5	4.1	.71	.53	13	2.1	9.5	.13	3.3	0.022	0.6	5.88	MW	CG	N
0.300	7.62	70785S	.75	19.1	.256	6.5	3.4	.60	.41	10	1.4	6.3	.13	3.3	0.022	0.6	5.88	SST	CG	N
0.300	7.62	70808	.75	19.1	.248	6.3	7.5	1.3	.44	11	3.3	15	.16	4.1	0.026	0.7	6.25	MW	CG	N
0.300	7.62	70808S	.75	19.1	.248	6.3	6.3	1.1	.35	8.9	2.2	9.8	.16	4.1	0.026	0.7	6.25	SST	CG	N
0.300	7.62	70831	.75	19.1	.240	6.1	11	2.0	.44	11	5.0	22	.21	5.4	0.030	0.8	7.13	MW	CG	N
0.300	7.62	70831S	.75	19.1	.240	6.1	9.7	1.7	.35	8.8	3.4	15	.21	5.4	0.030	0.8	7.13	SST	CG	N
0.300	7.62	70853	.75	19.1	.236	6.0	15	2.6	.41	10	6.1	27	.23	5.9	0.032	0.8	7.25	MW	CG	N
0.300	7.62	70853S	.75	19.1	.236	6.0	13	2.2	.32	8.1	4.1	18	.23	5.9	0.032	0.8	7.25	SST	CG	N
0.300	7.62	70874	.75	19.1	.230	5.8	21	3.6	.36	9.2	7.5	34	.27	6.8	0.035	0.9	7.63	MW	CG	N
0.300	7.62	70874S	.75	19.1	.230	5.8	18	3.1	.29	7.3	5.1	23	.27	6.8	0.035	0.9	7.63	SST	CG	N
0.300	7.62	70893	.75	19.1	.224	5.7	28	4.9	.34	8.7	9.6	43	.30	7.7	0.038	1.0	8.00	MW	CG	N
0.300	7.62	70893S	.75	19.1	.224	5.7	24	4.2	.27	6.9	6.5	29	.30	7.7	0.038	1.0	8.00	SST	CG	N
0.300	7.62	70912	.75	19.1	.220	5.6	34	6.0	.32	8.2	11	50	.33	8.3	0.040	1.0	8.13	MW	CG	N
0.300	7.62	70912S	.75	19.1	.220	5.6	29	5.1	.26	6.5	7.5	33	.33	8.3	0.040	1.0	8.13	SST	CG	N
0.300	7.62	70931	.75	19.1	.216	5.5	42	7.3	.31	7.8	13	57	.35	8.8	0.042	1.1	8.25	MW	CG	N
0.300	7.62	70931S	.75	19.1	.216	5.5	36	6.2	.24	6.2	8.7	39	.35	8.8	0.042	1.1	8.25	SST	CG	N
0.300	7.62	70950	.75	19.1	.210	5.3	55													




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70832	.81	20.6	.240	6.1	10	1.8	.48	12	5.0	22	.23	5.8	0.030	0.8	7.63	MW	CG	N
0.300	7.62	70832S	.81	20.6	.240	6.1	8.9	1.6	.38	9.6	3.4	15	.23	5.8	0.030	0.8	7.63	SST	CG	N
0.300	7.62	70854	.81	20.6	.236	6.0	14	2.4	.45	11	6.1	27	.25	6.3	0.032	0.8	7.75	MW	CG	N
0.300	7.62	70854S	.81	20.6	.236	6.0	12	2.0	.35	9.0	4.1	18	.25	6.3	0.032	0.8	7.75	SST	CG	N
0.300	7.62	70875	.81	20.6	.230	5.8	19	3.3	.40	10	7.5	34	.28	7.2	0.035	0.9	8.13	MW	CG	N
0.300	7.62	70875S	.81	20.6	.230	5.8	16	2.8	.31	8.0	5.1	23	.28	7.2	0.035	0.9	8.13	SST	CG	N
0.300	7.62	70894	.81	20.6	.224	5.7	26	4.5	.37	9.4	9.6	43	.32	8.1	0.038	1.0	8.38	MW	CG	N
0.300	7.62	70894S	.81	20.6	.224	5.7	22	3.9	.29	7.5	6.5	29	.32	8.1	0.038	1.0	8.38	SST	CG	N
0.300	7.62	70913	.81	20.6	.220	5.6	32	5.5	.35	9.0	11	50	.35	8.8	0.040	1.0	8.63	MW	CG	N
0.300	7.62	70913S	.81	20.6	.220	5.6	27	4.7	.28	7.1	7.5	33	.35	8.8	0.040	1.0	8.63	SST	CG	N
0.300	7.62	70932	.81	20.6	.216	5.5	38	6.6	.34	8.6	13	57	.37	9.5	0.042	1.1	8.88	MW	CG	N
0.300	7.62	70932S	.81	20.6	.216	5.5	32	5.6	.27	6.9	8.7	39	.37	9.5	0.042	1.1	8.88	SST	CG	N
0.300	7.62	70951	.81	20.6	.210	5.3	51	9.0	.31	7.8	16	70	.41	10.3	0.045	1.1	9.00	MW	CG	N
0.300	7.62	70951S	.81	20.6	.210	5.3	43	7.6	.24	6.2	11	47	.41	10.3	0.045	1.1	9.00	SST	CG	N
0.300	7.62	70970	.81	20.6	.206	5.2	63	11	.28	7.1	18	79	.42	10.6	0.047	1.2	8.88	MW	CG	N
0.300	7.62	70970S	.81	20.6	.206	5.2	54	9.4	.22	5.7	12	53	.42	10.6	0.047	1.2	8.88	SST	CG	N
0.300	7.62	70991	.81	20.6	.202	5.1	75	13	.27	6.8	20	89	.44	11.2	0.049	1.2	9.00	MW	CG	N
0.300	7.62	70991S	.81	20.6	.202	5.1	64	11	.21	5.4	14	60	.44	11.2	0.049	1.2	9.00	SST	CG	N
0.300	7.62	71012	.81	20.6	.198	5.0	89	16	.24	6.0	21	94	.47	11.8	0.051	1.3	9.13	MW	CG	N
0.300	7.62	71012S	.81	20.6	.198	5.0	75	13	.19	4.8	14	63	.47	11.8	0.051	1.3	9.13	SST	CG	N
0.300	7.62	70787	.88	22.4	.256	6.5	3.3	.58	.65	16	2.1	9.5	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.300	7.62	70787S	.88	22.4	.256	6.5	2.8	.49	.51	13	1.4	6.3	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.300	7.62	70810	.88	22.4	.248	6.3	6.1	1.1	.55	14	3.3	15	.19	4.8	0.026	0.7	7.25	MW	CG	N
0.300	7.62	70810S	.88	22.4	.248	6.3	5.1	.90	.43	11	2.2	9.8	.19	4.8	0.026	0.7	7.25	SST	CG	N
0.300	7.62	70833	.88	22.4	.240	6.1	9.7	1.7	.52	13	5.0	22	.24	6.2	0.030	0.8	8.13	MW	CG	N
0.300	7.62	70833S	.88	22.4	.240	6.1	8.2	1.4	.41	10	3.4	15	.24	6.2	0.030	0.8	8.13	SST	CG	N
0.300	7.62	70855	.88	22.4	.236	6.0	12	2.2	.49	13	6.1	27	.27	6.8	0.032	0.8	8.38	MW	CG	N
0.300	7.62	70855S	.88	22.4	.236	6.0	10	1.8	.39	9.9	4.1	18	.27	6.8	0.032	0.8	8.38	SST	CG	N
0.300	7.62	70876	.88	22.4	.230	5.8	18	3.1	.43	11	7.5	34	.30	7.7	0.035	0.9	8.63	MW	CG	N
0.300	7.62	70876S	.88	22.4	.230	5.8	15	2.6	.34	8.7	5.1	23	.30	7.7	0.035	0.9	8.63	SST	CG	N
0.300	7.62	70895	.88	22.4	.224	5.7	23	4.0	.41	11	9.6	43	.35	8.9	0.038	1.0	9.25	MW	CG	N
0.300	7.62	70895S	.88	22.4	.224	5.7	20	3.4	.33	8.4	6.5	29	.35	8.9	0.038	1.0	9.25	SST	CG	N
0.300	7.62	70914	.88	22.4	.220	5.6	29	5.1	.38	9.7	11	50	.37	9.3	0.040	1.0	9.13	MW	CG	N
0.300	7.62	70914S	.88	22.4	.220	5.6	25	4.3	.30	7.7	7.5	33	.37	9.3	0.040	1.0	9.13	SST	CG	N
0.300	7.62	70933	.88	22.4	.216	5.5	34	5.9	.38	9.6	13	57	.40	10.3	0.042	1.1	9.63	MW	CG	N
0.300	7.62	70933S	.88	22.4	.216	5.5	29	5.0	.30	7.7	8.7	39	.40	10.3	0.042	1.1	9.63	SST	CG	N
0.300	7.62	70952	.88	22.4	.210	5.3	46	8.1	.34	8.6	16	70	.44	11.1	0.045	1.1	9.75	MW	CG	N
0.300	7.62	70952S	.88	22.4	.210	5.3	39	6.9	.27	6.9	11	47	.44	11.1	0.045	1.1	9.75	SST	CG	N
0.300	7.62	70971	.88	22.4	.206	5.2	58	10	.31	7.8	18	79	.45	11.3	0.047	1.2	9.50	MW	CG	N
0.300	7.62	70971S	.88	22.4	.206	5.2	49	8.6	.24	6.2	12	53	.45	11.3	0.047	1.2	9.50	SST	CG	N
0.300	7.62	70992	.88	22.4	.202	5.1	68	12	.29	7.4	20	89	.47	12.0	0.049	1.2	9.63	MW	CG	N
0.300	7.62	70992S	.88	22.4	.202	5.1	58	10	.23	5.9	14	60	.47	12.0	0.049	1.2	9.63	SST	CG	N
0.300	7.62	71013	.88	22.4	.198	5.0	81	14	.26	6.6	21	94	.50	12.6	0.051	1.3	9.75	MW	CG	N
0.300	7.62	71013S	.88	22.4	.198	5.0	69	12	.21	5.3	14	63	.50	12.6	0.051	1.3	9.75	SST	CG	N
0.300	7.62	70789	.94	23.9	.256	6.5	3.3	.58	.65	16	2.1	9.5	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.300	7.62	70789S	.94	23.9	.256	6.5	2.8	.49	.51	13	1.4	6.3	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.300	7.62	70811	.94	23.9	.248	6.3	5.5	.96	.60	15	3.3	15	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.300	7.62	70811S	.94	23.9	.248	6.3	4.7	.82	.47	12	2.2	9.8	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.300	7.62	70834	.94	23.9	.240	6.1	9.0	1.6	.56	14	5.0	22	.26	6.6	0.030	0.8	8.63	MW	CG	N
0.300	7.62	70834S	.94	23.9	.240	6.1	7.6	1.3	.44	11	3.4	15	.26	6.6	0.030	0.8	8.63	SST	CG	N
0.300	7.62	70856	.94	23.9	.236	6.0	11	2.0	.55	14	6.1	27	.29	7.3	0.032	0.8	9.00	MW	CG	N
0.300	7.62	70856S	.94	23.9	.236	6.0	9.5	1.7	.43	11	4.1	18	.29	7.3	0.032	0.8	9.00	SST	CG	N
0.300	7.62	70877	.94	23.9	.230	5.8	16	2.8	.46	12	7.5	34	.32	8.1	0.035	0.9	9.13	MW	CG	N
0.300	7.62	70877S	.94	23.9	.230	5.8	14	2.4	.37	9.4	5.1	23	.32	8.1	0.035	0.9	9.13	SST	CG	N
0.300	7.62	70896	.94	23.9	.224	5.7	22	3.8	.44	11	9.6	43	.37	9.3	0.038	1.0	9.63	MW	CG	N
0.300	7.62	70896S	.94	23.9	.224	5.7	19	3.3	.35	8.8	6.5	29	.37	9.3	0.038	1.0	9.63	SST	CG	N
0.300	7.62	70915	.94	23.9	.220	5.6	27	4.8	.41	10	11	50	.39	9.9	0.040	1.0	9.75	MW	CG	N
0.300	7.62	70915S	.94	23.9	.220	5.6	23	4.0	.33	8.3	7.5	33	.39	9.9	0.040	1.0	9.75	SST	CG	N
0.300	7.62	70934	.94	23.9	.216	5.5	32	5.6	.40	10	13	57	.43	10.8	0.042	1.1	10.1	MW	CG	N
0.300	7.62	70934S	.94	23.9	.216	5.5	27	4.8	.32	8.1	8.7	39	.43	10.8	0.042	1.1	10.1	SST	CG	N
0.300	7.62	70953	.94	23.9	.210	5.3	42	7.4	.37	9.4	16	70	.47	11.9	0.045	1.1	10.4	MW	CG	N
0.300	7.62	70953S	.94	23.9	.210	5.3	36	6.3	.30	7.5	11	47	.47	11.9	0.045	1.1	10.4	SST	CG	N
0.300	7.62	70972	.94	23.9	.206	5.2	54	9.4	.33	8.4	18	79	.47	11.9	0.047	1.2	10.0	MW	CG	N
0.300	7.62	70972S	.94	23.9	.206	5.2	46	8.0	.26	6.7	12	53	.47	11.9	0.047	1.2	10.0	SST	CG	N
0.300	7.62	70993	.94	23.9	.202	5.1	64	11	.32	8.0	20	89	.50	12.8	0.049	1.2	10.3	MW	CG	N
0.300	7.62	70993S	.94	23.9	.202	5.1	54	9.5	.25	6.4	14	60	.50	12.8	0.049	1.2	10.3	SST	CG	N
0.300	7.62	71014	.94	23.9	.198	5.0	75	13	.28	7.1	21	94	.53	13.4	0.051	1.3	10.4	MW	CG	N
0.300	7.62	71014S	.94	23.9	.198	5.0	64	11	.22	5.7	14	63	.53	13.4	0.051	1.3	10.4	SST	CG	N
0.300	7.62	70790	1.00	25.4	.256	6.5	3.0	.53	.71	18	2.1	9								




1-800-237-5225
1-213-749-1466
Fax (213)749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70916	1.00	25.4	.220	5.6	25	4.4	.44	11	11	50	.41	10.4	0.040	1.0	10.3	MW	CG	N
0.300	7.62	70916S	1.00	25.4	.220	5.6	22	3.8	.35	8.9	7.5	33	.41	10.4	0.040	1.0	10.3	SST	CG	N
0.300	7.62	70935	1.00	25.4	.216	5.5	30	5.3	.43	11	13	57	.45	11.3	0.042	1.1	10.6	MW	CG	N
0.300	7.62	70935S	1.00	25.4	.216	5.5	26	4.5	.34	8.6	8.7	39	.45	11.3	0.042	1.1	10.6	SST	CG	N
0.300	7.62	70954	1.00	25.4	.210	5.3	40	7.0	.39	9.9	16	70	.49	12.4	0.045	1.1	10.9	MW	CG	N
0.300	7.62	70954S	1.00	25.4	.210	5.3	34	6.0	.31	7.9	11	47	.49	12.4	0.045	1.1	10.9	SST	CG	N
0.300	7.62	70973	1.00	25.4	.206	5.2	50	8.8	.35	9.0	18	79	.50	12.7	0.047	1.2	10.6	MW	CG	N
0.300	7.62	70973S	1.00	25.4	.206	5.2	43	7.5	.28	7.2	12	53	.50	12.7	0.047	1.2	10.6	SST	CG	N
0.300	7.62	70994	1.00	25.4	.202	5.1	59	10	.34	8.6	20	89	.53	13.5	0.049	1.2	10.9	MW	CG	N
0.300	7.62	70994S	1.00	25.4	.202	5.1	50	8.8	.27	6.8	14	60	.53	13.5	0.049	1.2	10.9	SST	CG	N
0.300	7.62	71015	1.00	25.4	.198	5.0	70	12	.30	7.6	21	94	.56	14.2	0.051	1.3	11.0	MW	CG	N
0.300	7.62	71015S	1.00	25.4	.198	5.0	60	10	.24	6.1	14	63	.56	14.2	0.051	1.3	11.0	SST	CG	N
0.300	7.62	70792	1.13	28.7	.256	6.5	2.7	.47	.79	20	2.1	9.5	.17	4.3	0.022	0.6	7.75	MW	CG	N
0.300	7.62	70792S	1.13	28.7	.256	6.5	2.3	.40	.62	16	1.4	6.3	.17	4.3	0.022	0.6	7.75	SST	CG	N
0.300	7.62	70814	1.13	28.7	.248	6.3	4.6	.81	.72	18	3.3	15	.23	5.9	0.026	0.7	9.00	MW	CG	N
0.300	7.62	70814S	1.13	28.7	.248	6.3	3.9	.68	.57	14	2.2	9.8	.23	5.9	0.026	0.7	9.00	SST	CG	N
0.300	7.62	70837	1.13	28.7	.240	6.1	7.6	1.3	.66	17	5.0	22	.29	7.4	0.030	0.8	9.75	MW	CG	N
0.300	7.62	70837S	1.13	28.7	.240	6.1	6.5	1.1	.52	13	3.4	15	.29	7.4	0.030	0.8	9.75	SST	CG	N
0.300	7.62	70859	1.13	28.7	.236	6.0	9.5	1.7	.64	16	6.1	27	.33	8.3	0.032	0.8	10.3	MW	CG	N
0.300	7.62	70859S	1.13	28.7	.236	6.0	8.1	1.4	.50	13	4.1	18	.33	8.3	0.032	0.8	10.3	SST	CG	N
0.300	7.62	70879	1.13	28.7	.230	5.8	13	2.4	.56	14	7.5	34	.37	9.4	0.035	0.9	10.6	MW	CG	N
0.300	7.62	70879S	1.13	28.7	.230	5.8	11	2.0	.45	11	5.1	23	.37	9.4	0.035	0.9	10.6	SST	CG	N
0.300	7.62	70898	1.13	28.7	.224	5.7	19	3.3	.51	13	9.6	43	.41	10.5	0.038	1.0	10.9	MW	CG	N
0.300	7.62	70898S	1.13	28.7	.224	5.7	16	2.8	.41	10	6.5	29	.41	10.5	0.038	1.0	10.9	SST	CG	N
0.300	7.62	70917	1.13	28.7	.220	5.6	22	3.9	.50	13	11	50	.46	11.6	0.040	1.0	11.4	MW	CG	N
0.300	7.62	70917S	1.13	28.7	.220	5.6	19	3.3	.40	10	7.5	33	.46	11.6	0.040	1.0	11.4	SST	CG	N
0.300	7.62	70936	1.13	28.7	.216	5.5	28	4.8	.47	12	13	57	.48	12.3	0.042	1.1	11.5	MW	CG	N
0.300	7.62	70936S	1.13	28.7	.216	5.5	23	4.1	.37	9.4	8.7	39	.48	12.3	0.042	1.1	11.5	SST	CG	N
0.300	7.62	70955	1.13	28.7	.210	5.3	36	6.3	.43	11	16	70	.53	13.6	0.045	1.1	11.9	MW	CG	N
0.300	7.62	70955S	1.13	28.7	.210	5.3	31	5.4	.35	8.8	11	47	.53	13.6	0.045	1.1	11.9	SST	CG	N
0.300	7.62	70974	1.13	28.7	.206	5.2	44	7.7	.40	10	18	79	.55	14.0	0.047	1.2	11.8	MW	CG	N
0.300	7.62	70974S	1.13	28.7	.206	5.2	38	6.6	.32	8.1	12	53	.55	14.0	0.047	1.2	11.8	SST	CG	N
0.300	7.62	70995	1.13	28.7	.202	5.1	52	9.2	.38	9.7	20	89	.59	14.9	0.049	1.2	12.0	MW	CG	N
0.300	7.62	70995S	1.13	28.7	.202	5.1	44	7.8	.30	7.7	14	60	.59	14.9	0.049	1.2	12.0	SST	CG	N
0.300	7.62	71016	1.13	28.7	.198	5.0	62	11	.34	8.7	21	94	.62	15.9	0.051	1.3	12.3	MW	CG	N
0.300	7.62	71016S	1.13	28.7	.198	5.0	52	9.2	.27	6.9	14	63	.62	15.9	0.051	1.3	12.3	SST	CG	N
0.300	7.62	70793	1.25	31.8	.256	6.5	2.4	.42	.89	23	2.1	9.5	.19	4.7	0.022	0.6	8.50	MW	CG	N
0.300	7.62	70793S	1.25	31.8	.256	6.5	2.0	.36	.70	18	1.4	6.3	.19	4.7	0.022	0.6	8.50	SST	CG	N
0.300	7.62	70815	1.25	31.8	.248	6.3	4.3	.75	.77	19	3.3	15	.24	6.2	0.026	0.7	9.38	MW	CG	N
0.300	7.62	70815S	1.25	31.8	.248	6.3	3.7	.64	.60	15	2.2	9.8	.24	6.2	0.026	0.7	9.38	SST	CG	N
0.300	7.62	70838	1.25	31.8	.240	6.1	6.6	1.2	.76	19	5.0	22	.33	8.4	0.030	0.8	11.0	MW	CG	N
0.300	7.62	70838S	1.25	31.8	.240	6.1	5.6	.98	.60	15	3.4	15	.33	8.4	0.030	0.8	11.0	SST	CG	N
0.300	7.62	70860	1.25	31.8	.236	6.0	8.6	1.5	.71	18	6.1	27	.36	9.0	0.032	0.8	11.1	MW	CG	N
0.300	7.62	70860S	1.25	31.8	.236	6.0	7.3	1.3	.56	14	4.1	18	.36	9.0	0.032	0.8	11.1	SST	CG	N
0.300	7.62	70880	1.25	31.8	.230	5.8	12	2.1	.63	16	7.5	34	.41	10.4	0.035	0.9	11.8	MW	CG	N
0.300	7.62	70880S	1.25	31.8	.230	5.8	10	1.8	.50	13	5.1	23	.41	10.4	0.035	0.9	11.8	SST	CG	N
0.300	7.62	70899	1.25	31.8	.224	5.7	16	2.9	.59	15	9.6	43	.47	11.8	0.038	1.0	12.3	MW	CG	N
0.300	7.62	70899S	1.25	31.8	.224	5.7	14	2.4	.47	12	6.5	29	.47	11.8	0.038	1.0	12.3	SST	CG	N
0.300	7.62	70918	1.25	31.8	.220	5.6	20	3.4	.57	14	11	50	.51	12.8	0.040	1.0	12.6	MW	CG	N
0.300	7.62	70918S	1.25	31.8	.220	5.6	17	2.9	.45	11	7.5	33	.51	12.8	0.040	1.0	12.6	SST	CG	N
0.300	7.62	70937	1.25	31.8	.216	5.5	24	4.2	.53	14	13	57	.54	13.7	0.042	1.1	12.9	MW	CG	N
0.300	7.62	70937S	1.25	31.8	.216	5.5	20	3.6	.42	11	8.7	39	.54	13.7	0.042	1.1	12.9	SST	CG	N
0.300	7.62	70956	1.25	31.8	.210	5.3	32	5.6	.49	12	16	70	.59	14.9	0.045	1.1	13.0	MW	CG	N
0.300	7.62	70956S	1.25	31.8	.210	5.3	27	4.8	.39	9.9	11	47	.59	14.9	0.045	1.1	13.0	SST	CG	N
0.300	7.62	70975	1.25	31.8	.206	5.2	39	6.9	.45	11	18	79	.61	15.5	0.047	1.2	13.0	MW	CG	N
0.300	7.62	70975S	1.25	31.8	.206	5.2	36	5.9	.36	9.1	12	53	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.300	7.62	70996	1.25	31.8	.202	5.1	46	8.1	.43	11	20	89	.65	16.5	0.049	1.2	13.3	MW	CG	N
0.300	7.62	70996S	1.25	31.8	.202	5.1	39	6.9	.34	8.7	14	60	.65	16.5	0.049	1.2	13.3	SST	CG	N
0.300	7.62	71017	1.25	31.8	.198	5.0	55	9.6	.38	9.8	21	94	.69	17.5	0.051	1.3	13.5	MW	CG	N
0.300	7.62	71017S	1.25	31.8	.198	5.0	47	8.2	.31	7.8	14	63	.69	17.5	0.051	1.3	13.5	SST	CG	N
0.300	7.62	70795	1.38	35.1	.256	6.5	2.2	.39	.97	25	2.1	9.5	.20	5.1	0.022	0.6	9.13	MW	CG	N
0.300	7.62	70795S	1.38	35.1	.256	6.5	1.9	.33	.76	19	1.4	6.3	.20	5.1	0.022	0.6	9.13	SST	CG	N
0.300	7.62	70817	1.38	35.1	.248	6.3	3.8	.67	.87	22	3.3	15	.27	6.9	0.026	0.7	10.4	MW	CG	N
0.300	7.62	70817S	1.38	35.1	.248	6.3	3.2	.57	.68	17	2.2	9.8	.27	6.9	0.026	0.7	10.4	SST	CG	N
0.300	7.62	70840	1.38	35.1	.240	6.1	6.1	1.1	.83	21	5.0	22	.35	9.0	0.030	0.8	11.8	MW	CG	N
0.300	7.62	70840S	1.38	35.1	.240	6.1	5.2	.91	.65	17	3.4	15	.35	9.0	0.030	0.8	11.8	SST	CG	N
0.300	7.62	70862	1.38	35.1	.236	6.0	7.7	1.3	.79	20	6.1	27	.39	9.9	0.032	0.8	12.1	MW	CG	N
0.300	7.62	70862S	1.38	35.1																




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70997	1.38	35.1	.202	5.1	42	7.3	.48	12	20	89	.72	18.2	0.049	1.2	14.6	MW	CG	N
0.300	7.62	70997S	1.38	35.1	.202	5.1	35	6.2	.38	9.7	14	60	.72	18.2	0.049	1.2	14.6	SST	CG	N
0.300	7.62	71018	1.38	35.1	.198	5.0	49	8.6	.43	11	21	94	.75	19.1	0.051	1.3	14.8	MW	CG	N
0.300	7.62	71018S	1.38	35.1	.198	5.0	42	7.3	.34	8.6	14	63	.75	19.1	0.051	1.3	14.8	SST	CG	N
0.300	7.62	70796	1.50	38.1	.256	6.5	2.1	.36	1.0	26	2.1	9.5	.21	5.4	0.022	0.6	9.63	MW	CG	N
0.300	7.62	70796S	1.50	38.1	.256	6.5	1.7	.31	.81	21	1.4	6.3	.21	5.4	0.022	0.6	9.63	SST	CG	N
0.300	7.62	70818	1.50	38.1	.248	6.3	3.5	.61	.94	24	3.3	15	.29	7.3	0.026	0.7	11.1	MW	CG	N
0.300	7.62	70818S	1.50	38.1	.248	6.3	3.0	.52	.74	19	2.2	9.8	.29	7.3	0.026	0.7	11.1	SST	CG	N
0.300	7.62	70841	1.50	38.1	.240	6.1	5.5	.95	.92	23	5.0	22	.39	9.8	0.030	0.8	12.9	MW	CG	N
0.300	7.62	70841S	1.50	38.1	.240	6.1	4.6	.81	.73	18	3.4	15	.39	9.8	0.030	0.8	12.9	SST	CG	N
0.300	7.62	70863	1.50	38.1	.236	6.0	7.1	1.2	.86	22	6.1	27	.42	10.7	0.032	0.8	13.1	MW	CG	N
0.300	7.62	70863S	1.50	38.1	.236	6.0	6.0	1.0	.68	17	4.1	18	.42	10.7	0.032	0.8	13.1	SST	CG	N
0.300	7.62	70882	1.50	38.1	.230	5.8	9.9	1.7	.76	19	7.5	34	.48	12.2	0.035	0.9	13.8	MW	CG	N
0.300	7.62	70882S	1.50	38.1	.230	5.8	8.4	1.5	.61	15	5.1	23	.48	12.2	0.035	0.9	13.8	SST	CG	N
0.300	7.62	70901	1.50	38.1	.224	5.7	14	2.4	.70	18	9.6	43	.54	13.6	0.038	1.0	14.1	MW	CG	N
0.300	7.62	70901S	1.50	38.1	.224	5.7	12	2.0	.56	14	6.5	29	.54	13.6	0.038	1.0	14.1	SST	CG	N
0.300	7.62	70920	1.50	38.1	.220	5.6	16	2.8	.70	18	11	50	.61	15.4	0.040	1.0	15.1	MW	CG	N
0.300	7.62	70920S	1.50	38.1	.220	5.6	14	2.4	.55	14	7.5	33	.61	15.4	0.040	1.0	15.1	SST	CG	N
0.300	7.62	70939	1.50	38.1	.216	5.5	20	3.5	.65	16	13	57	.64	16.1	0.042	1.1	15.1	MW	CG	N
0.300	7.62	70939S	1.50	38.1	.216	5.5	17	3.0	.51	13	8.7	39	.64	16.1	0.042	1.1	15.1	SST	CG	N
0.300	7.62	70958	1.50	38.1	.210	5.3	26	4.6	.60	15	16	70	.70	17.7	0.045	1.1	15.5	MW	CG	N
0.300	7.62	70958S	1.50	38.1	.210	5.3	22	3.9	.48	12	11	47	.70	17.7	0.045	1.1	15.5	SST	CG	N
0.300	7.62	12758	1.50	38.1	.206	5.2	27	4.8	.44	11	12	53	.74	18.8	0.047	1.2	15.8	SST	CG	N
0.300	7.62	70977	1.50	38.1	.206	5.2	32	5.7	.55	14	18	79	.72	18.4	0.047	1.2	15.4	MW	CG	N
0.300	7.62	70977S	1.50	38.1	.206	5.2	27	4.8	.44	11	12	53	.72	18.4	0.047	1.2	15.4	SST	CG	N
0.300	7.62	70998	1.50	38.1	.202	5.1	38	6.7	.53	13	20	89	.77	19.6	0.049	1.2	15.8	MW	CG	N
0.300	7.62	70998S	1.50	38.1	.202	5.1	32	5.7	.42	11	14	60	.77	19.6	0.049	1.2	15.8	SST	CG	N
0.300	7.62	71019	1.50	38.1	.198	5.0	45	7.9	.47	12	21	94	.82	20.7	0.051	1.3	16.0	MW	CG	N
0.300	7.62	71019S	1.50	38.1	.198	5.0	38	6.7	.37	9.5	14	63	.82	20.7	0.051	1.3	16.0	SST	CG	N
0.300	7.62	70797	1.75	44.5	.256	6.5	1.7	.30	1.2	31	2.1	9.5	.24	6.2	0.022	0.6	11.1	MW	CG	N
0.300	7.62	70797S	1.75	44.5	.256	6.5	1.5	.26	.97	25	1.4	6.3	.24	6.2	0.022	0.6	11.1	SST	CG	N
0.300	7.62	70819	1.75	44.5	.248	6.3	3.0	.53	1.1	28	3.3	15	.33	8.3	0.026	0.7	12.6	MW	CG	N
0.300	7.62	70819S	1.75	44.5	.248	6.3	2.6	.45	.87	22	2.2	9.8	.33	8.3	0.026	0.7	12.6	SST	CG	N
0.300	7.62	70842	1.75	44.5	.240	6.1	4.7	.81	1.1	27	5.0	22	.44	11.2	0.030	0.8	14.8	MW	CG	N
0.300	7.62	70842S	1.75	44.5	.240	6.1	4.0	.69	.85	22	3.4	15	.44	11.2	0.030	0.8	14.8	SST	CG	N
0.300	7.62	70864	1.75	44.5	.236	6.0	6.0	1.1	1.0	26	6.1	27	.48	12.2	0.032	0.8	15.0	MW	CG	N
0.300	7.62	70864S	1.75	44.5	.236	6.0	5.1	.89	.80	20	4.1	18	.48	12.2	0.032	0.8	15.0	SST	CG	N
0.300	7.62	70883	1.75	44.5	.230	5.8	8.4	1.5	.90	23	7.5	34	.55	14.0	0.035	0.9	15.8	MW	CG	N
0.300	7.62	70883S	1.75	44.5	.230	5.8	7.1	1.3	.71	18	5.1	23	.55	14.0	0.035	0.9	15.8	SST	CG	N
0.300	7.62	70902	1.75	44.5	.224	5.7	11	2.0	.85	22	9.6	43	.64	16.3	0.038	1.0	16.9	MW	CG	N
0.300	7.62	70902S	1.75	44.5	.224	5.7	9.5	1.7	.68	17	6.5	29	.64	16.3	0.038	1.0	16.9	SST	CG	N
0.300	7.62	70921	1.75	44.5	.220	5.6	14	2.4	.81	20	11	50	.69	17.4	0.040	1.0	17.1	MW	CG	N
0.300	7.62	70921S	1.75	44.5	.220	5.6	12	2.1	.64	16	7.5	33	.69	17.4	0.040	1.0	17.1	SST	CG	N
0.300	7.62	70940	1.75	44.5	.216	5.5	16	2.9	.78	20	13	57	.75	19.1	0.042	1.1	17.9	MW	CG	N
0.300	7.62	70940S	1.75	44.5	.216	5.5	14	2.4	.62	16	8.7	39	.75	19.1	0.042	1.1	17.9	SST	CG	N
0.300	7.62	70959	1.75	44.5	.210	5.3	22	3.8	.72	18	16	70	.83	21.0	0.045	1.1	18.4	MW	CG	N
0.300	7.62	70959S	1.75	44.5	.210	5.3	18	3.2	.57	15	11	47	.83	21.0	0.045	1.1	18.4	SST	CG	N
0.300	7.62	70978	1.75	44.5	.206	5.2	28	4.8	.65	16	18	79	.83	21.2	0.047	1.2	17.8	MW	CG	N
0.300	7.62	70978S	1.75	44.5	.206	5.2	23	4.1	.51	13	12	53	.83	21.2	0.047	1.2	17.8	SST	CG	N
0.300	7.62	70999	1.75	44.5	.202	5.1	32	5.7	.62	16	20	89	.89	22.6	0.049	1.2	18.1	MW	CG	N
0.300	7.62	70999S	1.75	44.5	.202	5.1	28	4.8	.49	13	14	60	.89	22.6	0.049	1.2	18.1	SST	CG	N
0.300	7.62	71020	1.75	44.5	.198	5.0	38	6.7	.55	14	21	94	.94	24.0	0.051	1.3	18.5	MW	CG	N
0.300	7.62	71020S	1.75	44.5	.198	5.0	32	5.7	.44	11	14	63	.94	24.0	0.051	1.3	18.5	SST	CG	N
0.300	7.62	70798	2.00	50.8	.256	6.5	1.5	.25	1.5	37	2.1	9.5	.28	7.1	0.022	0.6	12.8	MW	CG	N
0.300	7.62	70798S	2.00	50.8	.256	6.5	1.2	.22	1.2	29	1.4	6.3	.28	7.1	0.022	0.6	12.8	SST	CG	N
0.300	7.62	70820	2.00	50.8	.248	6.3	2.6	.46	1.3	32	3.3	15	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.300	7.62	70820S	2.00	50.8	.248	6.3	2.2	.39	1.0	25	2.2	9.8	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.300	7.62	70843	2.00	50.8	.240	6.1	4.0	.70	1.3	32	5.0	22	.50	12.8	0.030	0.8	16.8	MW	CG	N
0.300	7.62	70843S	2.00	50.8	.240	6.1	3.4	.60	.99	25	3.4	15	.50	12.8	0.030	0.8	16.8	SST	CG	N
0.300	7.62	70865	2.00	50.8	.236	6.0	5.3	.93	1.1	29	6.1	27	.54	13.6	0.032	0.8	16.8	MW	CG	N
0.300	7.62	70865S	2.00	50.8	.236	6.0	4.5	.79	.90	23	4.1	18	.54	13.6	0.032	0.8	16.8	SST	CG	N
0.300	7.62	70884	2.00	50.8	.230	5.8	7.3	1.3	1.0	26	7.5	34	.63	15.9	0.035	0.9	17.9	MW	CG	N
0.300	7.62	70884S	2.00	50.8	.230	5.8	6.2	1.1	.82	21	5.1	23	.63	15.9	0.035	0.9	17.9	SST	CG	N
0.300	7.62	70903	2.00	50.8	.224	5.7	9.6	1.7	1.0	25	9.6	43	.74	18.7	0.038	1.0	19.4	MW	CG	N
0.300	7.62	70903S	2.00	50.8	.224	5.7	8.2	1.4	.79	20	6.5	29	.74	18.7	0.038	1.0	19.4	SST	CG	N
0.300	7.62	70922	2.00	50.8	.220	5.6	12	2.1	.94	24	11	50	.79	19.9	0.040	1.0	19.6	MW	CG	N
0.300	7.62	70922S	2.00	50.8	.220	5.6	10	1.8	.74	19	7.5	33	.79	19.9	0.040	1.0	19.6	SST	CG	N
0.300	7.62	70941	2.00	50.8	.216	5.5	14	2.5	.89	23	13	57	.85	21.5	0.042	1.1	20.1	MW		




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com


O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70821S	2.25	57.2	.248	6.3	2.0	.36	1.1	27	2.2	9.8	.40	10.1	0.026	0.7	15.3	SST	CG	N
0.300	7.62	70844	2.25	57.2	.240	6.1	3.6	.63	1.4	36	5.0	22	.56	14.2	0.030	0.8	18.6	MW	CG	N
0.300	7.62	70844S	2.25	57.2	.240	6.1	3.0	.53	1.1	28	3.4	15	.56	14.2	0.030	0.8	18.6	SST	CG	N
0.300	7.62	70866	2.25	57.2	.236	6.0	4.8	.84	1.3	32	6.1	27	.59	14.9	0.032	0.8	18.4	MW	CG	N
0.300	7.62	70866S	2.25	57.2	.236	6.0	4.1	.71	1.0	25	4.1	18	.59	14.9	0.032	0.8	18.4	SST	CG	N
0.300	7.62	70885	2.25	57.2	.230	5.8	6.5	1.1	1.2	30	7.5	34	.70	17.8	0.035	0.9	20.0	MW	CG	N
0.300	7.62	70885S	2.25	57.2	.230	5.8	5.5	.96	.93	24	5.1	23	.70	17.8	0.035	0.9	20.0	SST	CG	N
0.300	7.62	70904	2.25	57.2	.224	5.7	8.8	1.5	1.1	28	9.6	43	.80	20.3	0.038	1.0	21.0	MW	CG	N
0.300	7.62	70904S	2.25	57.2	.224	5.7	7.5	1.3	.87	22	6.5	29	.80	20.3	0.038	1.0	21.0	SST	CG	N
0.300	7.62	70923	2.25	57.2	.220	5.6	11	1.8	1.1	27	11	50	.88	22.2	0.040	1.0	21.9	MW	CG	N
0.300	7.62	70923S	2.25	57.2	.220	5.6	9.0	1.6	.84	21	7.5	33	.88	22.2	0.040	1.0	21.9	SST	CG	N
0.300	7.62	70942	2.25	57.2	.216	5.5	13	2.2	1.0	25	13	57	.94	23.9	0.042	1.1	22.4	MW	CG	N
0.300	7.62	70942S	2.25	57.2	.216	5.5	11	1.9	.80	20	8.7	39	.94	23.9	0.042	1.1	22.4	SST	CG	N
0.300	7.62	70961	2.25	57.2	.210	5.3	17	2.9	.93	24	16	70	1.04	26.4	0.045	1.1	23.1	MW	CG	N
0.300	7.62	70961S	2.25	57.2	.210	5.3	14	2.5	.74	19	11	47	1.04	26.4	0.045	1.1	23.1	SST	CG	N
0.300	7.62	70980	2.25	57.2	.206	5.2	21	3.7	.84	21	18	79	1.06	26.9	0.047	1.2	22.5	MW	CG	N
0.300	7.62	70980S	2.25	57.2	.206	5.2	18	3.1	.67	17	12	53	1.06	26.9	0.047	1.2	22.5	SST	CG	N
0.300	7.62	71001	2.25	57.2	.202	5.1	25	4.3	.81	21	20	89	1.13	28.8	0.049	1.2	23.1	MW	CG	N
0.300	7.62	71001S	2.25	57.2	.202	5.1	21	3.7	.64	16	14	60	1.13	28.8	0.049	1.2	23.1	SST	CG	N
0.300	7.62	71022	2.25	57.2	.198	5.0	29	5.1	.72	18	21	94	1.20	30.4	0.051	1.3	23.5	MW	CG	N
0.300	7.62	71022S	2.25	57.2	.198	5.0	25	4.4	.57	15	14	63	1.20	30.4	0.051	1.3	23.5	SST	CG	N
0.300	7.62	70800	2.50	63.5	.256	6.5	1.2	.21	1.8	46	2.1	9.5	.34	8.5	0.022	0.6	15.3	MW	CG	N
0.300	7.62	70800S	2.50	63.5	.256	6.5	1.0	.18	1.4	36	1.4	6.3	.34	8.5	0.022	0.6	15.3	SST	CG	N
0.300	7.62	70822	2.50	63.5	.248	6.3	2.1	.37	1.5	39	3.3	15	.44	11.1	0.026	0.7	16.9	MW	CG	N
0.300	7.62	70822S	2.50	63.5	.248	6.3	1.8	.32	1.2	31	2.2	9.8	.44	11.1	0.026	0.7	16.9	SST	CG	N
0.300	7.62	70845	2.50	63.5	.240	6.1	3.2	.57	1.6	39	5.0	22	.61	15.4	0.030	0.8	20.3	MW	CG	N
0.300	7.62	70845S	2.50	63.5	.240	6.1	2.8	.48	1.2	31	3.4	15	.61	15.4	0.030	0.8	20.3	SST	CG	N
0.300	7.62	70867	2.50	63.5	.236	6.0	4.3	.74	1.4	36	6.1	27	.65	16.6	0.032	0.8	20.4	MW	CG	N
0.300	7.62	70867S	2.50	63.5	.236	6.0	3.6	.63	1.1	29	4.1	18	.65	16.6	0.032	0.8	20.4	SST	CG	N
0.300	7.62	70886	2.50	63.5	.230	5.8	5.9	1.0	1.3	33	7.5	34	.77	19.4	0.035	0.9	21.9	MW	CG	N
0.300	7.62	70886S	2.50	63.5	.230	5.8	5.0	.87	1.0	26	5.1	23	.77	19.4	0.035	0.9	21.9	SST	CG	N
0.300	7.62	70905	2.50	63.5	.224	5.7	8.0	1.4	1.2	31	9.6	43	.87	22.2	0.038	1.0	23.0	MW	CG	N
0.300	7.62	70905S	2.50	63.5	.224	5.7	6.8	1.2	.96	24	6.5	29	.87	22.2	0.038	1.0	23.0	SST	CG	N
0.300	7.62	70924	2.50	63.5	.220	5.6	9.5	1.7	1.2	30	11	50	.96	24.4	0.040	1.0	24.0	MW	CG	N
0.300	7.62	70924S	2.50	63.5	.220	5.6	8.1	1.4	.93	24	7.5	33	.96	24.4	0.040	1.0	24.0	SST	CG	N
0.300	7.62	70943	2.50	63.5	.216	5.5	12	2.0	1.1	28	13	57	1.02	25.9	0.042	1.1	24.3	MW	CG	N
0.300	7.62	70943S	2.50	63.5	.216	5.5	9.9	1.7	.87	22	8.7	39	1.02	25.9	0.042	1.1	24.3	SST	CG	N
0.300	7.62	70962	2.50	63.5	.210	5.3	15	2.7	1.0	26	16	70	1.13	28.6	0.045	1.1	25.0	MW	CG	N
0.300	7.62	70962S	2.50	63.5	.210	5.3	13	2.3	.81	21	11	47	1.13	28.6	0.045	1.1	25.0	SST	CG	N
0.300	7.62	70981	2.50	63.5	.206	5.2	19	3.3	.94	24	18	79	1.17	29.7	0.047	1.2	24.9	MW	CG	N
0.300	7.62	70981S	2.50	63.5	.206	5.2	16	2.8	.75	19	12	53	1.17	29.7	0.047	1.2	24.9	SST	CG	N
0.300	7.62	71002	2.50	63.5	.202	5.1	22	3.9	.90	23	20	89	1.25	31.7	0.049	1.2	25.5	MW	CG	N
0.300	7.62	71002S	2.50	63.5	.202	5.1	19	3.3	.72	18	14	60	1.25	31.7	0.049	1.2	25.5	SST	CG	N
0.300	7.62	71023	2.50	63.5	.198	5.0	26	4.6	.80	20	21	94	1.33	33.7	0.051	1.3	26.0	MW	CG	N
0.300	7.62	71023S	2.50	63.5	.198	5.0	22	3.9	.64	16	14	63	1.33	33.7	0.051	1.3	26.0	SST	CG	N
0.300	7.62	70982	2.75	69.9	.206	5.2	17	3.0	1.0	26	18	79	1.29	32.7	0.047	1.2	27.4	MW	CG	N
0.300	7.62	70982S	2.75	69.9	.206	5.2	15	2.5	.83	21	12	53	1.29	32.7	0.047	1.2	27.4	SST	CG	N
0.300	7.62	71003	2.75	69.9	.202	5.1	20	3.5	.99	25	20	89	1.37	34.8	0.049	1.2	28.0	MW	CG	N
0.300	7.62	71003S	2.75	69.9	.202	5.1	17	3.0	.79	20	14	60	1.37	34.8	0.049	1.2	28.0	SST	CG	N
0.300	7.62	71024	2.75	69.9	.198	5.0	24	4.2	.88	22	21	94	1.45	36.9	0.051	1.3	28.5	MW	CG	N
0.300	7.62	71024S	2.75	69.9	.198	5.0	20	3.5	.71	18	14	63	1.45	36.9	0.051	1.3	28.5	SST	CG	N
0.300	7.62	12640	2.88	73.0	.260	6.6	.33	.06	2.3	57	.73	3.3	.62	15.7	0.020	0.5	30.0	SST	C	N
0.300	7.62	70983	3.00	76.2	.206	5.2	16	2.7	1.1	29	18	79	1.39	35.4	0.047	1.2	29.6	MW	CG	N
0.300	7.62	70983S	3.00	76.2	.206	5.2	13	2.3	.90	23	12	53	1.39	35.4	0.047	1.2	29.6	SST	CG	N
0.300	7.62	71004	3.00	76.2	.202	5.1	18	3.2	1.1	28	20	89	1.49	38.0	0.049	1.2	30.5	MW	CG	N
0.300	7.62	71004S	3.00	76.2	.202	5.1	16	2.7	.87	22	14	60	1.49	38.0	0.049	1.2	30.5	SST	CG	N
0.300	7.62	71025	3.00	76.2	.198	5.0	22	3.8	.97	25	21	94	1.58	40.2	0.051	1.3	31.0	MW	CG	N
0.300	7.62	71025S	3.00	76.2	.198	5.0	18	3.2	.77	20	14	63	1.58	40.2	0.051	1.3	31.0	SST	CG	N
0.304	7.72	A9-39	.78	19.8	.190	4.8	93	16	.22	5.6	21	92	.46	11.8	0.057	1.4	8.00	PB	CG	N
0.312	7.92	II-25	.19	4.8	.252	6.4	45	7.9	.07	1.7	3.1	14	.12	3.0	0.030	0.8	3.00	SST	C	N
0.312	7.92	KK-86	.22	5.6	.260	6.6	17	2.9	.10	2.6	1.7	7.5	.12	3.0	0.026	0.7	3.50	SST	C	N
0.312	7.92	NN-86	.25	6.4	.258	6.6	17	2.9	.12	2.9	1.9	8.4	.14	3.4	0.027	0.7	4.00	MW	C	N
0.312	7.92	A15-5	.25	6.4	.252	6.4	16	2.7	.10	2.5	1.6	7.0	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.312	7.92	EE-4	.25	6.4	.232	5.9	80	14	.09	2.3	7.2	32	.16	4.1	0.040	1.0	4.00	SST	CG	N
0.312	7.92	S-1267	.31	7.9	.288	7.3	.26	.04	.23	5.9	.06	.26	.08	2.1	0.012	0.3	5.75	SST	C	N
0.312	7.92	A-81	.31	7.9	.262	6.7	12	2.1	.19	4.7	2.2	9.9	.13	3.2	0.025	0.6	4.00	MW	C	Z
0.312	7.92	12482	.31	7.9	.248	6.3	46	8.0	.09	2.3	4.2	19	.14	3.7	0.032	0.8	3.50	SPR	C	N
0.312	7.92	GG-15	.31	7.9	.202	5.1	34													



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.312	7.92	EE-9	.38	9.5	.226	5.7	101	18	.09	2.4	9.6	43	.19	4.9	0.043	1.1	4.50	SPR	CG	Z
0.312	7.92	S-1086	.38	9.5	.218	5.5	131	23	.09	2.2	12	52	.21	5.4	0.047	1.2	4.50	SST	CG	N
0.312	7.92	K-93	.38	9.5	.218	5.5	94	17	.09	2.4	8.8	39	.28	7.2	0.047	1.2	6.00	SPR	CG	Z
0.312	7.92	S-1125	.38	9.5	.214	5.4	158	28	.08	2.1	13	58	.22	5.6	0.049	1.2	4.50	SST	CG	N
0.312	7.92	3688	.41	10.3	.272	6.9	2.3	.40	.27	6.8	.61	2.7	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	JJ-22	.41	10.3	.244	6.2	26	4.6	.18	4.5	4.7	21	.20	5.2	0.034	0.9	5.00	SST	C	N
0.312	7.92	FF-3	.44	11.1	.280	7.1	.91	.16	.33	8.3	.30	1.3	.11	2.8	0.016	0.4	6.00	MW	C	N
0.312	7.92	KK-92	.44	11.1	.252	6.4	11	2.0	.23	5.8	2.6	11	.21	5.3	0.030	0.8	6.00	SST	C	N
0.312	7.92	A11-23	.44	11.1	.246	6.2	26	4.6	.18	4.5	4.6	21	.17	4.3	0.033	0.8	5.00	SPR	CG	GI
0.312	7.92	A14-25	.44	11.1	.236	6.0	39	6.8	.16	4.1	6.24	27.72	.12	3.0	0.038	1.0	5.25	SST	CG	N
0.312	7.92	LL-16	.44	11.1	.232	5.9	41	7.1	.18	4.6	7.3	32	.24	6.1	0.040	1.0	6.00	SST	CG	N
0.312	7.92	S-484	.44	11.1	.230	5.8	43	7.5	.18	4.6	7.8	35	.25	6.4	0.041	1.0	6.13	SST	CG	N
0.312	7.92	B9-30	.44	11.1	.230	5.8	82	14	.10	2.6	8.3	37	.18	4.7	0.041	1.0	4.50	SPR	CG	N
0.312	7.92	H-96	.44	11.1	.212	5.4	167	29	.08	2.1	14	62	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.312	7.92	II-23	.44	11.1	.212	5.4	136	24	.10	2.4	13	58	.26	6.7	0.050	1.3	5.25	SST	CG	N
0.312	7.92	2920	.44	11.1	.180	4.6	697	122	.04	1.1	30	136	.31	7.8	0.066	1.7	4.63	SPR	CG	Z
0.312	7.92	NN-6	.47	11.9	.272	6.9	2.0	.36	.33	8.3	.67	3.0	.14	3.6	0.020	0.5	6.00	SST	C	N
0.312	7.92	J-27	.47	11.9	.252	6.4	11	2.0	.26	6.6	2.9	13	.21	5.3	0.030	0.8	6.00	SST	C	N
0.312	7.92	A10-36	.47	11.9	.250	6.4	18	3.1	.20	5.1	3.6	16	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.312	7.92	DD-85	.47	11.9	.242	6.1	29	5.2	.17	4.2	4.9	22	.21	5.3	0.035	0.9	5.00	SST	C	N
0.312	7.92	J-52	.47	11.9	.238	6.0	43	7.6	.14	3.6	6.2	27	.22	5.6	0.037	0.9	5.00	SPR	C	N
0.312	7.92	10487	.50	12.7	.284	7.2	1.0	.18	.43	11	.45	2.0	.07	1.8	0.014	0.4	4.00	MW	C	N
0.312	7.92	4231	.50	12.7	.282	7.2	.51	.09	.37	9.5	.19	.84	.13	3.2	0.015	0.4	7.50	MW	C	N
0.312	7.92	4199	.50	12.7	.276	7.0	1.2	.21	.36	9.0	.42	1.9	.14	3.7	0.018	0.5	7.00	MW	C	Z
0.312	7.92	H-69	.50	12.7	.272	6.9	1.4	.24	.32	8.1	.44	1.9	.18	4.6	0.020	0.5	8.00	SST	C	N
0.312	7.92	B14-5	.50	12.7	.270	6.9	2.3	.40	.35	9.0	.80	3.6	.15	3.7	0.021	0.5	7.00	MW	CG	N
0.312	7.92	S-727	.50	12.7	.268	6.8	4.8	.84	.28	7.2	1.4	6.1	.12	3.1	0.022	0.6	4.50	SST	C	N
0.312	7.92	B2-28	.50	12.7	.266	6.8	7.4	1.3	.32	8.0	2.3	10	.12	3.1	0.023	0.6	4.25	MW	C	N
0.312	7.92	PP-31	.50	12.7	.256	6.5	13	2.3	.31	7.8	4.0	18	.14	3.6	0.028	0.7	5.00	MW	CG	N
0.312	7.92	10229	.50	12.7	.248	6.3	17	3.0	.25	6.2	4.2	19	.22	5.7	0.032	0.8	6.00	SPR	C	Z
0.312	7.92	931	.50	12.7	.238	6.0	37	6.5	.23	5.9	8.5	38	.20	5.2	0.037	0.9	5.50	MW	CG	Z
0.312	7.92	L-8	.50	12.7	.236	6.0	42	7.4	.15	3.8	6.3	28	.23	5.8	0.038	1.0	5.00	SST	C	N
0.312	7.92	10856	.50	12.7	.230	5.8	51	8.9	.16	4.1	8.3	37	.25	6.2	0.041	1.0	6.00	SPR	CG	N
0.312	7.92	DD-34	.50	12.7	.192	4.9	291	51	.08	2.0	23	104	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.312	7.92	S-1265	.53	13.5	.238	6.0	28	4.9	.21	5.2	5.8	26	.26	6.6	0.037	0.9	6.00	SST	C	N
0.312	7.92	HH-29	.53	13.5	.232	5.9	36	6.3	.20	5.1	7.3	32	.26	6.6	0.040	1.0	6.50	SST	CG	N
0.312	7.92	CC-11	.53	13.5	.232	5.9	52	9.1	.15	3.8	7.8	35	.26	6.6	0.040	1.0	5.50	SPR	C	N
0.312	7.92	MM-65	.53	13.5	.212	5.4	148	26	.09	2.2	13	58	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.312	7.92	S-27	.53	13.5	.210	5.3	121	21	.11	2.9	14	61	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.312	7.92	S-1016	.56	14.3	.282	7.2	.44	.08	.43	11	.19	.85	.13	3.2	0.015	0.4	7.50	SST	C	N
0.312	7.92	A-24	.56	14.3	.278	7.1	.49	.09	.37	9.3	.18	.80	.20	5.0	0.017	0.4	10.5	SST	C	Z
0.312	7.92	2850	.56	14.3	.272	6.9	4.6	.81	.34	8.5	1.5	6.9	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.312	7.92	YY-41	.56	14.3	.272	6.9	.73	.13	.28	7.2	.21	.92	.28	7.1	0.020	0.5	13.0	SST	C	N
0.312	7.92	10931	.56	14.3	.268	6.8	3.9	.69	.42	11	1.7	7.4	.14	3.6	0.022	0.6	5.50	MW	C	Z
0.312	7.92	3853	.56	14.3	.264	6.7	6.7	1.2	.40	10	2.7	12	.14	3.7	0.024	0.6	5.00	MW	C	Z
0.312	7.92	K-76	.56	14.3	.262	6.7	5.9	1.0	.39	9.8	2.3	10	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.312	7.92	B7-13	.56	14.3	.262	6.7	9.5	1.7	.30	7.6	2.8	13	.11	2.9	0.025	0.6	4.50	MW	CG	N
0.312	7.92	MM-15	.56	14.3	.252	6.4	12	2.0	.37	9.3	4.2	19	.20	5.0	0.030	0.8	6.50	MW	CG	N
0.312	7.92	H-66	.56	14.3	.204	5.2	237	42	.07	1.8	17	77	.27	6.9	0.054	1.4	5.00	SPR	CG	N
0.312	7.92	LL-73	.56	14.3	.192	4.9	258	45	.08	2.2	22	98	.36	9.1	0.060	1.5	6.00	SST	CG	N
0.312	7.92	10509	.59	15.1	.220	5.6	76	13	.15	3.9	12	52	.35	8.8	0.046	1.2	6.50	SPR	C	Z
0.312	7.92	A11-67	.63	15.9	.266	6.8	4.4	.78	.47	12	2.1	9.3	.16	3.9	0.023	0.6	5.75	MW	C	N
0.312	7.92	S-388	.63	15.9	.262	6.7	5.3	.93	.36	9.0	1.9	8.4	.17	4.4	0.025	0.6	5.88	SST	C	N
0.312	7.92	530	.63	15.9	.260	6.6	7.0	1.2	.44	11	3.1	14	.18	4.6	0.026	0.7	6.00	MW	C	Z
0.312	7.92	PP-97	.63	15.9	.258	6.6	9.6	1.7	.25	6.3	2.4	11	.16	4.1	0.027	0.7	5.00	SST	C	N
0.312	7.92	QQ-67	.63	15.9	.256	6.5	11	1.9	.36	9.1	4.0	18	.18	4.6	0.028	0.7	5.50	MW	C	Z
0.312	7.92	Y-20	.63	15.9	.246	6.2	26	4.6	.18	4.5	4.6	21	.20	5.0	0.033	0.8	5.00	SPR	C	N
0.312	7.92	PP-53	.63	15.9	.244	6.2	30	5.2	.17	4.3	5.0	22	.20	5.2	0.034	0.9	5.00	SPR	C	Z
0.312	7.92	FF-85	.63	15.9	.236	6.0	27	4.7	.23	6.0	6.3	28	.26	6.5	0.038	1.0	6.75	SST	CG	N
0.312	7.92	WW-32	.63	15.9	.236	6.0	32	5.5	.20	5.0	6.3	28	.23	5.8	0.038	1.0	6.00	SST	CG	N
0.312	7.92	A14-22	.63	15.9	.230	5.8	41	7.1	.20	5.2	8.3	37	.29	7.3	0.041	1.0	7.00	SPR	CG	GI
0.312	7.92	S-1065	.63	15.9	.204	5.2	124	22	.13	3.3	16	72	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.312	7.92	S-1226	.63	15.9	.188	4.8	278	49	.09	2.2	24	107	.39	9.8	0.062	1.6	6.25	SST	CG	N
0.312	7.92	2846	.66	16.7	.272	6.9	2.3	.40	.52	13	1.2	5.3	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	PP-67	.66	16.7	.272	6.9	2.3	.40	.52	13	1.2	5.3	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	I-42	.66	16.7	.238	6.0	16	2.9	.32	8.2	5.3	24	.33	8.5	0.037	0.9	9.00	SST	CG	N
0.312	7.92	2700	.66	16.7	.230	5.8	45	7.9	.18	4.7	8.3	37	.27	6.8	0.041	1.0	6.50	HD	CG	Z
0.312	7.92	A15-41	.66	16.7	.230	5.8	48	8.5	.16	4.1	7.8	35	.24	6.0	0.041	1.0	5.75	SST	CG	N
0.312	7.92	XX-25	.69	17.4	.256	6.5	7.7	1.4	.46	12	3.6	16	.22	5.7	0.028	0.7	7.00	MW	C	GI
0.312	7.92	4245	.69	17.4	.254	6.5	7.5	1.3	.43											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	B9-39	.66	16.7	.521	13.2	19	3.3	.40	10	7.4	33	.26	6.6	0.052	1.3	5.00	SPR	CG	N
0.625	15.88	XX-56	.69	17.4	.545	13.8	8.0	1.4	.47	12	3.8	17	.20	5.1	0.040	1.0	4.00	SST	C	N
0.625	15.88	A9-66	.72	18.2	.561	14.2	2.3	.41	.57	14	1.3	5.9	.15	3.8	0.032	0.8	4.75	SST	CG	N
0.625	15.88	522	.75	19.1	.543	13.8	10	1.8	.42	11	4.3	19	.21	5.2	0.041	1.0	4.00	HD	C	Z
0.625	15.88	918	.75	19.1	.543	13.8	6.8	1.2	.50	13	3.4	15	.25	6.2	0.041	1.0	5.00	HD	C	Z
0.625	15.88	CC-24	.75	19.1	.525	13.3	16	2.8	.46	12	7.3	32	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.625	15.88	S-766	.75	19.1	.515	13.1	27	4.8	.33	8.4	9.0	40	.29	7.3	0.055	1.4	4.25	SST	C	N
0.625	15.88	S-286	.75	19.1	.481	12.2	50	8.7	.32	8.1	16	70	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.625	15.88	10279	.75	19.1	.465	11.8	182	32	.15	3.8	27	122	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
0.625	15.88	4205	.75	19.1	.415	10.5	414	73	.14	3.6	58	258	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
0.625	15.88	S-58	.78	19.8	.501	12.7	69	12	.19	4.7	13	57	.22	5.5	0.062	1.6	3.50	SST	CG	N
0.625	15.88	K-59	.78	19.8	.445	11.3	154	27	.24	6.1	37	165	.54	13.7	0.090	2.3	6.00	SPR	CG	N
0.625	15.88	A11-43	.81	20.6	.519	13.2	23	4.0	.35	8.9	8.1	36	.23	5.8	0.053	1.3	4.33	SST	CG	N
0.625	15.88	S-826	.81	20.6	.425	10.8	247	43	.19	4.8	47	208	.55	14.0	0.100	2.5	5.50	SST	CG	N
0.625	15.88	10888	.84	21.4	.589	15.0	.17	.03	.73	18	.12	.55	.12	3.0	0.018	0.5	5.50	SST	C	N
0.625	15.88	S-68	.88	22.2	.549	13.9	4.7	.82	.69	17	3.2	14	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.625	15.88	2831	.88	22.2	.531	13.5	7.3	1.3	.50	13	3.6	16	.38	9.6	0.047	1.2	7.00	HD	C	Z
0.625	15.88	B12-58	.88	22.2	.515	13.1	14	2.5	.49	12	7.0	31	.39	9.8	0.055	1.4	7.00	SPR	CG	Z
0.625	15.88	3911	.88	22.2	.501	12.7	30	5.2	.46	12	14	61	.37	9.4	0.062	1.6	6.00	HD	CG	Z
0.625	15.88	3192	.88	22.2	.439	11.2	238	42	.17	4.4	41	182	.47	11.8	0.093	2.4	5.00	SPR	CG	Z
0.625	15.88	10982	.88	22.2	.431	10.9	219	38	.20	5.0	43	190	.53	13.6	0.097	2.5	5.50	SST	CG	N
0.625	15.88	A9-69	.91	23.0	.543	13.8	7.4	1.3	.58	15	4.3	19	.19	4.9	0.041	1.0	4.75	SPR	CG	Z
0.625	15.88	W-30	.94	23.8	.551	14.0	1.5	.26	.49	13	.73	3.2	.44	11.3	0.037	0.9	11.0	SPR	C	Z
0.625	15.88	AA-75	.94	23.8	.505	12.8	28	4.8	.45	11	12	55	.35	8.8	0.060	1.5	5.75	SPR	CG	N
0.625	15.88	3129	.97	24.6	.563	14.3	2.1	.37	.78	20	1.7	7.3	.19	4.7	0.031	0.8	5.00	MW	C	Z
0.625	15.88	3031	1.00	25.4	.539	13.7	5.5	.97	.68	17	3.8	17	.32	8.2	0.043	1.1	6.50	SPR	C	Z
0.625	15.88	2799	1.00	25.4	.533	13.5	13	2.3	.46	12	6.1	27	.21	5.3	0.046	1.2	4.50	SPR	CG	GI
0.625	15.88	B11-59	1.00	25.4	.529	13.4	11	2.0	.61	15	6.9	31	.26	6.7	0.048	1.2	5.50	SPR	CG	N
0.625	15.88	11456	1.00	25.4	.521	13.2	14	2.4	.58	15	8.1	36	.36	9.2	0.052	1.3	6.00	SPR	C	Z
0.625	15.88	N-53	1.00	25.4	.517	13.1	13	2.3	.62	16	8.2	36	.38	9.6	0.054	1.4	7.00	SPR	CG	GI
0.625	15.88	S-767	1.00	25.4	.515	13.1	19	3.3	.48	12	9.0	40	.34	8.7	0.055	1.4	5.25	SST	C	N
0.625	15.88	12121	1.00	25.4	.509	12.9	11	2.0	.36	9.2	4.0	18	.64	16.2	0.058	1.5	10.0	SPR	C	Z
0.625	15.88	S-770	1.00	25.4	.499	12.7	32	5.6	.43	11	14	60	.41	10.4	0.063	1.6	5.50	SST	C	N
0.625	15.88	EE-40	1.00	25.4	.485	12.3	50	8.8	.37	9.4	19	83	.42	10.7	0.070	1.8	6.00	SPR	CG	N
0.625	15.88	S-367	1.00	25.4	.481	12.2	50	8.7	.38	9.7	19	84	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.625	15.88	944	1.00	25.4	.465	11.8	121	21	.23	5.8	27	122	.48	12.2	0.080	2.0	5.00	HD	C	Z
0.625	15.88	2745	1.00	25.4	.455	11.6	159	28	.29	7.3	46	204	.43	10.8	0.085	2.2	5.00	MW	CG	Z
0.625	15.88	10354	1.03	26.2	.471	12.0	51	9.0	.42	11	21	94	.62	15.6	0.077	2.0	8.00	SPR	CG	Z
0.625	15.88	BB-88	1.06	27.0	.547	13.9	3.3	.58	.79	20	2.6	12	.27	6.9	0.039	1.0	7.00	SPR	CG	Z
0.625	15.88	B15-24	1.06	27.0	.535	13.6	10	1.8	.56	14	5.7	25	.23	5.7	0.045	1.1	5.00	SPR	CG	N
0.625	15.88	S-1451	1.06	27.0	.509	12.9	14	2.5	.63	16	8.8	39	.44	11.0	0.058	1.5	7.50	SST	CG	N
0.625	15.88	L-64	1.06	27.0	.491	12.5	28	4.9	.53	13	15	65	.54	13.6	0.067	1.7	8.00	SPR	CG	N
0.625	15.88	12289	1.06	27.0	.435	11.0	157	28	.28	7.0	43	193	.67	16.9	0.095	2.4	7.00	SPR	CG	GI
0.625	15.88	3856	1.06	27.0	.371	9.4	757	133	.13	3.2	96	429	.76	19.4	0.127	3.2	6.00	SPR	CG	Z
0.625	15.88	12469	1.09	27.8	.495	12.6	27	4.7	.59	15	16	70	.49	12.4	0.065	1.7	7.50	SPR	CG	Z
0.625	15.88	10747	1.09	27.8	.415	10.5	220	39	.24	6.2	54	239	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.625	15.88	4317	1.13	28.6	.575	14.6	.58	.10	.94	24	.54	2.4	.19	4.8	0.025	0.6	6.50	MW	C	Z
0.625	15.88	S-1588	1.13	28.6	.507	12.9	14	2.5	.65	17	9.3	41	.47	12.0	0.059	1.5	8.00	SST	CG	N
0.625	15.88	S-890	1.13	28.6	.491	12.5	26	4.6	.61	16	16	72	.50	12.8	0.067	1.7	7.50	SST	CG	N
0.625	15.88	S-1423	1.13	28.6	.481	12.2	33	5.8	.55	14	18	81	.58	14.6	0.072	1.8	8.00	SST	CG	N
0.625	15.88	12190	1.13	28.6	.425	10.8	136	24	.28	7.0	37	166	.85	21.6	0.100	2.5	8.50	SPR	CG	Z
0.625	15.88	L-50	1.13	28.6	.415	10.5	355	62	.16	4.2	58	258	.58	14.7	0.105	2.7	5.50	SPR	CG	Z
0.625	15.88	2972	1.16	29.4	.551	14.0	1.4	.24	.73	19	1.0	4.5	.43	10.8	0.037	0.9	11.5	SPR	CG	Z
0.625	15.88	12137	1.16	29.4	.525	13.3	12	2.1	.61	16	7.3	32	.30	7.6	0.050	1.3	6.00	SPR	CG	Z
0.625	15.88	3980	1.16	29.4	.329	8.4	1338	234	.11	2.7	143	637	1.00	25.4	0.148	3.8	6.75	SPR	CG	N
0.625	15.88	S-117	1.19	30.2	.561	14.2	1.3	.22	.93	24	1.2	5.3	.26							




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	3879	1.44	36.5	.551	14.0	1.5	.26	.99	25	1.5	6.5	.44	11.3	0.037	0.9	11.0	SPR	C	Z
0.625	15.88	A10-59	1.44	36.5	.481	12.2	29	5.0	.71	18	20	90	.72	18.3	0.072	1.8	10.0	SPR	CG	Z
0.625	15.88	S-1225	1.44	36.5	.455	11.6	64	11	.48	12	31	137	.72	18.4	0.085	2.2	8.50	SST	CG	N
0.625	15.88	10452	1.47	37.3	.477	12.1	32	5.6	.68	17	22	97	.74	18.8	0.074	1.9	10.0	SPR	CG	N
0.625	15.88	11473	1.50	38.1	.555	14.1	1.4	.25	1.1	29	1.7	7.4	.36	9.1	0.035	0.9	9.25	MW	C	Z
0.625	15.88	523	1.50	38.1	.543	13.8	3.4	.60	1.1	29	3.8	17	.37	9.4	0.041	1.0	8.00	HD	C	Z
0.625	15.88	S-1186	1.50	38.1	.531	13.5	5.3	.92	1.1	27	5.7	25	.42	10.7	0.047	1.2	8.00	SST	C	N
0.625	15.88	4213	1.50	38.1	.529	13.4	6.9	1.2	1.0	25	6.9	31	.42	10.7	0.048	1.2	7.75	SPR	C	Z
0.625	15.88	S-769	1.50	38.1	.515	13.1	12	2.1	.77	20	9.0	40	.45	11.5	0.055	1.4	7.25	SST	C	N
0.625	15.88	S-772	1.50	38.1	.499	12.7	19	3.4	.70	18	14	60	.55	14.0	0.063	1.6	7.75	SST	C	N
0.625	15.88	S-773	1.50	38.1	.481	12.2	32	5.6	.59	15	19	84	.67	16.9	0.072	1.8	8.25	SST	C	N
0.625	15.88	XX-58	1.50	38.1	.481	12.2	28	5.0	.67	17	19	84	.65	16.5	0.072	1.8	9.00	SST	CG	N
0.625	15.88	11304	1.50	38.1	.451	11.5	82	14	.40	10	33	146	.76	19.3	0.087	2.2	7.75	SST	C	N
0.625	15.88	11445	1.50	38.1	.435	11.0	157	28	.39	9.8	61	270	.67	16.9	0.095	2.4	7.00	MW	CG	Z
0.625	15.88	3917	1.63	41.3	.529	13.4	3.6	.63	.95	24	3.4	15	.67	17.1	0.048	1.2	13.0	HD	C	Z
0.625	15.88	3252	1.63	41.3	.465	11.8	40	7.1	.68	17	27	122	.88	22.4	0.080	2.0	11.0	HD	CG	Z
0.625	15.88	11688	1.69	42.8	.531	13.5	3.5	.61	1.1	28	3.8	17	.59	14.9	0.047	1.2	12.5	SPR	CG	Z
0.625	15.88	4128	1.69	42.8	.445	11.3	103	18	.36	9.2	37	165	.81	20.6	0.090	2.3	8.00	SPR	CG	Z
0.625	15.88	3887	1.69	42.8	.355	9.0	541	95	.21	5.2	111	494	1.28	32.6	0.135	3.4	9.50	SPR	CG	Z
0.625	15.88	4125	1.75	44.5	.481	12.2	33	5.7	.62	16	20	90	.72	18.3	0.072	1.8	9.00	SPR	C	Z
0.625	15.88	S-774	1.75	44.5	.481	12.2	26	4.6	.71	18	19	84	.76	19.2	0.072	1.8	9.50	SST	C	N
0.625	15.88	882	1.75	44.5	.443	11.3	72	13	.53	14	38	171	1.09	27.7	0.091	2.3	11.0	HD	C	Z
0.625	15.88	S-3259	1.78	45.2	.565	14.4	1.2	.21	1.4	34	1.7	7.4	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.625	15.88	B18-134	1.78	45.2	.329	8.4	794	139	.15	3.9	122	541	1.63	41.4	0.148	3.8	10.0	SPR	CG	N
0.625	15.88	S-1568	1.81	46.0	.497	12.6	15	2.7	.93	24	14	63	.64	16.3	0.064	1.6	10.0	SST	CG	N
0.625	15.88	11124	1.81	46.0	.443	11.3	66	12	.58	15	38	171	1.16	29.5	0.091	2.3	11.8	HD	C	Z
0.625	15.88	3209	1.84	46.8	.443	11.3	65	11	.59	15	38	171	1.09	27.7	0.091	2.3	12.0	SPR	CG	Z
0.625	15.88	4295	1.88	47.6	.531	13.5	8.1	1.4	.80	20	6.5	29	.31	7.8	0.047	1.2	6.50	SPR	CG	Z
0.625	15.88	B32-32	1.91	48.4	.483	12.3	19	3.3	.95	24	18	81	.85	21.6	0.071	1.8	12.0	SST	CG	N
0.625	15.88	11852	2.00	50.8	.567	14.4	.87	.15	1.8	45	1.6	6.9	.22	5.5	0.029	0.7	7.50	MW	CG	N
0.625	15.88	S-775	2.00	50.8	.481	12.2	23	4.0	.83	21	19	84	.85	21.5	0.072	1.8	10.8	SST	C	N
0.625	15.88	B8-28	2.00	50.8	.475	12.1	29	5.0	.79	20	23	101	.86	21.9	0.075	1.9	11.5	SPR	CG	N
0.625	15.88	12272	2.09	53.2	.501	12.7	13	2.3	1.0	26	14	61	.68	17.3	0.062	1.6	11.0	SPR	CG	Z
0.625	15.88	11767	2.09	53.2	.465	11.8	33	5.8	.83	21	27	122	1.04	26.4	0.080	2.0	13.0	SPR	CG	Z
0.625	15.88	11295	2.19	55.6	.459	11.7	37	6.5	.82	21	31	136	1.12	28.5	0.083	2.1	13.5	SPR	CG	Z
0.625	15.88	B18-153	2.22	56.4	.425	10.8	81	14	.62	16	50	224	1.43	36.2	0.100	2.5	14.3	SPR	CG	Z
0.625	15.88	S-1470	2.25	57.2	.559	14.2	1.4	.25	1.5	39	2.2	9.8	.23	5.9	0.033	0.8	7.00	SST	CG	N
0.625	15.88	4260	2.25	57.2	.501	12.7	13	2.3	1.0	26	14	61	.74	18.9	0.062	1.6	11.0	SPR	C	Z
0.625	15.88	916	2.25	57.2	.481	12.2	20	3.5	1.0	26	20	90	1.04	26.5	0.072	1.8	13.5	HD	C	Z
0.625	15.88	2672	2.25	57.2	.415	10.5	113	20	.51	13	58	258	1.37	34.7	0.105	2.7	13.0	SPR	CG	Z
0.625	15.88	11438	2.25	57.2	.401	10.2	134	23	.50	13	68	300	1.62	41.2	0.112	2.8	14.5	SPR	CG	Z
0.625	15.88	S-809	2.31	58.7	.355	9.0	483	85	.21	5.3	100	445	1.37	34.8	0.135	3.4	10.0	SST	CG	N
0.625	15.88	47	2.																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	1899	4.81	122.2	.449	11.4	24	4.3	2.1	53	51	225	2.18	55.3	0.088	2.2	24.8	MW	CG	Z
0.625	15.88	12419	4.84	123.0	.443	11.3	27	4.7	1.4	36	38	171	2.37	60.1	0.091	2.3	26.0	SPR	CG	N
0.625	15.88	12441	4.94	125.4	.441	11.2	27	4.7	1.5	38	40	176	2.62	66.6	0.092	2.3	27.5	SPR	C	N
0.625	15.88	874	5.00	127.0	.443	11.3	24	4.2	1.6	41	38	171	2.64	67.0	0.091	2.3	29.0	HD	CG	Z
0.625	15.88	3803	5.00	127.0	.441	11.2	25	4.4	1.6	40	40	176	2.76	70.1	0.092	2.3	29.0	SPR	CG	Z
0.625	15.88	870	5.00	127.0	.415	10.5	41	7.1	1.4	36	58	258	3.43	87.1	0.105	2.7	32.7	HD	CG	Z
0.625	15.88	1657	6.00	152.4	.517	13.1	2.8	.49	3.2	82	9.1	41	1.42	36.0	0.054	1.4	25.3	SPR	C	Z
0.625	15.88	3334	6.00	152.4	.481	12.2	5.8	1.0	3.0	77	17	77	2.99	75.9	0.072	1.8	41.5	HD	CG	GI
0.625	15.88	1944	7.00	177.8	.455	11.6	15	2.6	2.2	56	33	146	2.98	75.6	0.085	2.2	34.0	SPR	C	Z
0.625	15.88	888	9.00	228.6	.465	11.8	8.4	1.5	3.3	83	27	122	3.72	94.5	0.080	2.0	45.5	HD	C	Z
0.625	15.88	10542	9.50	241.3	.477	12.1	6.1	1.1	3.6	91	22	97	3.33	84.6	0.074	1.9	44.0	SPR	C	Z
0.625	15.88	10150	9.75	247.7	.443	11.3	15	2.5	2.6	67	38	171	4.32	109.8	0.091	2.3	46.5	SPR	C	Z
0.625	15.88	4143	11.9	301.6	.481	12.2	4.0	.70	5.0	128	20	90	4.32	109.7	0.072	1.8	59.0	HD	C	Z
0.625	15.88	881	12.0	304.8	.501	12.7	2.1	.36	6.7	169	14	61	3.78	96.1	0.062	1.6	60.0	HD	C	Z
0.625	15.88	878	12.0	304.8	.481	12.2	3.5	.62	5.7	145	20	90	4.86	123.4	0.072	1.8	66.0	HD	C	Z
0.625	15.88	876	12.0	304.8	.465	11.8	6.2	1.1	4.4	112	27	122	4.92	125.0	0.080	2.0	60.0	HD	C	Z
0.625	15.88	S-3045	15.0	381.0	.491	12.5	1.9	.34	8.4	214	16	72	5.19	131.9	0.067	1.7	77.0	SST	CG	N
0.640	16.26	S-105	.34	8.7	.582	14.8	3.1	.54	.22	5.6	.68	3.0	.12	3.1	0.029	0.7	3.25	SST	C	N
0.640	16.26	B10-13	.38	9.5	.508	12.9	57	10	.09	2.4	5.4	24	.28	7.1	0.066	1.7	4.25	SST	CG	N
0.640	16.26	O-70	.41	10.3	.516	13.1	110	19	.12	3.1	13	60	.19	4.7	0.062	1.6	3.00	SPR	CG	Z
0.640	16.26	S-1187	.41	10.3	.506	12.9	134	23	.12	3.0	16	70	.20	5.1	0.067	1.7	3.00	SST	CG	N
0.640	16.26	3181	.44	11.1	.512	13.0	126	22	.12	3.0	15	65	.19	4.9	0.064	1.6	3.00	SPR	CG	GI
0.640	16.26	10124	.50	12.7	.516	13.1	55	9.6	.19	4.8	10	46	.31	7.9	0.062	1.6	4.00	HD	C	Z
0.640	16.26	B15-27	.50	12.7	.500	12.7	110	19	.15	3.9	17	76	.25	6.2	0.070	1.8	3.50	SST	CG	N
0.640	16.26	3248	.63	15.9	.564	14.3	9.2	1.6	.37	9.3	3.4	15	.17	4.3	0.038	1.0	3.50	SPR	C	Z
0.640	16.26	S-1106	.63	15.9	.560	14.2	3.7	.65	.35	8.8	1.3	5.7	.28	7.1	0.040	1.0	6.00	SST	C	N
0.640	16.26	Q0-61	.69	17.4	.522	13.3	44	7.8	.26	6.6	12	51	.30	7.5	0.059	1.5	4.00	SPR	C	GI
0.640	16.26	3221	.69	17.4	.518	13.2	51	9.0	.25	6.3	13	57	.24	6.2	0.061	1.5	4.00	SPR	CG	GI
0.640	16.26	10595	.69	17.4	.430	10.9	368	64	.14	3.6	53	234	.50	12.7	0.105	2.7	4.75	SST	CG	N
0.640	16.26	S-889	.75	19.1	.542	13.8	9.2	1.6	.46	12	4.2	19	.29	7.3	0.049	1.2	6.00	SST	CG	N
0.640	16.26	KK-30	.75	19.1	.540	13.7	22	3.8	.32	8.2	7.1	32	.20	5.1	0.050	1.3	4.00	SPR	CG	Z
0.640	16.26	S-1428	.75	19.1	.430	10.9	397	70	.13	3.4	53	234	.47	12.0	0.105	2.7	4.50	SST	CG	N
0.640	16.26	BB-96	.84	21.4	.490	12.4	37	6.4	.24	6.2	8.9	40	.60	15.2	0.075	1.9	8.00	SST	CG	N
0.640	16.26	10134	.88	22.2	.512	13.0	42	7.4	.35	8.9	15	65	.32	8.1	0.064	1.6	5.00	SPR	CG	Z
0.640	16.26	10789	.88	22.2	.470	11.9	111	19	.27	6.9	30	134	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.640	16.26	GG-94	.94	23.8	.532	13.5	13	2.3	.61	16	8.1	36	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.640	16.26	MM-52	.94	23.8	.520	13.2	32	5.6	.38	9.7	12	54	.30	7.6	0.060	1.5	5.00	SPR	CG	Z
0.640	16.26	S-3197	.94	23.8	.468	11.9	117	21	.27	6.7	31	138	.47	12.0	0.086	2.2	5.50	SST	CG	N
0.640	16.26	10787	.97	24.6	.470	11.9	110	19	.29	7.4	32	143	.51	13.0	0.085	2.2	6.00	SPR	CG	N
0.640	16.26	UU-53	1.00	25.4	.550	14.0	7.0	1.2	.69	17	4.8	21	.32	8.0	0.045	1.1	6.00	SPR	C	Z
0.640	16.26	3144	1.00	25																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com


O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.640	16.26	10335	2.00	50.8	.546	13.9	3.2	.56	1.4	36	4.5	20	.59	14.9	0.047	1.2	12.5	SPR	CG	Z
0.640	16.26	11750	2.00	50.8	.516	13.1	12	2.1	1.1	28	13	60	.68	17.3	0.062	1.6	11.0	SPR	CG	Z
0.640	16.26	12580	2.00	50.8	.480	12.2	36	6.3	.74	19	27	120	.98	24.9	0.080	2.0	11.3	SPR	CG	N
0.640	16.26	4316	2.13	54.0	.530	13.5	8.2	1.4	1.1	29	9.4	42	.55	14.0	0.055	1.4	10.0	SPR	CG	Z
0.640	16.26	S-321	2.19	55.6	.316	8.0	956	167	.16	4.1	156	693	1.66	42.2	0.162	4.1	10.3	SST	CG	N
0.640	16.26	3808	2.25	57.2	.430	10.9	104	18	.55	14	57	253	1.61	40.8	0.105	2.7	14.0	SPR	CG	Z
0.640	16.26	LL-96	2.38	60.3	.480	12.2	30	5.2	.85	22	25	112	.96	24.4	0.080	2.0	12.0	SST	CG	N
0.640	16.26	2926	2.47	62.7	.532	13.5	6.1	1.1	1.5	37	8.9	40	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.640	16.26	RR-11	2.50	63.5	.568	14.4	1.3	.23	2.1	53	2.7	12	.41	10.5	0.036	0.9	10.5	SPR	CG	Z
0.640	16.26	10522	2.63	66.7	.516	13.1	10	1.8	1.3	34	13	60	.81	20.5	0.062	1.6	13.0	SPR	CG	Z
0.640	16.26	11374	2.63	66.7	.496	12.6	20	3.5	.91	23	18	82	.81	20.6	0.072	1.8	11.3	SST	CG	N
0.640	16.26	11596	2.69	68.2	.370	9.4	278	49	.39	10	109	485	2.20	56.0	0.135	3.4	15.3	SPR	CG	Z
0.640	16.26	2624	2.91	73.8	.430	10.9	71	12	.80	20	57	253	2.00	50.7	0.105	2.7	18.0	HD	C	Z
0.640	16.26	S-805	2.94	74.6	.558	14.2	1.6	.27	2.4	61	3.7	17	.55	14.1	0.041	1.0	12.5	SST	C	N
0.640	16.26	12455	3.00	76.2	.480	12.2	24	4.2	1.1	29	27	120	1.36	34.5	0.080	2.0	16.0	SPR	C	Z
0.640	16.26	S-3037	3.25	82.6	.430	10.9	58	10	.90	23	53	234	2.10	53.3	0.105	2.7	19.0	SST	C	N
0.640	16.26	10414	3.31	84.1	.430	10.9	67	12	.85	22	57	253	2.00	50.7	0.105	2.7	19.0	SPR	CG	Z
0.640	16.26	11800	3.50	88.9	.526	13.4	7.7	1.3	1.4	35	10	46	.74	18.8	0.057	1.4	12.0	SPR	CG	Z
0.640	16.26	10771	4.00	101.6	.478	12.1	18	3.1	1.6	40	28	124	1.78	45.3	0.081	2.1	22.0	SPR	CG	GI
0.640	16.26	3437	4.50	114.3	.530	13.5	3.9	.68	2.4	62	9.4	42	1.10	27.9	0.055	1.4	19.0	SPR	C	Z
0.640	16.26	3154	4.50	114.3	.480	12.2	19	3.3	1.4	36	27	120	1.57	40.0	0.080	2.0	19.8	SPR	CG	Z
0.640	16.26	1593	4.88	123.8	.400	10.2	92	16	.87	22	81	358	3.00	76.2	0.120	3.0	25.0	SPR	CG	Z
0.640	16.26	3332	6.00	152.4	.496	12.6	5.2	.91	2.9	73	15	66	3.13	79.6	0.072	1.8	42.5	HD	C	Z
0.640	16.26	1531	8.00	203.2	.500	12.7	5.6	.98	3.2	82	18	81	2.54	64.5	0.070	1.8	35.3	SPR	C	Z
0.640	16.26	11691	9.75	247.7	.458	11.6	13	2.3	2.8	71	38	167	4.23	107.5	0.091	2.3	46.5	SPR	CG	GI
0.640	16.26	10152	11.0	279.4	.570	14.5	.28	.05	9.5	241	2.6	12	1.33	33.8	0.035	0.9	37.0	SPR	C	Z
0.653	16.59	12682	.69	17.4	.527	13.4	32	5.6	.31	7.8	9.9	44	.38	9.6	0.063	1.6	5.00	SST	C	N
0.656	16.66	10241	.34	8.7	.496	12.6	411	72	.06	1.6	26	117	.22	5.6	0.080	2.0	2.75	SPR	CG	Z
0.656	16.66	B4-70	.38	9.5	.600	15.2	3.1	.54	.26	6.7	.82	3.6	.11	2.8	0.028	0.7	3.00	SST	C	N
0.656	16.66	3645	.38	9.5	.574	14.6	17	3.1	.21	5.4	3.7	16	.16	4.2	0.041	1.0	3.00	HD	C	Z
0.656	16.66	11-97	.44	11.1	.574	14.6	15	2.7	.25	6.4	3.9	17	.16	4.2	0.041	1.0	3.00	SST	C	N
0.656	16.66	1763	.47	11.9	.562	14.3	18	3.1	.25	6.2	4.3	19	.22	5.7	0.047	1.2	3.75	HD	C	Z
0.656	16.66	S-883	.53	13.5	.546	13.9	28	4.9	.31	7.8	8.6	38	.21	5.4	0.055	1.4	4.00	SST	CG	N
0.656	16.66	12266	.56	14.3	.556	14.1	17	3.0	.35	8.8	6.0	27	.22	5.5	0.050	1.3	4.25	SPR	CG	Z
0.656	16.66	A-48	.66	16.7	.296	7.5	13992	2450	.02	.40	218	968	.54	13.7	0.180	4.6	3.00	HD	CG	Z
0.656	16.66	O0-48	.69	17.4	.576	14.6	5.2	.92	.45	11	2.3	10	.24	6.1	0.040	1.0	5.00	SPR	C	GI
0.656	16.66	A11-28	.69	17.4	.560	14.2	15	2.6	.41	10	6.2	27	.19	4.9	0.048	1.2	4.00	SST	CG	N
0.656	16.66	S-1264	.69	17.4	.474	12.0	136	24	.19	4.7	25	113	.50	12.7	0.091	2.3	5.50	SST	CG	N
0.656	16.66	S-1210	.75	19.1	.574	14.6	7.6	1.3	.51	13	3.9									



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.850	21.59	72253S	2.00	50.8	.680	17.3	22	3.9	1.0	26	23	103	.71	18.1	0.085	2.2	8.38	SST	CG	N
0.850	21.59	72269	2.00	50.8	.668	17.0	35	6.1	1.2	29	40	180	.77	19.6	0.091	2.3	8.50	MW	CG	N
0.850	21.59	72269S	2.00	50.8	.668	17.0	30	5.2	.90	23	27	119	.77	19.6	0.091	2.3	8.50	SST	CG	N
0.850	21.59	72281	2.00	50.8	.666	16.9	35	6.0	1.2	30	41	182	.82	20.7	0.092	2.3	8.88	MW	CG	N
0.850	21.59	72281S	2.00	50.8	.666	16.9	29	5.1	.94	24	28	123	.82	20.7	0.092	2.3	8.88	SST	CG	N
0.850	21.59	72291	2.00	50.8	.654	16.6	45	7.9	1.1	28	50	224	.87	22.1	0.098	2.5	8.88	MW	CG	N
0.850	21.59	72291S	2.00	50.8	.654	16.6	38	6.7	.87	22	33	148	.87	22.1	0.098	2.5	8.88	SST	CG	N
0.850	21.59	72301	2.00	50.8	.650	16.5	55	9.7	.96	24	53	237	.81	20.6	0.100	2.5	8.13	MW	CG	N
0.850	21.59	72301S	2.00	50.8	.650	16.5	47	8.2	.75	19	35	157	.81	20.6	0.100	2.5	8.13	SST	CG	N
0.850	21.59	72316	2.00	50.8	.640	16.3	60	10	1.0	26	62	274	.96	24.3	0.105	2.7	9.13	MW	CG	N
0.850	21.59	72316S	2.00	50.8	.640	16.3	51	8.9	.80	20	41	181	.96	24.3	0.105	2.7	9.13	SST	CG	N
0.850	21.59	72155	2.25	57.2	.740	18.8	5.4	.95	1.8	47	9.9	44	.38	9.6	0.055	1.4	6.88	MW	CG	N
0.850	21.59	72155S	2.25	57.2	.740	18.8	4.6	.80	1.5	37	6.7	30	.38	9.6	0.055	1.4	6.88	SST	CG	N
0.850	21.59	72179	2.25	57.2	.714	18.1	10	1.8	1.7	43	18	79	.55	14.0	0.068	1.7	8.13	MW	CG	N
0.850	21.59	72179S	2.25	57.2	.714	18.1	8.8	1.5	1.4	36	13	56	.55	14.0	0.068	1.7	8.13	SST	CG	N
0.850	21.59	72203	2.25	57.2	.702	17.8	14	2.5	1.6	40	23	102	.62	15.7	0.074	1.9	8.38	MW	CG	N
0.850	21.59	72203S	2.25	57.2	.702	17.8	12	2.1	1.3	32	15	68	.62	15.7	0.074	1.9	8.38	SST	CG	N
0.850	21.59	72224	2.25	57.2	.690	17.5	19	3.3	1.5	39	29	128	.71	18.0	0.080	2.0	8.88	MW	CG	N
0.850	21.59	72224S	2.25	57.2	.690	17.5	16	2.8	1.2	31	19	86	.71	18.0	0.080	2.0	8.88	SST	CG	N
0.850	21.59	72241	2.25	57.2	.688	17.5	19	3.4	1.5	39	29	131	.73	18.5	0.081	2.1	9.00	MW	CG	N
0.850	21.59	72241S	2.25	57.2	.688	17.5	16	2.9	1.2	31	20	89	.73	18.5	0.081	2.1	9.00	SST	CG	N
0.850	21.59	72254	2.25	57.2	.680	17.3	23	4.1	1.5	37	34	153	.78	19.7	0.085	2.2	9.13	MW	CG	N
0.850	21.59	72254S	2.25	57.2	.680	17.3	20	3.5	1.2	30	23	103	.78	19.7	0.085	2.2	9.13	SST	CG	N
0.850	21.59	72270	2.25	57.2	.668	17.0	31	5.4	1.3	33	40	180	.84	21.4	0.091	2.3	9.25	MW	CG	N
0.850	21.59	72270S	2.25	57.2	.668	17.0	26	4.6	1.0	26	27	119	.84	21.4	0.091	2.3	9.25	SST	CG	N
0.850	21.59	72282	2.25	57.2	.666	16.9	30	5.3	1.4	34	41	183	.90	22.8	0.092	2.3	9.75	MW	CG	N
0.850	21.59	72282S	2.25	57.2	.666	16.9	26	4.5	1.1	27	28	123	.90	22.8	0.092	2.3	9.75	SST	CG	N
0.850	21.59	72292	2.25	57.2	.654	16.6	39	6.9	1.3	32	50	224	.97	24.6	0.098	2.5	9.88	MW	CG	N
0.850	21.59	72292S	2.25	57.2	.654	16.6	33	5.8	1.0	25	33	148	.97	24.6	0.098	2.5	9.88	SST	CG	N
0.850	21.59	72302	2.25	57.2	.650	16.5	49	8.5	1.1	28	53	237	.90	22.9	0.100	2.5	9.00	MW	CG	N
0.850	21.59	72302S	2.25	57.2	.650	16.5	41	7.2	.85	22	35	157	.90	22.9	0.100	2.5	9.00	SST	CG	N
0.850	21.59	72318	2.25	57.2	.640	16.3	52	9.2	1.2	30	62	274	1.06	27.0	0.105	2.7	10.1	MW	CG	N
0.850	21.59	72318S	2.25	57.2	.640	16.3	44	7.8	.92	23	41	181	1.06	27.0	0.105	2.7	10.1	SST	CG	N
0.850	21.59	72142	2.50	63.5	.750	19.1	3.5	.61	2.1	54	7.5	33	.35	8.9	0.050	1.3	7.00	MW	CG	N
0.850	21.59	72142S	2.50	63.5	.750	19.1	3.0	.52	1.7	43	5.1	23	.35	8.9	0.050	1.3	7.00	SST	CG	N
0.850	21.59	72156	2.50	63.5	.740	18.8	4.8	.85	2.1	52	9.9	44	.41	10.3	0.055	1.4	7.38	MW	CG	N
0.850	21.59	72156S	2.50	63.5	.740	18.8	4.1	.72	1.6	42	6.7	30	.41	10.3	0.055	1.4	7.38	SST	CG	N
0.850	21.59	72168	2.50	63.5	.716	18.2	8.9	1.6	1.9	49	17	76	.59	14.9	0.067	1.7	8.75	MW	CG	N
0.850	21.59	72168S	2.50	63.5	.716	18.2	7.6	1.3	1.6	41	12	54	.59	14.9	0.067	1.7	8.75	SST	CG	N
0.850	21.59	72180	2.50	63.5	.714	18.1	9.3	1.6	1.9	48	18	78	.60	15.3	0.068	1.7	8.88	MW	CG	N
0.850	21.59	72180S	2.50	63.5	.714	18.1	7.9	1.4	1.6	41	13	56	.60	15.3	0.068	1.7	8.88	SST	CG	N
0.850	21.59	72192	2.50	63.5	.706	17.9	12	2.2	1.7	43	21	94	.62	15.8	0.072	1.8	8.63	MW	CG	N
0.850	21.59	72192S	2.50	63.5	.706	17.9	11	1.9	1.3	34	14	63	.62	15.8	0.072	1.8	8.63	SST	CG	N
0.850	21.59	72204	2.50	63.5	.702	17.8	12	2.2	1.8	46	22	99	.70	17.9	0.074	1.9	9.50	MW	CG	N
0.850	21.59	72204S	2.50	63.5	.702	17.8	11	1.8	1.5	37	15	68	.70	17.9	0.074	1.9	9.50	SST	CG	N
0.850	21.59	72226	2.50	63.5	.690	17.5	17	2.9	1.7	44	29	128	.77	19.6	0.080	2.0	9.63	MW	CG	N
0.850	21.59	72226S	2.50	63.5	.690	17.5	14	2.5	1.4	34	19	86	.77	19.6	0.080	2.0	9.63	SST	CG	N
0.850	21.59	72242	2.50	63.5	.688	17.5	17	3.0	1.7	43	29	130	.80	20.3	0.081	2.1	9.88	MW	CG	N
0.850	21.59	72242S	2.50	63.5	.688	17.5	15	2.6	1.4	35	20	89	.80	20.3	0.081	2.1	9.88	SST	CG	N
0.850	21.59	72255	2.50	63.5	.680	17.3	21	3.7	1.7	42	34	153	.85	21.6	0.085	2.2	10.0	MW	CG	N
0.850	21.59	72255S	2.50	63.5	.680	17.3	18	3.1	1.3	33	23	103	.85	21.6	0.085	2.2	10.0	SST	CG	N
0.850	21.59	72271	2.50	63.5	.668	17.0	28	4.9	1.4	37	40	180	.91	23.1	0.091	2.3	10.0	MW	CG	N
0.850	21.59	72271S	2.50	63.5	.668	17.0	24	4.2	1.1	29	27	119	.91	23.1	0.091	2.3	10.0	SST	CG	N
0.850	21.59	72283	2.50	63.5	.666	16.9	27	4.7	1.5	38	41	182	.99	25.1	0.092	2.3	10.8	MW	CG	N
0.850	21.59	72283S	2.50	63.5	.666	16.9	23	4.0	1.2	31	28	123	.99	25.1	0.092	2.3	10.8	SST	CG	N
0.850	21.59	72293	2.50	63.5	.654	16.6	35	6.2	1.4	36	50	224	1.07	27.1	0.098	2.5	10.9	MW	CG	N
0.850	21.59	72293S	2.50	63.5	.654	16.6	30													




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.859	21.82	11710	.66	16.7	.743	18.9	21	3.7	.39	10	8.3	37	.20	5.2	0.058	1.5	3.50	SPR	CG	Z
0.859	21.82	11678	.72	18.2	.677	17.2	174	30	.16	4.2	29	127	.30	7.5	0.091	2.3	3.25	SPR	CG	Z
0.859	21.82	A13-35	.75	19.1	.793	20.1	1.3	.23	.59	15	.78	3.5	.17	4.2	0.033	0.8	4.00	SST	C	N
0.859	21.82	S-345	.75	19.1	.699	17.8	28	4.8	.27	6.9	7.5	33	.48	12.2	0.080	2.0	6.00	SST	CG	N
0.859	21.82	10793	.81	20.6	.639	16.2	162	28	.27	6.9	44	196	.52	13.3	0.110	2.8	4.75	SST	CG	N
0.859	21.82	S-3091	.88	22.2	.757	19.2	5.3	.94	.57	14	3.0	14	.31	7.8	0.051	1.3	5.00	SST	C	N
0.859	21.82	12284	.88	22.2	.695	17.7	69	12	.32	8.0	22	98	.33	8.3	0.082	2.1	4.00	SPR	CG	Z
0.859	21.82	KK-85	.88	22.2	.639	16.2	250	44	.19	4.9	48	215	.44	11.2	0.110	2.8	4.00	SPR	CG	N
0.859	21.82	12486	.91	23.0	.699	17.8	62	11	.33	8.3	20	91	.40	10.2	0.080	2.0	4.00	SPR	C	N
0.859	21.82	2951	.91	23.0	.669	17.0	131	23	.25	6.3	32	144	.38	9.7	0.095	2.4	4.00	SPR	CG	Z
0.859	21.82	B12-46	1.00	25.4	.765	19.4	4.0	.71	.71	18	2.8	13	.29	7.5	0.047	1.2	5.25	SPR	C	N
0.859	21.82	PP-92	1.00	25.4	.725	18.4	25	4.4	.47	12	12	53	.27	6.8	0.067	1.7	4.00	SST	CG	N
0.859	21.82	N-55	1.03	26.2	.739	18.8	9.1	1.6	.67	17	6.1	27	.36	9.1	0.060	1.5	6.00	SPR	CG	Z
0.859	21.82	K-50	1.13	28.6	.735	18.7	21	3.7	.48	12	10	45	.25	6.3	0.062	1.6	4.00	SPR	CG	N
0.859	21.82	S-185	1.25	31.8	.769	19.5	1.2	.21	.76	19	.90	4.0	.50	12.6	0.045	1.1	10.0	SST	C	N
0.859	21.82	B11-69	1.25	31.8	.753	19.1	8.7	1.5	.73	19	6.3	28	.24	6.1	0.053	1.3	4.50	SPR	CG	Z
0.859	21.82	A15-52	1.25	31.8	.737	18.7	14	2.5	.63	16	9.1	40	.30	7.6	0.061	1.5	4.75	SST	CG	N
0.859	21.82	11512	1.25	31.8	.731	18.6	19	3.4	.58	15	11	49	.35	8.9	0.064	1.6	4.50	SPR	CG	Z
0.859	21.82	10148	1.25	31.8	.723	18.4	23	4.0	.59	15	13	59	.32	8.2	0.068	1.7	4.75	SPR	CG	Z
0.859	21.82	12138	1.25	31.8	.699	17.8	25	4.4	.69	18	17	76	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
0.859	21.82	12225	1.28	32.5	.751	19.1	12	2.1	.57	15	6.7	30	.27	6.9	0.054	1.4	4.00	SPR	C	Z
0.859	21.82	12488	1.28	32.5	.699	17.8	42	7.3	.49	12	20	91	.48	12.2	0.080	2.0	5.00	SPR	C	N
0.859	21.82	2773	1.41	35.7	.645	16.4	111	19	.58	15	64	286	.64	16.3	0.107	2.7	6.00	MW	CG	Z
0.859	21.82	S-1307	1.44	36.5	.725	18.4	14	2.5	.83	21	12	53	.37	9.4	0.067	1.7	5.50	SST	CG	N
0.859	21.82	3864	1.44	36.5	.723	18.4	21	3.6	.64	16	13	59	.41	10.4	0.068	1.7	5.00	SPR	C	Z
0.859	21.82	B7-65	1.50	38.1	.735	18.7	14	2.4	.72	18	10	45	.31	7.9	0.062	1.6	5.00	SPR	CG	N
0.859	21.82	11776	1.50	38.1	.723	18.4	18	3.1	.75	19	13	59	.44	11.2	0.068	1.7	5.50	SPR	C	Z
0.859	21.82	10023	1.50	38.1	.719	18.3	22	3.8	.64	16	14	61	.37	9.3	0.070	1.8	5.25	SPR	CG	Z
0.859	21.82	00-53	1.50	38.1	.639	16.2	137	24	.32	8.2	44	196	.58	14.7	0.110	2.8	5.25	SST	CG	N
0.859	21.82	B15-1	1.53	38.9	.779	19.8	1.1	.19	1.2	30	1.3	5.7	.34	8.6	0.040	1.0	7.50	SST	C	N
0.859	21.82	MM-88	1.59	40.5	.519	13.2	667	117	.24	6.1	160	713	1.28	32.4	0.170	4.3	7.50	SPR	CG	Z
0.859	21.82	S-73	1.63	41.3	.751	19.1	3.3	.57	1.2	30	3.8	17	.45	11.3	0.054	1.4	8.25	SST	CG	N
0.859	21.82	TT-69	1.63	41.3	.649	16.5	79	14	.51	13	40	180	.68	17.3	0.105	2.7	6.50	SST	CG	N
0.859	21.82	11435	1.63	41.3	.609	15.5	127	22	.50	13	63	282	1.13	28.6	0.125	3.2	9.00	SPR	CG	Z
0.859	21.82	10646	1.63	41.3	.567	14.4	360	63	.30	7.5	107	474	1.02	26.0	0.146	3.7	7.00	SPR	CG	Z
0.859	21.82	S-1175	1.75	44.5	.505	12.8	774	135	.21	5.2	159	709	1.24	31.5	0.177	4.5	7.00	SST	CG	N
0.859	21.82	3321	1.88	47.6	.575	14.6	248	43	.40	10	98	438	1.12	28.4	0.142	3.6	8.00	SPR	CG	Z
0.859	21.82	B8-33	1.94	49.2	.651	16.5	78	14	.54	14	42	188	.73	18.5	0.104	2.6	7.00	SPR	CG	N
0.859	21.82	B17-195	1.97	50.0	.499	12.7	599	105	.26	6.6	155	689	1.62	41.1	0.180	4.6	9.00	SST	CG	N
0.859	21.82	2776	2.00	50.8	.673	17.1	55	9.6	.56	14	31	136	.69	17.4	0.093	2.4	6.33	SPR	C	Z
0.859	21.82	10502	2.00	50.8	.663	16.8	43	7.5	.83	21	36	158	.88	22.4	0.098	2.5	9.00	SPR	CG	Z
0.859	21.82	12465	2.00	50.8	.619	15.7	123	22	.51	13	62	277	.96	24.4	0.120	3.0	8.00	SPR	CG	Z
0.859	21.82	S-459	2.06	52.4	.675	17.1	25	4.3	1.1	28	27	122	.92	23.4	0.092	2.3	10.0	SST	CG	N
0.859	21.82	KK-81	2.25	57.2	.539	13.7	460	81	.29	7.5	135	601	1.28	32.5	0.160	4.1	8.00	SPR	CG	Z
0.859	21.82	A13-39	2.34	59.5	.697	17.7	15	2.6	1.4	35	20	88	.81	20.6	0.081	2.1	10.0	SST	CG	N
0.859	21.82	10370	2.38	60.3	.709	18.0	11	1.9	1.5	38	16	72	.88	22.4	0.075	1.9	10.8	SPR	C	Z
0.859	21.82	S-465	2.44	61.9	.649	16.5	48	8.5	.84	21	40	180	.98	24.9	0.105	2.7	9.33	SST	CG	N
0.859	21.82	10829	2.50	63.5	.699	17.8	17	3.0	1.2	31	20	91	.75	19.0	0.080	2.0	9.33	SPR	CG	Z
0.859	21.82	11430	2.50	63.5	.659	16.7	36	6.4	.96	24	35	156	1.00	25.4	0.100	2.5	10.0	SST	CG	N
0.859	21.82	11174	2.53	64.3	.641	16.3	53	9.3	.84	21	45	200	1.09	27.7	0.109	2.8	10.0	SST	CG	N
0.859	21.82	S-381	2.63	66.7	.765	19.4	1.8	.31	2.2	57	3.9	17	.40	10.1	0.047	1.2	8.50	SST	CG	N
0.859	21.82	11510	2.63	66.7	.563	14.3	202	35	.55	14	111	493	1.85	47.0	0.148	3.8	11.5	SPR	CG	Z
0.859	21.82	11953	2.69	68.2	.687	17.4	24	4.3	1.0	26	25	112	.77	19.7	0.086	2.2	9.00	SPR	CG	Z
0.859	21.82	2908	2.75	69.9	.669	17.0	26	4.6	1.2	31	32	144	1.14	29.0	0.095	2.4	12.0	SPR	CG	Z
0.859	21.82	4305	2.75	69.9	.609	15.5	83	14	.85	22	70	312	1.59	40.5	0.125	3.2	12.8	SPR	CG	Z
0.859	21.82	11591	2.78	70.6	.643	16.3	58	10	.82	21	47	210	1.19	30.2	0.108	2.7	10.0	SPR	CG	GI
0.859	21.82	10935	2.84	72.2	.777	19.7	.93	.16	2.4	61	2.2	9.9	.45	11.5	0.0					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.875	22.23	10469	.66	16.7	.751	19.1	40	6.9	.25	6.4	9.9	44	.25	6.3	0.062	1.6	3.00	SPR	C	Z
0.875	22.23	3702	.66	16.7	.635	16.1	346	61	.18	4.5	61	271	.48	12.2	0.120	3.0	4.00	SPR	CG	Z
0.875	22.23	10942	.69	17.4	.605	15.4	1178	206	.07	1.8	84	372	.41	10.3	0.135	3.4	3.00	SPR	CG	Z
0.875	22.23	11386	.75	19.1	.785	19.9	4.6	.80	.57	14	2.6	12	.18	4.6	0.045	1.1	4.00	SST	CG	N
0.875	22.23	S-3177	.75	19.1	.767	19.5	15	2.7	.40	10	6.2	28	.18	4.5	0.054	1.4	3.25	SST	CG	N
0.875	22.23	1733	.75	19.1	.751	19.1	14	2.5	.39	10	5.6	25	.36	9.1	0.062	1.6	4.75	HD	C	Z
0.875	22.23	S-1438	.81	20.6	.825	21.0	.27	.05	.66	17	.18	.78	.15	3.8	0.025	0.6	5.00	SST	C	N
0.875	22.23	LL-3	.88	22.2	.775	19.7	2.8	.50	.53	13	1.5	6.6	.35	8.9	0.050	1.3	7.00	SST	CG	N
0.875	22.23	S-1698	.88	22.2	.705	17.9	88	15	.25	6.5	22	100	.30	7.6	0.085	2.2	3.50	SST	CG	N
0.875	22.23	26	.88	22.2	.693	17.6	88	15	.32	8.2	28	125	.49	12.3	0.091	2.3	4.33	HD	C	Z
0.875	22.23	S-886	.94	23.8	.793	20.1	4.1	.71	.72	18	2.9	13	.18	4.7	0.041	1.0	3.50	SST	C	N
0.875	22.23	10315	.94	23.8	.751	19.1	26	4.6	.38	9.6	9.9	44	.28	7.1	0.062	1.6	3.50	SPR	C	Z
0.875	22.23	4184	1.00	25.4	.675	17.1	77	14	.40	10	31	137	.60	15.2	0.100	2.5	6.00	SPR	CG	Z
0.875	22.23	12133	1.03	26.2	.757	19.2	16	2.8	.53	14	8.6	38	.24	6.0	0.059	1.5	4.00	SPR	CG	Z
0.875	22.23	3686	1.06	27.0	.715	18.2	59	10	.34	8.7	20	89	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
0.875	22.23	S-1437	1.09	27.8	.665	16.9	111	19	.36	9.1	40	177	.53	13.3	0.105	2.7	5.00	SST	CG	N
0.875	22.23	GG-53	1.13	28.6	.655	16.6	157	27	.30	7.7	47	211	.55	14.0	0.110	2.8	5.00	SPR	CG	Z
0.875	22.23	11118	1.16	29.4	.799	20.3	1.4	.24	.90	23	1.2	5.5	.26	6.5	0.038	1.0	5.75	MW	C	N
0.875	22.23	H-37	1.25	31.8	.785	19.9	1.2	.22	.74	19	.92	4.1	.51	13.0	0.045	1.1	10.3	MW	C	N
0.875	22.23	S-127	1.28	32.5	.775	19.7	2.5	.44	.90	22.8	2.28	10.1	.38	9.5	0.050	1.3	7.50	SST	CG	N
0.875	22.23	10307	1.31	33.3	.715	18.2	23	4.1	.75	19	18	78	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
0.875	22.23	S-1446	1.38	34.9	.751	19.1	8.6	1.5	1.0	25	8.6	38	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.875	22.23	11263	1.38	34.9	.693	17.6	32	5.5	.67	17	21	94	.71	17.9	0.091	2.3	7.75	SST	CG	N
0.875	22.23	914	1.38	34.9	.665	16.9	96	17	.45	11	43	190	.74	18.7	0.105	2.7	6.00	HD	C	Z
0.875	22.23	3167	1.44	36.5	.615	15.6	221	39	.34	8.6	75	334	.85	21.5	0.130	3.3	6.50	SPR	CG	Z
0.875	22.23	S-1359	1.50	38.1	.813	20.7	.96	.17	1.3	34	1.3	5.7	.16	3.9	0.031	0.8	4.00	SST	C	N
0.875	22.23	11550	1.50	38.1	.789	20.0	2.8	.50	1.2	32	3.5	16	.26	6.6	0.043	1.1	5.00	SPR	C	Z
0.875	22.23	10497	1.50	38.1	.731	18.6	12	2.1	.91	23	11	48	.59	15.1	0.072	1.8	8.25	SPR	CG	Z
0.875	22.23	10398	1.50	38.1	.715	18.2	18	3.2	.82	21	15	66	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.875	22.23	4389	1.56	39.7	.731	18.6	10	1.8	.90	23	9.2	41	.67	16.9	0.072	1.8	9.25	SPR	CG	Z
0.875	22.23	S-1574	1.59	40.5	.775	19.7	3.5	.62	1.2	32	4.4	20	.35	8.9	0.050	1.3	6.00	SST	C	N
0.875	22.23	S-208	1.63	41.3	.751	19.1	6.9	1.2	1.2	30	8.2	36	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.875	22.23	S-42	1.63	41.3	.727	18.5	15	2.6	1.0	25	15	66	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.875	22.23	11584	1.75	44.5	.733	18.6	9.4	1.6	1.0	26	9.4	42	.75	18.9	0.071	1.8	9.50	SPR	CG	Z
0.875	22.23	11999	1.78	45.2	.665	16.9	70	12	.62	16	43	190	.79	20.0	0.105	2.7	7.50	SPR	CG	Z
0.875	22.23	S-1390	1.88	47.6	.715	18.2	17	3.0	1.1	28	19	83	.72	18.3	0.080	2.0	8.00	SST	C	N
0.875	22.23	3525	1.88	47.6	.491	12.5	943	165	.22	5.7	212	943	1.63	41.5	0.192	4.9	8.50	HD	CG	Z
0.875	22.23	B7-52	1.91	48.4	.643	16.3	64	11	.72	18	46	204	1.19	30.2	0.116	2.9	10.3	SST	CG	N
0.875	22.23	2588	1.94	49.2	.693	17.6	41	7.2	.69	17	28	125	.64	16.2	0.091	2.3	7.00	HD	CG	Z
0.875	22.23	A13-70	1.97	50.0	.731	18.6	15	2.6	.94	24	14	61	.54	13.7	0.072	1.8	6.50	SST	C	N
0.875	22.23	12264	2.00	50.8	.749	19.0	11	1.9	.98	25	10	46	.44	11.2	0.063	1.6	6.00	SPR	C	Z
0.875	22.23	1916	2.00	50.8	.731	18.6	16	2.8	.92	23	15	65	.55	14.0	0.072	1.8	6.67	SPR	C	Z
0.875	22.23	II-65	2.00	50.8	.695	17.7	32	5.7	.84	21	27	121	.81	20.6	0.090	2.3	8.00	SPR	C	Z
0.875	22.23	3308	2.00	50.8	.691	17.6	61	11	.47	12	29	129	.60	15.2	0.092	2.3	5.50	SPR	C	Z
0.875	22.23	3926	2.00	50.8	.665	16.9	77	13	.56	14	43	190	.84	21.3	0.105	2.7	7.00	SPR	C	Z
0.875	22.23	68	2.00	50.8	.635	16.1	99	17	.62	16	61	272	1.08	27.4	0.120	3.0	9.00	HD	CG	Z
0.875	22.23	808	2.00	50.8	.521	13.2	572	100	.31	7.9	177	787	1.64	41.6	0.177	4.5	9.25	HD	CG	Z
0.875	22.23	2825	2.03	51.6	.631	16.0	76	13	.58	15	44	196	1.45	36.8	0.122	3.1	12.0	SPR	CG	GI
0.875	22.23	10552	2.06	52.4	.765	19.4	4.3	.76	1.6	40	6.9	31	.47	11.9	0.055	1.4	7.50	SPR	C	Z
0.875	22.23	11841	2.06	52.4	.667	16.9	46	8.0	.91	23	42	185	1.04	26.4	0.104	2.6	10.0	SPR	CG	Z
0.875	22.23	12449	2.06	52.4	.633	16.1	120	21	.52	13	63	279	.97	24.6	0.121	3.1	8.00	SPR	CG	N
0.875	22.23	11205	2.13	54.0	.745	18.9	5.4	.94	1.4	36	7.5	34	.72	18.2	0.065	1.7	10.0	SST	C	N
0.875	22.23	3025	2.13	54.0	.625	15.9	139	24	.50	13	69	307	1.13	28.6	0.125	3.2	8.00	SPR	C	Z
0.875	22.23	A14-66	2.16	54.8	.741	18.8	12	2.1	.97	25	12	52	.40	10.2	0.067	1.7	6.00	SST	CG	N
0.875	22.23	2971	2.19	55.6	.691	17.6	48	8.3	.61	15	29	129	.69	17.5	0.092	2.3	6.50	SPR	C	Z
0.875	22.23	12005	2.19	55.6	.689	17.5	45	7.9	.67	17	30	133	.65	16.5	0.093	2.4	7.00	SPR	CG	Z
0.875	22.23	S-299	2.22	56.4	.795	20.2	.92	.16	1.9	47	1.7	7.6	.36	9.1	0.040	1.0	8.00	SST	C	N
0.875	22.23	11104	2.25	57.2	.761	19.3	5.0	.88	1.5	39	7.7	34	.48	12.3	0.057	1.4	7.50	SPR	C	N
0.875	22.23	3895	2.25	57.2	.725	18.4	11	1.9	1.5	38	17	74	.75	19.1	0.075	1.9	10.0	SPR	CG	Z
0.875	22.23	10119	2.25	57.2	.649	16.5	59	10	.87	22	51	228	1.24	31.6	0.113	2.9	11.0	SPR	CG	Z
0.875	22.23	2927	2.38	60.3	.767	19.5	2.2	.39	1.7	44	3.9	17	.64	16.3	0.054	1.4	12.0	SPR	CG	GI
0.875	22.23	3952	2.38	60.3	.731	18.6	11	1.9	1.4	35	15	65	.72	18.3	0.072	1.8	9.00	SPR	C	Z
0.875	22.23	S-1314	2.44	61.9	.665	16.9	35	6.1	1.1	29	40	177	1.21	30.7	0.105	2.7	11.5	SST	CG	N
0.875	22.23	11272	2.50	63.5	.665	16.9	59	10	.73	18	43	190	.89	22.7	0.105	2.7	8.50	SPR	CG	Z
0.875	22.23	864	2.50	63.5	.635	16.1	69	12	.88	22	61	272	1.44	36.6	0.120	3.0	12.0	HD	CG	Z
0.875	22.23	49	2.50	63.5	.605	15.4	118	21	.71	18	84	372	1.62	41.1	0.135	3.4	12.0	HD	CG	Z
0.875	22.23	4142	2.75	69.9	.663	16.8	47	8.2	.94	24	44	196	1.11	28.3	0.106	2.7	10.5	SPR	CG	Z




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.875	22.23	10808	4.00	101.6	.731	18.6	6.8	1.2	2.2	55	15	65	1.01	25.6	0.072	1.8	13.0	SPR	C	Z
0.875	22.23	2711	4.00	101.6	.715	18.2	8.4	1.5	2.4	61	20	89	1.52	38.5	0.080	2.0	17.5	SPR	C	Z
0.875	22.23	2808	4.00	101.6	.715	18.2	7.5	1.3	2.5	64	19	84	1.49	37.8	0.080	2.0	17.8	HD	C	Z
0.875	22.23	891	4.00	101.6	.715	18.2	9.0	1.6	2.2	56	20	89	1.28	32.5	0.080	2.0	15.0	HD	C	Z
0.875	22.23	S-460	4.00	101.6	.691	17.6	16	2.8	1.7	43	27	120	1.36	34.5	0.092	2.3	13.8	SST	C	N
0.875	22.23	3279	4.00	101.6	.685	17.4	18	3.1	1.8	46	32	142	1.62	41.0	0.095	2.4	16.0	SPR	C	Z
0.875	22.23	4253	4.00	101.6	.665	16.9	27	4.7	1.6	40	43	190	1.81	46.0	0.105	2.7	16.3	SPR	C	Z
0.875	22.23	12797	4.31	109.5	.625	15.9	50	8.8	1.9	49	96	428	2.33	59.1	0.125	3.2	18.6	MW	CG	N
0.875	22.23	11151	4.41	111.9	.625	15.9	58	10	1.2	30	69	307	2.16	54.8	0.125	3.2	16.0	HD	C	Z
0.875	22.23	2826	4.50	114.3	.675	17.1	17	3.0	2.5	64	43	193	1.99	50.5	0.100	2.5	20.0	MW	CG	GI
0.875	22.23	653	4.50	114.3	.521	13.2	227	40	.78	20	177	787	3.58	91.0	0.177	4.5	20.3	HD	CG	Z
0.875	22.23	2732	4.94	125.4	.691	17.6	15	2.6	2.0	50	29	129	1.52	38.6	0.092	2.3	16.5	SPR	CG	Z
0.875	22.23	3933	5.50	139.7	.693	17.6	12	2.1	2.3	59	28	125	1.73	43.9	0.091	2.3	19.0	SPR	CG	Z
0.875	22.23	11973	5.63	142.9	.675	17.1	16	2.8	3.2	81	52	231	2.10	53.3	0.100	2.5	21.0	MW	CG	Z
0.875	22.23	883	6.00	152.4	.693	17.6	9.3	1.6	3.0	77	28	125	2.18	55.5	0.091	2.3	24.0	HD	CG	Z
0.875	22.23	872	6.00	152.4	.665	16.9	16	2.8	2.7	67	43	190	2.81	71.3	0.105	2.7	25.8	HD	C	Z
0.875	22.23	865	6.00	152.4	.635	16.1	29	5.1	2.1	54	61	272	3.12	79.2	0.120	3.0	26.0	HD	CG	Z
0.875	22.23	855	6.00	152.4	.605	15.4	46	8.0	1.8	46	84	372	3.75	95.2	0.135	3.4	27.8	HD	CG	Z
0.875	22.23	818	6.00	152.4	.579	14.7	70	12	1.6	40	109	485	4.11	104.3	0.148	3.8	27.8	HD	CG	Z
0.875	22.23	1939	6.50	165.1	.689	17.5	7.6	1.3	3.5	88	27	118	3.02	76.8	0.093	2.4	31.5	SPR	C	Z
0.875	22.23	395	7.13	181.0	.647	16.4	20	3.5	2.7	68	53	234	3.41	86.7	0.114	2.9	30.0	SPR	CG	Z
0.875	22.23	892	7.75	196.9	.715	18.2	4.5	.79	4.4	113	20	89	2.32	58.9	0.080	2.0	28.0	HD	C	Z
0.875	22.23	11686	7.75	196.9	.661	16.8	13	2.2	3.6	92	45	201	3.88	98.5	0.107	2.7	35.3	SPR	C	Z
0.875	22.23	11982	8.22	208.8	.671	17.0	10	1.8	3.9	98	39	175	3.57	90.7	0.102	2.6	35.0	SPR	CG	Z
0.875	22.23	11525	8.28	210.3	.685	17.4	12	2.1	2.7	69	32	142	2.28	57.9	0.095	2.4	23.0	SPR	CG	Z
0.875	22.23	377	8.50	215.9	.731	18.6	3.7	.65	3.9	100	15	65	1.66	42.1	0.072	1.8	22.0	HD	C	Z
0.875	22.23	10004	8.88	225.4	.635	16.1	18	3.2	3.4	85	61	272	4.80	121.9	0.120	3.0	40.0	SPR	CG	Z
0.875	22.23	289	12.0	304.8	.751	19.1	1.2	.22	8.0	204	9.9	44	2.17	55.1	0.062	1.6	34.0	HD	C	Z
0.875	22.23	899	12.0	304.8	.731	18.6	2.1	.36	7.1	181	15	65	2.83	71.8	0.072	1.8	38.3	HD	C	Z
0.875	22.23	893	12.0	304.8	.715	18.2	2.9	.50	7.0	177	20	89	3.49	88.7	0.080	2.0	42.7	HD	C	Z
0.875	22.23	10677	12.3	311.2	.645	16.4	11	1.9	5.0	127	54	240	6.33	160.7	0.115	2.9	55.0	SPR	CG	Z
0.875	22.23	4015	18.5	469.9	.715	18.2	1.9	.33	11	272	20	89	5.24	133.1	0.080	2.0	64.5	HD	C	Z
0.875	22.23	4037	26.5	673.1	.605	15.4	10	1.8	8.2	207	84	372	15.8	401.2	0.135	3.4	117.0	SPR	CG	Z
0.890	22.61	2827	.63	15.9	.730	18.5	37	6.5	.23	5.7	8.3	37	.40	10.2	0.080	2.0	5.00	HD	CG	Z
0.890	22.61	AA-64	.63	15.9	.630	16.0	468	82	.11	2.7	49	218	.52	13.2	0.130	3.3	4.00	SPR	CG	Z
0.890	22.61	10584	.91	23.0	.650	16.5	261	46	.23	5.9	60	268	.54	13.7	0.120	3.0	4.50	SPR	CG	Z
0.890	22.61	10031	1.00	25.4	.796	20.2	2.9	.51	.67	17	2.0	8.7	.33	8.4	0.047	1.2	6.00	SPR	C	Z
0.890	22.61	1910	1.00	25.4	.780	19.8	11	2.0	.61	15	6.8	30	.22	5.6	0.055	1.4	4.00	SPR	CG	Z
0.890	22.61	11919	1.09	27.8	.682	17.3	102	18	.37	9.4	38	169	.52	13.2	0.104	2.6	5.00	SST	CG	N
0.890	22.61	PP-64	1.38	34.9	.770	19.6	8.1	1.4	1.0	26	8.3	37	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.890	22.61	11232	1.38	34.9	.748	19.0	11	1.9	.81	20	8.9	40	.57	14.4	0.071	1.8	8.00	SPR	CG	N
0.890	22.61	3383	1.38	34.9	.736	18.7	34	6.0	.52	13	18	78	.44	11.2	0.077	2.0	4.75	SPR	C	Z
0.890	22.61	11412	1.38	34.9	.680	17.3	90	16	.47	12	42	187	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
0.890	22.61	S-324	1.38	34.9	.566	14.4	595	104	.20	5.1	121	536	.93	23.7	0.162	4.1	5.75	SST	CG	N
0.890	22.61	11863	1.41	35.7	.768	19.5	5.0	.87	.80	20	4.0	18	.61	15.5	0.061	1.5	9.00	SPR	C	N
0.890	22.61	10293	1.44	36.5	.746	18.9	14	2.5	.93	24	13	59	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.890	22.61	10165	1.44	36.5	.578	14.7	431	75	.28	7.2	122	542	1.09	27.7	0.156	4.0	7.00	SPR	CG	Z
0.890	22.61	A14-54	1.50	38.1	.806	20.5	1.8	.32	1.2	32	2.3	10	.25	6.4	0.042	1.1	6.00	SPR	CG	N
0.890	22.61	11318	1.50	38.1	.748	19.0	13	2.2	.99	25	12	56	.51	13.1	0.071	1.8	7.25	SPR	CG	Z
0.890	22.61	10338	1.50	38.1	.730	18.5	18	3.1	.84	21	15	66	.66	16.8	0.080	2.0	8.25	SPR	CG	Z
0.890	22.61	11171	1.50	38.1	.730	18.5	20	3.5	.90	23	18	81	.60	15.2	0.080	2.0	7.50	SPR	CG	Z
0.890	22.61	WW-66	1.63	41.3	.786	20.0	2.2	.39	1.1	28	2.5	11	.52	13.2	0.052	1.3	9.00	SST	C	N
0.890	22.61	10656	1.63	41.3	.750	19.1	10	1.8	1.0	27	10	47	.58	14.7	0.070	1.8	8.25	SPR	CG	Z
0.890	22.61	10488	1.69	42.8	.626	15.9	154	27	.50	13	77	343	1.12	28.5	0.132	3.4	8.50	SPR	CG	Z
0.890	22.61	12175	1.78	45.2	.620	15.7	185	32	.45	11	82	367	1.08	27.4	0.135	3.4	8.00	SPR	CG	N
0.890	22.61	00-88	1.88	47.6	.658	16.7	57	10	.66	17	38	168	1.22	30.9	0.116	2.9	10.5	SST	CG	N
0.890	22.61																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.890	22.61	11962	5.56	141.3	.688	17.5	16	2.8	2.3	60	38	167	2.12	53.9	0.101	2.6	21.0	SPR	CG	Z
0.890	22.61	11764	6.00	152.4	.620	15.7	43	7.5	1.9	49	82	367	3.75	95.2	0.135	3.4	27.8	SPR	CG	Z
0.890	22.61	12395	6.13	155.6	.650	16.5	27	4.8	2.2	56	60	268	3.24	82.3	0.120	3.0	26.0	SPR	C	Z
0.890	22.61	12604	6.88	174.6	.578	14.7	82	14	2.1	53	171	759	4.56	115.9	0.156	4.0	28.3	MW	C	N
0.906	23.01	2766	.50	12.7	.686	17.4	417	73	.11	2.8	46	205	.33	8.4	0.110	2.8	3.00	SPR	CG	Z
0.906	23.01	1777	.59	15.1	.782	19.9	11	1.9	.21	5.2	2.2	9.9	.39	9.9	0.062	1.6	5.25	HD	C	Z
0.906	23.01	3542	.59	15.1	.780	19.8	19	3.3	.34	8.7	6.4	29	.25	6.4	0.063	1.6	4.00	HD	CG	Z
0.906	23.01	12410	.63	15.9	.798	20.3	20	3.5	.32	8.2	6.4	28	.22	5.5	0.054	1.4	3.00	SPR	C	N
0.906	23.01	10008	.63	15.9	.782	19.9	35	6.2	.27	6.9	9.6	43	.19	4.7	0.062	1.6	3.00	SPR	CG	Z
0.906	23.01	10118	.63	15.9	.782	19.9	18	3.1	.32	8.0	5.6	25	.31	7.9	0.062	1.6	4.00	HD	C	Z
0.906	23.01	2954	.75	19.1	.786	20.0	15	2.7	.51	13	7.8	35	.24	6.1	0.060	1.5	4.00	SPR	CG	Z
0.906	23.01	A11-51	.75	19.1	.664	16.9	340	59	.18	4.5	61	270	.47	11.9	0.121	3.1	4.00	SPR	CG	Z
0.906	23.01	10551	.81	20.6	.834	21.2	2.4	.43	.65	17	1.6	7.1	.16	4.1	0.036	0.9	3.50	SPR	C	Z
0.906	23.01	2538	.91	23.0	.656	16.7	368	65	.18	4.6	67	297	.50	12.7	0.125	3.2	4.00	SPR	CG	Z
0.906	23.01	11847	1.16	29.4	.812	20.6	4.9	.86	.86	22	4.2	19	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.906	23.01	11536	1.16	29.4	.760	19.3	24	4.1	.63	16	15	66	.44	11.1	0.073	1.9	5.00	SPR	CG	Z
0.906	23.01	10390	1.22	31.0	.736	18.7	27	4.7	.62	16	17	75	.60	15.1	0.085	2.2	7.00	SPR	CG	Z
0.906	23.01	1579	1.25	31.8	.746	18.9	42	7.3	.46	12	19	86	.44	11.2	0.080	2.0	4.50	SPR	C	Z
0.906	23.01	PP-72	1.25	31.8	.746	18.9	23	4.1	.73	19	17	75	.52	13.2	0.080	2.0	6.50	SPR	CG	BO
0.906	23.01	10463	1.25	31.8	.734	18.6	25	4.3	.58	15	14	64	.67	16.9	0.086	2.2	7.75	SPR	CG	Z
0.906	23.01	11121	1.25	31.8	.724	18.4	33	5.8	.57	14	19	84	.68	17.3	0.091	2.3	7.50	HD	CG	Z
0.906	23.01	PP-45	1.28	32.5	.846	21.5	.17	.03	.89	23	.15	.69	.39	9.9	0.030	0.8	12.0	MW	C	GI
0.906	23.01	2881	1.31	33.3	.782	19.9	12	2.1	.81	21	9.6	43	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.906	23.01	10567	1.38	34.9	.746	18.9	17	2.9	.72	18	12	53	.66	16.8	0.080	2.0	8.25	SPR	CG	Z
0.906	23.01	10397	1.47	37.3	.750	19.1	16	2.7	.84	21	13	59	.62	15.8	0.078	2.0	8.00	SPR	CG	Z
0.906	23.01	S-1546	1.50	38.1	.864	21.9	.03	.01	1.2	31	.04	.19	.28	7.1	0.021	0.5	12.3	SST	C	N
0.906	23.01	11319	1.50	38.1	.750	19.1	19	3.3	.88	22	16	73	.62	15.8	0.078	2.0	7.00	SPR	C	Z
0.906	23.01	10377	1.50	38.1	.746	18.9	16	2.8	.82	21	13	59	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.906	23.01	10345	1.50	38.1	.736	18.7	23	4.0	.74	19	17	74	.77	19.4	0.085	2.2	8.00	SPR	C	Z
0.906	23.01	S-1196	1.50	38.1	.696	17.7	49	8.6	.66	17	33	145	.84	21.3	0.105	2.7	8.00	SST	CG	N
0.906	23.01	B17-187	1.53	38.9	.734	18.6	29	5.0	.84	21	24	107	.60	15.3	0.086	2.2	7.00	SPR	CG	Z
0.906	23.01	10674	1.56	39.7	.766	19.5	9.8	1.7	.93	24	9.2	41	.63	16.0	0.070	1.8	8.00	SPR	C	Z
0.906	23.01	10842	1.56	39.7	.746	18.9	20	3.5	.90	23	18	80	.66	16.8	0.080	2.0	7.25	SPR	C	N
0.906	23.01	3149	1.56	39.7	.666	16.9	112	20	.53	13	59	264	.90	22.9	0.120	3.0	7.50	SPR	CG	Z
0.906	23.01	3754	1.75	44.5	.696	17.7	68	12	.61	15	41	184	.74	18.7	0.105	2.7	7.00	HD	CG	Z
0.906	23.01	11941	1.75	44.5	.636	16.2	174	30	.47	12	81	361	1.08	27.4	0.135	3.4	8.00	SPR	CG	Z
0.906	23.01	1603	2.13	54.0	.810	20.6	1.1	.19	1.5	38	1.6	7.3	.62	15.8	0.048	1.2	13.0	MW	CG	Z
0.906	23.01	10739	2.25	57.2	.790	20.1	4.9	.85	1.6	41	7.9	35	.49	12.5	0.058	1.5	7.50	SPR	C	N
0.906	23.01	10614	2.31	58.7	.746	18.9	12	2.0	1.4	36	17	74	.88	22.4	0.080	2.0	11.0	SPR	CG	Z
0.906	23.01	11924	2.34	59.5	.746	18.9	16	2.8	1.2	31	19	86	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.906	23.01	11853	2.38	60.3	.840	21.3	.65	.11	2.2	55	1.4	6.2	.21	5.4	0.033	0.8	5.50	SST	C	N
0.906	23.01	10378	2.38	60.3	.782	19.9	2.9	.52	1.5	38	4.4	20	.87	22.0	0.062	1.6	14.0	SPR	CG	Z
0.906	23.01	12104	2.47	62.7	.550	14.0	416	73	.42	11	175	777	1.96	49.7	0.178	4.5	11.0	SPR	CG	Z
0.906	23.01	53	2.75	69.9	.696	17.7	35	6.2	1.2	30	41	184	1.33	33.8	0.105	2.7	11.7	HD	C	Z
0.906	23.01	1665	3.13	79.4	.756	19.2	8.8	1.5	2.2	57	20	87	.90	22.9	0.075	1.9	11.0	MW	C	Z
0.906	23.01	1537	3.16	80.2	.762	19.4	7.2	1.3	2.0	50	14	63	.88	22.4	0.072	1.8	11.3	SPR	C	Z
0.906	23.01	2679	3.19	81.0	.724	18.4	14	2.4	1.7	43	23	104	1.48	37.6	0.091	2.3	15.3	MW	C	Z
0.906	23.01	3463	3.38	85.7	.722	18.3	20	3.5	1.4	36	28	125	1.15	29.2	0.092	2.3	11.5	HD	C	Z
0.906	23.01	B9-55	3.50	88.9	.826	21.0	.52	.09	3.0	76	1.5	6.8	.52	13.2	0.040	1.0	13.0	SPR	CG	N
0.906	23.01	3233	3.56	90.5	.714	18.1	19	3.3	1.7	43	32	142	1.46	37.2	0.096	2.4	14.3	SPR	C	Z
0.906	23.01	12109	3.59	91.3	.760	19.3	8.8	1.5	1.7	43	15	66	.73	18.5	0.073	1.9	10.0	SPR	CG	Z
0.906	23.01	S-3042	3.63	92.1	.610	15.5	115	20	.83	21	95	424	2.07	52.6	0.148	3.8	14.0	SST	CG	N
0.906	23.01	3342	4.00	101.6	.756	19.2	3.7	.65	2.2	57	8.2	37	1.76	44.8	0.075	1.9	23.5	SPR	CG	Z
0.906	23.01	3435	4.25	108.0	.806	20.5	1.4	.25	3.5	90	5.1	23	.65	16.5	0.050	1.3	12.0	SPR	C	Z
0.906	23.01	1689	5.00	127.0	.746	18.9	7.1	1.2	2.7	70	19	86	1.34	34.0	0.080	2.0	16.8	SPR	CG	Z
0.906	23.01	12677	5.38	136.5	.656	16.7	35	6.1	1.9	48	67	297	3.00	76.2	0.125	3.2	23.0	SPR	C	N
0.906	23.01	12158	8.75	222.3	.756	19.2	2.5	.43	6.2	157	15	68	2.55	64.8	0.075	1.9	34.0	SPR	CG	Z
0.906	23.01	3912	9.0																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.921	23.39	S-140	1.50	38.1	.547	13.9	1104	193	.15	3.7	163	725	1.03	26.1	0.187	4.7	5.50	SST	CG	N
0.921	23.39	10254	1.56	39.7	.771	19.6	33	5.8	.47	12	16	70	.32	8.1	0.075	1.9	4.25	SPR	CG	Z
0.921	23.39	10610	1.56	39.7	.703	17.9	79	14	.53	14	42	188	.68	17.3	0.109	2.8	6.25	SST	CG	N
0.921	23.39	3189	1.59	40.5	.761	19.3	15	2.7	.91	23	14	62	.68	17.3	0.080	2.0	8.50	SPR	CG	GI
0.921	23.39	11207	1.69	42.8	.721	18.3	58	10	.57	14	33	146	.60	15.2	0.100	2.5	6.00	SST	CG	N
0.921	23.39	3815	1.75	44.5	.661	16.8	166	29	.43	11	72	319	.91	23.1	0.130	3.3	7.00	SPR	CG	Z
0.921	23.39	PP-1	2.03	51.6	.621	15.8	244	43	.43	11	106	470	1.28	32.4	0.150	3.8	8.50	SPR	CG	Z
0.921	23.39	11637	2.06	52.4	.799	20.3	4.5	.78	1.5	38	6.8	30	.55	13.9	0.061	1.5	9.00	SPR	CG	Z
0.921	23.39	11236	2.38	60.3	.797	20.2	2.8	.49	1.5	38	4.2	19	.87	22.0	0.062	1.6	14.0	SPR	CG	Z
0.921	23.39	1737	2.75	69.9	.665	16.9	72	13	.98	25	70	313	1.63	41.5	0.128	3.3	12.8	HD	CG	Z
0.921	23.39	S-1611	2.78	70.6	.731	18.6	17	2.9	1.5	39	26	115	1.24	31.4	0.095	2.4	13.0	SST	CG	N
0.921	23.39	10597	3.00	76.2	.777	19.7	7.0	1.2	2.0	51	14	62	.86	21.9	0.072	1.8	11.0	SPR	C	Z
0.921	23.39	3351	3.00	76.2	.761	19.3	9.9	1.7	1.9	49	19	85	.96	24.4	0.080	2.0	12.0	HD	CG	Z
0.921	23.39	3070	3.00	76.2	.671	17.0	75	13	.87	22	66	293	1.41	35.7	0.125	3.2	11.3	SPR	CG	GI
0.921	23.39	MM-92	3.00	76.2	.541	13.7	505	88	.39	10	198	880	2.19	55.5	0.190	4.8	11.5	SPR	CG	N
0.921	23.39	12103	3.22	81.8	.821	20.9	1.5	.26	2.7	68	4.0	18	.55	14.0	0.050	1.3	11.0	SPR	CG	Z
0.921	23.39	1888	3.31	84.1	.777	19.7	7.0	1.2	2.0	51	14	62	.86	21.9	0.072	1.8	11.0	HD	C	Z
0.921	23.39	1685	4.50	114.3	.711	18.1	25	4.3	1.7	42	41	182	1.68	42.7	0.105	2.7	15.0	SPR	C	Z
0.921	23.39	12174	4.75	120.7	.711	18.1	21	3.8	1.9	48	41	182	1.79	45.3	0.105	2.7	17.0	SPR	CG	Z
0.921	23.39	12040	5.50	139.7	.791	20.1	2.0	.36	4.1	103	8.3	37	1.43	36.3	0.065	1.7	22.0	SPR	CG	Z
0.921	23.39	S-462	6.25	158.8	.777	19.7	3.7	.65	3.5	89	13	58	1.28	32.5	0.072	1.8	16.8	SST	C	N
0.921	23.39	3285	6.50	165.1	.701	17.8	19	3.3	2.4	61	45	201	2.53	64.3	0.110	2.8	23.0	SPR	CG	Z
0.921	23.39	4017	19.8	501.7	.631	16.0	20	3.5	5.0	126	98	437	10.2	259.7	0.145	3.7	70.5	SPR	CG	Z
0.938	23.83	3663	.44	11.1	.828	21.0	19	3.3	.27	6.9	5.2	23	.17	4.2	0.055	1.4	3.00	SPR	CG	Z
0.938	23.83	3687	.63	15.9	.828	21.0	19	3.3	.34	8.6	6.5	29	.22	5.6	0.055	1.4	3.00	SPR	C	Z
0.938	23.83	S-3040	.75	19.1	.678	17.2	451	79	.14	3.6	63	282	.46	11.6	0.130	3.3	3.50	SST	CG	N
0.938	23.83	4235	.75	19.1	.668	17.0	615	108	.13	3.2	79	350	.47	12.0	0.135	3.4	3.50	SPR	CG	Z
0.938	23.83	MM-75	.78	19.8	.758	19.3	46	8.0	.33	8.4	15	67	.45	11.4	0.090	2.3	5.00	SST	CG	N
0.938	23.83	1855	.94	23.8	.698	17.7	218	38	.37	9.4	80	357	.54	13.7	0.120	3.0	4.50	MW	CG	Z
0.938	23.83	S-902	.94	23.8	.694	17.6	260	46	.21	5.4	55	245	.49	12.4	0.122	3.1	4.00	SST	CG	N
0.938	23.83	924	1.13	28.6	.728	18.5	86	15	.44	11	38	170	.68	17.3	0.105	2.7	5.50	HD	C	Z
0.938	23.83	11762	1.16	29.4	.622	15.8	755	132	.16	4.1	121	537	.71	18.1	0.158	4.0	4.50	SPR	CG	Z
0.938	23.83	2609	1.19	30.2	.614	15.6	605	106	.21	5.4	130	577	.89	22.6	0.162	4.1	5.50	HD	CG	Z
0.938	23.83	GG-41	1.22	31.0	.758	19.3	46	8.0	.52	13	24	105	.45	11.4	0.090	2.3	5.00	SST	CG	N
0.938	23.83	1617	1.25	31.8	.826	21.0	5.2	.90	.86	22	4.4	20	.39	10.0	0.056	1.4	6.00	SPR	C	Z
0.938	23.83	10524	1.25	31.8	.734	18.6	71	12	.52	13	37	164	.59	14.9	0.102	2.6	5.75	SPR	CG	Z
0.938	23.83	B2-59	1.25	31.8	.668	17.0	284	50	.39	9.8	110	489	.71	18.0	0.135	3.4	5.25	MW	CG	N
0.938	23.83	10211	1.38	34.9	.814	20.7	9.0	1.6	1.0	26	9.3	41	.34	8.7	0.062	1.6	5.50	SPR	CG	Z
0.938	23.83	10268	1.38	34.9	.814	20.7	11	1.8	.88	22	9.3	41	.37	9.4	0.062	1.6	5.00	SPR	C	N
0.938	23.83	S-1123	1.38	34.9	.768	19.5	26	4.6	.78	20	21	91	.60	15.1	0.085	2.2	6.00	SST	C	N
0.938	23.83	11794	1.38	34.9	.700	17.8	105	18	.53	14	56	249	.83	21.2	0.119	3.0	7.00	SPR	CG	Z
0.938	23.83	11738	1.38	34.9	.666	16.9	318	56	.25	6.4	80	357	.68	17.3	0.136	3.5	5.00	SPR	CG	Z
0.938	23.83	11724	1.41	35.7	.754	19.2	43	7.4	.64	16	27	121	.55	14.0	0.092	2.3	6.00	SPR	CG	Z
0.938	23.83	10726	1.50	38.1	.848	21.5	.97	.17	.98	25	.96	4.3	.52	13.1	0.045	1.1	10.5	SPR	C	Z
0.938	23.83	3885	1.50	38.1	.738	18.7	54	9.5	.64	16	35	155	.65	16.5	0.100	2.5	6.50	SPR	CG	GI
0.938	23.83	10977	1.50	38.1	.728	18.5	76	13	.53	13	40	179	.63	16.0	0.105	2.7	6.00	HD	CG	Z
0.938	23.83	PP-62	1.50	38.1	.718	18.2	93	16	.48	12	45	198	.66	16.8	0.110	2.8	6.00	SPR	CG	Z
0.938	23.83	3625	1.50	38.1	.688	17.5	137	24	.66	17	90	401	.84	21.4	0.125	3.2	6.75	MW	CG	Z
0.938	23.83	CC-34	1.50	38.1	.618	15.7	355	62	.31	8.0	111	495	1.12	28.4	0.160	4.1	7.00	SST	CG	N
0.938	23.83	11149	1.59	40.5	.698	17.7	121	21	.47	12	57	255	.78	19.8	0.120	3.0	6.50	SPR	CG	Z
0.938	23.83	S-443	1.66	42.1	.838	21.3	3.8	.66	1.2	31	4.6	20	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.938	23.83	828	1.75	44.5	.698	17.7	99	17	.58	15	57	255	1.02	25.9	0.120	3.0	7.50	HD	C	Z
0.938	23.83	S-940	1.78	45.2	.794	20.2	13	2.3	.98	25	13	57	.50	12.8	0.072	1.8	6.00	SST	C	N
0.938	23.83	10622	1.78	45.2	.728	18.5	54	9.4	.69	18	37	166	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.938	23.83	11719	1.84	46.8	.666	16.9	191	33	.42	11	80	357	1.09	27.6	0.136	3.5	7.00	SPR	C	Z
0.938	23.83	3683	1.94	49.2	.810	20.6	5.8	1.0	1.4	36	8.1	36	.53	13.4	0.064	1.6	8.25	SPR	CG	Z
0.938	23.83	67	2.00	50.8	.778	19.8	17	3.1	1.1	27	19									




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.938	23.83	3125	4.31	109.5	.798	20.3	5.3	.92	2.4	61	13	56	.84	21.3	0.070	1.8	12.0	SPR	CG	Z
0.938	23.83	S-1407	4.38	111.1	.814	20.7	1.8	.32	3.3	84	6.1	27	1.05	26.8	0.062	1.6	17.0	SST	CG	N
0.938	23.83	3931	4.50	114.3	.626	15.9	122	21	.95	24	116	518	2.43	61.6	0.156	4.0	15.8	SPR	CG	Z
0.938	23.83	4342	5.00	127.0	.742	18.8	15	2.7	2.2	55	33	146	1.64	41.7	0.098	2.5	16.8	SPR	CG	Z
0.938	23.83	332	5.00	127.0	.584	14.8	175	31	.96	24	167	743	3.60	91.4	0.177	4.5	20.3	HD	CG	Z
0.938	23.83	2843	5.13	130.2	.764	19.4	10	1.8	2.3	59	24	107	1.31	33.1	0.087	2.2	15.0	SPR	CG	GI
0.938	23.83	S-154	5.25	133.4	.642	16.3	55	9.7	1.7	42	92	411	3.55	90.2	0.148	3.8	24.0	SST	CG	N
0.938	23.83	11627	5.25	133.4	.642	16.3	67	12	1.5	39	103	456	3.37	85.5	0.148	3.8	22.8	SPR	CG	Z
0.938	23.83	4149	6.00	152.4	.754	19.2	9.0	1.6	3.0	77	27	121	2.02	51.4	0.092	2.3	21.0	SPR	CG	Z
0.938	23.83	3113	6.38	161.9	.794	20.2	4.1	.72	3.3	85	14	61	1.19	30.2	0.072	1.8	16.5	SPR	CG	Z
0.938	23.83	2569	7.25	184.2	.728	18.5	15	2.6	2.7	67	40	179	2.42	61.3	0.105	2.7	22.0	SPR	CG	Z
0.938	23.83	11945	8.75	222.3	.810	20.6	1.1	.19	6.5	165	7.1	32	2.24	56.9	0.064	1.6	35.0	SPR	CG	Z
0.938	23.83	4233	9.75	247.7	.698	17.7	23	4.0	2.5	64	57	255	3.24	82.3	0.120	3.0	26.0	SPR	C	Z
0.938	23.83	3076	10.5	266.7	.756	19.2	6.8	1.2	3.9	98	26	117	2.34	59.5	0.091	2.3	25.8	SPR	CG	Z
0.938	23.83	1938	11.1	282.6	.664	16.9	29	5.0	2.9	73	82	365	5.00	127.0	0.137	3.5	36.5	SPR	CG	Z
0.953	24.21	NN-24	.69	17.4	.633	16.1	1511	265	.08	2.1	124	549	.52	13.2	0.160	4.1	3.25	SPR	CG	GI
0.953	24.21	11915	.88	22.2	.771	19.6	68	12	.35	9.0	24	107	.36	9.2	0.091	2.3	4.00	SST	CG	N
0.953	24.21	KK-68	.94	23.8	.833	21.2	6.5	1.1	.58	15	3.8	17	.36	9.1	0.060	1.5	6.00	SPR	CG	Z
0.953	24.21	3343	.94	23.8	.823	20.9	9.2	1.6	.55	14	5.0	22	.39	9.9	0.065	1.7	6.00	SPR	CG	Z
0.953	24.21	3010	.97	24.6	.771	19.6	77	13	.34	8.6	26	115	.36	9.2	0.091	2.3	4.00	SPR	CG	GI
0.953	24.21	S-1559	.98	25.0	.849	21.6	5.0	.88	.70	18	3.5	16	.29	7.3	0.052	1.3	4.50	SST	C	N
0.953	24.21	12699	1.00	25.4	.873	22.2	2.8	.49	.82	21	2.3	10	.18	4.6	0.040	1.0	3.50	SST	C	N
0.953	24.21	10683	1.00	25.4	.849	21.6	5.7	.99	.73	18	4.1	18	.27	6.9	0.052	1.3	4.25	SST	C	N
0.953	24.21	CC-72	1.00	25.4	.833	21.2	13	2.3	.63	16	8.3	37	.30	7.6	0.060	1.5	4.00	SPR	C	Z
0.953	24.21	3396	1.13	28.6	.825	21.0	12	2.2	.76	19	9.4	42	.37	9.3	0.064	1.6	4.75	SPR	C	Z
0.953	24.21	1907	1.25	31.8	.845	21.5	4.2	.74	.93	24	3.9	17	.32	8.2	0.054	1.4	6.00	SPR	CG	Z
0.953	24.21	4271	1.25	31.8	.829	21.1	7.5	1.3	.82	21	6.1	27	.43	11.0	0.062	1.6	6.00	SPR	C	Z
0.953	24.21	N-126	1.25	31.8	.797	20.2	14	2.5	.70	18	9.9	44	.55	13.9	0.078	2.0	7.00	SST	CG	N
0.953	24.21	2761	1.25	31.8	.639	16.2	433	76	.31	7.8	133	593	.94	23.9	0.157	4.0	6.00	MW	CG	Z
0.953	24.21	S-1254	1.28	32.5	.793	20.1	15	2.7	.72	18	11	49	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.953	24.21	12213	1.31	33.3	.599	15.2	863	151	.19	4.9	165	733	.97	24.7	0.177	4.5	5.50	SPR	CG	GI
0.953	24.21	11385	1.41	35.7	.743	18.9	64	11	.62	16	39	175	.79	20.0	0.105	2.7	6.50	SPR	C	Z
0.953	24.21	11541	1.47	37.3	.721	18.3	137	24	.38	9.5	51	228	.73	18.4	0.116	2.9	5.25	SPR	CG	GI
0.953	24.21	S-94	1.50	38.1	.703	17.9	90	16	.50	13	45	199	1.00	25.4	0.125	3.2	8.00	SST	CG	N
0.953	24.21	B18-140	1.50	38.1	.619	15.7	430	75	.29	7.3	124	552	1.13	28.6	0.167	4.2	6.75	SST	CG	N
0.953	24.21	11856	1.63	41.3	.805	20.4	11	2.0	1.1	28	12	55	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.953	24.21	3954	1.75	44.5	.809	20.5	6.6	1.2	.92	23	6.1	27	.83	21.0	0.072	1.8	10.5	SPR	C	Z
0.953	24.21	3385	1.75	44.5	.797	20.2	26	4.6	.65	16	17	76	.39	9.9	0.078	2.0	5.00	SPR	CG	Z
0.953	24.21	11492	1.75	44.5	.689	17.5	158	28	.46	12	73	323	1.06	26.8	0.132	3.4	7.00	SPR	CG	GI
0.953	24.21	2932	1.81	46.0	.739	18.8	44	7.8	.85	22	38	168	.96	24.5	0.107	2.7	9.00	SPR	CG	Z
0.953	24.21	S-984	1.91	48.4	.791	20.1	11	1.9	1.1	29	12	55	.77	19.5	0.081	2.1	9.50	SST	CG	N
0.953	24.21	AA-72	1.94	49.2	.693	17.6	98	17	.70	18	69	307	1.24	31.4	0.130	3.3	9.50	SPR	CG	Z
0.953	24.21	11157	2.00	50.8	.699	17.8	140	24	.48	12	67	297	.86	21.8	0.127	3.2	6.75	SPR	CG	Z
0.953	24.21	2875	2.13	54.0	.717	18.2	77	13	.70	18	54	240	1.09	27.7	0.118	3.0	8.25	SPR	C	Z
0.953	24.21	10566	2.28	57.9	.823	20.9	7.0	1.2	1.5	38	11	47	.54	13.6	0.065	1.7	7.25	SPR	C	Z
0.953	24.21	MM-54	2.44	61.9	.593	15.1	483	85	.29	7.5	142	633	1.44	36.6	0.180	4.6	8.00	SST	CG	N
0.953	24.21	S-1149	2.75	69.9	.793	20.1	11	1.9	1.6	40	17	77	.80	20.3	0.080	2.0	9.00	SST	C	N
0.953	24.21	11868	3.00	76.2	.783	19.9	12	2.2	1.7	43	21	92	.87	22.1	0.085	2.2	10.3	SST	CG	N
0.953	24.21	2917	3.69	93.6	.711	18.1	51	8.9	1.1	29	58	258	1.63	41.5	0.121	3.1	12.5	SPR	C	Z
0.953	24.21	2914	3.75	95.3	.793	20.1	11	1.9	1.7	42	18	82	.88	22.4	0.080	2.0	10.0	SPR	C	Z
0.953	24.21	11524	3.94	100.0	.743	18.9	23	4.0	1.7	44	40	176	1.63	41.3	0.105	2.7	14.5	SPR	CG	Z
0.953	24.21	11955	4.00	101.6	.763	19.4	19	3.2	1.6	40	29	131	1.24	31.4	0.095	2.4	12.0	SPR	C	Z
0.953	24.21	3423	4.38	111.1	.819	20.8	4.6	.81	2.5	63	12	51	.80	20.4	0.067	1.7	11.0	SPR	C	Z
0.953	24.21	3335	4.44	112.7	.693	17.6	59	10	1.2	30	69	309	2.02	51.2	0.130	3.3	14.5	SPR	C	Z
0.953	24.21	2642	4.81	122.2	.641	16.3	99	17	1.2	29	115	511	2.96	75.3	0.156	4.0	19.0	SPR	CG	Z
0.953	24.21	11558	7.75	196.9	.793	20.1	3.3	.57	5.4	136	18	78	2.40	61.0	0.080	2.0	29.0	SPR	CG	Z
0.953	24.21	3341	8.00	203.2	.539	13.7	254	45	.96	24	245	1088	5.59	142.0	0.207	5.3	2			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.968	24.59	2952	2.34	59.5	.824	20.9	11	1.9	1.2	32	13	59	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.968	24.59	3018	2.44	61.9	.808	20.5	11	1.8	1.6	42	17	77	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
0.968	24.59	3223	2.53	64.3	.812	20.6	15	2.6	1.1	28	17	75	.62	15.8	0.078	2.0	7.00	SPR	C	Z
0.968	24.59	4272	2.63	66.7	.688	17.5	111	19	.76	19	85	378	1.51	38.2	0.140	3.6	10.8	SPR	CG	Z
0.968	24.59	A13-68	2.78	70.6	.832	21.1	7.5	1.3	1.5	38	11	50	.48	12.1	0.068	1.7	7.00	SST	CG	N
0.968	24.59	11913	2.81	71.4	.788	20.0	15	2.7	1.5	38	23	102	.90	22.9	0.090	2.3	10.0	SST	CG	N
0.968	24.59	S-429	3.06	77.8	.780	19.8	15	2.7	1.7	43	26	116	1.08	27.5	0.094	2.4	11.5	SST	CG	N
0.968	24.59	B17-176	3.28	83.3	.718	18.2	42	7.4	1.4	35	57	255	1.79	45.5	0.125	3.2	14.3	SST	CG	N
0.968	24.59	3175	3.38	85.7	.878	22.3	.94	.16	2.9	74	2.7	12	.45	11.4	0.045	1.1	10.0	SPR	CG	Z
0.968	24.59	11436	3.38	85.7	.728	18.5	47	8.2	1.2	30	56	248	1.50	38.1	0.120	3.0	12.5	SPR	CG	Z
0.968	24.59	3106	3.38	85.7	.698	17.7	83	14	.92	23	76	340	1.62	41.1	0.135	3.4	12.0	SPR	CG	Z
0.968	24.59	1661	3.50	88.9	.758	19.3	30	5.3	1.3	33	39	173	1.26	32.0	0.105	2.7	11.0	SPR	C	Z
0.968	24.59	11486	4.09	104.0	.808	20.5	8.4	1.5	2.2	55	18	81	1.04	26.4	0.080	2.0	12.0	SPR	CG	Z
0.968	24.59	11640	4.38	111.1	.808	20.5	5.6	.98	3.0	77	17	75	1.36	34.5	0.080	2.0	17.0	SPR	CG	Z
0.968	24.59	10655	4.56	115.9	.720	18.3	49	8.6	1.2	32	61	273	1.67	42.5	0.124	3.1	13.5	SPR	CG	Z
0.968	24.59	11563	7.25	184.2	.778	19.8	7.7	1.3	3.8	96	29	129	2.47	62.7	0.095	2.4	25.0	SPR	CG	Z
0.968	24.59	12457	12.0	304.8	.728	18.5	14	2.4	4.1	103	56	248	4.38	111.3	0.120	3.0	35.5	SPR	CG	Z
0.968	24.59	3065	15.3	387.4	.758	19.3	5.8	1.0	6.7	171	39	173	5.15	130.7	0.105	2.7	49.0	SPR	CG	GI
0.968	24.59	3077	16.1	409.6	.808	20.5	2.0	.34	9.3	236	18	81	3.60	91.4	0.080	2.0	45.0	SPR	CG	Z
0.975	24.77	72327	.75	19.1	.849	21.6	26	4.5	.51	13	13	58	.20	5.0	0.063	1.6	3.13	MW	CG	N
0.975	24.77	72327S	.75	19.1	.849	21.6	22	3.8	.40	10	8.8	39	.20	5.0	0.063	1.6	3.13	SST	CG	N
0.975	24.77	72339	.75	19.1	.831	21.1	40	6.9	.47	12	18	82	.24	6.2	0.072	1.8	3.38	MW	CG	N
0.975	24.77	72339S	.75	19.1	.831	21.1	34	5.9	.37	9.4	12	55	.24	6.2	0.072	1.8	3.38	SST	CG	N
0.975	24.77	72351	.75	19.1	.827	21.0	40	7.0	.49	12	20	87	.26	6.6	0.074	1.9	3.50	MW	CG	N
0.975	24.77	72351S	.75	19.1	.827	21.0	34	5.9	.40	10	13	60	.26	6.6	0.074	1.9	3.50	SST	CG	N
0.975	24.77	72367	.75	19.1	.813	20.7	61	11	.43	11	26	117	.27	6.9	0.081	2.1	3.38	MW	CG	N
0.975	24.77	72367S	.75	19.1	.813	20.7	51	9.0	.34	8.7	18	78	.27	6.9	0.081	2.1	3.38	SST	CG	N
0.975	24.77	72352	.88	22.4	.827	21.0	33	5.8	.60	15	20	88	.28	7.0	0.074	1.9	3.75	MW	CG	N
0.975	24.77	72352S	.88	22.4	.827	21.0	28	4.9	.48	12	13	60	.28	7.0	0.074	1.9	3.75	SST	CG	N
0.975	24.77	72379	.88	22.4	.805	20.4	54	9.4	.54	14	29	129	.34	8.6	0.085	2.2	4.00	MW	CG	N
0.975	24.77	72379S	.88	22.4	.805	20.4	46	8.0	.44	11	20	90	.34	8.6	0.085	2.2	4.00	SST	CG	N
0.975	24.77	72394	.88	22.4	.791	20.1	72	13	.50	13	36	160	.38	9.6	0.092	2.3	4.13	MW	CG	N
0.975	24.77	72394S	.88	22.4	.791	20.1	61	11	.40	10	24	108	.38	9.6	0.092	2.3	4.13	SST	CG	N
0.975	24.77	72403	.88	22.4	.783	19.9	85	15	.48	12	41	182	.40	10.1	0.096	2.4	4.13	MW	CG	N
0.975	24.77	72403S	.88	22.4	.783	19.9	72	13	.38	9.7	28	123	.40	10.1	0.096	2.4	4.13	SST	CG	N
0.975	24.77	72415	.88	22.4	.765	19.4	119	21	.43	11	52	230	.45	11.3	0.105	2.7	4.25	MW	CG	N
0.975	24.77	72415S	.88	22.4	.765	19.4	101	18	.35	9.0	36	160	.45	11.3	0.105	2.7	4.25	SST	CG	N
0.975	24.77	72427	.88	22.4	.751	19.1	155	27	.40	10	62	278	.48	12.1	0.112	2.8	4.25	MW	CG	N
0.975	24.77	72427S	.88	22.4	.751	19.1	131	23	.31	8.0	41	184	.48	12.1	0.112	2.8	4.25	SST	CG	N
0.975	24.77	72455	.88	22.4	.725	18.4	247	43	.33	8.5	82	365	.55	13.9	0.125	3.2	4.38	MW	CG	N
0.975	24.77	72455S	.88	22.4	.725	18.4	210	37	.27	6.9	57	253	.55	13.9	0.125	3.2	4.38	SST	CG	N
0.975	24.77	72467	.88	22.4	.705	17.9	357	62	.30	7.6	106	473	.57	14.6	0.135	3.4	4.25	MW	CG	N
0.975	24.77	72467S	.88	22.4	.705	17.9	303	53	.23	5.7	68	304	.57	14.6	0.135	3.4	4.25	SST	CG	N
0.975	24.77	72328	1.00	25.4	.849	21.6	18	3.2	.71	18	13	58	.23	5.8	0.063	1.6	3.63	MW	CG	N
0.975	24.77	72328S	1.00	25.4	.849	21.6	16	2.7	.57	14	8.8	39	.23	5.8	0.063	1.6	3.63	SST	CG	N
0.975	24.77	72340	1.00	25.4	.831	21.1	28	4.9	.66	17	18	82	.28	7.1	0.072	1.8	3.88	MW	CG	N
0.975	24.77	72340S	1.00	25.4	.831	21.1	24	4.2	.52	13	12	55	.28	7.1	0.072	1.8	3.88	SST	CG	N
0.975	24.77	72353	1.00	25.4	.827	21.0	28	4.9	.69	18	20	87	.31	7.8	0.074	1.9	4.13	MW	CG	N
0.975	24.77	72353S	1.00	25.4	.827	21.0	24	4.2	.56	14	13	60	.31	7.8	0.074	1.9	4.13	SST	CG	N
0.975	24.77	72368	1.00	25.4	.813	20.7	44	7.6	.60	15	26	117	.32	8.2	0.081	2.1	4.00	MW	CG	N
0.975	24.77	72368S	1.00	25.4	.813	20.7	37	6.5	.47	12	18	78	.32	8.2	0.081	2.1	4.00	SST	CG	N
0.975	24.77	72380	1.00	25.4	.805	20.4	52	9.0	.59	15	30	134	.35	8.9	0.085	2.2	4.13	MW	CG	N
0.975	24.77	72380S	1.00	25.4	.805	20.4	44	7.7	.46	12	20	90	.35	8.9	0.085	2.2	4.13	SST	CG	N
0.975	24.77	72395	1.00	25.4	.791	20.1	61	11	.59	15	36	159	.41	10.5	0.092	2.3	4.50	MW	CG	N
0.975	24.77	72395S	1.00	25.4	.791	20.1	52	9.1	.47	12	24	108	.41	10.5	0.092	2.3	4.50	SST	CG	N
0.975	24.77	72404	1.00	25.4	.783	19.9	74	13	.56	14	42	185	.42	10.7	0.096	2.4	4.38	MW	CG	N
0.975	24.77	72404S	1.00	25.4	.783	19.9	63	11	.44	11	28	123	.42	10.7	0.096	2.4				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F W S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72396S	1.25	31.8	.791	20.1	40	7.0	.61	16	24	108	.48	12.3	0.092	2.3	5.25	SST	CG	N
0.975	24.77	72405	1.25	31.8	.783	19.9	56	9.9	.74	19	42	185	.49	12.5	0.096	2.4	5.13	MW	CG	N
0.975	24.77	72405S	1.25	31.8	.783	19.9	48	8.4	.57	15	28	123	.49	12.5	0.096	2.4	5.13	SST	CG	N
0.975	24.77	72417	1.25	31.8	.765	19.4	81	14	.67	17	54	241	.55	14.0	0.105	2.7	5.25	MW	CG	N
0.975	24.77	72417S	1.25	31.8	.765	19.4	69	12	.52	13	36	160	.55	14.0	0.105	2.7	5.25	SST	CG	N
0.975	24.77	72430	1.25	31.8	.751	19.1	102	18	.62	16	63	281	.62	15.6	0.112	2.8	5.50	MW	CG	N
0.975	24.77	72430S	1.25	31.8	.751	19.1	87	15	.48	12	41	184	.62	15.6	0.112	2.8	5.50	SST	CG	N
0.975	24.77	72457	1.25	31.8	.725	18.4	155	27	.55	14	85	378	.70	17.9	0.125	3.2	5.63	MW	CG	N
0.975	24.77	72457S	1.25	31.8	.725	18.4	132	23	.43	11	57	253	.70	17.9	0.125	3.2	5.63	SST	CG	N
0.975	24.77	72330	1.50	38.1	.849	21.6	12	2.0	1.1	28	13	58	.29	7.4	0.063	1.6	4.63	MW	CG	N
0.975	24.77	72330S	1.50	38.1	.849	21.6	9.9	1.7	.89	23	8.8	39	.29	7.4	0.063	1.6	4.63	SST	CG	N
0.975	24.77	72342	1.50	38.1	.831	21.1	18	3.1	1.0	27	18	82	.36	9.1	0.072	1.8	5.00	MW	CG	N
0.975	24.77	72342S	1.50	38.1	.831	21.1	15	2.6	.83	21	12	55	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.975	24.77	72355	1.50	38.1	.827	21.0	18	3.1	1.1	28	20	87	.40	10.1	0.074	1.9	5.38	MW	CG	N
0.975	24.77	72355S	1.50	38.1	.827	21.0	15	2.6	.89	23	13	60	.40	10.1	0.074	1.9	5.38	SST	CG	N
0.975	24.77	72370	1.50	38.1	.813	20.7	28	4.8	.95	24	26	117	.42	10.5	0.081	2.1	5.13	MW	CG	N
0.975	24.77	72370S	1.50	38.1	.813	20.7	23	4.1	.75	19	18	78	.42	10.5	0.081	2.1	5.13	SST	CG	N
0.975	24.77	72382	1.50	38.1	.805	20.4	32	5.6	.94	24	30	134	.45	11.3	0.085	2.2	5.25	MW	CG	N
0.975	24.77	72382S	1.50	38.1	.805	20.4	27	4.8	.74	19	20	90	.45	11.3	0.085	2.2	5.25	SST	CG	N
0.975	24.77	72397	1.50	38.1	.791	20.1	38	6.6	.95	24	36	159	.55	14.0	0.092	2.3	6.00	MW	CG	N
0.975	24.77	72397S	1.50	38.1	.791	20.1	32	5.6	.76	19	24	108	.55	14.0	0.092	2.3	6.00	SST	CG	N
0.975	24.77	72406	1.50	38.1	.783	19.9	46	8.0	.91	23	42	185	.56	14.3	0.096	2.4	5.88	MW	CG	N
0.975	24.77	72406S	1.50	38.1	.783	19.9	39	6.8	.71	18	28	123	.56	14.3	0.095	2.4	5.88	SST	CG	N
0.975	24.77	72418	1.50	38.1	.765	19.4	65	11	.83	21	54	241	.63	16.0	0.105	2.7	6.00	MW	CG	N
0.975	24.77	72418S	1.50	38.1	.765	19.4	56	9.7	.65	16	36	160	.63	16.0	0.105	2.7	6.00	SST	CG	N
0.975	24.77	72431	1.50	38.1	.751	19.1	82	14	.77	20	63	281	.70	17.8	0.112	2.8	6.25	MW	CG	N
0.975	24.77	72431S	1.50	38.1	.751	19.1	70	12	.59	15	41	184	.70	17.8	0.112	2.8	6.25	SST	CG	N
0.975	24.77	72447	1.50	38.1	.735	18.7	114	20	.68	17	77	344	.75	19.1	0.120	3.0	6.25	MW	CG	N
0.975	24.77	72447S	1.50	38.1	.735	18.7	97	17	.52	13	51	225	.75	19.1	0.120	3.0	6.25	SST	CG	N
0.975	24.77	72458	1.50	38.1	.725	18.4	131	23	.66	17	87	388	.80	20.2	0.125	3.2	6.38	MW	CG	N
0.975	24.77	72458S	1.50	38.1	.725	18.4	112	20	.51	13	57	253	.80	20.2	0.125	3.2	6.38	SST	CG	N
0.975	24.77	72469	1.50	38.1	.705	17.9	177	31	.60	15	106	473	.88	22.3	0.135	3.4	6.50	MW	CG	N
0.975	24.77	72469S	1.50	38.1	.705	17.9	150	26	.45	12	68	304	.88	22.3	0.135	3.4	6.50	SST	CG	N
0.975	24.77	72476	1.50	38.1	.679	17.2	268	47	.52	13	139	617	.96	24.4	0.148	3.8	6.50	MW	CG	N
0.975	24.77	72476S	1.50	38.1	.679	17.2	228	40	.39	9.9	89	397	.96	24.4	0.148	3.8	6.50	SST	CG	N
0.975	24.77	72482	1.50	38.1	.651	16.5	415	73	.42	11	176	782	1.05	26.7	0.162	4.1	6.50	MW	CG	N
0.975	24.77	72482S	1.50	38.1	.651	16.5	353	62	.32	8.0	111	496	1.05	26.7	0.162	4.1	6.50	SST	CG	N
0.975	24.77	72331	1.75	44.5	.849	21.6	9.9	1.7	1.3	34	13	58	.32	8.0	0.063	1.6	5.00	MW	CG	N
0.975	24.77	72331S	1.75	44.5	.849	21.6	8.4	1.5	1.1	27	8.8	39	.32	8.0	0.063	1.6	5.00	SST	CG	N
0.975	24.77	72343	1.75	44.5	.831	21.1	15	2.6	1.2	32	18	82	.40	10.1	0.072	1.8	5.50	MW	CG	N
0.975	24.77	72343S	1.75	44.5	.831	21.1	13	2.2	.98	25	12	55	.40	10.1	0.072	1.8	5.50	SST	CG	N
0.975	24.77	72357	1.75	44.5	.827	21.0	16	2.7	1.3	33	20	89	.43	10.8	0.074	1.9	5.75	MW	CG	N
0.975	24.77	72357S	1.75	44.5	.827	21.0	13	2.3	1.0	26	13	60	.43	10.8	0.074	1.9	5.75	SST	CG	N
0.975	24.77	72371	1.75	44.5	.813	20.7	23	4.1	1.1	29	26	117	.47	11.8	0.081	2.1	5.75	MW	CG	N
0.975	24.77	72371S	1.75	44.5	.813	20.7	20	3.5	.89	23	18	78	.47	11.8	0.081	2.1	5.75	SST	CG	N
0.975	24.77	72383	1.75	44.5	.805	20.4	30	5.3	1.0	25	30	134	.47	11.9	0.085	2.2	5.50	MW	CG	N
0.975	24.77	72383S	1.75	44.5	.805	20.4	26	4.5	.79	20	20	90	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.975	24.77	72384	1.75	44.5	.805	20.4	25	4.3	1.2	31	30	134	.53	13.5	0.085	2.2	6.25	MW	CG	N
0.975	24.77	72384S	1.75	44.5	.805	20.4	21	3.7	.96	24	20	90	.53	13.5	0.085	2.2	6.25	SST	CG	N
0.975	24.77	72407	1.75	44.5	.783	19.9	40	7.0	1.0	27	42	185	.62	15.8	0.096	2.4	6.50	MW	CG	N
0.975	24.77	72407S	1.75	44.5	.783	19.9	34	5.9	.82	21	28	123	.62	15.8	0.096	2.4	6.50	SST	CG	N
0.975	24.77	72419	1.75	44.5	.765	19.4	54	9.5	1.0	25	54	241	.72	18.3	0.105	2.7	6.88	MW	CG	N
0.975	24.77	72419S	1.75	44.5	.765	19.4	46	8.1	.78	20	36	160	.72	18.3	0.105	2.7	6.88	SST	CG	N
0.975	24.77	72432	1.75	44.5	.751	19.1	71	12	.89	23	63	281	.78	19.9	0.112	2.8	7.00	MW	CG	N
0.975	24.77	72432S	1.75	44.5	.751	19.1	60	11	.68	17	41	184	.78	19.9	0.112	2.8	7.00	SST	CG	N
0.975	24.77	72440	1.75	44.5	.745	18.9	78	14	.88	22	68	304	.82	20.8	0.115	2.9	7.13	MW	CG	N
0.975	24.77	72440S	1.75	44.5	.745	18.9	66	12	.67	17	45	199	.82	20.8	0.115	2.9	7.13	SST	CG	N
0.975																				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72441S	2.00	50.8	.745	18.9	58	10	.77	20	45	199	.91	23.0	0.115	2.9	7.88	SST	CG	N
0.975	24.77	72449	2.00	50.8	.735	18.7	82	14	.94	24	77	344	.95	24.0	0.120	3.0	7.88	MW	CG	N
0.975	24.77	72449S	2.00	50.8	.735	18.7	70	12	.73	18	51	225	.95	24.0	0.120	3.0	7.88	SST	CG	N
0.975	24.77	72460	2.00	50.8	.725	18.4	94	16	.93	24	87	388	1.02	25.8	0.125	3.2	8.13	MW	CG	N
0.975	24.77	72460S	2.00	50.8	.725	18.4	80	14	.71	18	57	253	1.02	25.8	0.125	3.2	8.13	SST	CG	N
0.975	24.77	72470	2.00	50.8	.705	17.9	126	22	.85	21	106	473	1.13	28.7	0.135	3.4	8.38	MW	CG	N
0.975	24.77	72470S	2.00	50.8	.705	17.9	107	19	.64	16	68	304	1.13	28.7	0.135	3.4	8.38	SST	CG	N
0.975	24.77	72477	2.00	50.8	.679	17.2	190	33	.73	19	139	617	1.24	31.5	0.148	3.8	8.38	MW	CG	N
0.975	24.77	72477S	2.00	50.8	.679	17.2	161	28	.55	14	89	397	1.24	31.5	0.148	3.8	8.38	SST	CG	N
0.975	24.77	72483	2.00	50.8	.651	16.5	291	51	.60	15	176	782	1.36	34.5	0.162	4.1	8.38	MW	CG	N
0.975	24.77	72483S	2.00	50.8	.651	16.5	248	43	.45	11	111	496	1.36	34.5	0.162	4.1	8.38	SST	CG	N
0.975	24.77	72333	2.25	57.2	.849	21.6	7.5	1.3	1.7	44	13	58	.38	9.6	0.063	1.6	6.00	MW	CG	N
0.975	24.77	72333S	2.25	57.2	.849	21.6	6.4	1.1	1.4	35	8.8	39	.38	9.6	0.063	1.6	6.00	SST	CG	N
0.975	24.77	72345	2.25	57.2	.831	21.1	11	2.0	1.6	41	18	82	.48	12.1	0.072	1.8	6.63	MW	CG	N
0.975	24.77	72345S	2.25	57.2	.831	21.1	9.7	1.7	1.3	33	12	55	.48	12.1	0.072	1.8	6.63	SST	CG	N
0.975	24.77	72360	2.25	57.2	.827	21.0	12	2.1	1.7	43	20	89	.52	13.2	0.074	1.9	7.00	MW	CG	N
0.975	24.77	72360S	2.25	57.2	.827	21.0	10	1.8	1.3	34	13	60	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.975	24.77	72373	2.25	57.2	.813	20.7	18	3.1	1.5	38	26	117	.56	14.1	0.081	2.1	6.88	MW	CG	N
0.975	24.77	72373S	2.25	57.2	.813	20.7	15	2.6	1.2	30	18	78	.56	14.1	0.081	2.1	6.88	SST	CG	N
0.975	24.77	72386	2.25	57.2	.805	20.4	23	4.0	1.3	33	30	134	.56	14.3	0.085	2.2	6.63	MW	CG	N
0.975	24.77	72386S	2.25	57.2	.805	20.4	19	3.4	1.0	26	20	90	.56	14.3	0.085	2.2	6.63	SST	CG	N
0.975	24.77	72387	2.25	57.2	.805	20.4	19	3.3	1.6	41	30	134	.65	16.5	0.085	2.2	7.63	MW	CG	N
0.975	24.77	72387S	2.25	57.2	.805	20.4	16	2.8	1.3	32	20	90	.65	16.5	0.085	2.2	7.63	SST	CG	N
0.975	24.77	72409	2.25	57.2	.783	19.9	30	5.3	1.4	35	42	185	.77	19.5	0.096	2.4	8.00	MW	CG	N
0.975	24.77	72409S	2.25	57.2	.783	19.9	26	4.5	1.1	27	28	123	.77	19.5	0.096	2.4	8.00	SST	CG	N
0.975	24.77	72421	2.25	57.2	.765	19.4	41	7.2	1.3	33	54	241	.89	22.7	0.105	2.7	8.50	MW	CG	N
0.975	24.77	72421S	2.25	57.2	.765	19.4	35	6.1	1.0	26	36	160	.89	22.7	0.105	2.7	8.50	SST	CG	N
0.975	24.77	72434	2.25	57.2	.751	19.1	54	9.5	1.2	30	63	281	.95	24.2	0.112	2.8	8.50	MW	CG	N
0.975	24.77	72434S	2.25	57.2	.751	19.1	46	8.0	.90	23	41	184	.95	24.2	0.112	2.8	8.50	SST	CG	N
0.975	24.77	72442	2.25	57.2	.745	18.9	59	10	1.2	29	68	304	1.01	25.6	0.115	2.9	8.75	MW	CG	N
0.975	24.77	72442S	2.25	57.2	.745	18.9	50	8.8	.89	23	45	199	1.01	25.6	0.115	2.9	8.75	SST	CG	N
0.975	24.77	72450	2.25	57.2	.735	18.7	71	12	1.1	28	77	344	1.05	26.7	0.120	3.0	8.75	MW	CG	N
0.975	24.77	72450S	2.25	57.2	.735	18.7	60	11	.84	21	51	225	1.05	26.7	0.120	3.0	8.75	SST	CG	N
0.975	24.77	72461	2.25	57.2	.725	18.4	82	14	1.1	27	87	388	1.13	28.6	0.125	3.2	9.00	MW	CG	N
0.975	24.77	72461S	2.25	57.2	.725	18.4	70	12	.82	21	57	253	1.13	28.6	0.125	3.2	9.00	SST	CG	N
0.975	24.77	72334	2.50	63.5	.849	21.6	6.7	1.2	1.9	49	13	58	.40	10.2	0.063	1.6	6.38	MW	CG	N
0.975	24.77	72334S	2.50	63.5	.849	21.6	5.7	1.0	1.5	39	8.8	39	.40	10.2	0.063	1.6	6.38	SST	CG	N
0.975	24.77	72346	2.50	63.5	.831	21.1	10	1.8	1.8	46	18	82	.51	13.0	0.072	1.8	7.13	MW	CG	N
0.975	24.77	72346S	2.50	63.5	.831	21.1	8.6	1.5	1.4	36	12	55	.51	13.0	0.072	1.8	7.13	SST	CG	N
0.975	24.77	72361	2.50	63.5	.827	21.0	10	1.8	1.9	49	20	87	.57	14.6	0.074	1.9	7.75	MW	CG	N
0.975	24.77	72361S	2.50	63.5	.827	21.0	8.7	1.5	1.6	39	13	60	.57	14.6	0.074	1.9	7.75	SST	CG	N
0.975	24.77	72374	2.50	63.5	.813	20.7	16	2.8	1.7	42	26	117	.61	15.4	0.081	2.1	7.50	MW	CG	N
0.975	24.77	72374S	2.50	63.5	.813	20.7	13	2.4	1.3	33	18	78	.61	15.4	0.081	2.1	7.50	SST	CG	N
0.975	24.77	72388	2.50	63.5	.805	20.4	18	3.2	1.6	42	30	134	.66	16.7	0.085	2.2	7.75	MW	CG	N
0.975	24.77	72388S	2.50	63.5	.805	20.4	16	2.7	1.3	33	20	90	.66	16.7	0.085	2.2	7.75	SST	CG	N
0.975	24.77	72399	2.50	63.5	.791	20.1	22	3.8	1.7	42	36	160	.83	21.0	0.092	2.3	9.00	MW	CG	N
0.975	24.77	72399S	2.50	63.5	.791	20.1	18	3.2	1.3	34	24	108	.83	21.0	0.092	2.3	9.00	SST	CG	N
0.975	24.77	72410	2.50	63.5	.783	19.9	26	4.5	1.6	41	42	185	.85	21.6	0.096	2.4	8.88	MW	CG	N
0.975	24.77	72410S	2.50	63.5	.783	19.9	22	3.9	1.2	32	28	123	.85	21.6	0.096	2.4	8.88	SST	CG	N
0.975	24.77	72422	2.50	63.5	.765	19.4	36	6.4	1.5	38	54	241	.97	24.7	0.105	2.7	9.25	MW	CG	N
0.975	24.77	72422S	2.50	63.5	.765	19.4	31	5.4	1.2	29	36	160	.97	24.7	0.105	2.7	9.25	SST	CG	N
0.975	24.77	72435	2.50	63.5	.751	19.1	46	8.0	1.4	35	63	281	1.08	27.4	0.112	2.8	9.63	MW	CG	N
0.975	24.77	72435S	2.50	63.5	.751	19.1	39	6.8	1.1	27	41	184	1.08	27.4	0.112	2.8	9.63	SST	CG	N
0.975	24.77	72443	2.50	63.5	.745	18.9	52	9.1	1.3	33	68	304	1.11	28.1	0.115	2.9	9.63	MW	CG	N
0.975	24.77	72443S	2.50	63.5	.745	18.9	44	7.7	1.0	26	45	199	1.11	28.1	0.115	2.9	9.63	SST	CG	N
0.975	24.77	72451	2.50	63.5	.735	18.7	64	11	1.2	31	77	344	1.14	29.0	0.120	3.0	9.50	MW	CG	N
0.975	24.77	72451S	2.50	63.																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72423S	2.75	69.9	.765	19.4	28	4.9	1.3	33	36	160	1.06	27.0	0.105	2.7	10.1	SST	CG	N
0.975	24.77	72436	2.75	69.9	.751	19.1	43	7.5	1.5	37	63	281	1.13	28.8	0.112	2.8	10.1	MW	CG	N
0.975	24.77	72436S	2.75	69.9	.751	19.1	37	6.4	1.1	29	41	184	1.13	28.8	0.112	2.8	10.1	SST	CG	N
0.975	24.77	72463	2.75	69.9	.725	18.4	62	11	1.3	34	84	372	1.41	35.7	0.125	3.2	11.3	MW	CG	N
0.975	24.77	72463S	2.75	69.9	.725	18.4	53	9.3	1.1	27	57	253	1.41	35.7	0.125	3.2	11.3	SST	CG	N
0.975	24.77	72336	3.00	76.2	.849	21.6	5.6	.97	2.3	59	13	58	.46	11.8	0.063	1.6	7.38	MW	CG	N
0.975	24.77	72336S	3.00	76.2	.849	21.6	4.7	.83	1.9	47	8.8	39	.46	11.8	0.063	1.6	7.38	SST	CG	N
0.975	24.77	72348	3.00	76.2	.831	21.1	8.4	1.5	2.2	56	18	82	.59	15.1	0.072	1.8	8.25	MW	CG	N
0.975	24.77	72348S	3.00	76.2	.831	21.1	7.1	1.2	1.7	44	12	55	.59	15.1	0.072	1.8	8.25	SST	CG	N
0.975	24.77	72364	3.00	76.2	.827	21.0	8.4	1.5	2.3	59	20	87	.67	16.9	0.074	1.9	9.00	MW	CG	N
0.975	24.77	72364S	3.00	76.2	.827	21.0	7.1	1.3	1.9	48	13	60	.67	16.9	0.074	1.9	9.00	SST	CG	N
0.975	24.77	72376	3.00	76.2	.813	20.7	13	2.3	2.0	51	26	117	.70	17.7	0.081	2.1	8.63	MW	CG	N
0.975	24.77	72376S	3.00	76.2	.813	20.7	11	1.9	1.6	40	18	78	.70	17.7	0.081	2.1	8.63	SST	CG	N
0.975	24.77	72391	3.00	76.2	.805	20.4	15	2.6	2.0	51	30	134	.77	19.4	0.085	2.2	9.00	MW	CG	N
0.975	24.77	72391S	3.00	76.2	.805	20.4	13	2.3	1.6	40	20	90	.77	19.4	0.085	2.2	9.00	SST	CG	N
0.975	24.77	72400	3.00	76.2	.791	20.1	18	3.1	2.0	52	36	160	.97	24.5	0.092	2.3	10.5	MW	CG	N
0.975	24.77	72400S	3.00	76.2	.791	20.1	15	2.6	1.6	41	24	108	.97	24.5	0.092	2.3	10.5	SST	CG	N
0.975	24.77	72412	3.00	76.2	.783	19.9	21	3.7	1.9	49	42	185	1.00	25.3	0.096	2.4	10.4	MW	CG	N
0.975	24.77	72412S	3.00	76.2	.783	19.9	18	3.2	1.5	39	28	123	1.00	25.3	0.096	2.4	10.4	SST	CG	N
0.975	24.77	72424	3.00	76.2	.765	19.4	30	5.2	1.8	46	54	241	1.14	29.0	0.105	2.7	10.9	MW	CG	N
0.975	24.77	72424S	3.00	76.2	.765	19.4	25	4.4	1.4	36	36	160	1.14	29.0	0.105	2.7	10.9	SST	CG	N
0.975	24.77	72437	3.00	76.2	.751	19.1	38	6.6	1.7	43	63	281	1.26	32.0	0.112	2.8	11.3	MW	CG	N
0.975	24.77	72437S	3.00	76.2	.751	19.1	32	5.6	1.3	33	41	184	1.26	32.0	0.112	2.8	11.3	SST	CG	N
0.975	24.77	72444	3.00	76.2	.745	18.9	43	7.5	1.6	40	68	304	1.29	32.9	0.115	2.9	11.3	MW	CG	N
0.975	24.77	72444S	3.00	76.2	.745	18.9	37	6.4	1.2	31	45	199	1.29	32.9	0.115	2.9	11.3	SST	CG	N
0.975	24.77	72452	3.00	76.2	.735	18.7	52	9.1	1.5	38	77	344	1.34	33.9	0.120	3.0	11.1	MW	CG	N
0.975	24.77	72452S	3.00	76.2	.735	18.7	44	7.7	1.1	29	51	225	1.34	33.9	0.120	3.0	11.1	SST	CG	N
0.975	24.77	72464	3.00	76.2	.725	18.4	60	10	1.5	37	87	388	1.45	36.9	0.125	3.2	11.6	MW	CG	N
0.975	24.77	72464S	3.00	76.2	.725	18.4	51	8.9	1.1	29	57	253	1.45	36.9	0.125	3.2	11.6	SST	CG	N
0.975	24.77	72472	3.00	76.2	.705	17.9	80	14	1.3	34	106	473	1.64	41.6	0.135	3.4	12.1	MW	CG	N
0.975	24.77	72472S	3.00	76.2	.705	17.9	68	12	1.0	26	68	304	1.64	41.6	0.135	3.4	12.1	SST	CG	N
0.975	24.77	72479	3.00	76.2	.679	17.2	120	21	1.2	29	139	617	1.81	46.1	0.148	3.8	12.3	MW	CG	N
0.975	24.77	72479S	3.00	76.2	.679	17.2	102	18	.88	22	89	397	1.81	46.1	0.148	3.8	12.3	SST	CG	N
0.975	24.77	72485	3.00	76.2	.651	16.5	183	32	.96	24	176	782	1.96	49.9	0.162	4.1	12.1	MW	CG	N
0.975	24.77	72485S	3.00	76.2	.651	16.5	155	27	.72	18	111	496	1.96	49.9	0.162	4.1	12.1	SST	CG	N
0.975	24.77	72337	3.50	88.9	.849	21.6	4.7	.83	2.7	70	13	58	.52	13.2	0.063	1.6	8.25	MW	CG	N
0.975	24.77	72337S	3.50	88.9	.849	21.6	4.0	.71	2.2	56	8.8	39	.52	13.2	0.063	1.6	8.25	SST	CG	N
0.975	24.77	72349	3.50	88.9	.831	21.1	7.1	1.2	2.6	66	18	82	.68	17.1	0.072	1.8	9.38	MW	CG	N
0.975	24.77	72349S	3.50	88.9	.831	21.1	6.1	1.1	2.0	52	12	55	.68	17.1	0.072	1.8	9.38	SST	CG	N
0.975	24.77	72365	3.50	88.9	.827	21.0	7.1	1.2	2.7	70	19	87	.76	19.3	0.074	1.9	10.3	MW	CG	N
0.975	24.77	72365S	3.50	88.9	.827	21.0	6.0	1.1	2.2	57	13	60	.76	19.3	0.074	1.9	10.3	SST	CG	N
0.975	24.77	72377	3.50	88.9	.813	20.7	11	1.9	2.4	60	26	117	.79	20.1	0.081	2.1	9.75	MW	CG	N
0.975	24.77	72377S	3.50	88.9	.813	20.7	9.4	1.7	1.9	47	18	78	.79	20.1	0.081	2.1	9.75	SST	CG	N
0.975	24.77	72392	3.50	88.9	.805	20.4	13	2.3	2.3	60	30	134	.87	22.1	0.085	2.2	10.3	MW	CG	N
0.975	24.77	72392S	3.50	88.9	.805	20.4	11	1.9	1.9	47	20	90	.87	22.1	0.085	2.2	10.3	SST	CG	N
0.975	24.77	72401	3.50	88.9	.791	20.1	15	2.6	2.4	61	36	160	1.10	28.0	0.092	2.3	12.0	MW	CG	N
0.975	24.77	72401S	3.50	88.9	.791	20.1	13	2.2	1.9	48	24	108	1.10	28.0	0.092	2.3	12.0	SST	CG	N
0.975	24.77	72413	3.50	88.9	.783	19.9	18	3.2	2.3	58	42	185	1.14	29.0	0.096	2.4	11.9	MW	CG	N
0.975	24.77	72413S	3.50	88.9	.783	19.9	15	2.7	1.8	45	28	123	1.14	29.0	0.096	2.4	11.9	SST	CG	N
0.975	24.77	72425	3.50	88.9	.765	19.4	26	4.5	2.1	54	54	241	1.30	33.0	0.105	2.7	12.4	MW	CG	N
0.975	24.77	72425S	3.50</																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72426S	4.00	101.6	.765	19.4	19	3.3	1.9	48	36	160	1.46	37.0	0.105	2.7	13.9	SST	CG	N
0.975	24.77	72439	4.00	101.6	.751	19.1	29	5.0	2.2	56	63	281	1.60	40.5	0.112	2.8	14.3	MW	CG	N
0.975	24.77	72439S	4.00	101.6	.751	19.1	24	4.3	1.7	43	41	184	1.60	40.5	0.112	2.8	14.3	SST	CG	N
0.975	24.77	72446	4.00	101.6	.745	18.9	32	5.6	2.1	54	68	304	1.65	42.0	0.115	2.9	14.4	MW	CG	N
0.975	24.77	72446S	4.00	101.6	.745	18.9	27	4.8	1.6	42	45	199	1.65	42.0	0.115	2.9	14.4	SST	CG	N
0.975	24.77	72454	4.00	101.6	.735	18.7	38	6.7	2.0	52	77	344	1.74	44.2	0.120	3.0	14.5	MW	CG	N
0.975	24.77	72454S	4.00	101.6	.735	18.7	32	5.7	1.6	40	51	225	1.74	44.2	0.120	3.0	14.5	SST	CG	N
0.975	24.77	72466	4.00	101.6	.725	18.4	44	7.7	2.0	51	87	388	1.89	48.0	0.125	3.2	15.1	MW	CG	N
0.975	24.77	72466S	4.00	101.6	.725	18.4	37	6.5	1.5	39	57	253	1.89	48.0	0.125	3.2	15.1	SST	CG	N
0.975	24.77	72474	4.00	101.6	.705	17.9	58	10	1.8	46	106	473	2.14	54.4	0.135	3.4	15.9	MW	CG	N
0.975	24.77	72474S	4.00	101.6	.705	17.9	50	8.7	1.4	35	68	304	2.14	54.4	0.135	3.4	15.9	SST	CG	N
0.975	24.77	72481	4.00	101.6	.679	17.2	87	15	1.6	40	139	617	2.37	60.1	0.148	3.8	16.0	MW	CG	N
0.975	24.77	72481S	4.00	101.6	.679	17.2	74	13	1.2	31	89	397	2.37	60.1	0.148	3.8	16.0	SST	CG	N
0.975	24.77	72487	4.00	101.6	.651	16.5	133	23	1.3	34	176	782	2.57	65.3	0.162	4.1	15.9	MW	CG	N
0.975	24.77	72487S	4.00	101.6	.651	16.5	113	20	.99	25	111	496	2.57	65.3	0.162	4.1	15.9	SST	CG	N
0.984	24.99	3336	.72	18.2	.794	20.2	111	19	.26	6.5	29	127	.33	8.4	0.095	2.4	3.50	SPR	CG	Z
0.984	24.99	2832	.81	20.6	.800	20.3	97	17	.38	9.5	36	162	.41	10.5	0.092	2.3	3.50	MW	C	Z
0.984	24.99	12579	.81	20.6	.794	20.2	111	19	.26	6.5	29	127	.33	8.5	0.095	2.4	3.50	SPR	CG	Z
0.984	24.99	S-3104	.88	22.2	.904	23.0		1.3	.64	16	.81	3.6	.24	6.1	0.040	1.0	5.00	SST	C	N
0.984	24.99	10652	.94	23.8	.824	20.9	29	5.1	.48	12	14	62	.46	11.7	0.080	2.0	4.75	SPR	C	GI
0.984	24.99	1659	1.00	25.4	.860	21.8	11	1.9	.66	17	7.1	32	.34	8.7	0.062	1.6	4.50	SPR	C	Z
0.984	24.99	11942	1.00	25.4	.792	20.1	44	7.6	.42	11	18	82	.58	14.6	0.096	2.4	6.00	SPR	CG	Z
0.984	24.99	2635	1.00	25.4	.690	17.5	763	134	.18	4.5	135	600	.51	13.1	0.147	3.7	3.50	MW	CG	Z
0.984	24.99	3146	1.03	26.2	.894	22.7		2.5	.81	21	2.0	8.9	.22	5.6	0.045	1.1	5.00	SPR	CG	Z
0.984	24.99	1513	1.06	27.0	.914	23.2		1.0	.87	22	.88	3.9	.19	4.9	0.035	0.9	4.50	HD	C	Z
0.984	24.99	B12-24	1.06	27.0	.890	22.6		2.8	.83	21	2.4	10	.24	6.0	0.047	1.2	5.00	SPR	CG	N
0.984	24.99	S-1048	1.19	30.2	.840	21.3	15	2.6	.83	21	12	54	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.984	24.99	322	1.19	30.2	.824	20.9	30	5.2	.60	15	18	80	.45	11.5	0.080	2.0	4.67	SPR	C	GI
0.984	24.99	S-3087	1.25	31.8	.894	22.7		3.1	1.0	26	3.2	14	.23	5.7	0.045	1.1	4.00	SST	C	N
0.984	24.99	3402	1.25	31.8	.656	16.7	539	94	.24	6.1	129	574	.90	22.9	0.164	4.2	5.50	SPR	CG	Z
0.984	24.99	11866	1.31	33.3	.862	21.9	13	2.2	.67	17	8.4	38	.31	7.7	0.061	1.5	4.00	SPR	C	N
0.984	24.99	12041	1.34	34.1	.674	17.1	485	85	.23	5.7	110	488	.78	19.7	0.155	3.9	5.00	SPR	CG	Z
0.984	24.99	S-183	1.41	35.7	.784	19.9	53	9.2	.58	15	31	137	.55	14.0	0.100	2.5	5.50	SST	CG	N
0.984	24.99	S-3084	1.47	37.3	.814	20.7	26	4.5	.78	20	20	89	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.984	24.99	12205	1.50	38.1	.800	20.3	32	5.6	.81	20	26	116	.60	15.2	0.092	2.3	6.50	SPR	CG	Z
0.984	24.99	2599	1.50	38.1	.774	19.7	57	10	.67	17	38	171	.68	17.3	0.105	2.7	6.50	SPR	CG	Z
0.984	24.99	12704	1.63	41.3	.796	20.2	40	7.0	.97	25	38	171	.66	16.7	0.094	2.4	6.00	MW	C	N
0.984	24.99	S-1570	1.72	43.6	.916	23.3		.53	1.5	38	.79	3.5	.23	5.8	0.034	0.9	5.75	SST	C	N
0.984	24.99	10861	1.75	44.5	.914	23.2		.60	1.5	38	.90	4.0	.24	6.0	0.035	0.9	5.75	SST	C	N
0.984	24.99	II-78	1.75	44.5	.704	17.9	153	27	.55	14	84	372	1.12	28.4	0.140	3.6	8.00	SPR	CG	Z
0.984	24.99	S-470	1.78	45.2	.688	17.5	209	37	.42	11	89	394	1.04	26.3	0.148	3.8	7.00	SST	CG	N
0.984	24.99	S-1201	1.81	46.0	.814	20.7		9.0	.79	20	7.1	32	1.02	25.9	0.085	2.2	12.0	SST	CG	N
0.984	24.99	3862	1.88	47.6	.774	19.7	37	6.4	.93	24	34	152	.95	24.0	0.105	2.7	9.00	HD	CG	Z
0.984	24.99	B18-199	2.09	53.2	.784	19.9	31	5.4	1.0	25	31	137	.90	22.9	0.100	2.5	8.00	SST	C	N
0.984	24.99	12427	2.16	54.8	.884	22.5		3.3	1.3	34	4.4	20	.30	7.6	0.050	1.3	5.00	SST	C	N
0.984	24.99	S-1590	2.25	57.2	.906	23.0		.58	1.9	48	1.1	4.9	.35	8.9	0.039	1.0	8.00	SST	C	N
0.984	24.99	10395	2.25	57.2	.834	21.2	15	2.7	.98	25	15	66	.53	13.3	0.075	1.9	6.00	SPR	C	Z
0.984	24.99	11673	2.38	60.3	.686	17.4	187	33	.54	14	100	446	1.27	32.2	0.149	3.8	8.50	SPR	CG	Z
0.984	24.99	M-141	2.47	62.7	.484	12.3	2367	414	.16	4.1	385	1714	2.00	50.8	0.250	6.4	8.00	SPR	CG	Z
0.984	24.99	11752	2.50	63.5	.824	20.9	10	1.7	1.7	43	17	75	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
0.984	24.99	2622	2.72	69.0	.600	15.2	562	98	.34	8.7	193									




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.000	25.40	10164	1.25	31.8	.750	19.1	175	31	.35	8.9	61	271	.63	15.9	0.125	3.2	5.00	SPR	CG	Z
1.000	25.40	10251	1.25	31.8	.750	19.1	190	33	.32	8.1	61	271	.59	15.1	0.125	3.2	4.75	SPR	CG	Z
1.000	25.40	Q-82	1.34	34.1	.814	20.7	29	5.0	.69	18	20	89	.65	16.5	0.093	2.4	7.00	SPR	CG	N
1.000	25.40	S-899	1.38	34.9	.930	23.6	.52	.09	1.1	29	.59	2.6	.25	6.2	0.035	0.9	6.00	SST	C	N
1.000	25.40	00-90	1.38	34.9	.892	22.7	6.3	1.1	.87	22	5.4	24	.27	6.9	0.054	1.4	4.00	SST	CG	N
1.000	25.40	S-53	1.38	34.9	.840	21.3	17	3.0	.91	23	15	68	.47	11.9	0.080	2.0	6.00	SST	CG	N
1.000	25.40	S-1573	1.50	38.1	.892	22.7	3.7	.64	1.2	31	4.4	20	.30	7.5	0.054	1.4	5.50	SST	CG	N
1.000	25.40	2864	1.50	38.1	.790	20.1	54	9.5	.70	18	38	168	.68	17.3	0.105	2.7	6.50	HD	CG	Z
1.000	25.40	10969	1.50	38.1	.646	16.4	595	104	.27	6.8	158	704	1.11	28.2	0.177	4.5	6.25	HD	CG	BO
1.000	25.40	S-75	1.72	43.6	.790	20.1	41	7.2	.85	22	35	156	.76	19.3	0.105	2.7	7.25	SST	CG	N
1.000	25.40	10791	1.75	44.5	.930	23.6	.57	.10	1.5	38	.86	3.8	.24	6.0	0.035	0.9	5.75	SST	C	N
1.000	25.40	12523	1.75	44.5	.884	22.5	4.9	.85	1.4	36	6.8	30	.35	8.8	0.058	1.5	6.00	SPR	CG	Z
1.000	25.40	912	1.75	44.5	.876	22.3	5.7	1.0	1.3	33	7.3	33	.47	11.8	0.062	1.6	6.50	MW	C	Z
1.000	25.40	11812	1.75	44.5	.868	22.0	7.4	1.3	1.3	34	9.8	44	.43	10.9	0.066	1.7	6.50	SPR	CG	Z
1.000	25.40	11751	1.75	44.5	.840	21.3	22	3.8	.82	21	18	78	.44	11.2	0.080	2.0	5.50	SPR	CG	Z
1.000	25.40	11832	1.75	44.5	.790	20.1	41	7.2	.85	22	35	156	.76	19.3	0.105	2.7	7.25	SST	CG	N
1.000	25.40	3935	1.75	44.5	.760	19.3	87	15	.62	16	54	241	.84	21.3	0.120	3.0	7.00	SPR	CG	Z
1.000	25.40	S-3033	1.75	44.5	.704	17.9	194	34	.45	11	87	388	1.04	26.3	0.148	3.8	7.00	SST	CG	N
1.000	25.40	12260	1.78	45.2	.840	21.3	15	2.6	1.1	29	17	77	.64	16.3	0.080	2.0	7.00	SPR	C	Z
1.000	25.40	S-3195	1.88	47.6	.798	20.3	52	9.1	.60	15	31	139	.56	14.1	0.101	2.6	5.50	SST	CG	N
1.000	25.40	10561	1.94	49.2	.818	20.8	22	3.8	1.1	27	23	102	.67	16.9	0.091	2.3	7.33	SST	CG	N
1.000	25.40	S-1485	2.00	50.8	.918	23.3	1.3	.23	1.8	45	2.3	10	.25	6.2	0.041	1.0	5.00	SST	C	N
1.000	25.40	S-3021	2.00	50.8	.876	22.3	3.7	.65	1.5	38	5.6	25	.50	12.6	0.062	1.6	8.00	SST	CG	N
1.000	25.40	2767	2.00	50.8	.840	21.3	14	2.5	1.2	32	18	78	.59	14.9	0.080	2.0	7.33	HD	CG	Z
1.000	25.40	10091	2.00	50.8	.818	20.8	26	4.6	.94	24	25	110	.73	18.5	0.091	2.3	7.00	SPR	C	Z
1.000	25.40	1771	2.00	50.8	.760	19.3	109	19	.69	18	76	336	.84	21.3	0.120	3.0	6.00	MW	C	Z
1.000	25.40	10321	2.03	51.6	.774	19.7	75	13	.61	15	45	202	.73	18.7	0.113	2.9	6.50	SPR	CG	Z
1.000	25.40	10006	2.09	53.2	.676	17.2	240	42	.51	13	123	546	1.46	37.0	0.162	4.1	9.00	SPR	CG	Z
1.000	25.40	S-3226	2.13	54.0	.816	20.7	17	3.1	1.2	31	21	93	.92	23.4	0.092	2.3	9.00	SST	C	N
1.000	25.40	B17-189	2.13	54.0	.540	13.7	1469	257	.29	7.2	419	1862	1.84	46.7	0.230	5.8	8.00	MW	CG	Z
1.000	25.40	2662	2.16	54.8	.730	18.5	148	26	.50	13	74	330	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
1.000	25.40	S-395	2.19	55.6	.898	22.8	3.3	.58	1.4	35	4.6	20	.31	7.8	0.051	1.3	5.00	SST	C	N
1.000	25.40	S-1386	2.19	55.6	.892	22.7	3.1	.55	1.7	44	5.4	24	.38	9.6	0.054	1.4	6.00	SST	C	N
1.000	25.40	S-3056	2.25	57.2	.910	23.1	1.2	.21	1.9	48	2.2	9.9	.36	9.1	0.045	1.1	7.00	SST	C	N
1.000	25.40	S-1147	2.25	57.2	.876	22.3	4.7	.83	1.7	44	8.2	36	.42	10.6	0.062	1.6	6.75	SST	CG	N
1.000	25.40	11391	2.25	57.2	.860	21.8	6.1	1.1	1.6	39	9.5	42	.70	17.8	0.070	1.8	9.00	SPR	C	Z
1.000	25.40	FF-79	2.25	57.2	.820	20.8	16	2.7	1.4	34	21	94	.90	22.9	0.090	2.3	10.0	SPR	CG	N
1.000	25.40	S-106	2.25	57.2	.706	17.9	171	30	.50	13	86	381	1.10	28.0	0.147	3.7	7.50	SST	CG	N
1.000	25.40	11912	2.28	57.9	.878	22.3	4.3	.75	1.8	47	7.8	35	.43	10.8	0.061	1.5	7.00	SST	CG	N
1.000	25.40	10697	2.31	58.7	.814	20.7	18	3.1	1.3	32	22	99	1.04	26.5	0.093	2.4	10.5	SPR	C	N
1.000	25.40	S-293	2.38	60.3	.790	20.1	30	5.3	1.2	29	35	156	.95	24.0	0.105	2.7	9.00	SST	CG	N
1.000	25.40	4141	2.38	60.3	.760	19.3	58	10	.93	24	54	241	1.26	32.0	0.120	3.0	9.50	SPR	C	Z
1.000	25.40	DD-67	2.50	63.5	.860	21.8	5.4	.94	1.8	46	9.7	43	.70	17.8	0.070	1.8	10.0	SPR	CG	Z
1.000	25.40	B17-184	2.50	63.5	.800	20.3	28	4.9	1.6	41	45	200	.90	22.9	0.100	2.5	9.00	MW	CG	GI
1.000	25.40	375	2.50	63.5	.790	20.1	35	6.1	1.1	28	38	168	1.05	26.7	0.105	2.7	9.00	HD	C	Z
1.000	25.40	71	2.50	63.5	.760	19.3	55	9.6	.99	25	54	241	1.20	30.5	0.120	3.0	10.0	HD	CG	Z
1.000	25.40	S-408	2.59	65.9	.676	17.2	260	45	.42	11	109	485	1.26	31.9	0.162	4.1	7.75	SST	CG	N
1.000	25.40	4311	2.63	66.7	.704	17.9	131	23	.74	19	97	431	1.55	39.5	0.148	3.8	10.5	SPR	CG	Z
1.000	25.40	10964	2.72	69.0	.750	19.1	62	11	.87	22	53	238	1.85	47.0	0.125	3.2	10.5	HD	CG	Z
1.000	25.40	2587	2.75	69.9	.866	22.0	5.9	1.0	1.8	47	11	49	.54	13.6	0.067	1.7	8.00	HD	CG	Z
1.000	25.40	12477	2.75	69.9	.840	21.3	9.5	1.7	1.9	47	18	78	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
1.000	25.40	4207	2.88	73.0	.816	20.7														




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.000	25.40	7001	4.50	114.3	.760	19.3	25	4.4	2.1	53	53	234	2.40	61.0	0.120	3.0	19.5	HD	C	Z
1.000	25.40	656	4.50	114.3	.646	16.4	153	27	1.0	26	158	704	3.27	83.2	0.177	4.5	18.5	HD	CG	Z
1.000	25.40	1949	4.69	119.0	.704	17.9	74	13	1.3	33	97	431	2.52	63.9	0.148	3.8	17.0	SPR	CG	Z
1.000	25.40	4365	4.75	120.7	.840	21.3	6.0	1.1	2.9	74	18	78	1.16	29.5	0.080	2.0	14.5	SPR	CG	Z
1.000	25.40	3062	4.81	122.2	.818	20.8	12	2.1	2.1	52	25	110	1.17	29.8	0.091	2.3	13.0	SPR	CG	Z
1.000	25.40	10115	4.88	123.8	.676	17.2	120	21	1.0	26	123	546	2.59	65.8	0.162	4.1	16.0	SPR	CG	N
1.000	25.40	333	5.00	127.0	.646	16.4	137	24	1.2	29	158	704	3.63	92.2	0.177	4.5	20.5	HD	CG	Z
1.000	25.40	S-3106	5.13	130.2	.840	21.3	4.7	.82	3.5	89	17	73	1.28	32.5	0.080	2.0	16.0	SST	CG	N
1.000	25.40	S-270	5.13	130.2	.820	20.8	7.8	1.4	2.9	73	22	99	1.44	36.6	0.090	2.3	16.0	SST	CG	N
1.000	25.40	2605	5.25	133.4	.790	20.1	15	2.7	2.5	63	38	168	2.00	50.7	0.105	2.7	18.0	SPR	C	Z
1.000	25.40	12150	5.50	139.7	.700	17.8	54	9.4	1.8	46	98	437	3.60	91.4	0.150	3.8	24.0	SPR	CG	Z
1.000	25.40	848	6.00	152.4	.676	17.2	74	13	1.7	42	123	546	4.00	101.5	0.162	4.1	24.7	HD	CG	Z
1.000	25.40	11617	6.50	165.1	.814	20.7	8.0	1.4	3.3	84	26	118	1.95	49.6	0.093	2.4	20.0	SPR	CG	Z
1.000	25.40	2880	6.88	174.6	.706	17.9	49	8.6	1.9	49	95	423	3.53	89.6	0.147	3.7	24.0	SPR	CG	Z
1.000	25.40	S-1251	7.25	184.2	.818	20.8	8.2	1.4	2.8	72	23	102	1.46	37.0	0.091	2.3	16.0	SST	CG	N
1.000	25.40	12115	7.50	190.5	.660	16.8	66	11	1.7	44	113	502	5.78	146.8	0.170	4.3	34.0	SPR	CG	Z
1.000	25.40	S-121	8.00	203.2	.930	23.6	.15	.03	7.4	188	1.1	4.9	.60	15.1	0.035	0.9	16.0	SST	C	N
1.000	25.40	884	8.00	203.2	.818	20.8	5.6	.98	4.4	113	25	110	2.41	61.3	0.091	2.3	25.5	HD	C	Z
1.000	25.40	873	8.00	203.2	.790	20.1	9.3	1.6	4.1	103	38	168	2.97	75.3	0.105	2.7	28.3	HD	CG	Z
1.000	25.40	866	8.00	203.2	.760	19.3	15	2.7	3.5	90	54	241	3.78	96.0	0.120	3.0	30.5	HD	C	Z
1.000	25.40	856	8.00	203.2	.730	18.5	25	4.3	3.0	77	74	330	4.32	109.7	0.135	3.4	32.0	HD	CG	Z
1.000	25.40	S-464	8.00	203.2	.730	18.5	21	3.7	3.1	79	67	297	4.32	109.7	0.135	3.4	32.0	SST	CG	N
1.000	25.40	819	8.00	203.2	.704	17.9	37	6.4	2.7	67	97	431	4.81	122.2	0.148	3.8	32.5	HD	CG	Z
1.000	25.40	360	8.00	203.2	.586	14.9	183	32	1.3	33	235	1047	6.42	163.0	0.207	5.3	31.0	HD	CG	Z
1.000	25.40	10175	8.50	215.9	.646	16.4	114	20	1.4	35	158	704	4.29	109.0	0.177	4.5	24.3	SPR	CG	Z
1.000	25.40	2962	9.00	228.6	.790	20.1	8.3	1.5	4.5	115	38	168	3.39	86.0	0.105	2.7	31.3	SPR	C	Z
1.000	25.40	910	10.0	254.0	.790	20.1	7.0	1.2	5.4	138	38	168	3.99	101.3	0.105	2.7	37.0	HD	C	Z
1.000	25.40	11576	11.0	279.4	.828	21.0	3.5	.61	6.3	160	22	97	2.82	71.5	0.086	2.2	31.8	SPR	C	N
1.000	25.40	901	12.0	304.8	.856	21.7	1.8	.32	7.1	181	13	57	2.14	54.4	0.072	1.8	28.8	HD	C	Z
1.000	25.40	298	12.0	304.8	.840	21.3	2.4	.41	7.5	190	18	78	2.80	71.1	0.080	2.0	34.0	HD	C	Z
1.000	25.40	341	12.0	304.8	.616	15.6	99	17	1.9	49	190	847	7.58	192.6	0.192	4.9	39.5	HD	CG	Z
1.000	25.40	3069	16.8	425.5	.704	17.9	20	3.5	4.8	123	97	431	8.55	217.1	0.148	3.8	57.8	SPR	CG	GI
1.010	25.65	72489	1.00	25.4	.786	20.0	105	18	.44	11	46	206	.56	14.2	0.112	2.8	5.00	MW	CG	N
1.010	25.65	72489S	1.00	25.4	.786	20.0	90	16	.44	11	39	175	.56	14.2	0.112	2.8	5.00	SST	CG	N
1.010	25.65	72491	1.50	38.1	.786	20.0	64	11	.73	19	47	208	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.010	25.65	72491S	1.50	38.1	.786	20.0	54	9.5	.73	19	40	177	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.010	25.65	72493	2.00	50.8	.786	20.0	46	8.1	1.0	26	47	209	.98	24.9	0.112	2.8	8.75	MW	CG	N
1.010	25.65	72493S	2.00	50.8	.786	20.0	39	6.8	1.0	26	40	177	.98	24.9	0.112	2.8	8.75	SST	CG	N
1.010	25.65	72495	2.50	63.5	.786	20.0	36	6.3	1.3	33	47	207	1.20	30.6	0.112	2.8	10.8	MW	CG	N
1.010	25.65	72495S	2.50	63.5	.786	20.0	31	5.3	1.3	33	40	176	1.20	30.6	0.112	2.8	10.8	SST	CG	N
1.010	25.65	72497	3.00	76.2	.786	20.0	29	5.1	1.6	40	47	207	1.41	35.9	0.112	2.8	12.6	MW	CG	N
1.010	25.65	72497S	3.00	76.2	.786	20.0	25	4.4	1.6	40	40	176	1.41	35.9	0.112	2.8	12.6	SST	CG	N
1.010	25.65	72499	3.50	88.9	.786	20.0	25	4.4	1.9	48	47	208	1.62	41.2	0.112	2.8	14.5	MW	CG	N
1.010	25.65	72499S	3.50	88.9	.786	20.0	21	3.7	1.9	48	40	177	1.62	41.2	0.112	2.8	14.5	SST	CG	N
1.010	25.65	72501	4.00	101.6	.786	20.0	22	3.8	2.2	55	46	207	1.85	46.9	0.112	2.8	16.5	MW	CG	N
1.010	25.65	72501S	4.00	101.6	.786	20.0	18	3.2	2.2	55	40	176	1.85	46.9	0.112	2.8	16.5	SST	CG	N
1.010	25.65	72503	4.50	114.3	.786	20.0	19	3.3	2.4	62	47	207	2.06	52.3	0.112	2.8	18.4	MW	CG	N
1.010	25.65	72503S	4.50	114.3	.786	20.0	16	2.8	2.4	62	40	176	2.06	52.3	0.112	2.8	18.4	SST	CG	N
1.015	25.78	3882	.69	17.4	.775	19.7	416	73	.13	3.3	53	237	.36	9.1	0.120	3.0	3.00	HD	CG	Z
1.015	25.78	S-896	.88	22.2	.829	21.1	40	7.0	.41	10	16	73	.47	11.8	0.093	2.4	5.00	SST	CG	N
1.015	25.78	12136	1																	




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.031	26.19	10107	.81	20.7	.907	23.0	12	2.0	.57	14	6.6	29	.25	6.3	0.062	1.6	4.00	SPR	CG	Z
1.031	26.19	S-3054	.88	22.2	.915	23.2	15	2.7	.43	11	6.5	29	.23	5.9	0.058	1.5	3.00	SST	C	N
1.031	26.19	A10-65	1.03	26.2	.869	22.1	21	3.7	.63	16	13	59	.41	10.3	0.081	2.1	5.00	SST	CG	N
1.031	26.19	2678	1.13	28.6	.849	21.6	40	6.9	.58	15	23	102	.55	13.9	0.091	2.3	5.00	HD	C	Z
1.031	26.19	10852	1.38	34.9	.875	22.2	18	3.2	.82	21	15	66	.39	9.9	0.078	2.0	5.00	SST	CG	N
1.031	26.19	3339	1.44	36.5	.907	23.0	4.9	.86	1.0	26	5.0	22	.42	10.6	0.062	1.6	6.75	HD	CG	GI
1.031	26.19	10740	1.50	38.1	.929	23.6	5.2	.90	.92	23	4.7	21	.20	5.2	0.051	1.3	4.00	SPR	CG	Z
1.031	26.19	S-1417	1.50	38.1	.857	21.8	17	3.0	.80	20	14	61	.70	17.7	0.087	2.2	7.00	SST	C	N
1.031	26.19	10659	1.53	38.9	.741	18.8	244	43	.36	9.3	89	395	.83	21.2	0.145	3.7	5.75	SPR	CG	Z
1.031	26.19	12447	1.56	39.7	.791	20.1	53	9.2	.42	11	22	99	1.14	29.0	0.120	3.0	9.50	SPR	CG	N
1.031	26.19	10409	1.94	49.2	.657	16.7	487	85	.35	9.0	172	766	1.50	38.0	0.187	4.7	8.00	SPR	CG	Z
1.031	26.19	10676	1.97	50.0	.807	20.5	36	6.4	.74	19	27	119	1.23	31.3	0.112	2.8	10.0	SPR	C	Z
1.031	26.19	S-1532	2.00	50.8	.923	23.4	2.8	.50	1.7	43	4.8	21	.32	8.2	0.054	1.4	6.00	SST	CG	N
1.031	26.19	10457	2.19	55.6	.707	18.0	224	39	.53	14	119	531	1.42	36.0	0.162	4.1	8.75	SPR	CG	Z
1.031	26.19	NN-20	2.19	55.6	.571	14.5	1305	228	.23	5.8	297	1321	1.84	46.7	0.230	5.8	8.00	SPR	CG	Z
1.031	26.19	10722	2.28	57.9	.747	19.0	145	25	.58	15	84	372	1.10	28.0	0.142	3.6	7.75	SPR	CG	Z
1.031	26.19	2730	2.34	59.5	.911	23.1	5.1	.89	1.9	49	9.8	44	.42	10.7	0.060	1.5	6.00	MW	C	Z
1.031	26.19	2702	2.47	62.7	.761	19.3	111	19	.91	23	101	449	1.08	27.4	0.135	3.4	8.00	MW	CG	Z
1.031	26.19	2677	2.63	66.7	.871	22.1	12	2.1	1.4	37	17	76	.62	15.7	0.080	2.0	7.75	HD	CG	Z
1.031	26.19	10988	2.81	71.4	.657	16.7	325	57	.53	13	172	766	2.06	52.2	0.187	4.7	11.0	HD	CG	Z
1.031	26.19	S-1473	3.00	76.2	.871	22.1	4.8	.83	1.8	47	8.8	39	1.16	29.5	0.080	2.0	14.5	SST	CG	N
1.031	26.19	3401	3.63	92.1	.917	23.3	1.5	.26	2.8	72	4.2	19	.80	20.3	0.057	1.4	13.0	SPR	C	Z
1.031	26.19	B18-197	3.75	95.3	.959	24.4	.49	.09	3.5	88	1.7	7.5	.29	7.3	0.036	0.9	7.00	SPR	C	Z
1.031	26.19	1631	3.75	95.3	.851	21.6	10	1.7	2.3	59	23	104	1.29	32.8	0.090	2.3	13.3	SPR	C	Z
1.031	26.19	B9-48	3.88	98.4	.637	16.2	325	57	.62	16	200	888	2.66	67.6	0.197	5.0	13.5	SPR	CG	N
1.031	26.19	12004	9.88	250.8	.837	21.3	4.9	.85	6.0	151	29	129	3.30	83.8	0.097	2.5	34.0	SPR	CG	Z
1.046	26.57	1895	.75	19.1	.944	24.0	9.9	1.7	.47	12	4.7	21	.20	5.2	0.051	1.3	3.00	HD	C	Z
1.046	26.57	S-1035	.81	20.6	.806	20.5	154	27	.31	7.8	47	211	.50	12.6	0.120	3.0	4.00	SST	CG	N
1.046	26.57	S-3004	.81	20.6	.806	20.5	163	29	.29	7.4	47	211	.48	12.2	0.120	3.0	4.00	SST	CG	N
1.046	26.57	10973	.94	23.8	.934	23.7	13	2.3	.45	11	5.8	26	.22	5.7	0.056	1.4	3.00	SST	C	N
1.046	26.57	B18-193	1.03	26.2	.866	22.0	36	6.3	.49	12	18	79	.54	13.7	0.090	2.3	5.00	SPR	C	Z
1.046	26.57	A14-56	1.19	30.2	.916	23.3	7.8	1.4	.83	21	6.4	29	.36	9.1	0.065	1.7	5.50	SPR	CG	Z
1.046	26.57	S-1444	1.31	33.3	.864	21.9	33	5.7	.67	17	22	98	.46	11.6	0.091	2.3	5.00	SPR	CG	N
1.046	26.57	3338	1.44	36.5	.916	23.3	5.4	.95	.98	25	5.3	24	.46	11.6	0.065	1.7	7.00	SPR	CG	Z
1.046	26.57	2985	1.47	37.3	.806	20.5	94	16	.55	14	52	231	.72	18.3	0.120	3.0	6.00	SPR	CG	Z
1.046	26.57	S-1199	1.50	38.1	.930	23.6	2.9	.51	1.0	26	3.0	14	.46	11.8	0.058	1.5	7.00	SST	C	N
1.046	26.57	3826	1.50	38.1	.918	23.3	5.1	.89	1.1	27	5.4	24	.45	11.4	0.064	1.6	7.00	SPR	CG	Z
1.046	26.57	12066	1.50	38.1	.808	20.5	90	16	.56	14	51	225	.71	18.1	0.119	3.0	6.00	SPR	CG	Z
1.046	26.57	11561	1.69	42.8	.924	23.5	10	1.8	.76	19	8.0	35	.31	7.7	0.061	1.5	4.00	SPR	C	Z
1.046	26.57	12245	1.72	43.6	.884	22.5	14	2.4	1.2	29	16	71	.57	14.4	0.081	2.1	7.00	SPR	CG	GI
1.046	26.57	S-1496	1.81	46.0	.902	22.9	12	2.1	.96	24	12	52	.36	9.1	0.072	1.8	5.00	SST	CG	N
1.046	26.57	11231	1.91	48.4	.896	22.8	13	2.3	1.1	27	14	62	.51	12.9	0.075	1.9	5.75	SPR	C	Z
1.046	26.57	3213	2.00	50.8	.934	23.7	3.8	.66	1.6	42	6.2	27	.33	8.4	0.056	1.4	6.00	SPR	CG	Z
1.046	26.57	S-350	2.00	50.8	.836	21.2	52	9.1	.64	16	34	149	.58	14.7	0.105	2.7	5.50	SST	CG	N
1.046	26.57	3067	2.00	50.8	.750	19.1	159	28	.59	15	93	414	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.046	26.57	3757	2.25	57.2	.836	21.2	47	8.2	.78	20	36	161	.68	17.3	0.105	2.7	6.50	SPR	CG	Z
1.046	26.57	3009	2.25	57.2	.722	18.3	205	36	.58	15	118	525	1.46	37.0	0.162	4.1	9.00	SPR	CG	Z
1.046	26.57	S-1425	2.63	66.7	.896	22.8	6.9	1.2	1.9	48	13	58	.62	15.7	0.075	1.9	8.25	SST	C	N
1.046	26.57	S-3244	2.66	67.5	.898	22.8	6.6	1.2	1.9	49	13	56	.62	15.7	0.074	1.9	8.33	SST	CG	N
1.046	26.57	2744	3.88	98.4	.922	23.4	1.7	.29												




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.062	26.97	11636	2.25	57.2	.842	21.4	35	6.1	1.1	29	40	176	.99	25.1	0.110	2.8	9.00	SPR	CG	Z
1.062	26.97	CC-44	2.25	57.2	.742	18.8	190	33	.53	13	100	443	1.28	32.5	0.160	4.1	8.00	SST	CG	N
1.062	26.97	12520	2.31	58.7	.812	20.6	71	12	.81	21	58	257	1.13	28.6	0.125	3.2	8.00	SPR	C	N
1.062	26.97	3133	2.38	60.3	.922	23.4	9.4	1.7	1.2	30	11	50	.47	12.0	0.070	1.8	5.75	SPR	C	Z
1.062	26.97	3942	2.50	63.5	.766	19.5	113	20	.81	21	92	408	1.48	37.6	0.148	3.8	10.0	SPR	CG	Z
1.062	26.97	A13-56	2.69	68.2	.916	23.3	4.4	.77	1.9	49	8.5	38	.77	19.5	0.073	1.9	10.5	SST	CG	N
1.062	26.97	S-437	3.38	85.7	.904	23.0	4.7	.83	2.4	60	11	49	1.02	25.8	0.079	2.0	13.0	SST	CG	N
1.062	26.97	S-1326	3.50	88.9	.918	23.3	3.5	.61	2.6	67	9.1	41	.86	21.9	0.072	1.8	12.0	SST	CG	N
1.062	26.97	3272	3.63	92.1	.848	21.5	22	3.8	1.7	44	38	168	1.28	32.6	0.107	2.7	12.0	SPR	CG	Z
1.062	26.97	12436	3.88	98.4	.938	23.8	2.2	.39	3.1	79	6.9	31	.78	19.7	0.062	1.6	11.5	SPR	C	Z
1.062	26.97	S-444	4.63	117.5	.862	21.9	12	2.0	2.5	62	29	128	1.40	35.6	0.100	2.5	14.0	SST	CG	N
1.062	26.97	S-3217	5.00	127.0	.992	25.2	.15	.03	4.5	114	.69	3.1	.51	12.9	0.035	0.9	13.5	SST	C	N
1.062	26.97	4108	5.00	127.0	.822	20.9	27	4.8	1.9	47	51	228	1.92	48.8	0.120	3.0	15.0	SPR	C	Z
1.062	26.97	334	6.00	152.4	.708	18.0	96	17	1.6	40	150	668	4.12	104.5	0.177	4.5	23.3	HD	CG	Z
1.062	26.97	2755	7.25	184.2	.738	18.7	61	11	1.9	49	116	518	3.94	100.1	0.162	4.1	24.3	SPR	CG	Z
1.062	26.97	1936	7.63	193.7	.880	22.4	6.3	1.1	3.7	94	23	104	1.73	43.9	0.091	2.3	19.0	SPR	CG	Z
1.062	26.97	1703	7.63	193.7	.738	18.7	60	10	1.9	49	116	518	4.16	105.6	0.162	4.1	24.7	SPR	C	Z
1.062	26.97	385	11.5	292.1	.852	21.6	12	2.2	2.9	73	36	159	2.00	50.7	0.105	2.7	18.0	HD	C	Z
1.062	26.97	4170	11.5	292.1	.852	21.6	5.7	1.0	6.3	159	36	159	3.99	101.3	0.105	2.7	37.0	SPR	C	Z
1.070	27.18	12804	4.00	101.6	.656	16.7	315	55	.71	18	223	991	3.10	78.7	0.207	5.3	15.0	HD	CG	Z
1.078	27.38	11507	.78	19.8	.934	23.7	19	3.3	.42	11	8.0	36	.36	9.1	0.072	1.8	4.00	SPR	CG	Z
1.078	27.38	12074	1.00	25.4	.918	23.3	30	5.2	.55	14	16	73	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
1.078	27.38	10525	1.00	25.4	.868	22.0	47	8.3	.37	9.4	18	78	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
1.078	27.38	11702	1.13	28.6	.992	25.2	1.3	.22	.89	23	1.1	5.0	.24	6.0	0.043	1.1	5.50	SPR	CG	Z
1.078	27.38	10685	1.13	28.6	.908	23.1	27	4.8	.66	17	18	79	.47	11.9	0.085	2.2	4.50	SST	C	N
1.078	27.38	11728	1.13	28.6	.828	21.0	135	24	.42	11	57	253	.63	15.9	0.125	3.2	5.00	SPR	CG	Z
1.078	27.38	12318	1.19	30.2	.992	25.2	1.3	.22	.91	23	1.2	5.1	.28	7.1	0.043	1.1	5.50	SPR	C	Z
1.078	27.38	11850	1.34	34.1	.922	23.4	12	2.1	.88	22	10	46	.47	11.9	0.078	2.0	6.00	SST	CG	N
1.078	27.38	12307	1.47	37.3	.958	24.3	3.5	.62	.99	25	3.5	16	.48	12.2	0.060	1.5	7.00	SPR	C	Z
1.078	27.38	A13-69	1.47	37.3	.894	22.7	23	4.0	.90	23	21	93	.56	14.3	0.092	2.3	6.13	SST	CG	N
1.078	27.38	12268	1.50	38.1	.966	24.5	3.8	.66	1.2	30	4.5	20	.31	7.8	0.056	1.4	5.50	SPR	CG	Z
1.078	27.38	1908	1.50	38.1	.852	21.6	65	11	.65	16	42	188	.68	17.2	0.113	2.9	6.00	SPR	CG	Z
1.078	27.38	1739	1.63	41.3	.782	19.9	229	40	.55	14	127	564	.85	21.6	0.148	3.8	5.75	MW	CG	Z
1.078	27.38	1741	1.75	44.5	.896	22.8	34	6.0	.68	17	23	103	.55	13.9	0.091	2.3	5.00	HD	C	Z
1.078	27.38	11564	1.81	46.0	.960	24.4	4.7	.82	1.4	36	6.7	30	.38	9.7	0.059	1.5	5.50	SPR	CG	Z
1.078	27.38	S-844	1.88	47.6	.908	23.1	14	2.4	1.3	33	18	78	.58	14.8	0.085	2.2	6.88	SST	CG	N
1.078	27.38	S-356	2.00	50.8	.988	25.1	1.6	.27	1.7	44	2.7	12	.27	6.9	0.045	1.1	5.00	SST	C	N
1.078	27.38	11586	2.00	50.8	.896	22.8	21	3.6	1.1	29	23	103	.73	18.5	0.091	2.3	7.00	SPR	CG	N
1.078	27.38	12156	2.00	50.8	.808	20.5	104	18	.67	17	69	308	1.01	25.7	0.135	3.4	7.50	SPR	CG	Z
1.078	27.38	B11-29	2.00	50.8	.808	20.5	127	22	.55	14	69	308	.88	22.3	0.135	3.4	6.50	SPR	CG	N
1.078	27.38	10992	2.00	50.8	.754	19.2	224	39	.51	13	115	511	1.42	36.0	0.162	4.1	7.75	HD	CG	Z
1.078	27.38	10939	2.06	52.4	.934	23.7	6.3	1.1	1.5	38	9.4	42	.58	14.6	0.072	1.8	8.00	SPR	CG	Z
1.078	27.38	3121	2.13	54.0	.934	23.7	9.5	1.7	1.3	32	12	53	.43	11.0	0.072	1.8	6.00	SPR	CG	Z
1.078	27.38	11870	2.13	54.0	.894	22.7	20	3.4	1.2	31	24	106	.69	17.5	0.092	2.3	7.50	SPR	CG	N
1.078	27.38	11165	2.13	54.0	.782	19.9	202	35	.45	11	91	403	.93	23.5	0.148	3.8	6.25	SPR	CG	Z
1.078	27.38	S-129	2.19	55.6	.932	23.7	8.2	1.4	1.4	36	12	52	.46	11.6	0.073	1.9	6.25	SST	CG	N
1.078	27.38	S-3166	2.25	57.2	.954	24.2	4.1	.73	1.8	47	7.6	34	.39	9.8	0.062	1.6	6.25	SST	CG	N
1.078	27.38	S-1672	2.25	57.2	.898	22.8	14	2.5	1.4	36	21	92	.72	18.3	0.090	2.3	8.00	SST	CG	N
1.078	27.38	B17-132	2.50	63.5	1.026	26.1	.08	.01	2.3	58	.19	.84	.23	5.9	0.026	0.7	8.00	SST	C	N
1.078	27.38	S-422	2.50	63.5	.894	22.7	18	3.1	1.2	32	22	98	.67	16.9	0.092	2.3	7.25	SST	CG	N
1.078	27.38	11827	2.50	63.5	.808	20.5	70	12	.90	23	62	277	1.25	31.7	0.135	3.4	9.25	SST	CG	N
1.078	27.38	10369	2.50	63.5	.796	20.2	138	24	.57	14	79	350	.99	25.1	0.141	3.6	7.00	SPR	CG	Z
1.078	27.38	2649	2.50	63.5	.784	19.9	104	18	.85	22	89	395	1.47	37.3	0.147	3.7	10.0	HD	CG	Z
1.078	27.38	RR-58	2.75	69.9	.998	25.3	.41	.07	2.3	59	.95	4.2	.44	11.2	0.040	1.0	10.0	SPR	C	Z
1.078	27.38	11759	2.84	72.2	.954	24.2	1.6	.27	1.9	47	2.9	13	.99	25.2	0.062	1.6	15.0	SPR	C	Z
1.078	27.38	S-95	3.00	76.2	.578															




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.094	27.79	12111	1.53	38.9	.934	23.7	11	1.9	.93	24	10	46	.60	15.2	0.080	2.0	6.50	SST	C	N
1.094	27.79	3132	1.59	40.5	.894	22.7	33	5.7	.92	23	30	134	.65	16.5	0.100	2.5	6.50	SPR	CG	Z
1.094	27.79	12006	1.59	40.5	.782	19.9	295	52	.34	8.8	102	452	.86	21.8	0.156	4.0	5.50	SPR	CG	Z
1.094	27.79	1671	1.63	41.3	.798	20.3	217	38	.41	10	89	397	.85	21.6	0.148	3.8	5.75	SPR	CG	Z
1.094	27.79	11278	1.69	42.8	.782	19.9	258	45	.39	10	102	452	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
1.094	27.79	10332	1.88	47.6	.810	20.6	159	28	.50	13	79	352	.89	22.6	0.142	3.6	6.25	SPR	CG	Z
1.094	27.79	945	2.00	50.8	.974	24.7	3.7	.66	1.6	39	5.8	26	.45	11.4	0.060	1.5	6.50	MW	C	Z
1.094	27.79	1577	2.00	50.8	.884	22.5	34	5.9	1.0	26	35	154	.77	19.6	0.105	2.7	7.33	SPR	CG	Z
1.094	27.79	3262	2.00	50.8	.824	20.9	98	17	.69	18	68	304	1.01	25.7	0.135	3.4	7.50	HD	CG	Z
1.094	27.79	10325	2.13	54.0	.810	20.6	135	24	.58	15	79	352	.99	25.2	0.142	3.6	7.00	SPR	CG	Z
1.094	27.79	S-1246	2.19	55.6	.950	24.1	7.9	1.4	1.4	36	11	49	.43	11.0	0.072	1.8	6.00	SST	C	N
1.094	27.79	11284	2.19	55.6	.798	20.3	172	30	.52	13	89	397	1.00	25.4	0.148	3.8	6.75	SPR	CG	Z
1.094	27.79	3697	2.25	57.2	1.006	25.6	1.2	.20	1.9	49	2.3	10	.31	7.8	0.044	1.1	6.00	SPR	C	Z
1.094	27.79	11971	2.38	60.3	.914	23.2	14	2.5	1.4	36	20	91	.70	17.7	0.090	2.3	7.75	SST	CG	N
1.094	27.79	11381	2.50	63.5	.944	24.0	7.6	1.3	1.6	42	13	56	.53	13.3	0.075	1.9	7.00	SST	CG	N
1.094	27.79	3309	2.50	63.5	.814	20.7	91	16	.84	21	76	338	1.26	32.0	0.140	3.6	9.00	SPR	CG	Z
1.094	27.79	S-448	2.63	66.7	.872	22.1	32	5.6	1.1	29	36	161	.92	23.3	0.111	2.8	8.25	SST	CG	N
1.094	27.79	10381	2.63	66.7	.868	22.0	31	5.4	1.3	34	42	186	1.13	28.7	0.113	2.9	10.0	SPR	CG	Z
1.094	27.79	3913	2.75	69.9	1.012	25.7	.43	.08	2.3	58	1.0	4.4	.45	11.5	0.041	1.0	10.0	SPR	C	Z
1.094	27.79	S-1439	2.75	69.9	.992	25.2	1.4	.24	2.3	59	3.1	14	.43	11.0	0.051	1.3	7.50	SST	C	N
1.094	27.79	3163	2.75	69.9	.782	19.9	163	29	.62	16	102	452	1.33	33.9	0.156	4.0	8.50	SPR	CG	Z
1.094	27.79	11388	3.41	86.5	.844	21.4	38	6.7	1.3	34	51	228	1.38	34.9	0.125	3.2	11.0	SST	CG	N
1.094	27.79	S-279	3.63	92.1	.912	23.2	6.3	1.1	2.2	56	14	62	1.41	35.8	0.091	2.3	15.5	SST	CG	N
1.094	27.79	3711	4.00	101.6	.984	25.0	1.2	.21	3.3	83	3.9	17	.72	18.2	0.055	1.4	12.0	SPR	C	Z
1.094	27.79	3374	4.00	101.6	.814	20.7	55	9.7	1.4	35	76	338	1.89	48.0	0.140	3.6	13.5	SPR	CG	GI
1.094	27.79	12169	4.06	103.2	.782	19.86	115	20	.88	22.35	101	447	1.72	43.69	0.158	4.0	11.0	SPR	CG	GI
1.094	27.79	10948	4.19	106.4	.854	21.7	26	4.6	1.7	44	45	202	1.56	39.6	0.120	3.0	13.0	SST	CG	N
1.094	27.79	2713	4.75	120.7	.894	22.7	11	1.9	2.8	70	30	134	1.55	39.4	0.100	2.5	15.5	SPR	CG	Z
1.094	27.79	11775	4.91	124.6	.900	22.9	9.7	1.7	2.6	67	25	113	1.33	33.9	0.097	2.5	13.8	SST	CG	N
1.094	27.79	12312	5.00	127.0	.884	22.5	15	2.6	2.3	59	35	154	1.58	40.0	0.105	2.7	14.0	HD	C	Z
1.094	27.79	S-3046	5.13	130.2	.844	21.4	24	4.2	2.1	54	51	228	2.00	50.8	0.125	3.2	16.0	SST	CG	N
1.094	27.79	4130	5.38	136.5	.914	23.2	9.3	1.6	2.4	60	22	98	1.08	27.4	0.090	2.3	12.0	SPR	CG	Z
1.094	27.79	11709	6.00	152.4	.910	23.1	7.9	1.4	3.0	76	24	105	1.38	35.1	0.092	2.3	15.0	SPR	CG	Z
1.094	27.79	3471	7.50	190.5	.766	19.5	57	10	2.0	52	117	522	4.18	106.2	0.164	4.2	24.5	SPR	C	Z
1.094	27.79	1643	7.88	200.0	.884	22.5	7.5	1.3	4.6	117	35	154	2.73	69.3	0.105	2.7	26.0	SPR	CG	Z
1.094	27.79	12180	8.19	207.9	.888	22.6	6.9	1.2	4.7	120	33	146	2.68	68.0	0.103	2.6	26.0	SPR	CG	Z
1.094	27.79	361	11.3	285.8	.740	18.8	46	8.0	3.2	81	146	651	7.43	188.8	0.177	4.5	42.0	HD	CG	Z
1.100	27.94	72504	.88	22.4	.936	23.8	43	7.5	.57	14	24	108	.29	7.3	0.082	2.1	3.50	MW	CG	N
1.100	27.94	72504S	.88	22.4	.936	23.8	36	6.3	.45	11	16	72	.29	7.3	0.082	2.1	3.50	SST	CG	N
1.100	27.94	72514	.88	22.4	.930	23.6	45	7.9	.57	15	26	115	.31	7.8	0.085	2.2	3.63	MW	CG	N
1.100	27.94	72514S	.88	22.4	.930	23.6	38	6.7	.47	12	18	80	.31	7.8	0.085	2.2	3.63	SST	CG	N
1.100	27.94	72527	.88	22.4	.914	23.2	65	11	.52	13	34	150	.34	8.6	0.093	2.4	3.63	MW	CG	N
1.100	27.94	72527S	.88	22.4	.914	23.2	55	9.6	.41	10	22	100	.34	8.6	0.093	2.4	3.63	SST	CG	N
1.100	27.94	72537	.88	22.4	.908	23.1	70	12	.52	13	36	161	.36	9.1	0.096	2.4	3.75	MW	CG	N
1.100	27.94	72537S	.88	22.4	.908	23.1	59	10	.41	11	25	109	.36	9.1	0.096	2.4	3.75	SST	CG	N
1.100	27.94	72549	.88	22.4	.890	22.6	98	17	.47	12	46	206	.41	10.3	0.105	2.7	3.88	MW	CG	N
1.100	27.94	72549S	.88	22.4	.890	22.6	83	15	.39	9.8	32	142	.41	10.3	0.105	2.7	3.88	SST	CG	N
1.100	27.94	72560	.88	22.4	.876	22.3	126	22	.45	11	56	249	.43	11.0	0.112	2.8	3.88	MW	CG	N
1.100	27.94	72560S	.88	22.4	.876	22.3	107	19	.35	8.8	37	164	.43	11.0	0.112	2.8	3.88	SST	CG	N
1.100	27.94	72582	.88	22.4	.850	21.6	194	34	.38	9.7	74	328	.50	12.7	0.125	3.2	4.00	MW	CG	N
1.100	27.94	72582S	.88	22.4	.850	21.6	165	29	.31	7.8	51	227	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.100	27.94	72505	1.00	25.4	.936	23.8	36	6.3	.67	17	24	108	.31	7.8	0.082	2.1	3.75	MW	CG	N
1.100	27.94	72505S	1.00	25.4	.936	23.8	31	5.4	.53	13	16	72	.31	7.8	0.082	2.1	3.75	SST	CG	N
1.100	27.94	72515	1.00	25.4	.930	23.6	38	6.7	.67	17	26	114	.33	8.4	0.085	2.2	3.88	MW	CG	N
1.100	27.94	72515S	1.00	25.4	.930	23.6	33	5.7	.55	14	18	80	.33	8.4	0.085	2.2	3.88	SST	CG	N
1.100	27.94	72528	1.00	25.4	.914	23.2	55	9.6	.62	16	34	150	.36	9.2	0.093	2.4	3.88	MW	CG	N
1.100	27.94																			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72584S	1.25	31.8	.850	21.6	104	18	.49	12	51	227	.64	16.3	0.125	3.2	5.13	SST	CG	N
1.100	27.94	72507	1.50	38.1	.936	23.8	23	4.0	1.1	27	24	108	.39	9.9	0.082	2.1	4.75	MW	CG	N
1.100	27.94	72507S	1.50	38.1	.936	23.8	19	3.4	.84	21	16	72	.39	9.9	0.082	2.1	4.75	SST	CG	N
1.100	27.94	72517	1.50	38.1	.930	23.6	24	4.2	1.1	27	26	114	.43	10.8	0.085	2.2	5.00	MW	CG	N
1.100	27.94	72517S	1.50	38.1	.930	23.6	20	3.6	.89	23	18	80	.43	10.8	0.085	2.2	5.00	SST	CG	N
1.100	27.94	72530	1.50	38.1	.914	23.2	34	6.0	.98	25	34	150	.48	12.1	0.093	2.4	5.13	MW	CG	N
1.100	27.94	72530S	1.50	38.1	.914	23.2	29	5.1	.77	19	22	100	.48	12.1	0.093	2.4	5.13	SST	CG	N
1.100	27.94	72540	1.50	38.1	.908	23.1	37	6.4	1.0	25	36	162	.50	12.8	0.096	2.4	5.25	MW	CG	N
1.100	27.94	72540S	1.50	38.1	.908	23.1	31	5.4	.79	20	25	109	.50	12.8	0.096	2.4	5.25	SST	CG	N
1.100	27.94	72552	1.50	38.1	.890	22.6	50	8.8	.92	23	46	206	.58	14.7	0.105	2.7	5.50	MW	CG	N
1.100	27.94	72552S	1.50	38.1	.890	22.6	43	7.5	.75	19	32	142	.58	14.7	0.105	2.7	5.50	SST	CG	N
1.100	27.94	72563	1.50	38.1	.876	22.3	68	12	.84	21	56	251	.62	15.6	0.112	2.8	5.50	MW	CG	N
1.100	27.94	72563S	1.50	38.1	.876	22.3	57	10	.64	16	37	164	.62	15.6	0.112	2.8	5.50	SST	CG	N
1.100	27.94	72573	1.50	38.1	.860	21.8	93	16	.75	19	69	308	.65	16.4	0.120	3.0	5.38	MW	CG	N
1.100	27.94	72573S	1.50	38.1	.860	21.8	79	14	.57	15	45	201	.65	16.4	0.120	3.0	5.38	SST	CG	N
1.100	27.94	72585	1.50	38.1	.850	21.6	105	18	.74	19	78	347	.70	17.9	0.125	3.2	5.63	MW	CG	N
1.100	27.94	72585S	1.50	38.1	.850	21.6	89	16	.57	15	51	227	.70	17.9	0.125	3.2	5.63	SST	CG	N
1.100	27.94	72594	1.50	38.1	.830	21.1	137	24	.69	18	95	423	.79	20.1	0.135	3.4	5.88	MW	CG	N
1.100	27.94	72594S	1.50	38.1	.830	21.1	116	20	.53	13	61	272	.79	20.1	0.135	3.4	5.88	SST	CG	N
1.100	27.94	72508	1.75	44.5	.936	23.8	19	3.3	1.3	32	24	108	.43	10.9	0.082	2.1	5.25	MW	CG	N
1.100	27.94	72508S	1.75	44.5	.936	23.8	16	2.8	1.0	25	16	72	.43	10.9	0.082	2.1	5.25	SST	CG	N
1.100	27.94	72519	1.75	44.5	.930	23.6	21	3.6	1.3	33	27	119	.47	11.9	0.085	2.2	5.50	MW	CG	N
1.100	27.94	72519S	1.75	44.5	.930	23.6	18	3.1	1.0	26	18	80	.47	11.9	0.085	2.2	5.50	SST	CG	N
1.100	27.94	72531	1.75	44.5	.914	23.2	29	5.1	1.2	30	34	150	.52	13.3	0.093	2.4	5.63	MW	CG	N
1.100	27.94	72531S	1.75	44.5	.914	23.2	25	4.3	.91	23	22	100	.52	13.3	0.093	2.4	5.63	SST	CG	N
1.100	27.94	72542	1.75	44.5	.908	23.1	31	5.3	1.2	30	36	159	.58	14.6	0.096	2.4	6.00	MW	CG	N
1.100	27.94	72542S	1.75	44.5	.908	23.1	26	4.5	.95	24	25	109	.58	14.6	0.096	2.4	6.00	SST	CG	N
1.100	27.94	72553	1.75	44.5	.890	22.6	42	7.4	1.1	28	46	204	.66	16.7	0.105	2.7	6.25	MW	CG	N
1.100	27.94	72553S	1.75	44.5	.890	22.6	36	6.3	.90	23	32	142	.66	16.7	0.105	2.7	6.25	SST	CG	N
1.100	27.94	72564	1.75	44.5	.876	22.3	56	9.9	1.0	25	56	251	.69	17.4	0.112	2.8	6.13	MW	CG	N
1.100	27.94	72564S	1.75	44.5	.876	22.3	48	8.4	.77	20	37	164	.69	17.4	0.112	2.8	6.13	SST	CG	N
1.100	27.94	72574	1.75	44.5	.860	21.8	77	14	.90	23	69	308	.74	18.7	0.120	3.0	6.13	MW	CG	N
1.100	27.94	72574S	1.75	44.5	.860	21.8	66	11	.69	17	45	201	.74	18.7	0.120	3.0	6.13	SST	CG	N
1.100	27.94	72586	1.75	44.5	.850	21.6	86	15	.90	23	78	347	.80	20.2	0.125	3.2	6.38	MW	CG	N
1.100	27.94	72586S	1.75	44.5	.850	21.6	73	13	.69	18	51	227	.80	20.2	0.125	3.2	6.38	SST	CG	N
1.100	27.94	72596	1.75	44.5	.830	21.1	113	20	.84	21	95	423	.89	22.7	0.135	3.4	6.63	MW	CG	N
1.100	27.94	72596S	1.75	44.5	.830	21.1	96	17	.63	16	61	272	.89	22.7	0.135	3.4	6.63	SST	CG	N
1.100	27.94	72605	1.75	44.5	.816	20.7	150	26	.73	19	110	490	.91	23.0	0.142	3.6	6.38	MW	CG	N
1.100	27.94	72605S	1.75	44.5	.816	20.7	128	22	.56	14	71	316	.91	23.0	0.142	3.6	6.38	SST	CG	N
1.100	27.94	72617	1.75	44.5	.804	20.4	175	31	.71	18	124	553	.98	24.9	0.148	3.8	6.63	MW	CG	N
1.100	27.94	72617S	1.75	44.5	.804	20.4	149	26	.54	14	80	356	.98	24.9	0.148	3.8	6.63	SST	CG	N
1.100	27.94	72509	2.00	50.8	.936	23.8	17	2.9	1.5	37	24	108	.47	12.0	0.082	2.1	5.75	MW	CG	N
1.100	27.94	72509S	2.00	50.8	.936	23.8	14	2.5	1.2	29	16	72	.47	12.0	0.082	2.1	5.75	SST	CG	N
1.100	27.94	72520	2.00	50.8	.930	23.6	17	3.0	1.5	38	26	114	.52	13.2	0.085	2.2	6.13	MW	CG	N
1.100	27.94	72520S	2.00	50.8	.930	23.6	15	2.6	1.2	31	18	80	.52	13.2	0.085	2.2	6.13	SST	CG	N
1.100	27.94	72532	2.00	50.8	.914	23.2	25	4.4	1.4	34	34	150	.58	14.8	0.093	2.4	6.25	MW	CG	N
1.100	27.94	72532S	2.00	50.8	.914	23.2	21	3.7	1.1	27	22	100	.58	14.8	0.093	2.4	6.25	SST	CG	N
1.100	27.94	72543	2.00	50.8	.908	23.1	26	4.6	1.4	35	36	160	.64	16.2	0.096	2.4	6.63	MW	CG	N
1.100	27.94	72543S	2.00	50.8	.908	23.1	22	3.9	1.1	28	25	109	.64	16.2	0.096	2.4	6.63	SST	CG	N
1.100	27.94	72554	2.00	50.8	.890	22.6	36	6.3	1.3	32	46	206	.72	18.3	0.105	2.7	6.88	MW	CG	N
1.100	27.94	72554S	2.00	50.8	.890	22.6	31	5.4	1.0	26	32	142	.72	18.3	0.105	2.7	6.88	SST	CG	N
1.100	27.94	72565	2.00	50.8	.876	22.3	49	8.5	1.2	30	56	251	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.100	27.94	72565S	2.00	50.8	.876	22.3	41	7.2	.89	23	37	164	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.100	27.94	72575	2.00	50.8	.860	21.8	66	12	1.0	27	69	308	.81	20.6	0.120	3.0	6.75	MW	CG	N
1.100	27.94	72575S	2.00	50.8	.860	21.8	56	9.9	.80	20	45	201	.81	20.6	0.120	3.0	6.75	SST	CG	N
1.100	27.94	72587	2.00	50.8	.850	21.6	74	13	1.0	27	78	347	.89	22.6	0.125	3.2	7.13	MW	CG	N
1.100	27.94	72587S	2.00	50.8	.850	21.6	63	11	.80	20	51	227	.89	22.6	0.125	3.2	7.13	SST	CG	N
1.100	27.94	72597	2.00	50.8	.830	21.1	98	17	.97	25	95	423	1.01	25.7	0.135	3.4	7.50	MW	CG	N
1.100	27.94	72597S	2.00	50.8	.830	21.1	83	15	.74	19	61	272	1.01	25.7	0.135	3.4	7.50	SST	CG	N
1.100	27.94	72606	2.00	50.8	.816	20.7	129	23	.85	22	110	490	1.01	25.7	0.142	3.6	7.13	MW	CG	N
1.100	27.94	72606S	2.00	50.8	.816	20.7	110	19	.65	16	71	316	1.01	25.7	0.142	3.6	7.13	SST	CG	N
1.100	27.94	72618	2.00	50.8	.804	20.4	149	26	.83	21	124	553	1.09	27.7	0.148	3.8	7.38	MW	CG	N
1.100	27.94	72618S	2.00	50.8	.804	20.4	127	22	.63	16	80	356	1.09	27.7	0.148	3.8	7.38	SST	CG	N
1.100	27.94	72607	2.19	55.6	.816	20.7	100	18	.97	25	97	429	1.22	31.1	0.142	3.6	8.63	MW	CG	N
1.100	27.94	72607S	2.19	55.6	.816	20.7	85	15	.83	21	71	316	1.22	31.1	0.142	3.6	8.63	SST	CG	N
1.100	27.94	72566	2.25	57.2	.876	22.3	43	7.5	1.3	34	56	251	.84	21.3	0.112	2.8	7.50	MW	CG	N
1.100	27.94	72566S	2.25	57.2	.876	22.3	36	6.3	1.0	26	37	164	.84	21.3	0.112	2.8	7.50	SST	CG	N




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72521S	2.50	63.5	.930	23.6	12	2.0	1.5	39	18	80	.62	15.7	0.085	2.2	7.25	SST	CG	N
1.100	27.94	72533	2.50	63.5	.914	23.2	20	3.4	1.7	44	34	150	.69	17.4	0.093	2.4	7.38	MW	CG	N
1.100	27.94	72533S	2.50	63.5	.914	23.2	17	2.9	1.4	34	22	100	.69	17.4	0.093	2.4	7.38	SST	CG	N
1.100	27.94	72544	2.50	63.5	.908	23.1	21	3.6	1.7	44	36	161	.76	19.2	0.096	2.4	7.88	MW	CG	N
1.100	27.94	72544S	2.50	63.5	.908	23.1	18	3.1	1.4	35	25	109	.76	19.2	0.096	2.4	7.88	SST	CG	N
1.100	27.94	72555	2.50	63.5	.890	22.6	28	5.0	1.6	41	46	206	.87	22.0	0.105	2.7	8.25	MW	CG	N
1.100	27.94	72555S	2.50	63.5	.890	22.6	24	4.2	1.3	34	32	142	.87	22.0	0.105	2.7	8.25	SST	CG	N
1.100	27.94	72567	2.50	63.5	.876	22.3	38	6.6	1.5	38	56	251	.92	23.5	0.112	2.8	8.25	MW	CG	N
1.100	27.94	72567S	2.50	63.5	.876	22.3	32	5.6	1.1	29	37	164	.92	23.5	0.112	2.8	8.25	SST	CG	N
1.100	27.94	72577	2.50	63.5	.860	21.8	52	9.0	1.3	34	69	308	.98	24.8	0.120	3.0	8.13	MW	CG	N
1.100	27.94	72577S	2.50	63.5	.860	21.8	44	7.7	1.0	26	45	201	.98	24.8	0.120	3.0	8.13	SST	CG	N
1.100	27.94	72589	2.50	63.5	.850	21.6	58	10	1.4	34	78	347	1.08	27.4	0.125	3.2	8.63	MW	CG	N
1.100	27.94	72589S	2.50	63.5	.850	21.6	49	8.6	1.0	26	51	227	1.08	27.4	0.125	3.2	8.63	SST	CG	N
1.100	27.94	72599	2.50	63.5	.830	21.1	76	13	1.3	32	95	423	1.22	30.9	0.135	3.4	9.00	MW	CG	N
1.100	27.94	72599S	2.50	63.5	.830	21.1	65	11	.95	24	61	272	1.22	30.9	0.135	3.4	9.00	SST	CG	N
1.100	27.94	72609	2.50	63.5	.816	20.7	98	17	1.1	29	110	490	1.24	31.6	0.142	3.6	8.75	MW	CG	N
1.100	27.94	72609S	2.50	63.5	.816	20.7	83	15	.85	22	71	316	1.24	31.6	0.142	3.6	8.75	SST	CG	N
1.100	27.94	72620	2.50	63.5	.804	20.4	115	20	1.1	27	124	553	1.31	33.4	0.148	3.8	8.88	MW	CG	N
1.100	27.94	72620S	2.50	63.5	.804	20.4	98	17	.82	21	80	356	1.31	33.4	0.148	3.8	8.88	SST	CG	N
1.100	27.94	72610	2.75	69.9	.816	20.7	88	15	1.3	32	110	490	1.35	34.3	0.142	3.6	9.50	MW	CG	N
1.100	27.94	72610S	2.75	69.9	.816	20.7	75	13	.95	24	71	316	1.35	34.3	0.142	3.6	9.50	SST	CG	N
1.100	27.94	72621	2.75	69.9	.804	20.4	104	18	1.2	30	124	553	1.44	36.7	0.148	3.8	9.75	MW	CG	N
1.100	27.94	72621S	2.75	69.9	.804	20.4	88	15	.91	23	80	356	1.44	36.7	0.148	3.8	9.75	SST	CG	N
1.100	27.94	72511	3.00	76.2	.936	23.8	11	1.9	2.3	57	24	108	.64	16.1	0.082	2.1	7.75	MW	CG	N
1.100	27.94	72511S	3.00	76.2	.936	23.8	9.1	1.6	1.8	45	16	72	.64	16.1	0.082	2.1	7.75	SST	CG	N
1.100	27.94	72522	3.00	76.2	.930	23.6	11	2.0	2.3	58	26	114	.71	18.1	0.085	2.2	8.38	MW	CG	N
1.100	27.94	72522S	3.00	76.2	.930	23.6	9.5	1.7	1.9	48	18	80	.71	18.1	0.085	2.2	8.38	SST	CG	N
1.100	27.94	72534	3.00	76.2	.914	23.2	16	2.8	2.1	54	34	150	.80	20.4	0.093	2.4	8.63	MW	CG	N
1.100	27.94	72534S	3.00	76.2	.914	23.2	14	2.4	1.6	42	22	100	.80	20.4	0.093	2.4	8.63	SST	CG	N
1.100	27.94	72545	3.00	76.2	.908	23.1	17	3.0	2.1	54	36	161	.88	22.3	0.096	2.4	9.13	MW	CG	N
1.100	27.94	72545S	3.00	76.2	.908	23.1	14	2.5	1.7	43	25	109	.88	22.3	0.096	2.4	9.13	SST	CG	N
1.100	27.94	72556	3.00	76.2	.890	22.6	23	4.1	2.0	51	46	206	1.01	25.7	0.105	2.7	9.63	MW	CG	N
1.100	27.94	72556S	3.00	76.2	.890	22.6	20	3.5	1.6	41	32	142	1.01	25.7	0.105	2.7	9.63	SST	CG	N
1.100	27.94	72568	3.00	76.2	.876	22.3	31	5.4	1.8	46	56	251	1.06	27.0	0.112	2.8	9.50	MW	CG	N
1.100	27.94	72568S	3.00	76.2	.876	22.3	26	4.6	1.4	35	37	164	1.06	27.0	0.112	2.8	9.50	SST	CG	N
1.100	27.94	72578	3.00	76.2	.860	21.8	42	7.4	1.6	42	69	308	1.14	29.0	0.120	3.0	9.50	MW	CG	N
1.100	27.94	72578S	3.00	76.2	.860	21.8	36	6.3	1.3	32	45	201	1.14	29.0	0.120	3.0	9.50	SST	CG	N
1.100	27.94	72590	3.00	76.2	.850	21.6	47	8.3	1.7	42	78	347	1.25	31.8	0.125	3.2	10.0	MW	CG	N
1.100	27.94	72590S	3.00	76.2	.850	21.6	40	7.0	1.3	32	51	227	1.25	31.8	0.125	3.2	10.0	SST	CG	N
1.100	27.94	72600	3.00	76.2	.830	21.1	62	11	1.5	39	95	423	1.42	36.0	0.135	3.4	10.5	MW	CG	N
1.100	27.94	72600S	3.00	76.2	.830	21.1	53	9.3	1.2	29	61	272	1.42	36.0	0.135	3.4	10.5	SST	CG	N
1.100	27.94	72611	3.00	76.2	.816	20.7	80	14	1.4	35	110	490	1.46	37.0	0.142	3.6	10.3	MW	CG	N
1.100	27.94	72611S	3.00	76.2	.816	20.7	68	12	1.0	27	71	316	1.46	37.0	0.142	3.6	10.3	SST	CG	N
1.100	27.94	72622	3.00	76.2	.804	20.4	94	16	1.3	34	124	553	1.55	39.5	0.148	3.8	10.5	MW	CG	N
1.100	27.94	72622S	3.00	76.2	.804	20.4	80	14	1.0	25	80	356	1.55	39.5	0.148	3.8	10.5	SST	CG	N
1.100	27.94	72612	3.31	84.1	.816	20.7	64	11	1.6	39	99	442	1.76	44.6	0.142	3.6	12.4	MW	CG	N
1.100	27.94	72612S	3.31	84.1	.816	20.7	54	9.5	1.3	33	71	316	1.76	44.6	0.142	3.6	12.4	SST	CG	N
1.100	27.94	72512	3.50	88.9	.936	23.8	9.1	1.6	2.7	68	24	108	.72	18.2	0.082	2.1	8.75	MW	CG	N
1.100	27.94	72512S	3.50	88.9	.936	23.8	7.7	1.4	2.1	53	16	72	.72	18.2	0.082	2.1	8.75	SST	CG	N
1.100	27.94	72523	3.50	88.9	.930	23.6	9.6	1.7	2.7	68	26	115	.81	20.5	0.085	2.2	9.50	MW	CG	N
1.100	27.94	72523S	3.50	88.9	.930	23.6	8.2	1.4	2.2	56	18	80	.81	20.5	0.085	2.2	9.50	SST	CG	N
1.100	27.94	72535	3.50	88.9	.914	23.2	14	2.4	2.5	63	34	150	.91	23.0	0.093	2.4	9.75	MW	CG	N
1.100	27.94	72535S	3.50	88.9	.914	23.2	12	2.0	1.9	49	22	100	.91	23.0	0.093	2.4	9.75	SST	CG	N
1.100	27.94	72546	3.50	88.9	.908	23.1	14	2.5	2.5	64	36	160	1.00	25.3	0.096	2.4	10.4	MW	CG	N
1.100	27.94	72546S	3.50	88.9	.908	23.1	12	2.1	2.0	51	25	109	1.00	25.3	0.096	2.4	10.4	SST	CG	N
1.100	27.94	72557	3.50	88.9	.890	22.6	20	3.4	2.3	60	46	205	1.16	29.3	0.105	2.7	11.0	MW	CG	N
1.100	27.94	72557S	3.50	88.9	.890	22.6	17	2.9	1.											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72570S	4.00	101.6	.876	22.3	19	3.4	1.9	48	37	164	1.37	34.8	0.112	2.8	12.3	SST	CG	N
1.100	27.94	72580	4.00	101.6	.860	21.8	31	5.4	2.2	57	69	308	1.47	37.3	0.120	3.0	12.3	MW	CG	N
1.100	27.94	72580S	4.00	101.6	.860	21.8	26	4.6	1.7	44	45	201	1.47	37.3	0.120	3.0	12.3	SST	CG	N
1.100	27.94	72592	4.00	101.6	.850	21.6	34	6.0	2.3	58	78	347	1.63	41.3	0.125	3.2	13.0	MW	CG	N
1.100	27.94	72592S	4.00	101.6	.850	21.6	29	5.1	1.7	44	51	227	1.63	41.3	0.125	3.2	13.0	SST	CG	N
1.100	27.94	72602	4.00	101.6	.830	21.1	45	7.9	2.1	54	95	423	1.86	47.1	0.135	3.4	13.8	MW	CG	N
1.100	27.94	72602S	4.00	101.6	.830	21.1	38	6.7	1.6	41	61	272	1.86	47.1	0.135	3.4	13.8	SST	CG	N
1.100	27.94	72614	4.00	101.6	.816	20.7	59	10	1.9	47	110	490	1.88	47.8	0.142	3.6	13.3	MW	CG	N
1.100	27.94	72614S	4.00	101.6	.816	20.7	50	8.8	1.4	36	71	316	1.88	47.8	0.142	3.6	13.3	SST	CG	N
1.100	27.94	72624	4.00	101.6	.804	20.4	69	12	1.8	46	124	553	2.02	51.2	0.148	3.8	13.6	MW	CG	N
1.100	27.94	72624S	4.00	101.6	.804	20.4	58	10	1.4	35	80	356	2.02	51.2	0.148	3.8	13.6	SST	CG	N
1.100	27.94	72525	4.50	114.3	.930	23.6	7.3	1.3	3.5	89	25	113	1.01	25.6	0.085	2.2	11.9	MW	CG	N
1.100	27.94	72525S	4.50	114.3	.930	23.6	6.2	1.1	2.9	74	18	80	1.01	25.6	0.085	2.2	11.9	SST	CG	N
1.100	27.94	72548	4.50	114.3	.908	23.1	11	1.9	3.3	83	36	161	1.24	31.4	0.096	2.4	12.9	MW	CG	N
1.100	27.94	72548S	4.50	114.3	.908	23.1	9.4	1.7	2.6	66	25	109	1.24	31.4	0.096	2.4	12.9	SST	CG	N
1.100	27.94	72559	4.50	114.3	.890	22.6	15	2.6	3.1	78	46	205	1.44	36.7	0.105	2.7	13.8	MW	CG	N
1.100	27.94	72559S	4.50	114.3	.890	22.6	13	2.2	2.5	64	32	142	1.44	36.7	0.105	2.7	13.8	SST	CG	N
1.100	27.94	72571	4.50	114.3	.876	22.3	20	3.5	2.8	71	56	251	1.53	38.8	0.112	2.8	13.6	MW	CG	N
1.100	27.94	72571S	4.50	114.3	.876	22.3	17	3.0	2.2	55	37	164	1.53	38.8	0.112	2.8	13.6	SST	CG	N
1.100	27.94	72581	4.50	114.3	.860	21.8	27	4.8	2.5	64	69	308	1.64	41.5	0.120	3.0	13.6	MW	CG	N
1.100	27.94	72581S	4.50	114.3	.860	21.8	23	4.1	1.9	49	45	201	1.64	41.5	0.120	3.0	13.6	SST	CG	N
1.100	27.94	72593	4.50	114.3	.850	21.6	30	5.3	2.6	65	78	347	1.81	46.0	0.125	3.2	14.5	MW	CG	N
1.100	27.94	72593S	4.50	114.3	.850	21.6	26	4.5	2.0	50	51	227	1.81	46.0	0.125	3.2	14.5	SST	CG	N
1.100	27.94	72603	4.50	114.3	.830	21.1	39	6.9	2.4	61	95	422	2.09	53.1	0.135	3.4	15.5	MW	CG	N
1.100	27.94	72603S	4.50	114.3	.830	21.1	34	5.9	1.8	46	61	272	2.09	53.1	0.135	3.4	15.5	SST	CG	N
1.100	27.94	72615	4.50	114.3	.816	20.7	51	8.9	2.2	55	110	490	2.13	54.1	0.142	3.6	15.0	MW	CG	N
1.100	27.94	72615S	4.50	114.3	.816	20.7	43	7.6	1.6	42	71	316	2.13	54.1	0.142	3.6	15.0	SST	CG	N
1.100	27.94	72625	4.50	114.3	.804	20.4	61	11	2.1	52	124	553	2.26	57.3	0.148	3.8	15.3	MW	CG	N
1.100	27.94	72625S	4.50	114.3	.804	20.4	51	9.0	1.6	40	80	356	2.26	57.3	0.148	3.8	15.3	SST	CG	N
1.100	27.94	72526	5.00	127.0	.930	23.6	6.6	1.2	3.9	99	26	115	1.09	27.8	0.085	2.2	12.9	MW	CG	N
1.100	27.94	72526S	5.00	127.0	.930	23.6	5.6	.98	3.2	82	18	80	1.09	27.8	0.085	2.2	12.9	SST	CG	N
1.100	27.94	72604	5.00	127.0	.830	21.1	35	6.2	2.7	68	95	423	2.30	58.3	0.135	3.4	17.0	MW	CG	N
1.100	27.94	72604S	5.00	127.0	.830	21.1	30	5.3	2.0	52	61	272	2.30	58.3	0.135	3.4	17.0	SST	CG	N
1.100	27.94	72616	5.00	127.0	.816	20.7	46	8.1	2.4	61	110	490	2.34	59.5	0.142	3.6	16.5	MW	CG	N
1.100	27.94	72616S	5.00	127.0	.816	20.7	39	6.8	1.8	46	71	316	2.34	59.5	0.142	3.6	16.5	SST	CG	N
1.100	27.94	72626	5.00	127.0	.804	20.4	54	9.5	2.3	58	124	553	2.48	63.0	0.148	3.8	16.8	MW	CG	N
1.100	27.94	72626S	5.00	127.0	.804	20.4	46	8.1	1.7	44	80	356	2.48	63.0	0.148	3.8	16.8	SST	CG	N
1.109	28.17	II-8	.69	17.4	.869	22.1	308	54	.16	4.1	49	219	.36	9.1	0.120	3.0	3.00	SPR	CG	N
1.109	28.17	1869	.75	19.1	.965	24.5	87	1.5	.32	8.1	2.8	12	.43	11.0	0.072	1.8	6.00	HD	CG	Z
1.109	28.17	S-1258	1.00	25.4	.899	22.8	75	13	.42	11	32	141	.42	10.7	0.105	2.7	4.00	SST	CG	N
1.109	28.17	3752	1.00	25.4	.859	21.8	134	23	.41	10	54	242	.59	15.1	0.125	3.2	4.75	SPR	CG	Z
1.109	28.17	DD-27	1.06	27.0	.769	19.5	857	150	.13	3.4	114	508	.60	15.1	0.170	4.3	3.50	SST	CG	N
1.109	28.17	LL-100	1.09	27.8	.949	24.1	13	2.2	.59	15	7.6	34	.50	12.7	0.080	2.0	6.25	SPR	CG	N
1.109	28.17	S-34	1.16	29.4	.983	25.0	2.9	.51	.67	17	2.0	8.7	.48	12.3	0.063	1.6	7.50	SST	CG	N
1.109	28.17	11705	1.16	29.4	.921	23.4	36	6.3	.69	17	25	109	.47	11.9	0.094	2.4	5.00	SPR	CG	Z
1.109	28.17	12160	1.25	31.8	.919	23.3	56	9.8	.45	12	26	113	.38	9.7	0.095	2.4	4.00	SPR	CG	Z
1.109	28.17	10621	1.28	32.5	.927	23.5	31	5.5	.72	18	22	100	.46	11.6	0.091	2.3	5.00	SPR	CG	N
1.109	28.17	12562	1.30	32.9	.993	25.2	7.0	1.2	.92	23	6.5	29	.29	7.4	0.058	1.5	4.00	SPR	C	N
1.109	28.17	S-55	1.38	34.9	.869	22.1	62	11	.62	16	38	169	.76	19.3	0.120	3.0	6.33	SST	CG	N
1.109	28.17	HH-33	1.38	34.9	.809	20.5	206	36	.43	11	90	398	.90	22.9	0.150	3.8	6.00	SPR	CG	N
1.109	28.17	11697	1.53	38.9	.885	22.5	57	10	.70	18	40	178	.67	17.1	0.112	2.8	6.00	SPR	CG	Z
1.109	28.17	2681	1.78	45.2	.861	21.9	59	10	.79	20	47	208	.99	25.2	0.124	3.1	8.00	HD	CG	Z
1.109	28.17	UU-39	1.78	45.2	.795	20.2	184	32	.56	14	102	455	1.18	29.9	0.157	4.0	7.50	SPR	CG	Z
1.109	28.17	S-3060	2.00	50.8	.813	20.7	135	24	.59	15	79	353	1.04	26.3	0.148	3.8	7.00	SST	CG	N
1.109	28.17	B17-150	2.13	54.0	1.013	25.7	.94	.17	1.7	44	1.6	7.3	.38	9.8	0.048	1.2	8.00	SST	CG	N
1.109	28.17	S-1415	2.19	55.6	.959	24.4	4.8	.84	1.5	37	7.0	31	.71	18.1						




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.125	28.58	S-931	.97	24.6	1.023	26.0	1.7	.30	.66	17	1.1	5.0	.31	7.8	0.051	1.3	6.00	SST	CG	N
1.125	28.58	11963	.97	24.6	1.003	25.5	4.1	.72	.60	15	2.5	11	.37	9.3	0.061	1.5	6.00	SPR	CG	Z
1.125	28.58	10482	1.00	25.4	.965	24.5	26	4.5	.61	16	16	70	.32	8.1	0.080	2.0	4.00	SPR	CG	N
1.125	28.58	S-1383	1.06	27.0	.915	23.2	57	10	.55	14	31	139	.47	12.0	0.105	2.7	4.50	SST	CG	N
1.125	28.58	3947	1.19	30.2	.941	23.9	31	5.5	.73	18	23	101	.46	11.7	0.092	2.3	5.00	SPR	CG	Z
1.125	28.58	B17-147	1.22	31.0	1.005	25.5	7.7	1.4	.91	23	7.1	31	.24	6.1	0.060	1.5	4.00	SPR	CG	N
1.125	28.58	S-1236	1.25	31.8	.981	24.9	9.6	1.7	.89	23	8.5	38	.36	9.1	0.072	1.8	5.00	SST	CG	N
1.125	28.58	11742	1.25	31.8	.895	22.7	122	21	.35	8.9	43	190	.46	11.7	0.115	2.9	4.00	SPR	CG	Z
1.125	28.58	12271	1.38	34.9	.995	25.3	4.2	.74	.95	24	4.0	18	.42	10.7	0.065	1.7	6.50	SST	CG	N
1.125	28.58	S-147	1.41	35.7	1.031	26.2	.89	.16	1.0	26	.89	4.0	.40	10.1	0.047	1.2	7.50	SST	C	N
1.125	28.58	S-911	1.47	37.3	.981	24.9	7.3	1.3	1.0	26	7.6	34	.43	11.0	0.072	1.8	6.00	SST	CG	N
1.125	28.58	2945	1.50	38.1	1.017	25.8	5.0	.87	1.0	26	5.2	23	.27	6.9	0.054	1.4	4.00	SPR	C	Z
1.125	28.58	12001	1.50	38.1	.935	23.7	27	4.7	.93	24	25	111	.57	14.5	0.095	2.4	6.00	SPR	CG	Z
1.125	28.58	S-1249	1.50	38.1	.915	23.2	48	8.4	.66	17	31	139	.53	13.3	0.105	2.7	5.00	SST	CG	N
1.125	28.58	S-1561	1.50	38.1	.875	22.2	87	15	.57	15	50	222	.69	17.5	0.125	3.2	5.50	SST	CG	N
1.125	28.58	10624	1.56	39.7	.815	20.7	303	53	.32	8.1	97	432	.78	19.7	0.155	3.9	5.00	SPR	CG	Z
1.125	28.58	M-80	1.59	40.5	.859	21.8	115	20	.55	14	64	283	.80	20.3	0.133	3.4	6.00	SPR	CG	Z
1.125	28.58	S-3242	1.72	43.6	1.003	25.5	3.7	.64	1.4	34	5.0	22	.37	9.3	0.061	1.5	6.00	SST	CG	N
1.125	28.58	3302	1.75	44.5	.875	22.2	58	10	.75	19	44	195	1.00	25.4	0.125	3.2	8.00	HD	CG	Z
1.125	28.58	11433	1.88	47.6	.885	22.5	56	9.8	.87	22	48	216	.87	22.1	0.120	3.0	7.25	HD	CG	Z
1.125	28.58	11335	2.00	50.8	.829	21.1	148	26	.59	15	87	387	1.04	26.3	0.148	3.8	7.00	SPR	CG	Z
1.125	28.58	CC-96	2.00	50.8	.805	20.4	210	37	.51	13	107	474	1.12	28.4	0.160	4.1	7.00	SPR	CG	Z
1.125	28.58	S-3239	2.09	53.2	.945	24.0	19	3.3	1.1	27	20	88	.54	13.7	0.090	2.3	6.00	SST	CG	N
1.125	28.58	4340	2.13	54.0	.855	21.7	66	11	.84	21	55	246	1.28	32.6	0.135	3.4	9.50	SPR	CG	Z
1.125	28.58	S-973	2.28	57.9	.965	24.5	8.2	1.4	1.7	43	14	61	.60	15.2	0.080	2.0	7.50	SST	CG	N
1.125	28.58	2694	2.31	58.7	.933	23.7	20	3.6	1.3	32	26	115	.72	18.3	0.096	2.4	7.50	HD	CG	Z
1.125	28.58	S-1569	2.38	60.3	.875	22.2	69	12	.72	18	50	222	.81	20.6	0.125	3.2	6.50	SST	CG	N
1.125	28.58	10483	2.38	60.3	.831	21.1	159	28	.54	14	85	380	.96	24.3	0.147	3.7	6.50	SPR	CG	Z
1.125	28.58	S-194	2.44	61.9	1.045	26.5	.72	.13	2.2	55	1.6	6.9	.26	6.6	0.040	1.0	5.50	SST	C	N
1.125	28.58	1629	2.50	63.5	.965	24.5	8.6	1.5	1.8	47	16	70	.64	16.3	0.080	2.0	8.00	SPR	CG	Z
1.125	28.58	3965	2.50	63.5	.905	23.0	31	5.4	1.2	31	38	167	.94	23.7	0.110	2.8	8.50	SPR	CG	Z
1.125	28.58	S-466	2.50	63.5	.885	22.5	59	10	.75	19	44	197	.76	19.3	0.120	3.0	6.33	SST	CG	N
1.125	28.58	12017	2.53	64.3	.831	21.1	120	21	.71	18	85	380	1.18	29.9	0.147	3.7	8.00	SPR	CG	Z
1.125	28.58	B8-67	2.66	67.5	.875	22.2	64	11	.86	22	55	243	1.06	27.0	0.125	3.2	7.50	SPR	C	N
1.125	28.58	2567	2.69	68.2	.995	25.3	4.3	.75	2.1	53	9.0	40	.46	11.6	0.065	1.7	7.00	SPR	CG	Z
1.125	28.58	11143	2.69	68.2	.901	22.9	29	5.1	1.4	35	40	176	1.18	29.9	0.112	2.8	9.50	SPR	C	Z
1.125	28.58	11785	2.72	69.0	.919	23.3	28	4.8	1.2	29	32	142	.77	19.6	0.103	2.6	7.50	SPR	CG	N
1.125	28.58	10540	2.72	69.0	.895	22.7	31	5.3	1.4	36	43	190	1.15	29.2	0.115	2.9	10.0	SPR	CG	Z
1.125	28.58	B7-47	2.72	69.0	.845	21.5	82	14	.81	21	67	297	1.16	29.3	0.140	3.6	8.25	SST	CG	N
1.125	28.58	11203	2.75	69.9	.901	22.9	27	4.8	1.5	37	40	176	1.23	31.3	0.112	2.8	10.0	SPR	C	Z
1.125	28.58	12076	2.78	70.6	.811	20.6	175	31	.58	15	101	449	1.18	29.9	0.157	4.0	7.50	SPR	CG	Z
1.125	28.58	2736	2.84	72.2	.855	21.7	70	12	1.3	34	93	414	1.22	30.9	0.135	3.4	9.00	MW	CG	Z
1.125	28.58	825	2.88	73.0	.855	21.7	60	10	1.1	28	67	296	1.52	38.6	0.135	3.4	10.3	HD	C	Z
1.125	28.58	2824	2.94	74.6	.875	22.2	39	6.8	1.6	40	61	271	1.38	34.9	0.125	3.2	11.0	MW	CG	Z
1.125	28.58	S-1131	3.00	76.2	.965	24.5	5.6	.98	2.2	56	12	55	.80	20.3	0.080	2.0	10.0	SST	CG	N
1.125	28.58	10643	3.00	76.2	.943	24.0	14	2.5	1.6	39	22	99	.75	19.1	0.091	2.3	8.25	SPR	CG	Z
1.125	28.58	366	3.00	76.2	.915	23.2	22	3.8	1.5	39	34	150	1.00	25.3	0.105	2.7	9.50	HD	CG	Z
1.125	28.58	59	3.00	76.2	.741	18.8	275	48	.63	16	172	766	2.06	52.4	0.192	4.9	10.8	HD	CG	Z
1.125	28.58	3157	3.19	81.0	.781	19.8	156	27	.84	21	131	585	1.95	49.5	0.172	4.4	11.3	SPR	CG	Z
1.125	28.58	11935	3.25	82.6	.965	24.5	3.2	.56	1.8	46	5.8	26	1.44	36.6	0.080	2.0	18.0	SPR	CG	Z
1.125	28.58	S-169	3.38	85.7																





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.140	28.96	11907	1.09	27.8	1.012	25.7	2.9	.50	.58	15	1.7	7.4	.51	13.0	0.064	1.6	8.00	SST	CG	N
1.140	28.96	S-1047	1.25	31.8	.900	22.9	81	14	.54	14	44	194	.60	15.2	0.120	3.0	5.00	SST	CG	N
1.140	28.96	10889	1.31	33.3	1.046	26.6	.79	.14	.94	24	.74	3.3	.38	9.6	0.047	1.2	8.00	SST	CG	N
1.140	28.96	12321	1.50	38.1	1.030	26.2	2.2	.38	1.1	29	2.4	11	.37	9.4	0.055	1.4	6.75	SPR	CG	Z
1.140	28.96	12644	1.83	46.4	1.032	26.2	2.4	.42	1.5	38	3.5	16	.35	8.9	0.054	1.4	5.50	SST	C	N
1.140	28.96	S-3008	1.88	47.6	.880	22.4	99	17	.54	14	53	236	.72	18.2	0.130	3.3	5.50	SST	CG	N
1.140	28.96	S-1203	1.94	49.2	.880	22.4	87	15	.61	16	53	236	.78	19.8	0.130	3.3	6.00	SST	CG	N
1.140	28.96	S-254	2.00	50.8	.756	19.2	352	62	.42	11	147	653	1.47	37.4	0.192	4.9	7.67	SST	CG	N
1.140	28.96	3999	2.25	57.2	.956	24.3	19	3.3	1.2	30	23	100	.62	15.8	0.092	2.3	6.75	SPR	CG	Z
1.140	28.96	11343	2.41	61.1	.844	21.4	157	27	.55	14	86	383	.96	24.4	0.148	3.8	6.50	SPR	CG	Z
1.140	28.96	3173	2.56	65.1	.956	24.3	13	2.2	1.7	44	22	99	.83	21.0	0.092	2.3	9.00	SPR	CG	Z
1.140	28.96	3156	2.63	66.7	1.028	26.1	2.8	.49	2.0	52	5.7	25	.34	8.5	0.056	1.4	6.00	SPR	CG	Z
1.140	28.96	11130	2.84	72.2	.756	19.2	270	47	.63	16	170	758	2.02	51.2	0.192	4.9	10.5	SPR	CG	Z
1.140	28.96	12755	2.84	72.2	.766	19.5	232	41	.77	19	178	790	2.01	51.1	0.187	4.7	10.8	OT	CG	N
1.140	28.96	S-1168	3.00	76.2	.960	24.4	8.9	1.6	2.1	53	19	83	.90	22.9	0.090	2.3	10.0	SST	CG	N
1.140	28.96	11799	3.13	79.4	.830	21.1	124	22	.77	20	96	427	1.40	35.4	0.155	3.9	9.00	SPR	CG	Z
1.140	28.96	10365	3.19	81.0	.844	21.4	76	13	1.1	29	86	383	1.67	42.3	0.148	3.8	11.3	SPR	CG	Z
1.140	28.96	4312	3.88	98.4	.870	22.1	51	8.9	1.3	33	66	292	1.52	38.6	0.135	3.4	11.3	SPR	CG	Z
1.140	28.96	3158	4.00	101.6	.890	22.6	30	5.2	1.8	46	54	240	1.78	45.2	0.125	3.2	14.0	SPR	CG	Z
1.140	28.96	S-1458	4.88	123.8	.970	24.6	5.1	.88	3.5	88	17	78	1.11	28.1	0.085	2.2	13.0	SST	CG	N
1.140	28.96	10571	4.88	123.8	.890	22.6	23	4.1	2.3	59	54	240	2.06	52.4	0.125	3.2	16.5	SPR	CG	Z
1.140	28.96	12179	5.16	131.0	.814	20.7	75	13	1.5	38	111	494	2.69	68.3	0.163	4.1	16.5	SPR	CG	Z
1.140	28.96	10458	5.25	133.4	.968	24.6	6.7	1.2	2.9	73	19	86	1.03	26.2	0.086	2.2	12.0	SPR	CG	Z
1.140	28.96	10376	5.31	134.9	.966	24.5	7.1	1.2	2.8	72	20	89	1.04	26.5	0.087	2.2	12.0	HD	CG	Z
1.140	28.96	3024	5.63	142.9	.786	20.0	88	15	1.6	41	141	628	3.54	89.9	0.177	4.5	20.0	SPR	CG	Z
1.156	29.36	S-262	.50	12.7	1.062	27.0	2.2	.39	.27	6.7	.59	2.6	.24	6.0	0.047	1.2	4.00	SST	C	N
1.156	29.36	3306	.69	17.4	.996	25.3	32	5.5	.33	8.3	10	46	.36	9.1	0.080	2.0	3.50	SPR	C	Z
1.156	29.36	10831	.81	20.6	1.066	27.1	1.9	.33	.59	15	1.1	5.0	.23	5.7	0.045	1.1	4.00	SST	C	N
1.156	29.36	B8-47	.88	22.2	1.056	26.8	2.4	.41	.65	17	1.5	6.8	.23	5.7	0.050	1.3	4.50	SST	CG	N
1.156	29.36	Q-32	.88	22.2	1.044	26.5	9.4	1.6	.56	14	5.3	23	.17	4.3	0.056	1.4	3.00	SST	CG	N
1.156	29.36	S-1018	.94	23.8	.886	22.5	223	39	.26	6.7	58	260	.51	12.9	0.135	3.4	3.75	SST	CG	N
1.156	29.36	S-1070	1.00	25.4	.832	21.1	584	102	.16	4.2	96	426	.57	14.4	0.162	4.1	3.50	SST	CG	N
1.156	29.36	12237	1.25	31.8	1.046	26.6	2.0	.35	.87	22	1.7	7.6	.39	9.8	0.055	1.4	7.00	SPR	CG	Z
1.156	29.36	3468	1.25	31.8	.980	24.9	24	4.1	.81	21	19	85	.44	11.2	0.088	2.2	5.00	SPR	CG	Z
1.156	29.36	3027	1.25	31.8	.976	24.8	21	3.6	.73	19	15	68	.52	13.1	0.090	2.3	5.75	SPR	CG	Z
1.156	29.36	PP-40	1.28	32.5	.896	22.8	109	19	.53	14	58	258	.72	18.2	0.130	3.3	5.50	SPR	CG	Z
1.156	29.36	4120	1.38	34.9	.986	25.0	20	3.6	.87	22	18	78	.51	13.0	0.085	2.2	5.00	SPR	CG	Z
1.156	29.36	PP-38	1.38	34.9	.896	22.8	52	9.1	.27	6.9	14	62	1.11	28.1	0.130	3.3	8.50	SST	CG	N
1.156	29.36	S-1183	1.44	36.5	1.052	26.7	.80	.14	.84	21	.67	3.0	.60	15.2	0.052	1.3	10.5	SST	C	N
1.156	29.36	10168	1.50	38.1	1.048	26.6	1.9	.34	1.1	29	2.2	9.7	.36	9.3	0.054	1.4	6.75	SPR	CG	Z
1.156	29.36	S-468	1.69	42.8	.946	24.0	26	4.6	.95	24	25	111	.74	18.7	0.105	2.7	7.00	SST	CG	N
1.156	29.36	12208	1.78	45.2	.900	22.9	71	12	.76	19	54	239	1.02	26.0	0.128	3.3	7.00	MW	C	Z
1.156	29.36	11528	1.88	47.6	1.084	27.5	.57	.10	1.7	42	.95	4.2	.22	5.5	0.036	0.9	5.00	SPR	C	Z
1.156	29.36	S-79	1.94	49.2	1.050	26.7	1.5	.27	1.6	40	2.4	11	.36	9.1	0.053	1.3	6.75	SST	CG	N
1.156	29.36	3013	2.00	50.8	1.028	26.1	3.1	.54	1.5	38	4.6	20	.51	13.0	0.064	1.6	8.00	SPR	CG	Z
1.156	29.36	3255	2.13	54.0	.870	22.1	105	18	.73	19	77	342	1.07	27.2	0.143	3.6	7.50	SPR	CG	Z
1.156	29.36	2969	2.50	63.5	1.012	25.7	5.5	.97	2.0	50	11	48	.54	13.7	0.072	1.8	7.50	SPR	CG	Z
1.156	29.36	3368	2.63	66.7	.946	24.0	21	3.6	1.6	40	33	147	.97	24.7	0.105	2.7	9.25	SPR	CG	GI
1.156	29.36	Y-63	2.75	69.9	1.028	26.1	2.8	.49	2.2	56	6.1	27	.56	14.2	0.064	1.6	7.75	SST	C	N
1.156	29.36	3487	2.75	69.9	1.026	26.1	4.0	.69	2.2	56	8.7	39	.52	13.2	0.065	1.7	7.00	HD	C	Z
1.156	29.36	S-469	2.88	73.0	1.048	26.6	1.3	.23	2.4	61	3.2	14	.49	12.3	0.054	1				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.172	29.77	1797	2.44	61.9	.902	22.9	66	12	.97	25	64	285	1.15	29.2	0.135	3.4	8.50	HD	CG	Z
1.172	29.77	11862	2.94	74.6	1.016	25.8	9.1	1.6	1.6	39	14	62	.51	12.9	0.078	2.0	6.50	SPR	CG	N
1.172	29.77	B17-188	3.50	88.9	1.082	27.5	.41	.07	3.0	76	1.2	5.4	.50	12.6	0.045	1.1	11.0	SST	CG	N
1.172	29.77	S-1244	3.63	92.1	1.012	25.7	7.9	1.4	1.8	46	14	63	.56	14.2	0.080	2.0	7.00	SST	CG	N
1.172	29.77	3016	4.17	106.0	.888	22.6	49	8.5	1.5	39	74	330	1.85	46.9	0.142	3.6	13.0	SPR	CG	GI
1.172	29.77	3670	4.28	108.7	1.074	27.3	.73	.13	3.7	95	2.7	12	.54	13.7	0.049	1.2	10.0	SPR	CG	Z
1.172	29.77	11220	6.00	152.4	.788	20.0	143	25	1.2	30	166	740	3.17	80.5	0.192	4.9	16.5	SPR	CG	Z
1.172	29.77	S-1616	7.00	177.8	.988	25.1	3.3	.58	4.7	119	15	69	2.30	58.4	0.092	2.3	24.0	SST	CG	N
1.172	29.77	10675	10.8	273.1	.860	21.8	27	4.7	3.5	90	95	424	4.99	126.8	0.156	4.0	32.0	SPR	CG	Z
1.172	29.77	2742	11.3	285.8	.908	23.1	11	2.0	5.2	133	60	267	4.88	124.1	0.132	3.4	36.0	SPR	CG	Z
1.188	30.18	10160	.44	11.1	1.028	26.1	43	7.6	.20	5.0	8.6	38	.24	6.1	0.080	2.0	3.00	SPR	CG	Z
1.188	30.18	10661	.66	16.7	1.000	25.4	86	15	.27	6.9	23	103	.28	7.2	0.094	2.4	3.00	SPR	CG	Z
1.188	30.18	S-3078	.75	19.1	.928	23.6	241	42	.21	5.4	51	227	.42	10.7	0.130	3.3	3.25	SST	CG	N
1.188	30.18	S-3178	.75	19.1	.908	23.1	417	73	.15	3.9	63	282	.42	10.7	0.140	3.6	3.00	SST	CG	N
1.188	30.18	2844	.81	20.6	.808	20.5	1256	220	.13	3.2	159	709	.67	16.9	0.190	4.8	3.50	SPR	CG	Z
1.188	30.18	11918	1.00	25.4	1.066	27.1	4.1	.72	.70	18	2.9	13	.31	7.7	0.061	1.5	5.00	SST	CG	N
1.188	30.18	1902	1.13	28.6	1.038	26.4	6.6	1.2	.60	15	4.0	18	.53	13.3	0.075	1.9	7.00	SPR	CG	Z
1.188	30.18	11632	1.22	31.0	1.006	25.6	15	2.6	.58	15	8.7	39	.64	16.2	0.091	2.3	7.00	SPR	CG	Z
1.188	30.18	12540	1.38	34.9	1.028	26.1	17	3.0	.86	22	15	66	.44	11.2	0.080	2.0	4.50	SPR	CG	N
1.188	30.18	533	1.38	34.9	.978	24.8	50	8.8	.64	16	32	143	.60	15.3	0.105	2.7	4.75	HD	CG	Z
1.188	30.18	11259	1.41	35.7	1.028	26.1	19	3.4	.78	20	15	66	.42	10.7	0.080	2.0	4.25	SPR	CG	Z
1.188	30.18	12334	1.50	38.1	1.032	26.2	9.7	1.7	1.0	26	10	45	.47	11.9	0.078	2.0	6.00	SPR	CG	Z
1.188	30.18	11642	1.50	38.1	1.028	26.1	14	2.5	1.0	26	15	66	.40	10.2	0.080	2.0	5.00	SPR	CG	Z
1.188	30.18	3186	1.50	38.1	.774	19.7	932	163	.22	5.6	204	907	1.04	26.3	0.207	5.3	5.00	SPR	CG	Z
1.188	30.18	1849	1.53	38.9	1.006	25.6	30	5.2	.98	25	29	131	.41	10.4	0.091	2.3	4.50	MW	CG	Z
1.188	30.18	11485	1.59	40.5	1.020	25.9	18	3.1	.97	25	17	77	.50	12.8	0.084	2.1	5.00	SPR	CG	Z
1.188	30.18	S-3058	1.88	47.6	1.068	27.1	3.2	.56	1.5	38	4.8	21	.39	9.9	0.060	1.5	5.50	SST	CG	N
1.188	30.18	2992	1.88	47.6	.938	23.8	65	11	.80	20	52	231	.81	20.6	0.125	3.2	6.50	SPR	CG	Z
1.188	30.18	1889	2.00	50.8	1.044	26.5	6.2	1.1	1.5	37	9.0	40	.54	13.7	0.072	1.8	6.50	HD	CG	Z
1.188	30.18	12437	2.00	50.8	1.040	26.4	7.3	1.3	1.5	37	11	48	.54	13.6	0.074	1.9	6.25	SPR	CG	Z
1.188	30.18	S-3133	2.00	50.8	.978	24.8	28	4.9	1.1	27	30	132	.76	19.3	0.105	2.7	6.25	SST	CG	N
1.188	30.18	S-3186	2.00	50.8	.918	23.3	71	12	.80	20	57	253	.95	24.0	0.135	3.4	7.00	SST	CG	N
1.188	30.18	S-3012	2.00	50.8	.774	19.7	442	77	.40	10	176	781	1.55	39.4	0.207	5.3	7.50	SST	CG	N
1.188	30.18	2792	2.19	55.6	.918	23.3	58	10	.97	25	57	253	1.22	30.9	0.135	3.4	9.00	SPR	CG	Z
1.188	30.18	12036	2.28	57.9	1.068	27.1	3.1	.53	1.9	48	5.8	26	.38	9.5	0.060	1.5	6.25	SPR	CG	Z
1.188	30.18	11160	2.28	57.9	.876	22.3	163	29	.58	15	94	419	1.05	26.7	0.156	4.0	6.75	SPR	CG	Z
1.188	30.18	1924	2.38	60.3	1.004	25.5	16	2.7	1.4	35	22	97	.74	18.7	0.092	2.3	7.00	SPR	CG	GI
1.188	30.18	857	2.38	60.3	.918	23.3	68	12	.93	24	63	281	1.22	30.9	0.135	3.4	8.00	HD	CG	Z
1.188	30.18	11251	2.41	61.1	.864	21.9	203	36	.46	12	93	415	.97	24.7	0.162	4.1	6.00	SST	CG	N
1.188	30.18	821	2.50	63.5	.892	22.7	85	15	.98	25	83	368	1.37	34.8	0.148	3.8	9.25	HD	CG	Z
1.188	30.18	3382	2.63	66.7	.908	23.1	69	12	1.0	26	70	313	1.26	32.0	0.140	3.6	9.00	SPR	CG	Z
1.188	30.18	869	2.75	69.9	.948	24.1	35	6.1	1.3	33	46	205	1.20	30.5	0.120	3.0	9.00	HD	CG	Z
1.188	30.18	3469	2.75	69.9	.918	23.3	58	10	1.1	28	63	281	1.22	30.9	0.135	3.4	9.00	HD	CG	Z
1.188	30.18	B8-64	3.00	76.2	.862	21.9	119	21	.80	20	95	423	1.47	37.3	0.163	4.1	9.00	SST	CG	N
1.188	30.18	11960	3.06	77.8	.908	23.1	64	11	1.1	28	70	313	1.33	33.8	0.140	3.6	9.50	SPR	CG	Z
1.188	30.18	11414	3.13	79.4	.978	24.8	18	3.2	1.8	44	32	143	1.00	25.3	0.105	2.7	9.50	HD	CG	Z
1.188	30.18	11175	3.25	82.6	.892	22.7	88	15	.95	24	83	368	1.33	33.8	0.148	3.8	9.00	SPR	CG	Z
1.188	30.18	840	3.25	82.6	.804	20.4	203	36	.81	21	164	731	2.26	57.3	0.192	4.9	11.8	HD	CG	Z
1.188	30.18	43	3.25	82.6	.734	18.6	434	76	.59	15	255	1136	2.59	65.7	0.227	5.8	11.5	HD	CG	Z
1.188	30.18	S-165	3.50	88.9	1.094	27.8	.46	.08	3.0	76	1.4	6.1	.52	13.1	0.047	1.2	11.0	SST	CG	N
1.188	30																			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.203	30.56	12087	2.06	52.4	.933	23.7	78	14	.80	20	63	278	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
1.203	30.56	B18-166	2.28	57.9	1.003	25.5	19	3.4	1.4	36	27	122	.75	19.1	0.100	2.5	7.50	SPR	CG	N
1.203	30.56	S-241	2.34	59.5	.963	24.5	45	7.9	.92	23	42	185	.78	19.8	0.120	3.0	6.50	SST	CG	N
1.203	30.56	S-337	2.38	60.3	.993	25.2	23	4.0	1.3	33	29	131	.74	18.7	0.105	2.7	7.00	SST	CG	N
1.203	30.56	10291	2.38	60.3	.907	23.0	98	17	.84	21	82	364	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.203	30.56	S-281	2.38	60.3	.907	23.0	93	16	.79	20	74	328	1.11	28.2	0.148	3.8	7.50	SST	CG	N
1.203	30.56	3626	2.75	69.9	1.113	28.3	.54	.09	2.3	58	1.2	5.5	.45	11.4	0.045	1.1	9.00	HD	C	Z
1.203	30.56	10461	2.75	69.9	.999	25.4	20	3.6	1.4	36	29	130	.79	20.1	0.102	2.6	7.75	SPR	CG	Z
1.203	30.56	12301	3.00	76.2	1.113	28.3	.54	.09	2.6	66	1.4	6.3	.41	10.3	0.045	1.1	9.00	SPR	CG	Z
1.203	30.56	4339	3.25	82.6	.753	19.1	485	85	.51	13	246	1096	2.36	60.0	0.225	5.7	10.5	SPR	CG	Z
1.203	30.56	12090	3.38	85.7	1.079	27.4	1.6	.28	2.8	70	4.4	19	.62	15.7	0.062	1.6	10.0	SST	CG	N
1.203	30.56	12002	3.38	85.7	1.013	25.7	14	2.5	1.6	42	24	105	.76	19.3	0.095	2.4	8.00	SPR	CG	Z
1.203	30.56	B18-201	3.47	88.1	1.061	26.9	2.5	.43	2.7	68	6.7	30	.78	19.8	0.071	1.8	11.0	SST	CG	N
1.203	30.56	S-306	3.50	88.9	1.033	26.2	6.7	1.2	2.5	63	17	74	.85	21.6	0.085	2.2	9.00	SST	C	N
1.203	30.56	2955	3.56	90.5	1.063	27.0	2.5	.44	2.7	68	6.7	30	.88	22.2	0.070	1.8	11.5	SPR	C	Z
1.203	30.56	2548	4.38	111.1	.983	25.0	14	2.4	2.6	65	35	157	1.51	38.4	0.110	2.8	13.8	SPR	CG	Z
1.203	30.56	1745	5.13	130.2	1.079	27.4	.99	.17	4.0	103	4.0	18	1.09	27.6	0.062	1.6	16.5	SPR	C	Z
1.203	30.56	10974	5.88	149.2	.963	24.5	15	2.6	3.1	79	46	202	2.16	54.9	0.120	3.0	18.0	HD	CG	Z
1.203	30.56	11826	7.25	184.2	.991	25.2	8.7	1.5	3.5	88	30	135	1.80	45.8	0.106	2.7	16.0	SST	C	N
1.203	30.56	1551	7.75	196.9	.909	23.1	25	4.4	3.2	81	80	357	3.63	92.1	0.147	3.7	24.7	SPR	CG	Z
1.203	30.56	S-346	16.0	406.4	1.023	26.0	1.6	.29	11	290	19	83	3.56	90.3	0.090	2.3	38.5	SST	C	N
1.219	30.96	11552	.94	23.8	.949	24.1	.02	.003	.88	22	.02	.07	.06	1.5	0.135	3.4	3.50	MW	CG	Z
1.219	30.96	3444	.94	23.8	.943	24.0	275	48	.24	6.1	66	293	.48	12.3	0.138	3.5	3.50	SPR	CG	Z
1.219	30.96	B10-8	1.00	25.4	.969	24.6	119	21	.39	9.9	46	206	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.219	30.96	S-974	1.16	29.4	.979	24.9	104	18	.39	10	41	182	.47	11.8	0.120	3.0	4.00	SST	CG	N
1.219	30.96	12701	1.31	33.3	1.057	26.8	17	2.9	.87	22	15	65	.45	11.3	0.081	2.1	4.50	SPR	C	N
1.219	30.96	10875	1.31	33.3	1.009	25.6	28	4.9	.68	17	19	85	.63	16.0	0.105	2.7	6.00	SST	CG	N
1.219	30.96	10704	1.38	34.9	1.075	27.3	9.1	1.6	1.1	27	9.5	42	.32	8.2	0.072	1.8	4.50	SST	CG	N
1.219	30.96	12631	1.38	34.9	1.059	26.9	16	2.8	.91	23	15	65	.44	11.2	0.080	2.0	4.50	HD	C	N
1.219	30.96	11353	1.38	34.9	.895	22.7	297	52	.31	7.8	91	406	.73	18.5	0.162	4.1	4.50	SST	CG	N
1.219	30.96	3451	1.44	36.5	1.035	26.3	36	6.3	.59	15	21	94	.37	9.3	0.092	2.3	4.00	HD	CG	Z
1.219	30.96	2885	1.53	38.9	1.017	25.8	37	6.5	.75	19	28	124	.49	12.5	0.101	2.6	5.00	SPR	CG	Z
1.219	30.96	11164	1.63	41.3	.907	23.0	236	41	.39	9.9	92	409	.78	19.8	0.156	4.0	5.00	SPR	CG	Z
1.219	30.96	KK-71	1.75	44.5	1.039	26.4	29	5.1	.63	16	18	82	.36	9.1	0.090	2.3	4.00	SST	CG	N
1.219	30.96	10304	1.75	44.5	1.009	25.6	32	5.5	.99	25	31	139	.74	18.7	0.105	2.7	6.00	SPR	C	Z
1.219	30.96	12096	1.75	44.5	.859	21.8	384	67	.35	8.8	133	593	.99	25.1	0.180	4.6	5.50	SPR	CG	Z
1.219	30.96	11120	1.97	50.0	.879	22.3	198	35	.60	15	118	526	1.23	31.3	0.170	4.3	7.25	SPR	CG	Z
1.219	30.96	11579	2.22	56.4	.951	24.2	60	11	1.0	25	60	269	1.21	30.6	0.134	3.4	8.00	SPR	CG	N
1.219	30.96	4391	2.33	59.1	.923	23.4	94	16	.86	22	81	360	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.219	30.96	S-955	2.34	59.5	1.035	26.3	14	2.4	1.4	36	20	87	.60	15.2	0.092	2.3	6.50	SST	CG	N
1.219	30.96	S-1336	2.38	60.3	1.037	26.3	14	2.4	1.4	36	19	85	.68	17.3	0.091	2.3	6.50	SST	C	N
1.219	30.96	11320	2.38	60.3	.907	23.0	177	31	.52	13	92	409	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
1.219	30.96	B18-194	2.44	61.9	1.129	28.7	.52	.09	2.0	52	1.1	4.7	.41	10.3	0.045	1.1	9.00	SPR	CG	N
1.219	30.96	11932	2.50	63.5	.829	21.1	387	68	.43	11	168	747	1.37	34.7	0.195	5.0	7.00	SPR	CG	N
1.219	30.96	3404	2.75	69.9	1.009	25.6	23	4.0	1.4	35	31	139	.86	21.7	0.105	2.7	8.00	SPR	CG	Z
1.219	30.96	S-3053	2.88	73.0	1.075	27.3	5.6	.97	1.8	46	10	44	.50	12.8	0.072	1.8	6.00	SST	C	N
1.219	30.96	12328	3.00	76.2	1.119	28.4	1.0	.18	2.6	65	2.6	12	.43	10.8	0.050	1.3	7.50	SPR	C	Z
1.219	30.96	S-1375	3.00	76.2	1.117	28.4	.59	.10	2.4	61	1.4	6.3	.61	15.5	0.051	1.3	11.0	SST	C	N
1.219	30.96	B18-182	3.22	81.8	.725	18.4	574	101	.47	12	267	1188	2.72	69.0	0.247	6.3	11.0	SST	CG	N
1.219	30.96	4302	3.25	82.6	1.009	25.6	16	2.8	2.0	50	31	139	1.05	26.7	0.105	2.7	10.0	SPR	CG	Z
1.219	30.96	11858	3.84	97.6	1.043	26.5	7.6	1.3	2.4	61	18	81	.79	20.1	0.088	2.2	9.00	SST	CG	N
1.219	30.96	7056	4.00	101.6	.865	22.0	99	17	1.2	30	118	525	2.48	62.9	0.177	4.5	13.0	SST	C	N
1.219	30.96	10989	4.06	103.2	.805	20.4	255	45	.78	20	199	887	2.48	63.1	0.207	5.3	12.0	HD	CG	Z
1.219	30.96	283	4.50	114.3	.895	22.7	70	12	1.5	37	103	457	2.27	57.6	0.162	4.1	14.0	HD	CG	Z
1.219	30.96	11731	7.50	190.5	.895	22.7	41	7.2	2.5	64	103	457	3.65	92.6	0.162	4.1	22.5	SPR	CG	Z
1.219	30.96	2841	7.75	196.9	.923	23.4	24	4.2	3.4	86	81	360	3.77	95.9	0.148	3.8	25.5	HD	CG	Z
1.219	30.96	4174	12.0	304.8	1.039	26.4	3													




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72680S	1.00	25.4	.975	24.8	114	20	.40	10	46	205	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.225	31.12	72694	1.00	25.4	.955	24.3	183	32	.46	12	84	375	.54	13.7	0.135	3.4	4.00	MW	CG	N
1.225	31.12	72694S	1.00	25.4	.955	24.3	156	27	.36	9.0	55	246	.54	13.7	0.135	3.4	4.00	SST	CG	N
1.225	31.12	72709	1.00	25.4	.929	23.6	270	47	.41	10	110	489	.59	15.0	0.148	3.8	4.00	MW	CG	N
1.225	31.12	72709S	1.00	25.4	.929	23.6	229	40	.32	8.0	73	322	.59	15.0	0.148	3.8	4.00	SST	CG	N
1.225	31.12	72729	1.00	25.4	.901	22.9	415	73	.35	8.8	143	637	.65	16.5	0.162	4.1	4.00	MW	CG	N
1.225	31.12	72729S	1.00	25.4	.901	22.9	352	62	.26	6.5	91	404	.65	16.5	0.162	4.1	4.00	SST	CG	N
1.225	31.12	72639	1.25	31.8	1.033	26.2	39	6.7	.84	21	32	144	.41	10.4	0.096	2.4	4.25	MW	CG	N
1.225	31.12	72639S	1.25	31.8	1.033	26.2	33	5.7	.68	17	22	99	.41	10.4	0.096	2.4	4.25	SST	CG	N
1.225	31.12	72653	1.25	31.8	1.015	25.8	53	9.2	.79	20	42	186	.46	11.7	0.105	2.7	4.38	MW	CG	N
1.225	31.12	72653S	1.25	31.8	1.015	25.8	45	7.9	.64	16	29	129	.46	11.7	0.105	2.7	4.38	SST	CG	N
1.225	31.12	72666	1.25	31.8	1.001	25.4	67	12	.75	19	50	221	.50	12.8	0.112	2.8	4.50	MW	CG	N
1.225	31.12	72666S	1.25	31.8	1.001	25.4	57	9.9	.59	15	33	148	.50	12.8	0.112	2.8	4.50	SST	CG	N
1.225	31.12	72681	1.25	31.8	.975	24.8	101	18	.67	17	68	301	.58	14.7	0.125	3.2	4.63	MW	CG	N
1.225	31.12	72681S	1.25	31.8	.975	24.8	86	15	.54	14	46	205	.58	14.7	0.125	3.2	4.63	SST	CG	N
1.225	31.12	72695	1.25	31.8	.955	24.3	136	24	.61	15	83	369	.64	16.3	0.135	3.4	4.75	MW	CG	N
1.225	31.12	72695S	1.25	31.8	.955	24.3	116	20	.48	12	55	246	.64	16.3	0.135	3.4	4.75	SST	CG	N
1.225	31.12	72710	1.25	31.8	.929	23.6	199	35	.55	14	109	484	.70	17.9	0.148	3.8	4.75	MW	CG	N
1.225	31.12	72710S	1.25	31.8	.929	23.6	169	30	.43	11	73	322	.70	17.9	0.148	3.8	4.75	SST	CG	N
1.225	31.12	72629	1.50	38.1	1.055	26.8	19	3.4	1.1	28	21	96	.39	10.0	0.085	2.2	4.63	MW	CG	N
1.225	31.12	72629S	1.50	38.1	1.055	26.8	16	2.9	.99	25	16	72	.39	10.0	0.085	2.2	4.63	SST	CG	N
1.225	31.12	72640	1.50	38.1	1.033	26.2	31	5.4	1.0	27	32	144	.46	11.6	0.096	2.4	4.75	MW	CG	N
1.225	31.12	72640S	1.50	38.1	1.033	26.2	26	4.6	.84	21	22	99	.46	11.6	0.096	2.4	4.75	SST	CG	N
1.225	31.12	72654	1.50	38.1	1.015	25.8	43	7.4	.99	25	42	187	.51	13.0	0.105	2.7	4.88	MW	CG	N
1.225	31.12	72654S	1.50	38.1	1.015	25.8	36	6.3	.80	20	29	129	.51	13.0	0.105	2.7	4.88	SST	CG	N
1.225	31.12	72667	1.50	38.1	1.001	25.4	54	9.4	.94	24	50	224	.56	14.2	0.112	2.8	5.00	MW	CG	N
1.225	31.12	72667S	1.50	38.1	1.001	25.4	46	8.0	.73	19	33	148	.56	14.2	0.112	2.8	5.00	SST	CG	N
1.225	31.12	72682	1.50	38.1	.975	24.8	81	14	.84	21	68	302	.66	16.7	0.125	3.2	5.25	MW	CG	N
1.225	31.12	72682S	1.50	38.1	.975	24.8	69	12	.67	17	46	205	.66	16.7	0.125	3.2	5.25	SST	CG	N
1.225	31.12	72696	1.50	38.1	.955	24.3	116	20	.74	19	86	383	.69	17.6	0.135	3.4	5.13	MW	CG	N
1.225	31.12	72696S	1.50	38.1	.955	24.3	98	17	.56	14	55	246	.69	17.6	0.135	3.4	5.13	SST	CG	N
1.225	31.12	72711	1.50	38.1	.929	23.6	158	28	.69	17	108	481	.81	20.7	0.148	3.8	5.50	MW	CG	N
1.225	31.12	72711S	1.50	38.1	.929	23.6	134	23	.54	14	73	322	.81	20.7	0.148	3.8	5.50	SST	CG	N
1.225	31.12	72730	1.50	38.1	.901	22.9	238	42	.60	15	143	637	.89	22.6	0.162	4.1	5.50	MW	CG	N
1.225	31.12	72730S	1.50	38.1	.901	22.9	203	35	.45	11	91	404	.89	22.6	0.162	4.1	5.50	SST	CG	N
1.225	31.12	72743	1.50	38.1	.871	22.1	353	62	.52	13	185	824	.97	24.7	0.177	4.5	5.50	MW	CG	N
1.225	31.12	72743S	1.50	38.1	.871	22.1	300	53	.39	9.9	118	523	.97	24.7	0.177	4.5	5.50	SST	CG	N
1.225	31.12	72751	1.50	38.1	.841	21.4	516	90	.44	11	226	1005	1.03	26.2	0.192	4.9	5.38	MW	CG	N
1.225	31.12	72751S	1.50	38.1	.841	21.4	439	77	.31	8.0	138	613	1.03	26.2	0.192	4.9	5.38	SST	CG	N
1.225	31.12	72641	1.75	44.5	1.033	26.2	26	4.6	1.2	32	33	145	.50	12.8	0.096	2.4	5.25	MW	CG	N
1.225	31.12	72641S	1.75	44.5	1.033	26.2	22	3.9	1.0	25	22	99	.50	12.8	0.096	2.4	5.25	SST	CG	N
1.225	31.12	72656	1.75	44.5	1.015	25.8	37	6.5	1.2	30	44	194	.56	14.3	0.105	2.7	5.38	MW	CG	N
1.225	31.12	72656S	1.75	44.5	1.015	25.8	31	5.5	.92	23	29	129	.56	14.3	0.105	2.7	5.38	SST	CG	N
1.225	31.12	72669	1.75	44.5	1.001	25.4	51	8.9	1.0	25	51	227	.59	14.9	0.112	2.8	5.25	MW	CG	N
1.225	31.12	72669S	1.75	44.5	1.001	25.4	43	7.6	.77	19	33	148	.59	14.9	0.112	2.8	5.25	SST	CG	N
1.225	31.12	72683	1.75	44.5	.975	24.8	67	12	1.0	26	68	304	.73	18.7	0.125	3.2	5.88	MW	CG	N
1.225	31.12	72683S	1.75	44.5	.975	24.8	57	10	.81	20	46	205	.73	18.7	0.125	3.2	5.88	SST	CG	N
1.225	31.12	72698	1.75	44.5	.955	24.3	92	16	.93	24	86	383	.81	20.6	0.135	3.4	6.00	MW	CG	N
1.225	31.12	72698S	1.75	44.5	.955	24.3	78	14	.71	18	55	246	.81	20.6	0.135	3.4	6.00	SST	CG	N
1.225	31.12	72713	1.75	44.5	.929	23.6	134	23	.84	21	113	501	.91	23.0	0.148	3.8	6.13	MW	CG	N
1.225	31.12	72713S	1.75	44.5	.929	23.6	114	20	.64	16	73	322	.91	23.0	0.148	3.8	6.13	SST	CG	N
1.225	31.12	72630	2.00	50.8	1.055	26.8	14	2.5	1.5	39	21	95	.48	12.1	0.085	2.2	5.63	MW	CG	N
1.225	31.12	72630S	2.00	50.8	1.055	26.8	12	2.1	1.4	34	16	72	.48	12.1	0.085	2.2	5.63	SST	CG	N
1.225	31.12	72642	2.00	50.8	1.033	26.2	23	3.9	1.4	37	33	145	.55	14.0	0.096	2.4	5.75	MW	CG	N
1.225	31.12	72642S	2.00	50.8	1.033	26.2	19	3.3	1.2	29	22	99	.55	14.0	0.096	2.4	5.75	SST	CG	N
1.225	31.12	72657	2.00	50.8	1.015	25.8	31	5.4	1.4	35	42	187	.63	16.0	0.105	2.7	6.00	MW	CG	N
1.225	31.12	72657S	2.00	50.8	1.015	25.8	26	4.6	1.1	28	29	129	.63							




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72732S	2.25	57.2	.901	22.9	128	22	.71	18	91	404	1.22	30.9	0.162	4.1	7.50	SST	CG	N
1.225	31.12	72631	2.50	63.5	1.055	26.8	11	1.9	1.9	49	21	96	.56	14.3	0.085	2.2	6.63	MW	CG	N
1.225	31.12	72631S	2.50	63.5	1.055	26.8	9.4	1.7	1.7	44	16	72	.56	14.3	0.085	2.2	6.63	SST	CG	N
1.225	31.12	72644	2.50	63.5	1.033	26.2	18	3.1	1.8	47	32	144	.66	16.8	0.096	2.4	6.88	MW	CG	N
1.225	31.12	72644S	2.50	63.5	1.033	26.2	15	2.6	1.5	38	22	99	.66	16.8	0.096	2.4	6.88	SST	CG	N
1.225	31.12	72658	2.50	63.5	1.015	25.8	24	4.2	1.8	44	42	187	.75	19.0	0.105	2.7	7.13	MW	CG	N
1.225	31.12	72658S	2.50	63.5	1.015	25.8	20	3.6	1.4	36	29	129	.75	19.0	0.105	2.7	7.13	SST	CG	N
1.225	31.12	72671	2.50	63.5	1.001	25.4	30	5.3	1.7	42	50	222	.84	21.3	0.112	2.8	7.50	MW	CG	N
1.225	31.12	72671S	2.50	63.5	1.001	25.4	26	4.5	1.3	33	33	148	.84	21.3	0.112	2.8	7.50	SST	CG	N
1.225	31.12	72686	2.50	63.5	.975	24.8	45	7.8	1.5	38	68	302	.98	25.0	0.125	3.2	7.88	MW	CG	N
1.225	31.12	72686S	2.50	63.5	.975	24.8	38	6.7	1.2	31	46	205	.98	25.0	0.125	3.2	7.88	SST	CG	N
1.225	31.12	72700	2.50	63.5	.955	24.3	64	11	1.3	34	86	383	1.05	26.6	0.135	3.4	7.75	MW	CG	N
1.225	31.12	72700S	2.50	63.5	.955	24.3	54	9.5	1.0	26	55	246	1.05	26.6	0.135	3.4	7.75	SST	CG	N
1.225	31.12	72715	2.50	63.5	.929	23.6	86	15	1.3	32	109	483	1.24	31.5	0.148	3.8	8.38	MW	CG	N
1.225	31.12	72715S	2.50	63.5	.929	23.6	73	13	.99	25	73	322	1.24	31.5	0.148	3.8	8.38	SST	CG	N
1.225	31.12	72722	2.50	63.5	.913	23.2	113	20	1.1	29	128	571	1.27	32.2	0.156	4.0	8.13	MW	CG	N
1.225	31.12	72722S	2.50	63.5	.913	23.2	96	17	.85	22	81	362	1.27	32.2	0.156	4.0	8.13	SST	CG	N
1.225	31.12	72733	2.50	63.5	.901	22.9	131	23	1.1	28	143	637	1.34	33.9	0.162	4.1	8.25	MW	CG	N
1.225	31.12	72733S	2.50	63.5	.901	22.9	111	19	.82	21	91	404	1.34	33.9	0.162	4.1	8.25	SST	CG	N
1.225	31.12	72745	2.50	63.5	.871	22.1	189	33	.98	25	185	824	1.50	38.2	0.177	4.5	8.50	MW	CG	N
1.225	31.12	72745S	2.50	63.5	.871	22.1	160	28	.73	19	118	523	1.50	38.2	0.177	4.5	8.50	SST	CG	N
1.225	31.12	72753	2.50	63.5	.841	21.4	272	48	.83	21	226	1005	1.63	41.5	0.192	4.9	8.50	MW	CG	N
1.225	31.12	72753S	2.50	63.5	.841	21.4	231	41	.60	15	138	613	1.63	41.5	0.192	4.9	8.50	SST	CG	N
1.225	31.12	72760	2.50	63.5	.811	20.6	384	67	.73	19	281	1248	1.76	44.7	0.207	5.3	8.50	MW	CG	N
1.225	31.12	72760S	2.50	63.5	.811	20.6	326	57	.52	13	171	761	1.76	44.7	0.207	5.3	8.50	SST	CG	N
1.225	31.12	72645	2.75	69.9	1.033	26.2	16	2.8	2.0	52	32	144	.71	18.0	0.096	2.4	7.38	MW	CG	N
1.225	31.12	72645S	2.75	69.9	1.033	26.2	14	2.4	1.6	42	22	99	.71	18.0	0.096	2.4	7.38	SST	CG	N
1.225	31.12	72687	2.75	69.9	.975	24.8	40	7.1	1.7	43	68	302	1.06	27.0	0.125	3.2	8.50	MW	CG	N
1.225	31.12	72687S	2.75	69.9	.975	24.8	34	6.0	1.3	34	46	205	1.06	27.0	0.125	3.2	8.50	SST	CG	N
1.225	31.12	72632	3.00	76.2	1.055	26.8	9.1	1.6	2.4	60	21	95	.65	16.5	0.085	2.2	7.63	MW	CG	N
1.225	31.12	72632S	3.00	76.2	1.055	26.8	7.7	1.4	2.1	53	16	72	.65	16.5	0.085	2.2	7.63	SST	CG	N
1.225	31.12	72646	3.00	76.2	1.033	26.2	15	2.5	2.2	57	33	145	.76	19.2	0.096	2.4	7.88	MW	CG	N
1.225	31.12	72646S	3.00	76.2	1.033	26.2	12	2.2	1.8	46	22	99	.76	19.2	0.096	2.4	7.88	SST	CG	N
1.225	31.12	72659	3.00	76.2	1.015	25.8	20	3.4	2.1	54	42	186	.88	22.3	0.105	2.7	8.38	MW	CG	N
1.225	31.12	72659S	3.00	76.2	1.015	25.8	17	2.9	1.7	44	29	129	.88	22.3	0.105	2.7	8.38	SST	CG	N
1.225	31.12	72672	3.00	76.2	1.001	25.4	25	4.3	2.0	52	50	223	.97	24.5	0.112	2.8	8.63	MW	CG	N
1.225	31.12	72672S	3.00	76.2	1.001	25.4	21	3.7	1.6	40	33	148	.97	24.5	0.112	2.8	8.63	SST	CG	N
1.225	31.12	72688	3.00	76.2	.975	24.8	37	6.4	1.9	47	68	304	1.14	29.0	0.125	3.2	9.13	MW	CG	N
1.225	31.12	72688S	3.00	76.2	.975	24.8	31	5.5	1.5	37	46	205	1.14	29.0	0.125	3.2	9.13	SST	CG	N
1.225	31.12	72701	3.00	76.2	.955	24.3	52	9.1	1.6	42	86	383	1.23	31.3	0.135	3.4	9.13	MW	CG	N
1.225	31.12	72701S	3.00	76.2	.955	24.3	44	7.8	1.2	32	55	246	1.23	31.3	0.135	3.4	9.13	SST	CG	N
1.225	31.12	72716	3.00	76.2	.929	23.6	70	12	1.5	39	108	480	1.46	37.1	0.148	3.8	9.88	MW	CG	N
1.225	31.12	72716S	3.00	76.2	.929	23.6	60	10	1.2	31	73	322	1.46	37.1	0.148	3.8	9.88	SST	CG	N
1.225	31.12	72723	3.00	76.2	.913	23.2	93	16	1.4	35	128	571	1.48	37.6	0.156	4.0	9.50	MW	CG	N
1.225	31.12	72723S	3.00	76.2	.913	23.2	79	14	1.0	26	81	362	1.48	37.6	0.156	4.0	9.50	SST	CG	N
1.225	31.12	72734	3.00	76.2	.901	22.9	107	19	1.3	34	143	637	1.56	39.6	0.162	4.1	9.63	MW	CG	N
1.225	31.12	72734S	3.00	76.2	.901	22.9	91	16	1.0	25	91	404	1.56	39.6	0.162	4.1	9.63	SST	CG	N
1.225	31.12	72746	3.00	76.2	.871	22.1	153	27	1.2	31	185	824	1.77	45.0	0.177	4.5	10.0	MW	CG	N
1.225	31.12	72746S	3.00	76.2	.871	22.1	130	23	.90	23	118	523	1.77	45.0	0.177	4.5	10.0	SST	CG	N
1.225	31.12	72754	3.00	76.2	.841	21.4	220	39	1.0	26	226	1005	1.92	48.8	0.192	4.9	10.0	MW	CG	N
1.225	31.12	72754S	3.00	76.2																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72736S	3.75	95.3	.901	22.9	72	13	1.3	32	91	404	1.90	48.3	0.162	4.1	11.8	SST	CG	N
1.225	31.12	72634	4.00	101.6	1.055	26.8	6.7	1.2	3.2	81	21	95	.81	20.5	0.085	2.2	9.50	MW	CG	N
1.225	31.12	72634S	4.00	101.6	1.055	26.8	5.7	1.0	2.9	73	16	72	.81	20.5	0.085	2.2	9.50	SST	CG	N
1.225	31.12	72648	4.00	101.6	1.033	26.2	11	1.9	3.1	78	33	145	.95	24.1	0.096	2.4	9.88	MW	CG	N
1.225	31.12	72648S	4.00	101.6	1.033	26.2	9.1	1.6	2.4	62	22	99	.95	24.1	0.096	2.4	9.88	SST	CG	N
1.225	31.12	72661	4.00	101.6	1.015	25.8	15	2.5	2.9	73	42	186	1.12	28.3	0.105	2.7	10.6	MW	CG	N
1.225	31.12	72661S	4.00	101.6	1.015	25.8	12	2.2	2.3	60	29	129	1.12	28.3	0.105	2.7	10.6	SST	CG	N
1.225	31.12	72674	4.00	101.6	1.001	25.4	18	3.2	2.8	70	50	222	1.25	31.6	0.112	2.8	11.1	MW	CG	N
1.225	31.12	72674S	4.00	101.6	1.001	25.4	15	2.7	2.2	55	33	148	1.25	31.6	0.112	2.8	11.1	SST	CG	N
1.225	31.12	72690	4.00	101.6	.975	24.8	27	4.7	2.5	64	68	303	1.47	37.3	0.125	3.2	11.8	MW	CG	N
1.225	31.12	72690S	4.00	101.6	.975	24.8	23	4.0	2.0	51	46	205	1.47	37.3	0.125	3.2	11.8	SST	CG	N
1.225	31.12	72703	4.00	101.6	.955	24.3	41	7.1	2.1	54	86	383	1.50	38.1	0.135	3.4	11.1	MW	CG	N
1.225	31.12	72703S	4.00	101.6	.955	24.3	34	6.0	1.6	41	55	246	1.50	38.1	0.135	3.4	11.1	SST	CG	N
1.225	31.12	72718	4.00	101.6	.929	23.6	51	9.0	2.1	54	108	481	1.89	47.9	0.148	3.8	12.8	MW	CG	N
1.225	31.12	72718S	4.00	101.6	.929	23.6	44	7.6	1.7	42	73	322	1.89	47.9	0.148	3.8	12.8	SST	CG	N
1.225	31.12	72726	4.00	101.6	.913	23.2	68	12	1.9	48	128	571	1.91	48.5	0.156	4.0	12.3	MW	CG	N
1.225	31.12	72726S	4.00	101.6	.913	23.2	58	10	1.4	36	81	362	1.91	48.5	0.156	4.0	12.3	SST	CG	N
1.225	31.12	72737	4.00	101.6	.901	22.9	78	14	1.8	47	143	637	2.05	51.9	0.162	4.1	12.6	MW	CG	N
1.225	31.12	72737S	4.00	101.6	.901	22.9	66	12	1.4	35	91	404	2.05	51.9	0.162	4.1	12.6	SST	CG	N
1.225	31.12	72748	4.00	101.6	.871	22.1	111	19	1.7	42	185	824	2.30	58.4	0.177	4.5	13.0	MW	CG	N
1.225	31.12	72748S	4.00	101.6	.871	22.1	94	17	1.2	32	118	523	2.30	58.4	0.177	4.5	13.0	SST	CG	N
1.225	31.12	72756	4.00	101.6	.841	21.4	159	28	1.4	36	226	1005	2.52	64.0	0.192	4.9	13.1	MW	CG	N
1.225	31.12	72756S	4.00	101.6	.841	21.4	135	24	1.0	26	138	613	2.52	64.0	0.192	4.9	13.1	SST	CG	N
1.225	31.12	72763	4.00	101.6	.811	20.6	223	39	1.3	32	281	1248	2.74	69.7	0.207	5.3	13.3	MW	CG	N
1.225	31.12	72763S	4.00	101.6	.811	20.6	190	33	.90	23	171	761	2.74	69.7	0.207	5.3	13.3	SST	CG	N
1.225	31.12	72635	4.50	114.3	1.055	26.8	6.0	1.1	3.6	92	22	96	.89	22.7	0.085	2.2	10.5	MW	CG	N
1.225	31.12	72635S	4.50	114.3	1.055	26.8	5.1	.89	3.2	81	16	72	.89	22.7	0.085	2.2	10.5	SST	CG	N
1.225	31.12	72649	4.50	114.3	1.033	26.2	9.5	1.7	3.5	88	33	146	1.04	26.5	0.096	2.4	10.9	MW	CG	N
1.225	31.12	72649S	4.50	114.3	1.033	26.2	8.1	1.4	2.7	70	22	99	1.04	26.5	0.096	2.4	10.9	SST	CG	N
1.225	31.12	72662	4.50	114.3	1.015	25.8	13	2.2	3.3	83	42	186	1.23	31.3	0.105	2.7	11.8	MW	CG	N
1.225	31.12	72662S	4.50	114.3	1.015	25.8	11	1.9	2.7	67	29	129	1.23	31.3	0.105	2.7	11.8	SST	CG	N
1.225	31.12	72676	4.50	114.3	1.001	25.4	18	3.2	2.8	71	51	227	1.23	31.3	0.112	2.8	11.0	MW	CG	N
1.225	31.12	72676S	4.50	114.3	1.001	25.4	15	2.7	2.2	55	33	148	1.23	31.3	0.112	2.8	11.0	SST	CG	N
1.225	31.12	72691	4.50	114.3	.975	24.8	24	4.2	2.9	73	68	301	1.64	41.7	0.125	3.2	13.1	MW	CG	N
1.225	31.12	72691S	4.50	114.3	.975	24.8	20	3.5	2.3	58	46	205	1.64	41.7	0.125	3.2	13.1	SST	CG	N
1.225	31.12	72705	4.50	114.3	.955	24.3	32	5.7	2.7	68	86	383	1.81	45.9	0.135	3.4	13.4	MW	CG	N
1.225	31.12	72705S	4.50	114.3	.955	24.3	27	4.8	2.0	51	55	246	1.81	45.9	0.135	3.4	13.4	SST	CG	N
1.225	31.12	72719	4.50	114.3	.929	23.6	45	7.9	2.4	61	108	480	2.11	53.6	0.148	3.8	14.3	MW	CG	N
1.225	31.12	72719S	4.50	114.3	.929	23.6	38	6.7	1.9	48	73	322	2.11	53.6	0.148	3.8	14.3	SST	CG	N
1.225	31.12	72727	4.50	114.3	.913	23.2	60	11	2.1	54	128	571	2.13	54.0	0.156	4.0	13.6	MW	CG	N
1.225	31.12	72727S	4.50	114.3	.913	23.2	51	8.9	1.6	41	81	362	2.13	54.0	0.156	4.0	13.6	SST	CG	N
1.225	31.12	72738	4.50	114.3	.901	22.9	69	12	2.1	53	143	637	2.27	57.6	0.162	4.1	14.0	MW	CG	N
1.225	31.12	72738S	4.50	114.3	.901	22.9	58	10	1.6	40	91	404	2.27	57.6	0.162	4.1	14.0	SST	CG	N
1.225	31.12	72749	4.50	114.3	.871	22.1	98	17	1.9	48	185	824	2.57	65.2	0.177	4.5	14.5	MW	CG	N
1.225	31.12	72749S	4.50	114.3	.871	22.1	83	15	1.4	36	118	523	2.57	65.2	0.177	4.5	14.5	SST	CG	N
1.225	31.12	72757	4.50	114.3	.841	21.4	140	24	1.6	41	226	1005	2.81	71.3	0.192	4.9	14.6	MW	CG	N
1.225	31.12	72757S	4.50	114.3	.841	21.4	119	21	1.2	29	138	613	2.81	71.3	0.192	4.9	14.6	SST	CG	N
1.225	31.12	72764	4.50	114.3	.811	20.6	196	34	1.4	36	281	1248	3.05	77.6	0.207	5.3	14.8	MW	CG	N
1.225	31.12	72764S	4.50	114.3	.811	20.6	167	29	1.0	26	171	761								




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.234	31.34	II-92	.78	19.8	1.074	27.3	38	6.7	.38	9.5	14	64	.24	6.1	0.080	2.0	3.00	SPR	CG	N
1.234	31.34	3237	.84	21.4	1.082	27.5	31	5.4	.40	10	12	55	.23	5.8	0.076	1.9	3.00	SPR	CG	Z
1.234	31.34	3045	.88	22.2	1.110	28.2	7.0	1.2	.63	16	4.5	20	.24	6.1	0.062	1.6	4.00	SPR	CG	Z
1.234	31.34	1805	.88	22.2	1.080	27.4	33	5.7	.55	14	18	80	.23	5.9	0.077	2.0	3.00	MW	CG	Z
1.234	31.34	EE-77	.94	23.8	.954	24.2	281	49	.24	6.1	68	302	.49	12.4	0.140	3.6	3.50	SPR	CG	Z
1.234	31.34	12495	1.03	26.2	1.040	26.4	58	10	.42	11	24	109	.34	8.6	0.097	2.5	3.50	SPR	CG	Z
1.234	31.34	12094	1.19	30.2	.984	25.0	103	18	.49	12	50	223	.56	14.3	0.125	3.2	4.50	SPR	CG	Z
1.234	31.34	11597	1.31	33.3	.994	25.2	54	9.4	.47	12	25	113	.84	21.3	0.120	3.0	6.00	SPR	CG	Z
1.234	31.34	10120	1.38	34.9	1.100	27.9	3.7	.64	.91	23	3.3	15	.47	11.9	0.067	1.7	7.00	SPR	CG	Z
1.234	31.34	10499	1.41	35.7	1.040	26.4	58	10	.42	11	24	109	.34	8.6	0.097	2.5	3.50	SPR	CG	Z
1.234	31.34	10913	1.44	36.5	1.122	28.5	1.6	.29	1.1	27	1.8	7.8	.37	9.5	0.056	1.4	6.67	SST	CG	N
1.234	31.34	3202	1.50	38.1	1.080	27.4	8.7	1.5	1.1	27	9.2	41	.44	11.2	0.077	2.0	5.75	SPR	CG	Z
1.234	31.34	3430	1.63	41.3	1.050	26.7	28	4.8	.76	19	21	93	.41	10.5	0.092	2.3	4.50	SPR	CG	Z
1.234	31.34	2663	1.63	41.3	.910	23.1	268	47	.38	9.6	102	452	.81	20.6	0.162	4.1	5.00	SPR	CG	Z
1.234	31.34	S-338	1.75	44.5	1.110	28.2	2.3	.40	1.3	33	3.0	13	.43	11.0	0.062	1.6	7.00	SST	CG	N
1.234	31.34	S-1677	1.75	44.5	1.026	26.1	26	4.5	1.1	27	28	124	.62	15.8	0.104	2.6	6.00	SST	CG	N
1.234	31.34	S-963	1.81	46.0	1.066	27.1	20	3.6	.76	19	16	69	.34	8.5	0.084	2.1	4.00	SST	CG	N
1.234	31.34	EE-88	2.00	50.8	.694	17.6	2132	373	.18	4.6	390	1734	1.62	41.1	0.270	6.9	6.00	SPR	CG	Z
1.234	31.34	12000	2.25	57.2	.848	21.5	272	48	.59	15	161	717	1.64	41.7	0.193	4.9	8.50	SPR	CG	Z
1.234	31.34	2641	2.34	59.5	1.024	26.0	24	4.3	1.5	38	36	162	.84	21.3	0.105	2.7	7.00	MW	C	Z
1.234	31.34	PP-44	2.69	68.2	1.134	28.8	.40	.07	1.9	47	.75	3.3	.83	21.0	0.050	1.3	15.5	SPR	C	Z
1.234	31.34	10578	2.75	69.9	1.024	26.0	20	3.5	1.5	39	31	138	.84	21.3	0.105	2.7	8.00	SPR	CG	Z
1.234	31.34	1759	2.78	70.6	1.064	27.0	11	2.0	1.5	39	17	77	.50	12.6	0.085	2.2	6.00	SPR	CG	Z
1.234	31.34	S-3061	3.13	79.4	1.062	27.0	10	1.8	1.7	42	17	74	.65	16.4	0.086	2.2	6.50	SST	C	N
1.234	31.34	11787	3.16	80.2	.852	21.6	211	37	.74	19	156	696	1.91	48.5	0.191	4.9	10.0	SPR	CG	Z
1.234	31.34	3465	3.50	88.9	.794	20.2	359	63	.63	16	226	1006	2.42	61.5	0.220	5.6	11.0	SPR	CG	N
1.234	31.34	S-458	3.63	92.1	1.110	28.2	.96	.17	2.8	70	2.6	12	.87	22.0	0.062	1.6	14.0	SST	CG	N
1.234	31.34	2724	4.00	101.6	.994	25.2	21	3.7	2.1	54	44	198	1.59	40.4	0.120	3.0	12.3	HD	C	Z
1.234	31.34	2768	4.19	106.4	.964	24.5	36	6.3	1.7	43	61	272	1.62	41.1	0.135	3.4	12.0	SPR	CG	Z
1.234	31.34	397	5.44	138.1	.880	22.4	94	16	1.4	36	131	585	2.61	66.3	0.177	4.5	14.8	SPR	CG	Z
1.234	31.34	10341	6.00	152.4	.820	20.8	174	30	1.1	29	197	878	3.31	84.1	0.207	5.3	16.0	SPR	CG	Z
1.250	31.75	BB-44	.50	12.7	1.176	29.9	1.3	.23	.35	8.9	.46	2.1	.15	3.8	0.037	0.9	3.00	SST	C	N
1.250	31.75	10830	.50	12.7	1.070	27.2	54	9.4	.23	5.8	12	55	.27	6.9	0.090	2.3	3.00	SST	CG	N
1.250	31.75	2891	.63	15.9	1.126	28.6	5.3	.93	.35	9.0	1.9	8.4	.27	6.9	0.062	1.6	4.33	SPR	CG	Z
1.250	31.75	10971	.75	19.1	1.060	26.9	67	12	.31	7.9	21	94	.29	7.2	0.095	2.4	3.00	SST	CG	N
1.250	31.75	12207	.75	19.1	1.050	26.7	47	8.3	.35	8.9	17	74	.40	10.2	0.100	2.5	4.00	SPR	CG	Z
1.250	31.75	3963	.75	19.1	1.046	26.6	118	21	.24	6.1	28	125	.29	7.4	0.102	2.6	3.00	SPR	CG	Z
1.250	31.75	2887	.94	23.8	1.130	28.7	7.4	1.3	.73	18	5.4	24	.21	5.3	0.060	1.5	3.50	SPR	CG	Z
1.250	31.75	10231	1.06	27.0	.800	20.3	1955	342	.12	3.1	239	1061	.84	21.4	0.225	5.7	3.75	SPR	CG	Z
1.250	31.75	S-3158	1.13	28.6	1.068	27.1	20	3.5	.69	18	14	62	.43	11.0	0.091	2.3	4.75	SST	CG	N
1.250	31.75	S-148	1.25	31.8	1.126	28.6	5.5	.96	.94	24	5.2	23	.31	7.9	0.062	1.6	4.00	SST	C	N
1.250	31.75	829	1.25	31.8	1.010	25.7	89	16	.50	13	44	195	.64	16.3	0.120	3.0	4.33	HD	C	Z
1.250	31.75	S-1436	1.31	33.3	1.040	26.4	40	7.1	.70	18	28	126	.47	12.0	0.105	2.7	4.50	SST	CG	N
1.250	31.75	3044	1.34	34.1	1.106	28.1	7.9	1.4	.98	25	7.7	34	.36	9.1	0.072	1.8	5.00	SPR	CG	Z
1.250	31.75	S-475	1.38	34.9	.8															




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.250	31.75	33	4.00	101.6	.800	20.3	302	53	.79	20	239	1061	3.00	76.2	0.225	5.7	13.3	HD	CG	Z
1.250	31.75	4264	4.50	114.3	1.010	25.7	23	4.0	1.9	49	44	195	1.44	36.6	0.120	3.0	11.0	SPR	C	Z
1.250	31.75	3179	4.59	116.7	1.024	26.0	10	1.8	2.6	65	26	115	2.02	51.3	0.113	2.9	18.0	SPR	CG	Z
1.250	31.75	11681	4.63	117.5	.980	24.9	26	4.5	2.4	60	60	268	2.09	53.1	0.135	3.4	15.5	SPR	CG	Z
1.250	31.75	S-954	4.75	120.7	1.124	28.5	.74	.13	3.6	90	2.6	12	1.20	30.4	0.063	1.6	18.0	SST	C	N
1.250	31.75	1765	4.75	120.7	1.068	27.1	5.8	1.0	3.5	88	20	89	1.18	30.0	0.091	2.3	13.0	HD	CG	Z
1.250	31.75	4100	5.00	127.0	.814	20.7	328	57	.69	18	226	1007	2.40	60.9	0.218	5.5	11.0	SPR	CG	Z
1.250	31.75	3145	5.06	128.6	.896	22.8	143	25	.91	23	130	578	1.77	45.0	0.177	4.5	10.0	SPR	CG	Z
1.250	31.75	12772	5.75	146.1	.950	24.1	36	6.2	2.15	56	77.4	344	2.56	65.1	0.148	3.8	16.3	HD	C	Z
1.250	31.75	3448	6.00	152.4	1.136	28.9	1.1	.20	4.9	124	5.5	24	.63	15.9	0.057	1.4	10.0	SPR	C	Z
1.250	31.75	248	6.25	158.8	.926	23.5	51	9.0	2.0	50	100	447	2.75	70.0	0.162	4.1	17.0	HD	CG	Z
1.250	31.75	3043	6.38	161.9	.990	25.1	19	3.2	2.9	74	54	240	2.31	58.6	0.130	3.3	17.8	SPR	CG	Z
1.250	31.75	S-959	6.88	174.6	.956	24.3	22	3.8	3.2	81	70	310	3.23	82.1	0.147	3.7	22.0	SST	CG	N
1.250	31.75	3210	7.00	177.8	.926	23.5	57	10	1.8	45	100	447	2.51	63.8	0.162	4.1	15.5	SPR	CG	Z
1.250	31.75	2725	7.63	193.7	.954	24.2	26	4.6	3.0	76	79	351	3.18	80.8	0.148	3.8	21.5	SPR	CG	Z
1.250	31.75	12648	8.00	203.2	1.066	27.1	12	2.1	1.7	44	21	92	.78	19.9	0.092	2.3	7.50	SPR	C	Z
1.250	31.75	12658	8.00	203.2	1.062	27.0	4.6	.81	6.2	158	29	128	1.76	44.8	0.094	2.4	17.8	MW	C	Z
1.250	31.75	4181	8.00	203.2	1.010	25.7	9.8	1.7	4.5	113	44	195	2.88	73.2	0.120	3.0	23.0	SPR	C	Z
1.250	31.75	849	8.00	203.2	.926	23.5	32	5.6	3.1	80	100	447	4.21	107.0	0.162	4.1	26.0	HD	CG	Z
1.250	31.75	2996	8.38	212.7	1.022	26.0	7.3	1.3	5.2	132	38	168	2.82	71.7	0.114	2.9	24.8	SPR	CG	Z
1.250	31.75	822	10.0	254.0	.954	24.2	18	3.2	4.3	110	79	351	4.48	113.7	0.148	3.8	30.3	HD	CG	Z
1.250	31.75	3460	11.8	298.5	1.066	27.1	2.8	.48	7.5	190	21	92	2.48	63.1	0.092	2.3	26.0	HD	C	GI
1.250	31.75	868	12.0	304.8	1.010	25.7	6.7	1.2	6.6	167	44	195	4.08	103.6	0.120	3.0	33.0	HD	C	Z
1.250	31.75	860	12.0	304.8	.980	24.9	11	1.8	5.7	146	60	268	4.83	122.6	0.135	3.4	34.8	HD	C	Z
1.250	31.75	839	12.0	304.8	.866	22.0	55	9.6	2.9	73	157	699	6.14	156.1	0.192	4.9	32.0	HD	CG	Z
1.250	31.75	802	12.0	304.8	.836	21.2	67	12	2.9	73	195	868	7.56	191.9	0.207	5.3	36.5	HD	CG	Z
1.250	31.75	834	12.0	304.8	.800	20.3	93	16	2.6	65	239	1061	8.72	221.5	0.225	5.7	38.8	HD	CG	Z
1.250	31.75	S-3047	16.0	406.4	1.070	27.2	1.5	.26	12	313	18	80	3.51	89.2	0.090	2.3	38.0	SST	C	N
1.250	31.75	4000	19.0	482.6	1.000	25.4	5.9	1.0	8.4	214	50	220	5.50	139.7	0.125	3.2	44.0	SPR	CG	Z
1.250	31.75	4045	24.8	628.7	.750	19.1	97	17	3.3	84	322	1431	15.0	381.0	0.250	6.4	60.0	SPR	CG	Z
1.266	32.16	S-3199	.75	19.1	1.124	28.5	19	3.3	.49	12	9.2	41	.21	5.4	0.071	1.8	3.00	SST	CG	N
1.266	32.16	2957	1.41	35.7	1.056	26.8	45	7.8	.68	17	30	134	.47	12.0	0.105	2.7	4.50	SPR	CG	Z
1.266	32.16	10292	1.44	36.5	1.094	27.8	19	3.4	.91	23	17	77	.39	9.8	0.086	2.2	4.50	SPR	CG	Z
1.266	32.16	11212	1.53	38.9	.926	23.5	304	53	.38	9.5	114	508	.85	21.6	0.170	4.3	5.00	SPR	CG	Z
1.266	32.16	11210	1.63	41.3	.970	24.6	165	29	.47	12	78	347	.89	22.6	0.148	3.8	5.00	SPR	C	Z
1.266	32.16	2600	1.75	44.5	1.056	26.8	41	7.1	1.0	26	42	188	.50	12.7	0.105	2.7	4.75	MW	CG	Z
1.266	32.16	11796	1.97	50.0	1.164	29.6	1.1	.19	1.6	42	1.7	7.8	.33	8.4	0.051	1.3	6.50	SST	CG	N
1.266	32.16	B18-186	2.03	51.6	.766	19.5	1357	238	.20	5.0	268	1192	1.38	34.9	0.250	6.4	5.50	SST	CG	N
1.266	32.16	11857	2.47	62.7	1.128	28.7	6.3	1.1	1.5	38	9.5	42	.35	8.8	0.069	1.8	5.00	SPR	CG	N
1.266	32.16	S-348	2.75	69.9	1.016	25.8	37	6.5	1.2	30	45	199	.94	23.8	0.125	3.2	7.50	SST	CG	N
1.266	32.16	10169	2.75	69.9	.912	23.2	156	27	.82	21	128	571	1.59	40.5	0.177	4.5	9.00	SPR	CG	Z
1.266	32.16	11503	2.75	69.9	.850	21.6	284	50	.46	12	131	584	2.29	58.1	0.208	5.3	10.0	SPR	CG	Z
1.266	32.16	11700	3.09	78.6	1.182	30.0	.81	.14	2.8	72	2.3	10	.25	6.4	0.042	1.1	5.00	SPR	C	Z
1.266	32.16	11788	3.31	84.1	1.054	26.8	17	2.9	1.9	48	31	138	.95	24.2	0.106	2.7	9.00	SPR	CG	Z
1.266	32.16	S-335	4.00	101.6	.882	22.4	224	39	.60	15	134	595	1.56	39.6	0.192	4.9	8.00	SST	CG	N
1.266	32.16	10515	4.13	104.8	1.056	26.8	9.7	1.7	2.7	69	26	117	1.42	36.0	0.105	2.7	13.5	SPR	CG	Z
1.266	32.16	12512	4.19	106.3	.922	23.4	120	21	1.4	35	165	736	1.89	48.1	0.172	4.4	10.0	MW	C	N
1.266	32.16	S-1128	4.25	108.0	1.142	29.0	1.1	.19	3.4	87</										




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.296	32.92	11527	1.25	31.8	1.086	27.6	52	9.1	.57	15	30	131	.53	13.3	0.105	2.7	4.00	SPR	CG	Z
1.296	32.92	3655	1.50	38.1	1.114	28.3	20	3.6	.94	24	19	86	.43	11.0	0.091	2.3	4.75	SPR	CG	Z
1.296	32.92	10402	1.63	41.3	1.086	27.6	34	6.0	.86	22	30	131	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
1.296	32.92	3409	1.63	41.3	1.080	27.4	39	6.8	.83	21	32	143	.54	13.7	0.108	2.7	5.00	SPR	CG	Z
1.296	32.92	3955	1.69	42.8	1.172	29.8	2.8	.49	1.3	32	3.5	16	.43	11.0	0.062	1.6	6.00	SPR	C	Z
1.296	32.92	2550	1.75	44.5	1.100	27.9	22	3.9	1.2	31	27	119	.54	13.7	0.098	2.5	5.50	MW	CG	Z
1.296	32.92	12015	1.75	44.5	1.086	27.6	34	6.0	.86	22	30	131	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
1.296	32.92	10902	2.38	60.3	1.116	28.3	7.9	1.4	1.7	42	13	59	.72	18.3	0.090	2.3	8.00	SST	CG	N
1.296	32.92	11771	2.50	63.5	1.046	26.6	55	9.6	.88	22	48	213	.75	19.1	0.125	3.2	6.00	SPR	CG	Z
1.296	32.92	3151	2.56	65.1	1.184	30.1	1.2	.22	2.1	54	2.6	12	.45	11.4	0.056	1.4	8.00	SPR	CG	Z
1.296	32.92	S-977	2.66	67.5	1.026	26.1	44	7.7	1.2	30	53	234	1.08	27.4	0.135	3.4	8.00	SST	CG	N
1.296	32.92	11638	2.72	69.0	1.086	27.6	13	2.3	1.7	42	22	96	1.05	26.7	0.105	2.7	10.0	SPR	CG	Z
1.296	32.92	1845	2.75	69.9	1.100	27.9	22	3.9	1.5	39	34	150	.54	13.7	0.098	2.5	5.50	MW	CG	Z
1.296	32.92	3359	2.75	69.9	1.046	26.6	40	7.0	1.2	31	48	213	1.06	27.0	0.125	3.2	7.50	SPR	C	Z
1.296	32.92	3744	2.94	74.6	1.096	27.8	17	2.9	1.5	39	26	114	.70	17.8	0.100	2.5	7.00	SPR	CG	Z
1.296	32.92	S-3017	3.00	76.2	1.172	29.8	1.4	.25	2.4	60	3.3	15	.62	15.7	0.062	1.6	9.00	SST	C	N
1.296	32.92	11265	3.00	76.2	.972	24.7	97	17	1.0	25	97	432	1.46	37.0	0.162	4.1	9.00	SPR	CG	N
1.296	32.92	2828	3.75	95.3	.796	20.2	497	87	.63	16	312	1389	2.97	75.4	0.250	6.4	12.0	SPR	CG	Z
1.296	32.92	11966	4.00	101.6	.984	25.0	52	9.1	1.7	42	87	387	2.03	51.5	0.156	4.0	13.0	SPR	CG	Z
1.296	32.92	S-160	4.50	114.3	1.112	28.2	5.4	.95	3.4	85	18	80	1.15	29.2	0.092	2.3	11.5	SST	C	N
1.296	32.92	12128	4.94	125.4	1.188	30.2	.80	.14	4.3	110	3.5	15	.59	15.1	0.054	1.4	10.0	SPR	C	Z
1.296	32.92	11734	4.94	125.4	1.008	25.6	35	6.2	2.0	51	70	314	1.94	49.4	0.144	3.7	13.5	SPR	CG	Z
1.296	32.92	S-1657	6.00	152.4	1.156	29.4	1.7	.29	5.2	131	8.6	38	.84	21.3	0.070	1.8	12.0	SST	CG	N
1.296	32.92	4133	6.75	171.5	.992	25.2	39	6.9	2.0	52	81	358	2.28	57.9	0.152	3.9	15.0	SPR	CG	GI
1.296	32.92	4025	22.0	558.8	1.046	26.6	3.4	.59	13	330	44	194	7.31	185.7	0.125	3.2	58.5	SST	CG	N
1.312	33.32	S-1499	.94	23.8	1.188	30.2	2.7	.47	.60	15	1.6	7.2	.34	8.7	0.062	1.6	5.50	SST	CG	N
1.312	33.32	10053	1.13	28.6	.812	20.6	3125	547	.10	2.5	309	1375	.88	22.2	0.250	6.4	3.50	SPR	CG	Z
1.312	33.32	3325	1.19	30.2	1.072	27.2	88	15	.48	12	42	187	.48	12.2	0.120	3.0	4.00	SPR	CG	Z
1.312	33.32	S-198	1.22	31.0	1.102	28.0	44	7.7	.61	16	27	120	.42	10.7	0.105	2.7	4.00	SST	CG	N
1.312	33.32	S-1275	1.38	34.9	1.112	28.2	20	3.5	.83	21	17	74	.55	14.0	0.100	2.5	5.50	SST	CG	N
1.312	33.32	S-3223	1.44	36.5	1.152	29.3	14	2.4	.91	23	13	57	.32	8.1	0.080	2.0	4.00	SST	CG	N
1.312	33.32	10670	1.81	46.0	1.102	28.0	29	5.1	.92	23	27	120	.53	13.3	0.105	2.7	5.00	SST	CG	N
1.312	33.32	271	1.88	47.6	.988	25.1	145	25	.66	17	96	427	1.05	26.7	0.162	4.1	6.50	HD	CG	Z
1.312	33.32	12127	1.91	48.4	1.050	26.7	86	15	.62	16	53	235	.66	16.6	0.131	3.3	5.00	SPR	CG	Z
1.312	33.32	10505	1.94	49.2	1.126	28.6	17	3.0	1.2	31	20	91	.51	13.0	0.093	2.4	5.50	SPR	CG	Z
1.312	33.32	3021	1.94	49.2	1.102	28.0	25	4.4	1.2	30	29	130	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
1.312	33.32	11986	2.09	53.2	.897	22.8	396	69	.48	12	188	837	1.45	36.9	0.208	5.3	7.00	SPR	CG	Z
1.312	33.32	S-1422	2.38	60.3	1.152	29.3	7.3	1.3	1.7	44	13	57	.54	13.7	0.080	2.0	5.75	SST	C	N
1.312	33.32	S-3170	2.50	63.5	1.136	28.9	5.8	1.0	1.7	43	10	44	.79	20.1	0.088	2.2	9.00	SST	CG	N
1.312	33.32	3169	2.63	66.7	.986	25.0	103	18	.95	24	98	435	1.39	35.2	0.163	4.1	8.50	SPR	CG	Z
1.312	33.32	1877	2.88	73.0	1.116	28.3	21	3.7	1.6	40	33	148	.64	16.2	0.098	2.5	5.50	MW	C	Z
1.312	33.32	2988	2.94	74.6	1.062	27.0	35	6.1	1.4	35	47	210	1.08	27.4	0.125	3.2	8.50	SPR	CG	Z
1.312	33.32	10109	3.25	82.6	1.192	30.3	2.7	.47	2.2	57	6.1	27	.39	9.9	0.060	1.5	5.50	SPR	C	Z
1.312	33.32	3397	3.50	88.9	1.172	29.8	4.5	.79</												




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.328	33.73	4306	8.25	209.6	.974	24.7	54	9.5	2.3	57	123	547	3.36	85.4	0.177	4.5	19.0	SPR	CG	Z
1.343	34.11	2634	.88	22.2	1.183	30.0	29	5.1	.45	12	13	59	.24	6.1	0.080	2.0	3.00	SPR	CG	Z
1.343	34.11	2774	1.50	38.1	1.191	30.3	5.9	1.0	1.0	27	6.2	27	.46	11.6	0.076	1.9	6.00	SPR	CG	Z
1.343	34.11	11807	1.50	38.1	1.181	30.0	12	2.2	1.1	28	14	61	.36	9.3	0.081	2.1	4.50	SPR	CG	Z
1.343	34.11	10639	1.72	43.6	.843	21.4	1229	215	.25	6.3	303	1348	1.38	34.9	0.250	6.4	5.50	SPR	CG	GI
1.343	34.11	2777	1.75	44.5	1.193	30.3	5.8	1.0	1.3	33	7.5	34	.44	11.2	0.075	1.9	6.00	MW	CG	Z
1.343	34.11	3061	1.88	47.6	1.155	29.3	18	3.1	1.2	29	21	91	.49	12.5	0.094	2.4	5.25	SPR	CG	Z
1.343	34.11	11643	1.88	47.6	1.151	29.2	25	4.4	.87	22	22	97	.43	11.0	0.096	2.4	4.50	SPR	CG	Z
1.343	34.11	1717	2.09	53.2	1.233	31.3	2.5	.43	1.8	45	4.4	20	.30	7.7	0.055	1.4	4.50	HD	C	Z
1.343	34.11	11567	2.34	59.5	1.205	30.6	2.6	.46	1.7	44	4.5	20	.62	15.8	0.069	1.8	8.00	SPR	CG	Z
1.343	34.11	10425	2.38	60.3	1.217	30.9	2.9	.50	2.0	51	5.8	26	.36	9.2	0.063	1.6	5.75	SPR	CG	Z
1.343	34.11	11387	2.38	60.3	1.163	29.5	9.6	1.7	1.7	44	17	74	.63	16.0	0.090	2.3	7.00	MW	CG	Z
1.343	34.11	11929	2.41	61.1	1.111	28.2	20	3.5	1.4	35	27	122	1.04	26.5	0.116	2.9	9.00	SPR	CG	Z
1.343	34.11	4370	2.56	65.1	.893	22.7	479	84	.47	12	224	998	1.69	42.9	0.225	5.7	7.50	SPR	CG	GI
1.343	34.11	3278	2.63	66.7	1.029	26.1	100	17	.86	22	86	381	1.14	28.9	0.157	4.0	7.25	SPR	CG	Z
1.343	34.11	12112	2.69	68.2	1.103	28.0	33	5.7	1.3	32	41	182	.84	21.3	0.120	3.0	7.00	SPR	CG	Z
1.343	34.11	11721	3.06	77.8	1.101	28.0	28	4.9	1.5	38	42	187	.97	24.6	0.121	3.1	8.00	SPR	CG	Z
1.343	34.11	3267	3.13	79.4	.969	24.6	175	31	.78	20	136	607	1.59	40.4	0.187	4.7	8.50	SPR	CG	Z
1.343	34.11	10658	3.31	84.1	1.219	31.0	1.8	.31	2.8	70	4.9	22	.54	13.8	0.062	1.6	7.75	SPR	C	Z
1.343	34.11	S-1605	4.03	102.4	1.139	28.9	8.3	1.4	2.8	72	23	104	1.20	30.4	0.102	2.6	10.8	SST	CG	N
1.343	34.11	11904	4.13	104.8	1.227	31.2	1.2	.21	3.6	93	4.5	20	.48	12.2	0.058	1.5	8.25	SPR	CG	N
1.343	34.11	S-155	4.50	114.3	1.227	31.2	1.1	.19	4.0	102	4.3	19	.48	12.2	0.058	1.5	8.25	SST	CG	N
1.343	34.11	S-353	4.50	114.3	1.199	30.5	1.6	.29	3.6	92	5.9	26	.86	21.9	0.072	1.8	12.0	SST	CG	N
1.343	34.11	10090	5.50	139.7	.893	22.7	176	31	1.3	32	224	998	3.83	97.2	0.225	5.7	17.0	SPR	CG	Z
1.343	34.11	4137	5.75	146.1	1.073	27.3	23	4.0	2.5	63	56	251	1.89	48.0	0.135	3.4	14.0	SPR	CG	Z
1.343	34.11	10445	5.75	146.1	1.073	27.3	19	3.3	3.0	77	56	251	2.23	56.6	0.135	3.4	16.5	SPR	CG	Z
1.343	34.11	396	7.09	180.2	1.103	28.0	9.1	1.6	4.5	115	41	182	2.39	60.7	0.120	3.0	20.0	SPR	CG	Z
1.343	34.11	12439	10.0	254.0	1.017	25.8	25	4.3	3.9	98	96	426	4.56	115.9	0.163	4.1	27.0	SPR	C	N
1.343	34.11	1623	10.4	263.5	.989	25.1	33	5.8	3.7	93	122	541	5.09	129.3	0.177	4.5	28.8	SPR	CG	Z
1.343	34.11	4014	15.8	400.1	1.049	26.6	8.5	1.5	8.5	216	72	322	7.06	179.2	0.147	3.7	48.0	SPR	CG	Z
1.359	34.52	10424	.50	12.7	1.177	29.9	73	13	.25	6.5	18	82	.24	6.2	0.091	2.3	2.67	SPR	CG	GI
1.359	34.52	LL-79	.50	12.7	1.159	29.4	128	22	.18	4.5	23	101	.25	6.4	0.100	2.5	2.50	SST	CG	N
1.359	34.52	EE-84	1.19	30.2	1.099	27.9	55	9.7	.41	10	23	100	.78	19.8	0.130	3.3	6.00	SPR	CG	N
1.359	34.52	2664	1.19	30.2	.977	24.8	639	112	.22	5.7	144	638	.74	18.8	0.191	4.9	4.00	SPR	CG	Z
1.359	34.52	11677	1.22	31.0	1.199	30.5	7.0	1.2	.74	19	5.2	23	.48	12.2	0.080	2.0	6.00	SPR	CG	Z
1.359	34.52	S-1261	1.25	31.8	1.253	31.8	2.5	.44	1.0	25	2.5	11	.25	6.4	0.053	1.3	3.75	SST	C	N
1.359	34.52	11824	1.28	32.5	1.179	29.9	18	3.2	.90	23	16	73	.38	9.7	0.090	2.3	4.25	SST	CG	N
1.359	34.52	JJ-52	1.28	32.5	1.119	28.4	78	14	.52	13	41	180	.48	12.2	0.120	3.0	4.00	SPR	CG	N
1.359	34.52	11551	1.31	33.3	1.135	28.8	58	10	.57	14	33	147	.56	14.2	0.112	2.8	4.00	SPR	CG	Z
1.359	34.52	11867	1.47	37.3	1.221	31.0	5.1	.89	1.1	27	5.3	24	.41	10.5	0.069	1.8	5.00	SPR	C	N
1.359	34.52	10511	1.50	38.1	1.247	31.7	2.6	.45	1.2	30	3.0	14	.31	7.8	0.056	1.4	4.50	SPR	C	Z
1.359	34.52	B18-180	1.50	38.1	.859	21.82	1302	228	.190	4.83	247	1101	1.190	30.23	0.250	6.35	4.75	SST	CG	N
1.359	34.52	3433	1.88	47.6	1.159	29.4	21	3.6	1.2	30	24	109	.65	16.5	0.100	2.5	5.50	SPR	C	Z
1.359	34.52	11789	1.94	49																




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.375	34.93	S-1087	1.63	41.3	1.135	28.8	48	8.4	.77	19	37	163	.57	14.5	0.120	3.0	4.75	SST	CG	N
1.375	34.93	11628	1.63	41.3	1.123	28.5	41	7.2	.81	20	33	148	.82	20.8	0.126	3.2	6.50	SPR	CG	Z
1.375	34.93	S-326	1.69	42.8	1.105	28.1	63	11	.78	20	50	221	.74	18.9	0.135	3.4	5.50	SST	CG	N
1.375	34.93	3560	1.75	44.5	.991	25.2	393	69	.37	9.3	144	641	.96	24.4	0.192	4.9	5.00	SPR	CG	Z
1.375	34.93	10401	1.97	50.0	1.063	27.0	104	18	.79	20	82	366	1.01	25.8	0.156	4.0	6.50	SPR	CG	Z
1.375	34.93	12610	2.00	50.8	1.041	26.4	141	25	.71	18	100	447	1.09	27.6	0.167	4.2	6.50	SPR	CG	Z
1.375	34.93	10299	2.13	54.0	1.193	30.3	13	2.3	1.4	35	18	81	.50	12.7	0.091	2.3	5.50	SPR	CG	Z
1.375	34.93	11671	2.13	54.0	1.041	26.4	141	25	.71	18	100	447	1.09	27.6	0.167	4.2	6.50	SPR	CG	Z
1.375	34.93	12779	2.19	55.6	1.079	27.4	79	14	.92	23	72	321	1.00	25.4	0.148	3.8	6.75	HD	CG	Z
1.375	34.93	4400	2.22	56.4	1.179	29.9	15	2.6	1.5	39	23	101	.61	15.6	0.098	2.5	6.25	SPR	CG	Z
1.375	34.93	4343	2.25	57.2	1.193	30.3	10	1.8	1.7	42	17	76	.59	15.0	0.091	2.3	6.50	SPR	CG	Z
1.375	34.93	S-1388	2.31	58.7	1.191	30.3	6.8	1.2	1.6	39	11	47	.76	19.3	0.092	2.3	8.25	SST	CG	N
1.375	34.93	11839	2.34	59.5	1.187	30.1	7.6	1.3	1.6	40	12	53	.78	19.7	0.094	2.4	8.25	SST	CG	N
1.375	34.93	S-450	2.44	61.9	1.191	30.3	7.1	1.2	1.7	43	12	54	.74	18.7	0.092	2.3	8.00	SST	CG	N
1.375	34.93	10309	2.44	61.9	1.021	25.9	164	29	.73	18	119	530	1.24	31.5	0.177	4.5	7.00	SPR	CG	Z
1.375	34.93	10348	2.50	63.5	1.193	30.3	8.5	1.5	1.8	46	15	68	.68	17.3	0.091	2.3	7.50	SPR	CG	Z
1.375	34.93	12092	2.50	63.5	1.167	29.6	18	3.2	1.4	35	25	112	.73	18.5	0.104	2.6	6.00	SST	C	N
1.375	34.93	73	2.50	63.5	1.105	28.1	48	8.4	1.2	29	55	245	.98	24.9	0.135	3.4	7.25	HD	CG	Z
1.375	34.93	S-347	2.50	63.5	1.105	28.1	46	8.0	1.1	28	50	221	.91	23.1	0.135	3.4	6.75	SST	CG	N
1.375	34.93	12420	2.75	69.9	1.277	32.4	.89	.16	2.4	61	2.1	9.5	.34	8.7	0.049	1.2	6.00	SPR	C	Z
1.375	34.93	269	2.75	69.9	1.135	28.8	27	4.8	1.5	37	40	178	1.02	25.9	0.120	3.0	7.50	HD	C	Z
1.375	34.93	3464	2.75	69.9	1.105	28.1	31	5.5	1.3	32	40	176	1.49	37.7	0.135	3.4	10.0	HD	C	Z
1.375	34.93	54	2.75	69.9	1.021	25.9	122	21	.98	25	119	530	1.55	39.3	0.177	4.5	8.75	HD	CG	Z
1.375	34.93	10742	2.88	73.0	1.215	30.9	5.4	.95	2.3	59	13	56	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
1.375	34.93	4355	2.94	74.6	1.205	30.6	4.0	.70	2.0	51	8.1	36	.91	23.2	0.085	2.2	10.8	SPR	CG	Z
1.375	34.93	S-1209	3.00	76.2	1.135	28.8	20	3.5	1.8	46	37	163	1.02	25.9	0.120	3.0	8.50	SST	CG	N
1.375	34.93	11266	3.00	76.2	1.021	25.9	153	27	.69	18	106	471	1.19	30.3	0.177	4.5	6.75	SST	CG	N
1.375	34.93	12048	3.47	88.1	1.125	28.6	28	4.8	1.6	42	45	201	1.06	27.0	0.125	3.2	8.50	SPR	CG	N
1.375	34.93	1557	3.50	88.9	1.259	32.0	.89	.16	2.9	73	2.5	11	.64	16.2	0.058	1.5	10.0	SPR	C	Z
1.375	34.93	S-289	3.75	95.3	1.251	31.8	1.5	.26	3.2	82	4.8	21	.53	13.4	0.062	1.6	7.50	SST	C	N
1.375	34.93	2591	3.75	95.3	1.231	31.3	1.6	.27	2.8	71	4.3	19	.95	24.2	0.072	1.8	13.3	HD	CG	Z
1.375	34.93	S-103	3.75	95.3	1.231	31.3	2.6	.46	3.1	79	8.2	37	.63	16.0	0.072	1.8	7.75	SST	C	N
1.375	34.93	S-1355	3.75	95.3	1.199	30.5	7.0	1.2	2.1	58	16	72	.62	15.6	0.088	2.2	7.00	SST	CG	N
1.375	34.93	S-445	3.75	95.3	1.175	29.8	6.0	1.1	2.6	65	15	68	1.20	30.5	0.100	2.5	12.0	SST	CG	N
1.375	34.93	898	3.75	95.3	1.105	28.1	29	5.2	1.9	48	55	245	1.55	39.4	0.135	3.4	10.5	HD	C	Z
1.375	34.93	S-195	3.75	95.3	1.063	27.0	63	11	1.2	30	73	325	1.33	33.7	0.156	4.0	8.50	SST	CG	N
1.375	34.93	S-327	3.88	98.4	1.231	31.3	2.6	.46	3.2	82	8.6	38	.63	16.0	0.072	1.8	7.75	SST	C	N
1.375	34.93	3987	4.00	101.6	1.021	25.9	80	14	1.5	38	119	530	2.17	55.1	0.177	4.5	12.3	SPR	CG	Z
1.375	34.93	861	4.13	104.8	1.105	28.1	27	4.7	2.1	52	55	245	1.53	38.9	0.135	3.4	11.3	HD	CG	Z
1.375	34.93	11513	4.38	111.1	1.217	30.9	3.7	.64	3.4	86	12	56	.79	20.1	0.079	2.0	9.00	SPR	CG	Z
1.375	34.93	823	4.38	111.1	1.079	27.4	36	6.3	2.0	51	72	321	1.83	46.4	0.148	3.8	12.3	HD	CG	Z
1.375	34.93	811	4.50	114.3	1.021	25.9	70	12	1.7	43	119	530	2.43	61.8	0.177	4.5	13.8	HD	CG	Z
1.375	34.93	10363	4.75	120.7	1.181	30.0	6.8	1.2	3.3	83	22	98	1.07	27.1	0.097	2.5	11.0	SPR	CG	Z
1.375	34.93	S-3002	5.38	136.5	1.221	31.0	3.3	.59	3.2	82	11	48	.69	17.6	0.077	2.0	8.00	SST	C	N
1.375	34.93	7005	5.38	136.5	1.001	25.4	75	13	1.8	45	134	594	3.30	83.8	0.187	4.7	16.3	HD	C	Z
1.375	34.93	389	6.00	152.4	1.135	28.8	13	2.2	3.2	81	40	178	1.68	42.7	0.120	3.0	14.0	HD	CG	Z
1.375	34.93	11977	6.50	165.1	.989	25.1	107	19	1.4	35	146	651	2.56	65.0	0.193	4.9	13.3	SPR	CG	Z
1.375	34.93	845	8.00	203.2	1.021	25.9	44	7.8	2.7	68	119	530	3.63	92.2	0.177	4.5	20.5	HD	CG	Z
1.375	34.93	383	9.75	247.7	1.215	30.9	1.1	.19	7.5	191	8.1	36	2.24	56.9	0.080	2.0	27.0	HD	C	Z
1.375	34.93	850	10.0	254.0	1.051	26.7														




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.400	35.56	72775	2.25	57.2	1.046	26.6	169	30	.97	25	164	730	1.17	29.8	0.177	4.5	6.63	MW	CG	N
1.400	35.56	72775S	2.25	57.2	1.046	26.6	143	25	.73	18	104	463	1.17	29.8	0.177	4.5	6.63	SST	CG	N
1.400	35.56	72767	2.50	63.5	1.076	27.3	103	18	1.2	31	127	563	1.15	29.3	0.162	4.1	7.13	MW	CG	N
1.400	35.56	72767S	2.50	63.5	1.076	27.3	87	15	.92	23	80	357	1.15	29.3	0.162	4.1	7.13	SST	CG	N
1.400	35.56	72776	2.50	63.5	1.046	26.6	149	26	1.1	28	164	730	1.26	32.0	0.177	4.5	7.13	MW	CG	N
1.400	35.56	72776S	2.50	63.5	1.046	26.6	127	22	.82	21	104	463	1.26	32.0	0.177	4.5	7.13	SST	CG	N
1.400	35.56	72768	3.00	76.2	1.076	27.3	84	15	1.5	39	127	563	1.34	33.9	0.162	4.1	8.25	MW	CG	N
1.400	35.56	72768S	3.00	76.2	1.076	27.3	71	12	1.1	29	80	357	1.34	33.9	0.162	4.1	8.25	SST	CG	N
1.400	35.56	72777	3.00	76.2	1.046	26.6	120	21	1.4	35	164	730	1.48	37.7	0.177	4.5	8.38	MW	CG	N
1.400	35.56	72777S	3.00	76.2	1.046	26.6	102	18	1.0	26	104	463	1.48	37.7	0.177	4.5	8.38	SST	CG	N
1.400	35.56	72769	3.50	88.9	1.076	27.3	70	12	1.8	46	127	563	1.52	38.6	0.162	4.1	9.38	MW	CG	N
1.400	35.56	72769S	3.50	88.9	1.076	27.3	60	10	1.3	34	80	357	1.52	38.6	0.162	4.1	9.38	SST	CG	N
1.400	35.56	72778	3.50	88.9	1.046	26.6	100	18	1.6	42	164	730	1.73	43.8	0.177	4.5	9.75	MW	CG	N
1.400	35.56	72778S	3.50	88.9	1.046	26.6	85	15	1.2	31	104	463	1.73	43.8	0.177	4.5	9.75	SST	CG	N
1.400	35.56	72770	4.00	101.6	1.076	27.3	61	11	2.1	53	127	563	1.72	43.7	0.162	4.1	10.6	MW	CG	N
1.400	35.56	72770S	4.00	101.6	1.076	27.3	52	9.0	1.6	39	80	357	1.72	43.7	0.162	4.1	10.6	SST	CG	N
1.400	35.56	72779	4.00	101.6	1.046	26.6	87	15	1.9	48	164	730	1.92	48.9	0.177	4.5	10.9	MW	CG	N
1.400	35.56	72779S	4.00	101.6	1.046	26.6	74	13	1.4	36	104	463	1.92	48.9	0.177	4.5	10.9	SST	CG	N
1.400	35.56	72771	4.25	108.0	1.076	27.3	57	10	2.2	57	127	563	1.80	45.8	0.162	4.1	11.1	MW	CG	N
1.400	35.56	72771S	4.25	108.0	1.076	27.3	48	8.5	1.7	42	80	357	1.80	45.8	0.162	4.1	11.1	SST	CG	N
1.400	35.56	72780	4.25	108.0	1.046	26.6	81	14	2.0	51	164	730	2.04	51.7	0.177	4.5	11.5	MW	CG	N
1.400	35.56	72780S	4.25	108.0	1.046	26.6	69	12	1.5	38	104	463	2.04	51.7	0.177	4.5	11.5	SST	CG	N
1.400	35.56	72772	4.50	114.3	1.076	27.3	54	9.4	2.4	60	127	563	1.90	48.3	0.162	4.1	11.8	MW	CG	N
1.400	35.56	72772S	4.50	114.3	1.076	27.3	45	8.0	1.8	45	80	357	1.90	48.3	0.162	4.1	11.8	SST	CG	N
1.400	35.56	72781	4.50	114.3	1.046	26.6	76	13	2.2	55	164	730	2.15	54.5	0.177	4.5	12.1	MW	CG	N
1.400	35.56	72781S	4.50	114.3	1.046	26.6	65	11	1.6	41	104	463	2.15	54.5	0.177	4.5	12.1	SST	CG	N
1.400	35.56	72773	5.00	127.0	1.076	27.3	48	8.4	2.7	67	127	563	2.09	53.0	0.162	4.1	12.9	MW	CG	N
1.400	35.56	72773S	5.00	127.0	1.076	27.3	41	7.1	2.0	50	80	357	2.09	53.0	0.162	4.1	12.9	SST	CG	N
1.400	35.56	72782	5.00	127.0	1.046	26.6	69	12	2.4	60	164	730	2.32	59.0	0.177	4.5	13.1	MW	CG	N
1.400	35.56	72782S	5.00	127.0	1.046	26.6	59	10	1.8	45	104	463	2.32	59.0	0.177	4.5	13.1	SST	CG	N
1.400	35.56	72774	5.25	133.4	1.076	27.3	45	7.9	2.8	71	127	563	2.19	55.5	0.162	4.1	13.5	MW	CG	N
1.400	35.56	72774S	5.25	133.4	1.076	27.3	39	6.8	2.1	53	80	357	2.19	55.5	0.162	4.1	13.5	SST	CG	N
1.400	35.56	72783	5.25	133.4	1.046	26.6	65	11	2.5	64	164	730	2.46	62.4	0.177	4.5	13.9	MW	CG	N
1.400	35.56	72783S	5.25	133.4	1.046	26.6	55	9.7	1.9	48	104	463	2.46	62.4	0.177	4.5	13.9	SST	CG	N
1.406	35.71	S-1241	.75	19.1	1.136	28.9	202	35	.24	6.1	49	216	.41	10.3	0.135	3.4	3.00	SST	CG	N
1.406	35.71	S-70	.88	22.2	1.246	31.6	15	2.6	.60	15	8.7	39	.28	7.1	0.080	2.0	3.50	SST	CG	N
1.406	35.71	S-3246	1.00	25.4	1.322	33.6	.78	.14	.83	21	.65	2.9	.17	4.3	0.042	1.1	4.00	SST	CG	N
1.406	35.71	S-3024	1.00	25.4	1.256	31.9	9.6	1.7	.64	16	6.2	27	.36	9.0	0.075	1.9	3.75	SST	C	N
1.406	35.71	S-3018	1.13	28.6	1.226	31.1	18	3.2	.68	17	12	54	.45	11.4	0.090	2.3	4.00	SST	C	N
1.406	35.71	S-3075	1.13	28.6	1.032	26.2	563	99	.20	5.1	113	501	.65	16.6	0.187	4.7	3.50	SST	CG	N
1.406	35.71	NN-77	1.22	31.0	1.086	27.6	288	50	.27	6.8	77	343	.56	14.2	0.160	4.1	3.50	SST	CG	N
1.406	35.71	3017	1.25	31.8	1.282	32.6	2.5	.44	.85	22	2.1	9.4	.40	10.2	0.062	1.6	5.50	SPR	C	Z
1.406	35.71	11980	1.25	31.8	1.082	27.5	3													




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.421	36.09	4194	4.00	101.6	1.281	32.5	1.3	.22	3.0	77	3.8	17	.98	24.9	0.070	1.8	13.0	SPR	C	Z
1.421	36.09	3141	5.13	130.2	1.261	32.0	2.6	.45	4.1	105	11	47	1.00	25.4	0.080	2.0	11.5	SPR	C	Z
1.421	36.09	12460	12.0	304.8	1.003	25.5	55	9.5	3.3	83	179	796	6.32	160.6	0.209	5.3	30.3	SPR	CG	N
1.421	36.09	4018	27.5	698.5	.921	23.4	60	11	4.8	122	289	1285	15.0	381.0	0.250	6.4	60.0	SPR	CG	N
1.437	36.50	S-1550	.56	14.3	1.237	31.4	70	12	.29	7.3	20	89	.28	7.0	0.100	2.5	2.75	SST	CG	N
1.437	36.50	DD-88	.69	17.4	1.217	30.9	45	7.9	.25	6.3	11	49	.44	11.2	0.110	2.8	4.00	SPR	CG	Z
1.437	36.50	S-3059	.88	22.2	1.281	32.5	12	2.2	.52	13	6.4	29	.35	8.9	0.078	2.0	3.50	SST	C	N
1.437	36.50	12222	1.00	25.4	1.293	32.8	15	2.7	.60	15	9.1	40	.22	5.5	0.072	1.8	3.00	SPR	CG	Z
1.437	36.50	S-151	1.50	38.1	1.347	34.2	.32	.06	1.1	28	.35	1.5	.41	10.3	0.045	1.1	8.00	SST	C	N
1.437	36.50	S-1033	1.50	38.1	1.277	32.4	5.9	1.0	.98	25	5.7	26	.52	13.2	0.080	2.0	5.50	SST	C	N
1.437	36.50	11360	1.50	38.1	1.255	31.9	12	2.1	1.0	27	12	56	.46	11.6	0.091	2.3	5.00	SST	CG	N
1.437	36.50	3071	1.50	38.1	1.173	29.8	56	9.8	.77	20	43	193	.73	18.4	0.132	3.4	5.50	SPR	CG	Z
1.437	36.50	S-944	1.69	42.8	1.237	31.4	26	4.6	.82	21	21	95	.40	10.2	0.100	2.5	4.00	SST	CG	N
1.437	36.50	12487	1.75	44.5	1.317	33.5	1.0	.18	1.2	31	1.3	5.6	.54	13.7	0.060	1.5	8.00	SST	C	N
1.437	36.50	B17-167	1.84	46.8	1.125	28.6	135	24	.58	15	79	351	.78	19.8	0.156	4.0	5.00	SPR	CG	N
1.437	36.50	11531	2.72	69.0	1.013	25.7	234	41	.65	17	152	678	2.07	52.5	0.212	5.4	8.75	SPR	CG	Z
1.437	36.50	3909	2.75	69.9	1.317	33.5	1.8	.31	2.3	59	4.2	18	.42	10.7	0.060	1.5	6.00	SPR	C	Z
1.437	36.50	3288	2.75	69.9	1.017	25.8	275	48	.65	17	180	799	1.58	40.0	0.210	5.3	7.50	SPR	CG	Z
1.437	36.50	12069	2.88	73.0	1.287	32.7	3.0	.53	2.3	58	6.8	30	.60	15.2	0.075	1.9	8.00	SPR	CG	Z
1.437	36.50	3704	3.00	76.2	1.327	33.7	1.2	.22	2.7	68	3.3	15	.33	8.4	0.055	1.4	6.00	SPR	CG	Z
1.437	36.50	2753	3.13	79.4	1.287	32.7	3.0	.53	2.5	64	7.6	34	.60	15.2	0.075	1.9	8.00	HD	CG	Z
1.437	36.50	10719	3.31	84.1	1.335	33.9	.52	.09	2.9	72	1.5	6.6	.46	11.7	0.051	1.3	9.00	SPR	CG	Z
1.437	36.50	3407	3.38	85.7	1.177	29.9	31	5.4	1.5	39	47	210	1.04	26.4	0.130	3.3	8.00	SPR	CG	Z
1.437	36.50	S-303	3.59	91.3	1.277	32.4	2.6	.46	2.8	71	7.3	32	.80	20.3	0.080	2.0	10.0	SST	CG	N
1.437	36.50	10594	3.75	95.3	1.265	32.1	3.2	.56	2.7	69	8.7	39	1.03	26.2	0.086	2.2	12.0	SPR	CG	Z
1.437	36.50	10823	4.00	101.6	1.167	29.6	30	5.2	1.8	45	53	235	1.38	35.1	0.135	3.4	9.25	SPR	C	Z
1.437	36.50	S-369	4.88	123.8	1.137	28.9	37	6.5	1.7	43	63	278	1.50	38.1	0.150	3.8	10.0	SST	CG	N
1.437	36.50	7007	5.63	142.9	1.023	26.0	100	18	1.7	44	172	767	3.60	91.4	0.207	5.3	16.3	HD	C	Z
1.437	36.50	3049	6.88	174.6	1.077	27.4	47	8.3	2.4	62	115	510	3.26	82.9	0.180	4.6	18.0	SPR	CG	Z
1.437	36.50	10454	8.88	225.4	1.187	30.1	13	2.2	3.5	88	43	193	2.02	51.2	0.125	3.2	15.8	SPR	CG	Z
1.437	36.50	4236	14.5	368.3	1.083	27.5	20	3.6	5.6	142	114	509	6.64	168.6	0.177	4.5	36.5	SPR	C	Z
1.437	36.50	4040	20.5	520.7	1.113	28.3	12	2.1	7.4	188	88	392	6.40	162.6	0.162	4.1	40.0	SPR	CG	Z
1.437	36.50	4029	23.0	584.2	1.113	28.3	12	2.1	7.2	183	88	392	6.64	168.7	0.162	4.1	41.0	SPR	CG	Z
1.453	36.91	3299	1.53	38.9	1.227	31.2	49	8.5	.65	17	32	142	.45	11.5	0.113	2.9	4.00	SPR	CG	Z
1.453	36.91	3297	1.75	44.5	1.243	31.6	12	2.1	.91	23	11	48	.84	21.3	0.105	2.7	8.00	HD	CG	Z
1.453	36.91	12297	1.94	49.2	1.323	33.6	3.2	.56	1.6	41	5.2	23	.33	8.3	0.065	1.7	5.00	SPR	CG	Z
1.453	36.91	10339	2.06	52.4	1.233	31.3	35	6.1	.85	21	29	131	.50	12.6	0.110	2.8	4.50	SPR	CG	Z
1.453	36.91	4359	2.06	52.4	1.069	27.2	216	38	.63	16	137	610	1.25	31.7	0.192	4.9	6.50	SPR	CG	Z
1.453	36.91	11791	2.41	61.1	1.203	30.6	37	6.6	1.1	29	43	191	.75	19.1	0.125	3.2	6.00	SPR	CG	Z
1.453	36.91	12616	2.50	63.5	1.203	30.6	37	6.6	1.6	41	60	267	.88	22.2	0.125	3.2	6.00	MW	C	N
1.453	36.91	B11-63	2.84	72.2	1.157	29.4	62	11	1.1	28	69	305	1.04	26.3	0.148	3.8	7.00	SPR	CG	N
1.453	36.91	B17-203	2.88	73.0	1.275	32.4	6.3	1.1	2.3	57	14	63	.62	15.8	0.089	2.3	7.00	SST	CG	N
1.453	36.91	11238	3.00	76.2	1.141	29.0	58	10	1.4	34	78	348	1.37	34.7	0.156	4.0	8.75	SPR	CG	Z
1.453	36.91	12177	3.03	77.0	1.269	32.2	7.8	1.4	2.3	58	18	80	.67	16.9	0.092	2.3	7.25	SPR	CG	GI
1.453	36.91	4026	20.3	514.4	1.123	28.5	12	2.1	7.8	197	92	410	7.26	184.4	0.165	4.2	44.0	SPR	CG	Z
1.453	36.91	4038	21.0	533.4	1.099	27.9	16	2.9	6.9	176	113	503	7.70	195.6	0.177	4.5	43.5	SPR	CG	Z
1.453	36.91	4032	22.5	571.5	1.093	27.8	16	2.7	7.3	185	114	505	8.82	224.0	0.180	4.6	49.0	SPR	CG	Z
1.460	37.08	72784	1.50	38.1	1.236	31.4	41	7.2	1.0	26	42	188	.48	12.1	0.112	2.8	4.25	MW	CG	N
1.460	3																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.460	37.08	72802S	2.50	63.5	1.190	30.2	38	6.6	1.2	32	47	209	.89	22.7	0.135	3.4	6.63	SST	CG	N
1.460	37.08	72812	2.50	63.5	1.164	29.6	62	11	1.5	38	92	409	1.02	25.8	0.148	3.8	6.88	MW	CG	N
1.460	37.08	72812S	2.50	63.5	1.164	29.6	53	9.2	1.2	30	62	274	1.02	25.8	0.148	3.8	6.88	SST	CG	N
1.460	37.08	72821	2.50	63.5	1.148	29.2	78	14	1.4	36	109	485	1.07	27.2	0.156	4.0	6.88	MW	CG	N
1.460	37.08	72821S	2.50	63.5	1.148	29.2	66	12	1.0	27	69	307	1.07	27.2	0.156	4.0	6.88	SST	CG	N
1.460	37.08	72834	2.50	63.5	1.136	28.9	88	15	1.3	34	118	526	1.15	29.3	0.162	4.1	7.13	MW	CG	N
1.460	37.08	72834S	2.50	63.5	1.136	28.9	75	13	1.0	26	77	343	1.15	29.3	0.162	4.1	7.13	SST	CG	N
1.460	37.08	72845	2.50	63.5	1.106	28.1	128	22	1.2	31	156	693	1.28	32.6	0.177	4.5	7.25	MW	CG	N
1.460	37.08	72845S	2.50	63.5	1.106	28.1	109	19	.92	23	100	445	1.28	32.6	0.177	4.5	7.25	SST	CG	N
1.460	37.08	72856	2.50	63.5	1.086	27.6	168	29	1.1	27	179	795	1.33	33.8	0.187	4.7	7.13	MW	CG	N
1.460	37.08	72856S	2.50	63.5	1.086	27.6	143	25	.76	19	109	484	1.33	33.8	0.187	4.7	7.13	SST	CG	N
1.460	37.08	72787	3.00	76.2	1.236	31.4	19	3.3	2.2	57	42	188	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.460	37.08	72787S	3.00	76.2	1.236	31.4	16	2.8	1.7	44	28	125	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.460	37.08	72797	3.00	76.2	1.210	30.7	28	4.8	2.1	53	57	255	.92	23.4	0.125	3.2	7.38	MW	CG	N
1.460	37.08	72797S	3.00	76.2	1.210	30.7	23	4.1	1.7	42	39	173	.92	23.4	0.125	3.2	7.38	SST	CG	N
1.460	37.08	72803	3.00	76.2	1.190	30.2	36	6.3	2.0	50	71	317	1.03	26.1	0.135	3.4	7.63	MW	CG	N
1.460	37.08	72803S	3.00	76.2	1.190	30.2	31	5.4	1.5	39	47	209	1.03	26.1	0.135	3.4	7.63	SST	CG	N
1.460	37.08	72813	3.00	76.2	1.164	29.6	51	8.9	1.8	46	92	409	1.18	30.1	0.148	3.8	8.00	MW	CG	N
1.460	37.08	72813S	3.00	76.2	1.164	29.6	43	7.5	1.4	36	62	274	1.18	30.1	0.148	3.8	8.00	SST	CG	N
1.460	37.08	72823	3.00	76.2	1.148	29.2	63	11	1.7	44	109	485	1.25	31.7	0.156	4.0	8.00	MW	CG	N
1.460	37.08	72823S	3.00	76.2	1.148	29.2	54	9.4	1.3	33	69	307	1.25	31.7	0.156	4.0	8.00	SST	CG	N
1.460	37.08	72835	3.00	76.2	1.136	28.9	71	13	1.6	42	117	522	1.36	34.5	0.162	4.1	8.38	MW	CG	N
1.460	37.08	72835S	3.00	76.2	1.136	28.9	61	11	1.3	32	77	343	1.36	34.5	0.162	4.1	8.38	SST	CG	N
1.460	37.08	72847	3.00	76.2	1.106	28.1	104	18	1.5	39	158	701	1.48	37.7	0.177	4.5	8.38	MW	CG	N
1.460	37.08	72847S	3.00	76.2	1.106	28.1	88	15	1.1	29	100	445	1.48	37.7	0.177	4.5	8.38	SST	CG	N
1.460	37.08	72857	3.00	76.2	1.086	27.6	138	24	1.3	33	179	795	1.52	38.6	0.187	4.7	8.13	MW	CG	N
1.460	37.08	72857S	3.00	76.2	1.086	27.6	117	21	.93	24	109	484	1.52	38.6	0.187	4.7	8.13	SST	CG	N
1.460	37.08	72788	3.50	88.9	1.236	31.4	16	2.8	2.6	67	42	188	.87	22.0	0.112	2.8	7.75	MW	CG	N
1.460	37.08	72788S	3.50	88.9	1.236	31.4	14	2.4	2.1	52	28	125	.87	22.0	0.112	2.8	7.75	SST	CG	N
1.460	37.08	72798	3.50	88.9	1.210	30.7	23	4.1	2.5	62	57	254	1.05	26.6	0.125	3.2	8.38	MW	CG	N
1.460	37.08	72798S	3.50	88.9	1.210	30.7	20	3.5	2.0	50	39	173	1.05	26.6	0.125	3.2	8.38	SST	CG	N
1.460	37.08	72804	3.50	88.9	1.190	30.2	31	5.4	2.3	59	71	316	1.18	30.0	0.135	3.4	8.75	MW	CG	N
1.460	37.08	72804S	3.50	88.9	1.190	30.2	26	4.6	1.8	46	47	209	1.18	30.0	0.135	3.4	8.75	SST	CG	N
1.460	37.08	72814	3.50	88.9	1.164	29.6	43	7.5	2.1	55	92	408	1.35	34.3	0.148	3.8	9.13	MW	CG	N
1.460	37.08	72814S	3.50	88.9	1.164	29.6	36	6.4	1.7	43	62	274	1.35	34.3	0.148	3.8	9.13	SST	CG	N
1.460	37.08	72825	3.50	88.9	1.148	29.2	53	9.4	2.0	52	109	485	1.44	36.7	0.156	4.0	9.25	MW	CG	N
1.460	37.08	72825S	3.50	88.9	1.148	29.2	45	7.9	1.5	39	69	307	1.44	36.7	0.156	4.0	9.25	SST	CG	N
1.460	37.08	72836	3.50	88.9	1.136	28.9	60	11	2.0	50	118	524	1.54	39.1	0.162	4.1	9.50	MW	CG	N
1.460	37.08	72836S	3.50	88.9	1.136	28.9	51	8.9	1.5	38	77	343	1.54	39.1	0.162	4.1	9.50	SST	CG	N
1.460	37.08	72849	3.50	88.9	1.106	28.1	87	15	1.8	46	157	698	1.70	43.3	0.177	4.5	9.63	MW	CG	N
1.460	37.08	72849S	3.50	88.9	1.106	28.1	74	13	1.3	34	100	445	1.70	43.3	0.177	4.5	9.63	SST	CG	N
1.460	37.08	72858	3.50	88.9	1.086	27.6	116	20	1.5	39	179	795	1.75	44.5	0.187	4.7	9.38	MW	CG	N
1.460	37.08	72858S	3.50	88.9	1.086	27.6	99	17	1.1	28	109	484	1.75	44.5	0.187	4.7	9.38	SST	CG	N
1.460	37.08	72789	4.00	101.6	1.236	31.4	14	2.4	3.0	77	42	188	.97	24.5	0.112	2.8	8.63	MW	CG	N
1.460	37.08	72789S	4.00	101.6	1.236	31.4	12	2.1	2.4	61	28	125	.97	24.5	0.112	2.8	8.63	SST	CG	N
1.460	37.08	72799	4.00	101.6	1.210	30.7	20	3.5	2.8	72	57	256	1.16	29.4	0.125	3.2	9.25	MW	CG	N
1.460	37.08	72799S	4.00	101.6	1.210	30.7	17	3.0	2.3	58	39	173	1.16	29.4	0.125	3.2	9.25	SST	CG	N
1.460	37.08	72805	4.00	101.6	1.190	30.2	27	4.6	2.7	68	71	316	1.32	33.4	0.135	3.4	9.75	MW	CG	N
1.460	37.08	72805S	4.00	101.6	1.190	30.2	23	3.9	2.1	53	47	209	1.32	33.4	0.135	3.4	9.75	SST	CG	N
1.460	37.08	72815	4.00	101.6	1.164	29.6	37	6.5	2.5	63	92	409	1.52	38.5	0.148	3.8	10.3	MW	CG	N
1.460	37.08	72815S	4.00	101.6	1.164	29.6	31	5.5	2.0	50	62	274	1.52	38.5	0.148	3.8	10.3	SST	CG	N
1.460	37.08	72827	4.00	101.6	1.148	29.2	46	8.1	2.4	60	109	485	1.60	40.6	0.156	4.0	10.3	MW	CG	N
1.460	37.08																			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.460	37.08	72839S	5.00	127.0	1.136	28.9	35	6.1	2.2	57	77	343	2.13	54.0	0.162	4.1	13.1	SST	CG	N
1.460	37.08	72855	5.00	127.0	1.106	28.1	59	10	2.7	67	157	698	2.35	59.6	0.177	4.5	13.3	MW	CG	N
1.460	37.08	72855S	5.00	127.0	1.106	28.1	50	8.8	2.0	51	100	445	2.35	59.6	0.177	4.5	13.3	SST	CG	N
1.460	37.08	72862	5.00	127.0	1.086	27.6	77	13	2.3	59	179	795	2.45	62.3	0.187	4.7	13.1	MW	CG	N
1.460	37.08	72862S	5.00	127.0	1.086	27.6	65	11	1.7	42	109	484	2.45	62.3	0.187	4.7	13.1	SST	CG	N
1.460	37.08	72863	5.25	133.4	1.086	27.6	73	13	2.4	62	179	795	2.55	64.7	0.187	4.7	13.6	MW	CG	N
1.460	37.08	72863S	5.25	133.4	1.086	27.6	62	11	1.8	45	109	484	2.55	64.7	0.187	4.7	13.6	SST	CG	N
1.468	37.29	S-3052	.69	17.4	1.410	35.8		.30 .05	.57	15		.17 .75	.12	2.9	0.029	0.7	3.00	SST	C	N
1.468	37.29	1853	1.00	25.4	1.198	30.4	134	24	.39	9.8	52	231	.47	12.0	0.135	3.4	3.50	SPR	CG	Z
1.468	37.29	3496	1.31	33.3	1.258	32.0	28	4.8	.84	21	23	103	.47	12.0	0.105	2.7	4.50	SPR	CG	Z
1.468	37.29	3456	1.31	33.3	1.018	25.9	959	168	.22	5.5	207	922	.90	22.9	0.225	5.7	4.00	SPR	CG	Z
1.468	37.29	11426	1.50	38.1	1.054	26.8	389	68	.37	9.5	146	648	1.04	26.3	0.207	5.3	5.00	SST	CG	N
1.468	37.29	S-1669	1.56	39.7	1.308	33.2	13	2.3	.88	22	11	51	.28	7.1	0.080	2.0	3.50	SST	CG	N
1.468	37.29	S-1358	1.75	44.5	1.268	32.2	24	4.3	.86	22	21	93	.40	10.2	0.100	2.5	4.00	SST	CG	N
1.468	37.29	S-1443	1.84	46.8	1.054	26.8	327	57	.45	11	146	648	1.14	28.9	0.207	5.3	5.50	SST	CG	N
1.468	37.29	S-3192	2.00	50.8	1.272	32.3	18	3.2	1.1	27	20	88	.44	11.2	0.098	2.5	4.50	SST	CG	N
1.468	37.29	S-1632	2.06	52.4	1.094	27.8	212	37	.51	13	108	482	1.03	26.1	0.187	4.7	5.50	SST	CG	N
1.468	37.29	11881	2.13	54.0	1.230	31.2	39	6.9	.94	24	37	163	.60	15.1	0.119	3.0	5.00	SPR	CG	N
1.468	37.29	S-987	2.13	54.0	1.226	31.1	35	6.2	1.0	25	35	157	.60	15.2	0.121	3.1	5.00	SST	CG	N
1.468	37.29	10336	2.19	55.6	.718	18.2	7917	1386	.10	2.6	799	3554	1.78	45.2	0.375	9.5	4.75	SPR	CG	Z
1.468	37.29	10368	2.25	57.2	1.084	27.5	235	41	.58	15	136	604	1.15	29.3	0.192	4.9	6.00	SPR	CG	Z
1.468	37.29	10317	2.38	60.3	1.068	27.1	215	38	.71	18	153	680	1.45	36.8	0.200	5.1	7.25	SPR	CG	Z
1.468	37.29	1743	2.41	61.1	1.304	33.1	4.9	.85	1.8	44	8.5	38	.66	16.7	0.082	2.1	7.00	HD	C	Z
1.468	37.29	S-1595	2.44	61.9	1.258	32.0	7.9	1.4	1.3	33	10	46	1.13	28.7	0.105	2.7	9.75	SST	CG	N
1.468	37.29	10048	2.44	61.9	1.054	26.8	251	44	.67	17	169	752	1.50	38.1	0.207	5.3	7.25	SPR	CG	Z
1.468	37.29	S-3057	2.50	63.5	1.284	32.6	11	2.0	1.4	36	16	73	.55	14.0	0.092	2.3	5.00	SST	C	N
1.468	37.29	10204	2.50	63.5	1.084	27.5	235	41	.58	15	136	604	1.15	29.3	0.192	4.9	6.00	SPR	CG	Z
1.468	37.29	10371	2.53	64.3	1.068	27.1	215	38	.71	18	153	680	1.45	36.8	0.200	5.1	7.25	SPR	CG	Z
1.468	37.29	S-3165	2.69	68.2	1.258	32.0	12	2.1	2.0	50	23	104	.74	18.7	0.105	2.7	7.00	SST	CG	N
1.468	37.29	11496	2.75	69.9	1.048	26.6	234	41	.75	19	176	784	1.89	48.0	0.210	5.3	8.00	SPR	CG	Z
1.468	37.29	S-3222	3.00	76.2	1.172	29.8	53	9.3	1.2	29	61	272	1.04	26.3	0.148	3.8	7.00	SST	CG	N
1.468	37.29	B17-200	3.28	83.3	1.232	31.3	17	2.9	2.0	50	33	145	.94	24.0	0.118	3.0	8.00	SST	CG	N
1.468	37.29	S-1598	3.50	88.9	1.310	33.3	2.3	.41	2.6	67	6.1	27	.87	22.1	0.079	2.0	10.0	SST	CG	N
1.468	37.29	S-3066	3.63	92.1	1.298	33.0	5.5	.96	2.5	63	14	61	.55	14.0	0.085	2.2	6.50	SST	CG	N
1.468	37.29	S-3184	4.50	114.3	1.268	32.2	7.5	1.3	2.8	71	21	93	.85	21.6	0.100	2.5	8.50	SST	CG	N
1.468	37.29	12270	4.59	116.7	1.298	33.0	3.5	.62	3.7	95	13	59	.85	21.6	0.085	2.2	10.0	SPR	CG	Z
1.468	37.29	12440	4.81	122.2	1.032	26.2	148	26	1.3	34	196	874	2.89	73.4	0.218	5.5	13.3	SPR	CG	Z
1.468	37.29	S-970	5.13	130.2	1.240	31.5	8.8	1.5	3.4	85	30	131	1.33	33.8	0.114	2.9	11.7	SST	CG	N
1.468	37.29	S-3216	5.25	133.4	1.310	33.3	1.6	.28	4.2	106	6.7	30	1.07	27.1	0.079	2.0	13.5	SST	CG	N
1.468	37.29	10388	5.75	146.1	1.030	26.2	148	26	1.3	34	199	886	2.96	75.1	0.219	5.6	13.5	SPR	CG	Z
1.468	37.29	11172	6.00	152.4	1.028	26.1	161	28	1.2	31	194	864	3.03	76.8	0.220	5.6	12.8	SPR	C	Z
1.484	37.69	S-1603	1.53	38.9	1.072	27.2	367	64	.30	7.5	108	481	1.24	31.4	0.206	5.2	5.00	SST	CG	N
1.484	37.69	S-383	3.25	82.6	1.274	32.4	13	2.3	1.9	47	24	107	.68	17.3	0.105	2.7	6.50	SST	CG	N
1.484	37.69	3023	3.38	85.7	1.172	29.8	61	11	1.3	32	77	341	1.25	31.7	0.156	4.0	8.00	SPR	CG	Z
1.484	37.69	S-1655	3.75	95.3	1.070	27.2	125	22	1.2	29	144	641	2.28	57.8	0.207	5.3	11.0	SST	CG	N
1.484	37.69	12412	5.00	127.0	1.380	35.1	.80	.14	4.4	112	3.5	16	.39	9.9	0.052	1.3	6.50	SPR	C	Z
1.484	37.69	1735	9.00	228.6	1.160	29.5	20	3.6	4.2	107	86	381	3.73	94.6	0.162	4.1	23.0	SPR	CG	Z
1.500	38.10	11898	.84	21.4	1.230	31.2	125	22	.37	9.3	46	203	.45	11.4	0.135	3.4	3.33	SST	CG	N
1.500	38.10	3804	1.25	31.8	1.290	32.8	32	5.6	.80	20	26	114	.42	10.7	0.105	2.7	4.00	SPR	CG	Z
1.500	38.10	12635	1.56	39.7	1.184	30.1	185	32	.60	15	110	491	.79	20.1	0.158	4.0	4.00	MW	C	N
1.500	38.10	S-1197	1.75	44.5	1.380	35.1	2.0	.35	1.4	36	2.8	12	.35	8.8	0.060	1.5	4.75	SST	C	N
1.500	38.10	S-3032	1.75	44.5	1.374	34.9	2.5	.44	1.4	36	3.5	16	.34	8.7	0.063	1.6	4.50	SST	C	N
1.500	38.10	11471	1.75	44.5	1.340	34.0	6.3	1.1	1.3	34	8.4	37</								




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.500	38.10	32	4.00	101.6	1.230	31.2	24	4.2	2.1	53	51	226	1.32	33.4	0.135	3.4	9.75	HD	CG	Z
1.500	38.10	11514	4.16	105.6	1.282	32.6	11	1.9	2.7	68	29	128	1.09	27.7	0.109	2.8	9.00	SPR	CG	Z
1.500	38.10	3380	4.25	108.0	1.286	32.7	10	1.7	2.7	69	27	121	1.07	27.2	0.107	2.7	9.00	SPR	CG	Z
1.500	38.10	S-3167	4.50	114.3	1.300	33.0	7.3	1.3	2.8	72	21	92	.83	21.0	0.100	2.5	8.25	SST	CG	N
1.500	38.10	11976	4.50	114.3	1.260	32.0	22	3.8	1.7	43	37	164	.87	22.1	0.120	3.0	7.25	SPR	CG	Z
1.500	38.10	4259	4.50	114.3	1.012	25.7	321	56	.80	20	257	1143	2.44	62.0	0.244	6.2	10.0	SPR	CG	Z
1.500	38.10	3135	4.56	115.9	1.300	33.0	8.3	1.4	2.7	68	22	99	.83	21.2	0.100	2.5	8.33	SPR	CG	Z
1.500	38.10	12042	4.59	116.7	1.250	31.8	16	2.8	2.6	67	42	185	1.31	33.3	0.125	3.2	10.5	SPR	CG	Z
1.500	38.10	2847	4.88	123.8	1.176	29.9	57	10	1.5	38	85	377	1.50	38.1	0.162	4.1	9.25	SPR	CG	Z
1.500	38.10	7058	5.00	127.0	1.032	26.2	161	28	1.2	30	192	853	3.39	86.2	0.234	5.9	13.5	SST	C	N
1.500	38.10	S-467	5.13	130.2	1.250	31.8	9.8	1.7	3.4	86	33	147	1.75	44.5	0.125	3.2	14.0	SST	CG	N
1.500	38.10	7009	5.88	149.2	1.050	26.7	125	22	1.6	41	203	905	3.90	99.1	0.225	5.7	16.3	HD	C	Z
1.500	38.10	3440	6.00	152.4	1.290	32.8	4.0	.70	4.1	104	17	74	1.89	48.0	0.105	2.7	18.0	SPR	CG	Z
1.500	38.10	3378	6.75	171.5	1.070	27.2	90	16	2.0	52	185	823	3.87	98.3	0.215	5.5	18.0	SPR	CG	Z
1.500	38.10	S-985	6.88	174.6	1.250	31.8	9.0	1.6	4.2	107	38	169	1.88	47.6	0.125	3.2	15.0	SST	CG	N
1.500	38.10	846	8.00	203.2	1.146	29.1	31	5.5	3.5	89	110	489	3.81	96.7	0.177	4.5	21.5	HD	CG	Z
1.500	38.10	12152	8.63	219.1	1.156	29.4	27	4.7	3.8	96	101	449	3.78	96.1	0.172	4.4	22.0	SPR	CG	Z
1.500	38.10	4222	10.0	254.0	1.290	32.8	2.9	.50	7.4	189	21	95	2.57	65.3	0.105	2.7	24.5	SPR	CG	Z
1.500	38.10	10256	10.0	254.0	1.116	28.3	49	8.6	2.7	69	133	592	3.98	101.2	0.192	4.9	19.8	SPR	C	GI
1.500	38.10	863	12.0	304.8	1.230	31.2	7.5	1.3	6.8	172	51	226	3.65	92.6	0.135	3.4	27.0	HD	CG	Z
1.500	38.10	532	12.0	304.8	1.204	30.6	11	1.8	6.3	161	67	296	4.37	110.9	0.148	3.8	28.5	HD	C	Z
1.500	38.10	851	12.0	304.8	1.176	29.9	17	2.9	5.1	130	85	377	4.54	115.2	0.162	4.1	27.0	HD	C	Z
1.500	38.10	842	12.0	304.8	1.116	28.3	29	5.0	4.7	118	133	592	6.24	158.5	0.192	4.9	32.5	HD	CG	Z
1.500	38.10	804	12.0	304.8	1.086	27.6	39	6.9	4.2	107	166	737	6.83	173.5	0.207	5.3	33.0	HD	CG	Z
1.500	38.10	835	12.0	304.8	1.050	26.7	57	9.9	3.6	91	203	905	7.50	190.5	0.225	5.7	33.3	HD	CG	Z
1.515	38.48	12679	1.50	38.1	1.203	30.6	151	26	.50	13	75	334	.82	20.8	0.156	4.0	4.25	SPR	C	N
1.515	38.48	S-989	1.91	48.4	1.135	28.8	204	36	.54	14	110	490	1.05	26.5	0.190	4.8	5.50	SST	CG	N
1.515	38.48	S-288	2.13	54.0	1.371	34.8	2.5	.44	1.7	42	4.1	18	.47	11.9	0.072	1.8	6.50	SST	CG	N
1.515	38.48	11872	2.16	54.8	1.141	29.0	214	38	.57	14	122	543	1.03	26.1	0.187	4.7	5.50	SPR	CG	N
1.515	38.48	11178	2.31	58.7	1.099	27.9	344	60	.48	12	167	741	1.14	29.1	0.208	5.3	5.50	SPR	CG	Z
1.515	38.48	2923	2.50	63.5	1.245	31.6	28	5.0	1.2	30	34	150	1.31	33.2	0.135	3.4	8.67	SPR	C	Z
1.515	38.48	2775	2.50	63.5	1.227	31.2	37	6.5	1.1	29	42	186	1.37	34.7	0.144	3.7	8.50	SPR	C	Z
1.515	38.48	11116	2.50	63.5	1.141	29.0	214	38	.57	14	122	543	1.03	26.1	0.187	4.7	5.50	SPR	CG	N
1.515	38.48	1519	2.75	69.9	1.075	27.3	312	55	.660	16.76	206	922	1.69	42.9	0.225	5.72	7.50	SPR		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.562	39.67	11177	2.56	65.1	1.188	30.2	225	39	.53	13	119	528	.94	23.7	0.187	4.7	5.00	SPR	CG	Z
1.562	39.67	11996	2.63	66.7	.876	22.3	2312	405	.26	6.6	599	2665	2.32	58.8	0.343	8.7	6.75	SPR	CG	Z
1.562	39.67	852	2.75	69.9	1.238	31.4	69	12	1.2	30	82	363	1.17	29.8	0.162	4.1	7.25	HD	CG	Z
1.562	39.67	S-314	3.16	80.2	1.436	36.5	2.1	.37	2.6	66	5.6	25	.36	9.2	0.063	1.6	4.75	SST	C	N
1.562	39.67	4346	3.63	92.1	1.178	29.9	76	13	1.3	34	100	446	2.30	58.5	0.192	4.9	12.0	SPR	CG	Z
1.562	39.67	895	4.00	101.6	.996	25.3	497	87	.74	19	367	1633	3.08	78.2	0.283	7.2	11.0	HD	CG	Z
1.562	39.67	812	4.25	108.0	1.208	30.7	57	10	1.9	47	106	471	2.01	51.0	0.177	4.5	11.3	HD	CG	Z
1.562	39.67	678	4.38	111.1	1.076	27.3	213	37	1.2	29	245	1090	2.98	75.6	0.243	6.2	12.3	HD	CG	Z
1.562	39.67	11669	4.84	123.0	1.478	37.5	.07	.01	4.0	103	.30	1.3	.80	20.3	0.042	1.1	19.0	SPR	CG	N
1.562	39.67	3244	5.00	127.0	1.202	30.5	54	9.5	2.0	50	106	472	2.25	57.2	0.180	4.6	12.5	SPR	CG	Z
1.562	39.67	10570	5.00	127.0	1.108	28.1	153	27	1.3	33	201	895	3.07	77.9	0.227	5.8	12.5	SPR	C	Z
1.562	39.67	S-3110	5.50	139.7	1.380	35.1	4.7	.82	3.2	81	15	67	.71	17.9	0.091	2.3	7.75	SST	CG	N
1.562	39.67	11509	6.41	162.7	1.260	32.0	20	3.5	3.3	84	66	295	2.47	62.6	0.151	3.8	15.3	SPR	CG	Z
1.562	39.67	911	7.50	190.5	1.266	32.2	15	2.6	4.3	110	64	285	2.74	69.5	0.148	3.8	18.5	HD	CG	Z
1.562	39.67	2735	11.4	290.5	1.362	34.6	2.9	.51	7.3	186	21	95	1.78	45.1	0.100	2.5	17.8	SPR	CG	Z
1.578	40.08	12276	1.00	25.4	1.496	38.0	.37	.07	.75	19	.28	1.3	.25	6.2	0.041	1.0	5.00	SPR	C	Z
1.578	40.08	11148	1.25	31.8	1.266	32.2	169	30	.43	11	72	322	.59	14.9	0.156	4.0	3.75	SPR	CG	Z
1.578	40.08	3358	1.31	33.3	1.204	30.6	435	76	.27	6.9	118	523	.65	16.6	0.187	4.7	3.50	SPR	CG	Z
1.578	40.08	10349	1.56	39.7	1.368	34.7	14	2.4	.93	24	13	57	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
1.578	40.08	S-162	1.63	41.3	1.426	36.2	2.9	.51	1.2	29	3.3	15	.48	12.1	0.076	1.9	6.25	SST	CG	N
1.578	40.08	S-3227	1.72	43.6	1.394	35.4	5.6	.97	1.1	27	6.0	27	.64	16.4	0.092	2.3	7.00	SST	CG	N
1.578	40.08	11774	2.38	60.3	1.462	37.1	1.9	.32	2.1	54	3.9	17	.26	6.6	0.058	1.5	4.50	SPR	CG	Z
1.578	40.08	10329	2.44	61.9	1.164	29.6	241	42	.66	17	158	704	1.29	32.9	0.207	5.3	6.25	SPR	CG	Z
1.578	40.08	11629	2.50	63.5	1.338	34.0	14	2.4	1.4	36	20	87	1.08	27.4	0.120	3.0	9.00	SPR	CG	Z
1.578	40.08	S-3189	3.00	76.2	1.308	33.2	28	4.8	1.6	40	44	194	.95	24.0	0.135	3.4	7.00	SST	CG	N
1.578	40.08	10689	3.38	85.7	1.458	37.0	.74	.13	2.8	70	2.0	9.0	.62	15.6	0.060	1.5	9.25	SPR	C	Z
1.578	40.08	3486	3.75	95.3	1.328	33.7	16	2.9	2.4	62	40	176	1.13	28.6	0.125	3.2	9.00	HD	CG	Z
1.578	40.08	S-298	4.16	105.6	1.404	35.7	4.8	.84	2.8	72	14	61	.57	14.4	0.087	2.2	6.50	SST	CG	N
1.578	40.08	S-3193	6.75	171.5	1.398	35.5	1.7	.30	5.2	133	8.8	39	1.53	38.9	0.090	2.3	17.0	SST	CG	N
1.578	40.08	11965	7.69	195.2	1.190	30.2	52	9.1	2.5	64	131	583	3.1	78.7	0.192	4.9	16.1	SPR	CG	GI
1.580	40.13	72864	2.50	63.5	1.166	29.6	210	37	1.1	27	223	994	1.42	36.1	0.207	5.3	6.88	MW	CG	N
1.580	40.13	72864S	2.50	63.5	1.166	29.6	179	31	.76	19	136	606	1.42	36.1	0.207	5.3	6.88	SST	CG	N
1.580	40.13	72865	3.00	76.2	1.166	29.6	170	30	1.3	33	223	994	1.66	42.1	0.207	5.3	8.00	MW	CG	N
1.580	40.13	72865S	3.00	76.2	1.166	29.6	145	25	.94	24	136	606	1.66	42.1	0.207	5.3	8.00	SST	CG	N
1.580	40.13																			



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.625	41.28	12725	4.30	109.2	1.443	36.7	3.0	.53	3.2	81	9.7	43	1.09	27.7	0.091	2.3	11.0	HD	C	N
1.625	41.28	369	4.50	114.3	1.139	28.9	200	35	1.2	30	237	1053	2.79	71.0	0.243	6.2	11.5	HD	CG	Z
1.625	41.28	2793	5.63	142.9	1.343	34.1	13	2.3	3.5	89	47	209	2.12	53.7	0.141	3.6	15.0	SPR	CG	GI
1.625	41.28	10393	7.25	184.2	1.137	28.9	119	21	2.0	51	239	1065	4.45	113.1	0.244	6.2	18.3	SPR	CG	Z
1.625	41.28	843	12.0	304.8	1.241	31.5	24	4.2	5.1	130	124	550	5.66	143.9	0.192	4.9	29.5	HD	CG	Z
1.640	41.66	S-1465	1.38	34.9	1.464	37.2	13	2.3	.98	25	13	58	.40	10.1	0.088	2.2	3.50	SST	C	N
1.640	41.66	B17-193	1.47	37.3	1.280	32.5	215	38	.41	10	87	389	.72	18.3	0.180	4.6	4.00	SST	CG	N
1.640	41.66	S-965	1.69	42.8	1.344	34.1	60	11	.92	23	55	245	.74	18.8	0.148	3.8	5.00	SST	CG	N
1.640	41.66	3008	1.88	47.6	1.496	38.0	4.0	.70	1.6	39	6.2	28	.32	8.2	0.072	1.8	4.50	SPR	CG	GI
1.640	41.66	3105	2.00	50.8	1.370	34.8	49	8.5	.96	24	47	207	.66	16.7	0.135	3.4	5.00	SPR	CG	Z
1.640	41.66	S-1666	2.25	57.2	1.370	34.8	41	7.3	1.0	26	42	187	.68	17.1	0.135	3.4	5.00	SST	CG	N
1.640	41.66	3239	2.25	57.2	1.286	32.7	120	21	.84	21	101	450	1.02	25.9	0.177	4.5	5.75	SPR	CG	Z
1.640	41.66	S-3237	2.34	59.5	1.390	35.3	20	3.5	1.5	39	30	135	.81	20.6	0.125	3.2	6.50	SST	CG	N
1.640	41.66	10665	2.38	60.3	1.190	30.2	433	76	.43	11	188	835	1.13	28.6	0.225	5.7	5.00	SPR	CG	Z
1.640	41.66	S-102	3.25	82.6	1.328	33.7	38	6.6	1.6	42	62	275	1.25	31.7	0.156	4.0	8.00	SST	CG	N
1.640	41.66	4193	3.25	82.6	1.016	25.8	969	170	.47	12	452	2011	2.50	63.4	0.312	7.9	8.00	SPR	CG	Z
1.640	41.66	2990	3.38	85.7	1.476	37.5	3.4	.60	2.7	69	9.3	42	.66	16.7	0.082	2.1	7.00	SPR	C	Z
1.640	41.66	S-319	3.63	92.1	1.300	33.0	43	7.5	1.9	47	80	355	1.64	41.7	0.170	4.3	9.67	SST	CG	N
1.640	41.66	S-1188	3.75	95.3	1.506	38.3	1.3	.23	3.2	82	4.2	19	.54	13.6	0.067	1.7	7.00	SST	C	N
1.640	41.66	3174	4.00	101.6	1.506	38.3	.99	.17	3.3	84	3.3	15	.70	17.9	0.067	1.7	9.50	SPR	C	Z
1.640	41.66	1861	4.31	109.5	1.370	34.8	18	3.2	2.6	66	47	207	1.32	33.4	0.135	3.4	9.75	HD	CG	Z
1.640	41.66	1833	4.78	121.4	1.324	33.6	46	8.0	1.6	40	72	322	1.26	32.1	0.158	4.0	8.00	HD	CG	GI
1.640	41.66	3307	5.75	146.1	1.286	32.7	41	7.2	2.5	63	101	450	2.30	58.4	0.177	4.5	13.0	SPR	CG	Z
1.640	41.66	4404	8.00	203.2	1.430	36.3	4.6	.81	5.1	130	24	105	1.42	36.0	0.105	2.7	12.5	SPR	C	GI
1.656	42.06	10529	1.16	29.4	1.430	36.3	51	8.9	.55	14	28	125	.37	9.3	0.113	2.9	3.25	SPR	CG	Z
1.656	42.06	11542	2.03	51.6	1.416	36.0	18	3.2	1.1	29	21	92	.90	22.9	0.120	3.0	6.50	SPR	CG	GI
1.656	42.06	10373	2.38	60.3	1.206	30.6	457	80	.41	10	186	827	1.07	27.2	0.225	5.7	4.75	SPR	CG	Z
1.656	42.06	S-283	2.88	73.0	1.406	35.7	21	3.7	1.6	41	35	154	.75	19.1	0.125	3.2	6.00	SST	CG	N
1.																				

