


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		T	REVISED PER ECO-14-011315	24JUL2014	GG	LS

- ① DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- ② MATERIAL: HOUSING— POLYCARBONATE, CLEAR
TERMINAL— .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m [.000007] THICK GOLD IN LOCALIZED PLATE AREA OVER .762 μ m [.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m [.000100] THICK NICKEL ON ENTIRE CONTACT.
- ③ PLUG WILL ACCEPT 24 OR 26 AWG SOLID WIRE HAVING AN INSULATION DIAMETER RANGE OF 0.89–0.99[.035–.039] AND A MAXIMUM OVAL CABLE JACKET OF 2.29 X 6.61 [.09 X .260].
- ④ TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- ⑥ 1000 ASSEMBLIES PER PACKAGE.
- ⑦ 100 ASSEMBLIES PER PACKAGE.
- ⑨ REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.



OBSOLETE	⑦③	5-555042-3
	⑥③	5-555042-2
	REELED ③⑨	555042-1
	PACKAGED	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12DEC2007	TE Connectivity			
		CHK	12DEC2007				
		APVD	12DEC2007	NAME			
		PRODUCT SPEC	108-1163	MODULAR PLUG ASSEMBLY, 6 POSITION, SOLID WIRE -			
		APPLICATION SPEC	114-6016				
MATERIAL		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-	-	A2	00779	C=555042	-
CUSTOMER DRAWING		SCALE		4:1	SHEET	1 of 1	REV T