

Telecom OC12 VCXO

- 311.04 MHz Fixed Osc
- CMOS Output

Applications

- SDH / SONET
- Digital Switching
- Test Equipment
- Cellular Telephony
- Land Mobile Radio

Series

C3VFSC



Part Numbering Example: C3VFSC Z


C3VFSC

SERIES

Specifications:	Min	Typ	Max	Unit
Frequency Range:		311.04		MHz
Available Stability Options:	-30		30	ppm
Supply Voltage:	3.135	3.3	3.465	V
Operating Temperature Range Options:	-10		85	°C
Storage Temperature:	-55		125	°C
Duty Cycle:	45		55	%
Start-Up Time:		3	10	mS
Aging (PPM/1st Year): Ta=25°C, Vdd=3.3V			±5	
Static Discharge Voltage Mil-Std 883, method 3015	2000			V
Supply Current			40	mA
Short Circuit Current		± 50		mA
Jitter (RMS) Integrated (12KHz - 20MHz) Period		3 10	4	pS pS
Phase Noise @10KHz Offset		-122		dBc/Hz
Vcon Modulation BW 0V ≤ Vcon ≤ 3.3V, -3dB	25			KHz
Pull Range	-190		190	ppm
Linearity		5	10	%
Frequency Tuning Range		115		ppm/V

Output Level: CMOS

C3VFSC



PIN	FUNCTION
1	VCONTROL
2	OE
3	GND
4	CMOS Out
5	NC
6	VDD

DIMENSIONS ARE IN MM

Notes: Extended exposure exceeding maximum ratings may cause permanent damage and affect reliability. Operation outside of specifications is not supported.

Cardinal Components, Inc., 155 Rt. 46 W, Wayne, NJ. 07470 TEL: (973)785-1333 FAX: (973)785-0053
<http://www.cardinalxtal.com> E-Mail: cardinal@cardinalxtal.com

Specifications subject to change without notice. Check website for latest updates

