



DataTraveler 4000

Protect sensitive data with FIPS 140-2 Level 2 validation and 100-percent privacy.

Protect your organization's portable data with Kingston's ultra-secure DataTraveler® 4000 USB Flash drive. It's FIPS 140-2 Level 2 validated and features 256-bit AES hardware-based encryption in CBC mode. Complex password protection enforces device lockdown after a specified number of invalid attempts. DataTraveler 4000 is rugged and waterproof, with a titanium-coated, stainless steel casing for added protection. It's easy to set up and use, with no admin rights or application installation required.

Assembled in the U.S., DataTraveler 4000 is backed by a five-year warranty, free technical support and legendary Kingston® reliability.



Features/specs on reverse >>

DataTraveler 4000

FEATURES/BENEFITS

- > **FIPS 140-2 Level 2 validated**
- > **TAA-compliant**
- > **Secure** — drive locks down after 10 intrusion attempts and encryption key is destroyed
 - Enforced complex password— password is user set with a minimum of three of the four characteristics (lowercase, uppercase, characters and numbers) required to prevent unauthorized access
 - Can operate with AutoRun disabled
 - Enforces write-protected AutoRun files
- > **Read-Only Access Mode** — when selected, access files in Read-only Mode to avoid potential Malware risks
- > **Full Encryption** — 100 percent of stored data is protected by hardware-based, 256-bit Advanced Encryption Standard (AES) in CBC mode
- > **Customizable²** — password length, maximum number of password attempts, preload content
- > **Tamper evident** — coating/seal for physical security
- > **Guaranteed** — five-year warranty with free technical support
- > **Ruggedized** — waterproof¹ and titanium-coated stainless steel casing
- > **Easy to use** — no admin rights or application installation required
- > **Co-logo program available²**
- > **Assembled in the U.S.**

SPECIFICATIONS

- > **Dimensions** 3.06" x 0.9" x 0.47" (77.9mm x 22mm x 12.05mm)
- > **Speed³** up to 18MB/s read, 10MB/s write
- > **Capacities⁴** 2GB, 4GB, 8GB, 16GB, 32GB
- > **Compatibility** designed to USB 2.0 specifications
- > **Operating Temperature** 32°F to 140°F (0°C to 60°C)
- > **Storage Temperature** -4°F to 185°F (-20°C to 85°C)
- > **Minimum System Requirements:**
 - USB 2.0 compliant and 1.1 compatible
 - Two (2) free drive letters required for use⁵

¹ Up to 4 ft.; conforms to IEC 60529 IPX8. Product must be clean and dry before use.

² Minimum quantity required. Performed at the factory.

³ Speed may vary due to host hardware, software and usage.

⁴ Please note: Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/pdfs/FlashMemGuide.pdf.

⁵ First free drive letters after physical devices such as system partition, optical drives, etc.

⁶ Certain distributions of Linux will require super-user (root) privileges in order to execute the DataTraveler 4000 commands properly in the terminal application window.
THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.



UPDATED COMPATIBILITY TABLE

	🔒
Windows® 7	✓
Windows Vista® (SP1,SP2)	✓
Windows XP (SP2,SP3)	✓
Mac OS X(10.5.x - 10.6.x)	✓
Linux v2.6 kernel ⁶	✓

KINGSTON DT4000 PART NUMBERS

DT4000/2GB
DT4000/4GB
DT4000/8GB
DT4000/16GB
DT4000/32GB

