

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				E	REV PER 0G3A-0123-02	07MAR02	JR/MS



AMP WIRE RANGE	UL E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	M7928/7-4 CLASS 2 P/N 34112 & 2-34112-2 ONLY

- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16
- 2 GOLD PLATE, .000100 MIN THK PER
ASTM B-488 OVER NICKEL PLATE .000050 MIN
THK PER SAE-AMS-QQ-N-290.
- 3 0.00254 [.000100] MIN TIN PER
ASTM B-545.
- 4 CLEANED, UNPLATED

4	-	LOOSE PIECE	34112-3
2	-	LOOSE PIECE	34112-2
3	100	LOOSE PIECE, BOX	8-34112-1
3	5000	ON TAPE	2-34112-2
3	---	LOOSE PIECE	34112
FINISH	QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 3-10-93 TA BRINKMAN	 AMP Incorporated Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	MATERIAL COPPER PER ASTM B-152 ANNEALED	CHK 3-10-93 DA PATTERSON	NAME TERMINAL, RING TONGUE, SOLISTRAND,™		
		APPD 3-10-93 DE MILLER					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS SOLID OR STRANDED		APPD 3-10-93 JL MECKLEY			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	FINISH SEE NOTES	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO C-34112
				WEIGHT -	SCALE 10:1		SHEET 1 OF 1