

Camlocks

Specifying a product when ordering

**AFTER SELECTING THE PRODUCT YOU REQUIRE, PLEASE
ADD THE FOLLOWING:**

1. LOCK SPECIFICATIONSEE 12.10 FOR DETAILS

2. CAM DETAILSSEE 12.30 FOR DETAILS

3. KEYING DETAILSSEE 12.20 FOR DETAILS

**4. FIXING DETAILSSEE 12.20 AND PRODUCT
DATA SHEET FOR DETAILS**


PLEASE CONTACT OUR SALES DEPARTMENT IF YOU REQUIRE HELP

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Mini Camlock 8mm



0202

0207



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP	HEAD SHAPE
800 DOUBLE ENTRY	100	0201	0202	CONICAL HEAD
		0205	0206	CYLINDRICAL
		0207	0208	SQUARE
		0213	0214	ROUND
			0251	CONICAL
			0252	ROUND

MAXIMUM PANEL THICKNESS: NUT FIXING 2.5mm, HORSESHOE CLIP FIXING ACROSS ROUNDS 2.6mm, ACROSS FLATS 4mm
STANDARD MOVEMENTS: 1, 2, 3, 4, 8
STANDARD FINISH: BRIGHT CHROME
 CAMS FOR THESE PRODUCTS MAY NOT REFLECT STANDARD DIMENSIONS, PLEASE REFER TO SALES DEPARTMENT.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Mini Camlock 9.5mm and 10mm



0221/0257



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCK TYPE	CAM FIXING
800 DOUBLE ENTRY	100	0221	CLIP
800 M	200	0257	NUT & WASHER


MAXIMUM PANEL THICKNESS:

HORSESHOE CLIP FIXING 4mm ACROSS ROUNDS ONLY

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: BRIGHT CHROME



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	REFERENCE NUMBER
800 DOUBLE ENTRY	100	0225

MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING 4mm ACROSS ROUNDS ONLY

STANDARD MOVEMENTS: 1, 2, 8, 9

STANDARD FINISH: BRIGHT CHROME


CAMS FOR THESE PRODUCTS MAY NOT REFLECT STANDARD DIMENSIONS, PLEASE REFER TO SALES DEPARTMENT.

LOWE & FLETCHER LTD



MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Push to Lock ————— Camlock



F501



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCK REF
FH	SEE PAGE 12.22	F501

MAXIMUM PANEL THICKNESS: 4mm



STANDARD MOVEMENTS: 2

STANDARD FINISH: GREY PLASTIC RAL 7040

OTHER COLOURS AVAILABLE ON REQUEST

PLASTIC CLIP FIXING SUPPLIED

F503



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCK REF
FH	SEE PAGE 12.22	F503

MAXIMUM PANEL THICKNESS: 4mm

STANDARD MOVEMENTS: 2

STANDARD FINISH: GREY PLASTIC RAL 7040

OTHER COLOURS AVAILABLE ON REQUEST


PLASTIC CLIP FIXING SUPPLIED

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Flush Fitting Lock



F510




PRODUCT REFERENCE NUMBERS			
KEY SERIES	COMBINATIONS	WITH CAP	NO CAP
FH	SEE PAGE 12.22	F511	F510
1F M	SEE PAGE 12.22	F513	F512
H	SEE PAGE 12.22	F515	F514

MAXIMUM PANEL THICKNESS: TO SPECIFY ON ORDER
 FROM 0.75-1.05MM HOUSING F1116
 FROM 1.06-1.35MM HOUSING F1117
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1, 8
STANDARD FINISH: BLACK PLASTIC RAL 9011
 OTHER COLOURS AVAILABLE ON REQUEST
 4 FIXING CLIPS SUPPLIED
 FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
 TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 9.5mm



1320



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING	SNAP-IN FIXING
STANDARD VERSION			
92 M	200	1320	1319
95-97 M	2000	1420	1419
89	200	4620	4619
93E M	500	4720	-
92 M	200	-	F400


SHUTTERED VERSION

89	200	4617*	4616*
----	-----	-------	-------

MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING 5mm
ACROSS ROUNDS ONLY, SNAP-IN FIXING 1mm
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9
STANDARD FINISH: BRIGHT CHROME
BRIGHT NICKEL ONLY FOR F400
*THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS



1372



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	SNAP-IN FIXING
STANDARD VERSION		
92 M	200	1372
95-97	2000	1472
89	200	4672
SHUTTERED VERSION		
89	200	B181*

MAXIMUM PANEL THICKNESS: 1.8mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: BRIGHT CHROME


*THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock (Shuttered) 10.3mm — Camlock 10,5mm



B525



PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
2D	200	B525

MAXIMUM PANEL THICKNESS: 4mm


STANDARD MOVEMENTS: 1

STANDARD FINISH: BRIGHT CHROME

CYLINDER EQUIPPED WITH A DUST COVER.



B254



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCKING
1D	50	B254
2D	200	B434

MAXIMUM PANEL THICKNESS: 4mm

STANDARD MOVEMENTS: 1, 2

STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 8mm and 9.5mm — Camlock 9.5mm and 9.6mm



TJ5C



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING	DIM L	DIM T
STANDARD VERSION				
9000 M	500	TJ5C (F228)	9.7	6
	100	TJ5A (F123)	8.1	7.5
SHUTTERED VERSION*				
9000 M	500	F191	9.7	6
	500	F109	9.7	6


MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING
0.8 - 1.2 STANDARD, 5.5 MAXIMUM.
F191, F123 & TJ5A = 3.25 MAXIMUM

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY


STANDARD MOVEMENTS: 1, 3 (TJ5C, F109, F191 & F228)
8, 9 (TJ5A & F123)

STANDARD FINISH: BRIGHT CHROME (TJ5A, TJ5C & F109)
BRIGHT NICKEL (F191, F228 & F123)

*THE SHUTTERED BARREL CAN BE PASSIVATED AND
GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION
WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.



F143



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING		
		ROUND	SQUARE	CONICAL
FH	200	F143	-	F387
H		F358*	F336	F381
1F M		F324	F337	-
FH	200	F349*	F338	-
1F M		F347*	-	-
H	50	F292	-	-

MAXIMUM PANEL THICKNESS: 0.8 - 1.2 STANDARD, 2.65 MAXIMUM.

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3, 8, 9 (F358 MOVEMENTS 3 & 8 ONLY)

STANDARD FINISH: BRIGHT CHROME

BRIGHT NICKEL (F358, F349, F347)

* F358, F349, F347 WITHOUT CAP (NICKEL PLATED VERSION)


FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.



TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 9.5mm,11.1mm,12.6mm and 16.6mm



F378

0258/B913/B914



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING	DIM A	DIM B
9000 M	500	F378	15,5 MAX	6,9
FH	200	F399	18,3	4,4
FH	200	F418	15,5 MAX	4,4
FH	200	F423	15,5 MAX	4,4
1F M	200	F424	15,5 MAX	4,4
2000 M	2000	F416*	18,8 MAX	6,9

PANEL THICKNESS: F418, F399 = 3mm

F378, F423, F424 = 2mm, F416* = 2mm or 5mm

*F416 IS AVAILABLE WITH NUT OR HORSESHOE CLIP FIX. PANEL THICKNESS IS 2mm WITH HORSESHOE CLIP OR UP TO 5mm WITH NUT FIXING.

STANDARD MOVEMENTS: 1, 2, 3, 4 (F416)
3, 4 (F418, F399, F378, F423, F424)

STANDARD FINISHES: CHROME (F416, F418, F424).
NICKEL (F378, F399, F423).

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	
		ROUND HEAD	SQUARE HEAD
800 M	200	-	B913
800 M	200	0258	B914

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1, 3, 4

STANDARD FINISHES: BRIGHT CHROME (0258).
BLACK CHROME (B913, B914).

THE CAM IS RETAINED BY AN E-CLIP



LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk



Camlock 9.5mm

Camlock 11.0mm



F523

F291



PRODUCT REFERENCE NUMBERS		
KEY SERIES	COMBINATIONS	LOCK REFERENCE
FH	200	F523 (CAPPED)
FH	200	F525 (UNCAPPED)
1F M	200	F526 (CAPPED)
1F M	200	F527 (UNCAPPED)
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY		
MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING 1.2mm, NUT FIXING 4mm		
LOCK FIXING: HORSESHOE CLIP OR NUT FIXING		
CAM FIXING: E-CLIP		
STANDARD MOVEMENTS: 3		
STANDARD FINISH: BRIGHT CHROME		
FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.		

PRODUCT REFERENCE NUMBERS		
KEY SERIES	COMBINATIONS	LOCK REF
FH	200	F291 (CAP)
H	50	F322 (CAP)
1F M	200	F399 (NICKEL)
FH	200	F418 (CAP)
FH	200	F423 (NICKEL)
1F M	200	F424 (CAP)
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY		
MAXIMUM PANEL THICKNESS: 1.2mm, BY REQUEST 4mm		
LOCK FIXING: HORSESHOE CLIP, CAM FIXING: CIRCLIP		
STANDARD MOVEMENTS: 3, 4		
STANDARD FINISH: BRIGHT CHROME		
24mm SQUARE HEAD: F291, F322		
21.5mm ROUND HEAD: F399, F418, F423, F424		
FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.		

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
 TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk



Camlock 11.1mm

Camlock 12.6mm



F216

F450



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCK REF
9000 M	500	F216 (CAP)
9000 M	500	F306 (DUST COVER)
9000 M	500	F311 (DUST COVER)
9000 M	500	F316 (NICKEL)
9000 M	500	F378 (NICKEL)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

MAXIMUM PANEL THICKNESS: 1.2mm, BY REQUEST 4mm

LOCK FIXING: HORSESHOE CLIP

CAM FIXING: CIRCLIP

STANDARD MOVEMENTS: 1, 2, 3, 4

STANDARD FINISH: BRIGHT CHROME

FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	LOCK REF
9000 M	500	F450*
9000 M	500	F466*

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
MAXIMUM PANEL THICKNESS: 5mm

LOCK FIXING: HORSESHOE CLIP OR NUT

CAM FIXING: CIRCLIP (F450), SCREW & WASHER (F466)

STANDARD MOVEMENTS: 1, 2, 3, 4, 8 (NUT FIXING ONLY)

STANDARD FINISH: BRIGHT CHROME

* WITH DUST COVER

BARREL ASSEMBLED WITH ROUND GASKET ON REQUEST
FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12.


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk



Camlock 10.0mm

Camlock 11.1mm



C046

3105



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	PRODUCT REF
800	200	C046

MAXIMUM PANEL THICKNESS: 7mm

STANDARD MOVEMENTS: 08

STANDARD FINISH: NICKEL PLATED

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	CAPPED	NICKEL PLATED
6600 M	500	3105	3106

MAXIMUM PANEL THICKNESS: 4mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 01,03 & 04

STANDARD FINISH: NICKEL PLATED

LOCK FIXING: HORSESHOE CLIP OR NUT.



LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk




Camlock 11.1mm

Camlock 11.9mm



C330

C159



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS




KEY SERIES	COMBINATIONS	PRODUCT REF
800	200	C330

MAXIMUM PANEL THICKNESS: 5mm

STANDARD MOVEMENTS: 08, 03, 04

STANDARD FINISH: NICKEL PLATED

LOCK FIXING: HORSESHOE CLIP OR NUT



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	PRODUCT REF
1D	200	C159

MAXIMUM PANEL THICKNESS: 5mm

STANDARD MOVEMENT: 02

STANDARD FINISH: NICKEL PLATED


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm

Camlock 11mm



B726



FIXING HOLE SIZE


PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIX
800 M	200	B726

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1
STANDARD FINISH: BRIGHT NICKEL



B734



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	NUT FIXING
2D	200	B734

STANDARD MOVEMENTS: 1
STANDARD FINISH: BRIGHT NICKEL


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
 TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm



B735/B764/B906



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	SNAP IN FIXING
92 M	200	B735
92 M	200	B764
92 M	200	B906

MAXIMUM PANEL THICKNESS: B735 = 1 - 1,2mm
 B764 = 0,8 - 1mm
 B906 = 1,35 - 1,55mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1


STANDARD FINISH:

CYLINDER = BRIGHT NICKEL


HOUSING = BLACK PLASTIC

CAM RETAINED BY A CIRCLIP

Camlock 11mm



B713



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING	NUT FIXING
89	200	B713	
	75		B880

MAXIMUM PANEL THICKNESS: B713 = 7mm
 B880 = 9mm

STANDARD MOVEMENTS: 5,6 (B713 ONLY)
 8 (B880 ONLY)

STANDARD FINISH: BRIGHT CHROME

NB : THIS LOCK IS SIMILAR TO "4698" (PAGE 1.22)
 EXCEPT FOR THE "D" SHAPE

LOWE & FLETCHER LTD



MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm



1362



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
92 M	200	1361 (1328)	1362 (1329)
95-97 M	2000	1461	1462
89	200	4661	4662
93E M	500	4761	4762

MAXIMUM PANEL THICKNESS: NUT FIXING 4mm, HORSESHOE CLIP FIXING 7mm ACROSS FLATS, 3.2mm ACROSS ROUNDS.

(ACROSS FLATS NOT AVAILABLE WITH MOVEMENTS 5 & 6)



M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
REF. No.s IN () APPLY TO LOCKS WITH CAM RIVETTED ON

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6, 7

STANDARD FINISH: BRIGHT CHROME



1363



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
92 M	200	1363 (1330)	1364 (1331)
95-97 M	2000	1463	1464
89	200	4663	4664
93E M	500	4763	4764
25-27 M	2000		4264

MAXIMUM PANEL THICKNESS: NUT FIXING 4mm, HORSESHOE CLIP FIXING 7mm ACROSS FLATS, 3.2mm ACROSS ROUNDS

(ACROSS FLATS NOT AVAILABLE WITH MOVEMENTS 5 & 6)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
REF. No.s IN () APPLY TO LOCKS WITH CAM RIVETTED ON

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6, 7


STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm



0361



PRODUCT REFERENCE NUMBERS

KEY SERIES	COM-BINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
STANDARD VERSION			
92 M	200	0361	0362
89	200	0611	0612
25-27 M	2000	(B489)	

SHUTTERED VERSION

89	200	0609 (4669)*	0610 (4673)*
----	-----	--------------	--------------

MAXIMUM PANEL THICKNESS: NUT FIXING: 4mm,
HORSESHOE CLIP FIXING 7mm ACROSS FLATS 3.2mm ACROSS ROUNDS


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6
(ACROSS ROUNDS NOT AVAILABLE WITH MOVEMENTS 5, 6)


STANDARD FINISH: BRIGHT CHROME

REF. No.s IN () APPLY TO LOCKS WITH CAM RETAINED BY CIRCLIP

*THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS



0364



PRODUCT REFERENCE NUMBERS

KEY SERIES	COM-BINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
STANDARD VERSION			
92 M	200	0363	0364
89	200	0615 (B284)	0616

SHUTTERED VERSION

89	200	0613*	0614*
----	-----	-------	-------

MAXIMUM PANEL THICKNESS: NUT FIXING: 4mm,
HORSESHOE CLIP FIXING 7mm ACROSS FLATS 3.2mm ACROSS ROUNDS

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6
(ACROSS ROUNDS NOT AVAILABLE WITH MOVEMENTS 5, 6)

STANDARD FINISH: BRIGHT CHROME

REF. No.s IN () APPLY TO LOCKS WITH CONICAL HEAD

*THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm



4698



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
STANDARD VERSION		
92 M	200	1398
89	200	4698
25-27 M	2000	B566
25-27 M	2000	B802

SHUTTERED VERSION

89	200	4699*
----	-----	-------


MAXIMUM PANEL THICKNESS: 7mm ACROSS FLATS, 3.2mm ACROSS ROUNDS

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY


STANDARD MOVEMENTS: 1, 2, 3, 4 (8: B566 ONLY)
(3, 4: B802 ONLY)

STANDARD FINISH: BRIGHT CHROME

* THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS



0398



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
STANDARD VERSION		
92 M	200	0398
89	200	0620
SHUTTERED VERSION		
89	200	0618*

MAXIMUM PANEL THICKNESS: 7mm ACROSS FLATS, 3.2mm ACROSS ROUNDS

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4

STANDARD FINISH: BRIGHT CHROME


* THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 11mm and 12mm



0236



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
800 M	200	0236 (0244)	0223

MAXIMUM PANEL THICKNESS: NUT FIXING 5.5mm, HORSESHOE CLIP FIXING 7.4mm ACROSS FLATS, 5.6mm ACROSS ROUNDS.

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4


STANDARD FINISH: BRIGHT CHROME

REF. No.s IN () APPLY TO LOCKS WITH SPECIAL HEADS

0244 - CAN ONLY BE SUPPLIED WITH MOVEMENT 01



F20



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
A.C.E	SEE PAGE 12.25	F20

MAXIMUM PANEL THICKNESS: NUT FIXING 5mm, HORSESHOE CLIP FIXING 7mm ACROSS FLATS, 4mm ACROSS ROUNDS.

STANDARD MOVEMENTS: 1, 2, 3, 4

STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 12mm



1407



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
92 M	200	1307	1308
95-97 M	2000	1407	1408
93E M	500	4707	4708


MAXIMUM PANEL THICKNESS: NUT FIXING 5mm, HORSESHOE CLIP FIXING 7mm, ACROSS FLATS, 4mm ACROSS ROUNDS.

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY


STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

(ACROSS FLATS FIXING NOT AVAILABLE WITH MOVEMENTS 8 & 9)

STANDARD FINISH: BRIGHT CHROME



0604



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
92 M	200	0307	0308
89	200	0603	0604
93E M	500	0703	0704
800 M	200		B856
E	SEE PAGE 12.25		F285

SHUTTERED VERSION

9000 M	500	F122*	
MAXIMUM PANEL THICKNESS: NUT FIXING 5mm HORSESHOE CLIP FIXING ACROSS FLATS = 7mm (FOR B856 MAX = 5.5, MIN = 1.6) (3.2mm FOR F285). ACROSS ROUNDS = 3.2mm			
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9 (ACROSS FLATS FIXING NOT AVAILABLE WITH MOVEMENTS 8 & 9)			
STANDARD FINISH: BRIGHT CHROME NICKEL PLATED (F285 & B856 ONLY)			


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 13mm



Camlock 11,5mm



1310



F200



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS



KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
92 M	200	1309	1310
95-97 M	2000	1409	1410
93 E M	500	4709	4710
H	PLEASE ASK		F322

MAXIMUM PANEL THICKNESS: NUT FIXING 5mm
HORSESHOE CLIP FIXING 7mm ACROSS FLATS,
4mm ACROSS ROUNDS

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: BRIGHT CHROME



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	DIM X
92 M	200	F200	16 MAX
95-97 M	2000	F199	16 MAX
95-97 M	2000	F309	18 MAX

MAXIMUM PANEL THICKNESS: 4,5mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1

STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk


Camlock 13.5mm ————— Camlock



B604



B686



LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 13.1mm and 13.2mm



F45



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
9000 	500	F130	F45

MAXIMUM PANEL THICKNESS:

F45 = 1,2 STANDARD 5,5 MAXIMUM, F130 = 5,5 MAXIMUM

 = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3


STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD



MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 13mm



0309



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
92 M	200	0309	0310
89	200	0607	0608
9000 M	500	-	F415

MAXIMUM PANEL THICKNESS: NUT FIXING 5mm, HORSESHOE CLIP FIXING 7mm ACROSS FLATS, 4mm ACROSS ROUNDS



M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4

STANDARD FINISH: BRIGHT CHROME



F5A



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	
		STANDARD	SHUTTERED
93E M	500	F5	F55*
A.C.E	SEE PAGE 5.21 & 12.25	F5A(C)(E)	

MAXIMUM PANEL THICKNESS: 5mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4

STANDARD FINISH: BRIGHT CHROME

*THE SHUTTERED BARREL CAN BE GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.

LOWE & FLETCHER LTD



MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 13mm and 15mm



5101



PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
75 M	200	5101 (5102)	5103 (5104)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY



STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: 2A=BRIGHT CHROME

REF No.s IN () APPLY TO LOCKS WHICH HAVE A CAM RETAINED BY A CIRCLIP, ON ALL OTHER LOCKS THE CAM IS RETAINED BY A NUT.



0218



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
800 M	200	0218

MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING: 4.4mm ACROSS FLATS 2.6mm ACROSS ROUNDS

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 15mm

(Shuttered)



B740



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIX
89	200	B740


STANDARD MOVEMENTS: 9

STANDARD FINISH: OLIVE DRAP

Camlock 18,5mm



B654



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
25-27 M	2000	B654

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2

STANDARD FINISH: BLACK CHROME

THE CAM IS RETAINED BY NUT AND WASHER

THE LOCK CAN BE MOUNTED EITHER WITH AN

"01" OR AN "02" MOVEMENT WITH THE SAME HOUSING

BY REVERSING THE STOP PLATE

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock




Camlock Shuttered



B775



B828



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS




KEY SERIES	COMBINATIONS	SNAP IN FIXING
92 M	2000	B775

MAXIMUM PANEL THICKNESS: 1.2mm


M = MASTER KEY SYSTEM SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3, 4

STANDARD FINISHES: BLACK PLASTIC (HOUSING)
BRIGHT NICKEL (CYLINDER)



BARREL MOVEMENT
KEY REMOVABLE AT
12 O' CLOCK



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
89	200	B828

MAXIMUM PANEL THICKNESS: NUT FIXING 8mm

STANDARD MOVEMENTS: 1, SPECIAL

STANDARD FINISHES: BRIGHT CHROME


CYLINDER EQUIPPED WITH A DUST COVER

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 15mm



F313




PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	CAM FIXING	HORSESHOE CLIP FIXING
9000 M	500	CLIP	F272
		CLIP	F313
		NUT	F268
		CLIP	F398

MAXIMUM PANEL THICKNESS: F398: 3mm
F272, F313, F268: 0.9 TO 1.2mm STANDARD, 7.5mm MAX.
M = MASTER KEY SYSTEM SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 3 (3 & 4 F398 ONLY)
STANDARD FINISHES: NICKEL (WITHOUT CAP) F268, F313, F398. BRIGHT CHROME (WITH CAP) F272 ONLY.

Camlock 15mm



F396



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
9000 M	500	F396
		F395



MAXIMUM PANEL THICKNESS: 3mm
M = MASTER KEY SYSTEM SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 3 & 4.
STANDARD FINISHES:
F396: HOUSING & BARREL NICKEL
F395: NICKEL.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
 TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 17.5mm

Camlock 20mm



F402



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
FH	200	F402
1F M	200	F405
FH	200	F404*
1F M	200	F406*

MAXIMUM PANEL THICKNESS:

F404, F406: 2 TO 10mm

F402, F405: 12mm


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3, 4.

STANDARD FINISH: CHROME

*F404 & F406 ARE AVAILABLE WITH NUT OR HORSESHOE CLIP FIXING.

3803



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	WITH CAP	WITH CAP & DUST COVER	WITHOUT CAP
2000 M	2000	3801	-	-
2000 M	2000	-	3802	-
2000 M	2000	-	-	3803

MAXIMUM PANEL THICKNESS: HORSESHOE CLIP FIXING FROM 0.8mm TO 1.2mm AS STANDARD 13mm AS MAX. NUT FIXING: 13mm MAX

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

CAM FIXING: SCREW AND WASHER

STANDARD MOVEMENTS: 1, 3, 4.

STANDARD FINISH: CHROME, (3803 NICKEL PLATED)


BARREL ASSEMBLED WITH ROUND GASKET ON REQUEST

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk


Camlock 16.7mm



Camlock 17mm



F467



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	WITH CAP	WITHOUT CAP
2000 	2000	F467	-
		F468*	-
		-	F469

MAXIMUM PANEL THICKNESS: 0.8-1.2mm STANDARD, 8.8mm MAXIMUM

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3, 4


STANDARD FINISHES: NICKEL (F469), BRIGHT CHROME (F467, F469)

CAM FIXING: CIRCLIP LOCK FIXING: HORSESHOE CLIP

* WITH DUST COVER

FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12

F492



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	WITH CAP	WITHOUT CAP
2000 	2000	-	F492
		F493	-
		F494*	-

MAXIMUM PANEL THICKNESS: 0.8-1.2mm STANDARD, 10.0mm MAXIMUM

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3

STANDARD FINISHES: NICKEL (F492), BRIGHT CHROME (F493, F494)

CAM FIXING: SCREW & WASHER

LOCK FIXING: HORSESHOE CLIP OR NUT

* WITH DUST COVER

FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 17.2mm



F342




PRODUCT INFORMATION				
KEY SERIES	COMBINATION	LOCK REF	CAM FIXING	LOCK FIXING
2000 M	2000	F342	E-CLIP	HORSESHOE CLIP
MAXIMUM PANEL THICKNESS: 1.22 - 1.63mm (OTHER THICKNESS; MILLING FROM MACHINE) M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY STANDARD MOVEMENTS: 1,2,3,4 & 8 STANDARD FINISHES: OLIVE DRAB HOUSING & STAINLESS STEEL CAP GREASED BARREL CAMS AND ACCESSORIES: SEE PAGE 12.31				


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 15mm and 16mm



0233/3100/3133



PRODUCT REFERENCE NUMBERS

KEY SERIES	COM BINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
800	100	0233	0238
31 M	500	3100	-
31 M	500	3133	-


MAXIMUM PANEL THICKNESS: NUT FIXING 9.5mm, HORSESHOE CLIP FIXING 11mm ACROSS FLATS, 9.5mm ACROSS ROUNDS.

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9 (0233, 0238)
1, 2, 3, 4 (3100, 3133)

STANDARD FINISH: BRIGHT CHROME

1332



PRODUCT REFERENCE NUMBERS

KEY SERIES	COM BINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
STANDARD VERSION			
92 M	200	1332 (B332)	1333
95-97 M	2000	1432	1433
92 M	200	(B223)	(B197)
SHUTTERED VERSION			
92 M	200	1348	1358
89	200	(4648)	(4658)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6, 7

STANDARD FINISH: BRIGHT CHROME

REF. No.s IN () APPLY TO LOCKS WITH SPECIAL HEADS (SEE DRAWING)


THE BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 15.7mm, 16mm, 18mm, 18.2mm and 22.2mm



1334



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
92 M	200	1334	1335
95-97 M	2000	1434	1435

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY


STANDARD MOVEMENTS: 1, 2, 3, 4, 5*, 6*, 7*

STANDARD FINISH: BRIGHT CHROME

*MOVEMENTS 5, 6 & 7 NOT AVAILABLE ON PRODUCTS WITH A CYLINDRICAL HEAD.



0706



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	L
93E M	500	0706	18
9000 M	500	F348*	18
2000 M	2000	F356	18
2000 M	2000	F357*	18
45-47 M	2000	F391**	22
9000 M	500	F334	18
9000 M	500	F433*	15,5
45-47 M	2000	F522* **	22,2

MAXIMUM PANEL THICKNESS: 14mm, F334: 6mm, F433: 4mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4, 8

F433: 3 ONLY, F334: 3 & 4 ONLY

STANDARD FINISH: BRIGHT CHROME, F334 NICKEL ONLY

*WITH SHUTTER **AVAILABLE AS HORSESHOE CLIP ON REQUEST

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 19mm and 17,1mm — Camlock 18,6mm

Shuttered



F6



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	
		STANDARD	SHUTTERED
93E M	500	F6	F56*
A.C.E.Y	SEE PAGE 12.25	F6A(C)(E)(Y)	-
2000 M	2000	F430	F431

MAXIMUM PANEL THICKNESS: 14mm. 10mm FOR F430 & F431

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY.

STANDARD MOVEMENTS: 1, 3, 4, 8.


STANDARD FINISH: BRIGHT CHROME.

FIXING: NUT CAM

* THE SHUTTERED BARREL CAN BE GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.



B829



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
89	200	B829

MAXIMUM PANEL THICKNESS: 9mm

STANDARD MOVEMENTS: 8

STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 19,7mm

Camlock 20mm & 27.2mm



F341



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	CAM FIXING	REFERENCE NUMBER
9000 M	500	NUT	F341*
9000 M	500	SCREW & WASHER	F419*
2000 M	2000	NUT	F380*
2000 M	2000	NUT	F379
2000 M	500	NUT	F350

MAXIMUM PANEL THICKNESS: 12mm, LOCK FIXING WITH HORSESHOE CLIP OR NUT

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8

STANDARD FINISH: BRIGHT CHROME


*WITH DUST COVER.

BARREL ASSEMBLED WITH A ROUND GASKET ON REQUEST

FOR CAMS AND ACCESSORIES SEE PAGE 12.31



4239



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	SNAP-IN FIXING
25-27 M	2000	4239 (4238)
92 M	200	F373

MAXIMUM PANEL THICKNESS: 3mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4

F373 MOVEMENTS 3 & 4 ONLY.

STANDARD FINISH: BRIGHT CHROME

REF. No. IN () REFERS TO LOCKS WITH A CONICAL HEAD.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm



1336




PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
92 M	200	1336 (1375)	1337 (1376)
FS	80	(2724)	
95-97 M	2000	1436 (1475)	1437 (1476)
93E M	500	(4775)	(4776)
9000 M	500	(F350)	
2000 M	2000	(3875) (3836)	(3876) (3837)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6, 7
 1, 2, 3, 4, 8 (F350)
STANDARD FINISHES: BRIGHT CHROME
 STAINLESS STEEL CAP
 NICKEL
 REF. No.s IN () REFER TO LOCKS WITH A CONICAL HEAD WHICH ARE AVAILABLE IN CHROME FINISH ONLY (F350 NICKEL ONLY).



1339



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	SNAP IN FIXING	HORSESHOE CLIP FIXING
92 M	200	1339 (1338)	1344 (1343)
95-97 M	2000	1439 (1438)	1444 (1443)
93E M	500	4739 (4738)	4744 (4743)
89	200	(4601)*	
2000 M	2000	3839 (3838)	3844 (3843)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY
STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9
STANDARD FINISH: BRIGHT CHROME
 REF. No.s IN () REFER TO LOCKS WITH A CONICAL HEAD
 *LOCK 4601 IS SUPPLIED WITH THE CAM RETAINED BY A CIRCLIP


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
 TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm




2105



PRODUCT REFERENCE NUMBERS				
KEY SERIES		COM-BINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
66-68	DOUBLE ENTRY M	2000	2105	2107
81-83	DOUBLE ENTRY M	2000	2131	2133
85-87	DOUBLE ENTRY M	2000	2139	2141
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY				
STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6				
STANDARD FINISH: BRIGHT CHROME				



2106




PRODUCT REFERENCE NUMBERS				
KEY SERIES		COM-BINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
66-68	DOUBLE ENTRY M	2000	2106	2108
81-83	DOUBLE ENTRY M	2000	2132	2134
85-87	DOUBLE ENTRY M	2000	2140	2142
M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY				
STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6				
STANDARD FINISH: BRIGHT CHROME				


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm



0801



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
STANDARD VERSION			
45-47 M	2000	0801 (0805)	0803 (0807)
SHUTTERED VERSION*			
45-47 M	2000	0851 (0855)	0853 (0857)

MAXIMUM PANEL THICKNESS: 12mm ACROSS FLATS ONLY


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4


STANDARD FINISH: BRIGHT CHROME

*THE SHUTTERED BARREL CAN BE PASSIVATED AND GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS

REF No.s IN () REFER TO LOCKS WITH A CONICAL HEAD



0802/4223/4224



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	FIXING HOLE	NUT FIXING	HORSESHOE CLIP FIXING
STANDARD VERSION				
45-47 M	2000	'A'	0802 (0806)	0804 (0808)
45-47 M	2000	'B'	0812 (0816)	0814 (0818)
25-27 M	2000	'B'	(4224) (4223) (F353)	

SHUTTERED VERSION*

45-47 M	2000	'A'	0852* (0856)*	0854* (0858)*
45-47 M	2000	'B'	0862* (0866)*	0864* (0868)*

MAXIMUM PANEL THICKNESS: NUT FIXING 12mm
HORSESHOE CLIP FIXING 12mm ACROSS FLATS ONLY.

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, (8 - 0802 ONLY)

STANDARD FINISH: BRIGHT CHROME


*THE SHUTTERED BARREL CAN BE GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS. REF. No. IN () REFERS TO LOCKS WITH A CONICAL HEAD.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm



1345



PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING
92 M	200	1345	1377
95-97 M	2000	1445	1477
93E M	500	4745	4777
2000 M	2000	3845	3877

MAXIMUM PANEL THICKNESS: 12mm


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8, 9

STANDARD FINISH: BRIGHT CHROME



4202



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	FIXING HOLE TYPE	NUT FIXING	CLIP FIXING
25-27 M	2000	'A'	4202 (4206)	4204 (4208)
		'B'	4201 (4205)	4203 (4207)
		'C'	4212 (4216)	4214 (4218)
WITH REMOVABLE BARREL*				
25-27 M	2000	'A'	4215*	
		'B'	4220*	
		'C'	(4217)*	

MAXIMUM PANEL THICKNESS: 12mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4

(4212 - MOVEMENTS 1 & 3 ONLY)

(4215, 4217 & 4222 - MOVEMENT 3 ONLY)

STANDARD FINISHES: BRIGHT CHROME

REF No.s IN () APPLY TO LOCKS WITH A CONICAL HEAD.

*THESE LOCKS ARE EQUIPPED WITH AN INTERCHANGEABLE BARREL. THE BARREL IS REMOVABLE IN THE OPEN POSITION OF THE LOCK ONLY BY THE USE OF A SPECIAL KEY.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm



3101/3102



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	CAPPED VERSION	UNCAPPED VERSION
66 M	500	3101	3102

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4

STANDARD FINISH:

3101 HOUSING AND BARREL CAPPED

3102 HOUSING AND BARREL NICKLE PLATED


NUT FIXING: 8980203

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk


Camlock 20.3mm



Camlock



F344



PRODUCT INFORMATION

KEY SERIES	COMBINATION	LOCK REF	CAM FIXING	LOCK FIXING
2000 M	2000	F344	SCREW & WASHER	HORSESHOE CLIP OR NUT

MAXIMUM PANEL THICKNESS: 1.22 - 1.63mm AS STANDARD WITH HORSESHOE CLIP (OTHER THICKNESS; MILLING FROM MACHINE) & 7mm WITH SCREW FIXING


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1 & 3

STANDARD FINISHES: OLIVE DRAB HOUSING & STAINLESS STEEL CAP

BARREL ASSEMBLED WITH O-RING AND GREASED CAMS AND ACCESSORIES: SEE PAGE 12.31

3811/3821



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	BARREL	LOCK FIXING		
			NUT	HORSE-SHOE CLIP	SNAP IN
2000 M	2000	CAPPED	3811** 3821	*3814** *3824	3817** 3827
2000 M	2000	DUST COVER	3812** 3822	*3815** *3825	3818** 3828
2000 M	2000	UN CAPPED	3813** 3823	*3816** *3826	3819** 3829

MAXIMUM PANEL THICKNESS: 9MM MAX
0.5 - 0.80MM (CLIP 9106401) 1.5 - 1.83MM (CLIP 9106501)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3, 4, 8, 9

STANDARD FINISHES: OLIVE DRAB

*ONLY 500 COMBINATIONS FOR MOVEMENTS 8 & 9

BARREL ASSEMBLED WITH "O" RING ON REQUEST
CAMS AND ACCESSORIES SEE PAGE 12.31

LOWE & FLETCHER LTD



MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm and 22.4mm



4795



PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	SNAP-IN FIXING
93E M	500	4795
2000 M	2000	3895

MAXIMUM PANEL THICKNESS: 3mm


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 8



STANDARD FINISH: SATIN NICKEL



B356



B356
FIXING HOLE SIZE



B290
FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING
45-47 M	2000	B356
45-47	2000	B290

MAXIMUM PANEL THICKNESS: 17mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3


STANDARD FINISH: BRIGHT CHROME

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 22mm, 22.4mm, 27mm, 32mm



1342



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING	HORSESHOE CLIP FIXING
22MM			
92 M	200	1340	1384
95-97 M	2000	1440	1484
27MM			
92 M	200	1341 (B441)	1385
95-97 M	2000	1441	1485
32MM			
92 M	200	1342 (B442)	1386


M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 2, 3, 4, 5, 6


STANDARD FINISHES: BRIGHT CHROME
STAINLESS STEEL CAP

HOUSING NUT CAN ONLY BE FITTED OR REMOVED IF CAM IS REMOVED FIRST.

REF NO'S. IN () APPLY TO LOCKS WITH CONICAL HEAD.



B561



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	HORSESHOE CLIP FIXING	Ø A
25-27 M	2000		B561	25
45-47 M	2000	0815		24
45-47 M	2000	B938*		25
SHUTTERED VERSION				
45-47 M	2000	0865		24
89	200	B962		22.5

MAXIMUM PANEL THICKNESS: 10mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4

1, 2, 3, 4 (B962 ONLY)

STANDARD FINISH: BRIGHT CHROME

*B938: CAM RETAINED BY NUT AND WASHER

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 22.3mm



B743



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	HORSESHOE CLIP FIXING
89	200	B743

STANDARD MOVEMENTS: 1,31

STANDARD FINISH: EPOXY BLACK


CYLINDER EQUIPPED WITH A DUST COVER

Camlock 22mm

Shuttered



B850



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
89	200	B850

MAXIMUM PANEL THICKNESS: 13mm

STANDARD MOVEMENTS: 8, 9

STANDARD FINISH: BRIGHT CHROME


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 20mm, 22.4mm

Camlock 31mm



F177



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	CLIP FIXED CAM	NUT FIXED CAM
25 M	2000	F177	F355
25	2000	-	F497
45	2000	F278	-

MAXIMUM PANEL THICKNESS: 12mm

M = MASTER KEY SYSTEM SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 3


STANDARD FINISH: BRIGHT CHROME

KEYS: BRASS NICKEL

ANTI-KICKING SYSTEM

FOR DETAILS OF CAMS PLEASE REFER TO SECTION 12 .

F343



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATION	LOCK REF	CAM FIXING	LOCK FIXING
2000 M	2000	F343	SCREW & WASHER	HORSESHOE CLIP

MAXIMUM PANEL THICKNESS: 1.63 - 2.05mm
(OTHER THICKNESS; MILLING FROM MACHINE)

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1 & 3

STANDARD FINISHES: OLIVE DRAB HOUSING & STAINLESS STEEL CAP

BARREL ASSEMBLED WITH O'RING AND GREASED
CAMS AND ACCESSORIES: SEE PAGE 12.31

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 31.7mm, 32mm, 32.5mm and 33mm



0707



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	'L'
93E M	500	0707	32
25-27 M	2000	4221	32
45-47	2000	0817	32
2000	2000	F376*	32.5
9000 M	500	F397	31.7
2000 M	2000	F425	31.7

MAXIMUM PANEL THICKNESS: 28mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4, 8
(8 FOR 0817 WITH 400 COMBINATIONS ONLY)

STANDARD FINISH: BRIGHT CHROME


WE RECOMMEND THE USE OF PLATE B4141 WHEN FITTING LOCK IN WOODEN PANELS

*NO CAM SUPPLIED WITH RETAINING WASHER

WE CAN DELIVER OVER MOULDED KEYS ON DEMAND



F7



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING	
		STANDARD	SHUTTERED
93E M	500	F7	F57*
A.C.E	SEE PAGE 12.25	F7A(C)(E)	

MAXIMUM PANEL THICKNESS: 28mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 1, 3, 4, 8

STANDARD FINISH: BRIGHT CHROME

WE RECOMMEND THE USE OF PLATE B4141 WHEN FITTING LOCK IN WOODEN PANELS

*THE SHUTTERED BARREL CAN BE GREASED IF REQUIRED

TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.



TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 22mm

for harsh environments



1414



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXING
95/97 M	2000	1414

MAXIMUM PANEL THICKNESS: 12mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY


STANDARD MOVEMENTS: 1

STANDARD FINISH: STAINLESS STEEL CAP. 4


WITH SHUTTERED BARREL.

DESIGNED FOR OUTDOOR USE AT TEMPERATURES AS LOW AS -40° C

Camlock 22,6mm



5800



FIXING HOLE SIZE

PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIX	SNAP IN FIX	HORSE-SHOE FIX
18 M	200 *	5800	5801	5802
35 M	200 *	5600	5601	5602

MAXIMUM PANEL THICKNESS:

HORSESHOE & NUT FIX = 11mm SNAP IN FIX = MINIMUM 0.6m
MAXIMUM 1.82mm

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 18 SERIES - 1, 2, 3, 4, 8, 9 FIXED
BARREL. 35 SERIES - 3, 8 REMOVABLE BARREL.

STANDARD FINISHES: 2A = BRIGHT CHROME, 6N = BLACK FINISH
REFER TO SECTION 12 FOR DETAILS ON REMOVABLE
BARREL SYSTEM.

* 18 SERIES 1000 COMBINATIONS TO ORDER ONLY.

* 35 SERIES 500 COMBINATIONS TO ORDER ONLY.

USE 'T' CAMS SPECIFIED ON PAGE 12.31.

LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk


Slamlock 19.7mm and 20mm



1397



4681




LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.


TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Slamlocks Key Operated

Slamlock 22.5mm



0305/5836



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED	CLIP FIXED	DIM A	DIM B
92 M	200	0305	0336	20	14.7
18 M	200	5836		20	12.0
89 D/E M	200	(B586)		21	14.0

M = MASTER KEY SYSTEM: SUPPLIED TO ORDER ONLY

STANDARD MOVEMENTS: 0305 = 1

5836 = 0 (SEE SECTION 12)

B586 = 2

STANDARD FINISH: 2A = BRIGHT CHROME


2C = SATIN CHROME

2B = BLACK CHROME

ACCESSORIES: SUPPLIED WITH DIECAST STRIKER PLATE, RECOMMENDED FIXING SCREWS M3x8 (NOT SUPPLIED)

REF. NO.S IN () APPLY TO LOCKS IN SHUTTERED VERSION

B916



PRODUCT REFERENCE NUMBERS

SHUTTERED VERSION

KEY SERIES	COMBINATIONS	NUT FIXED
89	200	B916

STANDARD MOVEMENT: 1

STANDARD FINISH: BRIGHT CHROME

THE CAM IS RETAINED BY A NUT

CAM SLAM ACTION POSSIBLE WITH OR WITHOUT KEY IN LOCK

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.



TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock 22mm


With Caulking Cam



1301



B448



LOWE & FLETCHER LTD


MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk



Camlock 20mm



B505





B233



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	NUT FIXED HOUSING
2D	200	B505

STANDARD MOVEMENTS: 8
STANDARD FINISHES: BRIGHT CHROME



PRODUCT REFERENCE NUMBERS


KEY SERIES	COMBINATIONS	REFERENCE
SPECIAL	200	B233

STANDARD MOVEMENTS: 8
STANDARD FINISHES: BRIGHT NICKEL


LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk

Camlock




0869






LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.
TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk




Upper Grade Lock



UGL



CONICAL HEAD



PRODUCT REFERENCE NUMBERS

KEY SERIES	COMBINATIONS	FIXING HOLE	NUT FIXING	HORSESHOE CLIP FIXING
STANDARD VERSION				
UGL	10000	A	0902 (0906)	0904 (0908)
UGL	10000	B	0912 (0916)	0914 (0918)
UGL	10000	B	(0900)HOUSING WITH PLASTIC CAP	
UGL	10000	B	0901 (0905)	0903 (0907)
SHUTTERED VERSION				
UGL	10000	A	0952* (0956)*	0954* (0958)
UGL	10000	B	0962* (0966)*	0964* (0968)
UGL	10000	B	0951* (0955)*	0953* (0957)

MAXIMUM PANEL THICKNESS: NUT FIXING 12mm HORSESHOE CLIP FIXING 12mm ACROSS FLAT ONLY

STANDARD MOVEMENTS: 1,2,3 & 4 (MOVEMENT 8 & 9 ONLY WITH NUT FIXING OR HORSESHOE CLIP ACROSS THE ROUND SIDES OF THE HOUSING)

STANDARD FINISH: BRIGHT CHROME

* THE SHUTTERED BARREL CAN BE GREASED IF REQUIRED TO PROVIDE GREATER PROTECTION WHEN LOCK IS USED IN OUTSIDE APPLICATIONS.

REF NOS. IN () REFERS TO LOCK WITH CONICAL HEAD.

LOWE & FLETCHER LTD

MOORCROFT DRIVE, WEDNESBURY, WEST MIDLANDS, ENGLAND WS10 7DE.

TELEPHONE: 0121 505 0400. FAX: 0121 505 0420. E-MAIL: sales@lowe-and-fletcher.co.uk WEB SITE: www.lowe-and-fletcher.co.uk