


ENERGIZER E95

D



Industry Standard Dimensions




Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-13A, IEC-LR20
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)*
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	148.0 grams (5.2 oz.)
Typical Volume:	56.0 cubic centimeters (3.4 cubic inch)
Jacket:	Plastic Label
Shelf Life:	7 years at 21°C (80% of initial capacity)
Terminal:	Flat Contact

* For additional information, please reference the IR technical white paper.

Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C



Device Selection Guide:

Portable Stereo



Toy




Lighting



Radio



Battery Selection Indicator



Important Notice


This data sheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER E95

D


Constant Resistance Performance

Typical Characteristics (21°C)




Constant Current Performance

Typical Characteristics (21°C)




Industry Standard Tests (21°C)


RADIO 10 ohm 4 hrs/day




LIGHTING 1.5 ohm HIF




LIGHTING 2.2 ohm LIF



TOY 2.2 ohm 1 hr/day



PORTABLE STEREO 600 mA 2 hrs/day



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.