

Tab Contacts


**Tabs 9.5 x 1.2 mm
with Steel Top Spring,
Mates with
Maxi Power Timer**

Modular Dimensions

Standard Version:
min. 11.0 mm x 12.5 mm

**Modular Dimensions with
Single Wire Sealing System:**
18.0 mm x 18.0 mm

Extraction Tool:
Part No. **726551-1**



Standard Tab Contacts

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	Hand Tool
>2.5-4.0	3.3-4.7	-	-1 / -2	963764	700	963765	500	x-878592-x	734531-1
4.0-6.0	4.0-5.2	-	-1 / -2	963766	700	963767	500	x-878593-x	734532-1
6.0-10.0	4.7-6.6	-	-1 / -2	963768	700	963769	500	x-878659-x	734533-1

Tab Contacts with Single Wire Sealing System

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	Hand Tool
>2.5-4.0	4.0-4.5	-	-1 / -2	963770	550	963771	500	x-878980-x	-
4.0-6.0	4.7-5.3	-	-1 / -2	963772	550	963773	500	x-878734-x	-
6.0-10.0	6.2-6.6	-	-1 / -2	963774	550	963775	500	x-878735-x	-

***) Material and Finish:**
xxx-1 = CuSn, pre-tin plated
xxx-2 = CuFe, pre-tin plated

*) The pre- and suffix for the applicators depends on the applied termination equipment.