






RECOMMENDED PANEL CUTOUT

NOTES:

- ALL DIMENSIONS IN MM[INCH]
- GENERAL TOLERANCE: $x.x = \pm 0.4$
 $x.xx = \pm 0.25$
- TERM. NOS. FOR REFERENCE ONLY.
- RATING: 3A @125VAC, 1.5A @250VAC
- CONTACT RESISTANCE: 20milli-OHMS MAX
- DIELECTRIC STRENGTH: 1500 Vrms
- INSULATION RESISTANCE: 200 MEGA-OHMS MIN.
- MATERIALS:


HOUSING: ZINC ALLOY DIE CAST W/ CHROME PLATING
CYLINDER: ZINC ALLOY DIE CAST W/CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED
KEYS (2) KEY CODE 10003: TUBULAR ZINC ALLOY, CHROME PLATING
W/PLASTIC COVER

CIRCUIT: SPDT
CONTACT CONFIGURATION
90° INDEXING

SWITCH FUNCTION	
POS 1	POS 2
↑	→
ON	ON
TERM 1-2	TERM 3-4

LEGEND

- = INDICATES KEY PULL POSSIBLE
● = INDICATES DETENT POSITION



E-SWITCH®

B	16496	FIXED SWITCH FUNCTION TO ON-ON	9/28/2006	TN
A	16477	NEW PART RELEASE	9/26/2006	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE K0104A10003

SCALE 2:1

DATE 9/26/2006

DR TN

DWG K300112

REV B