

Model P232/P233
24mm Rotary Potentiometer
Sealed/ Dust Proof
Long Life Element
2 Million Cycle Life
Metal Shaft/ Bushing
RoHS Compliant



MODEL STYLE

Side Adjust, Solder Lugs, Single-Gang	P232
Side Adjust, Solder Lugs, Dual-Gang	P233

ELECTRICAL¹

Resistance Range, Ohms	1K-1M (for "B" taper) 5K-1M (for other tapers)
Standard Resistance Tolerance	± 10%
Residual Resistance	3 ohms max.
Input Voltage, Maximum	200 Vdc max.
Power rating, Watts	0.5W- B taper, 0.3W- others
Dielectric Strength	500Vac, 1 minute
Insulation Resistance, Minimum	100M ohms at 1,000Vdc/ 1 minute
Peak Noise (Contact Resistance Variation) @ 6 rpm	±3% max.
Linearity	±3% max.
Actual Electrical Travel, Nominal	280°
Gang Error	±3dB (-40dB to 0dB)

MECHANICAL

Total Mechanical Travel	300°± 5°
Static Stop Strength, Minimum	120 oz-in
Rotational Torque, Maximum, Single Gang (P232)	1.5 oz-in
Rotational Torque, Maximum, Dual Gang (P233)	3.0 oz-in


ENVIRONMENTAL

Operating Temperature Range	-10°C to +85°C
Rotational Life	2,000,000 cycles


¹ Specifications subject to change without notice.

Model P232/P233

ORDERING INFORMATION²




Shaft Types



Shaft Position (F-Type Shaft)

Dashed lines on Type "C" and Type "A" shows position of adjustment slot for E-Type shaft



STANDARD RESISTANCE VALUES, OHMS


500 1K 2K 5K 10K 20K 50K 100K 200K 500K 1 M

² Contact our customer service for custom designs and features.


Model P232/P233

OUTLINE DRAWING

Model P232




Model P233




CIRCUIT DIAGRAM

P232 (Single gang)



P233 (Dual gang)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BI Technologies:

[P232-SEC20AR20K](#) [P232-SFC25BR10K](#) [P232-SEC20BR10K](#) [P232-DEA20AR500K](#) [P232-SED20BR100K](#) [P232-SFC20BR10K](#) [P232-DEC20AR20K](#) [P232-SED20BR10K](#) [P232-DEC30BR2K](#) [P232-SFC20BR5K](#) [P232-SEB20BR100K](#) [P232-SEA20BR100K](#) [P232-SEC20BR100K](#) [P232-DEA20BR100K](#) [P232-DE20AR500K](#) [P232-DFC25BR10K](#) [P232-SFC20BR1K](#) [P232-SEB20BR10K](#) [P232-SFA25BR10K](#) [P232-DFC35BR5K](#) [P232-DEC20BR100K](#) [P232-SEA20BR10K](#) [P232-DEC22BR20K](#) [P232-SEC25BR10K](#) [P233-SEC25AR250K](#) [P232-DEC35BR5K](#) [P232-SFC35BR5K](#)

TT electronics:

[P232-DEC20BR10K](#) [P232-SEC20BR50K](#) [P232-DEA20AR1MEG](#) [P232-DEC30BR10K](#) [P232-SFD20AR5K](#) [P233-SEC20BR10K](#) [P232-SFB20BR100K](#) [P233-SFD20AR10K](#) [P232-SEC35BR5K](#) [P232-DEC22BR100K](#) [P232-DCF35BR5K](#) [P232-SEC20AR2K5](#) [P232-DFC35AR100K](#) [P232-DFC20BR5K](#) [P232-SEC20BR1K](#) [P232-SEC20BR5K](#) [P232-SEC22BR10K](#) [P232-SEC20BR1MEG](#)