


# DATA SHEET



## **BZX79 series** Voltage regulator diodes

Product specification  
Supersedes data of 1996 Apr 26

1999 May 25

Voltage regulator diodes

BZX79 series

FEATURES


- Total power dissipation:  
max. 500 mW
- Three tolerance series:  $\pm 1\%$ ,  $\pm 2\%$ ,  
and approx.  $\pm 5\%$
- Working voltage range:  
nom. 2.4 to 75 V (E24 range)
- Non-repetitive peak reverse power  
dissipation: max. 40 W.

APPLICATIONS

- Low voltage stabilizers or voltage  
references.

DESCRIPTION

Low-power voltage regulator diodes in hermetically sealed leaded glass SOD27 (DO-35) packages. The diodes are available in the normalized E24  $\pm 1\%$  (BZX79-A),  $\pm 2\%$  (BZX79-B), and approx.  $\pm 5\%$  (BZX79-C) tolerance range. The series consists of 37 types with nominal working voltages from 2.4 to 75 V.



LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 134).

| SYMBOL    | PARAMETER                                        | CONDITIONS                                                                       | MIN.                        | MAX. | UNIT       |
|-----------|--------------------------------------------------|----------------------------------------------------------------------------------|-----------------------------|------|------------|
| $I_F$     | continuous forward current                       |                                                                                  | –                           | 250  | mA         |
| $I_{ZSM}$ | non-repetitive peak reverse current              | $t_p = 100 \mu s$ ; square wave;<br>$T_j = 25^\circ C$ prior to surge            | see Tables<br>1, 2, 3 and 4 |      |            |
| $P_{tot}$ | total power dissipation                          | $T_{amb} = 50^\circ C$ ; note 1                                                  | –                           | 400  | mW         |
|           |                                                  | $T_{amb} = 50^\circ C$ ; note 2                                                  | –                           | 500  | mW         |
| $P_{ZSM}$ | non-repetitive peak reverse power<br>dissipation | $t_p = 100 \mu s$ ; square wave;<br>$T_j = 25^\circ C$ prior to surge; see Fig.3 | –                           | 40   | W          |
| $T_{stg}$ | storage temperature                              |                                                                                  | –65                         | +200 | $^\circ C$ |
| $T_j$     | junction temperature                             |                                                                                  | –65                         | +200 | $^\circ C$ |

Notes

1. Device mounted on a printed circuit-board without metallization pad; lead length max.
2. Tie-point temperature  $\leq 50^\circ C$ ; max. lead length 8 mm.

## Voltage regulator diodes

## BZX79 series

## ELECTRICAL CHARACTERISTICS

## Total BZX79-A, B and C series

$T_j = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

| SYMBOL | PARAMETER           | CONDITIONS                       | MAX. | UNIT          |
|--------|---------------------|----------------------------------|------|---------------|
| $V_F$  | forward voltage     | $I_F = 10\text{ mA}$ ; see Fig.4 | 0.9  | V             |
| $I_R$  | reverse current     |                                  |      |               |
|        | BZX79-A/B/C2V4      | $V_R = 1\text{ V}$               | 50   | $\mu\text{A}$ |
|        | BZX79-A/B/C2V7      | $V_R = 1\text{ V}$               | 20   | $\mu\text{A}$ |
|        | BZX79-A/B/C3V0      | $V_R = 1\text{ V}$               | 10   | $\mu\text{A}$ |
|        | BZX79-A/B/C3V3      | $V_R = 1\text{ V}$               | 5    | $\mu\text{A}$ |
|        | BZX79-A/B/C3V6      | $V_R = 1\text{ V}$               | 5    | $\mu\text{A}$ |
|        | BZX79-A/B/C3V9      | $V_R = 1\text{ V}$               | 3    | $\mu\text{A}$ |
|        | BZX79-A/B/C4V3      | $V_R = 1\text{ V}$               | 3    | $\mu\text{A}$ |
|        | BZX79-A/B/C4V7      | $V_R = 2\text{ V}$               | 3    | $\mu\text{A}$ |
|        | BZX79-A/B/C5V1      | $V_R = 2\text{ V}$               | 2    | $\mu\text{A}$ |
|        | BZX79-A/B/C5V6      | $V_R = 2\text{ V}$               | 1    | $\mu\text{A}$ |
|        | BZX79-A/B/C6V2      | $V_R = 4\text{ V}$               | 3    | $\mu\text{A}$ |
|        | BZX79-A/B/C6V8      | $V_R = 4\text{ V}$               | 2    | $\mu\text{A}$ |
|        | BZX79-A/B/C7V5      | $V_R = 5\text{ V}$               | 1    | $\mu\text{A}$ |
|        | BZX79-A/B/C8V2      | $V_R = 5\text{ V}$               | 700  | nA            |
|        | BZX79-A/B/C9V1      | $V_R = 6\text{ V}$               | 500  | nA            |
|        | BZX79-A/B/C10       | $V_R = 7\text{ V}$               | 200  | nA            |
|        | BZX79-A/B/C11       | $V_R = 8\text{ V}$               | 100  | nA            |
|        | BZX79-A/B/C12       | $V_R = 8\text{ V}$               | 100  | nA            |
|        | BZX79-A/B/C13       | $V_R = 8\text{ V}$               | 100  | nA            |
|        | BZX79-A/B/C15 to 75 | $V_R = 0.7V_{Znom}$              | 50   | nA            |

## Voltage regulator diodes

## BZX79 series

**Table 1** Per type BZX79-A/B2V4 to A/B24 $T_j = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

| BZX79-<br>A or B<br>XXX | WORKING VOLTAGE<br>$V_Z$ (V)<br>at $I_{Z\text{test}} = 5\text{ mA}$ |       |                    |       | DIFFERENTIAL RESISTANCE<br>$r_{\text{dif}}$ ( $\Omega$ ) |      |                                     |      | TEMP. COEFF.<br>$S_Z$ (mV/K)<br>at $I_{Z\text{test}} = 5\text{ mA}$<br>(see Figs 5 and 6) |      |      | DIODE CAP.<br>$C_d$ (pF)<br>at $f = 1\text{ MHz}$ ;<br>$V_R = 0\text{ V}$ | NON-REPETITIVE PEAK<br>REVERSE CURRENT<br>$I_{ZSM}$ (A)<br>at $t_p = 100\text{ }\mu\text{s}$ ; $T_{\text{amb}} = 25\text{ }^{\circ}\text{C}$ |
|-------------------------|---------------------------------------------------------------------|-------|--------------------|-------|----------------------------------------------------------|------|-------------------------------------|------|-------------------------------------------------------------------------------------------|------|------|---------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
|                         | Tol. $\pm 1\%$ (A)                                                  |       | Tol. $\pm 2\%$ (B) |       | at $I_{Z\text{test}} = 1\text{ mA}$                      |      | at $I_{Z\text{test}} = 5\text{ mA}$ |      | MIN.                                                                                      | TYP. | MAX. | MAX.                                                                      | MAX.                                                                                                                                         |
|                         | MIN.                                                                | MAX.  | MIN.               | MAX.  | TYP.                                                     | MAX. | TYP.                                | MAX. |                                                                                           |      |      |                                                                           |                                                                                                                                              |
| 2V4                     | 2.37                                                                | 2.43  | 2.35               | 2.45  | 275                                                      | 600  | 70                                  | 100  | -3.5                                                                                      | -1.6 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 2V7                     | 2.67                                                                | 2.73  | 2.65               | 2.75  | 300                                                      | 600  | 75                                  | 100  | -3.5                                                                                      | -2.0 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 3V0                     | 2.97                                                                | 3.03  | 2.94               | 3.06  | 325                                                      | 600  | 80                                  | 95   | -3.5                                                                                      | -2.1 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 3V3                     | 3.26                                                                | 3.34  | 3.23               | 3.37  | 350                                                      | 600  | 85                                  | 95   | -3.5                                                                                      | -2.4 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 3V6                     | 3.56                                                                | 3.64  | 3.53               | 3.67  | 375                                                      | 600  | 85                                  | 90   | -3.5                                                                                      | -2.4 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 3V9                     | 3.86                                                                | 3.94  | 3.82               | 3.98  | 400                                                      | 600  | 85                                  | 90   | -3.5                                                                                      | -2.5 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 4V3                     | 4.25                                                                | 4.35  | 4.21               | 4.39  | 410                                                      | 600  | 80                                  | 90   | -3.5                                                                                      | -2.5 | 0    | 450                                                                       | 6.0                                                                                                                                          |
| 4V7                     | 4.65                                                                | 4.75  | 4.61               | 4.79  | 425                                                      | 500  | 50                                  | 80   | -3.5                                                                                      | -1.4 | 0.2  | 300                                                                       | 6.0                                                                                                                                          |
| 5V1                     | 5.04                                                                | 5.16  | 5.00               | 5.20  | 400                                                      | 480  | 40                                  | 60   | -2.7                                                                                      | -0.8 | 1.2  | 300                                                                       | 6.0                                                                                                                                          |
| 5V6                     | 5.54                                                                | 5.66  | 5.49               | 5.71  | 80                                                       | 400  | 15                                  | 40   | -2.0                                                                                      | 1.2  | 2.5  | 300                                                                       | 6.0                                                                                                                                          |
| 6V2                     | 6.13                                                                | 6.27  | 6.08               | 6.32  | 40                                                       | 150  | 6                                   | 10   | 0.4                                                                                       | 2.3  | 3.7  | 200                                                                       | 6.0                                                                                                                                          |
| 6V8                     | 6.73                                                                | 6.87  | 6.66               | 6.94  | 30                                                       | 80   | 6                                   | 15   | 1.2                                                                                       | 3.0  | 4.5  | 200                                                                       | 6.0                                                                                                                                          |
| 7V5                     | 7.42                                                                | 7.58  | 7.35               | 7.65  | 30                                                       | 80   | 6                                   | 15   | 2.5                                                                                       | 4.0  | 5.3  | 150                                                                       | 4.0                                                                                                                                          |
| 8V2                     | 8.11                                                                | 8.29  | 8.04               | 8.36  | 40                                                       | 80   | 6                                   | 15   | 3.2                                                                                       | 4.6  | 6.2  | 150                                                                       | 4.0                                                                                                                                          |
| 9V1                     | 9.00                                                                | 9.20  | 8.92               | 9.28  | 40                                                       | 100  | 6                                   | 15   | 3.8                                                                                       | 5.5  | 7.0  | 150                                                                       | 3.0                                                                                                                                          |
| 10                      | 9.90                                                                | 10.10 | 9.80               | 10.20 | 50                                                       | 150  | 8                                   | 20   | 4.5                                                                                       | 6.4  | 8.0  | 90                                                                        | 3.0                                                                                                                                          |
| 11                      | 10.89                                                               | 11.11 | 10.80              | 11.20 | 50                                                       | 150  | 10                                  | 20   | 5.4                                                                                       | 7.4  | 9.0  | 85                                                                        | 2.5                                                                                                                                          |
| 12                      | 11.88                                                               | 12.12 | 11.80              | 12.20 | 50                                                       | 150  | 10                                  | 25   | 6.0                                                                                       | 8.4  | 10.0 | 85                                                                        | 2.5                                                                                                                                          |
| 13                      | 12.87                                                               | 13.13 | 12.70              | 13.30 | 50                                                       | 170  | 10                                  | 30   | 7.0                                                                                       | 9.4  | 11.0 | 80                                                                        | 2.5                                                                                                                                          |
| 15                      | 14.85                                                               | 15.15 | 14.70              | 15.30 | 50                                                       | 200  | 10                                  | 30   | 9.2                                                                                       | 11.4 | 13.0 | 75                                                                        | 2.0                                                                                                                                          |
| 16                      | 15.84                                                               | 16.16 | 15.70              | 16.30 | 50                                                       | 200  | 10                                  | 40   | 10.4                                                                                      | 12.4 | 14.0 | 75                                                                        | 1.5                                                                                                                                          |
| 18                      | 17.82                                                               | 18.18 | 17.60              | 18.40 | 50                                                       | 225  | 10                                  | 45   | 12.4                                                                                      | 14.4 | 16.0 | 70                                                                        | 1.5                                                                                                                                          |
| 20                      | 19.80                                                               | 20.20 | 19.60              | 20.40 | 60                                                       | 225  | 15                                  | 55   | 14.4                                                                                      | 16.4 | 18.0 | 60                                                                        | 1.5                                                                                                                                          |
| 22                      | 21.78                                                               | 22.22 | 21.60              | 22.40 | 60                                                       | 250  | 20                                  | 55   | 16.4                                                                                      | 18.4 | 20.0 | 60                                                                        | 1.25                                                                                                                                         |
| 24                      | 23.76                                                               | 24.24 | 23.50              | 24.50 | 60                                                       | 250  | 25                                  | 70   | 18.4                                                                                      | 20.4 | 22.0 | 55                                                                        | 1.25                                                                                                                                         |

## Voltage regulator diodes

## BZX79 series

**Table 2** Per type BZX79-A/B27 to A/B75 $T_j = 25\text{ °C}$  unless otherwise specified.

| BZX79-<br>A or B<br>XXX | WORKING VOLTAGE<br>$V_Z$ (V)<br>at $I_{Z\text{test}} = 2\text{ mA}$ |       |                    |       | DIFFERENTIAL RESISTANCE<br>$r_{\text{dif}}$ ( $\Omega$ ) |      |                                     |      | TEMP. COEFF.<br>$S_Z$ (mV/K)<br>at $I_{Z\text{test}} = 2\text{ mA}$<br>(see Figs 5 and 6) |      |      | DIODE CAP.<br>$C_d$ (pF)<br>at $f = 1\text{ MHz}$ ;<br>$V_R = 0\text{ V}$ | NON-REPETITIVE PEAK<br>REVERSE CURRENT<br>$I_{ZSM}$ (A)<br>at $t_p = 100\text{ }\mu\text{s}$ ; $T_{\text{amb}} = 25\text{ °C}$ |
|-------------------------|---------------------------------------------------------------------|-------|--------------------|-------|----------------------------------------------------------|------|-------------------------------------|------|-------------------------------------------------------------------------------------------|------|------|---------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
|                         | Tol. $\pm 1\%$ (A)                                                  |       | Tol. $\pm 2\%$ (B) |       | at $I_{Z\text{test}} = 0.5\text{ mA}$                    |      | at $I_{Z\text{test}} = 2\text{ mA}$ |      | MIN.                                                                                      | TYP. | MAX. | MAX.                                                                      | MAX.                                                                                                                           |
|                         | MIN.                                                                | MAX.  | MIN.               | MAX.  | TYP.                                                     | MAX. | TYP.                                | MAX. |                                                                                           |      |      |                                                                           |                                                                                                                                |
| 27                      | 26.73                                                               | 27.27 | 26.50              | 27.50 | 65                                                       | 300  | 25                                  | 80   | 21.4                                                                                      | 23.4 | 25.3 | 50                                                                        | 1.0                                                                                                                            |
| 30                      | 29.70                                                               | 30.30 | 29.40              | 30.60 | 70                                                       | 300  | 30                                  | 80   | 24.4                                                                                      | 26.6 | 29.4 | 50                                                                        | 1.0                                                                                                                            |
| 33                      | 32.67                                                               | 33.33 | 32.30              | 33.70 | 75                                                       | 325  | 35                                  | 80   | 27.4                                                                                      | 29.7 | 33.4 | 45                                                                        | 0.9                                                                                                                            |
| 36                      | 35.64                                                               | 36.36 | 35.30              | 36.70 | 80                                                       | 350  | 35                                  | 90   | 30.4                                                                                      | 33.0 | 37.4 | 45                                                                        | 0.8                                                                                                                            |
| 39                      | 38.61                                                               | 39.39 | 38.20              | 39.80 | 80                                                       | 350  | 40                                  | 130  | 33.4                                                                                      | 36.4 | 41.2 | 45                                                                        | 0.7                                                                                                                            |
| 43                      | 42.57                                                               | 43.43 | 42.10              | 43.90 | 85                                                       | 375  | 45                                  | 150  | 37.6                                                                                      | 41.2 | 46.6 | 40                                                                        | 0.6                                                                                                                            |
| 47                      | 46.53                                                               | 47.47 | 46.10              | 47.90 | 85                                                       | 375  | 50                                  | 170  | 42.0                                                                                      | 46.1 | 51.8 | 40                                                                        | 0.5                                                                                                                            |
| 51                      | 50.49                                                               | 51.51 | 50.00              | 52.00 | 90                                                       | 400  | 60                                  | 180  | 46.6                                                                                      | 51.0 | 57.2 | 40                                                                        | 0.4                                                                                                                            |
| 56                      | 55.44                                                               | 56.56 | 54.90              | 57.10 | 100                                                      | 425  | 70                                  | 200  | 52.2                                                                                      | 57.0 | 63.8 | 40                                                                        | 0.3                                                                                                                            |
| 62                      | 61.38                                                               | 62.62 | 60.80              | 63.20 | 120                                                      | 450  | 80                                  | 215  | 58.8                                                                                      | 64.4 | 71.6 | 35                                                                        | 0.3                                                                                                                            |
| 68                      | 67.32                                                               | 68.68 | 66.60              | 69.40 | 150                                                      | 475  | 90                                  | 240  | 65.6                                                                                      | 71.7 | 79.8 | 35                                                                        | 0.25                                                                                                                           |
| 75                      | 74.25                                                               | 75.75 | 73.50              | 76.50 | 170                                                      | 500  | 95                                  | 255  | 73.4                                                                                      | 80.2 | 88.6 | 35                                                                        | 0.2                                                                                                                            |

## Voltage regulator diodes

## BZX79 series

**Table 3** Per type BZX79-C2V4 to C24 $T_j = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

| BZX79<br>- C<br>XXX | WORKING VOLTAGE<br>V <sub>Z</sub> (V)<br>at I <sub>Ztest</sub> = 5 mA |      | DIFFERENTIAL RESISTANCE<br>r <sub>dif</sub> (Ω) |      |                              |      | TEMP. COEFF.<br>S <sub>Z</sub> (mV/K)<br>at I <sub>Ztest</sub> = 5 mA<br>(see Figs 5 and 6) |      |      | DIODE CAP.<br>C <sub>d</sub> (pF)<br>at f = 1 MHz;<br>V <sub>R</sub> = 0 V | NON-REPETITIVE PEAK<br>REVERSE CURRENT<br>I <sub>ZSM</sub> (A)<br>at t <sub>p</sub> = 100 μs; T <sub>amb</sub> = 25 °C |
|---------------------|-----------------------------------------------------------------------|------|-------------------------------------------------|------|------------------------------|------|---------------------------------------------------------------------------------------------|------|------|----------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
|                     | Tol. approx. ±5% (C)                                                  |      | at I <sub>Ztest</sub> = 1 mA                    |      | at I <sub>Ztest</sub> = 5 mA |      |                                                                                             |      |      |                                                                            |                                                                                                                        |
|                     | MIN.                                                                  | MAX. | TYP.                                            | MAX. | TYP.                         | MAX. | MIN.                                                                                        | TYP. | MAX. | MAX.                                                                       | MAX.                                                                                                                   |
| 2V4                 | 2.2                                                                   | 2.6  | 275                                             | 600  | 70                           | 100  | −3.5                                                                                        | −1.6 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 2V7                 | 2.5                                                                   | 2.9  | 300                                             | 600  | 75                           | 100  | −3.5                                                                                        | −2.0 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 3V0                 | 2.8                                                                   | 3.2  | 325                                             | 600  | 80                           | 95   | −3.5                                                                                        | −2.1 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 3V3                 | 3.1                                                                   | 3.5  | 350                                             | 600  | 85                           | 95   | −3.5                                                                                        | −2.4 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 3V6                 | 3.4                                                                   | 3.8  | 375                                             | 600  | 85                           | 90   | −3.5                                                                                        | −2.4 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 3V9                 | 3.7                                                                   | 4.1  | 400                                             | 600  | 85                           | 90   | −3.5                                                                                        | −2.5 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 4V3                 | 4.0                                                                   | 4.6  | 410                                             | 600  | 80                           | 90   | −3.5                                                                                        | −2.5 | 0    | 450                                                                        | 6.0                                                                                                                    |
| 4V7                 | 4.4                                                                   | 5.0  | 425                                             | 500  | 50                           | 80   | −3.5                                                                                        | −1.4 | 0.2  | 300                                                                        | 6.0                                                                                                                    |
| 5V1                 | 4.8                                                                   | 5.4  | 400                                             | 480  | 40                           | 60   | −2.7                                                                                        | −0.8 | 1.2  | 300                                                                        | 6.0                                                                                                                    |
| 5V6                 | 5.2                                                                   | 6.0  | 80                                              | 400  | 15                           | 40   | −2.0                                                                                        | 1.2  | 2.5  | 300                                                                        | 6.0                                                                                                                    |
| 6V2                 | 5.8                                                                   | 6.6  | 40                                              | 150  | 6                            | 10   | 0.4                                                                                         | 2.3  | 3.7  | 200                                                                        | 6.0                                                                                                                    |
| 6V8                 | 6.4                                                                   | 7.2  | 30                                              | 80   | 6                            | 15   | 1.2                                                                                         | 3.0  | 4.5  | 200                                                                        | 6.0                                                                                                                    |
| 7V5                 | 7.0                                                                   | 7.9  | 30                                              | 80   | 6                            | 15   | 2.5                                                                                         | 4.0  | 5.3  | 150                                                                        | 4.0                                                                                                                    |
| 8V2                 | 7.7                                                                   | 8.7  | 40                                              | 80   | 6                            | 15   | 3.2                                                                                         | 4.6  | 6.2  | 150                                                                        | 4.0                                                                                                                    |
| 9V1                 | 8.5                                                                   | 9.6  | 40                                              | 100  | 6                            | 15   | 3.8                                                                                         | 5.5  | 7.0  | 150                                                                        | 3.0                                                                                                                    |
| 10                  | 9.4                                                                   | 10.6 | 50                                              | 150  | 8                            | 20   | 4.5                                                                                         | 6.4  | 8.0  | 90                                                                         | 3.0                                                                                                                    |
| 11                  | 10.4                                                                  | 11.6 | 50                                              | 150  | 10                           | 20   | 5.4                                                                                         | 7.4  | 9.0  | 85                                                                         | 2.5                                                                                                                    |
| 12                  | 11.4                                                                  | 12.7 | 50                                              | 150  | 10                           | 25   | 6.0                                                                                         | 8.4  | 10.0 | 85                                                                         | 2.5                                                                                                                    |
| 13                  | 12.4                                                                  | 14.1 | 50                                              | 170  | 10                           | 30   | 7.0                                                                                         | 9.4  | 11.0 | 80                                                                         | 2.5                                                                                                                    |
| 15                  | 13.8                                                                  | 15.6 | 50                                              | 200  | 10                           | 30   | 9.2                                                                                         | 11.4 | 13.0 | 75                                                                         | 2.0                                                                                                                    |
| 16                  | 15.3                                                                  | 17.1 | 50                                              | 200  | 10                           | 40   | 10.4                                                                                        | 12.4 | 14.0 | 75                                                                         | 1.5                                                                                                                    |
| 18                  | 16.8                                                                  | 19.1 | 50                                              | 225  | 10                           | 45   | 12.4                                                                                        | 14.4 | 16.0 | 70                                                                         | 1.5                                                                                                                    |
| 20                  | 18.8                                                                  | 21.2 | 60                                              | 225  | 15                           | 55   | 14.4                                                                                        | 16.4 | 18.0 | 60                                                                         | 1.5                                                                                                                    |
| 22                  | 20.8                                                                  | 23.3 | 60                                              | 250  | 20                           | 55   | 16.4                                                                                        | 18.4 | 20.0 | 60                                                                         | 1.25                                                                                                                   |
| 24                  | 22.8                                                                  | 25.6 | 60                                              | 250  | 25                           | 70   | 18.4                                                                                        | 20.4 | 22.0 | 55                                                                         | 1.25                                                                                                                   |

## Voltage regulator diodes

## BZX79 series

**Table 4** Per type BZX79-C27 to C75 $T_j = 25\text{ °C}$  unless otherwise specified.

| BZX79<br>- C<br>XXX | WORKING<br>VOLTAGE<br>V <sub>Z</sub> (V)<br>at I <sub>Ztest</sub> = 2 mA |      | DIFFERENTIAL RESISTANCE<br>r <sub>diff</sub> (Ω) |      |                              |      | TEMP. COEFF.<br>S <sub>Z</sub> (mV/K)<br>at I <sub>Ztest</sub> = 2 mA<br>(see Figs 5 and 6) |      |      | DIODE CAP.<br>C <sub>d</sub> (pF)<br>at f = 1 MHz;<br>V <sub>R</sub> = 0 V | NON-REPETITIVE PEAK<br>REVERSE CURRENT<br>I <sub>ZSM</sub> (A)<br>at t <sub>p</sub> = 100 μs; T <sub>amb</sub> = 25 °C |
|---------------------|--------------------------------------------------------------------------|------|--------------------------------------------------|------|------------------------------|------|---------------------------------------------------------------------------------------------|------|------|----------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|
|                     | Tol.approx. ±5% (C)                                                      |      | at I <sub>Ztest</sub> = 0.5 mA                   |      | at I <sub>Ztest</sub> = 2 mA |      |                                                                                             |      |      |                                                                            |                                                                                                                        |
|                     | MIN.                                                                     | MAX. | TYP.                                             | MAX. | TYP.                         | MAX. | MIN.                                                                                        | TYP. | MAX. | MAX.                                                                       | MAX.                                                                                                                   |
| 27                  | 25.1                                                                     | 28.9 | 65                                               | 300  | 25                           | 80   | 21.4                                                                                        | 23.4 | 25.3 | 50                                                                         | 1.0                                                                                                                    |
| 30                  | 28.0                                                                     | 32.0 | 70                                               | 300  | 30                           | 80   | 24.4                                                                                        | 26.6 | 29.4 | 50                                                                         | 1.0                                                                                                                    |
| 33                  | 31.0                                                                     | 35.0 | 75                                               | 325  | 35                           | 80   | 27.4                                                                                        | 29.7 | 33.4 | 45                                                                         | 0.9                                                                                                                    |
| 36                  | 34.0                                                                     | 38.0 | 80                                               | 350  | 35                           | 90   | 30.4                                                                                        | 33.0 | 37.4 | 45                                                                         | 0.8                                                                                                                    |
| 39                  | 37.0                                                                     | 41.0 | 80                                               | 350  | 40                           | 130  | 33.4                                                                                        | 36.4 | 41.2 | 45                                                                         | 0.7                                                                                                                    |
| 43                  | 40.0                                                                     | 46.0 | 85                                               | 375  | 45                           | 150  | 37.6                                                                                        | 41.2 | 46.6 | 40                                                                         | 0.6                                                                                                                    |
| 47                  | 44.0                                                                     | 50.0 | 85                                               | 375  | 50                           | 170  | 42.0                                                                                        | 46.1 | 51.8 | 40                                                                         | 0.5                                                                                                                    |
| 51                  | 48.0                                                                     | 54.0 | 90                                               | 400  | 60                           | 180  | 46.6                                                                                        | 51.0 | 57.2 | 40                                                                         | 0.4                                                                                                                    |
| 56                  | 52.0                                                                     | 60.0 | 100                                              | 425  | 70                           | 200  | 52.2                                                                                        | 57.0 | 63.8 | 40                                                                         | 0.3                                                                                                                    |
| 62                  | 58.0                                                                     | 66.0 | 120                                              | 450  | 80                           | 215  | 58.8                                                                                        | 64.4 | 71.6 | 35                                                                         | 0.3                                                                                                                    |
| 68                  | 64.0                                                                     | 72.0 | 150                                              | 475  | 90                           | 240  | 65.6                                                                                        | 71.7 | 79.8 | 35                                                                         | 0.25                                                                                                                   |
| 75                  | 70.0                                                                     | 79.0 | 170                                              | 500  | 95                           | 255  | 73.4                                                                                        | 80.2 | 88.6 | 35                                                                         | 0.2                                                                                                                    |

Voltage regulator diodes

BZX79 series


THERMAL CHARACTERISTICS

| SYMBOL         | PARAMETER                                     | CONDITIONS                             | VALUE | UNIT |
|----------------|-----------------------------------------------|----------------------------------------|-------|------|
| $R_{th\ j-tp}$ | thermal resistance from junction to tie-point | lead length 8 mm.                      | 300   | K/W  |
| $R_{th\ j-a}$  | thermal resistance from junction to ambient   | lead length max.; see Fig.2 and note 1 | 380   | K/W  |

Note

1. Device mounted on a printed circuit-board without metallization pad.


GRAPHICAL DATA






Voltage regulator diodes

BZX79 series




- (1)  $T_j = 25\text{ }^{\circ}\text{C}$  (prior to surge).
- (2)  $T_j = 150\text{ }^{\circ}\text{C}$  (prior to surge).

Fig.3 Maximum permissible non-repetitive peak reverse power dissipation versus duration.




$T_j = 25\text{ }^{\circ}\text{C}$ .

Fig.4 Forward current as a function of forward voltage; typical values.



BZX79-A/B/C2V4 to A/B/C4V3.  
 $T_j = 25\text{ to }150\text{ }^{\circ}\text{C}$ .

Fig.5 Temperature coefficient as a function of working current; typical values.



BZX79-A/B/C4V7 to A/B/C12.  
 $T_j = 25\text{ to }150\text{ }^{\circ}\text{C}$ .

Fig.6 Temperature coefficient as a function of working current; typical values.

Voltage regulator diodes

BZX79 series

PACKAGE OUTLINE

Hermetically sealed glass package; axial leaded; 2 leads

SOD27

**DIMENSIONS (mm are the original dimensions)**

| UNIT | b<br>max. | D<br>max. | G <sub>1</sub><br>max. | L<br>min. |
|------|-----------|-----------|------------------------|-----------|
| mm   | 0.56      | 1.85      | 4.25                   | 25.4      |

0 1 2 mm  
scale

**Note**  
1. The marking band indicates the cathode.

| OUTLINE<br>VERSION | REFERENCES |       |       |  | EUROPEAN<br>PROJECTION | ISSUE DATE |
|--------------------|------------|-------|-------|--|------------------------|------------|
|                    | IEC        | JEDEC | EIAJ  |  |                        |            |
| SOD27              | A24        | DO-35 | SC-40 |  |                        | 97-06-09   |

DEFINITIONS

|                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>Data sheet status</b>                                                                                                                                                                                                                                                                                                                                                                                                                                  |                                                                                       |
| Objective specification                                                                                                                                                                                                                                                                                                                                                                                                                                   | This data sheet contains target or goal specifications for product development.       |
| Preliminary specification                                                                                                                                                                                                                                                                                                                                                                                                                                 | This data sheet contains preliminary data; supplementary data may be published later. |
| Product specification                                                                                                                                                                                                                                                                                                                                                                                                                                     | This data sheet contains final product specifications.                                |
| <b>Limiting values</b>                                                                                                                                                                                                                                                                                                                                                                                                                                    |                                                                                       |
| Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability. |                                                                                       |
| <b>Application information</b>                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                       |
| Where application information is given, it is advisory and does not form part of the specification.                                                                                                                                                                                                                                                                                                                                                       |                                                                                       |

LIFE SUPPORT APPLICATIONS

These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips for any damages resulting from such improper use or sale.

---

Voltage regulator diodes

BZX79 series

---

NOTES

# Philips Semiconductors – a worldwide company

**Argentina:** see South America

**Australia:** 34 Waterloo Road, NORTH RYDE, NSW 2113,  
Tel. +61 2 9805 4455, Fax. +61 2 9805 4466

**Austria:** Computerstr. 6, A-1101 WIEN, P.O. Box 213,  
Tel. +43 1 60 101 1248, Fax. +43 1 60 101 1210

**Belarus:** Hotel Minsk Business Center, Bld. 3, r. 1211, Volodarski Str. 6,  
220050 MINSK, Tel. +375 172 20 0733, Fax. +375 172 20 0773

**Belgium:** see The Netherlands

**Brazil:** see South America

**Bulgaria:** Philips Bulgaria Ltd., Energoproject, 15th floor,  
51 James Bourchier Blvd., 1407 SOFIA,  
Tel. +359 2 68 9211, Fax. +359 2 68 9102

**Canada:** PHILIPS SEMICONDUCTORS/COMPONENTS,  
Tel. +1 800 234 7381, Fax. +1 800 943 0087

**China/Hong Kong:** 501 Hong Kong Industrial Technology Centre,  
72 Tat Chee Avenue, Kowloon Tong, HONG KONG,  
Tel. +852 2319 7888, Fax. +852 2319 7700

**Colombia:** see South America

**Czech Republic:** see Austria

**Denmark:** Sydhavnsgade 23, 1780 COPENHAGEN V,  
Tel. +45 33 29 3333, Fax. +45 33 29 3905

**Finland:** Sinikalliontie 3, FIN-02630 ESPOO,  
Tel. +358 9 615 800, Fax. +358 9 6158 0920

**France:** 51 Rue Carnot, BP317, 92156 SURESNES Cedex,  
Tel. +33 1 4099 6161, Fax. +33 1 4099 6427

**Germany:** Hammerbrookstraße 69, D-20097 HAMBURG,  
Tel. +49 40 2353 60, Fax. +49 40 2353 6300

**Hungary:** see Austria

**India:** Philips INDIA Ltd, Band Box Building, 2nd floor,  
254-D, Dr. Annie Besant Road, Worli, MUMBAI 400 025,  
Tel. +91 22 493 8541, Fax. +91 22 493 0966

**Indonesia:** PT Philips Development Corporation, Semiconductors Division,  
Gedung Philips, Jl. Buncit Raya Kav.99-100, JAKARTA 12510,  
Tel. +62 21 794 0040 ext. 2501, Fax. +62 21 794 0080

**Ireland:** Newstead, Clonskeagh, DUBLIN 14,  
Tel. +353 1 7640 000, Fax. +353 1 7640 200

**Israel:** RAPAC Electronics, 7 Kehilat Saloniki St, PO Box 18053,  
TEL AVIV 61180, Tel. +972 3 645 0444, Fax. +972 3 649 1007

**Italy:** PHILIPS SEMICONDUCTORS, Piazza IV Novembre 3,  
20124 MILANO, Tel. +39 02 67 52 2531, Fax. +39 02 67 52 2557

**Japan:** Philips Bldg 13-37, Kohnan 2-chome, Minato-ku,  
TOKYO 108-8507, Tel. +81 3 3740 5130, Fax. +81 3 3740 5057

**Korea:** Philips House, 260-199 Itaewon-dong, Yongsan-ku, SEOUL,  
Tel. +82 2 709 1412, Fax. +82 2 709 1415

**Malaysia:** No. 76 Jalan Universiti, 46200 PETALING JAYA, SELANGOR,  
Tel. +60 3 750 5214, Fax. +60 3 757 4880

**Mexico:** 5900 Gateway East, Suite 200, EL PASO, TEXAS 79905,  
Tel. +9-5 800 234 7381, Fax +9-5 800 943 0087

**Middle East:** see Italy

**Netherlands:** Postbus 90050, 5600 PB EINDHOVEN, Bldg. VB,  
Tel. +31 40 27 82785, Fax. +31 40 27 88399

**New Zealand:** 2 Wagener Place, C.P.O. Box 1041, AUCKLAND,  
Tel. +64 9 849 4160, Fax. +64 9 849 7811

**Norway:** Box 1, Manglerud 0612, OSLO,  
Tel. +47 22 74 8000, Fax. +47 22 74 8341

**Pakistan:** see Singapore

**Philippines:** Philips Semiconductors Philippines Inc.,  
106 Valero St. Salcedo Village, P.O. Box 2108 MCC, MAKATI,  
Metro MANILA, Tel. +63 2 816 6380, Fax. +63 2 817 3474

**Poland:** Ul. Lukiska 10, PL 04-123 WARSZAWA,  
Tel. +48 22 612 2831, Fax. +48 22 612 2327

**Portugal:** see Spain

**Romania:** see Italy

**Russia:** Philips Russia, Ul. Usatcheva 35A, 119048 MOSCOW,  
Tel. +7 095 755 6918, Fax. +7 095 755 6919

**Singapore:** Lorong 1, Toa Payoh, SINGAPORE 319762,  
Tel. +65 350 2538, Fax. +65 251 6500

**Slovakia:** see Austria

**Slovenia:** see Italy

**South Africa:** S.A. PHILIPS Pty Ltd., 195-215 Main Road Martindale,  
2092 JOHANNESBURG, P.O. Box 58088 Newville 2114,  
Tel. +27 11 471 5401, Fax. +27 11 471 5398

**South America:** Al. Vicente Pinzon, 173, 6th floor,  
04547-130 SÃO PAULO, SP, Brazil,  
Tel. +55 11 821 2333, Fax. +55 11 821 2382

**Spain:** Balmes 22, 08007 BARCELONA,  
Tel. +34 93 301 6312, Fax. +34 93 301 4107

**Sweden:** Kottbygatan 7, Akalla, S-16485 STOCKHOLM,  
Tel. +46 8 5985 2000, Fax. +46 8 5985 2745

**Switzerland:** Allmendstrasse 140, CH-8027 ZÜRICH,  
Tel. +41 1 488 2741 Fax. +41 1 488 3263

**Taiwan:** Philips Semiconductors, 6F, No. 96, Chien Kuo N. Rd., Sec. 1,  
TAIPEI, Taiwan Tel. +886 2 2134 2886, Fax. +886 2 2134 2874

**Thailand:** PHILIPS ELECTRONICS (THAILAND) Ltd.,  
209/2 Sanpavuth-Bangna Road Prakanong, BANGKOK 10260,  
Tel. +66 2 745 4090, Fax. +66 2 398 0793

**Turkey:** Yukari Dudullu, Org. San. Blg., 2.Cad. Nr. 28 81260 Umraniye,  
ISTANBUL, Tel. +90 216 522 1500, Fax. +90 216 522 1813

**Ukraine:** PHILIPS UKRAINE, 4 Patrice Lumumba str., Building B, Floor 7,  
252042 KIEV, Tel. +380 44 264 2776, Fax. +380 44 268 0461

**United Kingdom:** Philips Semiconductors Ltd., 276 Bath Road, Hayes,  
MIDDLESEX UB3 5BX, Tel. +44 181 730 5000, Fax. +44 181 754 8421

**United States:** 811 East Arques Avenue, SUNNYVALE, CA 94088-3409,  
Tel. +1 800 234 7381, Fax. +1 800 943 0087

**Uruguay:** see South America

**Vietnam:** see Singapore

**Yugoslavia:** PHILIPS, Trg N. Pasica 5/v, 11000 BEOGRAD,  
Tel. +381 11 62 5344, Fax. +381 11 63 5777

**For all other countries apply to:** Philips Semiconductors,  
International Marketing & Sales Communications, Building BE-p, P.O. Box 218,  
5600 MD EINDHOVEN, The Netherlands, Fax. +31 40 27 24825

**Internet:** <http://www.semiconductors.philips.com>

© Philips Electronics N.V. 1999

SCA 65

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

115002/02/pp12

Date of release: 1999 May 25

Document order number: 9397 750 05894

*Let's make things better.*

**Philips  
Semiconductors**



**PHILIPS**