



LOADING PATTERN MATING SIDE


f	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	0	0	0	0	0	0
e	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	0	F	0	F	F	F
d	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	0	F	0	0	0	0
c	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	0	F	0	F	F	F
b	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	F	0	0	0	0	0	0
a	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	F	F	0	F	F	F
z	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	0	0	0	0	0	0
P	0																						
S	1																						

LOADED CONNECTOR ASSEMBLY
(FOR EXAMPLE)

CONTACT OVERVIEW



LAY-OUT P.C.B.-HOLE



HM2P08PNJ395

LEAD FREE INDICATOR : LF = LEAD FREE
(DIGIT 15 & 16)PLATING CODE (DIGIT 13 AND 14)
(REF DRW NO. BS,C , 201844 , 003)

NOTES

- THIS PRODUCT IS CSA APPROVED.
- THIS PRODUCT IS UL RECOGNIZED.
- MEASURED AT THE BOTTOM.
- MATERIAL CONTACT: PHOSPHORBRONZE
HOUSING: CREAM WHITE GLASS FILLED POLYESTER UL-94V0
- CONNECTOR PRINTED WITH P/N AND DATE CODE.
- FOR ACTUAL CONTACT LOADINGS, SEE LOADING PATTERN MATING SIDE.
- SHAPE OF CONNECTOR HOUSING CAN ALTER DEPENDING ON PRODUCTION LOCATION
- THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS, A , 201572 , 001

CATALOG NO: HM2P08PNJ395----

mat'l. code SEE NOTE 4				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family MILLIPACS			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title			
A	106-0184	MINI	2006-10-06	angles	linear		MPACS 5+2R STR HDR PF CONN TYPE B			
				0°±1°						
				dr	MINI K VANDANATH	2006-10-06	dwg no		sheet 1 of 1	size
				enr	BIJU K PAUL	2006-10-06	BS, C ,203028, 731		A3	
				chr	BIJU K PAUL	2006-10-06				
				appd	BIJU K PAUL	2006-10-06				
sheet index	revision	A					type		Product	Customer
	sheet	1							Drawing	