










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A3		REV PER ECO-20-013940	15OCT2020	RGV	CJS
A4		REV PER ECO-21-005624	19MAY2021	RGV	CS
A5		REV PER ECN-23-211153	10MAY2023	JMS	CJS
A6		REV PER ECN-24-270812	26JUN2024	SMR	CJS

- 1 HOUSING: PCT, COLOR - SEE TABLE
CONTACTS: BRASS
SOLDER CLIP: BRASS
- 2 SOLDER CLIP: 3.8µm MIN TIN OVER 1.27µm MIN NICKEL
- 3 CONTACT:0.8µm MIN TIN IN MATING AREA AND 2.5µm MIN TIN IS SOLDER TAIL ALL OVER 1.00µm NICKEL
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY THE CUSTOMER
- 5 ALLOW FOR OVER PRINTING ON PC BOARD
- 6 REMOVED
- 7 REMOVED
- 8 OPTIONAL FEATURE ON PART NUMBERS NOTED BELOW
- 9 PENDING DISCONTINUANCE



28.20	28.20	KEYING CODE "BF"	BLUE	1-1456549-3
26.20	26.20	KEYING CODE "BE"	GRAY	1-1456549-2
30.20	30.20	KEYING CODE "AE"	BLACK	1-1456549-1
28.20	28.20	KEYING CODE "BF"	BLUE	1456549-3
26.20	26.20	KEYING CODE "BE"	GRAY	1456549-2
30.20	30.20	KEYING CODE "AE"	BLACK	1456549-1
B	A	KEYING CODE	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL 16FEB2006	 TE Connectivity	
DIMENSIONS:		CHK D. FRY 2MAY2006		
mm		APVD J. MYER 2MAY2006		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
	0 PLC	±	NAME HEADER ASSEMBLY, 26 WAY, RIGHT ANGLE, WITH SOLDER CLIPS, RIGHT CABLE EXIT, SURFACE MOUNT, LAC	
	1 PLC	±		
	2 PLC	±		
	3 PLC	±		
	4 PLC	±		
ANGLES		±	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
FINISH				
MATERIAL		WEIGHT		
SEE TABLE		CUSTOMER DRAWING		
		SCALE 4:1 SHEET 1 OF 2 REV A6		



RECOMMENDED PC BOARD LAYOUT
CONNECTOR SIDE OF BOARD
SCALE 4:1