

1


2

3

4

FCI PART NO.	POWER TYPE	LENGTH "X"
10083511-Z0050YYLF	24V	500+25/-0
10083511-Z0100YYLF	24V	1000±15
10083511-Z0300YYLF	24V	3000±25
10083511-Z0500YYLF	24V	5000±25

LENGTH "X"



PIN ASSIGNMENT

P1	SIGNAL NAME	WIRE COLOR	WIRE AWG	P2
6	VBUS (+5V)	RED	20	1
5	DATA -	WHITE	28	2
4	DATA +	GREEN	28	3
3	GND	BLACK	20	4
1	24V RETURN	BLUE	20	5
2	+24V	BROWN	20	6
7	+24V	ORANGE	20	7
8	24V RETURN	YELLOW	20	8
SHELL	FRAME GND	BRAID		SHELL

Mark with
10075076001
REV. prai_revision
in area indicated
by X....

rev	ecn no	dr	date
A	N08-0120	ST	6/18/2008

TOLERANCES UNLESS OTHERWISE SPECIFIED

LINEAR				
ANGULAR	0°	±2°		

Material			Spec ref		spec_ref			
Mat code			surface		tolerance		projection	
Heattreat			ISO 1302		ISO 406			
Plating/Finish					ISO 1101			
Dr Sunny Tsai			11/7/2007				size	
Eng Sunny Tsai			11/7/2007		Product family		A3	
Chr Jackson Wang			11/7/2007		Model Name		ECN	
Appr Jackson Wang			11/7/2007		Model Revision		REL Level	
			title			dwg no		Rev.
			CABLE: USB+POWER(24V) TO 1X8 LATCH-N-LOK (ROHS)			10083511		A
Pro/E file			catalog no			CUSTOMER DWG		sheet 1 of 2

REV F - 2006-04-17

2

3PDM: Rev:A

STATUSReleased

Printed: Jul 10, 2009

FCI CONFIDENTIAL

FCI

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

1

2

3

4

FCI PART NO. SEE SHEET 1

NOTES:

1. USB+POWER MATES WITH FCI PART NUMBER: 55917-6XXLF.
1x8 LATCH-N-LOK MATES WITH FCI PART NUMBER: 69913-XXXLF.

2. UNLESS OTHERWISE SPECIFIED ASSEMBLED LENGTH TOLERANCE:
=< 1 METER= ±15.0mm
> 1 METER TO 10 METER= ±2% OF L1 OR L2
> 10 METER= +0%/-4% OF L1 OR L2

3. PART NUMBER SCHEME FOR CABLE ASSEMBLY:

10083511 - Z X X X X Y Y LF

LF: LEAD FREE
NOT APPLICABLE TO THIS ASSEMBLY
NOT APPLICABLE TO THIS ASSEMBLY
LENGTH (METERS & CENTIMETERS)
0100: 1 METERS 00 CENTIMETERS
WIRE GAGE
Z: MULTIPLE WIRE GAGE

4. UNLESS OTHERWISE SPECIFIED LABEL POSITION SHALL BE APPROXIMATELY
60mm FROM REAR OF CONNECTOR.

5. UNLESS OTHERWISE SPECIFIED STANDARD LABEL SHALL BE BRADY LABEL
P/N THT-10-427-30.

LABEL DETAILS:

FCI	---	MANUFACTURER CODE OR NAME
10083511-ZXXXXYYLF	---	FCI P/N
REV.A	---	REVISION
WWYY	---	DATE CODE WWYY FORMAT
MADE IN CHINA	---	COUNTRY ORIGIN

6. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY
AS DEFINED IN WIRING LIST.

7. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE
100% HI-POT TESTED: DC 300V/10ms

8. OTHER ELECTRICAL SPECIFICATIONS:

DIELECTRIC RESISTANCE: 50M Ohms MIN.

CONNECTION RESISTANCE: 0.8 Ohms MAX. (-Z0050YYLF, 0.5MR LENGTH)
1.2 Ohms MAX. (-Z0100YYLF, 1.0MR LENGTH)
1.5 Ohms MAX. (-Z0300YYLF, 3.0MR LENGTH)
1.8 Ohms MAX. (-Z0500YYLF, 5.0MR LENGTH)

9. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.

10. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.

11. CONNECTOR ASSEMBLIES SHOWN ARE FOR REFERENCE ONLY AND MAY
NOT SHOWN ALL PART DETAIL, REFERENCE CONNECTOR ASSEMBLY DRAWINGS
FOR COMPLETE DETAILS.

12. PACKAGE: EACH CABLE ASSEMBLY IN CLEAR ZIP-LOCK BPLY BAG,
THEN BULK PACKED IN A BOX.

13. MATERIAL:

4	1	EA	ADHESIVE LABEL.
3	AR	MM	USB+POWER CABLE: 28AWG*1P+20AWG*6C+SHIELD.
2	1	EA	USB+POWER PLUG KIT (24V) TYPE A, KEY POSITION 2, FCI P/N: 74233-202LF.
1	1	EA	1X8 LATCH-N-LOK 360° SHIELDED PLUG CONNECTOR KIT, PEBBLE GRAY, FCI P/N: 74903-709LF.
ITEM	Q'TY	UNIT	DESCRIPTION

Mark with
10075076001
REV. proj_revision
in area indicated
by X....

rev	ecn no	dr	date
-	See sheet 1	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

TOLERANCES UNLESS OTHERWISE SPECIFIED			
LINEAR			
ANGULAR	0°	±2°	

Material				Spec ref		spec_ref			
Mat code				surface		tolerance		projection	
Heattreat				ISO 1302		ISO 406			
Plating/Finish						ISO 1101			
Dr		Sunny Tsai		11/7/2007				size	
Eng		Sunny Tsai		11/7/2007		Product family		CABLE ASS'Y	
Chr		Jackson Wang		11/7/2007		Model Name		ECN	
Appr		Jackson Wang		11/7/2007		Model Revision		REL Level	
		title				dwg no		10083511	
		CABLE :USB+POWER(24V) TO 1X8 LATCH-N-LOK (ROHS)							
Pro/E file		catalog no				CUSTOMER DWG		sheet 2 of 2	

REV F - 2006-04-17

2

3PDM: Rev:A

STATUSReleased

Printed: Jul 10, 2009