

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	08JAN2009	RG	PD
			B	REV PER ECO-09-027020	08JAN2010	RG	MS
			B I	REV PER ECO-10-003674	25FEB2010	RG	MS

1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TYCO ELECTRONICS APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.

2. MATERIAL:
HOUSING: GLASS FILLED POLYESTER, COLOR-BLACK
UL94V-0 FLAMMABILITY RATED
LATCHES: THERMOPLASTIC, GLASS REINFORCED
COLOR: BLACK, UL94V-0 FLAMMABILITY RATED
CONTACTS: COPPER ALLOY

3. FINISH:
CONTACTS:
GOLD PLATE 0.76µm MIN THK. OVER
NICKEL 1.27µm MIN THK.
SOLDER TAILS - TIN PLATE 3.05µm MIN THK. OVER
NICKEL 1.27µm MIN THK.

4. ITEMS PROVIDED TO THIS SPECIFICATION TO BE PERMANENTLY IDENTIFIED WITH PART NUMBER AND DATE CODE.

5. MAXIMUM BURR OF 0.013 ON CARD TAB AREA.

6. SET TRACE BACK FROM PC BOARD EDGE. NO SOLDERMASK ALLOWED BETWEEN PC BOARD EDGE AND TRACE.

7. CONNECTOR ACCEPTS 2.36±0.13 THICK PC BOARD.

8. KEEP OUT AREA FOR COMPONENTS ONLY.

9. FEATURE REQUIRED FOR USE WITH LATCH.


10. CAUTION:
LATCHES ARE INTENDED FOR RETENTION OF PC BOARD TO CONNECTOR. DO NOT ATTEMPT TO FULLY EJECT PC BOARD FROM CONNECTOR WHILE DISENGAGING LATCHES, DAMAGE TO LATCHES AND OR CONNECTOR MAY OCCUR.

11. RECOMMENDED GOLD FINGER LENGTH FOR RELIABLE CONTACT.

12. FOR DESIGN OBJECTIVES SEE 108-2301.

13. RECOMMENDED PRINTED CIRCUIT HOLE:
FINISHED HOLE: Ø1.02 ±.08
DRILLED HOLE: Ø1.15 ±.013
COPPER PLATE: .025 MIN. (PER SURFACE)
TIN PLATE: .008 MIN (PER SURFACE)




14. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER






AS SHOWN	1651864-1
DESCRIPTION	PART NO.

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE DRAWING. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		DWN R. GRZYBOWSKI 08JAN2009	Tyco Electronics Harrisburg, PA 17105-3608	
CHEK P. DAMATO 08JAN2009	APVD M. PERCHERIE 08JAN2009	NAME	SOCKET CONNECTOR ASSEMBLY W/LATCHES MC-P9S10	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE	CAGE CODE
mm	0 PLC ±.5 1 PLC ±.5 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±.5 FINISH	APPLICATION SPEC	A100779	C=1651864
MATERIAL	-	WEIGHT	-	RESTRICTED TO
-	-	CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 4


LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET I	-	-	-



TYP: IS SUBJECT TO CHANGE WITHOUT NOTICE FOR TYCO ELECTRONICS CORPORATION TYP: IS SUBJECT TO CHANGE WITHOUT NOTICE FOR TYCO ELECTRONICS CORPORATION TYP: IS SUBJECT TO CHANGE WITHOUT NOTICE FOR TYCO ELECTRONICS CORPORATION		DWN R. GRZYBOWSKI 08JAN2009	Tyco Electronics Harrisburg, PA 17105-3608	
CHK P. DAMATO 08JAN2009		APVD M. PERCHERIE 08JAN2009	NAME SOCKET CONNECTOR ASSEMBLY W/LATCHES MC-P9S10	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.5 1 PLC ±.5 3 PLC ±.25 5 PLC ±.5 4 PLC ±.5 ANGLES ±.5 FINISH -	PRODUCT SPEC APPLICATION SPEC WEIGHT -	
MATERIAL -		-	SIZE A100779C=1651864	
CUSTOMER DRAWING		SCALE 4:1	SHEET 2	OF 4
		REV B1		



LOC		DIST		REVISONS				
GP	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
				- - SEE SHEET 1	-	-	-	



RECOMMENDED P.C. BOARD GUIDELINE
AS VIEWED FROM THE CONNECTOR SIDE

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION IF IT IS NOT USED FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE DESTROYED IF IT IS NOT USED FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE DESTROYED IF IT IS NOT USED FOR THE PURPOSES SPECIFIED IN THE ORDER.		DWN R. GRZYBOWSKI 08JAN2009	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK P. DAMATO 08JAN2009	NAME	
mm		APVD M. PERCHERIE 08JAN2009	SOCKET CONNECTOR ASSEMBLY W/LATCHES MC-P9S10	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE	
9 PLC ±.5		APPLICATION SPEC	CAGE CODE	
2 PLC ±.5		WEIGHT	DRAWING NO	
3 PLC ±.25		CUSTOMER DRAWING	RESTRICTED TO	
5 PLC ±.25			A100779C=1651864	
4 PLC ±.5			SCALE	
ANGLES			4:1	
FINISH			SHEET	
			4 OF 4	
			REV	
			B1	