

HIGH SPEED GROUND PLANE HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?QTE

Insulator Material:

Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating: Au or Sn over 50µ" (1,27 µm) Ni

Current Rating:

Contact:

2 A per pin

(1 pin powered per row)

Ground Plane:

11.6 A per ground plane

(1 ground plane powered)

Operating Temp Range:

-55°C to +125°C

Voltage Rating:

225 VAC mated with QSE

& 5 mm Stack Height

Max Cycles: 100

RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (020-060)

Board Stacking:

For applications requiring more than two connectors per board contact ipg@samtec.com

Board Mates:

QSE

Cable Mates:


EQCD, EQDP, EQRF

(See Also Available note)



Integral metal plane
for power or ground

Standard stack heights
from 5 mm to 25 mm



QTE-040-01-L-D-A

**Protocols
Supported**

100 GbE
XAUI
PCI Express®
SATA
MGT (Rocket I/O)
InfiniBand™

Download app notes at:
www.samtec.com/appnote
Contact Sig @ samtec.com
for questions on protocols

QTE/QSE 5 mm Stack Height	Type	Rated @ 3dB Insertion Loss	
		with PCB effects*	w/o PCB effects**
Single-Ended Signaling	-D	9 GHz / 18 Gbps	9 GHz / 18 Gbps
Differential Pair Signaling	-D	8 GHz / 16 Gbps	14 GHz / 28 Gbps
Differential Pair Signaling	-DP	8.5 GHz / 17 Gbps	13.5 GHz / 27 Gbps

*Performance data includes effects of a non-optimized PCB.

**Test board losses de-embedded from performance data.

Performance data for other stack heights and complete test data available at www.samtec.com?QTE or contact sig@samtec.com

Final Inch
CERTIFIED

28+
Gbps

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594 FILE NO. 090871_0_000


ALSO AVAILABLE (MOQ Required)

- 14mm, 15 mm, 22 mm and 30 mm stack height (Caution: Some automatic placement/inspection machines may have component height restrictions. Please consult machinery specifications.)
 - 30µ" (0,76 µm) Gold (Specify -H plating for Data Rate cable mating applications.)
 - Edge Mount
 - 56 (-DP), 80, 100 positions per row
 - Guide Posts, Screw Down & Friction Lock
 - Retention Option
- Contact Samtec.

QTE	PINS PER ROW NO. OF PAIRS	LEAD STYLE	PLATING OPTION	TYPE	A	OTHER OPTION																					
	-020, -040, -060 (40 total pins per bank = -D) -014, -028, -042 (14 pairs per bank = -D-DP)	Specify LEAD STYLE from chart	-F = Gold Flash on Signal Pins and Ground Plane, Matte Tin on tails -L = 10µ" (0,25 µm) Gold on Signal Pins and Ground Plane, Matte Tin on tails -C* = Electro-Polished Selective 50µ" (1,27 µm) min Au over 150µ" (3,81 µm) Ni on Signal Pins in contact area, 10µ" (0,25 µm) min Au over 50µ" (1,27 µm) Ni on Ground Plane in contact area, Matte Tin over 50µ" (1,27 µm) min Ni on all solder tails	-D = Single-Ended -D-DP = Differential Pair (-01 only)	-K = (7,00 mm) .275" DIA Polyimide Film Pick & Place Pad -TR = Tape & Reel Packaging (N/A -05 & -07 lead style) -L = Latching Option (N/A on -042 & -060 positions)	<table border="1"> <thead> <tr> <th>QTE LEAD STYLE</th> <th>A</th> <th>HEIGHT WITH QSE*</th> </tr> </thead> <tbody> <tr> <td>-01</td> <td>(4,27) .168</td> <td>(5,00) .197</td> </tr> <tr> <td>-02</td> <td>(7,26) .286</td> <td>(8,00) .315</td> </tr> <tr> <td>-03</td> <td>(10,27) .404</td> <td>(11,00) .433</td> </tr> <tr> <td>-04</td> <td>(15,25) .600</td> <td>(16,00) .630</td> </tr> <tr> <td>-05</td> <td>(18,26) .718</td> <td>(19,00) .748</td> </tr> <tr> <td>-07</td> <td>(24,24) .954</td> <td>(25,00) .984</td> </tr> </tbody> </table> *Processing conditions will affect mated height.	QTE LEAD STYLE	A	HEIGHT WITH QSE*	-01	(4,27) .168	(5,00) .197	-02	(7,26) .286	(8,00) .315	-03	(10,27) .404	(11,00) .433	-04	(15,25) .600	(16,00) .630	-05	(18,26) .718	(19,00) .748	-07	(24,24) .954	(25,00) .984
QTE LEAD STYLE	A	HEIGHT WITH QSE*																									
-01	(4,27) .168	(5,00) .197																									
-02	(7,26) .286	(8,00) .315																									
-03	(10,27) .404	(11,00) .433																									
-04	(15,25) .600	(16,00) .630																									
-05	(18,26) .718	(19,00) .748																									
-07	(24,24) .954	(25,00) .984																									

OTHER SOLUTIONS

- Board Spacing Standoffs. See SO Series



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685