




THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO CONNECT POSITRONIC, INC. AND ITS SUBSIDIARIES. THE DATA ON THIS DRAWING TO BE RELIABLE. SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND ASSUMES ALL RESPONSIBILITY FOR ANY AND ALL RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

SK10879

DATE	REV	REVISION/RECORD	APP	DR	CK
7-02-09	NC	ECO 31265	COLL	BS	TK
12-9	A	ECO 33391	COLL	BE	COLL



NOTES:

1. MATERIALS AND FINISHES:

INSULATOR: NYLON RESIN, UL 94V-0, COLOR: BLACK.

CONTACTS: PRECISION MACHINED PHOSPHOR BRONZE, GOLD FLASH OVER NICKEL PLATE.

SHELLS: STEEL WITH TIN PLATE.

CLINCH NUTS: STEEL WITH TIN PLATE.

2. DETAILED PRODUCT, ELECTRICAL, AND MECHANICAL INFORMATION IS AVAILABLE IN

THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION. VISIT

CONNECTPOSITRONIC.COM/PRODUCTS/45/STANDARDENSITYD-SUBMINIATURE

OR CONNECTPOSITRONIC.COM.

3. WORKING TEMPERATURE: -55°C TO +125°C

4. DIMENSIONS ARE IN INCHES [MILLIMETERS]



POSITRONIC INDUSTRIES INC.
www.connectpositronic.com

FSC# 28198



DECIMAL TOL.
± 0.015 [0.38]

ANGULAR TOL.
± 5°

MD SERIES

SCALE
N.T.S.

DRAWN BY
B SHELLBY

APPROVED BY
S COLE

TITLE

MD15F2S500X

DATE

7-02-09

DRAWING NUMBER

SK10879

REV.

A