


ETMM-108-02-F-D-TH-LC



ETMM-112-02-F-D-RA

ETMM-125-02-L-D-SM-K

ETMM SERIES

(2,00 mm) .0787"

SHROUDED STRAIN RELIEF IDC HEADER

SPECIFICATIONS

For complete specifications see www.samtec.com?ETMM

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50 μ " (1,27 μ m) Ni

Operating Temp Range:

-55°C to +125°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:


(0,13 mm) .005" max

RoHS Compliant:

Yes

Mates with:
TCSD, TCMD

Shrouded pins
for protection



Surface Mount,
Through-hole and
Right Angle

Optional
Locking clips

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



TYPE STRIP

1

NO. OF POSITIONS

02

PLATING OPTION

D

TAIL OPTION

OTHER OPTION

ETMM
= Mates with
TCSD and
TCMD with
Strain Relief

05, 08, 10, 12, 13,
15, 17, 20, 22, 25
(Standard sizes)

-F
= Gold Flash on post,
Matte Tin on tail

-L
= 10 μ " (0,25 μ m)
Gold on post,
Matte Tin on tail

-TH
= Through-hole

-RA
= Right Angle

-SM
= Surface Mount

-“XX”
= Polarized Position

-LC
= Locking Clip
(Not available
for -RA)
(Manual
placement
required)

-TR
= Tape &
Reel Packaging
(-SM only)






-K
= (7,50 mm)
.295" DIA
Polyimide Film
Pick & Place Pad
(-SM only)

OTHER SOLUTIONS

- TCSD mates without Strain Relief. See STMM Series
- Shrouded header for mating with Connector Strips. See LTMM Series

ALSO AVAILABLE (MOQ Required)

- Other sizes
Contact Samtec.



Note: Some lengths, styles and options are non-standard, non-returnable.