


SWITCHING APPLICATION.
INTERFACE CIRCUIT AND DRIVER CIRCUIT APPLICATION.

FEATURES


- With Built-in Bias Resistors
- Simplify Circuit Design
- Reduce a Quantity of Parts and Manufacturing Process
- High Packing Density.

EQUIVALENT CIRCUIT




BIAS RESISTOR VALUES

TYPE NO.	R1(k Ω)	R2(k Ω)
KRA557U	10	47
KRA558U	22	47
KRA559U	47	22



EQUIVALENT CIRCUIT (TOP VIEW)




MAXIMUM RATING (Ta=25°C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Output Voltage	KRA557U ~ 559U	V _O	-50	V
Input Voltage	KRA557U	V _I	-30, 6	V
	KRA558U		-40, 7	
	KRA559U		-40, 15	
Output Current	KRA557U ~ 559U	I _O	-100	mA
Power Dissipation		P _D *	200	mW
Junction Temperature		T _j	150	°C
Storage Temperature Range		T _{stg}	-55 ~ 150	°C

Marking

MARK SPEC

TYPE	KRA557U	KRA558U	KRA559U
MARK	PH	PI	PJ









KRA557U~KRA559U

ELECTRICAL CHARACTERISTICS (Ta=25℃)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT		
Output Cut-off Current		KRA557U ~ 559U	I _{O(OFF)}	V _O =-50V, V _I =0	-	-	-500	nA	
DC Current Gain	KRA557U	G _I	V _O =-5V, I _O =-10mA	80	150	-			
	KRA558U			80	150	-			
	KRA559U			70	140	-			
Output Voltage		KRA557U ~ 559U	V _{O(ON)}	I _O =-10mA, I _I =-0.5mA	-	-0.1	-0.3	V	
Input Voltage (ON)	KRA557U	V _{I(ON)}	V _O =-0.2V, I _O =-5mA	-	-1.2	-1.8	V		
	KRA558U			-	-1.8	-2.6			
	KRA559U			-	-3.0	-5.8			
Input Votlage (OFF)	KRA557U	V _{I(OFF)}	V _O =-5V, I _O =-0.1mA	-0.5	-0.75	-	V		
	KRA558U			-0.6	-0.88	-			
	KRA559U			-1.5	-1.82	-			
Transition Frequency		KRA557U ~ 559U	f _T *	V _O =-10V, I _O =-5mA	-	200	-	MHz	
Input Current		KRA557U	I _I	V _I =-5V	-	-	-0.88	mA	
		KRA558U			-	-	-0.36		
		KRA559U			-	-	-0.16		
Switching Time	Rise Time	KRA557U	t _r	V _O =-5V, V _{IN} =-5V R _L =1k Ω	-	0.07	-	μS	
		KRA558U			-	0.20	-		
		KRA559U			-	0.38	-		
	Storage Time	KRA557U			t _{stg}	-	1.1		-
		KRA558U				-	1.3		-
		KRA559U				-	0.7		-
	Fall Time	KRA557U			t _f	-	0.35		-
		KRA558U				-	0.4		-
		KRA559U				-	0.48		-

Note : * Characteristic of Transistor Only.

KRA557U~KRA559U



KRA557U~KRA559U

