74CBTLV16211

24-bit bus switch

Rev. 6 — 15 December 2011   **Product data sheet**

1. General description

The 74CBTLV16211 provides a dual 12-bit high-speed bus switch with separate output enable inputs (1$\overline{OE}$, 2$\overline{OE}$). The low on-state resistance of the switch allows connections to be made with minimal propagation delay. The switch is disabled (high-impedance OFF-state) when the output enable (n$\overline{OE}$) input is HIGH.

To ensure the high-impedance OFF-state during power-up or power-down, 1$\overline{OE}$ and 2$\overline{OE}$ should be tied to the V_{CC} through a pull-up resistor. The minimum value of the resistor is determined by the current-sinking capability of the driver.

Schmitt trigger action at control input makes the circuit tolerant to slower input rise and fall times across the entire V_{CC} range from 2.3 V to 3.6 V.

This device is fully specified for partial power-down applications using I_{OFF}.
The I_{OFF} circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

2. Features and benefits

- Supply voltage range from 2.3 V to 3.6 V
- High noise immunity
- Complies with JEDEC standard:
  - JESD8-5 (2.3 V to 2.7 V)
  - JESD8-B/JESD36 (2.7 V to 3.6 V)
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V
  - CDM AEC-Q100-011 revision B exceeds 1000 V
- 5 Ω switch connection between two ports
- Rail to rail switching on data I/O ports
- CMOS low power consumption
- Latch-up performance exceeds 250 mA per JESD78B Class I level A
- I_{OFF} circuitry provides partial Power-down mode operation
- TSSOP56 packages: SOT364-1 and SOT481-2
- Specified from −40 °C to +85 °C and −40 °C to +125 °C

3. Ordering information

Table 1.   Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74CBTLV16211DGG	−40 °C to +125 °C	TSSOP56	plastic thin shrink small outline package; 56 leads; body width 6.1 mm	SOT364-1
74CBTLV16211DGV	−40 °C to +125 °C	TSSOP56	plastic thin shrink small outline package; 56 leads; body width 4.4 mm	SOT481-2

4. Functional diagram

Fig 1.   Logic symbol

Fig 2.   Logic diagram (one switch)

74CBTLV16211

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

Product data sheet

Rev. 6 — 15 December 2011

2 of 16

5. Pinning information

5.1 Pinning

n.c. 1	56 1$\overline{OE}$
1A0 2	55 2$\overline{OE}$
1A1 3	54 1B0
1A2 4	53 1B1
1A3 5	52 1B2
1A4 6	51 1B3
1A5 7	50 1B4
GND 8	49 GND
1A6 9	48 1B5
1A7 10	47 1B6
1A8 11	46 1B7
1A9 12	45 1B8
1A10 13	44 1B9
1A11 14	43 1B10
2A0 15	42 1B11
2A1 16	41 2B0
V_{CC} 17	40 2B1
2A2 18	39 2B2
GND 19	38 GND
2A3 20	37 2B3
2A4 21	36 2B4
2A5 22	35 2B5
2A6 23	34 2B6
2A7 24	33 2B7
2A8 25	32 2B8
2A9 26	31 2B9
2A10 27	30 2B10
2A11 28	29 2B11

74CBTLV16211

001aai100

Fig 3.   Pin configuration (SOT364-1 and SOT481-2)

5.2 Pin description

Table 2.   Pin description

Symbol	Pin	Description
n.c.	1	not connected
1A0 to 1A11	2, 3, 4, 5, 6, 7, 9, 10, 11, 12, 13, 14	independent input or output
2A0 to 2A11	15, 16, 18, 20, 21, 22, 23, 24, 25, 26, 27, 28	independent input or output
GND	8, 19, 38, 49	ground (0 V)
V_{CC}	17	supply voltage
2B0 to 2B11	41, 40, 39, 37, 36, 35, 34, 33, 32, 31, 30, 29	independent input or output

Table 2. **Pin description** *…continued*

Symbol	Pin	Description
1B0 to 1B11	54, 53, 52, 51, 50, 48, 47, 46, 45, 44, 43, 42	independent input or output
2$\overline{\text{OE}}$	55	output enable input (active-LOW)
1$\overline{\text{OE}}$	56	output enable input (active-LOW)

6. Functional description

Table 3. **Function table**[1]

Output enable input $\overline{\text{OE}}$	Function switch
L	ON-state
H	OFF-state

[1] H = HIGH voltage level; L = LOW voltage level.

7. Limiting values

Table 4. **Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V_{CC}	supply voltage			−0.5	+4.6	V
V_I	input voltage		[1]	−0.5	+4.6	V
V_{SW}	switch voltage	enable and disable mode	[1]	−0.5	V_{CC} + 0.5	V
I_{IK}	input clamping current	$V_I <$ −0.5 V		−50	-	mA
I_{SK}	switch clamping current	$V_I <$ −0.5 V		−50	-	mA
I_{SW}	switch current	V_{SW} = 0 V to V_{CC}		-	±128	mA
I_{CC}	supply current			-	+100	mA
I_{GND}	ground current			−100	-	mA
T_{stg}	storage temperature			−65	+150	°C
P_{tot}	total power dissipation	T_{amb} = −40 °C to +125 °C	[2]	-	600	mW

[1] The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For TSSOP56 packages: above 55 °C the value of P_{tot} derates linearly with 8.0 mW/K.

8. Recommended operating conditions

Table 5. **Recommended operating conditions**

Symbol	Parameter	Conditions		Min	Max	Unit
V_{CC}	supply voltage			2.3	3.6	V
V_I	input voltage			0	3.6	V
V_{SW}	switch voltage	enable and disable mode		0	V_{CC}	V
T_{amb}	ambient temperature			−40	+125	°C
$\Delta t/\Delta V$	input transition rise and fall rate	V_{CC} = 2.3 V to 3.6 V	[1]	0	200	ns/V

[1] Applies to control signal levels.

74CBTLV16211

Product data sheet **Rev. 6 — 15 December 2011** **4 of 16**

9. Static characteristics

Table 6. **Static characteristics**

At recommended operating conditions voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	T_{amb} = −40 °C to +85 °C			T_{amb} = −40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V_{IH}	HIGH-level input voltage	V_{CC} = 2.3 V to 2.7 V	1.7	-	-	1.7	-	V
		V_{CC} = 3.0 V to 3.6 V	2.0	-	-	2.0	-	V
V_{IL}	LOW-level input voltage	V_{CC} = 2.3 V to 2.7 V	-	-	0.7	-	0.7	V
		V_{CC} = 3.0 V to 3.6 V	-	-	0.9	-	0.9	V
I_I	input leakage current	pin n$\overline{OE}$; V_I = GND to V_{CC}; V_{CC} = 3.6 V	-	-	±1.0	-	±20	μA
$I_{S(OFF)}$	OFF-state leakage current	V_{CC} = 3.6 V; see Figure 4	-	-	±1	-	±20	μA
$I_{S(ON)}$	ON-state leakage current	V_{CC} = 3.6 V; see Figure 5	-	-	±1	-	±20	μA
I_{OFF}	power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±10	-	±50	μA
I_{CC}	supply current	V_I = GND or V_{CC}; I_O = 0 A; V_{SW} = GND or V_{CC}; V_{CC} = 3.6 V	-	-	10	-	50	μA
ΔI_{CC}	additional supply current	pin n$\overline{OE}$; V_I = V_{CC} − 0.6 V; V_{SW} = GND or V_{CC}; V_{CC} = 3.6 V [2]	-	-	300	-	2000	μA
C_I	input capacitance	pin n$\overline{OE}$; V_{CC} = 3.3 V; V_I = 0 V to 3.3 V	-	0.9	-	-	-	pF
$C_{S(OFF)}$	OFF-state capacitance	V_{CC} = 3.3 V; V_I = 0 V to 3.3 V	-	5.2	-	-	-	pF
$C_{S(ON)}$	ON-state capacitance	V_{CC} = 3.3 V; V_I = 0 V to 3.3 V	-	14.3	-	-	-	pF

[1] All typical values are measured at T_{amb} = 25 °C.

[2] One input at 3 V, other inputs at V_{CC} or GND.

9.1 Test circuits

V_I = V_{CC} or GND and V_O = GND or V_{CC}.

Fig 4. **Test circuit for measuring OFF-state leakage current (one channel)**

V_I = V_{CC} or GND and V_O = open circuit.

Fig 5. **Test circuit for measuring ON-state leakage current (one channel)**

74CBTLV16211

Product data sheet

**Rev. 6 — 15 December 2011**

5 of 16

9.2 ON resistance

Table 7.   Resistance R_{ON}

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Figure 6.

Symbol	Parameter	Conditions	T_{amb} = −40 °C to +85 °C			T_{amb} = −40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
R_{ON}	ON resistance	V_{CC} = 2.3 V to 2.7 V; [2] see Figure 7 to Figure 9						
		I_{SW} = 64 mA; V_I = 0 V	-	4.2	8.0	-	15.0	Ω
		I_{SW} = 24 mA; V_I = 0 V	-	4.2	8.0	-	15.0	Ω
		I_{SW} = 15 mA; V_I = 1.7 V	-	8.4	40	-	60.0	Ω
		V_{CC} = 3.0 V to 3.6 V; see Figure 10 to Figure 12						
		I_{SW} = 64 mA; V_I = 0 V	-	4.0	7.0	-	11.0	Ω
		I_{SW} = 24 mA; V_I = 0 V	-	4.0	7.0	-	11.0	Ω
		I_{SW} = 15 mA; V_I = 2.4 V	-	6.2	15	-	25.5	Ω

[1] Typical values are measured at T_{amb} = 25 °C and nominal V_{CC}.

[2] Measured by the voltage drop between the A and B terminals at the indicated current through the switch. ON-state resistance is determined by the lower of the voltages of the two (A or B) terminals.

## 9.3 ON resistance test circuit and graphs

$R_{ON} = V_{SW} / I_{SW}.$

Fig 6.   Test circuit for measuring ON resistance (one channel)

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 7.   ON resistance as a function of input voltage; V_{CC} = 2.5 V; I_{SW} = 15 mA

74CBTLV16211

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

Product data sheet

Rev. 6 — 15 December 2011

6 of 16

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 8. **ON resistance as a function of input voltage; V_{CC} = 2.5 V; I_{SW} = 24 mA**

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 9. **ON resistance as a function of input voltage; V_{CC} = 2.5 V; I_{SW} = 64 mA**

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 10. **ON resistance as a function of input voltage; V_{CC} = 3.3 V; I_{SW} = 15 mA**

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 11. **ON resistance as a function of input voltage; V_{CC} = 3.3 V; I_{SW} = 24 mA**

74CBTLV16211

Product data sheet

Rev. 6 — 15 December 2011

7 of 16

(1) T_{amb} = 125 °C.

(2) T_{amb} = 85 °C.

(3) T_{amb} = 25 °C.

(4) T_{amb} = −40 °C.

Fig 12. ON resistance as a function of input voltage; V_{CC} = 3.3 V; I_{SW} = 64 mA

10. Dynamic characteristics

Table 8. Dynamic characteristics
GND = 0 V; for test circuit see Figure 15

Symbol	Parameter	Conditions		T_{amb} = −40 °C to +85 °C			T_{amb} = −40 °C to +125 °C		Unit
				Min	Typ[1]	Max	Min	Max	
t_{pd}	propagation delay	nAn to nBn or nBn to nAn; see Figure 13	[2][3]						
		V_{CC} = 2.3 V to 2.7 V		-	-	0.13	-	0.2	ns
		V_{CC} = 3.0 V to 3.6 V		-	-	0.2	-	0.31	ns
t_{en}	enable time	nOE to nAn or nBn; see Figure 14	[4]						
		V_{CC} = 2.3 V to 2.7 V		1.0	2.0	7.0	1.0	7.8	ns
		V_{CC} = 3.0 V to 3.6 V		1.0	1.7	6.2	1.0	6.8	ns
t_{dis}	disable time	nOE to nAn or nBn; see Figure 14	[5]						
		V_{CC} = 2.3 V to 2.7 V		1.0	2.6	7.2	1.0	8.1	ns
		V_{CC} = 3.0 V to 3.6 V		1.0	3.0	7.7	1.0	8.8	ns

[1] All typical values are measured at T_{amb} = 25 °C and at nominal V_{CC}.

[2] The propagation delay is the calculated RC time constant of the on-state resistance of the switch and the load capacitance, when driven by an ideal voltage source (zero output impedance).

[3] t_{pd} is the same as t_{PLH} and t_{PHL}.

[4] t_{en} is the same as t_{PZH} and t_{PZL}.

[5] t_{dis} is the same as t_{PHZ} and t_{PLZ}.

11. Waveforms

Measurement points are given in Table 9.

Logic levels: V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.

Fig 13. The data input (nAn or nBn) to output (nBn or nAn) propagation delays

Table 9.   Measurement points

Supply voltage	Input			Output		
V_{CC}	V_M	V_I	$t_r = t_f$	V_M	V_X	V_Y
2.3 V to 2.7 V	$0.5V_{CC}$	V_{CC}	≤ 2.0 ns	$0.5V_{CC}$	$V_{OL} + 0.15$ V	$V_{OH} - 0.15$ V
3.0 V to 3.6 V	$0.5V_{CC}$	V_{CC}	≤ 2.0 ns	$0.5V_{CC}$	$V_{OL} + 0.3$ V	$V_{OH} - 0.3$ V

Measurement points are given in Table 9.

Logic levels: V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.

Fig 14. Enable and disable times

001aae331

Test data is given in Table 10.

Definitions for test circuit:

R_L = Load resistance.

C_L = Load capacitance including jig and probe capacitance.

R_T = Termination resistance should be equal to the output impedance Z_o of the pulse generator.

V_{EXT} = External voltage for measuring switching times.

Fig 15. Test circuit for measuring switching times

Table 10. Test data

Supply voltage	Load		V_{EXT}		
V_{CC}	C_L	R_L	t_{PLH}, t_{PHL}	t_{PZH}, t_{PHZ}	t_{PZL}, t_{PLZ}
2.3 V to 2.7 V	30 pF	500 Ω	open	GND	$2V_{CC}$
3.0 V to 3.6 V	50 pF	500 Ω	open	GND	$2V_{CC}$

74CBTLV16211

Product data sheet

Rev. 6 — 15 December 2011

10 of 16

12. Package outline

TSSOP56: plastic thin shrink small outline package; 56 leads; body width 6.1 mm   **SOT364-1**

DIMENSIONS (mm are the original dimensions).

UNIT	A max.	A₁	A₂	A₃	b_p	c	D[1]	E[2]	e	H_E	L	L_p	Q	v	w	y	Z	θ
mm	1.2	0.15 0.05	1.05 0.85	0.25	0.28 0.17	0.2 0.1	14.1 13.9	6.2 6.0	0.5	8.3 7.9	1	0.8 0.4	0.50 0.35	0.25	0.08	0.1	0.5 0.1	8° 0°

Notes

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.

2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT364-1		MO-153				~~99-12-27~~ 03-02-19

Fig 16. Package outline SOT364-1 (TSSOP56)

TSSOP56: plastic thin shrink small outline package; 56 leads; body width 4.4 mm

SOT481-2

DIMENSIONS (mm are the original dimensions)

UNIT	A max.	A₁	A₂	A₃	bₚ	c	D [1]	E [2]	e	H_E	L	Lₚ	v	w	y	Z [1]	θ
mm	1.2	0.15 0.05	1.05 0.80	0.25	0.23 0.13	0.20 0.09	11.4 11.2	4.5 4.3	0.4	6.6 6.2	1	0.75 0.45	0.2	0.07	0.08	0.4 0.1	8° 0°

Notes

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.

2. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT481-2	- - -	MO-194	- - -			01-11-24

Fig 17. Package outline SOT481-2 (TSSOP56)

74CBTLV16211

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

Product data sheet

Rev. 6 — 15 December 2011

12 of 16

13. Abbreviations

Table 11. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model
MM	Machine Model

14. Revision history

Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74CBTLV16211 v.6	20111215	Product data sheet	-	74CBTLV16211 v.5
Modifications:	• Legal pages updated.			
74CBTLV16211 v.5	20101230	Product data sheet	-	74CBTLV16211 v.4
74CBTLV16211 v.4	20100816	Product data sheet	-	74CBTLV16211 v.3
74CBTLV16211 v.3	20100112	Product data sheet	-	74CBTLV16211 v.2
74CBTLV16211 v.2	20090826	Product data sheet	-	74CBTLV16211 v.1
74CBTLV16211 v.1	20080620	Product data sheet	-	-

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

16. Contact information

For more information, please visit: **http://www.nxp.com**

For sales office addresses, please send an email to: **salesaddresses@nxp.com**

17. Contents