







LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	Flash Au Plating	0.76μ Au Plating
09	30.81	24.99	16.96	16.21	10.96	D09S33E4G*09LF	D09S33E6G*09LF
15	39.14	33.32	25.18	24.54	19.18	D15S33E4G*09LF	D15S33E6G*09LF
25	53.03	47.04	39.12	38.25	33.12	D25S33E4G*09LF	D25S33E6G*09LF

L --> ØT=M3
X --> ØT=UNC 4-40

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Technical characteristics:

Insulators: self-extinguishing thermoplastic, UL class 94V0, IR or reflow process compatible

Climatic characteristics:

Operating temperature range: -55°C +225°C

FOR ALL OTHER DETAILS REFER DWG.NO: C01-8646-0000

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified						title DD RA SOCKET CONNECTOR HIGH TEMPERATURE INSULATOR		
E	ELX-I-21461	AB	2015-07-22	angles	linear	.0±0.1						
						.00±0.1						
				0°±2°		.000±0.1		scale 2:1	dwg no C01—8646—0449			
				dr	JOHN SLEEBA	1996-06-21		sheet 1 of 1		size A3		
				engr	ALIAS BABU	2015-07-22		C01—8646—0449				
				chr	MITHUN PAUL	2015-07-22						
				appd	BIJU K PAUL	2015-07-22						
sheet index	revision sheet	E 1										