

Customer Information Sheet

DRAWING No.: M80-400XXX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:**MATERIAL:**

MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK

CONTACT CLIP = BERYLLIUM COPPER

CONTACT SHELL = BRASS

JACKSCREW, CIRCLIP = STAINLESS STEEL

FINISH:01 = 0.3 μ GOLD CLIP, 3.5-5.0 μ TIN/LEAD SHELL05 = 0.3 μ GOLD CLIP, 0.25-0.3 μ GOLD SHELL42 = 0.3 μ GOLD CLIP, 3.5-5.0 μ 100% TIN SHELL**ELECTRICAL:**

CURRENT RATING AT 25°C = 3.0A MAX

CURRENT RATING AT 85°C = 2.2A MAX

WORKING VOLTAGE = 120V AC/DC

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE = 25 m Ω MAXINSULATION RESISTANCE = 100 M Ω MIN**MECHANICAL:**

DURABILITY = 500 OPERATIONS

INSERTION FORCE ($\varnothing$ 0.5mm GAUGE) = 2.8N MAXWITHDRAWAL FORCE ($\varnothing$ 0.5mm GAUGE) = 0.2N MIN**ENVIRONMENTAL:**

TEMPERATURE RANGE = -55°C TO +125°C



PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT



SPECIFICATION C005XX

(LATEST ISSUE)



SECTION X-X

RECOMMENDED PCB LAYOUT




DIMENSION	CALCULATION
DIM 'A'	TOTAL No. OF CONTACTS - 2
DIM 'B'	TOTAL No. OF CONTACTS + 5
DIM 'C'	TOTAL No. OF CONTACTS + 10
EXAMPLE: CONNECTOR WITH 20 CONTACTS, GOLD CLIP AND 100% TIN SHELL, M80-4002042	
DIM 'A' = 18.00mm, DIM 'B' = 25.00mm, DIM 'C' = 30.00mm	

ORDER CODE:**M80-400XXX**TOTAL No. OF CONTACTS
04 TO 50
(EVEN NUMBERS ONLY)**FINISH**

01 - GOLD CLIP, TIN/LEAD SHELL

05 - GOLD CLIP, GOLD SHELL

42 - GOLD CLIP, 100% TIN SHELL



RA	F	09.10.08	10173
NAME	ISS.	DATE	C/NOTE
APPROVED: R.ADDE			
CHECKED: M.G.PLESTED			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCESX. = $\pm$ 1mmX.X = $\pm$ 0.25mmX.XX = $\pm$ 0.10mmX.XXX = $\pm$ 0.01mmANGLES = $\pm$ 5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²TITLE: JACKSCREW DATAMATE
DIL VERTICAL PC TAIL
FEMALE ASSEMBLY

DRAWING NUMBER:

M80-400XXXSHT
2 OF 2