


4.0 Amp. Glass Passivated Bridge Rectifiers

Dimensions in mm.	KBL	Voltage 400 V to 1000 V	Current 4.0 A
		• Glass passivated chip junction • Ideal for printed circuit board • Reliable low cost construction • High temperature soldering guaranteed: 260 °C / 10 seconds / 0.375" (9.5mm), lead lengths at 5lbs (2.3 Kg) tension.	
		MECHANICAL DATA • Case: Molded plastic body. • Mounting position: Any • Leads solderable per MIL-STD-202, Method 208	

Maximum Ratings and Electrical Characteristics at 25 °C

		KBL 404G	KBL 405G	KBL 406G	KBL 407G
V_{RRM}	Maximum Recurrent Peak Reverse Voltage (V)	400	600	800	1000
V_{RMS}	Maximum RMS Voltage (V)	280	420	560	700
V_{DC}	Maximum DC Blocking Voltage (V)	400	600	800	1000
$I_{F(AV)}$	Maximum Average Forward Rectified Current @ $T_A = 50\text{ °C}$	4.0 A			
I_{FSM}	Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC Method)	150 A			
T_j	Operating Temperature Range	-55 to +150 °C			
T_{stg}	Storage Temperature Range	-55 to +150 °C			


Electrical Characteristics at Tamb = 25 °C

V_F	Maximum Instantaneous Forward Voltage @ = 2.0 A @ = 4.0 A	1.0 V 1.1 V
I_R	Maximum DC Reverse Current @ $T_A = 25\text{ °C}$ at Rated DC Blocking Voltage @ $T_A = 125\text{ °C}$	10.0 μ A 500 μ A
$R_{th(j-a)}$ $R_{th(j-l)}$	Typical Thermal Resistance (Note)	19 °C/W 2.4 °C/W


Note: Thermal Resistance from Junction to Ambient and from Junction to Lead Mounted on P.C.B.
with 0.6" x 0.6" (16 mm x 16 mm) Copper Pads.

Rating And Characteristic Curves


TYPICAL FORWARD CHARACTERISTICS
PER BRIDGE ELEMENT




MAXIMUM FORWARD CURRENT DERATING
CURVE



MAXIMUM NON-REPETITIVE FORWARD
SURGE CURRENT PER BRIDGE ELEMENT



TYPICAL JUNCTION CAPACITANCE



TYPICAL REVERSE CHARACTERISTICS
PER BRIDGE ELEMENT

