


ASSEMBLY NUMBER		DETAILS				G MAX	L MAX	BB DIA +.000 -.010	CC DIA	Y THREAD		W +.000 -.010	SCREW SIZE
		NUT	CLAMP		SIZE-CLASS 2B					PITCH DIA			
			PART NUMBER	QTY									
10-101987-8		10-101970-8		10-130511-8	2	.775	1.190	.250	.540	.4375-28UNEF	.4143-.4189	.215	6-32NC
	-10		-10			.837	↓	.312	.665	.5625-24UNEF	.5354-.5405	↓	↓
	-12		-12			.963	↓	.438	.793	.6875-24UNEF	.6604-.6656	↓	↓
	-14		-14			1.087	↓	.562	.910	.8125-20UNEF	.7800-.7857	↓	↓
	-16		-16			1.150	1.292	.624	1.037	.9375-20UNEF	.9050-.9109	↓	↓
	-18		-18			1.400	1.292	.750	1.155	1.0625-18UNEF	1.0264-1.0326	↓	8-32NC
	-20		-20			1.400	1.332	.750	1.281	1.1875-18UNEF	1.1514-1.1577	.312	↓
	-22		-22			1.587	1.332	.938	1.408	1.3125-18UNEF	1.2764-1.2827	.312	↓
	-24		-24			1.681	1.332	1.000	1.533	1.4375-18UNEF	1.4014-1.4079	.312	↓

33508-95											
2											
3											
4											
5	42524-303										
A1	43524-558										
A2	43524-1481										
A3	43524-791										
A4	43524-791										
A5	53536-78										
B	23813										
C	84450										
D	86810										

SUPERCEDES PRIOR ISSUE
OF THE SAME REVISION



10-101987

Scanned

1. TO COMPLETE ASSEMBLY NO. AND DETAIL NO., ADD
APPLICABLE LAST DIGIT SUFFIX NO FOR DESIRED FINISH:

CHROMATE TREATED
BRIGHT CADMIUM PLATE
BLACK ANODIZE
CADMIUM PLATE OLIVE DRAB
GRAY ANODIZE
ANODIC COATING
NICKEL PLATED
CADMIUM PLATE NICKEL BASE
BRIGHT NICKEL
OLIVE DRAB CADMIUM NICKEL BASE PLATE
CHROMIUM PLATED
NICKEL ALLOY PLATE

SUFFIX-XX0
SUFFIX-XX1
SUFFIX-XX2
SUFFIX-XX3
SUFFIX-XX4
SUFFIX-XX5
SUFFIX-XX6
SUFFIX-XX7
SUFFIX-XX8
SUFFIX-XX9
SUFFIX-XXE
SUFFIX-XXG

RELEASE
42524-119
33508-95

43524-558
42524-303
43524-1481
53536-78

BLACK ZINC ALLOY CONDUCTIVE PLATE SUFFIX-XXX
BLACK ZINC ALLOY PLATE SUFFIX-XXY

SCINTILLA MAGNETO DIVISION		TO ORDER, UNLESS OTHERWISE SPECIFIED	
CLAMP ASSEMBLY, CABLE STRAIN RELIEF, ELECTRICAL CONNECTOR, TYPE PC(1)		QUANTITY: 10-117600/624 71-150700/724	
SEE NOTE 1		SEE PARTS LIST	
10-101987		10-101987	