

INTERCONNECTS

SERIES 350, 450, 801, 803 • .100" GRID (.025" DIA. PINS), LOW PROFILE HEADERS & VERSATILE SOCKETS • SINGLE & DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5

- Series 350 and 450 single and double row pin headers use MM #0290 pins. See page 215 for details
- Series 801 and 803 single and double row low profile sockets use MM #1303 receptacles. See page 180 for details
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #16 contact rated at 4.5 amps. Receptacles accept .025" diameter and .025" square pins. See page 256 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 350...001 Single Row .025" Pin / .018" Solder Tail			
	350-XX-1	-00-001000		
	Specify number of pins	01-64		
FIG. 2	Series 450...001 Double Row .025" Pin / .018" Solder Tail			
	450-XX-2	-00-001000		
	Specify number of pins	02-64		
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264				
SPECIFY PLATING CODE XX=				
Pin Plating	10 	90	40 	
	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn	

FIG. 3	Series 801...003 Low Profile Socket (short insulator)						
	801-XX-0	-10-003000					
	Specify number of pins	01-64					
FIG. 4	Series 801...013 Low Profile Socket (long insulator)						
	801-XX-0	-10-013000					
	Specify number of pins	01-36					
FIG. 5	Series 803...003 Double Row Low Profile Socket						
	803-XX-0	-10-003000					
	Specify number of pins	02-72					
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264							
SPECIFY PLATING CODE XX=							
Sleeve (Pin)					41 	43 	
					200 μ" Sn	200 μ" Sn	
Contact (Clip)					10 μ" Au	30 μ" Au	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[801-43-005-10-003000](#) [801-43-036-10-013000](#) [801-43-064-10-003000](#) [803-43-072-10-003000](#) [801-43-006-10-003000](#)