










SPECIFICATIONS	
CONTACT CARRIER MATERIAL/COLOR	PVC/BLACK
MOLDED MATERIAL/COLOR	PVC/BLACK
CONTACT MATERIAL/PLATING	BRASS or COPPER/GOLD
HOUSING MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	40.0 A
RATED VOLTAGE [V]	600 VAC
CABLE JACKET MATERIAL/COLOR	TPE/BLACK
CONDUCTOR INSULATION MATERIAL	PVC
NUMBERS OF CONDUCTORS [AWG]	3x10 AWG
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67, IP68, IP69K
APPROVALS AND CERTIFICATIONS	UL 2237, CE

MALE END VIEW	FEMALE END VIEW
 <p>2 (LONG) 1 3</p> <p>1 = BLACK 2 = GREEN/YELLOW 3 = WHITE</p>	 <p>2 3 1</p> <p>1 = BLACK 2 = GREEN/YELLOW 3 = WHITE</p>



<p>* METERS SEE NOTE 1</p> <p>105.1 [4.14]</p> <p>83.5 [3.29]</p> <p>63.0 [2.48]</p> <p>1 3/8-16UN</p> <p>80.8 [3.18]</p> <p>41.0 [1.61]</p> <p>17.7 [0.70]</p> <p>KEYWAY LOCATOR SYMBOL</p> <p>CAUTION LABEL</p> <p>STANDARD TURCK LABEL</p> <p>CAUTION LABEL</p>																																																																					
<table><tr><th>CABLE LENGTH</th><th>TOLERANCE*</th></tr><tr><td>ALL LENGTHS</td><td>+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER</td></tr><tr><th>STRIP LENGTH</th><th>TOLERANCE*</th></tr><tr><td>0-7mm</td><td>±0.5mm</td></tr><tr><td>8-29mm</td><td>±1.0mm</td></tr><tr><td>30-49mm</td><td>±2.0mm</td></tr><tr><td>50-69mm</td><td>±3.0mm</td></tr><tr><td>70-100mm</td><td>±4.0mm</td></tr><tr><td>OVER 100mm</td><td>±5.0mm</td></tr><tr><td colspan="2">* UNLESS OTHERWISE SPECIFIED</td></tr></table>		CABLE LENGTH	TOLERANCE*	ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER	STRIP LENGTH	TOLERANCE*	0-7mm	±0.5mm	8-29mm	±1.0mm	30-49mm	±2.0mm	50-69mm	±3.0mm	70-100mm	±4.0mm	OVER 100mm	±5.0mm	* UNLESS OTHERWISE SPECIFIED																																																	
CABLE LENGTH	TOLERANCE*																																																																				
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER																																																																				
STRIP LENGTH	TOLERANCE*																																																																				
0-7mm	±0.5mm																																																																				
8-29mm	±1.0mm																																																																				
30-49mm	±2.0mm																																																																				
50-69mm	±3.0mm																																																																				
70-100mm	±4.0mm																																																																				
OVER 100mm	±5.0mm																																																																				
* UNLESS OTHERWISE SPECIFIED																																																																					
<div><p><b>CAUTION:</b> RISK OF ELECTRICAL SHOCK DO NOT DISCONNECT UNDER LOAD</p></div> <div><p><b>SOURCE DRAWING - FOR REFERENCE ONLY</b></p></div>																																																																					
<table><tr><td colspan="2">RELATED DOCUMENTS</td><td colspan="2">3RD ANGLE PROJECTION</td><td colspan="2">THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</td><td colspan="2">3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</td></tr><tr><td>1.</td><td></td><td rowspan="8"></td><td rowspan="8"></td><td>DRFT</td><td>RDS</td><td>DATE</td><td>11/06/08</td></tr><tr><td>2.</td><td></td><td>APVD</td><td></td><td>SCALE</td><td>1=2.0</td></tr><tr><td>3.</td><td></td><td colspan="2" rowspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td><td colspan="2">UNIT OF MEASUREMENT</td><td colspan="2">DESCRIPTION</td></tr><tr><td>4.</td><td></td><td colspan="2">MILLIMETER [ INCH ]</td><td colspan="2">GSDM GKDWM 30-*M</td></tr><tr><td colspan="2">MATERIAL</td><td colspan="2" rowspan="2">CONTACT TURCK FOR MORE INFORMATION</td><td colspan="2" rowspan="2">DO NOT SCALE THIS DRAWING</td><td colspan="2">IDENTIFICATION NO.</td></tr><tr><td colspan="6">SEE SPECIFICATIONS</td><td colspan="2">REV</td></tr><tr><td colspan="2">FINISH</td><td colspan="2" rowspan="2">SEE SPECIFICATIONS</td><td colspan="2" rowspan="2"></td><td colspan="2"></td></tr><tr><td colspan="6"></td><td colspan="2"></td></tr></table>		RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us		1.				DRFT	RDS	DATE	11/06/08	2.		APVD		SCALE	1=2.0	3.		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT		DESCRIPTION		4.		MILLIMETER [ INCH ]		GSDM GKDWM 30-*M		MATERIAL		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		IDENTIFICATION NO.		SEE SPECIFICATIONS						REV		FINISH		SEE SPECIFICATIONS													
RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us																																																															
1.				DRFT	RDS	DATE	11/06/08																																																														
2.				APVD		SCALE	1=2.0																																																														
3.				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT		DESCRIPTION																																																													
4.						MILLIMETER [ INCH ]		GSDM GKDWM 30-*M																																																													
MATERIAL				CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		IDENTIFICATION NO.																																																													
SEE SPECIFICATIONS								REV																																																													
FINISH				SEE SPECIFICATIONS																																																																	
<table><tr><td>I</td><td>UPDATE RATED CURRENT</td><td>NF</td><td>04/25/19</td><td>69361</td></tr><tr><td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr></table>		I	UPDATE RATED CURRENT	NF	04/25/19	69361	REV	DESCRIPTION	BY	DATE	ECO NO.																																																										
I	UPDATE RATED CURRENT	NF	04/25/19	69361																																																																	
REV	DESCRIPTION	BY	DATE	ECO NO.																																																																	