


REV. U

DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED		TOLERANCES ARE:	ANGLES	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$ [.3]	THREE PLACE DECIMALS $\pm .005$ [.13]		$\pm 2^\circ$	LOW PROFILE SOCKET STRIP	SLW-1XX-01-X-X
TWO PLACE DECIMALS $\pm .01$ [.3]	FOUR PLACE DECIMALS $\pm .0020$ [.051]				SHEET 1 OF 1




SLW-1XX-01-X-X

POSITION SPECIFICATION
-01 THRU -50 PER ROW
"A"= NO. OF POS. x .100 [2.54]



CONTACT STYLE
-01: USE C-28-X

ROW SPECIFICATION
-D: DOUBLE (USE SLW-50-D)
-S: SINGLE (USE SLW-50-S)

PLATING SPECIFICATION
-G: GOLD-SPECIFY -G IN CONTACT SUFFIX -X
-T: TIN-SPECIFY -T IN CONTACT SUFFIX -X
-S: SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -S IN CONTACT SUFFIX -X
-F: FLASH SELECTIVE GOLD-SPECIFY -F IN CONTACT SUFFIX -X
-H: HEAVY GOLD-SPECIFY -H IN CONTACT SUFFIX -X
-L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -L IN CONTACT SUFFIX -X



- NOTES:
1. MIN PUSHOUT FORCE: 1 lb.
 2. MAX BOW: .005 in/in [mm/mm], .025 [.64]
 3. CUT END WALLS TO BE .012 [.30] MIN.
 4. (C) REPRESENTS CRITICAL DIM.
- FOR STATISTICAL PROCESS CONTROL
5. .010 [.25] MAX CUT FLASH
 6. NO TUBE PACKAGING REQUIRED



Do not scale
from this print

PLOT SCALE: 1=1

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING,
RECORDING, OR BY ANY
INFORMATION STORAGE AND
RETRIEVAL SYSTEM, WITHOUT
WRITTEN PERMISSION OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: PURVIS 9-4-87
CHECKED BY: McCARTIN

ENG. APPROVAL
DEM

SLW-1XX-01-X-X
SHEET 1 OF 1