


KENWOOD

ProTalk® TK-2402V16P/3402U16P

Compact VHF/UHF FM 5-Watt Portable Radios



Kenwood's TK-2402V16P/TK-3402U16P 16 channel portable two-way radios deliver professional performance with ergonomic ease. Based upon a proven design – with such features as scan, built-in VOX, and long battery life – the compact 5-watt ProTalk® has been expertly engineered to satisfy the toughest job requirements, in all conditions, thanks to MIL-STD 810 & IP54/55 weatherproofing.

COMPACT DESIGN

The rounded contours of the TK-2402V16P/3402U16P provide a superbly comfortable hold, while the non-slip elastomer channel knob with improved torque characteristics and an enlarged PTT button ensure positive tactile response during operation.

TOUGH & WATER RESISTANT

Built to take rough treatment in stride, the ProTalk® has passed the demanding IP54/55 dust and water intrusion tests – both with and without the KMC-45 optional speaker microphone. It also meets or exceeds 11 stringent MIL-STD 810 C/D/E/F/G environmental standards, including "driven rain".

ENHANCED AUDIO QUALITY

Success in business depends on smooth communications, but power output is not the only factor that determines audio clarity. As an experienced audio specialist, Kenwood has drawn on decades of expertise to ensure that the ProTalk®'s sound quality is undeniably clearer and crisper, as well as loud – thanks to the 36mm-diameter speaker, which delivers up to 1 watt audio output.

WIRELESS CLONING

This feature simplifies the setting up of multiple ProTalk® radios for identical functions, eliminating the need to customize individual radios. (Dealer function only)

FREQUENCY & QT/DQT (Narrowband Compliant)

Users can program a ProTalk® to any of the pre-stored frequencies and QT/DQT codes, thus assuring compatibility with other brands. The ProTalk® VHF (TK-2402V16P) 16-channel model has 27 pre-stored frequencies while the ProTalk® UHF (TK-3402U16P) 16-channel model has 90. Both models have 39 QT tones and 168 DQT codes. For licensing information, please contact the FCC at <http://www.fcc.gov>

2 PROGRAMMABLE FUNCTION KEYS

Both PF Keys can be programmed for any of the many functions available, permitting customization to suit your specific requirements.

INDEPENDENT SETTINGS PER CHANNEL (VOX, COMPANDER, SCRAMBLER)

Radio channels can be programmed independently for VOX, scrambler and compander functions. This means a user can switch a function on or off simply by changing channels (on the same frequency).

BUILT-IN VOICE-INVERSION SCRAMBLER

This feature provides basic protection against casual eavesdropping. Up to 16 of 2097 possible inversion frequencies can be chosen and assigned to any channel.

5 WATTS TRANSMIT POWER

VHF & UHF	In Steel and/or concrete reinforced buildings	High-rise buildings
UHF 1.5 Watt	Up to 225,000 sq.ft.	Up to 17 floors
UHF 2 Watt	Up to 250,000 sq.ft.	Up to 20 floors
UHF 5 Watt	Up to 370,000 sq.ft.	Up to 33 floors
VHF 2 Watt	Up to 220,000 sq.ft.	Up to 13 floors
VHF 5 Watt	Up to 300,000 sq.ft.	Up to 18 floors


*Talk range will vary based on terrain, conditions and type of radio

OTHER FEATURES

- Voice Annunciation • Battery Save • Channel Confirmation Mode
- B.C.L. (Busy Channel Lockout) • Key Lock • 4-color LEDs (blue, red, orange, green) • Scan Del/Add • KENWOOD ESN (Electronic Serial Number) • Adjustable Microphone Gain (by FPU): High/Normal/Low
- Time-Out Timer • Low Battery Warning • Two Year Radio Warranty

2 Year Warranty

Options

KNB-29N Ni-MH Battery Pack (1,500mAh)		KRA-22 VHF Low Profile Helical Antenna		KHS-7 Single Muff Headset		KHS-26 Earbud In-line PTT Headset	
KNB-45L 2,000mAh/7.4V Li-Ion Battery Pack		KRA-23 UHF Low Profile Helical Antenna		KHS-7A Single Muff Headset with In-line PTT		KHS-27 D-Ring In-line PTT Headset	
KSC-35SK Fast Charger For the KNB-45L (3-Hour)		KRA-26 VHF Helical Antenna		KHS-8BL 2-wire Palm Mic with Earphone (Black)		KHS-31 C-Ring PTT Ear Hanger Headset	
KSC-43K Dual Chemistry Fast Charger For the KNB-29N/45L		KRA-27 UHF Whip Antenna		KHS-9BL 3-wire Lapel Mic with Earphone (Black)		KMB-28 Six Unit Charger Adapter (for six KSC-35SK chargers)	
KVC-22 DC Vehicular Charger Adapter		KMC-45 Speaker Microphone		KHS-22 Behind-the-head Headset with PTT		KBH-10 Belt Clip	
KRA-41 VHF Stubby Antenna		KMC-21 Compact Speaker Microphone		KHS-23 2-wire Palm Mic		KLH-187 Nylon Case	
KRA-42 UHF Stubby Antenna		KEP-2 Earphone Kit for KMC-45 (2.5mm plug)		KHS-25 D-Ring Ear Hanger with PTT & Boom Mic			

All accessories and options may not be available in all markets.
Contact an authorized Kenwood dealer for details and complete list of all accessories and options.

Specifications

Model	TK-2402V16P	TK-3402U16P
GENERAL		
Pre-set Frequencies	27 (151-159 MHz)	90 (451-470 MHz)
Number of Channels	16	
Channel Spacing		
Wide/Narrow	25 kHz*	12.5 kHz
Operating Voltage	7.5V DC±20%	
Battery Life (5-5-90 during hi-power battery saver: OFF/ON) with KNB-45L (2000mAh)	More than 12 / 18 hours	
Operating Temperature Range**	-22°F ~ +140°F (-30°C ~ +60°C)	
Frequency Stability	±2.5 ppm (-30°C ~ +60°C)	
Antenna Impedance	50 Ω	
Dimensions (W x H x D), Projections not included with KNB-45L	2.13 x 4.8 x 1.32 inch (54 x 122 x 33.7 mm)	
Weight (Net)		
Radio Only	5.8oz (165g)	
with KNB-45L	9.9oz (281g)	
FCC ID	ALH434900	ALH435000

*25kHz is not for sale in the USA or US territories.

**-14°F ~ +140°F (-10°C ~ +60°C) When KNB-29N/45L is in use

Model	TK-2402V16P	TK-3402U16P
RECEIVER (Measurements made per TIA/EIA-603)		
Sensitivity (12dB SINAD)	Wide/Narrow	0.25µV/0.28µV
Selectivity	Wide/Narrow	70dB/60dB
Intermodulation Distortion	Wide/Narrow	70dB/60dB
Spurious Response		70 dB
Audio Distortion		less than 10% distortion
Audio Output		1 W / 12 Ω (Internal Speaker) 500mW / 8 Ω (External Speaker)
TRANSMITTER (Measurements made per TIA/EIA-603)		
RF Power Output	High/Low	5W/1W
Spurious Response		70 dB
FM Hum & Noise	Wide/Narrow	45/40dB
Audio Distortion		Less than 5%
Type of Emission	Wide/Narrow	16K0F3E* / 11K0F3E

Specifications shown are typical.

Specifications are subject to change without notice, due to advancements in technology.

ProTalk® is a registered trademark of JVCKENWOOD Corporation in the United States and other countries.

ACCESSORIES INCLUDED

- KNB-45L Li-Ion Battery
- KSC-35SK 3-Hour Fast Charger
- KBH-10 Spring Action Belt Clip
- Removable Antenna
- Channel Stopper

Applicable MIL-STD & IP

Standard	MIL 810C Methods/Procedures	MIL 810D Methods/Procedures	MIL 810E Methods/Procedures	MIL 810F Methods/Procedures	MIL 810G Methods/Procedures
Low Pressure	500.1/Procedure I	500.2/Procedure I, II	500.3/Procedure I, II	500.4/Procedure I, II	500.5/Procedure I, II
High Temperature	501.1/Procedure I, II	501.2/Procedure I, II	501.3/Procedure I, II	501.4/Procedure I, II	501.5/Procedure I, II
Low Temperature	502.1/Procedure I	502.2/Procedure I, II	502.3/Procedure I, II	502.4/Procedure I, II	502.5/Procedure I, II
Temperature Shock	503.1/Procedure I	503.2/Procedure I	503.3/Procedure I	503.4/Procedure I, II	503.5/Procedure I
Solar Radiation	505.1/Procedure I	505.2/Procedure I	505.3/Procedure I	505.4/Procedure I	505.5/Procedure I
Rain	506.1/Procedure I, II	506.2/Procedure I, II	506.3/Procedure I, II	506.4/Procedure I, III	506.5/Procedure I, III
Humidity	507.1/Procedure I, II	507.2/Procedure II, III	507.3/Procedure II, III	507.4	507.5/Procedure II
Salt Fog	509.1/Procedure I	509.2/Procedure I	509.3/Procedure I	509.4	509.5
Dust	510.1/Procedure I	510.2/Procedure I	510.3/Procedure I	510.4/Procedure I, III	510.5/Procedure I
Vibration	514.2/Procedure VIII, X	514.3/Procedure I	514.4/Procedure I	514.5/Procedure I	514.6/Procedure I
Shock	516.2/Procedure I, II, V	516.3/Procedure I, IV	516.4/Procedure I, IV	516.5/Procedure I, IV	516.6/Procedure I, IV

International Protection Standard

Dust & Water Protection IP54/55*

*To meet IP54/55, the 2-pin connector cover has to be connected on the radio or the locking bracket has to be attached to the KMC-45 external speaker microphone.

BUY TWO WAY RADIOS

528 S. Cherry Road
Rock Hill, SC 29732
1-800-584-1445

www.buytwowayradios.com

KENWOOD

Kenwood U.S.A. Corporation
Communications Sector Headquarters
3970 Johns Creek Court, Suite 100, Suwanee, GA 30024-1265

Order Administration/Distribution
P.O. BOX 22745, 2201 East Dominguez St., Long Beach, CA 90801-5745

www.kenwoodusa.com/protalkinfo



ISO9001 Registered
Professional Systems Business Group
JVCKENWOOD Corporation

ADS#50412 Printed in USA