


SEZIONE B-B
(SECTION B-B)

SEZIONE C-C
(SECTION C-C)



	N	NATURALE (NATURAL)	282236-2	3	\\\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
OBSOLETE	-	NERO (BLACK)	282236-1	2	VED. TABELLA (SEE TABLE)	GOMMA (RUBBER)	GUARNIZIONE (RUBBER GASKET)
				1	NERO (BLACK)	PA 6.6	BLOCCETTO 6 VIE (6 POS. HOUSING)
	REV.	COLORE GUARNIZIONE (SEALING COLOUR)	P/N ASSEM. ASS' P/N	N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)
	N	ECR-14-003472	MP	CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
	M1	OBSOLET.-1 CON ET00-0069-02 OBSOLETE-1 FOR ET00-0069-02	P.Z.	THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION
	M	AGGIORN. CON ET00-0222-01 REVISED WITH ET00-0222-01	M.P.	© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING			19
	L1	AGGIUN.-2 CON ET00-0249-00 ADDED-2 FOR ET00-0249-00	A.P.	TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)			DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0mm REDUCED INS. CABLE
	L	AGGIOR. CON ET00-0221-96 REVISED FOR ET00-0221-96	A.F.	± 0.3 ANGOLI (ANGLES) ±2°			RANGO FILO (WIRE RANGE) 0.5-2.5mm²
	B	AGGIOR. CON ET00-0108-95 REVISED FOR ET00-0108-95	M.P.	DIS. 25 SEPT 93 (DR.) R. MARTINI			SCALA (SCALE) 2:1
	A	PRIMA EMISSIONE (GIA' IN PRODUZIONE)	R.M.	CONT. 27 SEPT 93 (CHK) C. TARTARI			TE Connectivity
	REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DATE)	APP. (APP.)			DESCRIZIONE (DESCRIPTION) 6 WAY SPLASH PROOF CONN. ASSY with SECONDARY LOCK
	REV. (REV.)			LOC. SIZE NUMERO (DWG NO)			REV. FOGLIO (SHEET)
				I A3 C-282236			N 1 B1 (OF) 2

