


CATALOG LISTING
PAGE 1 OF 1
RELEASE NO. PR-18660
ISSUE **M**
3

REVISIONS
A PR-18660 SAV 10CT90
B CO-94402 JJA 5 MAR 99

DDM/CAD
DRAWN
SAV
1 OCT 90
CHECK




NOTES

- $\triangle 1$ MOUNTING HOLES WILL ACCEPT $\phi .087$ MAX PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- $\triangle 2$ ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- $\triangle 3$ WEIGHT OF SWITCH ONLY IS .26 OZ MAX WEIGHT OF SWITCH WITH WIRE LEADS IS .65 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS		ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE ——— 5-17 OZ		CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE ——— 4 OZ MIN		250 VAC-----5 AMP			
RELEASE TRAVEL ——— .004 MIN		30 VOLTS DC RATING	ONE PLACE (.0)		$\pm .030$
DIFFERENTIAL TRAVEL ——— .004 MAX		INDUCTIVE---SEA LEVEL---3 AMP	TWO PLACE (.00)		$\pm .015$
OVERTRAVEL ——— .003 MIN		50,000 FT---2.5 AMP	THREE PLACE (.000)		$\pm .005$
		RESISTIVE---SEA LEVEL---5 AMP	ANGLES		$\pm$
		50,000 FT---5 AMP	WEIGHT $\triangle 3$		
		MAXIMUM INRUSH-----24 AMP			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1SE211](#)