


SuperTan® Extended (STE) Capacitors, Wet Tantalum Capacitors with Hermetic Seal



FEATURES

Vishay SuperTan® Extended (STE) represents a major breakthrough in wet tantalum capacitor technology. Its unique cathode system, also used in the ST, provides the highest capacitance per unit volume available. The STE combines the inherent reliability of wet tantalum with the capacitance stability of solid tantalum, and there are no circuit impedance restrictions. The range is exceptionally well suited for low voltage filtering and energy storage applications. Ideal for designs targeting the military and aerospace industry.

The SuperTan® Extended (STE) is housed in an all tantalum, hermetically sealed case and is manufactured to withstand high stress and hazardous environments.

- Axial through-hole terminations: Standard tin/lead (Sn/Pb) 100 % tin (RoHS compliant) available
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

Note

* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.



PERFORMANCE CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C (to + 125 °C with voltage derating)

Capacitance Tolerance: At 120 Hz, + 25 °C. ± 20 % standard. ± 10 % available as special.

DC Leakage Current (DCL Max.): At + 25 °C and above: Leakage current shall not exceed the values listed in the Standard Ratings Tables.


Life Test: Capacitors are capable of withstanding a 2000 h life test at a temperature of + 85 °C at the applicable rated DC working voltage.

ORDERING INFORMATION

STE	6000	16	T4	M	I	E3
TYPE	CAPACITANCE μF	DC VOLTAGE RATING AT + 85 °C	CASE SIZE	CAPACITANCE TOLERANCE	INSULATING SLEEVE	RoHS COMPLIANT
				M = ± 20 % K = ± 10 %	I = Insulated X = Uninsulated	E3 = 100 % tin termination (RoHS compliant) Blank = SnPb termination (standard design)

Note

- Packaging: The use of formed plastic trays for packaging this type of axial lead component is standard. Tape and reel is not recommended due to the unit weight.

DIMENSIONS in inches [millimeters]


CASE CODE	D ± 0.016 [0.41]	MAX. INSULATED (DIA.)	L ₁ + 0.031 [0.79] UNINSULATED	E ± 0.250 [6.35] MAX.
T1	0.188 [4.78]	0.219 [5.56]	0.453 [11.51]	1.500 [38.10]
T2	0.281 [7.14]	0.312 [7.92]	0.641 [16.28]	2.250 [57.15]
T3	0.375 [9.52]	0.406 [10.31]	0.766 [19.46]	2.250 [57.15]
T4	0.375 [9.52]	0.406 [10.31]	1.062 [26.97]	2.250 [57.15]

Notes

- Material at egress is tantalum
- Insulation sleeving will lap over the ends of the capacitor case
- Tinned nickel leads, solderable and weldable
- Approx. weight:
T1: 2.3 g, T2: 5.7 g
T3: 9.4 g, T4: 14.8 g

STANDARD RATINGS

CAPACITANCE (μF)	VOLTAGE	CASE CODE	PART NUMBER	MAX. ESR AT + 25 °C 120 Hz (Ω)	TYP. ESR AT + 25 °C 1 kHz (Ω)	MAX. DCL AT + 25 °C (μA)	MAX. DCL AT + 85 °C/ + 125 °C (μA)	MAX. CAPACITANCE CHANGE AT - 55 °C (%)	MAX. CAPACITANCE CHANGE AT + 85 °C (%)	MAX. CAPACITANCE CHANGE AT + 125 °C (%)	MAX. IMP. AT - 55 °C 120 Hz (Ω)	AC RIPPLE 85 °C 40 kHz mA RMS
10 V _{DC} at + 85 °C; 7 V _{DC} at + 125 °C												
680	10	T1	Preliminary value, contact marketing									
2000	10	T2	Preliminary value, contact marketing									
4700	10	T3	STE4700-10T3MI	0.35	< 0.200	16	100	- 80	10	20	3.50	4000
10 000	10	T4	STE10000-10T4MI	0.25	< 0.100	25	150	- 85	20	35	3.00	5000
16 V _{DC} at + 85 °C; 11 V _{DC} at + 125 °C												
430	16	T1	Preliminary value, contact marketing									
1200	16	T2	Preliminary value, contact marketing									
3300	16	T3	STE3300-16T3MI	0.35	< 0.200	16	100	- 80	10	15	3.50	4000
6000	16	T4	STE6000-16T4MI	0.30	< 0.150	25	150	- 80	15	20	3.00	4500
25 V _{DC} at + 85 °C; 15 V _{DC} at + 125 °C												
270	25	T1	Preliminary value, contact marketing									
1000	25	T2	Preliminary value, contact marketing									
2200	25	T3	Preliminary value, contact marketing									
4000	25	T4	STE4000-25T4MI	0.35	< 0.150	25	125	- 80	15	20	5.00	4250
30 V _{DC} at + 85 °C; 20 V _{DC} at + 125 °C												
220	30	T1	Preliminary value, contact marketing									
820	30	T2	Preliminary value, contact marketing									
1800	30	T3	Preliminary value, contact marketing									
3300	30	T4	STE3300-30T4MI	0.35	< 0.200	25	125	- 80	20	25	4.00	2750
35 V _{DC} at + 85 °C; 22 V _{DC} at + 125 °C												
180	35	T1	Preliminary value, contact marketing									
680	35	T2	Preliminary value, contact marketing									
1500	35	T3	Preliminary value, contact marketing									
2800	35	T4	STE2800-35T4MI	0.35	< 0.200	25	125	- 80	20	30	4.50	4000



STANDARD RATINGS												
CAPACITANCE (μ F)	VOLTAGE	CASE CODE	PART NUMBER	MAX. ESR AT + 25 °C 120 Hz (Ω)	TYP. ESR AT + 25 °C 1 kHz (Ω)	MAX. DCL AT		MAX. CAPACITANCE CHANGE AT			MAX. IMP. AT - 55 °C 120 Hz (Ω)	AC RIPPLE 85 °C 40 kHz mA RMS
						+ 25 °C (μ A)	+ 85 °C/ + 125 °C (μ A)	- 55 °C (%)	+ 85 °C (%)	+ 125 °C (%)		
50 V _{DC} at + 85 °C; 30 V _{DC} at + 125 °C												
110	50	T1	STE110-50T1MI	1.60	< 1.000	2	7.5	- 40	10	15	40.00	1500
350	50	T2	<i>Preliminary value, contact marketing</i>									
900	50	T3	STE900-50T3MI	0.90	< 0.300	15	125	- 75	20	20	10.00	2500
1500	50	T3	STE1500-50T3MI	1.00	< 0.300	25	130	- 85	25	30	8.00	2400
1500	50	T4	STE1500-50T4MI	0.35	< 0.215	15	110	- 70	20	20	6.00	3500
2200	50	T4	STE2200-50T4MI	0.60	< 0.400	25	125	- 80	25	30	4.50	3000
60 V _{DC} at + 85 °C; 40 V _{DC} at + 125 °C												
68	60	T1	<i>Preliminary value, contact marketing</i>									
220	60	T2	<i>Preliminary value, contact marketing</i>									
560	60	T3	STE560-60T3MI	0.90	< 0.300	20	120	- 70	12	15	10.00	2500
1000	60	T4	STE1000-60T4MI	0.50	< 0.300	20	120	- 40	10	15	5.50	3500
75 V _{DC} at + 85 °C; 50 V _{DC} at + 125 °C												
56	75	T1	<i>Preliminary value, contact marketing</i>									
180	75	T2	STE180-75T2MI	1.50	< 0.500	5	25	- 35	15	20	30.00	2000
470	75	T3	STE470-75T3MI	0.60	< 0.325	25	100	- 45	10	25	10.00	3000
750	75	T4	STE750-75T4MI	0.50	< 0.400	20	120	- 35	10	15	6.50	3500
100 V _{DC} at + 85 °C; 65 V _{DC} at + 125 °C												
27	100	T1	<i>Preliminary value, contact marketing</i>									
86	100	T2	<i>Preliminary value, contact marketing</i>									
220	100	T3	STE220-100T3MI	1.40	< 0.200	5	25	- 55	10	15	18.00	2500
400	100	T4	STE400-100T4MI	0.70	< 0.400	10	120	- 40	6	12	15.00	3000
125 V _{DC} at + 85 °C; 85 V _{DC} at + 125 °C												
18	125	T1	<i>Preliminary value, contact marketing</i>									
56	125	T2	<i>Preliminary value, contact marketing</i>									
150	125	T3	<i>Preliminary value, contact marketing</i>									
240	125	T4	STE240-125T4MI	0.80	< 0.600	15	150	- 35	6	12	20.00	2500



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.