


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN 5811: DELETED SHIELDING NOTE, REVISED PACKAGING NOTE	11/1/11	D.FRISIELLO



WIRING MAP	
"P1"	"P2"
1	3
2	6
3	1
4	4
5	5
6	2
7	7
8	8
SHELL	SHELL

PART NUMBER	LENGTH		PART NUMBER	LENGTH	
	FEET	METERS		FEET	METERS
TRD855XCR-1	1	0.31	TRD855XCR-30	30	9.14
TRD855XCR-2	2	0.61	TRD855XCR-40	40	12.19
TRD855XCR-3	3	0.91	TRD855XCR-50	50	15.24
TRD855XCR-5	5	1.52	TRD855XCR-60	60	18.29
TRD855XCR-7	7	2.13	TRD855XCR-75	75	22.86
TRD855XCR-10	10	3.05	TRD855XCR-80	80	24.38
TRD855XCR-15	15	4.57	TRD855XCR-90	90	27.43
TRD855XCR-20	20	6.1	TRD855XCR-100	100	30.48
TRD855XCR-25	25	7.62			



NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
CONTACTS: PHOSPHOR BRONZE
CABLE JACKET: PVC, GRAY
SNAGLESS BOOT: LSZH THERMOPLASTIC, RED

FINISH:

CONTACTS: 50 μ INCHES GOLD IN CONTACT AREA
OVER 100 μ INCHES NICKEL PLATE OVERALL.
SHIELDING: NICKEL PLATED.

CABLE CHARACTERISTICS:

SHIELDED, ALUMINUM/POLYESTER.
FOUR TWISTED PAIRS MODULAR CABLE, 26 AWG (7X34)
STRANDED COPPER; UL LISTED COMMUNICATIONS CABLE,
TYPE CM.

MISCELLANEOUS:

PLUG CONFORMS TO TIA-1096.
OPERATING TEMPERATURE RANGE: -20°C TO +60°C.
CABLES TO BE TESTED FOR CONTINUITY.
CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE
WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 12/27/01 12/27/01 12/27/01	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY MODULAR		PRODUCT DESCRIPTION CBL RJ45 SHLD X-OVER CAT5E	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE	CAD FILE: TRD855XCR.SLDDRW	DWG. NO. TRD855XCR	REV. G