



	10	9	8	7	6	5	4	3	2	1						
	MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	"S" C2 ±.005/0.13	"W" MAX.	"C" MIN.	"L" MAX.	"ID" MIN.	STOCK THICKNESS	"H" ±.020/0.51				
F	190690027	AA-120-02	190690028	AA-120-02T	2	.094/(2.39)	.235/(6.00)	.157/(3.99)	.484/(12.29)	.062/(1.57)	.028/(0.71)	1.155/(29.34)				
	190690029	AA-120-04	190690030	AA-120-04T	4	.119/(3.02)										
	190690031	AA-120-06	190690032	AA-120-06T	6	.146/(3.71)										
	190690033	AA-121-06	190690034	AA-121-06T	6	.146/(3.71)	.322/(8.18)	.270/(6.86)	.641/(16.28)	.062/(1.57)	.028/(0.71)					
	190690035	AA-121-08	190690036	AA-121-08T	8	.173/(4.39)										
190690037	AA-121-10	190690038	AA-121-10T	10	.198/(5.03)											
190690039	AA-121-209	190690475	AA-121-209T	209	.209/(5.18)	.477/(12.11)							.386/(9.80)	.835/(21.21)	.062/(1.57)	.028/(0.71)
190690040	AA-122-10	190690041	AA-122-10T	10	.198/(5.03)											
190690042	AA-122-14	190690044	AA-122-14T	14	.265/(6.71)											
E	190690045	AA-122-56	190690046	AA-122-56T	56	.328/(8.33)	.544/(13.82)	.552/(14.02)	1.034/(26.26)	.055/(1.40)	.031/(0.79)	1.342/(34.09)				
	190690047	AA-126-10	-----	-----	10	.198/(5.03)										
	190690048	AA-126-14	190690128	AA-126-14T	14	.265/(6.71)										
	190690051	AA-126-56	-----	-----	56	.328/(8.33)	.264/(6.70)	.240/(6.10)	.582/(14.78)	.062/(1.57)	.028/(0.71)					
	190690049	AA-126-38	190690050	AA-126-38T	38	.390/(9.91)										
190690052	AA-132-04	190690053	AA-132-04T	4	.119/(3.02)											
D	190690054	AA-132-06	190690055	AA-132-06T	6	.146/(3.71)	.283/(7.20)	.240/(6.10)	.591/(15.00)	.062/(1.57)	.028/(0.71)		1.155/(29.34)			
	190690056	AA-132-08	190690057	AA-132-08T	8	.173/(4.39)										
	190690061	AA-133-10	190690062	AA-133-10T	10	.198/(5.03)										
	190690024	AA-1111-02	190690191	AA-1111-02T	2	.094/(2.39)	.197/(5.00)	.173/(4.40)	.490/(12.40)	.055/(1.40)	.031/(0.79)					
	190690025	AA-1111-04	190690026	AA-1111-04T	4	.119/(3.02)										



SALES DRAWING

- NOTE(S):**
1. MATERIAL: COPPER.
 2. PLATING: ELECTRO-TIN.
 3. ALL DIMENSIONS IN INCHES/(MM).

WIRE SIZE:
22-18 AWG
0.25-1.5 MM²

4. PARTS ARE ROHS COMPLIANT.

STDIZE STUD TOL EC NO: WNA2011-0225 2010/10/29 CHKD: JMACNEIL 2010/11/17 APPR: JMACNEIL 2010/11/17	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY BDEROSS	DATE 2000/6/13	TITLE RING TONGUE TERMINAL KRIMPTITE, 100 SERIES 22-18 AWG			
			4 PLACES	± ---	± ---	CHECKED BY JHACKNEY	DATE 2000/6/13				
			3 PLACES	± ---	± ---	APPROVED BY JMACNEIL	DATE 2010/11/17				
			2 PLACES	± ---	± ---	MOLEX MOLEX INCORPORATED					
			1 PLACE	± ---	± ---	MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
			ANGULAR ± ---°		SEE CHART		SD-19069-004	1 OF 1			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			C2		REV						