








Qty Per:		TRAY		CARTON	
		16		96	
PART NUMBER			STATEMENT		
SFP0-3040-L			INNER/OUTER LIGHT PIPES		
No.	DESCRIPTION	Q'ty	MATERIAL	PLATING	
01	SFP CAGE (Non-Logo)	1	COPPER ALLOY	NICKEL	
02	CONNECTOR	1	HIGH TEMP/COPPER ALLOY	GOLD	
03	LIGHT PIPE	1	POLYCARBONITE		


DETACHED LISTS	MM (INCH) TOLERANCES EXCEPT AS NOTED MM .0 ± 0.25 .00 ± 0.2 .000 ± 0.10 ANGLES ± 0.5		RoHS Compliant		Pulse A TECHNITROL COMPANY	
			TITLE		W/LIGHT PIPES	
			SFP 2 BY 1 CAGE+CONNECTOR_P			
	 THIRD ANGLE PROJECTION		DFTD Jack		DRAWING NO. CSFP0-3040-L	
			DATE 4/19/10		/PART NO. SFP0-3040-L	
			SCALE : 2:1		DO NOT SCALE DRAWING	
			SHEET 1		OF 4	






BEZEL CUT-OUT CENTER SPACING DETAIL
BEZEL THICKNESS:0.8-2.6




SECTION A-A


DETACHED LISTS	MM (INCH)		RoHS Compliant			
	TOLERANCES EXCEPT AS NOTED		TITLE			
	MM		SFP 2 BY 1 CAGE+CONNECTOR_P			
	.0 ± 0.25	±	W/LIGHT PIPES			
	.00 ± 0.2	±	DRAWING NO. CSFP0-3040-L			
	.000 ± 0.10	±	DATE 4/19/10			
	ANGLES ± 0.5		/PART NO. SFP0-3040-L		SIZE	REV
	THIRD ANGLE PROJECTION		SCALE : 2:1		SHEET 2	OF 4



CONNECTOR PIN-OUT
COMPONENT SIDE OF BOARD

DETACHED LISTS	MM (INCH) TOLERANCES EXCEPT AS NOTED MM .0 ± 0.25 .00 ± 0.2 .000 ± 0.10 ANGLES ± 0.5		RoHS Compliant		 Pulse A TECHNITROL COMPANY	
			TITLE		W/LIGHT PIPES	
			SFP 2 BY 1 CAGE+CONNECTOR_P			
	 THIRD ANGLE PROJECTION		DFTD Jack		SIZE	
			DATE 4/19/10		REV	
			DRAWING NO. CSFP0-3040-L		A3 3	
			/PART NO. SFP0-3040-L			
		SCALE : 2:1		SHEET 3 OF 4		
		DO NOT SCALE DRAWING				



DETACHED LISTS	MM (INCH) TOLERANCES EXCEPT AS NOTED MM .0 ± 0.25 .00 ± 0.2 .000 ± 0.10 ± ± ±		RoHS Compliant		 A TECHNITROL COMPANY	
	ANGLES ± 0.5		TITLE		W/LIGHT PIPES	
			SFP 2 BY 1 CAGE+CONNECTOR_P			
	 THIRD ANGLE PROJECTION		DFTD Jack		DRAWING NO. CSFP0-3040-L	
			DATE 4/19/10		/PART NO. SFP0-3040-L	
		SCALE : 2:1		DO NOT SCALE DRAWING		
				SHEET 4 OF 4		
				SIZE A3 REV 3		