



Miniblocks for EN 50045 (DIN 46277/2) rail Screw clamp ~ DIN 2


DR 4/6.... - 4 mm² blocks - 6 mm .236" spacing




DR 4/6




DR 4/6.1



BADRL



FEDR61



SCDR61



BJM62

Characteristics

		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.2 - 4	18-12 AWG	18-12 AWG
	Stranded	0.22 - 4		
Voltage	V	500 Gr.C	250	300/150
Current	A	30	20	10/25
Rated wire size	mm ² / AWG	4 mm ²	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended screwdriver	Nm / lb.in	4 mm / .16"		

Selection

Description	Type	Order P/N	Packaging Weight kg
DIN 2 standard block grey	DR 4/6	1SNA 110 251 R0500	50
DIN 2 standard block blue	DR 4/6.N	1SNA 120 251 R0700	50
DIN 2 block with partition grey	DR 4/6.1	1SNA 110 491 R1700	50
DIN 2 block with partition blue	DR 4/6.1.N	1SNA 120 491 R1100	50

Accessories

End stop V0			BADRL	6.5 mm	1SNA 199 420 R2100	50
End section	grey		FEDR61	1 mm	1SNA 117 600 R0300	25
	blue		FEDR61	1 mm	1SNA 127 600 R0500	10
Circuit separator	white		SCDR61	0.3 mm	1SNA 173 016 R1000	25
Assembled jumper bar (without IP20 protection)	2 poles		BJM62	32 A	1SNA 173 217 R2600	10
	3 poles		BJM62	32 A	1SNA 173 218 R0700	10
	5 poles		BJM62	32 A	1SNA 173 219 R0000	10
	10 poles		BJM62	32 A	1SNA 173 221 R2200	10
				BJM62	32 A	1SNA 173 226 R2700

DR 4/6.P - 4 mm² ground block - 6 mm .236" spacing

Characteristics


		IEC NFC DIN	UL	CSA
Wire size mm ² / AWG	Solid	0.2 - 4	18 - 12 AWG	18 - 12 AWG
	Stranded	0.22 - 4		
Rated wire size	mm ² / AWG	4 mm ²	12 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .37"		
Recommended screwdriver	Nm / lb.in	4 mm / .16"		
Recommended torque	Nm / lb.in	0.5 - 0.8 Nm / 4.4 - 7.1 lb.in		

Selection


Description	Type	Order P/N	Packaging Weight kg
Ground DIN 2 block green/yellow	DR 4/6.P	1SNA 160 496 R2600	50

Accessories


End stop V0		BADRL	6.5 mm	1SNA 199 420 P2100	50
End section	yellow	FEDR63	1 mm	1SNA 103 975 P2100	25
Circuit separator	white 	SCDR61	0.3 mm	1SNA 173 016 R1000	25




DR 4/6.P



BADRL



FEDR63



SCDR61