


# AUIRF1324WL

## WIDELEAD HEXFET® Power MOSFET



$V_{(BR)DSS}$	24V
$R_{DS(on)}$ typ.	1.16mΩ
max.	1.30mΩ
$I_D$ (Silicon Limited)	382A ①
$I_D$ (Package Limited)	240A



G	D	S
Gate	Drain	Source

## Description

Specifically design for automotive applications this Widelead TO-262 package part has the advantage of having over 50% lower lead resistance and delivering over 20% lower  $R_{DS(on)}$  when compared with a traditional TO-262 package housing the same silicon die. This greatly helps in reducing conduction losses, achieving higher current levels or enabling a system to run cooler and have improved efficiency. Additional features of this design are a 175°C junction operating temperature, fast switching speed and improved repetitive avalanche rating. These features combine to make this design an extremely efficient and reliable device for use in Automotive and other applications.

## Absolute Maximum Ratings

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only; and functional operation of the device at these or any other condition beyond those indicated in the specifications is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions. Ambient temperature ( $T_A$ ) is 25°C, unless otherwise specified.

	Parameter	Max.	Units
$I_D$ @ $T_C = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10\text{V}$ (Silicon Limited)	382①	A
$I_D$ @ $T_C = 100^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10\text{V}$ (Silicon Limited)	270①	
$I_D$ @ $T_C = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10\text{V}$ (Package Limited)	240	
$I_{DM}$	Pulsed Drain Current ②	1530	
$P_D$ @ $T_C = 25^\circ\text{C}$	Maximum Power Dissipation	300	W
	Linear Derating Factor	2.0	W/°C
$V_{GS}$	Gate-to-Source Voltage	± 20	V
$E_{AS}$ (Thermally limited)	Single Pulse Avalanche Energy ③	530	mJ
$I_{AAR}$	Avalanche Current ②	See Fig. 14, 15, 22a, 22b,	A
$E_{AAR}$	Repetitive Avalanche Energy ②		mJ
$dv/dt$	Peak Diode Recovery ④	1.3	V/ns
$T_J$	Operating Junction and	-55 to + 175	°C
$T_{STG}$	Storage Temperature Range		
	Soldering Temperature, for 10 seconds	300 (1.6mm from case)	

## Thermal Resistance

	Parameter	Typ.	Max.	Units
$R_{eJC}$	Junction-to-Case ⑤	—	0.50	°C/W

HEXFET® is a registered trademark of International Rectifier.

\*Qualification standards can be found at <http://www.irf.com/>


Static Electrical Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(\text{BR})\text{DSS}}$	Drain-to-Source Breakdown Voltage	24	—	—	V	$V_{\text{GS}} = 0\text{V}$ , $I_D = 250\mu\text{A}$
$\Delta V_{(\text{BR})\text{DSS}}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	0.022	—	V/ $^\circ\text{C}$	Reference to $25^\circ\text{C}$ , $I_D = 5\text{mA}$ ⑤
$R_{\text{DS}(\text{on})}$	Static Drain-to-Source On-Resistance	—	1.16	1.30	$\text{m}\Omega$	$V_{\text{GS}} = 10\text{V}$ , $I_D = 195\text{A}$ ⑤
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	2.0	—	4.0	V	$V_{\text{DS}} = V_{\text{GS}}$ , $I_D = 250\mu\text{A}$
$g_{\text{fs}}$	Forward Transconductance	210	—	—	S	$V_{\text{DS}} = 10\text{V}$ , $I_D = 195\text{A}$
$R_G$	Internal Gate Resistance	—	2.4	—	$\Omega$	
$I_{\text{DSS}}$	Drain-to-Source Leakage Current	—	—	20	$\mu\text{A}$	$V_{\text{DS}} = 24\text{V}$ , $V_{\text{GS}} = 0\text{V}$
		—	—	250	$\mu\text{A}$	$V_{\text{DS}} = 19\text{V}$ , $V_{\text{GS}} = 0\text{V}$ , $T_J = 125^\circ\text{C}$
$I_{\text{GSS}}$	Gate-to-Source Forward Leakage	—	—	200	nA	$V_{\text{GS}} = 20\text{V}$
	Gate-to-Source Reverse Leakage	—	—	-200	nA	$V_{\text{GS}} = -20\text{V}$

Dynamic Electrical Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$Q_g$	Total Gate Charge	—	120	180	nC	$I_D = 195\text{A}$
$Q_{\text{gs}}$	Gate-to-Source Charge	—	58	—		$V_{\text{DS}} = 12\text{V}$
$Q_{\text{gd}}$	Gate-to-Drain ("Miller") Charge	—	36	—		$V_{\text{GS}} = 10\text{V}$ ⑤
$Q_{\text{sync}}$	Total Gate Charge Sync. ( $Q_g - Q_{\text{gd}}$ )	—	84	—		$I_D = 195\text{A}$ , $V_{\text{DS}} = 0\text{V}$ , $V_{\text{GS}} = 10\text{V}$ ⑤
$t_{\text{d}(\text{on})}$	Turn-On Delay Time	—	18	—	ns	$V_{\text{DD}} = 16\text{V}$
$t_r$	Rise Time	—	200	—		$I_D = 195\text{A}$
$t_{\text{d}(\text{off})}$	Turn-Off Delay Time	—	75	—		$R_G = 2.7\Omega$
$t_f$	Fall Time	—	110	—		$V_{\text{GS}} = 10\text{V}$ ⑤
$C_{\text{iss}}$	Input Capacitance	—	7630	—	pF	$V_{\text{GS}} = 0\text{V}$
$C_{\text{oss}}$	Output Capacitance	—	3390	—		$V_{\text{DS}} = 19\text{V}$
$C_{\text{rss}}$	Reverse Transfer Capacitance	—	1960	—		$f = 1.0\text{MHz}$ , See Fig.5
$C_{\text{oss}}$ eff. (ER)	Effective Output Capacitance (Energy Related)	—	4660	—		$V_{\text{GS}} = 0\text{V}$ , $V_{\text{DS}} = 0\text{V}$ to $19\text{V}$ ⑦, See Fig.11
$C_{\text{oss}}$ eff. (TR)	Effective Output Capacitance (Time Related)	—	4685	—		$V_{\text{GS}} = 0\text{V}$ , $V_{\text{DS}} = 0\text{V}$ to $19\text{V}$ ⑥

## Diode Characteristics

	Parameter	Min.	Typ.	Max.	Units	Conditions
$I_S$	Continuous Source Current (Body Diode)	—	—	382①	A	MOSFET symbol showing the integral reverse p-n junction diode.
$I_{\text{SM}}$	Pulsed Source Current (Body Diode) ②	—	—	1530		
$V_{\text{SD}}$	Diode Forward Voltage	—	—	1.3	V	$T_J = 25^\circ\text{C}$ , $I_S = 195\text{A}$ , $V_{\text{GS}} = 0\text{V}$ ⑤
$t_{\text{rr}}$	Reverse Recovery Time	—	46	69	ns	$T_J = 25^\circ\text{C}$ $V_R = 20\text{V}$ ,
		—	45	68		$T_J = 125^\circ\text{C}$ $I_F = 195\text{A}$
$Q_{\text{rr}}$	Reverse Recovery Charge	—	395	593	nC	$T_J = 25^\circ\text{C}$ $\text{di}/\text{dt} = 100\text{A}/\mu\text{s}$ ⑤
		—	345	518		$T_J = 125^\circ\text{C}$
$I_{\text{RRM}}$	Reverse Recovery Current	—	1.9	—	A	$T_J = 25^\circ\text{C}$
$t_{\text{on}}$	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)				

## Notes:

① Calculated continuous current based on maximum allowable junction temperature. Package limitation current is 240A. Note that current limitations arising from heating of the device leads may occur with some lead mounting arrangements.(Refer to AN-1140 <http://www.irf.com/technical-info/appnotes/an-1140.pdf>)

② Repetitive rating; pulse width limited by max. junction temperature.

③ Limited by  $T_{\text{Jmax}}$ , starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.028\text{mH}$   $R_G = 50\Omega$ ,  $I_{\text{AS}} = 195\text{A}$ ,  $V_{\text{GS}} = 10\text{V}$ . Part not recommended for use above this value.

④  $I_{\text{SD}} \leq 195\text{A}$ ,  $\text{di}/\text{dt} \leq 600\text{A}/\mu\text{s}$ ,  $V_{\text{DD}} \leq V_{(\text{BR})\text{DSS}}$ ,  $T_J \leq 175^\circ\text{C}$ .

⑤ Pulse width  $\leq 400\mu\text{s}$ ; duty cycle  $\leq 2\%$ .

⑥  $C_{\text{oss}}$  eff. (TR) is a fixed capacitance that gives the same charging time as  $C_{\text{oss}}$  while  $V_{\text{DS}}$  is rising from 0 to 80%  $V_{\text{DSS}}$ .

⑦  $C_{\text{oss}}$  eff. (ER) is a fixed capacitance that gives the same energy as  $C_{\text{oss}}$  while  $V_{\text{DS}}$  is rising from 0 to 80%  $V_{\text{DSS}}$ .

⑧  $R_\theta$  is measured at  $T_J$  approximately  $90^\circ\text{C}$ .







**Qualification Information<sup>†</sup>**


		Automotive (per AEC-Q101) <sup>††</sup>	
<b>Qualification Level</b>		Comments: This part number(s) passed Automotive qualification. IR's Industrial and Consumer qualification level is granted by extension of the higher Automotive level.	
<b>Moisture Sensitivity Level</b>		TO-262 WideLead	MSL1
<b>ESD</b>	Machine Model	Class M4 (+/- 425V) <sup>†††</sup> AEC-Q101-002	
	Human Body Model	Class H2 (+/- 4000V) <sup>†††</sup> AEC-Q101-001	
	Charged Device Model	Class C5 (+/- 1125V) <sup>†††</sup> AEC-Q101-005	
<b>RoHS Compliant</b>		Yes	

<sup>†</sup> Qualification standards can be found at International Rectifier's web site: <http://www.irf.com/>


<sup>††</sup> Exceptions (if any) to AEC-Q101 requirements are noted in the qualification report.

<sup>†††</sup> Highest passing voltage.







**Fig 7.** Typical Source-Drain Diode Forward Voltage




**Fig 9.** Maximum Drain Current vs. Case Temperature




**Fig 11.** Typical  $C_{oss}$  Stored Energy




**Fig 8.** Maximum Safe Operating Area




**Fig 10.** Drain-to-Source Breakdown Voltage



**Fig 12.** Maximum Avalanche Energy vs. Drain Current



**Fig 13.** Maximum Effective Transient Thermal Impedance, Junction-to-Case



**Fig 14.** Typical Avalanche Current vs. Pulsewidth




Fig 15. Maximum Avalanche Energy vs. Temperature

Notes on Repetitive Avalanche Curves , Figures 14, 15:  
(For further info, see AN-1005 at [www.irf.com](http://www.irf.com))

1. Avalanche failures assumption:  
Purely a thermal phenomenon and failure occurs at a temperature far in excess of  $T_{jmax}$ . This is validated for every part type.
2. Safe operation in Avalanche is allowed as long as  $T_{jmax}$  is not exceeded.
3. Equation below based on circuit and waveforms shown in Figure 22a, 22b.
4.  $P_D(\text{ave})$  = Average power dissipation per single avalanche pulse.
5.  $BV$  = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6.  $I_{av}$  = Allowable avalanche current.
7.  $\Delta T$  = Allowable rise in junction temperature, not to exceed  $T_{jmax}$  (assumed as 25°C in Figure 14, 15).
8.  $t_{av}$  = Average time in avalanche.
9.  $D$  = Duty cycle in avalanche =  $t_{av} \cdot f$
10.  $Z_{thJC}(D, t_{av})$  = Transient thermal resistance, see Figures 13

$$P_D(\text{ave}) = 1/2 ( 1.3 \cdot BV \cdot I_{av} ) = \Delta T / Z_{thJC}$$

$$I_{av} = 2\Delta T / [1.3 \cdot BV \cdot Z_{th}]$$

$$E_{AS(AR)} = P_D(\text{ave}) \cdot t_{av}$$







Fig 16. Threshold Voltage vs. Temperature




**Fig 21.** Peak Diode Recovery  $dv/dt$  Test Circuit for N-Channel HEXFET® Power MOSFETs




**Fig 22a.** Unclamped Inductive Test Circuit




**Fig 22b.** Unclamped Inductive Waveforms




**Fig 23a.** Switching Time Test Circuit



**Fig 23b.** Switching Time Waveforms





**Fig 24a.** Gate Charge Test Circuit



**Fig 24b.** Gate Charge Waveform

## TO-262 WideLead Package Outline

Dimensions are shown in millimeters (inches)



S Y M B O L	DIMENSIONS				N O T E S	
	MILLIMETERS		INCHES			
	MIN.	MAX.	MIN.	MAX.		
A	4.06	4.83	.160	.190		
A1	2.03	3.02	.080	.119		
b	0.20	0.51	.008	.020		
b1	0.51	0.91	.020	.036	5	
b2	1.07	1.47	.042	.058		
b3	1.07	1.37	.042	.054	5	
b4	3.05	3.45	.120	.136		
b5	3.05	3.35	.120	.132	5	
b6	0.25	0.61	.010	.024		
b7	0.25	0.51	.010	.020	5	
b8	0.76	1.17	.030	.046		
b9	0.76	1.07	.030	.022	5	
c	0.38	0.74	.015	.029		
c1	0.38	0.58	.015	.023	5	
c2	1.14	1.65	.045	.065		
D	8.51	9.65	.335	.380	3	
D1	6.86	7.42	.270	.292	4	
E	9.65	10.67	.380	.420	3,4	
E1	6.22	8.48	.245	.334	4	
e	3.81	BSC	.150	BSC		
L	13.46	14.10	.530	.555		
L1	—	1.65	—	.065	4	
L2	8.64	9.40	.340	.370		


NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b3, b5, b7, b9 AND c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION: INCH.
7. OUTLINE CONFORM TO JEDEC TO-262 EXCEPT A1(max.), b(min.) AND D1(min.) WHERE DIMENSIONS DERIVED THE ACTUAL PACKAGE OUTLINE.


### LEAD ASSIGNMENTS

#### HEXFET

1. GATE
2. DRAIN
3. SOURCE



## TO-262 WideLead Part Marking Information



Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>  
www.irf.com

**Ordering Information**

Base part number	Package Type	Standard Pack		Complete Part Number
		Form	Quantity	
AUIRF1324WL	TO-262 WideLead	Tube	50	AUIRF1324WL

## IMPORTANT NOTICE

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

Only products certified as military grade by the Defense Logistics Agency (DLA) of the US Department of Defense, are designed and manufactured to meet DLA military specifications required by certain military, aerospace or other applications. Buyers acknowledge and agree that any use of IR products not certified by DLA as military-grade, in applications requiring military grade products, is solely at the Buyer's own risk and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

IR products are neither designed nor intended for use in automotive applications or environments unless the specific IR products are designated by IR as compliant with ISO/TS 16949 requirements and bear a part number including the designation "AU". Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, IR will not be responsible for any failure to meet such requirements.

For technical support, please contact IR's Technical Assistance Center  
<http://www.irf.com/technical-info/>

**WORLD HEADQUARTERS:**  
101 N. Sepulveda Blvd., El Segundo, California 90245  
Tel: (310) 252-7105