


PEG130, Aluminum Electrolytic, 105C, 900 uF, -10/+30%, 63 V, -40/+105C



Dimensions

D	20mm +/-0.5mm
L	29mm +/-1mm
L1	35mm MIN
LL Negative	40mm +/-2mm
LL Positive	40mm +/-2mm
F	1mm +/-0.03mm

Packaging Specifications

Weight:	13 g
Packaging:	Bulk, Bag
Packaging Quantity:	150

General Information

Supplier:	KEMET
Series:	PEG130
Dielectric:	Aluminum Electrolytic
Style:	Axial
Description:	Long Life Axial Aluminum Electrolytic
Features:	Long Life
RoHS:	Yes
Lead:	Wire Leads
Notes:	L1 is KEMET's recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article.

Specifications

Capacitance:	900 uF
Capacitance Tolerance:	-10/+30%
Voltage DC:	63 VDC
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	37000 Hrs
Resistance:	94 mOhms (100Hz 20C), 39.7 mOhms (100kHz 20C), 25.1 mOhms (5-100kHz 105C)
Current:	1.06 Amps (100Hz 105C), 7.2 Amps (5kHz 60C), 5.9 Amps (5kHz 80C), 3.3 Amps (5kHz 100C), 2.2 Amps (>=5kHz 105C)
Leakage Current:	174.1 uA (5min 20C)