





PRODUCT NUMBER
SEE SHEET 2

NOTES :

1. MINI PUSH-OUT FORCE TERMINAL IN BOTH DIRECTIONS 22N.
2. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 1 = 19.32$ mm



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
P	F07-0220	JCO	07.06.14	angles	.X ±0.3		SHR. HEADER
R	F08-0147	YOV	08.04.14	linear	.XX ±0.15	scale 5:1	STR DR TMT
S	B-19286	AMA	14.11.03		.XXX ±0.05		dwg no
T	B-21014	BVE	15.06.01	dr	G CORBOZ 01.01.12		sheet 1 of 2
				enrg	P NIZZI 01.01.12		size
M	F06-0228	LMU	06.07.11	chr	D LEGRAND 01.01.12		76385
N	F07-0147	LMU	07.03.01	appd	P N 01.01.12		A3
sheet	revision	T	G				type
index	sheet	1	2				CUSTOMER Drawing

RoHS COMPLIANT PRODUCT NUMBER
76385-YXXLF

PLATING CODE

RoHS COMPLIANT, SEE NOTE 5

- 3= 0.76µm GOLD/GXT ON CONTACT AREA.
2µm MIN MATTE TIN ON TAILS.
4= 2µm MIN MATTE TIN FULL PLATED

NUMBER OF POSITIONS PER ROW: 02 TO 18

1.27µm Ni MIN UNDERPLATING

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O COLOR: BLACK.
- 2 - TERMINAL MATERIAL: COPPER ALLOY.
- 3 - 2 UP TO 6 POSITIONS PER ROW, PRODUCT PACKED IN PLASTIC BAG.
7 UP TO 18 POSITIONS PER ROW, PRODUCT PACKED IN TUBE.
- 4 - ONLY DASH NUMBER -X02 AND -X03
ALWAYS TEN (10) PRODUCTS MOLDED ASSEMBLY
& DELIVERED TON STRIP ACCORDING PHANTOM LINES.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family DUBOX			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title SHR. HEADER STR DR TMT			
B	F06-0106	LMU	06.01.12	angles	linear					
C	F06-0228	LMU	06.07.11		linear	mm	scale 5:1			
D	F07-0147	LMU	07.03.01	dr	L.MULIN					
E	F07-0220	JCO	07.06.14	engr	J.COMPAGNON		dwg no 76385 sheet 2 of 6 size A3			
F	F08-0147	YOV	08.04.14	chr						
G	B-19286	AMA	14.11.03	appd	JM.C		type CUSTOMER Drawing			
sheet	revision									
index	sheet									