

Axial Lead and Cartridge Fuses


RoHS **Pb** **5 x 20 mm** Medium-Acting Fuse 232 Series




Agency Approvals

Agency Approvals		Ampere Range
	Certificate No.	Cartridge
	NBK010702-E10480 A	1A – 5A 125V 10,000A
	NBK290502-E10480 C	6.3A – 10A 125V 300A
	Leaded	
	NBK010702-E10480 B	1A – 5A 125V 10,000A
	NBK290502-E10480 E	6.3A – 10A 125V 300A
	Certificate No.	SU05001-2001
		1A – 10A (125V)
		1A – 10A


0232 000¹



0232 000 XW²



0232 000 XE²



All dimensions in mm

Notes:

* Ratings above 6.3A have 0.8 mm dia lead

1 For RoHS compliant parts add suffix 'XP'

2 For RoHS compliant parts add suffix 'P'

Average Time Current Curves

